

# Fluke Test Tools Price List

**FLUKE®**

Valid from: 13-07-2017

Model	Art. nr	Description	EUR
<b>Fluke Connect - 3000 Series</b>			
<b>Fluke Connect - 3000 Series</b>			
FLK-3000 FC	4401595	FC Wireless Digital Multimeter	285.00
FLK-3000 FC GM	4467750	FC Wireless General Maintenance System	815.00
FLK-3000 FC HVAC	4465607	FC Wireless HVAC System	591.00
FLK-3000 FC IND	4465599	FC Wireless Industrial System	1019.00
FLK-3000FC/TPAK	4699340	Fluke 3000FC with TPAK meter hanging kit	315.00
Fluke 3000FC/EDA2	4699333	Electronics DMM and deluxe accessory kit	366.00
Fluke 3000FC/1AC-II	4699302	Electrician's DMM voltage tester and accessory kit	407.00
FLK-A3000 FC	4401588	FC Wireless AC Current Clamp Module	183.00
FLK-A3000 FC KIT	4465618	FC Wireless Essential Kit with A3000	407.00
FLK-A3001 FC	4459439	FC Wireless iFlex AC Current Module	213.00
FLK-A3001 FC KIT	4465665	FC Wireless Essential Kit with i3000	438.00
FLK-A3002 FC	4459442	FC Wireless AC/DC Current Module	121.00
FLK-A3003 FC	4629295	FC Wireless 2000A DC Clamp meter	509.00
FLK-A3004 FC	4629301	FC Wireless 4-20mA DC Clamp meter	611.00
FLK-T3000 FC	4401563	FC Wireless K-Type Temperature Module	183.00
FLK-T3000 FC KIT	4465652	FC Wireless Essential Kit with T3000	407.00
FLK-V3000 FC	4401556	FC Wireless AC Voltage Module	193.00
FLK-V3000 FC KIT	4465641	FC Wireless Essential Kit with V3000	407.00
FLK-V3001 FC	4459421	FC Wireless DC Voltage Module	193.00
FLK-V3001 FC KIT	4467777	FC Wireless essential Kit with V3001	407.00
FLK-V3003 FC KIT	4467789	FC Wireless Kit w. DMM, AC+DC Voltage Modules	662.00
<b>Fluke Connect - Accessories</b>			
FLK-FC_SD Card	4463628	Fluke Connect Wireless SD Card	95.00
FLK-PC3000 FC	4401602	FC Wireless PC Adapter	101.00
FLUKE-IR3000FC	4460436	Connector, Infrared, FC	132.00
<b>Digital Multimeters</b>			
<b>110 Series Multimeters</b>			
Fluke 113	3088053	True RMS Multimeter	125.00
Fluke 114	2583552	True RMS Multimeter	165.00
Fluke 115	2583583	True RMS Multimeter	195.00
Fluke 116	2583601	True RMS Multimeter	229.00
116/62MAX+ Kit	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	415.00
Fluke 116/323 Kit	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	325.00
Fluke 117	2583647	True RMS Multimeter	239.00
Fluke 117/323 Kit	4296034	Fluke Electrician's Multimeter Combo Kit	310.00
C50	762823	Soft Meter Case	40.00
<b>170 Series Multimeters</b>			
Fluke 175	1592901	True RMS Multimeter	229.00
Fluke 177	1592874	True RMS Multimeter	279.00
Fluke 179	1592842	True RMS Multimeter	329.00
C90	466029	Soft Meter Case	40.00
Fluke 179/EDA2/EUR	3947719	Electronics Combo Kit	389.00
<b>200 Series Multimeters</b>			
Fluke 233	3469334	Remote Display Multimeter	325.00
Fluke 279FC	4755570	Wireless TRMS Thermal Multimeter	999.00
Fluke 279FC/iFlex	4684050	Wireless TRMS Thermal Multimeter w/iFlex	1199.00
Fluke 287/EUR	3947781	True RMS Electronic Logging Multimeter with TrendCapture	591.00
Fluke 287/FVF/EUR	3947796	FlukeView Forms Combo Kit	693.00
Fluke 289/EUR	3947801	True RMS Industrial Logging Multimeter with TrendCapture	642.00
Fluke 289/FVF/EUR	3947812	Industrial Logging Multimeter and Software Combo Kit	744.00
C280	3182785	Soft Meter Case	66.00
Fluke 287/FVF/IR3000	4699316	Fluke 287 FlukeView® Forms Combo Kit	764.00
Fluke 289/FVF/IR3000	4699325	Fluke 289 FlukeView® Forms Combo Kit	815.00

Model	Art. nr	Description	EUR
<b>20 Series Multimeters</b>			
Fluke 27II/EUR	3947770	Industrial Multimeter (IP67)	489.00
Fluke 28II/EUR	3947820	True RMS Industrial Multimeter (IP67)	489.00
Fluke 28 II Ex	4017165	Intrinsically safe true-rms digital multimeter	1274.00
C25	681114	Soft Meter Case	56.00
<b>70 Series Multimeters</b>			
Fluke 77-4/EUR	3947835	Multimeter	407.00
C90	466029	Soft Meter Case	40.00
<b>80 Series Multimeters</b>			
Fluke 83-V/EUR	3947847	Multimeter	458.00
Fluke 87-V/EUR	3947858	True RMS Multimeter	499.00
Fluke 87-V/E2K/EUR	3947864	Industrial Electricians Combo Kit	599.00
C25	681114	Soft Meter Case	56.00
<b>Bench Multimeters</b>			
Fluke 8808A 220V	2802372	5.5 Digit Multimeter	700.00
Fluke 8808A 240V	2802385	5.5 Digit Multimeter	700.00
Fluke 8808A/SU 240V	2802467	5.5 Digit Multimeter (software & cable)	895.00
Fluke 8808A/SU 220V	2802459	5.5 Digit Multimeter (software & cable)	895.00
Fluke 8808A/TL 240V	3111097	5.5 Digit Multimeter, 2X4W Test Lead Kit	780.00
Fluke 8808A/TL 220V	3111085	5.5 Digit Multimeter, 2X4W Test Lead Kit	780.00
Fluke 8845A 240V	2577365	6.5 Digit Precision Multimeter	1045.00
Fluke 8845A 220V	2577352	6.5 Digit Precision Multimeter	1045.00
Fluke 8845A/SU 240V	2675332	6.5 Digit Precision Multimeter (incl. software + cable)	1235.00
Fluke 8845A/SU 220V	2675315	6.5 Digit Precision Multimeter (incl. software + cable)	1235.00
Fluke 8846A 240V	2577390	6.5 Digit Precision Multimeter	1375.00
Fluke 8846A	2577383	6.5 Digit Precision Multimeter	1375.00
Fluke 8846A/SU 240V	2675380	6.5 Digit Precision Multimeter (incl. software + cable)	1565.00
Fluke 8846A/SU 220V	2675367	6.5 Digit Precision Multimeter (incl. software + cable)	1565.00
884X-CASE	2675552	Hard Case (8845A/8846A)	430.00
884X-RTD	2675468	100 OHM RTD Temperature Probe	565.00
884X-SHORT	2653346	4-wire short	31.00
884X-USB	2675479	USB to RS232 Cable Adapter	160.00
884X-1G	2675534	USB Memory 1 GB	133.00
8845A-EFPT	2742690	Extended Fine Point Tip Adapter Set	20.00
8845A-TPIT	2742683	Test Probe IC Tip Set	15.00
FVF-UG	1576741	FlukeView Forms Upgrade	131.00
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	281.00
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	161.00
RS43	946470	Serial Interface Cable	85.00
TL2X4W-PTII	2826215	2x4 Wire Ohms Test Lead 2 mm Probe Tip	77.00
TL2x4W-TWZ	2723629	2X4-Wire Ohms Tweezers Test Leads	100.00
Y8021	708289	IEEE-488 Shielded Interface Cable, 1 m	437.00
Y8022	708297	IEEE-488 Shielded Interface Cable, 2 m	510.00
Y8846S	2675518	Rack mount kit single (8845A/8846A)	122.00
Y8846D	2771721	Rack mount kit dual (8845A/8846A)	165.00
<b>Automotive Meters</b>			
Fluke 88V/A	2117440	Automotive Meter Combo Kit	713.00
<b>Clamp Meters</b>			
Fluke 323	4152628	True RMS Clamp Meter	129.00
Fluke 324	4152637	True RMS Clamp Meter	169.00
Fluke 325	4152643	True RMS Clamp Meter	229.00
Fluke 353	2840252	AC/DC True RMS Clamp Meter	611.00
Fluke 355	2840265	AC/DC True RMS Clamp Meter	764.00
Fluke 365	3790607	Detachable TRMS Clamp Meter	254.00
Fluke 368 FC	4709907	Wireless leakage current clamp, 40mm jaw	689.00
Fluke 369 FC	4709934	Wireless leakage current clamp, 61mm jaw	689.00
Fluke 373	3790564	600A TRMS Clamp Meter	254.00
Fluke 374FC	4696001	600A AC/DC TRMS Wireless Clamp Meter	356.00
Fluke 375FC	4695932	600A AC/DC TRMS Wireless Clamp Meter	427.00
Fluke 376FC	4695861	1000A AC/DC TRMS Wireless Clamp Meter with iFlex	489.00
Fluke 381	3610452	Remote Display TRMS Clamp Meter	570.00
Fluke 902 FC	4695814	TRMS Wireless HVAC ClampMeter	285.00
62MAX+/323/1AC Kit	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	254.00
Fluke 116/323 Kit	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	325.00
Fluke i2500-18	3676405	iFlex Probe	132.00
Fluke i2500-10	3676410	iFlex Probe	132.00
H3	1608458	Holster (330 Series)	44.00

Model	Art. nr	Description	EUR
<b>Electrical Testers</b>			
Fluke 1000FLT	4472387	Fluorescent Light Tester	234.00
Fluke T5-600	659612	Electrical Tester	159.00
T5-600/62MAX+/1AC kit	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	259.00
Fluke T5-1000	659570	Electrical Tester	179.00
Fluke T5-H5-1AC II Kit	2098657	Electrical Tester Kit with Holster and 1AC	199.00
Fluke T90	4016945	Voltage/continuity tester	59.00
Fluke T110	4016950	Voltage/continuity tester with switchable load	84.00
Fluke T130	4016961	Voltage/continuity tester with LCD, switchable load	124.00
Fluke T150	4016977	Voltage/continuity tester with LCD, Ohms, switchable load	144.00
Fluke 2042	2435038	Cable Locator (Transmitter + Receiver)	744.00
Fluke 2042T	2435045	Cable Locator Transmitter	387.00
Fluke 9040EUR	4014969	Phase Rotation Indicator	199.00
Fluke 9062	2435077	Motor and Phase Rotation Indicator	183.00
LVD1	4571403	Volt Light	35.00
LVD2	2740300	Volt Light	39.00
H5	649365	Electrical Tester Holster (Fluke T5)	33.00
FTL660	2280204	Fused Test Lead Set	60.00
Fluke 1AC II	2432932	Volt Alert	30.00
Fluke 1AC II 5PK	2433056	Volt Alert 5-pack	109.00
FLK2AC/200-1000VCL	3611985	ACV Detector 200-1000V	28.00
FLK2AC/90-1000V	3807928	ACV Detector 90-1000V, Flat-tip	28.00
FLK2AC/90-1000V5PK	3807937	Volt Alert 90-1000V, 5-pack, Flat-tip	99.00
PRV240	4566209	Proving unit	152.00
Fluke 117/PRV240	4636971	Proving unit, Fluke 117 DMM Kit	305.00
<b>Laser Levels</b>			
Fluke-3PR	4811457	3 Point laser level, red	199.00
Fluke-3PG	4811469	3 Point laser level, green	219.00
Fluke-18OLR	4811504	2 Line laser level, red	259.00
Fluke-18OLG	4811491	2 Line laser level, green	319.00
Fluke-18OLG System	4811519	Green line laser with LDG detector	379.00
Fluke-18OLR System	4811528	Red line laser with LDR detector	329.00
Fluke-LDR	4811543	Laser line detector red	89.00
Fluke-LDG	4819919	Laser line detector green	99.00
<b>Distance Meters</b>			
Fluke 414D	4106830	Laser Distance Meter	129.00
Fluke 419D	4106853	Laser Distance Meter	249.00
Fluke 424D	4106866	Laser Distance Meter	359.00
414D/62MAX+ Kit	4296052	Fluke Laser distance meter and IR thermometer kit	219.00
<b>Battery Analyzers</b>			
Fluke BT510	4489970	Battery Analyzer	2651.00
Fluke BT520	4489981	Battery Analyzer	3314.00
Fluke BT521	4489996	Advanced Battery Analyzer	3722.00
<b>Battery Analyzer Accessories</b>			
BTL10	4542264	Standard Battery Analyzer Probes	330.00
BTL20	4542273	Intelligent Test Probe Set, w/Extenders (no temp sensor)	499.00
BTL21	4542286	Intelligent Test Probe Set, w/Extenders & Temp Sensor	621.00
BTL-A	4542258	Voltage/Current Probe Adapter	40.00
BC500	4542299	AC Power Charger	121.00
BP500	4542300	Lithium-ion battery, 7.4V 3000 mAh	101.00
BT500	4561297	Probe tip, 10x replacement Probe tips, 2x long probe tip covers, 2x short probe tip covers	121.00
i410	617727	AC/DC Current Clamp (400 A)	254.00
<b>Insulation Testers</b>			
Fluke 1503	2427883	Insulation Tester	415.00
Fluke 1507	2427890	Insulation Tester	515.00
Fluke 1550C	3665021	Insulation Resistance Tester (5kV)	3569.00
Fluke 1550C/Kit	3665127	Insulation Resistance Tester Kit (5kV)	3875.00
Fluke 1555	3665056	Insulation Resistance Tester (10kV)	4283.00
Fluke 1555/Kit	3665111	Insulation Resistance Tester Kit (10kV)	4589.00
Fluke 1577	2157280	Insulation Multimeter	611.00
Fluke 1587T	2517605	Insulation Multimeter (Telecom)	713.00
Fluke 1587 FC	4691215	2-IN-1 Insulation Multimeter	764.00
Fluke 1587/MDT FC	4692716	2-IN-1 Advanced Motor & Drive Troubleshooting Kit with 9040, I400	1019.00
1587KIT/62MAX+ FC	4692778	2-IN-1 Advanced Electrical Troubleshooting Insulation Multi Kit with 62MAX+ I400	917.00
Fluke 1587/I400 FC	4692725	2-IN-1 Insulation Multimeter with Clamp i400	815.00
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	149.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	244.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	48.00

Model	Art. nr	Description	EUR
<b>Installation Testers</b>			
Fluke 1662 SCH	4546944	Installation Tester w/mem Schuko	999.00
Fluke 1663 SCH	4546980	Installation Tester w/RCD type B Schuko	1299.00
Fluke 1664FC SCH	4547054	FC Installation Tester w/insulation pre-test Schuko	1649.00
Fluke 166X-MTC-SCH	4601081	Fluke 166X-Main test cord, Schuko (EU)	59.00
Fluke DMS COMP	4718790	DMS Complete, Installation, PAT Software	549.00
Fluke DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	729.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	244.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	48.00
ES165X	2104706	Earth Spike Test Kit	152.00
MTC77	2457421	Mains Test Cord (CEE 7 7 Schuko)	60.00
TP165X	2107742	Remote Control Probe (1650 Series)	81.00
TL165X	2107756	Standard Test Lead Set (1650 Series)	111.00
ZERO ADAPTER	3261925	Zero adapter (165xB)	40.00
<b>Portable Appliance Testers</b>			
Fluke 6200-2 NL	4325052	Portable Appliance Tester NL	999.00
Fluke 6500-2 NL	4325065	Portable Appliance Tester NL	1699.00
Fluke 6500-2 NL Basic Kit	4377180	Portable Appliance Tester, Basic Kit, NL	1850.00
APP1000	1992611	Barcode Appliance Number Labels 0-1000	132.00
APP2000	1992627	Barcode Appliance Number Labels 1001-2000	132.00
AUTO200B	2141239	Auto Code Label	46.00
BDST3	2796907	Snap Tag (cable tie)	38.00
BDST4	2796918	Snap Tag (clip on)	38.00
CD-Card	4045991	Compact Flash Memory Card	40.00
Fluke DMS COMP	4718790	DMS Complete, Installation, PAT Software	549.00
Fluke DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	729.00
EXTL100	2389684	Extension Lead Test Adaptor	17.00
PASS560R	2141217	Appliance Pass Labels	81.00
SP6000 Printer	4325128	Printer for Portable Appliance Testers	611.00
SPSCAN6000	4325143	Scanner for Portable Appliance Testers	387.00
<b>Earth Ground Testers</b>			
Fluke 1621	2840276	Earth Ground Tester	611.00
Fluke 1630-2 FC	4829532	Earth Ground Loop and Leakage Clamp	1399.00
Fluke 1630-2	4829515	Earth Ground Loop and Leakage Clamp (non FC)	1399.00
Fluke 1623-2	4325155	Basic Geo Earth Ground Tester	1376.00
Fluke 1625-2	4325162	Advanced Geo Earth Ground Tester	2294.00
Fluke 1623-2 Kit	4325170	Basic Geo Earth Ground Tester, Kit	2345.00
Fluke 1625-2 Kit	4325181	Advanced Geo Earth Ground Tester, Kit	3365.00
Earth Stake	4325492	Geo Earth Ground Tester, Earth stake	63.00
Cable Reel 25M BL	4343731	25M Blue, Ground/Earth Cable Reel, 25M Wire	63.00
Cable Reel 25M GR	4343746	25M Green, Ground/Earth Cable Reel, 25M Wire	63.00
Cable Reel 50M RD	4343754	50M Red, Ground/Earth Cable Reel, 50M Wire	70.00
C1620	4359042	Carrying Case	197.00
ES-162P3-2	4359377	Earth Ground Stake Set for 3 Pole Measurement	244.00
ES-162P4-2	4359389	Earth Ground Stake Set for 4 Pole Measurement	356.00
<b>Indoor Air Quality Tools</b>			
Fluke 922	2679822	Airflow Meter	611.00
Fluke 922/Kit	2679831	Airflow Meter Kit	713.00
Fluke 971	2418208	Temperature Humidity Meter	244.00
Fluke 975	2519364	AirMeter	2039.00
Fluke 975V	2666111	AirMeter with Velocity	2345.00
Fluke CO-220	664711	Carbon Monoxide Meter	509.00
Fluke RLD2	3387163	Leak Detector Flashlight	50.00
CO-205	664714	Aspirator Kit	172.00
975VP	2631538	Air Velocity Probe	458.00
PT12	2740212	Pitot Tube, 12	112.00
Fluke 985	4131397	Airborne Particle Counter	4283.00
<b>Digital Thermometers</b>			
Fluke 51 II	1281142	Thermometer	325.00
Fluke 52 II	1281139	Thermometer	407.00
Fluke 53 II B	3821062	Single Input Thermometer, 60Hz	458.00
Fluke 53 II B	3821096	Single Input Thermometer, 50Hz	468.00
Fluke 54 II B	3821070	Dual Input Thermometer, 60Hz	560.00
Fluke 54 II B	3821081	Dual Input Thermometer, 50Hz	560.00
Fluke 61	1643896	Infrared Thermometer	193.00
Fluke 62 MAX	4130474	Infrared thermometer	91.00
Fluke 62 MAX+	4130488	Infrared Thermometer	101.00
T5-600/62MAX+/1AC kit	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	259.00
414D/62MAX+ Kit	4296052	Fluke Laser distance meter and IR thermometer kit	219.00
62MAX+/323/1AC Kit	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	254.00



Model	Art. nr	Description	EUR
116/62MAX+ Kit	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	415.00
Fluke 63	2148281	Infrared Thermometer	264.00
Fluke 64 MAX	4856105	Multifunction IR Thermometer 20:1 D:S	129.00
Fluke 561	2558118	Multipurpose Thermometer	193.00
Fluke 566	2837799	Multipurpose Thermometer	407.00
Fluke 568	2837806	Multipurpose Thermometer	509.00
Fluke 568Ex	4321662	Intrinsically safe Infrared Thermometer	1274.00
Fluke 572-2	4328074	Infrared Thermometer	611.00
Fluke FP	2644169	FoodPro Thermometer	121.00
Fluke FP Plus	2477950	FoodPro Plus Thermometer	203.00
C50	762823	Soft Meter Case	40.00
H6	2152040	Infrared Thermometer Holster (Fluke 63/65/68/561)	31.00
80PR-60	2148313	RTD Temperature Probe (Fluke 66/68)	72.00

Visual Thermometers			
Fluke VT04	4366444	Visual IR Thermometer	556.00
Fluke VT04A	4485211	Visual IR thermometer	505.00
Fluke charger VT04	4375752	Charger & adapter set VT04	41.00
Fluke Battery, VT04	4375741	Li-ion battery VT04	41.00

### Thermal Imagers

Thermal Imagers - Performance Series			
Fluke TIS10 9HZ	4697036	Thermal imager, fixed focus	1195.00
Fluke TIS20 9Hz	4697049	Thermal imager, fixed focus	1495.00
Fluke TIS40 9Hz	4697051	Thermal imager, fixed focus	1995.00
Fluke TIS45 30Hz	4697072	Thermal imager, manual focus	2395.00
Fluke TIS45 9Hz	4697060	Thermal imager, manual focus	2395.00
Fluke TIS50 9Hz	4697085	Thermal imager, fixed focus	2695.00
Fluke TIS55 30Hz	4697106	Thermal imager, manual focus	2995.00
Fluke TIS55 9Hz	4697097	Thermal imager, manual focus	2995.00
Fluke TIS60 9Hz	4697114	Thermal imager, fixed focus	3395.00
Fluke TIS65 30Hz	4697138	Thermal imager, manual focus	3695.00
Fluke TIS65 9Hz	4697123	Thermal imager, manual focus	3695.00
Fluke TIS75 30HZ	4754443	Thermal Imager, Manual Focus	3995.00
Fluke TIS75 9HZ	4754437	Thermal Imager, Manual Focus	3995.00

Thermal Imagers - Professional Series			
Fluke Ti200 9Hz	4335298	Thermal Imager, 9Hz	5095.00
Fluke Ti200 60Hz	4335306	Thermal Imager, 60Hz	5095.00
Fluke Ti300 9Hz	4335314	Thermal Imager, 9Hz	5495.00
Fluke Ti300 60Hz	4335323	Thermal Imager, 60Hz	5495.00
Fluke Ti400 9Hz	4335338	Thermal Imager, 9Hz	6795.00
Fluke Ti400 60Hz	4335345	Thermal Imager, 60Hz	6795.00
Fluke TI450 9HZ	4764729	Thermal Imager, Manual Focus	7495.00
Fluke TI450 60Hz	4764707	Thermal Imager, Manual Focus	7495.00
Fluke Ti450 SF6 60Hz	4907176	SF6 Gas leak detection, Thermal Imager	15399.00

Thermal Imagers - Expert Series			
Fluke TI480 60Hz	4842086	Thermal Imager; 640x480; 60 HZ, SR	12995.00
Fluke TI480 9Hz	4842105	Thermal Imager; 640x480; 9 HZ, SR	12995.00
Fluke TiX500 9HZ	4736664	Thermal Imager; 320x240; 9 HZ	8495.00
Fluke TiX500 60HZ	4736635	Thermal Imager; 320x240; 60 HZ	8495.00
Fluke TiX520 9 Hz	4596742	Thermal Imager; 320 x 240; 9 Hz	10995.00
Fluke TiX520 9Hz/NFC	4597027	Thermal Imager; 320 x 240; Non-FC; 9 Hz	10995.00
Fluke TiX520 60 Hz	4596717	Thermal Imager; 320 x 240; 60 Hz	10995.00
Fluke TiX560 9Hz	4597094	Thermal Imager; 320 x 240; IS	12995.00
Fluke TiX560 9Hz/NFC	4597100	Thermal Imager; 320 x 240; Non-FC; 9 Hz	12995.00
Fluke TiX560 60 Hz	4597066	Thermal Imager; 320 x 240; IS	12995.00
Fluke TiX580 60Hz	4842073	Thermal Imager; 640x480; 60 HZ, SR	15995.00
Fluke TiX580 9Hz	4841945	Thermal Imager; 640x480; 9 HZ, SR	15995.00
Fluke TiX5xx-Neck	4574715	Adjustable neck strap	30.00
Fluke TiX5xx-SBP4	4597142	Additional Smart Battery	130.00
Fluke TiX5xx Hand	4574703	Adjustable hand strap	15.00
Fluke TiX5xx-HDMI	4615511	HDMI video cable	20.00
Fluke TiX5x-Lens Cap	4550697	Lens cap	15.00
Fluke TI-Bluetooth	4603258	Bluetooth headset	75.00
Fluke TI-SBC3B	4354922	Charging base (Ti200/Ti300/Ti400)	170.00
Fluke lens/4xTELE2	4607058	4x Telephoto IR lens for TiX560-TiX520-Ti400-Ti300-Ti200	5799.00
Fluke lens/25MAC2	4607064	25Micron Macro IR lens for TiX560-TiX520	4195.00

Model	Art. nr	Description	EUR
<b>Thermal Imagers Accessories (general)</b>			
Ti-Visor2	3996500	Sun Visor	78.00
Ti-Visor3	4335377	Thermal imager visor	75.00
Ti-Tripod	3511872	Tripod Mounting Base	108.00
Ti-Tripod2	3996517	Mounting Base	99.00
Ti-Tripod3	4335389	Tripod mounting base accessory	95.00
FLK-LENS/TELE1	3441176	Telephoto Infrared Lens (Ti32/TiR32)	1346.00
FLK-LENS/WIDE1	3441183	Wide-angle Infrared Lens (Ti32/TiR32)	1346.00
FLK-LENS/TELE2	4335350	Telephoto Infrared Lens (Ti200/Ti300/Ti400)	1295.00
FLK-LENS/WIDE2	4335361	Wide-angle Infrared Lens (Ti200/Ti300/Ti400)	1295.00
Fluke lens/4xTELE2	4607058	4x Telephoto IR lens for TiX560-TiX520-Ti400-Ti300-Ti200	5799.00
Fluke lens/25MAC2	4607064	25Micron Macro IR lens for TiX560-TiX520	4195.00
Ti-Car Charger	3039779	Ti Car Charger (TiR/TiR1/Ti10/Ti20/Ti25)	120.00
Ti20-RBP	2577796	Rechargeable Battery Pack (Ti20)	173.00
FLK-TI-SBP3	3440365	Extra battery (Ti32/TiR32)	139.00
Fluke TI-SBC3B	4354922	Charging base (Ti200/Ti300/Ti400)	170.00
<b>Thermal Imagers IR-Windows</b>			
FLK-050-CLKT	3460346	50mm C-Range IR Windows, Kwik twist	172.00
FLK-075-CLKT	3460387	75 mm C-Range IR Window, Kwik Twist	218.00
FLK-100-CLKT	3460439	100mm C-Range IR Window, Kwik Twist	300.00
Fluke CV200	4326955	50mm IR Window, hand turn door latch	223.00
Fluke CV300	4326962	75mm IR Windows, hand turn door latch	295.00
Fluke CV301	4338164	75mm IR Windows, security turn door latch	305.00
Fluke CV400	4326996	100 mm IR Windows, hand turn door latch	407.00
Fluke CV401	4338173	100 mm IR Windows, security turn door latch	417.00
<b>ScopeMeters</b>			
<b>Industrial ScopeMeter</b>			
Fluke 123B/EU	4755659	Industrial ScopeMeter 20MHZ, EU	1529.00
Fluke 123B/INT	4755710	Industrial ScopeMeter 20MHZ, INT	1529.00
Fluke 124B/EU	4755731	Industrial ScopeMeter 40MHZ, EU	1835.00
Fluke 124B/INT	4755793	Industrial ScopeMeter 40MHZ, INT	1835.00
Fluke 125B/EU	4755818	Industrial ScopeMeter 40MHZ, EU	2192.00
Fluke 125B/INT	4755876	Industrial ScopeMeter 40MHZ, INT	2192.00
Fluke 123B/EU/S	4755890	Industrial ScopeMeter + SCC 20MHZ, EU	1937.00
Fluke 123B/INT/S	4755953	Industrial ScopeMeter + SCC 20MHZ, INT	1937.00
Fluke 124B/EU/S	4755975	Industrial ScopeMeter + SCC 40MHZ, EU	2243.00
Fluke 124B/INT/S	4756031	Industrial ScopeMeter + SCC 40MHZ, INT	2243.00
Fluke 125B/EU/S	4756054	Industrial ScopeMeter + SCC 40MHZ, EU	2600.00
Fluke 125B/INT/S	4756112	Industrial ScopeMeter + SCC 40MHZ, INT	2600.00
<b>190 Series ScopeMeters</b>			
Fluke 190-204/EU	3894409	ScopeMeter 4 Channel 200 MHZ Color	4487.00
Fluke 190-204/UN	3894411	ScopeMeter 4 Channel 200 MHZ Color	4491.00
Fluke 190-204/EU/S	3894475	ScopeMeter 4 Channel 200 MHZ Color SCC	4892.00
Fluke 190-204/UN/S	3894482	ScopeMeter 4 Channel 200 MHZ Color UNI SCC	4892.00
Fluke 190-104/EU	3894540	ScopeMeter 4 Channel 100 MHZ Color EU	3926.00
Fluke 190-104/UN	3894557	ScopeMeter 4 Channel 100 MHZ Color UNI	3929.00
Fluke 190-104/EU/S	3894617	ScopeMeter 4 Channel 100 MHZ Color EU SCC	4327.00
Fluke 190-104/UN/S	3894621	ScopeMeter 4 Channel 100 MHZ Color UNI SCC	4327.00
Fluke 190-062/EU	4025159	ScopeMeter 2 Channel 60 MHZ Color	2835.00
Fluke 190-062/UN	4025171	ScopeMeter 2 Channel 60MHZ Color	2803.00
Fluke 190-062/EU/S	4025230	ScopeMeter 2 Channel Color SCC	3235.00
Fluke 190-062/UN/S	4025248	ScopeMeter 2 Channel 60MHZ Color SCC	3235.00
Fluke 190-102/EU	4025318	ScopeMeter 2 Channel 100MHZ Color	3487.00
Fluke 190-102/UN	4025329	ScopeMeter 2 Channel 100MHZ Color SCC	3478.00
Fluke 190-102/EU/S	4025383	ScopeMeter 2 Channel 100MHZ Color SCC	3888.00
Fluke 190-102/UN/S	4025390	ScopeMeter 2 Channel 100MHZ Color SCC	3888.00
Fluke 190-202/EU	4025460	ScopeMeter 2 Channel 200MHZ Color	3936.00
Fluke 190-202/UN	4025472	ScopeMeter 2 Channel 200MHZ Color	3929.00
Fluke 190-202/EU/S	4025554	ScopeMeter 2 Channel 200MHZ Color SCC	4337.00
Fluke 190-202/UN/S	4025568	ScopeMeter 2 Channel 200MHZ Color SCC	4337.00
Fluke 190-502/EU	4025623	ScopeMeter 2 Channel 500 MHZ Color	4849.00
Fluke 190-502/UN	4025638	ScopeMeter 2 Channel 500 MHZColor UNI	4849.00
Fluke 190-502/EU/S	4025692	ScopeMeter 2 Channel 500 MHZ Color Europe SCC	5250.00
Fluke-190-502/UN/S	4025704	ScopeMeter 2 Channel 500 MHZ Color UNI SCC	5250.00
Fluke 190-504/EU	4419875	ScopeMeter 4 Channel 500MHz Color	5026.00
Fluke 190-504/UN	4419929	ScopeMeter 4 Channel 500MHz Color UNI	5026.00
Fluke 190-504/EU/S	4419941	ScopeMeter 4 Channel 500MHz Color Europe SCC	5426.00
Fluke 190-504/UN/S	4419990	ScopeMeter 4 Channel 500MHz Color UNI SCC	5426.00

Model	Art. nr	Description	EUR
<b>ScopeMeter Accessories</b>			
AC120	646163	Heavy Duty Alligator Clips	44.00
AS400	3894880	Probe Extension Set, for VPS400 Probes	111.00
BB120	646171	Banana to BNC Adapter Plug	51.00
BB120-II	4744369	Set of 2 banana to BNC adapter	46.00
BC190/808	1282244	Battery Charger/Line Voltage Adapter UNIVERSAL (190 Series)	188.00
BC190/820	4328652	Universal Power Supply 100-240V	184.00
BC430/820	4328676	Energy efficient Universal Power Supply 100-240V +/-10%	137.00
BHT190	3379374	Set of Break-out Adapters	361.00
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	101.00
BP190	677390	NiMH Battery Pack (190 Series)	203.00
BP290	4025762	Battery Pack Single Cap 190-series II	240.00
BP291	3894688	Battery Pack, Fluke 190 Series	336.00
C120	646189	Hard Case (43B/120 Series)	110.00
C120B	4744391	Soft carrying case for 120B series	138.00
C125	646858	Soft Meter Case	51.00
C190	677401	Hard Case (190 Series)	258.00
C195	677408	Soft Case	239.00
C290	3894803	Hard-Shell Carrying Case	215.00
CS20MA	677393	Current Shunt 4-20 mA	99.00
EBC290	3894906	External Battery Charger	106.00
HC120	646668	Hook Clips	58.00
HC120-II	4744357	Set of 2 hook clips	51.00
HC200	2086410	Hook Clips	41.00
HH290	3894844	Hanging Hook, ScopeMeter Series 190 II	75.00
MA190	1567481	Medical Accessory Kit (190 Series)	455.00
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	164.00
PM8907/801	613999	Battery Charger/Line Voltage Adapter EUR (120 Series)	123.00
PM8907/807	624764	POWER ADAPTOR/BATTERY CHARGER	123.00
PM8907/808	614039	Battery Charger/Line Voltage Adapter UNIVERSAL (120 Series)	146.00
PM9080	1641983	Serial Interface Adapter/Cable (RS232)	272.00
PM9081	916093	Dual Banana Plug to Female BNC Adapter	52.00
PM9082	916163	Dual Banana Jack to Male BNC Adapter	52.00
PM9091	935598	Coaxial BNC Cables (1.5 m)	123.00
PM9092	935601	Coaxial BNC Cables (0.5 m)	106.00
PM9093	935593	Male BNC to Female BNC Adapter	71.00
PM9096/201	651742	Secondary Pick-up	339.00
RS120-III	4023947	Probe Accessory Replacement Set	111.00
RS400	3894867	Probe Replacement Set, for VPS400 Probes	88.00
RS500	4025886	Probe accessory replacement set for VPS500 probes	158.00
SCC120B	4744423	Software soft carry case accessory kit 120B series	510.00
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	468.00
SCC128	2100199	Automotive Accessory Kit (120 Series)	727.00
SCC198	2100208	Automotive Accessory Kit (190 Series)	915.00
SCC190	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	655.00
SCC290	3894826	Software and Carrying Case for 190 Series II	400.00
SP120B	4744414	Screen protector for 120B series	46.00
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	253.00
STL120-III	4023901	Shielded Test Lead	194.00
STL120-IV	4744340	Shielded test lead set 600V CAT IV	163.00
SW90W	3894923	FlukeView Software	362.00
TAS90	614187	Automotive Accessory Set (120/190 Series)	71.00
TRM50	4025864	50 Ohm feed-through terminator BNC	190.00
UA120	4744384	USB Connector adapter	46.00
VPS41	4744378	Voltage probe set 40 MHz 600V CAT IV	158.00
VPS101	3086317	1:1 Voltage Probe Set, black, 30 MHz, 1.2m	221.00
VPS210-G	3086247	10:1 Voltage Probe Set, grey, 200 MHz, 1.2m	221.00
VPS210-R	3086235	10:1 Voltage Probe Set, 1 red, 200 MHz, 1.2m	221.00
VPS212-G	3086286	10:1 Voltage Probe Set, grey, 200 MHz, 2.5m	221.00
VPS212-R	3086273	10:1 Voltage Probe Set, red, 200 MHz, 2.5m	221.00
VPS220-G	3086300	100:1 Voltage Probe Set, grey, 200 MHz, 1.2m	221.00
VPS220-R	3086299	100:1 Voltage Probe Set, red, 200 MHz, 1.2m	221.00
VPS40-III	4023920	Voltage Probe	128.00
VPS410-II-B	4276937	Industrial Voltage Probe Set 500 MHz 10:1 Blue	211.00
VPS410-II-G	4276943	Industrial Voltage Probe Set 500 MHz 10:1 Grey	211.00
VPS410-II-R	4276928	Industrial Voltage Probe Set 500 MHz 10:1 Red	211.00
VPS410-II-V	4276955	Industrial Voltage Probe Set 500 MHz 10:1 Green	211.00
VPS420-R	3894783	High Working Voltage Probe 100:1 Red & Black	245.00
VPS420-B	4411541	High Working Voltage Ruggedized Probe; Blue/Black	245.00
VPS420-G	4411565	High Working Voltage Ruggedized Probe; Grey/Black	245.00
VPS420-V	4411583	High Working Voltage Ruggedized Probe; Green/Black	245.00
VPS510-R	4025781	Voltage Probe set 500 MHz 10:1 Red	211.00
VPS510-B	4025796	Voltage probe set 500 MHz 10:1 Blue	211.00
VPS510-G	4025801	Voltage probe set 500 MHz 10:1 Grey	211.00
VPS510-V	4025812	Voltage probe set 500 MHz 10:1 Green	211.00

Model	Art. nr	Description	EUR
<b>Power Quality Tools</b>			
Fluke 345	2584181	Power Quality Clamp Meter	1580.00
Fluke 430-II/MA	4779032	Motor Analyzer Upgrade Kit	1995.00
Fluke 434-II/BASIC	4116650	Power Quality and energy analyzer (w/o clamps)	3990.00
Fluke 434-II	4116638	Power Quality and energy analyzer	4610.00
Fluke 434-II/INTL	4778918	Power Quality and energy analyzer/International	4610.00
Fluke 435-II/BASIC	4116689	Advanced Power Quality and energy analyzer (w/o clamps)	5332.00
Fluke 435-II	4116661	Power Quality& Energy Analyzer	5919.00
Fluke 435-II/INTL	4778929	Power Quality and energy analyzer/International	5919.00
Fluke 437-II/BASIC	4116719	400 Hz Power Quality and Energy Analyzer (w/o clamps)	7557.00
Fluke 437-II	4116692	Power Quality& Energy Analyzer	8189.00
Fluke 437-II/INTL	4778934	Power Quality and energy analyzer/International	8189.00
Fluke 438-II/Basic	4778990	Power Quality & Motor Analyzer, without clamps and FC WiFi SD Card	6670.00
Fluke 438-II	4778976	Power Quality & Motor Analyzer	7290.00
Fluke 438-II/INTL	4779015	Power Quality& Motor Analyzer, without FC WiFi SD Card	7290.00
Fluke 1732/EUS	4706548	Energy Logger, EU/US version	2499.00
Fluke 1732/INTL	4706553	Energy Logger, international version	2499.00
Fluke 1732/B	4706566	Energy Logger, basic version	2199.00
Fluke 1734/EUS	4706594	Energy Logger, EU/US advanced version	2799.00
Fluke 1734/INTL	4706608	Energy Logger, international advanced version	2799.00
Fluke 1734/B	4706582	Energy Logger, advanced version no flexis	2499.00
Fluke 1734/WINTL	4710227	Energy Logger, wireless international	2799.00
Fluke 1736/EUS	4534519	3-Phase Power Logger, EU/US version	3999.00
Fluke 1736/B	4563561	3-Phase Poser Logger, basic version	3799.00
Fluke 1736/INTL	4563550	3-Phase Power Logger, International version	3999.00
Fluke 1738/EUS	4563577	3-Phase Power Logger, EU/US Advanced version no flexis	4499.00
Fluke 1738/B	4588378	3-Phase Power Logger, advanced version no flexis	3999.00
Fluke 1738/INTL	4588384	3-Phase Power Logger, international advanced version	4499.00
Fluke 1743 Basic	3034012	Power Quality Logger, Memobox	3690.00
Fluke 1743	2583446	Power Quality Logger, Memobox	4436.00
Fluke 1744 Basic	3034020	Power Quality Logger, Memobox	4918.00
Fluke 1744	2583422	Power Quality Logger, Memobox	5844.00
Fluke 1744/1PH	3345730	Power Quality Logger, Memobox	2584.00
Fluke 1745	2583468	Power Quality Logger, Memobox	7138.00
Fluke 1750-TF/ET	4871393	Three Phase Power Recorder incl. flexible current probes, incl. PC tablet	11340.00
Fluke 1750/ET	4871400	Three Phase Power Recorder incl. current probes, incl. PC tablet	10400.00
Fluke 1750/B/ET	4871417	Three Phase Power Recorder excl. current probes, incl. PC tablet	9608.00
Fluke 1750-TF/NT	4756236	Three Phase Power Recorder incl. flexible current probes, excl. PC tablet	10932.00
Fluke 1750/NT	4756208	Three Phase Power Recorder incl. current probes, excl. PC tablet	9992.00
Fluke 1750/B/NT	4756213	Three Phase Power Recorder, excl. current probes, excl. PC tablet	9200.00
Fluke 1760 Basic	2630732	Power Quality Recorder (three-phase), Topas	11617.00
Fluke 1760	2630744	Power Quality Recorder (three-phase), Topas	13460.00
Fluke 1760TR Basic	2637629	Power Quality Recorder (three-phase), Topas	15919.00
Fluke 1760TR	2637634	Power Quality Recorder (three-phase), Topas	17760.00
Fluke VR1710	3030923	Single-Phase Voltage Quality Recorder	857.00
C1740	4116762	Softcase for 174X and 43X-II PQ analyzer	202.00
C437-II	4116743	Hard case 430 Series II with rollers	482.00
EPE-Training-E/EMEA	4792349	Fluke EPE Training Set - English	199.00
Fluke-435-II/EPE-E	4816735	Fluke-435-II, PQ and Energy Analyzer plus EPE training - English	6020.00
<b>Power Quality Tools Accessories</b>			
1743/1744 Poleset	3024485	Pole Mounting Kit (Fluke 1743/1744)	40.00
3140R	2650136	Clip-on Current Transformer 2A-400A (Fluke 1750)	370.00
3210-PR-TF-II	4531769	1000A Fluke 1750 Thin flexi 61cm	611.00
3310-PR-TF-II	4531778	5000A Fluke 1750 Thin flexi 61cm	815.00
3PHVL-1730	4344712	Cable Assembly, Voltage Test Lead 3-Phase+N (1730)	83.00
3312-PR-TF-II	4531784	5000A Fluke 1750 Thin flexi 122cm	1019.00
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	101.00
BE345	2839604	Battery Eliminator (Fluke 345)	151.00
BC430/820	4328676	Energy efficient Universal Power Supply 100-240V +/- 10%	137.00
BP1730	4389436	Li Ion Battery Pack 3.7V 2500mAh (1730)	39.00
C120	646189	Hard Case (43B/120 Series)	110.00
C17xx	4637381	Soft Case	114.00
CS1750	2673962	Soft Case (Fluke 1750/1760)	250.00
1730 Hanger	4358028	Hanger kit (1730)	55.00
1730 Cable	4395217	Cable,AUX input cable (1730)	29.00
1750/Case	2650124	Hard Case (Fluke 1750)	539.00
FLUKE-1736/UPGRADE	4563589	UPGRADE KIT FOR 1736 TO 1738	799.00
1750/Seat-L	2673937	Fluke Power Analyze - Additional SEAT LICENSE	1067.00
1750/Site-L	2673928	Fluke Power Analyze - Additional SITE LICENCE	5338.00
FS17X5-TF-II	4531791	3000A 4-PH Fluke 1735 & 1745 Thin flexi set	1571.00
FS17XX IP65-TF-II	4531804	3000A IP65 4-PH Fluke 1743/4 Thin flexi set	1745.00
FS17XX-1PH-TF-II	4531819	FS3000A/6000A 4-PH 36-Inch Thin flexi set	393.00
FLUKE-173X ADPT	4717827	AUX input adapter, 173X	133.00



Model	Art. nr	Description	EUR
Fluke 17xx TL 0.1M	4715389	Test lead set for Fluke 173x; 0.1m	40.00
Fluke 17xx TL 1.5M	4715392	Test lead set for Fluke 173x; 1.5m	30.00
FS3000/6000A-TF-4-II	4531828	FS3000A/6000A 4-PH 36-Inch thin flexi set	1567.00
GPS430-II	4693803	GPS Synchronization module (430-II series)	1529.00
GPS-Time Sync	2539223	GPS Time Synchronization Module (Fluke 1760)	419.00
i17XX-flex1500	4637328	Fluke-17xx iFlexi 1500A 12 IN	162.00
i17XX-flex3000	4637343	Fluke-17xx iFlexi 3000A 24 IN	172.00
i17XX-flex6000	4637362	Fluke-17xx iFlexi 6000A 36 IN	183.00
i17XX-flex1500/3pk	4637337	Fluke-17xx iFlexi 1500A 12 IN, 3 pack	468.00
i17XX-flex3000/3pk	4637355	Fluke-17xx iFlexi 3000A 24 IN, 3 pack	499.00
i17XX-flex6000/3pk	4637370	Fluke-17xx iFlexi 6000A 36 IN, 3 pack	529.00
i17XX-Flex1500/4PK	4637411	Fluke-17xx iFlexi 1500A 12 IN, 4 Pack	611.00
i17XX-Flex3000/4PK	4637427	Fluke-17xx iFlexi 3000A 24 IN, 4 Pack	652.00
i17XX-Flex6000/4PK	4637430	Fluke-17xx iFlexi 6000A 36 IN, 4 Pack	693.00
i1A/10A Clamp PQ1	3345753	1-phase Mini Current Clamp Set	459.00
i1A/10A Clamp PQ3	3024413	3-phase Mini Current Clamp Set	527.00
i1A/10A Clamp PQ4	3024424	4-phase Mini Current Clamp Set	709.00
i5A/50A Clamp PQ1	3345766	1-Phase 5A/50A Mini Current Clamp set for PQ	459.00
i5A/50A Clamp PQ3	3024436	3-phase Mini Current Clamp Set	527.00
i5A/50A Clamp PQ4	3024449	4-phase Mini Current Clamp Set	709.00
i20/200A Clamp PQ3	3024451	3-phase Mini Current Clamp Set	527.00
i20/200A Clamp PQ4	3024460	4-phase Mini Current Clamp Set	709.00
i40S-EL	4637396	Fluke-17xx i40s-EL Clamp-on Current Transformer	203.00
i40S-EL/3pk	4637409	Fluke-17xxx i40s-EL Clamp-on Current Transformer, 3 pack	580.00
i400	2277225	AC Current Clamp (400 A)	152.00
i400s	2277202	AC Current Clamp (400A)	274.00
i430-Flexi-TF-II	4531725	6000A Fluke 430 Thin Flexi 61cm	396.00
i430-Flexi-TF-II-4PK	4531733	6000A Fluke 430 Thin Flexi 61cm 4 Pack	1206.00
i5s	2508467	AC Current Clamp (5 A)	509.00
i5S-PR	3949761	1750, 5A Current Clamp	315.00
i5sPQ3	2457508	AC Current Clamp (5 A), 3-pack	1223.00
IEEE519/REPORT	4589748	SOFTWARE LICENSE FOR IEEE519 REPORTING	509.00
MP1-Magnet Probe 1	4589220	Magnet probes for 4 mm banana, set of 4	91.00
MBX USB-RS232	2539565	EP0328Z, USB to Serial RS232 Adapter	45.00
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	164.00
PM9080	1641983	Serial Interface Adapter/Cable (RS232)	272.00
TLS430	2157713	Test Leads and Alligator Clips (4 black, 1 green) - 430 Series	122.00
TPS Clamp 10A/1A	2540445	Clip-on Current Transformer 10A/1A (Fluke 1760)	378.00
TPS Clamp 50A/5A	2540461	Clip-on Current Transformer 50A/5A (Fluke 1760)	378.00
TPS Clamp 200A/20A	2540450	Clip-on Current Transformer 200A/20A (Fluke 1760)	378.00
TPS Flex 18-TF-II	4531837	100/500A Fluke 1760 Thin Flexi 45cm (18in)	447.00
TPS Flex 24-TF-II	4531843	200/1000A Fluke 1760 Thin Flexi 61cm (24in)	447.00
TPS Flex 36-TF-II	4531855	3000/6000A Fluke 1760 Thin Flexi 91cm (36in)	878.00
TPS/MBX Dolph red	2540744	EP0326Z, Dolphin Clip, Red	21.00
TPS Nullmodem Cable	2540511	A550500510, RS232 Cross Link Cable, 3M	29.00
TPS Shunt 1A	2540548	A680501054, Shunt 1 A AC/DC	290.00
TPS Shunt 20MA	2540553	Shunt 20mA AC/DC (Fluke 1760)	304.00
TPS Voltprobe 10V	2540636	Voltage Probe 10V (Fluke 1760)	300.00
TPS Voltprobe 100V	2540624	Voltage Probe 100V (Fluke 1760)	300.00
TPS Voltprobe 400V	2540660	Voltage Probe 400V (Fluke 1760)	300.00
TPS Voltprobe 600V	2540697	Voltage Probe 600V (Fluke 1760)	300.00
TPS Voltprobe 1KV	2540649	Voltage Probe 1000V (Fluke 1760)	463.00
VL1735/45	3276205	Banana 4-Phase Voltage Lead set for Fluke-1735/45	239.00
Fluke WiFi/BLE	4591273	Dongle to USB adapter, WiFi/BLE	179.00

### Vibration Testers

Fluke 805	4094385	Vibration Meter	1709.00
Fluke 805 FC	4489229	Vibration Meter with Fluke Connect	1709.00
Fluke 805/ES	4636786	External Vibration Sensor	1019.00
Fluke 810	3542635	Vibration Tester	9383.00
Fluke 820-2	4550041	LED Stroboscope	872.00
Fluke 830	4454396	Laser Alignment Tool	7098.00
Fluke 830/Magnet	4528249	Magnetic Bracket	835.00
Fluke 830/Shims	4551330	Laser Alignment Tool, Shims	835.00
810S	3530828	Sensor	1417.00
810QDC	3530837	Quick Disconnect Cable	148.00
810SMM	3530862	Sensor Magnet Mount	208.00
810SMP	3530855	Sensor Mounting Pads (10-pack)	28.00
SBP-810	3530843	Smart Battery Pack	264.00
Fluke-810PA	3986002	AC Power Adapter with International Plug Set	84.00

### Process Calibrators

Model	Art. nr	Description	EUR
<b>700 Series Process Calibrators</b>			
Fluke 154 INTL	4805625	HART Calibration Assistant	3695.00
Fluke 705	665091	Loop Calibrator	744.00
Fluke 707	1617262	Loop Calibrator	856.00
Fluke 707Ex	2032187	Intrinsically Safe Loop Calibrator	1203.00
Fluke 709	4234350	Precision Loop Calibrator	849.00
Fluke 709H	4234361	Precision HART Loop Calibrator	1366.00
Fluke 712B	4387857	RTD Temperature Calibrator	1029.00
Fluke 714B	4387869	TC Temperature Calibrator	1029.00
Fluke 715	620101	Volt/mA Calibrator	1213.00
Fluke 717 1G	2547166	Pressure Calibrator (68.9 mbar)	1377.00
Fluke 717-15G	4058808	Pressure Calibrator (1 bar)	1377.00
Fluke 717 100G	1630430	Pressure Calibrator (7 bar)	1377.00
Fluke 717 30G	662897	Pressure Calibrator (2 bar)	1428.00
Fluke 717 300G	2547175	Pressure Calibrator (20 bar)	1377.00
Fluke 717 500G	2547182	Pressure Calibrator (34.7 bar)	1377.00
Fluke 717 1000G	2547194	Pressure Calibrator (69 bar)	1377.00
Fluke 717 1500G	2547203	Pressure Calibrator (103.4 bar)	1525.00
Fluke 717 3000G	2547215	Pressure Calibrator (207 bar)	1525.00
Fluke 717 5000G	2547232	Pressure Calibrator (345 bar)	1525.00
Fluke 717-10000G	4058813	Pressure Calibrator (690 bar)	1525.00
Fluke 718 30G	665075	Pressure Calibrator (2 bar)	2592.00
Fluke 718 1G	2547148	Pressure Calibrator (68.9 mbar)	2700.00
Fluke 718 100G	665080	Pressure Calibrator (7 bar)	2590.00
Fluke 718 300G	2547153	Pressure Calibrator (20 bar)	2692.00
Fluke 718Ex 30G	2096310	Intrinsically Safe Pressure Calibrator (2 bar)	3334.00
Fluke 718Ex 100G	2096322	Intrinsically Safe Pressure Calibrator (7 bar)	3334.00
Fluke 718Ex 300G	3023328	Intrinsically Safe Pressure Calibrator (20 bar)	3334.00
Fluke 719 30G	3315332	Electric Pressure Calibrator (2 bar)	3437.00
Fluke 719 100G	3315344	Electric Pressure Calibrator (7 bar)	3437.00
Fluke-719PRO 30G	4353218	Electric Pressure Calibrator, 2 bar	2827.00
Fluke-719PRO 150G	4353229	Electric Pressure Calibrator, 10 bar	2827.00
Fluke-719PRO 300G	4353234	Electric Pressure Calibrator, 20 bar	2835.00
Fluke 720URTD	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	159.00
Fluke-721-1601	4353241	Dual Sensor Pressure Calibrator, 1.1 bar, 6.9 bar	1974.00
Fluke-721-1603	4353283	Dual Sensor Pressure Calibrator, 1.1 bar, 20 bar	1974.00
Fluke-721-1605	4353327	Dual Sensor Pressure Calibrator, 1.1 bar, 34 bar	1974.00
Fluke-721-1610	4353366	Dual Sensor Pressure Calibrator, 1.1 bar, 69 bar	1974.00
Fluke-721-1615	4353401	Dual Sensor Pressure Calibrator, 1.1 bar, 103 bar	1974.00
Fluke-721-1630	4353447	Dual Sensor Pressure Calibrator, 1.1 bar, 200 bar	1974.00
Fluke-721-1650	4353486	Dual Sensor Pressure Calibrator, 1.1 bar, 345 bar	1974.00
Fluke-721-3601	4353252	Dual Sensor Pressure Calibrator, 2.48 bar, 6.9 bar	1974.00
Fluke-721-3603	4353290	Dual Sensor Pressure Calibrator, 2.48 bar, 20 bar	1974.00
Fluke-721-3605	4353330	Dual Sensor Pressure Calibrator, 2.48 bar, 34 bar	1974.00
Fluke-721-3610	4353375	Dual Sensor Pressure Calibrator, 2.48 bar, 69 bar	1974.00
Fluke-721-3615	4353412	Dual Sensor Pressure Calibrator, 2.48 bar, 103 bar	1974.00
Fluke-721-3630	4353458	Dual Sensor Pressure Calibrator, 2.48 bar, 200 bar	1974.00
Fluke-721-3650	4353499	Dual Sensor Pressure Calibrator, 2.48 bar, 345 bar	1974.00
Fluke 721EX-1601	4353265	Dual Sensor Pressure Calibrator, 16, 100 PSIG	2580.00
Fluke 721EX-1603	4353309	Dual Sensor Pressure Calibrator, 16, 300 PSIG	2580.00
Fluke 721EX-1605	4353348	Dual Sensor Pressure Calibrator, 16, 500 PSIG	2580.00
Fluke 721EX-1610	4353382	Dual Sensor Pressure Calibrator, 16, 1000 PSIG	2580.00
Fluke 721EX-1615	4353420	Dual Sensor Pressure Calibrator, 16, 1500 PSIG	2580.00
Fluke 721EX-1630	4353464	Dual Sensor Pressure Calibrator, 16, 3000 PSIG	2580.00
Fluke 721EX-1650	4353506	Dual Sensor Pressure Calibrator, 16, 5000 PSIG	2580.00
Fluke 721EX-3601	4353276	Dual Sensor Pressure Calibrator, 36, 100 PSIG	2580.00
Fluke 721EX-3603	4353311	Dual Sensor Pressure Calibrator, 36, 300 PSIG	2580.00
Fluke 721EX-3605	4353353	Dual Sensor Pressure Calibrator, 36, 500 PSIG	2580.00
Fluke 721EX-3610	4353394	Dual Sensor Pressure Calibrator, 36, 1000 PSIG	2580.00
Fluke 721EX-3615	4353435	Dual Sensor Pressure Calibrator, 36, 1500 PSIG	2580.00
Fluke 721EX-3630	4353473	Dual Sensor Pressure Calibrator, 36, 3000 PSIG	2580.00
Fluke 721EX-3650	4353514	Dual Sensor Pressure Calibrator, 36, 5000 PSIG	2580.00
Fluke 724	1553041	Temperature Calibrator	2263.00
Fluke 725	664133	Multifunction Process Calibrator	3161.00
Fluke 725Ex	2098179	Intrinsically Safe Multifunction Process Calibrator	3865.00
Fluke 726	2452080	Precision Multifunction Process Calibrator	3620.00
Fluke 729 30G FC	4856907	Automatic Pressure Calibrator , w/FC (2 Bar)	8195.00
Fluke 729 150G FC	4856894	Automatic Pressure Calibrator, w/FC (10 Bar)	8195.00
Fluke 729 300G FC	4856882	Automatic Pressure Calibrator, w/FC (20 Bar)	8195.00
Fluke 729 30G	4856990	Automatic Pressure Calibrator (2 Bar)	7995.00
Fluke 729 150G	4856983	Automatic Pressure Calibrator (10 Bar)	7995.00
Fluke 729 300G	4856976	Automatic Pressure Calibrator (20 Bar)	7995.00
Fluke 753 EU	4411027	Documenting Process Calibrator	5221.00
Fluke 754 EU	4400387	Documenting Process Calibrator	6578.00
Fluke 771	2646347	Milliamp Process Clamp Meter	540.00

Model	Art. nr	Description	EUR
Fluke 772	3362352	Milliamp Process Clamp Meter	712.00
Fluke 773	3362365	Milliamp Process Clamp Meter	1009.00
Fluke 787B	4777186	Process Meter	989.00
Fluke 789/E	3977194	Process Meter	1111.00
Fluke 789/IR3000FC	4604605	Process Meter and FC connector	1098.00
<b>Pressure Modules</b>			
Fluke-700G01	4353523	Pressure Gauge, -10" to 10" WC (27 mbar)	721.00
Fluke-700G02	4353538	Pressure Gauge, -30" to 30" WC (69 mbar)	721.00
700G04	4096972	Pressure Gauge, +/- 1 bar	721.00
700G05	4097514	Pressure Gauge, 2 bar	721.00
700G06	4097538	Pressure Gauge, 6.9 bar	721.00
700G07	4097561	Pressure Gauge, 34 bar	721.00
700G08	4097592	Pressure Gauge, 69 bar	721.00
700G27	4097545	Pressure Gauge, 20 bar	721.00
700G29	4097605	Pressure Gauge, 200 bar	743.00
700G30	4097610	Pressure Gauge, 345 bar	743.00
700G31	4097622	Pressure Gauge, 690 bar	743.00
Fluke-700GA4	4353545	Pressure Gauge, 1 bar absolute	721.00
Fluke-700GA5	4353550	Pressure Gauge, 2 bar absolute	721.00
Fluke-700GA6	4353561	Pressure Gauge, 6.9 bar absolute	721.00
Fluke-700GA27	4353577	Pressure Gauge, 20 bar absolute	721.00
700HTPK	4124358	Hydraulic Test Pump Kit, 0 to 690 bar	1121.00
Fluke 700HTPK2	4623314	Premium hydraulic test pump kit	1468.00
Fluke 700MTH	4623345	Premium metric pressure test hose	540.00
Fluke 700M2OTH	4623338	Premium M20 pressure test hose	540.00
700P01Ex	2097578	Differential Pressure Module (25 mbar)	2668.00
700P05Ex	2097591	Gage Pressure Module (2 bar)	2668.00
700P06Ex	2097600	Gage Pressure Module (7 bar)	2668.00
700P09Ex	2097617	Gage Pressure Module (100 bar)	2668.00
700P24Ex	2097584	Differential Pressure Module Wet (1001 mbar)	2668.00
700P27Ex	2097639	Gage Pressure Module (20 bar)	2291.00
700P29Ex	2097642	Gage Pressure Module (200 bar)	4571.00
700PA4Ex	2097621	Absolute Pressure Module (1000 mbar)	3066.00
700PCK	100062	Pressure Module Calibration Kit	1347.00
Fluke 700PTPK	4124364	Pneumatic Test Pump Kit, 0 to 41 bar	519.00
Fluke 700PTPK2	4623306	Premium pneumatic test pump kit	1356.00
700G/TRACK	4123225	Data Logging Cable & Software	399.00
Fluke-700RG05	4353589	Pressure Gauge, Reference, +2 bar	743.00
Fluke-700RG06	4353592	Pressure Gauge, Reference, 6.9 bar	743.00
Fluke-700RG07	4353605	Pressure Gauge, Reference, 34 bar	743.00
Fluke-700RG08	4353610	Pressure Gauge, Reference, 69 bar	743.00
Fluke-700G10	4353654	Pressure Gauge, 140 bar	721.00
Fluke-700RG29	4353622	Pressure Gauge, Reference, 200 bar	824.00
Fluke-700RG30	4353631	Pressure Gauge, Reference, 345 bar	824.00
Fluke-700RG31	4353646	Pressure Gauge, Reference, 690 bar	824.00
Fluke 700TTH5K	4623323	Premium pressure transmitter test hose	540.00
Fluke 700TTH10K	4636393	Premium pressure transmitter test hose kit, 10K	642.00
750P00	4352270	Pressure Module (0 - 2.5 mbar)	1576.00
750P01	4352281	Pressure Module (0 - 25 mbar)	1218.00
750P02	4352750	Pressure Module (0 - 70 mbar)	1218.00
750P22	4352296	Pressure Module (0 - 70 mbar)	1218.00
750P03	4352738	Pressure Module (0 - 350 mbar)	1218.00
750P23	4352308	Pressure Module (0 - 350 mbar)	1218.00
750P04	4352313	Pressure Module (0 - 1 bar)	1218.00
750P24	4352324	Pressure Module (0 - 1 bar)	1218.00
750P05	4352336	Pressure Module (0 - 2 bar)	1218.00
750P06	4352349	Pressure Module (0 - 7 bar)	1218.00
750P27	4352351	Pressure Module (0 - 20 bar)	1218.00
750P07	4352360	Pressure Module (0 - 35 bar)	1218.00
750P08	4352372	Pressure Module (0 - 70 bar)	1218.00
750P09	4352385	Pressure Module (0 - 100 bar)	1218.00
750P2000	4352397	Pressure Module (0 - 140 bar)	1218.00
750P29	4352403	Pressure Module (0 - 200 bar)	1932.00
750P30	4352415	Pressure Module (0 - 340 bar)	1932.00
750P31	4352426	Pressure Module (0 - 700 bar)	1932.00
750PA3	4352432	Pressure Module (0 - 350 mbar)	1401.00
750PA4	4352444	Pressure Module (0 - 1 bar)	1401.00
750PA5	4352459	Pressure Module (0 - 2 bar)	1401.00
750PA6	4352467	Pressure Module (0 - 7 bar)	1401.00
750PA27	4352471	Pressure Module (0 - 20 bar)	1401.00
750PA7	4352480	Pressure Module (0 - 35 bar)	1401.00
750PA8	4352498	Pressure Module (0 - 70 bar)	1374.00
750PA9	4352500	Pressure Module (0 - 100 bar)	1374.00
750PV3	4352517	Pressure Module (-350 mbar)	1374.00

Model	Art. nr	Description	EUR
750PV4	4352521	Pressure Module (-1 bar)	1374.00
750PD2	4352539	Pressure Module (-70 - 70 mbar)	1374.00
750PD3	4352542	Pressure Module (-350 - 350 mbar)	1374.00
750PD10	4352556	Pressure Module (-700 - 700 mbar)	1374.00
750PD4	4352563	Pressure Module (-1 - 1 bar)	1374.00
750PD5	4352574	Pressure Module (-1 - 2 bar)	1374.00
750PD50	4352588	Pressure Module (-1 - 3.5 bar)	1374.00
750PD6	4352595	Pressure Module (-1 - 7 bar)	1374.00
750PD7	4352602	Pressure Module (-1 - 14 bar)	1374.00
750PD27	4352616	Pressure Module (-1 - 20 bar)	1374.00
750R04	4352625	Pressure Module (0 - 1 bar)	1374.00
750R06	4352633	Pressure Module (0 - 7 bar)	1374.00
750R27	4352640	Pressure Module (0 - 20 bar)	1374.00
750R07	4352657	Pressure Module (0 - 35 bar)	1374.00
750R08	4352669	Pressure Module (0 - 70 bar)	1374.00
750R29	4352678	Pressure Module (0 - 200 bar)	2063.00
750R30	4352684	Pressure Module (0 - 340 bar)	2063.00
750R31	4352691	Pressure Module (0 - 700 bar)	2063.00
750RD5	4352706	Pressure Module (-1 - 2 bar)	1544.00
750RD6	4352714	Pressure Module (-1 - 7 bar)	1544.00
750RD27	4352723	Pressure Module (-0.8 - 20 bar)	1544.00

### Process Calibrator Accessories

700HTH-1	2811795	Hydraulic Test Hose	900.00
700ILF	1566730	In-Line Filter	95.00
700LTP-1	2811763	Low Pressure Test Pump	1333.00
700-IV	202561	Current Shunt	475.00
700PMP	617131	Pressure Pump (10 bar)	672.00
700PRV-1	2811808	Pressure Relief Valve for 700HTP	1104.00
700PTP-1	2811774	Pneumatic Test Pump	865.00
700SC	667425	Serial Interface Cable (Fluke 725/725Ex/726)	227.00
700TC1	620119	Thermocouple Plug Kits (10 types)	138.00
700TC2	620127	Thermocouple Plug Kits (5 types)	114.00
Fluke 720RTD	4366669	RTD Probe for 721, 721Ex and 719PRO	255.00
787CAL 230	662996	Calibration Module (Fluke 787)	1134.00
BC7217	668217	Battery Charger	308.00
BE9005 240	946652	Battery Eliminator	164.00
BP7235	668225	NiMH Battery Pack	244.00
C700	606928	Hard Case (700 Series)	342.00
C789	946694	Soft Meter Case	185.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	244.00
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	149.00
Fluke 700HTP-2	4096855	Hydraulic Test Pump, 690 bar	1104.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	48.00
BP7240	4022220	753/754 Spare Battery	168.00
Fluke 750SW	4090343	DPC/TRACK2-software	3299.00
BC7240	4022655	Battery Charger (753/754)	45.00
HART Drywell Cable	2111088	Cable Kit, HART Drywellcontrol	159.00
Fluke-71x	3345825	Hose kit	100.00
Fluke 700TLK	3829398	Process Test Lead Kit	135.00
Fluke 709H/TRACK	4281225	Logging software with cable	436.00
Fluke 720URTD	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	159.00

### General Accessories

#### Test Leads, Probes and Clips

80K-15	618113	Probe, Electronic Air Cleaner	279.00
AC175	4101772	Threaded Alligator Clip Set	28.00
AC220	1610103	SureGrip Alligator Clip Set	45.00
AC280	1610115	SureGrip Hook Clip Set	35.00
AC283	1610144	SureGrip Pincer Clip Set	40.00
AC285	1610159	SureGrip Alligator Clip Set	22.00
AC285-FTP	4073928	Alligator Clips and adaptors (FTP-1, FTPL-1)	26.00
AC288	4617784	SureGrip™ Terminal block probe	35.00
AC87	1278079	Heavy Duty Bus Bar Clip Set	47.00
AC89	873448	Heavy Duty Insulation Piercing Test Clip	51.00
BP980	1616807	Dual Banana Plug Kit	52.00
FTL660	2280204	Fused Test Lead Set	60.00
FTP-1	3869437	Fuse test probe set	91.00
FTPL-1	3869443	Fuse test probe set with test leads	101.00
H900	1616818	Test Lead Holder	31.00
Leadwrap	4083525	Durable Nylon Hook and Loop Fastener, 3 pack	9.00
T5-Kit	3971169	T5 Tester Accessory Starter Kit	50.00
T5-RLS	4089137	Replacement Test Lead Set (T5)	22.00



Model	Art. nr	Description	EUR
TL175	3521976	Twist Guard Test Leads	28.00
TL175E	3565554	Twist Guard Test Leads, 4mm	30.00
TL220-1	3971178	SureGrip Industrial Test Lead Set	77.00
TL221	2003602	SureGrip Extension Lead Set	34.00
TL222	2003616	SureGrip Silicone Test Lead Set	34.00
TL223-1	3971184	SureGrip Electrical Test Lead Set	70.00
TL224	1610198	SureGrip Silicone Test Lead Set	30.00
TL225-1	3971191	Stray Voltage Eliminator test Lead Set	102.00
TL238	2132831	SureGrip High Energy Test Lead Kit	77.00
TL27	668571	Heavy Duty Test Lead Set	35.00
TL40	1590606	Retractable Tip Test Lead Set	50.00
TL71-1	3971207	TL71, Test Lead Set	28.00
TL75-1	3971218	TL75, Test Lead Set	23.00
TL76	2032684	All-in-one Test Lead Set	40.00
TL80A-1	3971229	TL80A, Test Lead Set	73.00
TL81A	1277073	Deluxe Electronic Test Lead Kit	152.00
TL910	1616632	Electronic Test Lead Set (with replacement tips)	70.00
TL930	1616671	Patch Cords (60 cm)	17.00
TL932	1616680	Patch Cords (90 cm)	19.00
TL935	1616698	Patch Cord Kit (60, 90, 120 cm)	58.00
TL940	1616705	Mini-Hook Test Lead Set	19.00
TL950	1616710	Mini-Pincer Test Lead Set	35.00
TL960	1616722	Micro-Hook Test Lead Set	19.00
TL970	1616793	Hook and Pincer Test Lead Kit	73.00
TLK1550-RTL	4112351	Integral test lead & 10 kV clamp	221.00
TLK220	2097022	SureGrip Accessory Kit	142.00
TLK-225	3971234	TLK225, SureGrip Master Set	152.00
TLK281-1	3971241	TLK281, Automotive Test Lead Kit	135.00
TLK-282-1	3971252	TLK282, DeLuxe Automotive Test Lead Kit	172.00
TLK287	3045631	Electronic Master Test Lead Kit	162.00
TLK289	3092521	Industrial Master Test Lead Kit	162.00
TLK290	2435092	Test Probe Kit	60.00
TLK291	2435108	Fused Test Probe Set	60.00
TP1-1	3971265	TP1, Test Probes	17.00
TP175	3521983	TwistGuard test Probes, 2MM dia probe tips	19.00
TP175E	3565568	TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters	21.00
TP2-1	3971283	TP2, Test Probes	19.00
TP220-1	3971276	TP220, SureGrip Test Probes	19.00
TP38	1541636	Slim Reach Test Probe Set (insulated)	17.00
TP74	1541649	Lantern Tip Test Probe Set	19.00
TP80	873455	Electronic Test Probe Set	38.00
TP912	1616644	Replacement tips for TL910	35.00
TP920	1616659	Test Probe Adapter Kit	50.00

#### Current Clamps

80i-110s	114519	AC/DC Current Clamp (100 A)	764.00
90i-610s	201258	AC/DC Current Clamp (600 A)	421.00
i1000s	1568487	AC Current Clamp (1000 A)	611.00
i1010	617735	AC/DC Current Clamp (1000 A)	438.00
i1010 Kit	2096998	AC/DC Current Clamp (1000 A) with Soft Case	448.00
i200	664755	AC Current Clamp (200 A)	152.00
i2000 flex	2584912	AC Flexible Current Clamp (2000 A)	305.00
i200s	664760	AC Current Clamp (200 A)	254.00
i30	2584920	AC/DC Current Clamp (30A)	407.00
i3000 flex-4PK	2696367	AC Flexible Current Clamp (3000 A), 4-pack	1223.00
i3000s	657202	AC Current Clamp (3000 A)	734.00
i3000s flex-24	2584888	AC Flexible Current Clamp (3000 A), 610 mm	468.00
i3000s flex-36	2584901	AC Flexible Current Clamp (3000 A), 915 mm	560.00
i30s	2584935	AC/DC Current Clamp (30A)	560.00
i310s	2840309	AC/DC Current Clamp (300A)	336.00
i400	2277225	AC Current Clamp (400 A)	152.00
i400s	2277202	AC Current Clamp (400A)	274.00
i40S-PR (1750)	3949777	40A Current Clamp (1750)	373.00
i410	617727	AC/DC Current Clamp (400 A)	254.00
i410 Kit	2097005	AC/DC Current Clamp (400 A) with Soft Case	295.00
i6000s flex-24	2840311	AC Current Clamp (6000 A)	611.00
i6000s flex-36	2840327	AC Current Clamp (6000 A)	713.00
i800	2840283	AC Current Clamp (800 A)	219.00

#### Temperature Accessories

80AK-A	2747812	Thermocouple Adapter	32.00
80BK-A	2747801	Integrated DMM Temperature Probe (Type K)	36.00
80CJ-M	833046	Male Mini Connectors (Type J)	24.00
80CK-M	779942	Male Mini Connectors (Type K)	24.00
80PJ-1	1288191	Bead Probe (Type J)	26.00

Model	Art. nr	Description	EUR
80PJ-9	1288218	General Purpose Probe (Type J)	66.00
80PJ-EXT	1288234	Extension Wire Kit (Type J)	59.00
80PK-1	750422	Bead Probe (Type K)	34.00
80PK-10	3439199	Pipe Clamp Temperature Probe (Type K)	201.00
80PK-11	2724500	Velcro Temperature Probe	39.00
80PK-18 Kit	3448859	Pipe Clamp Temperature Probe Kit	325.00
80PK-22	2098684	SureGrip Immersion Probe	100.00
80PK-24	2098691	SureGrip Air Probe	130.00
80PK-25	2098706	SureGrip Piercing Probe	117.00
80PK-26	2098714	SureGrip General Purpose Probe	130.00
80PK-27	2098723	SureGrip Industrial Surface Probe	356.00
80PK-3A	874610	Surface Probe (Type K)	223.00
80PK-8	200360	Pipe Clamp Temperature Probe (Type K)	183.00
80PK-9	1288229	General Purpose Probe (Type K)	66.00
80PK-EXT	1288241	Extension Wire Kit (Type K)	59.00
80PR-60	2148313	RTD Temperature Probe (Fluke 66/68)	72.00
80PT-25	2104397	SureGrip Piercing Probe	104.00
80PT-EXT	1288252	Extension Wire Kit (Type T)	59.00
80T-150UA	3190456	Universal Temperature Probe (for DMMs)	281.00
80TK	736736	Thermocouple Module (Type K)	142.00

### Cases and Holsters

C10	897744	Meter Holster	27.00
C100	827055	Hard Meter and Accessory Case	71.00
C101	2437514	Hard Case	66.00
C115	2826063	Soft Meter Case	63.00
C116	2826074	Soft Meter Case	75.00
C120	646189	Hard Case (43B/120 Series)	110.00
C125	646858	Soft Meter Case	51.00
C12A	930529	Soft Meter Case	33.00
C150	4111540	Zippered Soft Carrying Case	30.00
C1600	2091049	Meter and Accessory Case	40.00
C1620	4359042	Carrying Case	197.00
C190	677401	Hard Case (190 Series)	258.00
C195	677408	Soft Case	239.00
C20	708396	Hard Meter Case	67.00
C23	1663209	Soft Meter Case	27.00
C25	681114	Soft Meter Case	56.00
C280	3182785	Soft Meter Case	66.00
C33	1664120	Soft Meter Case	30.00
C345	3311173	Soft Case	80.00
C35	2826056	Soft Meter Case	46.00
C43	1663230	Soft Meter Case	84.00
C50	762823	Soft Meter Case	40.00
C510	1547885	Leather Meter Case	79.00
C520A	1629104	Leather Tester Case	60.00
C550	1547919	Tool Bag	132.00
C75	865535	Soft Accessory Case	18.00
C781	619988	Soft Meter Case	97.00
C789	946694	Soft Meter Case	185.00
C800	896220	Hard Meter and Accessory Case	72.00
C90	466029	Soft Meter Case	40.00
CXT170	3352567	Rugged Pelican Hard Case	171.00
CXT280	3352571	Rugged Pelican Hard Case	171.00
CXT80	3352559	Rugged Pelican Hard Case	171.00
CXT1000	4628917	Extreme Hard case	171.00
H3	1608458	Holster (330 Series)	44.00
H5	649365	Electrical Tester Holster (Fluke T5)	33.00
H6	2152040	Infrared Thermometer Holster (Fluke 63/65/68/561)	31.00
H15	4111533	Belt Holster for T100 series	29.00
H80M	2138458	Holster + Magnetic Hanger	42.00

### Automotive Accessories

90i-610s	201258	AC/DC Current Clamp (600 A)	421.00
BP880	2150594	BNC to Female Double Stacking Banana Plug	15.00
BP881	2151015	BNC to Male Double Stacking Banana Plug	18.00
PV350	919811	Pressure Vacuum Module	285.00
RPM80	880849	Inductive Pick-up	97.00
SCC128	2100199	Automotive Accessory Kit (120 Series)	727.00
SCC198	2100208	Automotive Accessory Kit (190 Series)	915.00
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	253.00
TAS90	614187	Automotive Accessory Set (120/190 Series)	71.00
TL28A	1273185	Automotive Test Lead Set	58.00
TL82	2150636	Automotive Pin and Socket Adapter Set	116.00
TP40	1567573	Automotive Back Probe Pins (5 pcs) (4 mm)	41.00

Model	Art. nr	Description	EUR
TP81	2149098	Insulation Piercing Clip Set (4 mm)	56.00
TP82	2149080	Insulation Piercing Clip Set (2 mm)	53.00
TP88	2149102	Rigid Back Probe Pin Set	14.00
<b>Other Accessories</b>			
80K-40	382846	High Voltage Probe	285.00
80K-6	532424	High Voltage Probe	159.00
EBC290	3894906	External Battery Charger	106.00
FOM	200428	Fiber Optic Meter	564.00
FOS-850	200433	Fiber Optic Light Source	340.00
FOS-850/1300	200441	Fiber Optic Light Source	833.00
L200	2096346	Probe Light	24.00
L205	2098588	Mini Hat Light	31.00
L206	2098595	Deluxe Hat Light	40.00
L210	2096379	Probe light and probe extender	39.00
L215	2096368	SureGrip kit with probe light and probe extender	89.00
MC50	2092300	MeterCleaner Wipes, 50-pack	89.00
MC6	2092212	MeterCleaner Wipes, 6-pack	13.00
PV350	919811	Pressure Vacuum Module	285.00
SV225	3100477	Stray Voltage Adapter	68.00
TPAK	1281997	ToolPak, Meter Hanging Kit	40.00
<b>Fuses</b>			
943121	943121	Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm	4.65
803293	803293	Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm	8.55
830828	830828	Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm	7.50
2279339	2279339	Fuse, A:315mA (f), V:1000V, IR:10kA, 6.35x32 mm	11.00
740670	740670	Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm	3.60
<b>Software</b>			
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	149.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	244.00
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	281.00
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	161.00
FVF-UG	1576741	FlukeView Forms Upgrade	131.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	48.00
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	468.00
SCC120F	646692	FlukeView Software + USB Cable + Case (Fluke 123) - French	468.00
SCC190	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	655.00
SW90W	3894923	FlukeView Software	362.00

**Fluke Nederland B.V.**

Postbus 1337

5602 BH Eindhoven

Tel.: (040) 267 51 00

Fax: (040) 267 51 11

E-mail: [info@fluke.nl](mailto:info@fluke.nl)

Web: [www.fluke.nl](http://www.fluke.nl)

10001 - Fluke Test Tools Price List End

Customer - English

Rev. 39