

Information about the latest products and promotions from Beha-Amprobe.



2100 Series Two Pole Voltage Tester 2100-Alpha, 2100-Beta

NEW clamp meters
from the inventor
of the clamp meter

AMP-200-EUR series
TRMS Clamp Meters

AMP-300-EUR series
Motor Maintenance
TRMS Clamp Meters



The AM-500-EUR Digital Multimeter. Value for your money!

We offer the right multimeter for every application with an optimal price-performance ratio.



AM-500-EUR

- Electricians
- 600V AC/DC
- 10A AC/DC
- Including test leads

AM-510-EUR

- Electricians
- 600V AC/DC
- 10A AC/DC
- Including test leads

AM-520-EUR

- HVAC
- 750V AC/DC
- 10A AC/DC
- Including Carrying Case
- Including test leads

With FREE
IR-450-EUR
Thermometer

AM-530-EUR KIT

- Electrical
- AC 750V/DC 1000V
- 10A AC/DC
- Including Carrying Case
- Including test leads

With FREE
IR-450-EUR
Thermometer

AM-540-EUR KIT

- Advanced HVAC
- 1000V AC/DC
- 10A AC/DC
- Including Carrying Case
- Including test leads

With FREE
IR-450-EUR
Thermometer

AM-550-EUR KIT

- Industrial
- 1000V AC/DC
- 10A AC/DC
- Including Carrying Case
- Including test leads

£ 25

Order No. 4102332

£ 47

Order No. 4102344

£ 64

Order No. 4131281

~~£121~~

£ 85

Order No. 4490034

~~£139~~

£ 103

Order No. 4490041

~~£149~~

£ 113

Order No. 4490052

IR-450-EUR Pocket Thermometer



The IR-450-EUR
3-in-1 Infrared
Pocket
Thermometer,
Laser Pointer,
and Flashlight

£ 36

Order No. 4308539

The Beha-Amprobe 2100 series two pole voltage testers

- Built tough for use in industrial and commercial environments.
- Built according to latest voltage tester standard EN 61243-3:2010.
- Voltage test by LED*, phase rotation test, switchable load by two push buttons, single pole phase test and continuity.
- Working in dark environments and has an ingress protection rating of IP 64.
- Dual display for voltage test with an LED and LCD display.

**2100-Alpha
or 2100-Beta +
Carrying Bag CC-Vp-7xx****



Value £ 17

£ 46

Order No. 4312495

£ 70

Order No. 4312508

** Go to www.beha-amprobe.com/promotions to claim your gift. Not valid in combination with other promotions.

* only for 2100-Beta

Visit our new website:
beha-amprobe.com

NEW from the inventor of the clamps



£ 89

Order No. 4560581

AMP-210-EUR
AC Clamp Meter



£ 114

Order No. 4560596

AMP-220-EUR
AC/DC Clamp Meter

AMP-200 Series Features:

- True-RMS
- Low Pass Filter
- Amp-Tip Functions
- Non-Contact Voltage Detection (NCV)
- Audible Continuity and Diode Test
- Data Hold, Relative Zero
- Large LCD Backlit Display
- Safety Rated: CAT III 600 V



For our complete clampmeter range, visit our new website:
www.beha-amprobe.com



£ 122

Order No. 4560603

AMP-310-EUR
AC Clamp Meter
HVAC



£ 139

Order No. 4560615

AMP-320-EUR
AC/DC Clamp Meter
Electrical Motor Maintenance

AMP-300 Series Features:

- True-RMS
- Motor Testing Capabilities
 - Motor rotation
 - 3-phase sequence testing
 - Inrush current monitoring during motor start-up
- Amp-Tip Function
- Low Pass Filter for variable frequency drives
- HVAC Features
 - Temperature measurement; User selectable °F or °C
 - DC Microamps for flame sensor testing
 - Capacitance measurement for start and run motor capacitors
- Safety Rated: CAT III 600 V (AMP-310, AMP-320)
CAT IV 600 V, CAT III 1000 V (AMP-330)



£ 163

Order No. 4560626

AMP-330-EUR
AC/DC 1000 A Clamp Meter
Industrial Motor Maintenance

Visit our new website: **beha-amprobe.com**

GT-400-UK Handheld Portable Appliance Tester



The GT-400-UK Portable Appliance Tester, is a light-weight, portable appliance tester that tests the integrity of electrical devices, ensure safety, functionality and compliance of regulatory standards according EN61010 Safety Standards.

- Intuitive and simple to use
- Easily portable for on the go testing
- Fast answers - Instantly measures safety and integrity of electrical appliances

£ 435

Order No. 4381012



Digital Multifunction installation testers

KTS1625 Digital Multifunction Tester

The Robin-Amprobe KTS1625 Multifunction Installation tester verifies the safety of electrical installations in domestic, commercial and industrial applications. It can ensure that fixed wiring is safe and correctly installed to meet the requirements of BS7671 IEE 17th edition wiring regulations.



Action Price

KTS1625
~~£632~~ **£ 599**

Order No. 3730312

17th Edition Test Kits

Each test kit is supplied in a highly durable purpose-made soft carrying case for protection and contains an insulation-continuity tester, loop impedance tester, RCD tester and all necessary test leads and accessories for testing at final circuits or at distribution boards.

ROBIN AMPROBE

KIT 17A



KMP7036
£ 238
Order No. 3730274



KMP7020
£ 271
Order No. 3730295



KMP7030
£ 324
Order No. 3842833



Action Price

KIT 17A
~~£795~~ **£ 749**

Order No. 3842840

KIT 17B



KMP7036
£ 238
Order No. 3730274



KMP7021
£ 291
Order No. 3730301



KMP7030
£ 324
Order No. 3842833

KIT 17B
~~£815~~ **£ 779**

Order No. 3842857

Visit our new website www.beha-amprobe.com

Robin-Amprobe® Test Tools UK

52 Hurricane Way, Norwich, Norfolk, NR6 6JB, United Kingdom

Web: www.robin-amprobe.co.uk / www.beha-amprobe.com

Email: info@robin-amprobe.co.uk

Phone: +44 (0) 1603 25 6662 Fax: +44 (0) 1603 25 6664

Period: 1.2.2015 - 30.06.2015. Not coupled with other actions.

Order through your local sales representative. Only as long as stock lasts.

©2015 Beha-Amprobe. All rights reserved. Pub ID: 13290-eng