



**Fluke Europe B.V.**  
P.O. Box 1186  
5602 BD Eindhoven  
The Netherlands  
Web: [www.fluke.eu](http://www.fluke.eu)

For more information call:  
In Europe/M-East/Africa +31 (0)40 2 675 200  
or Fax +31 (0)40 2 675 222

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom

Tel.: (020) 7942 0700  
Fax: (020) 7942 0701  
E-mail: [industrial@uk.fluke.nl](mailto:industrial@uk.fluke.nl)  
Web: [www.fluke.co.uk](http://www.fluke.co.uk)

© Copyright 2011 Fluke Corporation. All rights reserved.  
Printed in the Netherlands 04/2011 Data subject to  
alteration without notice.

Pub\_ID: 11792-eng Rev. 01



P3  
Series

Proven  
Practical  
Performance

**FLUKE**®

Thermal Imagers

Six amazing models. One trusted name.

# The Fluke P<sup>3</sup> Series

For Industrial & Electrical  
For Building Diagnostics



P<sup>3</sup>  
Series

Proven  
Practical  
Performance

The only thing that precedes Fluke's high standards of quality is our reputation for making the finest measurement tools in the world. Fluke thermal imagers are no exception. And, the P<sup>3</sup> Series handily delivers on the promise to offer the most tool for the money.



# Nothing Feels Like a Fluke

It not only fits your hand, it fits your idea of how a great tool should feel: intuitively comfortable, strong and solid, heavy duty, so it works long hours over many years.

# The P<sup>3</sup> Series—Superior, not Superfluous

Fluke is how other tools are measured.

## Superior image quality

Industry-leading thermal sensitivity and spatial resolution combined with a high definition display, creates the sharpest images in the industry.

## One-handed, easy-to-use interface

With just a push of your thumb, go from one handed manual smart focus to adding picture-in-picture and even add comments in your own voice.

## Torture tested™

Before a Fluke goes into your hands, we drop it from ours. Only Fluke thermal imagers are designed from the inside out to withstand a 6.5' drop.



P3  
Series

Proven  
Practical  
Performance

### Fluke IR-Fusion®

(Picture-in-picture and auto blending)

Precision visible and IR image alignment allows Fluke to offer the only on-camera blended infrared and visible image to better diagnose issues.

## It isn't advanced if it isn't Easy to Use

The greatest technological advancement in thermography may be how Fluke has made it so simple to capture images and analyze data right out of the box.

### Interchangeable lenses


Interchangeable wide-angle and IR-Fusion compatible telephoto lenses to cover any application.



# Fluke set the standard for Superior Image Quality

Trust your eyes. That's where you see the difference between the quality of Fluke resolution versus our competitors'. The easier it is to see the problem, the easier it is to provide solutions. Fluke starts with a large 3.7" display (640x480 resolution) with full VGA color and LCD display.


Even the smallest temperature difference can indicate a big problem, or at least the start of one. Fluke integrates the P<sup>3</sup> Series with industry-leading thermal sensitivity and spatial resolution to create the sharpest images in the industry.



P3  
Series

Proven  
Practical  
Performance

# A passion for precision Creates Fluke IR-Fusion®



No other manufacturer can boast on-camera blending. Compare the images above. Only Fluke has mastered the ability to create the industry's only transparent, perfectly blended and aligned visible and infrared images.



A close-up photograph of a Fluke Ti32 thermal imager. The device is primarily orange and black. The lens is a prominent feature in the center, surrounded by a grey metal housing. To the left, a black handle is visible. A label on the orange part of the device reads "FLUKE Ti32 IR FUSION TECHNOLOGY".

FLUKE  
Ti32  
IR FUSION  
TECHNOLOGY

## Legendary Ruggedness

makes Fluke  
hard to beat.

No matter how sophisticated the technology, Fluke has never forgotten that they make tools—thermal imagers that do amazing things, like winning Plant Engineering Product of the Year. But at the heart of every model, what Fluke makes is a super-rugged, hard-working, dependable tool.

The Fluke P<sup>3</sup> Series of thermal imagers are sophisticated computers and high-resolution cameras, but that doesn't mean they have to be coddled. All Fluke thermal imagers are built to take punishment, bridging the gap between high-tech device and practical tool. This is one gutsy tool.



P3  
Series

Proven  
Practical  
Performance

## Not just tested, Torture Tested™

Before a Fluke goes into your hands, we drop it from ours.  
Only Fluke thermal imagers are built to withstand a 6.5' drop.  
Fluke conducts **8 tests** before a thermal imager earns the name Fluke.

- 1** Drop packaged product on each face, corner, and edge (8 corners, 6 sides, 12 edges) from approximately one meter onto a steel base.
- 2** Drop the unpackaged unit from 2 meters; 6 drops on each face of the unpackaged unit.
- 3** Subject the unit to extensive vibration for 30 minutes, (10 Hz-500 Hz, at 0.03 g<sup>2</sup>/Hz – equivalent to ~ 4.8 g rms) on three perpendicular axes.
- 4** Bombard the unit with electromagnetic fields and radio frequency emissions per EN61326-1:2006 to see if the readings change.
- 5** Spray the unit with water at 10 liters/minute with a pressure of 100 kN/m<sup>2</sup> and also test sealed joints from dust ingress.
- 6** Run the product at temperatures down to -10 °C and up to 50 °C and verify that the product operates within specifications.
- 7** Run the product and add humidity, up to 95 % at up to 40 °C, and run the tests again.
- 8** Simulate sending the unit 12,000 meters (7 miles) in altitude and verify that the product still functions properly.

Fluke P<sup>3</sup> for  
Industrial &  
Electrical



**“If given a choice, I don’t know any engineer who wouldn’t rather own Fluke.”**

# The first solution Is Finding the Problem



Industrial

Industrial, mechanical, electro-mechanical and general building maintenance.



Process

Process, refractory insulation, tank and vessel levels, steam systems and traps, pipes and valves, etc.



Electrical

Electrical, unbalanced loads, overloaded systems, wiring mistakes or component failure, etc.

Finding a potential problem before it becomes a costly disaster shows you just how much a Fluke thermal imager can save you in time, money and even lives. From a safe distance, you can quickly and accurately scan a large area for temperature differences, whether the objects are moving, out-of-reach, too hot or too risky to be near.

Whether you're checking for bad steam traps, load imbalances or overheating bearings, Fluke P<sup>3</sup> Series of thermal imagers keep the promise of performance. Dependability is the benchmark by which all tools should be measured. That's why, for more than 60 years, experienced industrial and electrical professionals have turned to Fluke to do the job that needs doing.

**Ti27**



- 240x180 IR resolution
- 43,200 total IR pixels

**Ti29**



- 280x210 IR resolution
- 58,800 total IR pixels

**Ti32**



- 320x240 IR resolution
- 76,800 total IR pixels

# For building diagnostics, it's not a question of why anymore. It's a Question of When



Green Energy

Energy audit, building inspection and weatherization.



Moisture Detection

Restoration, water damage and roofing.



Building Diagnostics

Building problems, defects and general maintenance.

The more aware your customers become of thermography, the more they'll demand it. Whether you're searching for energy waste, leaky roofs or moisture problems, Fluke P<sup>3</sup> Series thermal imagers offer tested and proven game-changing technology that takes the guesswork out of finding problems and provides solutions.

The highest resolution. The greatest durability. The easiest to use. Advantage Fluke. Advantage you.

## Fluke P<sup>3</sup> Series and the art of persuasion.

Telling someone they have a problem is not nearly as convincing as proving your point with a colorful, high-resolution thermal image. To make things even clearer, our pioneering IR-Fusion® lets you show both infrared and normal light images in the same picture, so you have a frame of reference that should convince even the most skeptical customers.

### TiR27



- 240x180 IR resolution
- 43,200 total IR pixels

### TiR29



- 280x210 IR resolution
- 58,800 total IR pixels

### TiR32



- 320x240 IR resolution
- 76,800 total IR pixels



Fluke P<sup>3</sup> for  
Building  
Diagnostics

**“It’s building a new level of trust with my customers while it’s building my bottom line.”**



# SmartView®

## The industry's most generous software package.


Compare Fluke's software to our competition's software and it's clear that Fluke doesn't leave you wanting. While others have been known to charge up to \$2,000 in additional software fees, Fluke's award-winning software package is standard.

## Free upgrades. Free to share.


Unlike other manufacturers, Fluke doesn't charge you for software upgrades. They're free for the life of the product. And, Fluke doesn't tie your hands with licensing agreements that keep you from sharing with others.

## SmartView is the smart choice.


- Extensive annotation, editing, and viewing options with full IR-Fusion capabilities, including 3D-IR™ analysis
- Multiple reporting options and templates
- Enhance and analyze images quickly and easily
- Easy access to editing functions with SmartView tools and controls
- Report Wizard guides you through automatic report generation
- Communicate image details with text annotation drag and drop feature
- Unlimited licenses and lifetime upgrades



Navigate, analyze and enhance IR images.



Organize data with extensive annotations.



Simplified, professional report generation.

## Everything you need to get started and finish the job

- SmartView analysis and reporting software
- 2 GB SD memory card
- Multi-function memory card reader for downloading images
- Fluke signature hard and soft transport cases
- Adjustable hand strap (Left or right-handed users)
- 2 rechargeable batteries
- AC charger/power supply
- All Fluke thermal imagers come with a full two-year warranty. Extended warranties are also available.\*

\* Availability and specifications subject to change without notice.

## Performance-tested Fluke accessories

From telephoto and wide-angle lenses to extra chargers, tripod mounts and light-shading visors, you can expand your capabilities with Fluke signature accessories.