

# Fluke Test Tools pricelist

Valid from: 02-10-2021

Model	Article Nr.	Description	EUR
<b>Fluke Connect</b>			
<b>Fluke Connect - 3000 Series</b>			
FLK-3000FC	4401595	FC Wireless Digital Multimeter	342
FLK-3000FC/1AC-II	4699302	Electrician's DMM voltage tester and accessory kit	489
FLK-3000FC/EDA2	4699333	Electronics DMM and deluxe accessory kit	441
FLK-3000FC/TPAK	4699340	Fluke 3000FC with TPAK meter hanging kit	380
FLK-A3000FC	4401588	FC Wireless AC Current Clamp Module	220
FLK-A3000FC KIT	4465618	FC Wireless Essential Kit with A3000	489
FLK-A3001FC	4459439	FC Wireless iFlex AC Current Module	257
FLK-A3001FC KIT	4465665	FC Wireless Essential Kit with i3000	527
FLK-A3002FC	4459442	FC Wireless AC/DC Current Module	147
FLK-A3003FC	4629295	FC Wireless 2000A DC Clamp meter	614
FLK-A3004FC	4629301	FC Wireless 4-20mA DC Clamp meter	735
FLK-T3000FC	4401563	FC Wireless K-Type Temperature Module	220
FLK-T3000FC KIT	4465652	FC Wireless Essential Kit with T3000	489
FLK-V3000FC	4401556	FC Wireless AC Voltage Module	232
FLK-V3000FC KIT	4465641	FC Wireless Essential Kit with V3000	489
FLK-V3001FC	4459421	FC Wireless DC Voltage Module	232
FLK-V3001FC KIT	4467777	FC Wireless essential Kit with V3001	489
<b>Fluke Connect - Accessories</b>			
FLK-FC-SD 8GB	4463628	Fluke Connect Wireless SD Card	109
FLUKE-IR3000FC	4460436	Connector, Infrared, FC	163
<b>Digital Multimeters</b>			
<b>110 Series Multimeters</b>			
C50	762823	Soft Meter Case	49
FLUKE-113 EUR	3088053	True RMS Multimeter	145
FLUKE-114 EUR	2583552	True RMS Multimeter	191
FLUKE-115 EUR	2583583	True RMS Multimeter	225
FLUKE-116 EUR	2583601	True RMS Multimeter	271
FLUKE-116/323 KIT	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	384
FLUKE-116/62 MAX+	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	348
FLUKE-117 EUR	2583647	Fluke 117 Electricians TRMS Multimeter with Non-Contact voltage	283
FLUKE-117/323 EUR	4296034	Fluke Electrician's Multimeter Combo Kit	366
FLUKE-117/PRV240	4636971	Proving unit, Fluke 117 DMM Kit	367
<b>170 Series Multimeters</b>			
C90	466029	Soft Meter Case	49
FLUKE-175 EGFID	1592901	True RMS Multimeter	277
FLUKE-177 EGFID	1592874	True RMS Multimeter	335
FLUKE-179 EGFID	1592842	True RMS Multimeter	395
FLUKE-179/EDA2/EUR	3947719	Electronics Combo Kit	452
FLUKE-179-2/IMSK	4370598	Industrial Multimeter Service Kit	490
<b>200 Series Multimeters</b>			
BC500TDMM	4820410	Battery charger for Fluke 279FC	144
C280	3182785	Soft Meter Case	81
FLK-287/FVF/IR3000	4699316	Fluke 287 FlukeView® Forms Combo Kit	920
FLK-289/FVF/IR3000	4699325	Fluke 289 FlukeView® Forms Combo Kit	983

Model	Article Nr.	Description	EUR
FLUKE-233 EU	3469334	Remote Display Multimeter	391
FLUKE-279FC I/B	4989200	Wireless TRMS Thermal Multimeter with iFlex & extra battery	1166
FLUKE-279FC/IFLEX	4684050	Wireless TRMS Thermal Multimeter w/iFlex	1060
FLUKE-287/EUR	3947781	True RMS Electronic Logging Multimeter with TrendCapture	712
FLUKE-287/FVF/EUR	3947796	FlukeView Forms Combo Kit	835
FLUKE-289/EUR	3947801	True RMS Industrial Logging Multimeter with TrendCapture	774
FLUKE-289/FVF/EUR	3947812	Industrial Logging Multimeter and Software Combo Kit	862
FLUKE-289/IMSK	3449156	Industrial Multimeter Service Kit	763
<b>20 Series Multimeters</b>			
C25	681114	Soft Meter Case	70
FLUKE-27II/EUR	3947770	Industrial Multimeter (IP67)	622
FLUKE-28II/EUR	3947820	True RMS Industrial Multimeter (IP67)	622
FLUKE-28IIEX	4017165	Intrinsically safe true-rms digital multimeter	1492
<b>70 Series Multimeters</b>			
FLUKE-77-4/EUR	3947835	Multimeter	489
<b>80 Series Multimeters</b>			
C25	681114	Soft Meter Case	70
FLUKE-83-5/EUR	3947847	Multimeter	550
FLUKE-87-5/E2K/EUR	3947864	Industrial Electricians Combo Kit	651
FLUKE-87-5/EUR	3947858	True RMS Multimeter	542
FLUKE-87V/IMSK	3448783	Digital multimeter Fluke 87V and the i400 AC current clamp	629
FLUKE-87V-MAX	5140033	True-rms Digital Multimeter	597
FLUKE-87V-MAX/E2 KIT	5160712	Fluke 87V MAX E2 Industrial Electrician Combo Kit	705
<b>Clamp Meters</b>			
FLUKE-323	4152628	True RMS Clamp Meter	147
FLUKE-324	4152637	True RMS Clamp Meter	191
FLUKE-325	4152643	True RMS Clamp Meter	265
FLUKE-353	2840252	AC/DC True RMS Clamp Meter	736
FLUKE-355	2840265	AC/DC True RMS Clamp Meter	919
FLUKE-365/E	3790607	Detachable TRMS Clamp Meter	306
FLUKE-368 FC	4709907	Wireless leakage current clamp, 40mm jaw	817
FLUKE-369 FC	4709934	Wireless leakage current clamp, 61mm jaw	817
FLUKE-373/E	3790564	600A TRMS Clamp Meter	306
FLUKE-374 FC	4696001	600A AC/DC TRMS Wireless Clamp Meter	430
FLUKE-375 FC	4695932	600A AC/DC TRMS Wireless Clamp Meter	514
FLUKE-376 FC	4695861	1000A AC/DC TRMS Wireless Clamp Meter with iFlex	583
FLUKE-377 FC/E	5111858	Fluke 377 FC True-rms Non-Contact Voltage AC/DC Clamp Meter with iFlex	649
FLUKE-377/E	5225745	Fluke 377 True-rms Non-Contact Voltage AC/DC Clamp Meter with iFlex	649
FLUKE-378 FC/E	5225723	Fluke 378 FC True-rms Non-Contact Voltage AC/DC Clamp Meter with iFlex	749
FLUKE-378/E	5225761	Fluke 378 True-rms Non-Contact Voltage AC/DC Clamp Meter with iFlex	749
FLUKE-381	3610452	Remote Display TRMS Clamp Meter	686
FLUKE-393/E	5274939	393 CAT III 1500 V True-rms Clamp Meter with iFlex	699
FLUKE-393FC/E	5274900	393 FC CAT III 1500 V True-rms Clamp Meter with iFlex	699
FLUKE-902 FC	4695814	TRMS Wireless HVAC ClampMeter	343
FLUKE-I2500-10	3676410	iFlex Probe	159
FLUKE-I2500-18	3676405	iFlex Probe	159
H3	1608458	Holster (330 Series)	53

Model	Article Nr.	Description	EUR
<b>Bench Multimeters</b>			
8808A 220V	2802372	5.5 Digit Multimeter	800
8808A 240V	2802385	5.5 Digit Multimeter	800
8808A/SU 220V	2802459	5.5 Digit Multimeter (software & cable)	1020
8808A/SU 240V	2802467	5.5 Digit Multimeter (software & cable)	1020
8808A/TL 220V	3111085	5.5 Digit Multimeter, 2X4W Test Lead Kit	889
8808A/TL 240V	3111097	5.5 Digit Multimeter, 2X4W Test Lead Kit	889
8845A 220V	2577352	6.5 Digit Precision Multimeter	1200
8845A 240V	2577365	6.5 Digit Precision Multimeter	1200
8845A/SU 220V	2675315	6.5 Digit Precision Multimeter (incl. software + cable)	1400
8845A/SU 240V	2675332	6.5 Digit Precision Multimeter (incl. software + cable)	1400
8845A-EFPT	2742690	Extended Fine Point Tip Adapter Set	23
8845A-TPIT	2742683	Test Probe IC Tip Set	17
8846A 220V	2577383	6.5 Digit Precision Multimeter	1570
8846A 240V	2577390	6.5 Digit Precision Multimeter	1570
8846A/SU 220V	2675367	6.5 Digit Precision Multimeter (incl. software + cable)	1790
8846A/SU 240V	2675380	6.5 Digit Precision Multimeter (incl. software + cable)	1790
884X-1G	2675534	USB Memory 1 GB	45
884X-CASE	2675552	Hard Case (8845A/8846A)	492
884X-RTD	2675468	100 OHM RTD Temperature Probe	644
884X-SHORT	2653346	4-wire short	34
884X-USB	2675479	USB to RS232 Cable Adapter	184
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	346
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	199
FVF-UG	1576741	FlukeView Forms Upgrade	162
RS43	946470	Serial Interface Cable	100
TL2X4W-PTII	2826215	2x4 Wire Ohms Test Lead 2 mm Probe Tip	89
TL2X4W-TWZ	2723629	2X4-Wire Ohms Tweezers Test Leads	112
Y8021	708289	IEEE-488 Shielded Interface Cable, 1 m	499
Y8022	708297	IEEE-488 Shielded Interface Cable, 2 m	583
Y8846D	2771721	Rack mount kit dual (8845A/8846A)	190
Y8846S	2675518	Rack mount kit single (8845A/8846A)	140
<b>Automotive Meters</b>			
FLUKE-88-5/A KIT	2117440	Automotive Meter Combo Kit	797
<b>Hand Tools</b>			
CPAK8	5081580	Magnetic hanging pouch	43
IB117KEUR	5195045	Fluke 117 Electrician's Multimeter + Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	423
IB117L	5133953	Fluke 117 Electrician's Multimeter + SLS3 + ISLS5 + IPHS2	317
IB117M	5133966	Fluke 117 Electrician's Multimeter + ISLS3 + ISLS5 + IPHS2 + IPHS1 + ISLS8	338
IB179K-EDSNF	5134028	Fluke 179 True-RMS Digital Multimeter + Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	529
IB179L-EDSNF	5134004	Fluke 179 True-RMS Digital Multimeter + ISLS3 + ISLS5 + IPHS2	423
IB179M-EDSNF	5134019	Fluke 179 True-RMS Digital Multimeter + ISLS3 + ISLS5 + IPHS2 + IPHS1 + ISLS8	444

Model	Article Nr.	Description	EUR
IB376KEUR	5195061	Fluke 376 FC Clamp Meter + Insulated Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	709
IB376L	5134134	Fluke 376 FC Clamp Meter + ISLS3 + ISLS5 + IPHS2	615
IB376M	5134141	Fluke 376 FC Clamp Meter + ISLS3 + ISLS5 + IPHS2 + IPHS1 + ISLS8	635
IB875KEUR	5195050	Fluke 87V Industrial Multimeter + Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	688
IB875L	5134096	Fluke 87V Industrial Multimeter + ISLS3 + ISLS5 + IPHS2	582
IB875M	5134107	Fluke 87V Industrial Multimeter + ISLS3 + ISLS5 + IPHS2 + IPHS1 + ISLS8	603
IBT6KEUR	5195077	T6-1000 Electrical Tester + Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	423
IBT6L	5134118	T6-1000 Electrical Tester + ISLS3 + ISLS5 + IPHS2	307
IBT6M	5134129	T6-1000 Electrical Tester + ISLS3 + ISLS5 + IPHS2 + IPHS1 + ISLS8	317
IKPK7	5067392	Fluke Pack30 Professional Tool Backpack + Insulated Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	381
IKPL3	5067377	Insulated 3 units Plier Kit, 1,000 V	158
IKSC7	5067345	Insulated 7 units Screwdriver Kit, 1,000 V (3 slotted, 2 Phillips, 2 square)	126
IKST7	5067389	Insulated Hand Tools Starter Kit—5 insulated screwdrivers and 3 insulated pliers, 1,000 V	254
INCP8	5067267	Insulated Lineman Combination Plier, 8 in, 200 mm, 1,000 V	53
INDC8	5067244	Insulated High Leverage Diagonal Cutter, 8 in, 200mm, 1,000 V	63
INLP8	5067232	Insulated Long Nose with Side Cutter, 8 in, 200mm, 1,000 V	58
INPP10	5067259	Insulated Pump Plier Fast adjustable, 10 in, 250 mm, 1,000 V	74
IPHS1	5067306	#1 Phillips screwdriver. Certified to 1000 V ac and 1500 V dc.	19
IPHS2	5067314	#2 Phillips screwdriver. Certified to 1000 V ac and 1500 V dc.	24
ISLS3	5067271	Insulated Slotted Screwdriver 3/32x3 in, 2.5 mm x 75 mm, 1,000 V	17
ISLS5	5067280	Insulated Slotted Screwdriver 5/32x4 in, 4 mm x 100 mm, 1,000 V	17
ISLS8	5067298	125 mm screwdriver with 6 mm slotted blade. Certified to 1000 V ac and 1500 V dc.	24
ISQS1	5067323	Insulated Squared Screwdriver #1, 4 in, 100 mm, 1,000 V	23
ISQS2	5067338	Insulated Squared Screwdriver #2, 5 in, 125 mm, 1,000 V	23
RUP8	5081598	Roll-up tool pouch	21
<b>Electrical Testers</b>			
FLK-1AC-A1-II-5PK	2433042	Fluke 1Ac li Voltalert™ 5-Pack	129
FLK-1AC-E1-II-5PK	2433056	Volt Alert 5-pack	129
FLK2AC/200-1000V5L	3806493	Volt Alert, 200-1000V, 5-pack	118
FLK2AC/200-1000VC	3611972	ACV Detector 200-1000V	34
FLK2AC/200-1000VCL	3611985	ACV Detector 200-1000V	34
FLK2AC/90-1000V	3807928	ACV Detector 90-1000V, Flat-tip	34
FLK2AC/90-1000V5PK	3807937	Volt Alert 90-1000V, 5-pack, Flat-tip	118
FLUKE-1000FLT	4472387	Fluorescent Light Tester	278
FLUKE-1AC-E2-II	2432971	Volt Alert	36
FLUKE-2042	2435038	Cable Locator (Transmitter + Receiver)	883
FLUKE-2042T	2435045	Cable Locator Transmitter	460
FLUKE-9040EUR	4014969	Fase Rotation Indicator	235
FLUKE-T110	4016950	Voltage, Continuity Tester with switchable load	93
FLUKE-T130	4016961	Voltage and Continuity Tester with backlit LCD readout	136

Model	Article Nr.	Description	EUR
FLUKE-T150	4016977	Voltage and Continuity Tester with LCD readout and additional resistance measurement	157
FLUKE-T150/PRV240	4637005	Fluke-T150 +PRV240 Proving Unit Kit	306
FLUKE-T90	4016945	Basic Voltage and Continuity Tester	64
FTL-660	2280204	Fused Test Lead Set	72
H5	649365	Electrical Tester Holster (Fluke T5)	42
H-T6	4910585	T6 Belt Holster	42
LVD1A	4571403	Volt Light	42
LVD2	2740300	Volt Light	46
PRV240	4566209	Proving unit	183
PRV240FS	4910310	Proving unit, T6/NCV	174
T5-1000 EUR1	659570	Electrical Tester	201
T5-600 EUR1	659612	Electrical Tester	179
T5-600/62MAX+/1ACE	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	292
T5-H5-1AC KIT/EUR	2098657	Electrical Tester Kit with Holster and 1AC	224
T6-1000/EU	4910257	Electrical Tester with FieldSense™, round	296
T6-1000PRO/EU	5134758	Fluke T6-1000 PRO Electrical Tester	305
T6-600/62MAX+/1ACE	4910524	Fluke T6-600 with 62MAX+ IR Temperature meter, 1AC Voltage detector and C60 softcase	338
T6-600/EU	4910322	Electrical Tester with FieldSense™, round	232
<b>Laser Levels</b>			
<b>3 point lasers</b>			
PLS 3G KIT	5009378	3-Point Green Laser Kit	272
PLS 3G Z	5009369	3-Point Green Laser Bare Tool	227
PLS 3R KIT	5009357	3-Point Red Laser Kit	229
PLS 3R Z	5009340	3-Point Red Laser Bare Tool	183
<b>5 point lasers</b>			
PLS 5G KIT	5009414	5-Point Green Laser Kit	364
PLS 5G Z	5009406	5-Point Green Laser Bare Tool	322
PLS 5R KIT	5009391	5-Point Red Laser Kit	315
PLS 5R Z	5009384	5-Point Red Laser Bare Tool	283
<b>Cross line and point lasers</b>			
PLS 6G RBP KIT	5116068	Cross Line and Point Green Laser Kit	529
PLS 6G RBP SYS	5116079	Cross Line and Point Green Laser System	635
PLS 6G Z	5009461	Cross Line and Point Green Bare Tool	434
PLS 6R RBP KIT	5195802	Cross Line and Point Red Laser Kit	423
PLS 6R RBP SYS	5195833	Cross Line and Point Red Laser System	529
PLS 6R Z	5009423	Cross Line and Point Red Laser Bare Tool	333
<b>Cross line lasers</b>			
PLS 180G RBP KIT	5116087	Cross Line Green Laser Kit	370
PLS 180G RBP SYS	5116093	"Cross Line Green Laser System"	423
PLS 180G Z	5017287	Cross Line Green Laser Bare Tool	319
PLS 180R RBP KIT	5195840	Cross Line Red Laser Kit	296
PLS 180R RBP SYS	5195857	"Cross Line Red Laser System"	370
PLS 180R Z	5017279	Cross Line Red Laser Bare Tool	249

Model	Article Nr.	Description	EUR
<b>3x360 Lasers</b>			
PLS 3X360R Z TOOL	5114111	Red three-plane laser, Bare Tool	281
PLS 3X360R KIT	5114127	Red three-plane laser, Kit	449
PLS 3X360G Z TOOL	5114148	Green three-plane laser, Bare Tool	349
PLS 3X360G KIT	5114153	Green three-plane laser, Kit	493
PLS HGI3X360R	5204916	PLS Housing Glass Insert for PLS 3X360R	24
PLS HGI3X360G	5214800	PLS Housing Glass Insert for PLS 3X360G	24
PLS 3X360 MLB	5214817	Magnetic L-Bracket w/ Micro and Elevation Adjustment	47
PLS 3X360 CB	5214821	Ceiling Bracket used w/ PLS 3X360MLB	25
PLS 3X360 HC	5221067	PLS 3X360 Blow Mold Hard Case	19
<b>Rotary lasers</b>			
<b>Horizontal rotary lasers</b>			
PLS H2 KIT	5022496	PLS H2 Red Rotary Laser Kit with Tripod and Grade Rod	1167
PLS H2 SYS	5022481	PLS H2 Red Rotary Laser System	907
PLS H2 Z	5022470	PLS H2 Red Rotary Laser Bare Tool	640
<b>Manual slope rotary lasers</b>			
PLS HV2G KIT	5022520	PLS HV2G Green Rotary Laser Kit	1556
PLS HV2G SYS	5022547	PLS HV2G Green Rotary Laser System with Detector	1301
PLS HV2G Z	5022535	PLS HV2G Green Rotary Laser Bare Tool	966
PLS HV2R KIT	5022558	PLS HV2R Red Rotary Laser Kit with Tripod and Grade Rod	1434
PLS HV2R SYS	5022512	PLS HV2R Red Rotary Laser System with Detector Laser Bare Tool	1167
PLS HV2R Z	5022501	PLS HV2R Red Rotary Laser Bare Tool	833
<b>Accessories</b>			
PLS BC20	5022618	Charging Cord for PLS RBP10	38
PLS BP10	5022599	Rotary Alkaline Battery for H2, HV2	52
PLS BP5	5031952	BP5 Alkaline Battery Pack	44
PLS C18	4985124	Laser Level Tool Box	86
PLS C19	5022586	Rotary Laser Carrying Case	74
PLS FS	5031929	Floor Stand for PLS 3, 5, 6	16
PLS GR16	5022652	Grade Rod with US and Metric	52
PLS GRT4	5022634	Green Magnetic Reflective Target	14
PLS MLB	5031934	Magnetic L-Bracket, PLS 3, 5, 6, 180	46
PLS RBC5	5031965	Charging cord with adapters for RBP5 Li-ion battery	14
PLS RBP10	5022607	Rechargeable Battery for H2, HV2	76
PLS RBP5	5023322	Li-ion battery for PLS hand held lasers with charging cord and adapters	68
PLS RBP5 SINGLE PK	5075484	Single pack RBP5 Li-ion battery for PLS line and dot lasers	57
PLS RC2	5022564	Rotary Laser Remote Control	63
PLS RRT4	5022629	Red Magnetic Reflective Target	14
PLS SLD GREEN	4978526	SLD Green Detector W/ Bracket	183
PLS SLD RED	4978515	SLD Red Detector W/ Bracket	168
PLS TPOD500	5022665	Elevating Tripod	286
PLS UB9	4966636	UB9 Universal Ceiling/Wall Bracket	95
PLS WCB10	5022641	Rotary Wall and Ceiling Mount	97
PLS XLD	5037696	Rotary Laser Detector with Clamp	215
PLS XLD CLAMP	5037709	Rotary Detector Clamp	38
PLS-21502	4919812	Tripod Extender PLS3/180	10
PLS-HGI180G	5067797	PLS 180G Replacement Window Glass Insert	25

Model	Article Nr.	Description	EUR
PLS-HGI180R	5042463	PLS 180R Replacement Window Glass Insert	25
PLS-HGI3G	5067760	PLS 3G Replacement Window Glass Insert	25
PLS-HGI3R	5042439	PLS 3R Replacement Window Glass Insert	25
PLS-HGI5G	5067772	Replacement Window Glass Insert PLS 5G	25
PLS-HGI5R	5042442	Replacement Window Glass Insert PLS 5R	25
PLS-HGI6G	5067785	Replacement Window Glass Insert PLS 6G	25
PLS-HGI6R	5042456	Replacement Window Glass Insert PLS 6R	25
<b>Distance Meters</b>			
FLUKE-417D	5099292	Laser Distance Measurer	108
FLUKE-417D/62MAX KIT	5112860	Fluke-417D/62Max Kit, 417D Laser Distance Meter and 62Max+ IR Thermometer	190
FLUKE-424D	4106866	Laser Distance Meter	425
<b>Battery Analyzers</b>			
<b>Battery Analyzers</b>			
FLUKE-BT510	4489970	Battery Analyzer	3217
FLUKE-BT520	4489981	Battery Analyzer	4089
FLUKE-BT520ANG	5104752	Battery Analyzer, with angled test probes	4972
FLUKE-BT521	4489996	Advanced Battery Analyzer	4480
FLUKE-BT521ANG	5104765	Advanced Battery Analyzer, with angled test probes	5419
<b>Battery Analyzer Accessories</b>			
BC500	4542299	AC Power Charger	146
BP500	4542300	Lithium-ion battery, 7.4V 3000 mAh	121
BT500-PROBE-TIP	4561297	Probe tip, 10x replacement Probe tips, 2x long probe tip covers, 2x short probe tip covers	146
BTL10	4542264	Standard Battery Analyzer Probes	390
BTL20	4542273	Intelligent Test Probe Set, w/Extenders (no temp sensor)	601
BTL20ANG	4969588	Interactive Battery Analyzer Test Probe with angled tip	795
BTL-A	4542258	Voltage/Current Probe Adapter	48
I410	617727	AC/DC Current Clamp (400 A)	308
<b>Insulation Testers</b>			
1587KIT/62MAX+ FC	4692778	2-IN-1 Advanced Electrical Troubleshooting Insulation Multi Kit with 62MAX+ I400	1063
FLUKE-1503	2427883	Insulation Tester	466
FLUKE-1507	2427890	Fluke 1507 Insulation resistance tester	579
FLUKE-1550C	3665021	Insulation Resistance Tester (5kV)	4634
FLUKE-1550C FC	4977402	Insulation Resistance Tester (5kV) with IR3000FC	4634
FLUKE-1550C FC KIT	4977457	Insulation Resistance Tester Kit (5kV) with IR3000FC	5108
FLUKE-1550C/KIT	3665127	Insulation Resistance Tester Kit (5kV)	5108
FLUKE-1555	3665056	Insulation Resistance Tester (10kV)	5108
FLUKE-1555 FC	4977519	Insulation Resistance Tester (10kV) with IR3000FC	5108
FLUKE-1555 FC KIT	4977469	Insulation Resistance Tester Kit (10kV) with IR3000FC	5580
FLUKE-1555/KIT	3665111	Insulation Resistance Tester Kit (10kV)	5580
FLUKE-1577	2157280	Insulation Multimeter	734
FLUKE-1587 FC	4691215	2-IN-1 Insulation Multimeter	885
FLUKE-1587 T	2517605	Insulation Multimeter (Telecom)	821
FLUKE-1587/I400 FC	4692725	2-IN-1 Insulation Multimeter with Clamp i400	944
FLUKE-1587/MDT FC	4692716	2-IN-1 Advanced Motor & Drive Troubleshooting Kit with 9040, I400	1180



Model	Article Nr.	Description	EUR
FLUKE-IR3000FC1550	4460451	Fluke ir3000 FC Connector	254
FVF-BASIC	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	183
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	302
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	58
<b>Installation Testers</b>			
ES165X	2104706	Earth Spike Test Kit	181
FLK-1662 UK	4546915	Installation Tester W/Mem Uk	1088
FLK-1664FC UK	4547031	Fc Installation Tester W/Insulation Pre-Test Uk	1716
FLK-166X-MTC-UK	4601070	Fluke 166X-Main Test Cord, Uk	63
FLK-DMS COMPL	4718790	DMS Complete, Installation, PAT Software	650
FLK-DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	865
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	302
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	58
TL165X	2107756	Standard Test Lead Set (1650 Series)	136
TP165X	2107742	Remote Control Probe (1650 Series)	98
ZERO ADAPTER	3261925	Zero adapter (165xB)	45
<b>Solar Testers</b>			
FLK-IRR1-SOL	5218288	Solar Irradiance Meter	329
<b>Portable Appliance Testers</b>			
110V-ADAPTER-KIT	4372377	110 V ADAPTER KIT, FLUKE-6500-2 UK	42
6200-2 UK KIT	4377198	Portable Appliance Tester, Kit, Uk	1332,8
6500-2 UK KIT	4377132	Portable Appliance Tester, Kit Uk	1608
APP1000	1992611	Barcode Appliance Number Labels 0-1000	153
APP2000	1992627	Barcode Appliance Number Labels 1001-2000	153
APP3000	1992630	Barcode Appliance Number Labels 2001-3000	153
APP4000	1992648	Barcode Appliance Number Labels 3001-4000	153
AUTO200B	2141221	Auto Code Label	53
BDST3	2796907	Snap Tag (cable tie)	45
BDST4	2796918	Snap Tag (clip on)	45
EXTL100	2414348	Extension Lead Test Adaptor	20
FLK-DMS COMPL	4718790	DMS Complete, Installation, PAT Software	650
FLK-DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	865
FLUKE-6200-2 UK	4324466	Portable Appliance Tester Uk	1406
FLUKE-6500-2 UK	4324475	Portable Appliance Tester UK	1644
IRP1	1993496	Pat Register	17
PASS 500S	2141138	Appliance Pass Labels (Rectangular)	46
PASS 560R	2141192	Appliance Pass Labels (Round)	94
SP6000 PRINTER	4325128	Printer for Portable Appliance Testers	707
SPSCAN6000	4325143	Scanner for Portable Appliance Testers	447
TA700	2389678	Appliance Adaptor For 110V Tools	47
<b>Earth Ground Testers</b>			
C1620	4359042	Carrying Case	234
CABLE REEL 25M BL	4343731	25M Blue, Ground/Earth Cable Reel, 25M Wire	76
CABLE REEL 25M GR	4343746	25M Green, Ground/Earth Cable Reel, 25M Wire	76
CABLE REEL 50M RD	4343754	50M Red, Ground/Earth Cable Reel, 50M Wire	85
EARTH STAKE	4325492	Geo Earth Ground Tester, Earth stake	76
EI-1623	2577115	Stakeless Clamp Set For 1623,Consists of EI-162X and EI-162AC	813



Model	Article Nr.	Description	EUR
EI-1625	2577126	Stakeless Clamp Set,With EI-162X,EI-162AC and 2-3 Wire Cable	972
EI-162BN	2577159	12.7 Inch (320mm) split core transformer	2437
ES-162P3-2	4359377	Earth Ground Stake Set for 3 Pole Measurement	292
ES-162P4-2	4359389	Earth Ground Stake Set for 4 Pole Measurement	425
FLUKE-1623-2	4325155	Basic Geo Earth Ground Tester	1644
FLUKE-1623-2 KIT	4325170	Basic Geo Earth Ground Tester, Kit	2803
FLUKE-1625-2	4325162	Advanced Geo Earth Ground Tester	2741
FLUKE-1625-2 KIT	4325181	Advanced Geo Earth Ground Tester, Kit	4022
FLUKE-1630-2	4829515	Earth Ground Loop and Leakage Clamp (non FC)	1672
FLUKE-1630-2 FC	4829532	Earth Ground Loop and Leakage Clamp	1672
<b>Indoor Air Quality Tools</b>			
FLUKE-922	2679822	Airflow Meter	779
FLUKE-922/KIT	2679831	Airflow Meter Kit	907
FLUKE-971	2418208	Temperature Humidity Meter	311
FLUKE-985	4131397	Airborne Particle Counter	5113
FLUKE-CO-205	664714	Aspirator Kit	218
FLUKE-CO-220	664711	Carbon Monoxide Meter	648
PT12	2740212	Pitot Tube, 12	142
RLD2	3387163	Leak Detector Flashlight	64
<b>Digital Thermometers</b>			
8OPR-60	2148313	RTD Temperature Probe (Fluke 66/68)	89
FL62MAX+/323/1AC	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	289
FLUKE-116/62 MAX+	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	348
FLUKE-51-2 50HZ	1281142	Thermometer	365
FLUKE-52-2 50HZ	1281139	Thermometer	462
FLUKE-53-2 B 50HZ	3821096	Single Input Thermometer, 50Hz	526
FLUKE-53-2 B 60HZ	3821062	Single Input Thermometer, 60Hz	526
FLUKE-54-2 B 50HZ	3821081	Dual Input Thermometer, 50Hz	645
FLUKE-54-2 B 60HZ	3821070	Dual Input Thermometer, 60Hz	645
FLUKE-561	2558118	Multipurpose Thermometer	170
FLUKE-566	2837799	Multipurpose Thermometer	473
FLUKE-568	2837806	Multipurpose Thermometer	591
FLUKE-568EX	4321662	Intrinsically safe Infrared Thermometer	1463
FLUKE-572-2	4328074	Infrared Thermometer	699
FLUKE-62 MAX	4130474	Infrared thermometer	106
FLUKE-62 MAX +	4130488	Infrared Thermometer	123
FLUKE-64 MAX	4856105	Multifunction IR Thermometer 20:1 D:S	158
FLUKE-PP	2477945	Foodpro Infrared Food Thermometer	129
T5-600/62MAX+/1ACE	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	292
<b>Industrial Imaging</b>			
EDBC290	5077735	EDBC290, EXTERNAL DUAL BAY CHARGER W/ POWER ADAPTER & CONNECTORS	423
FLK-3.8MM/1M PROBE	4962690	3.8 mm Scope, 1 m Probe, Forward View	766
FLK-5.5MM/1M PROBE	4962713	5.5 mm Scope, 1 m Probe, Dual View	553
FLK-8.5MM/1.2M PROBE	4962749	8.5 mm Scope, 1.2 m Probe, Dual View	223
FLK-8.5MM/1M UVPROBE	4962751	8.5 mm UV Scope, 1 m Probe, Dual View	766
FLK-8.5MM/3M PROBE	4962708	8.5 mm Scope, 3 m Probe, Dual View	659

Model	Article Nr.	Description	EUR
FLK-9MM/20M PROBE	4962760	9 mm Scope, Forward View, 20 m Probe Reel	2194
FLK-DS NECK STRAP	4962772	DS 7XX Neckstrap	52
FLK-DS701	4962652	Diagnostic Videoscope	1865
FLK-DS703 FC	4962665	High Resolution Diagnostic Videoscope with FC	2194
FLK-II900	5075603	Fluke ii900 Sonic Industrial Imager	17989
FLK-II900 ARRAY CVRS	5075982	FLK-II900 ARRAY CVRS, REPL. ARRAY COVERS FLKII900 SONIC INDUSTRIAL IMAGER,SET OF 2	74
FLK-II900 HAND STRAP	5075994	FLK-II900 HAND STRAP,REPL. HAND STRAP FLKII900 SONIC INDUSTRIAL IMAGER	31
FLK-II910	5233904	ii910 Precision Acoustic Imager	21419
<b>Thermal Imagers</b>			
<b>Handheld thermal cameras</b>			
FLK-PTI120 9HZ	5074148	Fluke PTi120 Pocket Thermal Imager; 120x90; 9HZ	769
FLK-PTI120 9HZ 400C	5302512	Fluke PTi120 Pocket Thermal Imager; 120x90; 9HZ; 400C	769
FLK-TIS20+ 9HZ	5124518	Fluke TiS20+ Thermal Imager; 120x90; 9HZ	1299
FLK-TIS20+ MAX 9HZ	5206249	Fluke TiS20+ MAX Thermal Imager; 120x90; 9HZ	1499
FLK-TIS55+ 27HZ	5160004	Fluke TiS55+ Thermal Camera 27HZ	2699
FLK-TIS55+ 9HZ	5159990	Fluke TiS55+ Thermal Camera 9HZ	2699
<b>High resolution thermal cameras</b>			
FLK-TI300+ 60HZ	5127961	Thermal Imager Ti300+	5999
FLK-TI300+ 9HZ	5127977	Fluke Ti300+ Thermal Camera	5999
FLK-TI401-PRO 60HZ	5085041	Fluke Ti401 PRO Thermal Imager; 640x480; 60HZ	7999
FLK-TI401-PRO 9HZ	5085052	Fluke Ti401 PRO Thermal Imager; 640x480; 9HZ	7999
FLK-TI480-PRO 60HZ	4947326	Fluke Ti480 PRO 60Hz Thermal Imager	10499
FLK-TI480-PRO 9HZ	4947332	Fluke Ti480 PRO 9Hz Thermal Imager	10499
FLK-TIS60+ 30HZ	5133399	Fluke TiS60+ Infrared Camera 30Hz	3299
FLK-TIS60+ 9HZ	5133402	Fluke TiS60+ Infrared Camera 9Hz	3299
FLK-TIS75+ 27HZ	5160043	Fluke TiS75+ Thermal Camera 27HZ	4499
FLK-TIS75+ 9HZ	5160037	Fluke TiS75+ Thermal Camera 9HZ	4499
FLK-TIX501 60HZ	5085119	Fluke TiX501 Thermal Imager; 640x480; 60HZ	11499
FLK-TIX501 9HZ	5085128	Fluke TiX501 Thermal Imager; 640x480; 9HZ	11499
FLK-TIX580 60HZ	4842073	Thermal Imager; 640x480; 60 HZ, SR	13999
FLK-TIX580 9HZ	4841945	Thermal Imager; 640x480; 9 HZ, SR	13999
<b>High definition mounted thermal cameras</b>			
FLK-0.75X-WIDE-LENS	4961174	Wide Angle Infrared Lens	1118
FLK-2X- LENS	4961163	2x Telephoto Infrared Smart Lens	2237
FLK-4X-LENS	4961188	4x Telephoto Infrared Smart Lens	5009
FLK-RSE300 60HZ	4944776	Thermal Imager; 320x240; 60 Hz	11709
FLK-RSE300 9HZ	4948166	Thermal Imager; 320x240; 9 Hz	11709
FLK-RSE600 60HZ	4944826	Thermal Imager; 640x480; 60 Hz	16639
FLK-RSE600 9HZ	4948175	Thermal Imager; 640x480; 9 Hz	16639
FLK-RSE-MB	4961344	Fluke Infrared Camera Mounting Bracket	137
FLK-RSE-ST	4973844	Infrared Camera Mounting Stand	148
<b>Thermal Imagers Accessories (general)</b>			
FLK-LENS/25MAC2	4607064	25Micron Macro IR lens for TiX560-TiX520	4647
FLK-LENS/4XTELE2	4607058	4x Telephoto IR lens for TiX560-TiX520-Ti400-Ti300-Ti200	6427
FLK-LENS/TELE2	4335350	Telephoto Infrared Lens (Ti200/Ti300/Ti400)	1416

Model	Article Nr.	Description	EUR
FLK-LENS/WIDE2	4335361	Wide-angle Infrared Lens (Ti200/Ti300/Ti400)	1416
FLK-MACRO-LENS	4961195	Macro Infrared Lens	3357
FLK-TI-BLUETOOTH	4603258	Bluetooth headset	84
FLK-TI-SBC3B	4354922	Charging base (Ti200/Ti300/Ti400)	196
FLK-TI-SBP3	3440365	Extra battery (Ti32/TiR32)	152
FLK-TI-TRIPOD2	3996517	Mounting Base	105
FLK-TI-TRIPOD3	4335389	Tripod mounting base accessory	105
FLK-TI-VISOR2	3996500	Sun Visor	84
FLK-TI-VISOR3	4335377	Thermal imager visor	84
FLK-TIX5X-LENS CAP	4550697	Lens cap	17
FLUKE-TIX5XX HAND	4574703	Adjustable hand strap	17
FLUKE-TIX5XX-HDMI	4615511	HDMI video cable	20
FLUKE-TIX5XX-NECK	4574715	Adjustable neck strap	33
FLUKE-TIX5XX-SBP4	4597142	Additional Smart Battery	137
TI20-RBP	2577796	Rechargeable Battery Pack (Ti20)	190
TI-CAR CHARGER	3039779	Ti Car Charger (TiR/TiR1/Ti10/Ti20/Ti25)	137
TI-TRIPOD	3511872	Tripod Mounting Base	120
<b>Thermal Imagers IR-Windows</b>			
FLK-050-CLKT	3460346	50mm C-Range IR Windows, Kwik twist	185
FLK-075-CLKT	3460387	75 mm C-Range IR Window, Kwik Twist	252
FLK-100-CLKT	3460439	100mm C-Range IR Window, Kwik Twist	339
FLUKE-CV200	4326955	50mm IR Window, hand turn door latch	239
FLUKE-CV300	4326962	75mm IR Windows, hand turn door latch	328
FLUKE-CV301	4338164	75mm IR Windows, security turn door latch	351
FLUKE-CV400	4326996	100 mm IR Windows, hand turn door latch	460
FLUKE-CV401	4338173	100 mm IR Windows, security turn door latch	460
<b>ScopeMeters</b>			
<b>Industrial ScopeMeter</b>			
FLUKE-123B/EU	4755659	Industrial ScopeMeter 20MHZ, EU	1713
FLUKE-123B/EU/S	4755890	Industrial ScopeMeter + SCC 20MHZ, EU	2170
FLUKE-123B/INT	4755710	Industrial ScopeMeter 20MHZ, INT	1713
FLUKE-123B/INT/S	4755953	Industrial ScopeMeter + SCC 20MHZ, INT	2170
FLUKE-123B/UK	4755671	Industrial Scopemeter 20Mhz, Uk	1713
FLUKE-123B/UK/S	4755911	Industrial Scopemeter + Scc 20Mhz, Uk	2170
FLUKE-124B/EU	4755731	Industrial ScopeMeter 40MHZ, EU	2056
FLUKE-124B/EU/S	4755975	Industrial ScopeMeter + SCC 40MHZ, EU	2513
FLUKE-124B/INT	4755793	Industrial ScopeMeter 40MHZ, INT	2056
FLUKE-124B/INT/S	4756031	Industrial ScopeMeter + SCC 40MHZ, INT	2513
FLUKE-124B/UK	4755754	Industrial Scopemeter 40Mhz, Uk	2056
FLUKE-124B/UK/S	4755994	Industrial Scopemeter + Scc 40Mhz, Uk	2513
FLUKE-125B/EU	4755818	Industrial ScopeMeter 40MHZ, EU	2454
FLUKE-125B/EU/S	4756054	Industrial ScopeMeter + SCC 40MHZ, EU	2913
FLUKE-125B/INT	4755876	Industrial ScopeMeter 40MHZ, INT	2454
FLUKE-125B/INT/S	4756112	Industrial ScopeMeter + SCC 40MHZ, INT	2913
FLUKE-125B/UK	4755834	Industrial Scopemeter 40Mhz, Uk	2454
FLUKE-125B/UK/S	4756079	Industrial Scopemeter + Scc 40Mhz, Uk	2913

Model	Article Nr.	Description	EUR
<b>190 Series ScopeMeters</b>			
FLUKE-190-062-III	5282331	ScopeMeter 190-062-III Test Tool	3176
FLUKE-190-062-III-S	5282354	ScopeMeter 190-062-III/S Test Tool with kit	3623
FLUKE-190-102-III	5282368	ScopeMeter 190-102-III Test Tool	3907
FLUKE-190-102-III-S	5282379	ScopeMeter 190-102-III/S Test Tool with kit	4356
FLUKE-190-104-III	5282393	ScopeMeter 190-104-III Test Tool	4398
FLUKE-190-104-III-S	5282417	ScopeMeter 190-104-III/S Test Tool with kit	4846
FLUKE-190-202-III	5282439	ScopeMeter 190-202-III Test Tool	4409
FLUKE-190-202-III-S	5282442	ScopeMeter 190-202-III/S Test Tool with kit	4859
FLUKE-190-204-III	5282463	ScopeMeter 190-204-III Test Tool	5032
FLUKE-190-204-III-S	5282474	ScopeMeter 190-204-III/S Test Tool with kit	5480
FLUKE-190-502-III	5282495	ScopeMeter 190-502-III Test Tool	5431
FLUKE-190-502-III-S	5282508	ScopeMeter 190-502-III/S Test Tool with kit	5881
FLUKE-190-504-III	5282513	ScopeMeter 190-504-III Test Tool	5630
FLUKE-190-504-III-S	5282524	ScopeMeter 190-504-III/S Test Tool with kit	6079
<b>Motor Drive Analyzers</b>			
FLUKE-MDA-550-III	5282560	MDA-550 Motor Drive Analyzer	7194
SB-500	5011046	Shaft brushes set, repl brushes for SVS-500 and MDA-500	287
SVS-500	5011031	Shaft voltage set and magnetic base	383
<b>ScopeMeter Accessories</b>			
AC120	646163	Heavy Duty Alligator Clips	52
AS400	3894880	Probe Extension Set, for VPS400 Probes	124
BB120	646171	Banana to BNC Adapter Plug	57
BC190/830	4821057	Fluke BC190/830 Universal Mains-Power Adapter	207
BHT190	3379374	Set of Break-out Adapters	405
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	113
BP190	677390	NiMH Battery Pack (190 Series)	227
BP290	4025762	Battery Pack Single Cap 190-series II	268
BP291	3894688	Battery Pack, Fluke 190 Series	376
C120	646189	Hard Case (43B/120 Series)	123
C120B	4744391	Soft carrying case for 120B series	155
C125	646858	Soft Meter Case	57
C190	677401	Hard Case (190 Series)	289
C195	677408	Soft Case	267
C290	3894803	Hard-Shell Carrying Case	241
CS20MA	677393	Current Shunt 4-20 mA	111
EBC290	3894906	External Battery Charger	119
HC120	646668	Hook Clips	66
HC200	2086410	Hook Clips	46
HH290	3894844	Hanging Hook, ScopeMeter Series 190 II	85
MA190	1567481	Medical Accessory Kit (190 Series)	511
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	183
PM9080/101	1641983	Serial Interface Adapter/Cable (RS232)	305
PM9081/001	916093	Dual Banana Plug to Female BNC Adapter	58
PM9082/001	916163	Dual Banana Jack to Male BNC Adapter	58
PM9091/001	935598	Coaxial BNC Cables (1.5 m)	137
PM9092/001	935601	Coaxial BNC Cables (0.5 m)	119

Model	Article Nr.	Description	EUR
PM9093/001	935593	Male BNC to Female BNC Adapter	80
PM9096/201	651742	Secondary Pick-up	380
RS120-III	4023947	Probe Accessory Replacement Set	124
RS400	3894867	Probe Replacement Set, for VPS400 Probes	99
RS500	4025886	Probe accessory replacement set for VPS500 probes	177
SCC 128	2100199	Automotive Accessory Kit (120 Series)	814
SCC 198	2100208	Automotive Accessory Kit (190 Series)	1024
SCC120B	4744423	Software soft carry case accessory kit 120B series	571
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	524
SCC190EFG	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	734
SCC290	3894826	Software and Carrying Case for 190 Series II	447
SCC298	4138312	Automotive troubleshooting Kit 190-Series-II	1088
SP120B	4744414	Screen protector for 120B series	51
STL120-III	4023901	Shielded Test Lead	217
STL120-IV	4744340	Shielded test lead set 600V CAT IV	182
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	284
SW90W	3894923	FlukeView Software	406
TAS90	614187	Automotive Accessory Set (120/190 Series)	80
TRM50	4025864	50 Ohm feed-through terminator BNC	213
UA120	4744384	USB Connector adapter	51
VPS101	3086317	1:1 Voltage Probe Set, black, 30 MHz, 1.2m	248
VPS210-G	3086247	10:1 Voltage Probe Set, grey, 200 MHz, 1.2m	248
VPS210-R	3086235	10:1 Voltage Probe Set, 1 red, 200 MHz, 1.2m	248
VPS212-G	3086286	10:1 Voltage Probe Set, grey, 200 MHz, 2.5m	248
VPS212-R	3086273	10:1 Voltage Probe Set, red, 200 MHz, 2.5m	248
VPS220-G	3086300	100:1 Voltage Probe Set, grey, 200 MHz, 1.2m	248
VPS220-R	3086299	100:1 Voltage Probe Set, red, 200 MHz, 1.2m	248
VPS40-III	4023920	Voltage Probe	144
VPS41	4744378	Voltage probe set 40 MHz 600V CAT IV	177
VPS410-II-B	4276937	Industrial Voltage Probe Set 500 MHz 10:1 Blue	235
VPS410-II-G	4276943	Industrial Voltage Probe Set 500 MHz 10:1 Grey	235
VPS410-II-R	4276928	Industrial Voltage Probe Set 500 MHz 10:1 Red	235
VPS410-II-V	4276955	Industrial Voltage Probe Set 500 MHz 10:1 Green	235
VPS420-V	4411583	High Working Voltage Ruggedized Probe; Green/Black	275
VPS510-B	4025796	Voltage probe set 500 MHZ 10:1 Blue	235
VPS510-G	4025801	Voltage probe set 500 MHZ 10:1 Grey	235
VPS510-R	4025781	Voltage Probe set 500 MHZ 10:1 Red	235
VPS510-V	4025812	Voltage probe set 500 MHZ 10:1 Green	235
<b>Power Quality Tools</b>			
1742-6/UPGRADE	4920964	1742 to 1746 Upgrade	1967
1742-8/UPGRADE	4920973	1742 to 1748 Upgrade	3636
1746-8/UPGRADE	4920986	1746 to 1748 Upgrade	1967
C1740	4116762	Softcase for 174X and 43X-II PQ analyzer	237
C437-II	4116743	Hard case 430 Series II with rollers	572
EPE-TRAINING-E/EMEA	4792349	Fluke EPE Training Set - English	204
FLUKE-1732/B	4706566	Energy Logger, basic version	2421
FLUKE-1732/EUS	4706548	Energy Logger, EU/US version	2699

Model	Article Nr.	Description	EUR
FLUKE-1732/INTL	4706553	Energy Logger, international version	2699
FLUKE-1734/B	4706582	Energy Logger, advanced version no flexis	2751
FLUKE-1734/EUS	4706594	Energy Logger, EU/US advanced version	3025
FLUKE-1734/INTL	4706608	Energy Logger, international advanced version	3025
FLUKE-1736/B	4563561	3-Phase Poser Logger, basic version	4272
FLUKE-1736/EUS	4534519	3-Phase Power Logger, EU/US version	4283
FLUKE-1736/INTL	4563550	3-Phase Power Logger, International version	4283
FLUKE-1738/B	4588378	3-Phase Power Logger, advanced version no flexis	4401
FLUKE-1738/EUS	4563577	3-Phase Power Logger, EU/US Advanced version no flexis	4947
FLUKE-1738/INTL	4588384	3-Phase Power Logger, international advanced version	4947
FLUKE-1742/15/EUS	4920613	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	4019
FLUKE-1742/15/INTL	4920672	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	4019
FLUKE-1742/30/EUS	4920651	Power Quality Logger with 60 cm 3,000A iflex, EUS version	4019
FLUKE-1742/30/INTL	4920685	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	4019
FLUKE-1742/B/EUS	4920660	Power Quality Logger without iFlex, EUS version	3676
FLUKE-1742/B/INTL	4920697	Power Quality Logger without iFlex, INTL version	3676
FLUKE-1746/15/EUS	4920703	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	5521
FLUKE-1746/15/INTL	4920732	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	5521
FLUKE-1746/30/EUS	4920715	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	5521
FLUKE-1746/30/INTL	4920744	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	5521
FLUKE-1746/B/EUS	4920726	Power Quality Logger without iFlex, EUS version	5170
FLUKE-1746/B/INTL	4920759	Power Quality Logger without iFlex, INTL version	5170
FLUKE-1748/15/EUS	4920767	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	6914
FLUKE-1748/15/INTL	4920798	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	6914
FLUKE-1748/30/EUS	4920771	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	6914
FLUKE-1748/30/INTL	4920800	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	6914
FLUKE-1748/B/EUS	4920780	Power Quality Logger without iFlex, EUS version	6586
FLUKE-1748/B/INTL	4920817	Power Quality Logger without iFlex, INTL version	6586
FLUKE-1760 BASIC	2630732	Power Quality Recorder (three-phase), Topas	13361
FLUKE-1760 INTL	2630744	Power Quality Recorder (three-phase), Topas	15481
FLUKE-1760 TR INTL	2637634	Power Quality Recorder (three-phase), Topas	20427
FLUKE-1760TR BASIC	2637629	Power Quality Recorder (three-phase), Topas	18310
FLUKE-430-II/MA	4779032	430-II Motor Analyzer Upgrade Kit	2340
FLUKE-435-II	4116661	Power Quality& Energy Analyzer	6949
FLUKE-435-II/BASIC	4116689	Advanced Power Quality and energy analyzer (w/o clamps)	6252
FLUKE-435-II/INTL	4778929	Power Quality and energy analyzer/International	6949
FLUKE-437-II	4116692	Power Quality& Energy Analyzer	9167
FLUKE-437-II/BASIC	4116719	400 Hz Power Quality and Energy Analyzer (w/o clamps)	8479
FLUKE-437-II/INTL	4778934	Power Quality and energy analyzer/International	9167
FLUKE-438-II	4778976	Power Quality & Motor Analyzer	8192
FLUKE-438-II/BASIC	4778990	Power Quality & Motor Analyzer, without clamps and FC WiFi SD Card	7484
FLUKE-438-II/INTL	4779015	Power Quality & Motor Analyzer, without FC WiFi SD Card	8192
FLUKE-VR1710	3030923	Single-Phase Voltage Quality Recorder	986
<b>Power Quality Tools Accessories</b>			
314OR	2650136	Clip-on Current Transformer 2A-400A (Fluke 1750)	452
3210-PR-TF-II	4531769	1000A Fluke 1750 Thin flexi 61cm	702
3310-PR-TF-II	4531778	5000A Fluke 1750 Thin flexi 61cm	938



Model	Article Nr.	Description	EUR
3312-PR-TF-II	4531784	5000A Fluke 1750 Thin flexi 122cm	1154
3PHVL-17XX	5014802	3PHVL-17XX,CABLE ASSEMBLY, VOLTAGE TEST LEAD 3-PHASE+N	98
3PHVL-17XX-5M	5014816	3PHVL-17XX-5M,CABLE ASSEMBLY, VOLTAGE TEST LEAD 3-PHASE+N 5M	137
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	113
BP1730-BATTERY	4389436	Li Ion Battery Pack 3.7V 2500mAh (1730)	44
C120	646189	Hard Case (43B/120 Series)	123
C17XX	4637381	Soft Case	130
CS1750/1760	2673962	Soft Case (Fluke 1750/1760)	288
DEMO PQ CASE	4483703	Fluke Power Quality Democase	2195
FLK-174X_3541-HANGER	4890129	Hanger Kit	69
FLUKE MA-C8	4945842	Wall outlet adapter, Fluke-174X	23
FLUKE-1730-CABLE	4395217	Cable,AUX input cable (1730)	33
FLUKE-1730-HANGER	4358028	Hanger kit (1730)	63
FLUKE-174X GPS-REC	4921133	GPS Receiver Antenna	374
FLUKE-174X-8066	4921140	Cable Marker set, 05MM	58
FLUKE-1750/CASE	2650124	Hard Case (Fluke 1750)	621
FLUKE-1750/SEAT-L	2673937	Fluke Power Analyze - Additional SEAT LICENSE	1227
FLUKE-1750/SITE-L	2673928	Fluke Power Analyze - Additional SITE LICENCE	6139
FLUKE-17XX AUX	4717827	AUX input adapter, 173X	151
FLUKE-17XX-TL	5016873	FLUKE-17XX-TL,TEST LEAD SET; 1000V CAT III, NONSTACK/STACK 0.18M	39
FLUKE-17XX-TL 2M	5020006	FLUKE-17XX-TL 2M,BLUE, NON-STACKABLE PLUG AND 2X ALLIGATOR CLIPS	30
FLUKE-PQ400	4920947	Electrical Measurement Window with 4 x male-male cable 2m	1859
FLUKE-PQ400/B	5075807	Basic Electrical Measurement Window without accessories	1467
FLUKE-PQ-MARKER	5046009	Cable marker set 3P+N+PE	10
FS17X5-TF-II	4531791	3000A 4-PH Fluke 1735 & 1745 Thin flexi set	1808
FS17XX IP65-TF-II	4531804	3000A IP65 4-PH Fluke 1743/4 Thin flexi set	2118
FS17XX-1PH-TF-II	4531819	FS3000A/6000A 4-PH 36-Inch Thin flexi set	456
FS3KA/6KA-TF-4-II	4531828	FS3000A/6000A 4-PH 36-Inch thin flexi set	1759
FTP17XXPQ	4954311	Fused test probes set, Three Phase PQ, AC285, R/B	175
GPS430-II	4693803	GPS Synchronization module (430-II series)	1683
GPS-TIME SYNC	2539223	GPS Time Synchronization Module (Fluke 1760)	482
I17XX-BNC-M2F	5076304	4 pin male to BNC female cable 0.1m (1 piece)	98
I17XX-BNC-M2M	5076297	4 pin male to BNC male cable 2m (1 piece)	98
I17XX-FLEX1.5KIP	4921003	IP65 iFlexi 1.5KA 60 cm	244
I17XX-FLEX1.5KIP/3PK	4921015	IP65 iFlexi 1.5KA 60 cm, 3 Pack	581
I17XX-FLEX1.5KIP/4PK	4921026	IP65 iFlexi 1.5KA 60 cm, 4 Pack	775
I17XX-FLEX1500	4637328	Fluke-17xx iFlexi 1500A 12 IN	185
I17XX-FLEX1500/3PK	4637337	Fluke-17xx iFlexi 1500A 12 IN, 3 pack	539
I17XX-FLEX1500/4PK	4637411	Fluke-17xx iFlexi 1500A 12 IN, 4 Pack	702
I17XX-FLEX2M-M2M1P	5076285	iFlex® male-male cable 2m, (1 piece)	147
I17XX-FLEX2M-M2M4P	5076272	iFlex® male-male cable 2m, (4 pieces)	564
I17XX-FLEX3000	4637343	Fluke-17xx iFlexi 3000A 24 IN	200
I17XX-FLEX3000/3PK	4637355	Fluke-17xx iFlexi 3000A 24 IN, 3 pack	573
I17XX-FLEX3000/4PK	4637427	Fluke-17xx iFlexi 3000A 24 IN, 4 Pack	750
I17XX-FLEX3KIP	4921032	IP65 iFlexi 3KA 60 cm	244
I17XX-FLEX3KIP/3PK	4921044	IP65 iFlexi 3KA 60 cm, 3 Pack	581
I17XX-FLEX3KIP/4PK	4921067	IP65 iFlexi 3KA 60 cm, 4 Pack	775



Model	Article Nr.	Description	EUR
I17XX-FLEX5M-EXT	4921116	iFlexi Extension Cable, 5m	146
I17XX-FLEX6000	4637362	Fluke-17xx iFlexi 6000A 36 IN	211
I17XX-FLEX6000/3PK	4637370	Fluke-17xx iFlexi 6000A 36 IN, 3 pack	609
I17XX-FLEX6000/4PK	4637430	Fluke-17xx iFlexi 6000A 36 IN, 4 Pack	797
I17XX-FLEX6KIP	4921071	IP65 iFlexi 6KA 90 cm	290
I17XX-FLEX6KIP/3PK	4921080	iFlexi 6KA 90 cm, 3 Pack	677
I17XX-FLEX6KIP/4PK	4921098	iFlexi 6KA 90 cm, 4 Pack	870
I1A/10A CLAMP PQ1	3345753	1-phase Mini Current Clamp Set	528
I1A/10A CLAMP PQ3	3024413	3-phase Mini Current Clamp Set	648
I1A/10A CLAMP PQ4	3024424	4-phase Mini Current Clamp Set	857
I20/200A CLAMP PQ3	3024451	3-phase Mini Current Clamp Set	648
I20/200A CLAMP PQ4	3024460	4-phase Mini Current Clamp Set	857
I400	2277225	AC Current Clamp (400 A)	186
I400S	2277202	AC Current Clamp (400A)	332
I40S-EL3X	4637396	Fluke-17xx i40s-EL Clamp-on Current Transformer	238
I40S-EL3X/3PK	4637409	Fluke-17xxx i40s-EL Clamp-on Current Transformer, 3 pack	667
I430-FLEXI-TF-II	4531725	6000A Fluke 430 Thin Flexi 61cm	465
I430-FLEXI-TFII-4P	4531733	6000A Fluke 430 Thin Flexi 61cm 4 Pack	1413
I430-FLX-TFII-12	4621205	Iflex 6000A probe, 12 "(30cm)	477
I430-FLX-TFII-48	4621231	Iflex 6000A probe, 48 "(122cm)	596
I5A/50A CLAMP PQ1	3345766	1-Phase 5A/50A Mini Current Clamp set for PQ	528
I5A/50A CLAMP PQ3	3024436	3-phase Mini Current Clamp Set	648
I5A/50A CLAMP PQ4	3024449	4-phase Mini Current Clamp Set	857
I5S	2508467	AC Current Clamp (5 A)	617
I5SPQ3	2457508	AC Current Clamp (5 A), 3-pack	1481
I5S-PR	3949761	1750, 5A Current Clamp	362
IEEE519/REPORT	4589748	SOFTWARE LICENSE FOR IEEE519 REPORTING	585
IP65 ADAPTER SET	4946241	IP65 rated Voltage Connector	244
MBX USB-RS232	2539565	EPO328Z, USB to Serial RS232 Adapter	66
MP1-3R/1B	4944790	3 red/1 black Magnet probe for 4 mm banana	104
MP1-MAGNET PROBE 1	4589220	Magnet probes for 4 mm banana, set of 4	104
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	183
PM9080/101	1641983	Serial Interface Adapter/Cable (RS232)	305
TLS430	2157713	Test Leads and Alligator Clips (4 black, 1 green) - 430 Series	151
TPS CLAMP 10A/1A	2540445	Clip-on Current Transformer 10A/1A (Fluke 1760)	494
TPS CLAMP 200/20	2540450	Clip-on Current Transformer 200A/20A (Fluke 1760)	494
TPS CLAMP 50A/5A	2540461	Clip-on Current Transformer 50A/5A (Fluke 1760)	494
TPS FLEX 18-TF-II	4531837	100/500A Fluke 1760 Thin Flexi 45cm (18in)	516
TPS FLEX 24-TF-II	4531843	200/1000A Fluke 1760 Thin Flexi 61cm (24in)	516
TPS FLEX 36-TF-II	4531855	3000/6000A Fluke 1760 Thin Flexi 91cm (36in)	1010
TPS SHUNT 1A	2540548	A680501054, Shunt 1 A AC/DC	439
TPS SHUNT 20MA	2540553	Shunt 20mA AC/DC (Fluke 1760)	439
TPS VOLTPROBE 100V	2540624	Voltage Probe 100V (Fluke 1760)	384
TPS VOLTPROBE 10V	2540636	Voltage Probe 10V (Fluke 1760)	384
TPS VOLTPROBE 1KV	2540649	Voltage Probe 1000V (Fluke 1760)	658
TPS VOLTPROBE 400V	2540660	Voltage Probe 400V (Fluke 1760)	384
TPS VOLTPROBE 600V	2540697	Voltage Probe 600V (Fluke 1760)	384

Model	Article Nr.	Description	EUR
TPS/MBX DOLPH RED	2540744	EPO326Z, Dolphin Clip, Red	45
VL1735/45	3276205	Banana 4-Phase Voltage Lead set for Fluke-1735/45	275
<b>Power Analyzers</b>			
<b>Norma 4000</b>			
FLUKE-N4K 1PP42	3108534	1 PH N4k power analyzer w/42	6427
FLUKE-N4K 2PP42I	3387174	2 PH N4K Power Analyzer w/42/IFC2	8567
FLUKE-N4K 3PP42	3108541	3 PH N4k power analyzer w/42	11053
FLUKE-N4K 3PP42B	3110957	3 PH N4k power analyzer w/42BP	12281
FLUKE-N4K 3PP42I	3108552	3 PH N4k power analyzer w/42/IFC2	13221
FLUKE-N4K 3PP42IB	3110969	3 PH N4k power analyzer w/42BP/IFC2	14422
FLUKE-N4K 3PP42IP	3108565	3 PH N4k power analyzer w/42/IFC2 & P11	15707
FLUKE-N4K 3PP42IPB	3110978	3 PH N4k power analyzer w/42BP/IFC2 & P11	17278
FLUKE-N4K 3PP50	3108576	3 PH N4k power analyzer w/50	17278
FLUKE-N4K 3PP50I	3108583	3 PH N4k power analyzer w/50/IFC2	19420
FLUKE-N4K 3PP50IP	3108590	3 PH N4k power analyzer w/50/IFC2 & P11	21945
FLUKE-N4K 3PP52IB	3312894	3 PH N4k power analyzer w/52BP/IFC2	24053
FLUKE-N4K 3PP54I	3108601	3 PH N4k power analyzer w/54/IFC2	17921
FLUKE-N4K 3PP54IP	3108612	3 PH N4k power analyzer w/54/IFC2 & P11	20468
<b>Norma 5000</b>			
FLUKE-N5K 3PP50	3108620	3 PH N5k power analyzer w/50	21664
FLUKE-N5K 3PP50I	3108635	3 PH N5k power analyzer w/50/IFC2	23773
FLUKE-N5K 3PP50IP	3108647	3 PH N5k power analyzer w/50/IFC2 & P11	26584
FLUKE-N5K 3PP50IR	3387195	3PH N5K PowerAnalyzer w/50/IFC2/PRNTR	25319
FLUKE-N5K 3PP54	3108658	3 PH N5k power analyzer w/54	20258
FLUKE-N5K 3PP54I	3108664	3 PH N5k power analyzer w/54/IFC2	22367
FLUKE-N5K 3PP54IP	3108673	3 PH N5k power analyzer w/54/IFC2 & P11	25178
FLUKE-N5K 3PP54IR	3312941	3 PH N5K power analyzer w/54/IFC2/printer	23915
FLUKE-N5K 3PP54R	3312934	3 PH N5K power analyzer w/54/printer	21804
FLUKE-N5K 3PP64	3108686	3 PH N5k power analyzer w/64	24476
FLUKE-N5K 3PP64I	3108699	3 PH N5k power analyzer w/64/IFC2	26581
FLUKE-N5K 3PP64IP	3108702	3 PH N5k power analyzer w/64/IFC2 & P11	29400
FLUKE-N5K 3PP64IPR	3312976	3 PH N5K power analyzer w/64/IFC2 & P11/printer	30945
FLUKE-N5K 3PP64IR	3312965	3 PH N5K power analyzer w/64/IFC2/printer	28134
FLUKE-N5K 3PP64R	3312952	3 PH N5K power analyzer w/64/printer	26023
FLUKE-N5K 4PP54	3108716	4 PH N5k power analyzer w/54	24053
FLUKE-N5K 4PP54IP	3108725	4 PH N5k power analyzer w/54/IFC2 & P11	29553
FLUKE-N5K 6PP42IB	3312929	6 PH N5K power analyzer w/42BP/IFC2	29983
FLUKE-N5K 6PP42IBR	3313044	6 PH N5K power analyzer W/42BP/IFC2/printer	31088
FLUKE-N5K 6PP50I	3312907	6 PH N5k power analyzer w/50/IFC2	39977
FLUKE-N5K 6PP50IP	3312918	6 PH N5K power analyzer w/50/IFC2 & P11	42832
FLUKE-N5K 6PP50IPR	3313015	6 PH N5K power analyzers W/50/IFC2 & P11/printer	46697
FLUKE-N5K 6PP50IR	3313003	6 PH N5K power analyzers w/50/IFC2/printer	43883
FLUKE-N5K 6PP54I	3108733	FLUKE-N5K 6PP54I,6 PH N5K POWER ANALYZER W/54/IFC2	36978
FLUKE-N5K 6PP54IP	3108740	FLUKE-N5K 6PP54IP,6 PH N5K POWER ANALYZER W/54/IFC2 & P11	39831
FLUKE-N5K 6PP54IPR	3312990	6 PH N5K power analyzer w/54/IFC2 & P11/printer	40793
FLUKE-N5K 6PP54IR	3312983	6 PH N5K power analyzer w/54/IFC2/printer	37976
FLUKE-N5K 6PP64I	3108757	6 PH N5k power analyzer w/64/IFC2	42338

Model	Article Nr.	Description	EUR
FLUKE-N5K 6PP64IP	3108769	6 PH N5k power analyzer w/64/IFC2 & PI1	45151
FLUKE-N5K 6PP64IPR	3313032	6 PH N5K power analyzer w/64/IFC2 & PI1/Printer	46692
FLUKE-N5K 6PP64IR	3313026	6 PH N5K power analyzer w/64/IFC2/printer	43883
<b>Norma 4000/5000 Accessories</b>			
FLUKE-N4K RACK KIT	3313059	N4K 19 inch rack mount kit with handles	238
FLUKE-N5K RACK KIT	3313067	N5K 19 inch rack mount kit with handles	232
NORMA 32A CABLES	3024689	Cables for 32A planar shunt	248
NORMA 32A SHUNT	3024677	32A planar shunt	977
NORMA LG SHUNT/CBL	3024692	LG Shunt Cables for High Current Shunts	330
NORMA STAR POINT	3024704	External accessory box	977
<b>Vibration Testers</b>			
810PA	3986002	AC Power Adapter with International Plug Set	95
810QDC	3530837	Quick Disconnect Cable	167
810S	3530828	Sensor	1611
810SMM	3530862	Sensor Magnet Mount	236
810SMP	3530855	Sensor Mounting Pads (10-pack)	33
FLUKE-805	4094385	Vibration Meter	2027
FLUKE-805 FC	4489229	Vibration Meter with Fluke Connect	2027
FLUKE-805 FC/805 ES	4918373	Vibration tester package	2763
FLUKE-805/805 ES	4918364	Vibration tester package	2763
FLUKE-805/ES	4636786	External Vibration Sensor	1181
FLUKE-810	3542635	Vibration Tester	10572
FLUKE-820-2	4550041	LED Stroboscope	1036
FLUKE-830/BT	5237143	Laser Alignment tool with Bluetooth installed	7602
FLUKE-830/MAGNET	4528249	Magnetic Bracket	938
FLUKE-830/SHIMS	4551330	Laser Alignment Tool, Shims	932
SBP810	3530843	Smart Battery Pack	301
<b>Process Calibrators</b>			
<b>700 Series Process Calibrators</b>			
FLK-729 150G	4856983	Automatic Pressure Calibrator (10 Bar)	9362
FLK-729 150G FC	4856894	Automatic Pressure Calibrator, w/FC (10 Bar)	9362
FLK-729 300G	4856976	Automatic Pressure Calibrator (20 Bar)	9362
FLK-729 300G FC	4856882	Automatic Pressure Calibrator, w/FC (20 Bar)	9362
FLK-729 30G	4856990	Automatic Pressure Calibrator (2 Bar)	9362
FLK-729 30G FC	4856907	Automatic Pressure Calibrator , w/FC (2 Bar)	9362
FLK-789/IR3000FC	4604605	Process Meter and FC connector	1212
FLK-789FC-MA/KIT	4722828	Kit Fluke 789, IR3000FC, A3004FC	1849
FLUKE-154 INTL	4805625	Hart Calibration Assistant	4222
FLUKE-705	665091	Loop Calibrator	850
FLUKE-707	1617262	Loop Calibrator	977
FLUKE-709	4234350	Precision Loop Calibrator	992
FLUKE-709H	4234361	Precision HART Loop Calibrator	1560
FLUKE-710	4991049	Fluke-710 Valve Testing Loop Calibrator with HART	2407
FLUKE-712B/EN	4387857	RTD Temperature Calibrator	1260
FLUKE-714B/EN	4387869	TC Temperature Calibrator	1260
FLUKE-715	620101	Volt/mA Calibrator	1418
FLUKE-717 30G	662897	Pressure Calibrator (2 bar)	1668

Model	Article Nr.	Description	EUR
FLUKE-717 10000G	4058813	Pressure Calibrator (690 bar)	1784
FLUKE-717 1000G	2547194	Pressure Calibrator (69 bar)	1609
FLUKE-717 100G	1630430	Pressure Calibrator (7 bar)	1609
FLUKE-717 1500G	2547203	Pressure Calibrator (103.4 bar)	1784
FLUKE-717 15G	4058808	Pressure Calibrator (1 bar)	1609
FLUKE-717 1G	2547166	Pressure Calibrator (68.9 mbar)	1609
FLUKE-717 3000G	2547215	Pressure Calibrator (207 bar)	1784
FLUKE-717 300G	2547175	Pressure Calibrator (20 bar)	1609
FLUKE-717 5000G	2547232	Pressure Calibrator (345 bar)	1784
FLUKE-717 500G	2547182	Pressure Calibrator (34.7 bar)	1609
FLUKE-718 100US	665080	Pressure Calibrator (7 bar)	3030
FLUKE-718 30US	665075	Pressure Calibrator (2 bar)	3030
FLUKE-718 1G	2547148	Pressure Calibrator (68.9 mbar)	3084
FLUKE-718 300G	2547153	Pressure Calibrator (20 bar)	3084
FLUKE-718EX 100	2096322	Intrinsically Safe Pressure Calibrator (7 bar)	3896
FLUKE-718EX 30	2096310	Intrinsically Safe Pressure Calibrator (2 bar)	3896
FLUKE-718EX 300	3023328	Intrinsically Safe Pressure Calibrator (20 bar)	3896
FLUKE-719 100G	3315344	Electric Pressure Calibrator (7 bar)	3926
FLUKE-719 30G	3315332	Electric Pressure Calibrator (2 bar)	3926
FLUKE-719PRO-150G	4353229	Electric Pressure Calibrator, 10 bar	3594
FLUKE-719PRO-300G	4353234	Electric Pressure Calibrator, 20 bar	3594
FLUKE-719PRO-30G	4353218	Electric Pressure Calibrator, 2 bar	3594
FLUKE-720URTD	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	206
FLUKE-721-1601	4353241	Dual Sensor Pressure Calibrator, 1.1 bar, 6.9 bar	2288
FLUKE-721-1603	4353283	Dual Sensor Pressure Calibrator, 1.1 bar, 20 bar	2288
FLUKE-721-1605	4353327	Dual Sensor Pressure Calibrator, 1.1 bar, 34 bar	2288
FLUKE-721-1610	4353366	Dual Sensor Pressure Calibrator, 1.1 bar, 69 bar	2288
FLUKE-721-1615	4353401	Dual Sensor Pressure Calibrator, 1.1 bar, 103 bar	2288
FLUKE-721-1630	4353447	Dual Sensor Pressure Calibrator, 1.1 bar, 200 bar	2288
FLUKE-721-1650	4353486	Dual Sensor Pressure Calibrator, 1.1 bar, 345 bar	2288
FLUKE-721-3601	4353252	Dual Sensor Pressure Calibrator, 2.48 bar, 6.9 bar	2288
FLUKE-721-3603	4353290	Dual Sensor Pressure Calibrator, 2.48 bar, 20 bar	2288
FLUKE-721-3605	4353330	Dual Sensor Pressure Calibrator, 2.48 bar, 34 bar	2288
FLUKE-721-3610	4353375	Dual Sensor Pressure Calibrator, 2.48 bar, 69 bar	2288
FLUKE-721-3615	4353412	Dual Sensor Pressure Calibrator, 2.48 bar, 103 bar	2288
FLUKE-721-3630	4353458	Dual Sensor Pressure Calibrator, 2.48 bar, 200 bar	2288
FLUKE-721-3650	4353499	Dual Sensor Pressure Calibrator, 2.48 bar, 345 bar	2288
FLUKE-721EX-1601	4353265	Dual Sensor Pressure Calibrator, 16, 100 PSIG	2956
FLUKE-721EX-1603	4353309	Dual Sensor Pressure Calibrator, 16, 300 PSIG	2956
FLUKE-721EX-1605	4353348	Dual Sensor Pressure Calibrator, 16, 500 PSIG	2956
FLUKE-721EX-1610	4353382	Dual Sensor Pressure Calibrator, 16, 1000 PSIG	2956
FLUKE-721EX-1615	4353420	Dual Sensor Pressure Calibrator, 16, 1500 PSIG	2956
FLUKE-721EX-1630	4353464	Dual Sensor Pressure Calibrator, 16, 3000 PSIG	2956
FLUKE-721EX-1650	4353506	Dual Sensor Pressure Calibrator, 16, 5000 PSIG	2956
FLUKE-721EX-3601	4353276	Dual Sensor Pressure Calibrator, 36, 100 PSIG	2956
FLUKE-721EX-3603	4353311	Dual Sensor Pressure Calibrator, 36, 300 PSIG	2956
FLUKE-721EX-3605	4353353	Dual Sensor Pressure Calibrator, 36, 500 PSIG	2956

Model	Article Nr.	Description	EUR
FLUKE-721EX-3610	4353394	Dual Sensor Pressure Calibrator, 36, 1000 PSIG	2956
FLUKE-721EX-3615	4353435	Dual Sensor Pressure Calibrator, 36, 1500 PSIG	2956
FLUKE-721EX-3630	4353473	Dual Sensor Pressure Calibrator, 36, 3000 PSIG	2956
FLUKE-721EX-3650	4353514	Dual Sensor Pressure Calibrator, 36, 5000 PSIG	2956
FLUKE-724/APAC/EMEA	5131125	Temperature Calibrator	2585
FLUKE-725/APAC/EMEA	5131140	Multifunction Process Calibrator	3610
FLUKE-726/APAC/EMEA	5131133	Precision Multifunction Process Calibrator	4230
FLUKE-729/750SW BU	4972518	Fluke-729 300G FC with software	10877
FLUKE-753 EU	4411027	Documenting Process Calibrator	6101
FLUKE-754 EU	4400387	Documenting Process Calibrator	7689
FLUKE-771	2646347	Milliamp Process Clamp Meter	685
FLUKE-772	3362352	Milliamp Process Clamp Meter	979
FLUKE-773	3362365	Milliamp Process Clamp Meter	1252
FLUKE-787B	4777186	Process Meter	1144
FLUKE-789/E	3977194	Fluke 789 ProcessMeter™	1351
<b>Pressure Modules</b>			
700G/TRACK	4123225	Data Logging Cable & Software	512
FLUKE-700G01	4353523	Pressure Gauge, -10" to 10" WC (27 mbar)	870
FLUKE-700G02	4353538	Pressure Gauge, -30" to 30" WC (69 mbar)	870
FLUKE-700G04	4096972	Pressure Gauge, +/- 1 bar	870
FLUKE-700G05	4097514	Pressure Gauge, 2 bar	870
FLUKE-700G06	4097538	Pressure Gauge, 6.9 bar	870
FLUKE-700G07	4097561	Pressure Gauge, 34 bar	870
FLUKE-700G08	4097592	Pressure Gauge, 69 bar	870
FLUKE-700G10	4353654	Pressure Gauge, 140 bar	870
FLUKE-700G27	4097545	Pressure Gauge, 20 bar	870
FLUKE-700G29	4097605	Pressure Gauge, 200 bar	870
FLUKE-700G30	4097610	Pressure Gauge, 345 bar	870
FLUKE-700G31	4097622	Pressure Gauge, 690 bar	870
FLUKE-700GA27	4353577	Pressure Gauge, 20 bar absolute	870
FLUKE-700GA4	4353545	Pressure Gauge, 1 bar absolute	870
FLUKE-700GA5	4353550	Pressure Gauge, 2 bar absolute	870
FLUKE-700GA6	4353561	Pressure Gauge, 6.9 bar absolute	870
FLUKE-700HTPK	4124358	Hydraulic Test Pump Kit, 0 to 690 bar	1324
FLUKE-700HTPK2	4623314	Premium hydraulic test pump kit	1678
FLUKE-700M20TH	4623338	Premium M20 pressure test hose	617
FLUKE-700MTH	4623345	Premium metric pressure test hose	617
FLUKE-700PCK	100062	Pressure Module Calibration Kit	1538
FLUKE-700PTPK	4124364	Pneumatic Test Pump Kit, 0 to 41 bar	935
FLUKE-700PTPK2	4623306	Premium pneumatic test pump kit	1186
FLUKE-700RG05	4353589	Pressure Gauge, Reference, +2 bar	963
FLUKE-700RG06	4353592	Pressure Gauge, Reference, 6.9 bar	963
FLUKE-700RG07	4353605	Pressure Gauge, Reference, 34 bar	963
FLUKE-700RG08	4353610	Pressure Gauge, Reference, 69 bar	963
FLUKE-700RG29	4353622	Pressure Gauge, Reference, 200 bar	963
FLUKE-700RG30	4353631	Pressure Gauge, Reference, 345 bar	963
FLUKE-700RG31	4353646	Pressure Gauge, Reference, 690 bar	963

Model	Article Nr.	Description	EUR
FLUKE-700TTH10K	4636393	Premium pressure transmitter test hose kit, 10K	733
FLUKE-700TTH5K	4623323	Premium pressure transmitter test hose	617
FLUKE-750P00	4352270	Pressure Module (0 - 2.5 mbar)	1847
FLUKE-750P01	4352281	Pressure Module (0 - 25 mbar)	1444
FLUKE-750P01EX	4558658	Ex Pressure Module (0 - 25 Mbar)	2688
FLUKE-750P02	4352750	Pressure Module (0 - 70 mbar)	1444
FLUKE-750P03	4352738	Pressure Module (0 - 350 mbar)	1444
FLUKE-750P04	4352313	Pressure Module (0 - 1 bar)	1444
FLUKE-750P05	4352336	Pressure Module (0 - 2 bar)	1444
FLUKE-750P05EX	4558664	Ex Pressure Module (0 - 2 Bar)	2750
FLUKE-750P06	4352349	Pressure Module (0 - 7 bar)	1444
FLUKE-750P06EX	4558673	Ex Pressure Module (0 - 7 Bar)	2750
FLUKE-750P07	4352360	Pressure Module (0 - 35 bar)	1444
FLUKE-750P08	4352372	Pressure Module (0 - 70 bar)	1444
FLUKE-750P09	4352385	Pressure Module (0 - 100 bar)	1444
FLUKE-750P09EX	4558725	Ex Pressure Module (0 - 100 Bar)	2750
FLUKE-750P2000	4352397	Pressure Module (0 - 140 bar)	1444
FLUKE-750P22	4352296	Pressure Module (0 - 70 mbar)	1444
FLUKE-750P23	4352308	Pressure Module (0 - 350 mbar)	1444
FLUKE-750P24	4352324	Pressure Module (0 - 1 bar)	1444
FLUKE-750P24EX	4558686	Ex Pressure Module (0 - 1 Bar)	2750
FLUKE-750P27	4352351	Pressure Module (0 - 20 bar)	1444
FLUKE-750P27EX	4558699	Ex Pressure Module (0 - 20 Bar)	2750
FLUKE-750P29	4352403	Pressure Module (0 - 200 bar)	2288
FLUKE-750P29EX	4558702	Ex Pressure Module (0 - 200 Bar)	4593
FLUKE-750P30	4352415	Pressure Module (0 - 340 bar)	2288
FLUKE-750P31	4352426	Pressure Module (0 - 700 bar)	2288
FLUKE-750P3IN	4555281	Pressure Module (0 - 7.5 mbar)	1501
FLUKE-750P5IN	4555296	Pressure Module (0 - 12.5 mbar)	1501
FLUKE-750PA27	4352471	Pressure Module (0 - 20 bar)	1661
FLUKE-750PA3	4352432	Pressure Module (0 - 350 mbar)	1661
FLUKE-750PA4	4352444	Pressure Module (0 - 1 bar)	1661
FLUKE-750PA4EX	4558716	Ex Pressure Module (0 - 1 Bar)	2912
FLUKE-750PA5	4352459	Pressure Module (0 - 2 bar)	1661
FLUKE-750PA6	4352467	Pressure Module (0 - 7 bar)	1661
FLUKE-750PA7	4352480	Pressure Module (0 - 35 bar)	1661
FLUKE-750PA8	4352498	Pressure Module (0 - 70 bar)	1661
FLUKE-750PA9	4352500	Pressure Module (0 - 100 bar)	1661
FLUKE-750PD10	4352556	Pressure Module (-700 - 700 mbar)	1661
FLUKE-750PD2	4352539	Pressure Module (-70 - 70 mbar)	1661
FLUKE-750PD27	4352616	Pressure Module (-1 - 20 bar)	1661
FLUKE-750PD3	4352542	Pressure Module (-350 - 350 mbar)	1661
FLUKE-750PD4	4352563	Pressure Module (-1 - 1 bar)	1661
FLUKE-750PD5	4352574	Pressure Module (-1 - 2 bar)	1661
FLUKE-750PD50	4352588	Pressure Module (-1 - 3.5 bar)	1661
FLUKE-750PD6	4352595	Pressure Module (-1 - 7 bar)	1661
FLUKE-750PD7	4352602	Pressure Module (-1 - 14 bar)	1661



Model	Article Nr.	Description	EUR
FLUKE-750PV3	4352517	Pressure Module (-350 mbar)	1661
FLUKE-750PV4	4352521	Pressure Module (-1 bar)	1661
FLUKE-750R04	4352625	Pressure Module (0 - 1 bar)	1661
FLUKE-750R06	4352633	Pressure Module (0 - 7 bar)	1661
FLUKE-750R07	4352657	Pressure Module (0 - 35 bar)	1661
FLUKE-750R08	4352669	Pressure Module (0 - 70 bar)	1661
FLUKE-750R27	4352640	Pressure Module (0 - 20 bar)	1661
FLUKE-750R29	4352678	Pressure Module (0 - 200 bar)	2411
FLUKE-750R30	4352684	Pressure Module (0 - 340 bar)	2411
FLUKE-750R31	4352691	Pressure Module (0 - 700 bar)	2411
FLUKE-750RD27	4352723	Pressure Module (-0.8 - 20 bar)	1819
FLUKE-750RD5	4352706	Pressure Module (-1 - 2 bar)	1819
FLUKE-750RD6	4352714	Pressure Module (-1 - 7 bar)	1819
<b>Process Calibrator Accessories</b>			
709H/TRACK	4281225	Logging software with cable	497
754HCC	3829410	HART communication cable for Fluke 754	99
BC7217 INTL	668217	Battery Charger	353
BC-7240	4022655	Battery Charger (753/754)	64
BP7235	668225	NiMH Battery Pack	288
BP7240	4022220	753/754 Spare Battery	197
C700	606928	Hard Case (700 Series)	391
C789	946694	Soft Meter Case	229
FLUKE-700HTH-1	2811795	Hydraulic Test Hose	1028
FLUKE-700HTP-2	4096855	Hydraulic Test Pump, 690 bar	1262
FLUKE-700ILF	1566730	In-Line Filter	120
FLUKE-700-IV	202561	Current Shunt	543
FLUKE-700LTP-1	2811763	Low Pressure Test Pump	1097
FLUKE-700PMP	617131	Pressure Pump (10 bar)	766
FLUKE-700PRV-1	2811808	Pressure Relief Valve for 700HTP	1237
FLUKE-700PTP-1	2811774	Pneumatic Test Pump	712
FLUKE-700SC	667425	Serial Interface Cable (Fluke 725/725Ex/726)	265
FLUKE-700TC1	620119	Thermocouple Plug Kits (10 types)	158
FLUKE-700TC2	620127	Thermocouple Plug Kits (5 types)	129
FLUKE-700TLK	3829398	Process Test Lead Kit	158
FLUKE-71X	3345825	Hose kit	116
FLUKE-71X-TRAP	4380747	Liquid dirt filter for Fluke 718 and 719 PRO	404
FLUKE-720RTD	4366669	RTD Probe for 721, 721Ex and 719PRO	305
FLUKE-720URTDA	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	206
FLUKE-750SW	4090343	DPC/TRACK2-software	3856
FVF-BASIC	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	183
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	302
HART DRYWELL CABLE	2111088	Cable Kit, HART Drywellcontrol	187
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	58
<b>General Accessories</b>			
<b>Test Leads, Probes and Clips</b>			
8OK-15	618113	Probe, Electronic Air Cleaner	343
AC175	4101772	Threaded Alligator Clip Set	34



Model	Article Nr.	Description	EUR
AC220	1610103	SureGrip Alligator Clip Set	53
AC280	1610115	SureGrip Hook Clip Set	43
AC283A	5130530	SureGrip Pincer Clip Set	47
AC285	1610159	SureGrip Alligator Clip Set	28
AC285-FTP	4073928	Alligator Clips and adaptors (FTP-1, FTPL-1)	32
AC288	4617784	SureGrip™ Terminal block probe	43
AC87	1278079	Heavy Duty Bus Bar Clip Set	56
AC89	873448	Heavy Duty Insulation Piercing Test Clip	63
BP980	1616807	Dual Banana Plug Kit	64
FTL-660	2280204	Fused Test Lead Set	72
FTP-1	3869437	Fuse test probe set	111
FTPL-1	3869443	Fuse test probe set with test leads	121
H900	1616818	Test Lead Holder	39
LEADWRAP	4083525	Durable Nylon Hook and Loop Fastener, 3 pack	9
T5-KIT-1	3971169	T5 Tester Accessory Starter Kit	63
T5-RLS	4089137	Replacement Test Lead Set (T5)	28
TL175	3521976	Twist Guard Test Leads	34
TL175E	3565554	Twist Guard Test Leads, 4mm	38
TL220-1	3971178	SureGrip Industrial Test Lead Set	95
TL221	2003602	SureGrip Extension Lead Set	42
TL222	2003616	SureGrip Silicone Test Lead Set	42
TL223-1	3971184	SureGrip Electrical Test Lead Set	87
TL224	1610198	SureGrip Silicone Test Lead Set	38
TL225-1	3971191	Stray Voltage Eliminator test Lead Set	125
TL238	2132831	SureGrip High Energy Test Lead Kit	95
TL27	668571	Heavy Duty Test Lead Set	43
TL40	1590606	Retractable Tip Test Lead Set	62
TL71-1	3971207	TL71, Test Lead Set	34
TL75-1	3971218	TL75, Test Lead Set	29
TL76	2032684	All-in-one Test Lead Set	48
TL80A-1	3971229	TL80A, Test Lead Set	89
TL81A	1277073	Deluxe Electronic Test Lead Kit	186
TL910	1616632	Electronic Test Lead Set (with replacement tips)	86
TL930	1616671	Patch Cords (60 cm)	21
TL932	1616680	Patch Cords (90 cm)	23
TL935	1616698	Patch Cord Kit (60, 90, 120 cm)	70
TL940	1616705	Mini-Hook Test Lead Set	23
TL950	1616710	Mini-Pincer Test Lead Set	43
TL960	1616722	Micro-Hook Test Lead Set	23
TL970	1616793	Hook and Pincer Test Lead Kit	89
TLK1550-RTLK	4112351	Integral test lead & 10 kV clamp	267
TLK-220 EUR	2097022	SureGrip Accessory Kit	175
TLK-225-1	3971234	TLK225, SureGrip Master Set	189
TLK281-1	3971241	TLK281, Automotive Test Lead Kit	166
TLK282-1	3971252	TLK282, DeLuxe Automotive Test Lead Kit	213
TLK287	3045631	Electronic Master Test Lead Kit	200
TLK289 EUR	3092521	Industrial Master Test Lead Kit	200

Model	Article Nr.	Description	EUR
TLK290	2435092	Test Probe Kit	74
TLK291	2435108	Fused Test Probe Set	74
TP1-1	3971265	TP1, Test Probes	21
TP175	3521983	TwistGuard test Probes, 2MM dia probe tips	23
TP175E	3565568	TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters	27
TP2-1	3971283	TP2, Test Probes	23
TP220-1	3971276	TP220, SureGrip Test Probes	23
TP38	1541636	Slim Reach Test Probe Set (insulated)	21
TP38-2001-OSP	2438858	Slim Reach Test Probe, red	16
TP74	1541649	Lantern Tip Test Probe Set	23
TP80	873455	Electronic Test Probe Set	46
TP912	1616644	Replacement tips for TL910	43
TP920	1616659	Test Probe Adapter Kit	62
<b>Current Clamps</b>			
80I-110S	114519	AC/DC Current Clamp (100 A)	856
I1000S	1568487	AC Current Clamp (1000 A)	740
I1010	617735	AC/DC Current Clamp (1000 A)	530
I1010-KIT	2096998	AC/DC Current Clamp (1000 A) with Soft Case	542
I200	664755	AC Current Clamp (200 A)	186
I2000 FLEX	2584912	AC Flexible Current Clamp (2000 A)	369
I200S	664760	AC Current Clamp (200 A)	308
I30	2584920	AC/DC Current Clamp (30A)	492
I3000 FLEX-4PK	2696367	AC Flexible Current Clamp (3000 A), 4-pack	1481
I3000S	657202	AC Current Clamp (3000 A)	889
I3000S FLEX-24	2584888	AC Flexible Current Clamp (3000 A), 610 mm	566
I3000S FLEX-36	2584901	AC Flexible Current Clamp (3000 A), 915 mm	678
I30S	2584935	AC/DC Current Clamp (30A)	678
I310S	2840309	AC/DC Current Clamp (300A)	407
I400	2277225	AC Current Clamp (400 A)	186
I400S	2277202	AC Current Clamp (400A)	332
I40S-PR	3949777	40A Current Clamp (1750)	431
I410	617727	AC/DC Current Clamp (400 A)	308
I410-KIT	2097005	AC/DC Current Clamp (400 A) with Soft Case	358
I6000S FLEX-24	2840311	AC Current Clamp (6000 A)	740
I6000S FLEX-36	2840327	AC Current Clamp (6000 A)	864
I800	2840283	AC Current Clamp (800 A)	265
<b>Temperature Accessories</b>			
80AK-A	2747812	Thermocouple Adapter	41
80BK-A	2747801	Integrated DMM Temperature Probe (Type K)	45
80CJ-M	833046	Male Mini Connectors (Type J)	30
80CK-M	779942	Male Mini Connectors (Type K)	30
80PJ-1	1288191	Bead Probe (Type J)	32
80PJ-9	1288218	General Purpose Probe (Type J)	81
80PJ-EXT	1288234	Extension Wire Kit (Type J)	73
80PK-1	750422	Bead Probe (Type K)	43
80PK-10	3439199	Pipe Clamp Temperature Probe (Type K)	249
80PK-11	2724500	Velcro Temperature Probe	48

Model	Article Nr.	Description	EUR
8OPK-18	3448859	Pipe Clamp Temperature Probe Kit	402
8OPK-22	2098684	SureGrip Immersion Probe	123
8OPK-24	2098691	SureGrip Air Probe	161
8OPK-25	2098706	SureGrip Piercing Probe	146
8OPK-26	2098714	SureGrip General Purpose Probe	161
8OPK-27	2098723	SureGrip Industrial Surface Probe	440
8OPK-3A	874610	Surface Probe (Type K)	276
8OPK-8	200360	Pipe Clamp Temperature Probe (Type K)	225
8OPK-9	1288229	General Purpose Probe (Type K)	81
8OPK-EXT	1288241	Extension Wire Kit (Type K)	73
8OPR-60	2148313	RTD Temperature Probe (Fluke 66/68)	89
8OPT-25	2104397	SureGrip Piercing Probe	127
8OPT-EXT	1288252	Extension Wire Kit (Type T)	73
8OT-150UA	3190456	Universal Temperature Probe (for DMMs)	346
8OTK	736736	Thermocouple Module (Type K)	175
<b>Cases and Holsters</b>			
C101	2437514	Hard Case	81
C115	2826063	Soft Meter Case	77
C116	2826074	Soft Meter Case	93
C125	646858	Soft Meter Case	57
C12A	930529	Soft Meter Case	42
C150	4111540	Zippered Soft Carrying Case	38
C1600	2091049	Meter and Accessory Case	49
C1620	4359042	Carrying Case	234
C190	677401	Hard Case (190 Series)	289
C195	677408	Soft Case	267
C23	1663209	Soft Meter Case	33
C25	681114	Soft Meter Case	70
C280	3182785	Soft Meter Case	81
C33	1664120	Soft Meter Case	38
C345	3311173	Soft Case	99
C35	2826056	Soft Meter Case	55
C43	1663230	Soft Meter Case	104
C50	762823	Soft Meter Case	49
C510	1547885	Leather Meter Case	98
C520A	1629104	Leather Tester Case	74
C550	1547919	Tool Bag	163
C75	865535	Soft Accessory Case	23
C781	619988	Soft Meter Case	120
C789	946694	Soft Meter Case	229
C799	4021731	Soft case for Fluke 75x series	130
C90	466029	Soft Meter Case	49
CAM0-C25	4110632	Camouflage carrying case for Fluke multimeters	47
CXT1000	4628917	Extreme Hard case	212
CXT170	3352567	Rugged Pelican Hard Case	212
CXT280	3352571	Rugged Pelican Hard Case	212
CXT80	3352559	Rugged Pelican Hard Case	212

Model	Article Nr.	Description	EUR
FLK-C3000	4582763	Premium modular toolbag	104
FLK-C3003	4582928	3-Compartment soft case	47
FLUKEPACK30	4983088	Professional Tool Backpack	179
H15	4111533	Belt Holster for T100 series	36
H3	1608458	Holster (330 Series)	53
H5	649365	Electrical Tester Holster (Fluke T5)	42
H80M	2138458	Holster + Magnetic Hanger	51
H-T6	4910585	T6 Belt Holster	42
<b>Automotive Accessories</b>			
BP880	2150594	BNC to Female Double Stacking Banana Plug	18
BP881	2151015	BNC to Male Double Stacking Banana Plug	23
PV350	919811	Pressure Vacuum Module	353
RPM80	880849	Inductive Pick-up	120
SCC 128	2100199	Automotive Accessory Kit (120 Series)	814
SCC 198	2100208	Automotive Accessory Kit (190 Series)	1024
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	284
TAS90	614187	Automotive Accessory Set (120/190 Series)	80
TL28A	1273185	Automotive Test Lead Set	70
TL82	2150636	Automotive Pin and Socket Adapter Set	144
TP40	1567573	Automotive Back Probe Pins (5 pcs) (4 mm)	50
TP81	2149098	Insulation Piercing Clip Set (4 mm)	70
TP82	2149080	Insulation Piercing Clip Set (2 mm)	67
TP88	2149102	Rigid Back Probe Pin Set	17
<b>Other Accessories</b>			
80K-40	382846	High Voltage Probe	353
80K-6	532424	High Voltage Probe	197
EBC290	3894906	External Battery Charger	119
FL-120 EX	4972431	120 lumen intrinsically safe flashlight	78
FL-150 EX	4972446	150 lumen intrinsically safe flashlight	102
FL-45 EX	4972422	45 lumen intrinsically safe flashlight	51
HL-200 EX	4972410	200 lumen intrinsically safe headlamp	102
L200	2096346	Probe Light	30
L205	2098588	Mini Hat Light	40
L206	2098595	Deluxe Hat Light	49
L210	2096379	Probe light and probe extender	48
L215	2096368	SureGrip kit with probe light and probe extender	111
LVD1A	4571403	Volt Light	42
LVD2	2740300	Volt Light	46
PV350	919811	Pressure Vacuum Module	353
SV225	3100477	Stray Voltage Adapter	84
TPAK	1281997	ToolPak, Meter Hanging Kit	49
<b>Fuses</b>			
7017240.0	2279339	Fuse, A:315mA (f), V:1000V, IR:10kA, 6.35x32 mm	12,15
FUSE	740670	Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm	4
FUSE	803293	Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm	9,45
FUSE	830828	Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm	8,45
FUSE	943121	Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm	5,2

Model	Article Nr.	Description	EUR
<b>Software</b>			
FVF-BASIC	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	183
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	346
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	199
FVF-UG	1576741	FlukeView Forms Upgrade	162
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	524
SCC190EFG	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	734
SW90W	3894923	FlukeView Software	406

Every effort has been made to ensure this guide is as accurate as possible. Fluke (UK) Ltd. reserve the right to alter details without prior notification.

Prices are recommended list prices excl. VAT.

**Fluke.** *Keeping your world up and running.*<sup>®</sup>

**Fluke UK Ltd**  
 52 Hurricane Way  
 Norwich  
 Norfolk, NR6 6JB  
 United Kingdom  
 Email: cs.uk@fluke.com  
 Phone +44 (0)20 7942 0708

©2021 Fluke Corporation. All rights reserved.  
 Data subject to alteration without notice.  
 10/2021 ieen

**Modification of this document is not permitted without written permission from Fluke Corporation.**