

# Fluke Test Tools Pricelist

Valid from: 01.03.2023

Model	Article Nr.	Description	GBP
<b>Fluke Connect</b>			
<b>Fluke Connect - 3000 Series</b>			
FLK-3000FC	4401595	FC Wireless Digital Multimeter	373
FLK-3000FC/1AC-II	4699302	Electrician's DMM voltage tester and accessory kit	514
FLK-3000FC/EDA2	4699333	Electronics DMM and deluxe accessory kit	465
FLK-3000FC/TPAK	4699340	Fluke 3000FC with TPAK meter hanging kit	398
FLK-A3000FC	4401588	FC Wireless AC Current Clamp Module	221
FLK-A3000FC KIT	4465618	FC Wireless Essential Kit with A3000	513
FLK-A3001FC	4459439	FC Wireless iFlex AC Current Module	256
FLK-A3001FC KIT	4465665	FC Wireless Essential Kit with i3000	560
FLK-A3002FC	4459442	FC Wireless AC/DC Current Module	152
FLK-A3003FC	4629295	FC Wireless 2000A DC Clamp meter	621
FLK-A3004FC	4629301	FC Wireless 4-20mA DC Clamp meter	729
FLK-T3000FC	4401563	FC Wireless K-Type Temperature Module	221
FLK-T3000FC KIT	4465652	FC Wireless Essential Kit with T3000	509
FLK-V3000FC	4401556	FC Wireless AC Voltage Module	236
FLK-V3000FC KIT	4465641	FC Wireless Essential Kit with V3000	509
FLK-V3001FC	4459421	FC Wireless DC Voltage Module	236
FLK-V3001FC KIT	4467777	FC Wireless essential Kit with V3001	509
<b>Fluke Connect - 3500 Sensor Series</b>			
FLK-3540 KIT UK/EU	5081559	Fluke 3540 FC Three-Phase Power Monitor and Condition Monitoring Kit	3175
<b>Fluke Connect - Accessories</b>			
FLUKE-IR3000FC	4460436	Connector, Infrared, FC	165
<b>Digital Multimeters</b>			
<b>110 Series Multimeters</b>			
C50	762823	Soft Meter Case	50
FLUKE-113 EUR	3088053	True RMS Multimeter	150
FLUKE-114 EUR	2583552	True RMS Multimeter	207
FLUKE-115 EUR	2583583	True RMS Multimeter	253
FLUKE-116 EUR	2583601	True RMS Multimeter	295
FLUKE-116/323 KIT	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	417
FLUKE-116/62 MAX+	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	374
FLUKE-117 EUR	2583647	Fluke 117 Electricians TRMS Multimeter with Non-Contact voltage	300
FLUKE-117/323 EUR	4296034	Fluke Electrician's Multimeter Combo Kit	383
FLUKE-117/PRV240	4636971	Proving unit, Fluke 117 DMM Kit	366
<b>170 Series Multimeters</b>			
C90	466029	Soft Meter Case	49
FLUKE-175 EGFID	1592901	True RMS Multimeter	328
FLUKE-177 EGFID	1592874	True RMS Multimeter	377
FLUKE-179 EGFID	1592842	True RMS Multimeter	410
FLUKE-179/EDA2/EUR	3947719	Electronics Combo Kit	470
FLUKE-179-2/IMSK	4370598	Industrial Multimeter Service Kit	545
<b>200 Series Multimeters</b>			
BC500TDMM	4820410	Battery charger for Fluke 279FC	152
C280	3182785	Soft Meter Case	83
FLK-287/FVF/IR3000	4699316	Fluke 287 FlukeView® Forms Combo Kit	994

Model	Article Nr.	Description	GBP
FLK-289/FVF/IR3000	4699325	Fluke 289 FlukeView® Forms Combo Kit	1076
FLUKE-233 EU	3469334	Remote Display Multimeter	429
FLUKE-279FC I/B	4989200	Wireless TRMS Thermal Multimeter with iFlex & extra battery	1210
FLUKE-279FC/IFLEX	4684050	Wireless TRMS Thermal Multimeter w/iFlex	1100
FLUKE-287/EUR	3947781	True RMS Electronic Logging Multimeter with TrendCapture	778
FLUKE-287/FVF/EUR	3947796	FlukeView Forms Combo Kit	846
FLUKE-289/EUR	3947801	True RMS Industrial Logging Multimeter with TrendCapture	846
FLUKE-289/FVF/EUR	3947812	Industrial Logging Multimeter and Software Combo Kit	925
FLUKE-289/IMSK	3449156	Industrial Multimeter Service Kit	864
<b>20 Series Multimeters</b>			
C25	681114	Soft Meter Case	67
FLUKE-27II/EUR	3947770	Industrial Multimeter (IP67)	697
FLUKE-28II/EUR	3947820	True RMS Industrial Multimeter (IP67)	697
FLUKE-28IIEX	4017165	Intrinsically safe true-rms digital multimeter	1418
<b>70 Series Multimeters</b>			
FLUKE-77-4/EUR	3947835	Multimeter	493
<b>80 Series Multimeters</b>			
C25	681114	Soft Meter Case	67
FLK-87VMAX-PVLEAD1	5337412	Fluke 87V MAX DMM and PVLEAD1 MC4 Test Leads Bundle	673
FLUKE-83-5/EUR	3947847	Multimeter	527
FLUKE-87-5/E2K/EUR	3947864	Industrial Electricians Combo Kit	648
FLUKE-87-5/EUR	3947858	True RMS Multimeter	576
FLUKE-87V/IMSK	3448783	Digital multimeter Fluke 87V and the i400 AC current clamp	701
FLUKE-87V-MAX	5140033	True-rms Digital Multimeter	668
FLUKE-87V-MAX/E2 KIT	5160712	Fluke 87V MAX E2 Industrial Electrician Combo Kit	793
<b>Clamp Meters</b>			
FLK-393FC-PVLEAD	5337394	Fluke 393 FC Clamp Meter and MC4 Test Leads Bundle	690
FLK-393-IRR-PVLEAD	5337401	Fluke 393 FC Clamp,IRR1 Irradiance Meter,MC4 Test Leads Bundle	978
FLUKE-323	4152628	True RMS Clamp Meter	154
FLUKE-324	4152637	True RMS Clamp Meter	187
FLUKE-325	4152643	True RMS Clamp Meter	253
FLUKE-353	2840252	AC/DC True RMS Clamp Meter	735
FLUKE-355	2840265	AC/DC True RMS Clamp Meter	935
FLUKE-365/E	3790607	Detachable TRMS Clamp Meter	344
FLUKE-368 FC	4709907	Wireless leakage current clamp, 40mm jaw	831
FLUKE-369 FC	4709934	Wireless leakage current clamp, 61mm jaw	864
FLUKE-373/E	3790564	600A TRMS Clamp Meter	317
FLUKE-374 FC	4696001	600A AC/DC TRMS Wireless Clamp Meter	484
FLUKE-375 FC	4695932	600A AC/DC TRMS Wireless Clamp Meter	542
FLUKE-376 FC	4695861	1000A AC/DC TRMS Wireless Clamp Meter with iFlex	641
FLUKE-377 FC/E	5111858	Fluke 377 FC True-rms Non-Contact Voltage AC/DC Clamp Meter with iFlex	620
FLUKE-377/E	5225745	Fluke 377 True-rms Non-Contact Voltage AC/DC Clamp Meter with iFlex	667
FLUKE-378 FC/E	5225723	Fluke 378 FC True-rms Non-Contact Voltage AC/DC Clamp Meter with iFlex	710
FLUKE-378/E	5225761	Fluke 378 True-rms Non-Contact Voltage AC/DC Clamp Meter with iFlex	764
FLUKE-381	3610452	Remote Display TRMS Clamp Meter	787
FLUKE-393/E	5274939	393 CAT III 1500 V True-rms Clamp Meter with iFlex	721
FLUKE-393FC/E	5274900	393 FC CAT III 1500 V True-rms Clamp Meter with iFlex	721

Model	Article Nr.	Description	GBP
FLUKE-902 FC	4695814	TRMS Wireless HVAC ClampMeter	327
FLUKE-I2500-10	3676410	iFlex Probe	159
FLUKE-I2500-18	3676405	iFlex Probe	159
H3	1608458	Holster (330 Series)	52
PVLEAD1	5301188	MC4 to 4MM test lead set, black/red	44,99
PVLEAD3	5301195	MC4 Solar power clamp set	71,77
<b>Bench Multimeters</b>			
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	358
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	194
FVF-UG	1576741	FlukeView Forms Upgrade	174
<b>Automotive Meters</b>			
FLUKE-88-5/A KIT	2117440	Automotive Meter Combo Kit	794
<b>Hand Tools</b>			
IB117KEUR	5195045	Fluke 117 Electrician's Multimeter + Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	441
IB117L	5133953	Fluke 117 Electrician's Multimeter + SLS3 + ISLS5 + IPHS2	330
IB117M	5133966	Fluke 117 Electrician's Multimeter + ISLS3 + ISLS5 + IPHS2 + IPHS1 + ISLS8	352
IB179K-EDSNF	5134028	Fluke 179 True-RMS Digital Multimeter + Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	551
IB179L-EDSNF	5134004	Fluke 179 True-RMS Digital Multimeter + ISLS3 + ISLS5 + IPHS2	441
IB179M-EDSNF	5134019	Fluke 179 True-RMS Digital Multimeter + ISLS3 + ISLS5 + IPHS2 + IPHS1 + ISLS8	463
IB376KEUR	5195061	Fluke 376 FC Clamp Meter + Insulated Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	734
IB376L	5134134	Fluke 376 FC Clamp Meter + ISLS3 + ISLS5 + IPHS2	639
IB376M	5134141	Fluke 376 FC Clamp Meter + ISLS3 + ISLS5 + IPHS2 + IPHS1 + ISLS8	663
IB875KEUR	5195050	Fluke 87V Industrial Multimeter + Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	718
IB875L	5134096	Fluke 87V Industrial Multimeter + ISLS3 + ISLS5 + IPHS2	606
IB875M	5134107	Fluke 87V Industrial Multimeter + ISLS3 + ISLS5 + IPHS2 + IPHS1 + ISLS8	629
IBT6KEUR	5195077	T6-1000 Electrical Tester + Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	442
IKPK7	5067392	Fluke Pack30 Professional Tool Backpack + Insulated Hand Tools Starter Kit (5 insulated screwdrivers and 3 insulated pliers)	427
IKPL3	5067377	Insulated 3 units Plier Kit, 1,000 V	178
IKSC7	5067345	Insulated 7 units Screwdriver Kit, 1,000 V (3 slotted, 2 Phillips, 2 square)	140
IKST7	5067389	Insulated Hand Tools Starter Kit—5 insulated screwdrivers and 3 insulated pliers, 1,000 V	285
INCP8	5067267	Insulated Lineman Combination Plier, 8 in, 200 mm, 1,000 V	60
INDC8	5067244	Insulated High Leverage Diagonal Cutter, 8 in, 200mm, 1,000 V	72
INLP8	5067232	Insulated Long Nose with Side Cutter, 8 in, 200mm, 1,000 V	64
INPP10	5067259	Insulated Pump Plier Fast adjustable, 10 in, 250 mm, 1,000 V	84
IPHS1	5067306	#1 Phillips screwdriver. Certified to 1000 V ac and 1500 V dc.	21
IPHS2	5067314	#2 Phillips screwdriver. Certified to 1000 V ac and 1500 V dc.	26
ISLS3	5067271	Insulated Slotted Screwdriver 3/32x3 in, 2.5 mm x 75 mm, 1,000 V	19
ISLS5	5067280	Insulated Slotted Screwdriver 5/32x4 in, 4 mm x 100 mm, 1,000 V	19

Model	Article Nr.	Description	GBP
ISLS8	5067298	125 mm screwdriver with 6 mm slotted blade. Certified to 1000 V ac and 1500 V dc.	26
ISQS1	5067323	Insulated Squared Screwdriver #1, 4 in, 100 mm, 1,000 V	26
ISQS2	5067338	Insulated Squared Screwdriver #2, 5 in, 125 mm, 1,000 V	26
RUP8	5081598	Roll-up tool pouch	24
<b>Electrical Testers</b>			
FLK-1AC-A1-II-5PK	2433042	Fluke 1Ac li Voltalert™ 5-Pack	146
FLK-1AC-E1-II-5PK	2433056	Volt Alert 5-pack	146
FLK2AC/200-1000V5L	3806493	Volt Alert, 200-1000V, 5-pack	126
FLK2AC/200-1000VC	3611972	ACV Detector 200-1000V	35
FLK2AC/200-1000VCL	3611985	ACV Detector 200-1000V	35
FLK2AC/90-1000V	3807928	ACV Detector 90-1000V, Flat-tip	35
FLK2AC/90-1000V5PK	3807937	Volt Alert 90-1000V, 5-pack, Flat-tip	119
FLUKE-1000FLT	4472387	Fluorescent Light Tester	296
FLUKE-1AC-E2-II	2432971	Volt Alert	36
FLUKE-2042	2435038	Cable Locator (Transmitter + Receiver)	931
FLUKE-2042T	2435045	Cable Locator Transmitter	476
FLUKE-9040UK	2435061	Phase Rotation Indicator	289
FLUKE-9062UK	2435089	Motor And Phase Rotation Indicator	254
FLUKE-T110	4016950	Voltage, Continuity Tester with switchable load	89
FLUKE-T130	4016961	Voltage and Continuity Tester with backlit LCD readout	136
FLUKE-T150	4016977	Voltage and Continuity Tester with LCD readout and additional resistance measurement	167
FLUKE-T150/PRV240	4637005	Fluke-T150 +PRV240 Proving Unit Kit	304
FLUKE-T90	4016945	Basic Voltage and Continuity Tester	64
FTL-660	2280204	Fused Test Lead Set	73
H5	649365	Electrical Tester Holster (Fluke T5)	37
H-T6	4910585	T6 Belt Holster	37
LVD1A	4571403	Volt Light	34
LVD2	2740300	Volt Light	50
PRV240	4566209	Proving unit	169
PRV240FS	4910310	Proving unit, T6/NCV	162
ST240+/UK	5310352	ST240+/UK Socket Tester	36
T5-1000/UK	609385	Electrical Tester	184
T5-600/62MAX+/1ACE	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	311
T5-600/UK	609377	Electrical Tester	174
T5-H5-1AC KIT/UK	2098640	Electrical Tester Kit With Holster And Iac	221
T6-1000/EU	4910257	Electrical Tester with FieldSense™, round	323
T6-1000PRO/EU	5134758	Fluke T6-1000 PRO Electrical Tester	333
T6-600/62MAX+/1ACE	4910524	Fluke T6-600 with 62MAX+ IR Temperature meter, 1AC Voltage detector and C60 softcase	364
T6-600/EU	4910322	Electrical Tester with FieldSense™, round	209
TL1500DC	5313782	Fluke TL1500DC Insulated Test Leads	34
<b>Laser Levels</b>			
<b>3 point lasers</b>			
PLS 3G KIT	5009378	3-Point Green Laser Kit	313
PLS 3G Z	5009369	3-Point Green Laser Bare Tool	262

Model	Article Nr.	Description	GBP
PLS 3R KIT	5009357	3-Point Red Laser Kit	264
PLS 3R Z	5009340	3-Point Red Laser Bare Tool	209
<b>5 point lasers</b>			
PLS 5G KIT	5009414	5-Point Green Laser Kit	419
PLS 5G Z	5009406	5-Point Green Laser Bare Tool	370
PLS 5R KIT	5009391	5-Point Red Laser Kit	362
PLS 5R Z	5009384	5-Point Red Laser Bare Tool	324
<b>Cross line and point lasers</b>			
PLS 6G RBP KIT	5116068	Cross Line and Point Green Laser Kit	586
PLS 6G RBP SYS	5116079	Cross Line and Point Green Laser System	719
PLS 6G Z	5009461	Cross Line and Point Green Bare Tool	496
PLS 6R RBP KIT	5195802	Cross Line and Point Red Laser Kit	493
PLS 6R RBP SYS	5195833	Cross Line and Point Red Laser System	627
PLS 6R Z	5009423	Cross Line and Point Red Laser Bare Tool	382
<b>Cross line lasers</b>			
PLS 180G RBP KIT	5116087	Cross Line Green Laser Kit	425
PLS 180G RBP SYS	5116093	"Cross Line Green Laser System"	493
PLS 180G Z	5017287	Cross Line Green Laser Bare Tool	367
PLS 180R RBP KIT	5195840	Cross Line Red Laser Kit	347
PLS 180R RBP SYS	5195857	"Cross Line Red Laser System"	425
PLS 180R Z	5017279	Cross Line Red Laser Bare Tool	284
<b>3x360 Lasers</b>			
PLS 3X360R Z TOOL	5114111	Red three-plane laser, Bare Tool	320
PLS 3X360R KIT	5114127	Red three-plane laser, Kit	512
PLS 3X360G Z TOOL	5114148	Green three-plane laser, Bare Tool	397
PLS 3X360G KIT	5114153	Green three-plane laser, Kit	559
PLS HGI3X360R	5204916	PLS Housing Glass Insert for PLS 3X360R	27
PLS HGI3X360G	5214800	PLS Housing Glass Insert for PLS 3X360G	27
PLS 3X360 MLB	5214817	Magnetic L-Bracket w/ Micro and Elevation Adjustment	55
PLS 3X360 CB	5214821	Ceiling Bracket used w/ PLS 3X360MLB	29
PLS 3X360 HC	5221067	PLS 3X360 Blow Mold Hard Case	23
<b>Rotary lasers</b>			
<b>Horizontal rotary lasers</b>			
PLS H2 KIT	5022496	PLS H2 Red Rotary Laser Kit with Tripod and Grade Rod	1207
PLS H2 Z	5022470	PLS H2 Red Rotary Laser Bare Tool	602
<b>Manual slope rotary lasers</b>			
PLS HV2G KIT	5022520	PLS HV2G Green Rotary Laser Kit	1651
PLS HV2G Z	5022535	PLS HV2G Green Rotary Laser Bare Tool	978
PLS HV2R KIT	5022558	PLS HV2R Red Rotary Laser Kit with Tripod and Grade Rod	1509
PLS HV2R Z	5022501	PLS HV2R Red Rotary Laser Bare Tool	831
<b>Accessories lasers</b>			
PLS BC20	5022618	Charging Cord for PLS RBP10	44
PLS BP5	5031952	BP5 Alkaline Battery Pack	52
PLS C18	4985124	Laser Level Tool Box	97
PLS FS	5031929	Floor Stand for PLS 3, 5, 6	19
PLS GR16	5022652	Grade Rod with US and Metric	60
PLS GRT4	5022634	Green Magnetic Reflective Target	17

Model	Article Nr.	Description	GBP
PLS MLB	5031934	Magnetic L-Bracket, PLS 3, 5, 6, 180	53
PLS RBC5	5031965	Charging cord with adapters for RBP5 Li-ion battery	15
PLS RBP10	5022607	Rechargeable Battery for H2, HV2	87
PLS RBP5	5023322	Li-ion battery for PLS hand held lasers with charging cord and adapters	75
PLS RBP5 SINGLE PK	5075484	Single pack RBP5 Li-ion battery for PLS line and dot lasers	65
PLS RC2	5022564	Rotary Laser Remote Control	73
PLS RRT4	5022629	Red Magnetic Reflective Target	17
PLS WCB10	5022641	Rotary Wall and Ceiling Mount	111
PLS XLD	5037696	Rotary Laser Detector with Clamp	228
PLS XLD CLAMP	5037709	Rotary Detector Clamp	44
PLS-HGI180G	5067797	PLS 180G Replacement Window Glass Insert	29
PLS-HGI180R	5042463	PLS 180R Replacement Window Glass Insert	29
PLS-HGI3G	5067760	PLS 3G Replacement Window Glass Insert	29
PLS-HGI3R	5042439	PLS 3R Replacement Window Glass Insert	29
PLS-HGI5G	5067772	Replacement Window Glass Insert PLS 5G	29
PLS-HGI5R	5042442	Replacement Window Glass Insert PLS 5R	29
PLS-HGI6G	5067785	Replacement Window Glass Insert PLS 6G	29
PLS-HGI6R	5042456	Replacement Window Glass Insert PLS 6R	29
<b>Distance Meters</b>			
FLUKE-417D	5099292	Laser Distance Measurer	122
FLUKE-417D/62MAX KIT	5112860	Fluke-417D/62Max Kit, 417D Laser Distance Meter and 62Max+ IR Thermometer	211
FLUKE-424D	4106866	Laser Distance Meter	486
<b>Battery Analyzers</b>			
<b>Battery Analyzers</b>			
FLUKE-BT510	4489970	Battery Analyzer	3380
FLUKE-BT520	4489981	Battery Analyzer	4447
FLUKE-BT520ANG	5104752	Battery Analyzer, with angled test probes	5587
FLUKE-BT521	4489996	Advanced Battery Analyzer	4853
FLUKE-BT521ANG	5104765	Advanced Battery Analyzer, with angled test probes	6091
<b>Battery Analyzer Accessories</b>			
BC500	4542299	AC Power Charger	155
BP500	4542300	Lithium-ion battery, 7.4V 3000 mAh	134
BT500-PROBE-TIP	4561297	Probe tip, 10x replacement Probe tips, 2x long probe tip covers, 2x short probe tip covers	160
BTL10	4542264	Standard Battery Analyzer Probes	418
BTL20	4542273	Intelligent Test Probe Set, w/Extenders (no temp sensor)	641
BTL20ANG	4969588	Interactive Battery Analyzer Test Probe with angled tip	894
BTL-A	4542258	Voltage/Current Probe Adapter	54
I410	617727	AC/DC Current Clamp (400 A)	329
<b>Insulation Testers</b>			
1587KIT/62MAX+ FC	4692778	2-IN-1 Advanced Electrical Troubleshooting Insulation Multi Kit with 62MAX+ I400	1035
FLUKE-1503	2427883	Insulation Tester	455
FLUKE-1507	2427890	Fluke 1507 Insulation resistance tester	594
FLUKE-1550C	3665021	Insulation Resistance Tester (5kV)	4604
FLUKE-1550C FC	4977402	Insulation Resistance Tester (5kV) with IR3000FC	4604



Model	Article Nr.	Description	GBP
FLUKE-1550C FC KIT	4977457	Insulation Resistance Tester Kit (5kV) with IR3000FC	5075
FLUKE-1550C/KIT	3665127	Insulation Resistance Tester Kit (5kV)	5075
FLUKE-1555	3665056	Insulation Resistance Tester (10kV)	5075
FLUKE-1555 FC	4977519	Insulation Resistance Tester (10kV) with IR3000FC	5075
FLUKE-1555 FC KIT	4977469	Insulation Resistance Tester Kit (10kV) with IR3000FC	5544
FLUKE-1555/KIT	3665111	Insulation Resistance Tester Kit (10kV)	5544
FLUKE-1577	2157280	Insulation Multimeter	745
FLUKE-1587 FC	4691215	2-IN-1 Insulation Multimeter	837
FLUKE-1587 T	2517605	Insulation Multimeter (Telecom)	861
FLUKE-1587/I400 FC	4692725	2-IN-1 Insulation Multimeter with Clamp i400	883
FLUKE-1587/MDT FC	4692716	2-IN-1 Advanced Motor & Drive Troubleshooting Kit with 9040, I400	1064
FLUKE-IR3000FC1550	4460451	Fluke ir3000 FC Connector	280
FVF-BASIC	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	194
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	332
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	60
<b>Installation Testers</b>			
1662 UK FTT KIT	5363294	FLUKE 1662 UK KIT,INSTALLATION TESTER + TRUTEST ADV.	1337
1662 UK/T90	5363266	Fluke 1662 Multifunction Installation tester with a FREE T90 Voltage and Continuity Tester	1062
1663 UK FTT KIT	5363307	FLUKE 1663 UK KIT,INSTALLATION TESTER + TRUTEST ADV.	1733
1663 UK/T110	5363275	Fluke 1663 Multifunction Installation tester with a FREE T110 Voltage and Continuity Tester	1562
1664FC UK FTT KIT	5363318	1664FC UK INSTALLATION TESTER UK + TRUTEST ADV.	1700
1664FC UK/T6PRO	5318224	Fluke 1664FC Multifunction Installation tester with a FREE T6-1000 PRO Electrical Tester	1700
1D-BS-TRN-VOUCH	5339659	1-DAY-BS 7671 TRAINING VOUCHER FOR 1 PERSON	389
3D-BS-TRN-VOUCH	5339667	3-DAY-BS 7671 TRAINING VOUCHER FOR 1 PERSON	1167
ES165X	2104706	Earth Spike Test Kit	193
FLK-1662 UK	4546915	Installation Tester W/Mem Uk	1125
FLK-1663 UK	4546971	Installation Tester W/Rcd Type B Uk	1655
FLK-1664FC UK	4547031	Fc Installation Tester W/Insulation Pre-Test Uk	1939
FLK-166X-MTC-UK	4601070	Fluke 166X-Main Test Cord, Uk	60
FLK-FEV300/KIT UK	5363606	TEST ADAPTER EV CHARGING W/TYPE 2 PLUG & 1664FC CH	2518
FLK-TRUTES-LITE-M10	5315203	Fluke TruTest Software License Code - Lite - 10 workstations	2143
FLK-TRUTEST-ADV	5265319	Fluke TruTest Software License Code - Advanced	387
FLK-TRUTEST-ADV-M10	5315182	Fluke TruTest Software License Code - Advanced - 10 workstations	3434
FLK-TRUTEST-ADV-M5	5315175	Fluke TruTest Software License Code - Advanced - 5 workstations	1718
FLK-TRUTEST-CD	5265337	Fluke TruTest Software - CD (Excl. License code)	39
FLK-TRUTEST-LITE	5265304	Fluke TruTest Software License Code - Lite	241
FLK-TRUTEST-LITE-M5	5315194	Fluke TruTest Software License Code - Lite - 5 workstations	1072
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	332
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	60
TL165X	2107756	Standard Test Lead Set (1650 Series)	142
TP165X	2107742	Remote Control Probe (1650 Series)	99
ZERO ADAPTER	3261925	Zero adapter (165xB)	60
<b>eMobility testers</b>			
FLK-FEV300/TY2	5347987	TEST ADAPTER EV CHARGING W/TYPE 2 PLUG, INTL	862

Model	Article Nr.	Description	GBP
FLK-FEV300/TY1 & TY2	5347993	TEST ADAPTER EV CHARGING W/TYPE 1 & 2 PLUG, INTL	988
FLK-FEV300/BASIC	5348008	TEST ADAPTER EV CHARGING W/TYPE 1 & 2 PLUG, INTL	539
FLK-FEV300-CON-TY2	5348123	TYPE 2 PLUG FOR TEST ADAPTER EV CHARGING, INTL	333
FLK-FEV300-CON-TY1	5348138	TYPE 1 PLUG FOR TEST ADAPTER EV CHARGING, INTL	342
<b>Solar Testers</b>			
FLK-SMFT-1000/KIT	5280005	Fluke SMFT-1000/KIT Multifunction PV Analyzer Kit	4679
FLK-SMFT-1000/PRO	5416417	Fluke SMFT-1000/PRO Multifunction PV Analyzer Kit	5099
FLK-IRR1-SOL	5218288	Solar Irradiance Meter	371
<b>Portable Appliance Testers</b>			
110V-ADAPTER-KIT	4372377	110 V ADAPTER KIT, FLUKE-6500-2 UK	37
6200-2 UK KIT	4377198	Portable Appliance Tester, Kit, Uk	1104,15
6500-2 UK FTT KIT 2	5363329	6500-2 UK FTT KIT 2, PORTABLE APPLIANCE TESTER, KIT, UK + TRUTEST	2273
APP1000	1992611	Barcode Appliance Number Labels 0-1000	153
APP2000	1992627	Barcode Appliance Number Labels 1001-2000	153
APP3000	1992630	Barcode Appliance Number Labels 2001-3000	153
APP4000	1992648	Barcode Appliance Number Labels 3001-4000	153
AUTO200B	2141221	Auto Code Label	53
BDST3	2796907	Snap Tag (cable tie)	41
BDST4	2796918	Snap Tag (clip on)	41
EXTL100	2414348	Extension Lead Test Adaptor	24
FAIL250	2095376	Appliance Fail Labels	30
FLK-TRUTES-LITE-M10	5315203	Fluke TruTest Software License Code - Lite - 10 workstations	2143
FLK-TRUTEST-ADV	5265319	Fluke TruTest Software License Code - Advanced	387
FLK-TRUTEST-ADV-M10	5315182	Fluke TruTest Software License Code - Advanced - 10 workstations	3434
FLK-TRUTEST-ADV-M5	5315175	Fluke TruTest Software License Code - Advanced - 5 workstations	1718
FLK-TRUTEST-CD	5265337	Fluke TruTest Software - CD (Excl. License code)	39
FLK-TRUTEST-LITE	5265304	Fluke TruTest Software License Code - Lite	241
FLK-TRUTEST-LITE-M5	5315194	Fluke TruTest Software License Code - Lite - 5 workstations	1072
FLUKE-6200-2 UK	4324466	Portable Appliance Tester Uk	1119
FLUKE-6500-2 UK	4324475	Portable Appliance Tester UK	1633
IRP1	1993496	Pat Register	18
PASS 500S	2141138	Appliance Pass Labels (Rectangular)	40
PASS 560R	2141192	Appliance Pass Labels (Round)	79
SP6000 PRINTER	4325128	Printer for Portable Appliance Testers	703
SPSCAN6000	4325143	Scanner for Portable Appliance Testers	449
TA700	2389678	Appliance Adaptor For 110V Tools	54
TDO1F	3062320	UK Electrical Installation Certificates	36
TDO2F	3062335	Certificates for Minor Electrical Works	36
TDO3F	3062347	Electrical Periodic inspection Reporting documents	36
TDO4F	3062358	Electrical Survey Schedule & Test Report	36
TDO5F	3062364	Electrical Inspection & Test Schedule Documents	36
TDO6F	3062373	Electrical Inspection & Test Schedule Documents	36
TDO7F	3062386	Electrical Test Certificate Part P UK Building Regulations	36
TD16F	3062399	Electrical Observe & Recommend Sheet	36
TD20F	3062402	Portable Appliance Test Certificate Book	36
<b>Earth Ground Testers</b>			
C1620	4359042	Carrying Case	265



Model	Article Nr.	Description	GBP
CABLE REEL 25M BL	4343731	25M Blue, Ground/Earth Cable Reel, 25M Wire	82
CABLE REEL 25M GR	4343746	25M Green, Ground/Earth Cable Reel, 25M Wire	82
CABLE REEL 50M RD	4343754	50M Red, Ground/Earth Cable Reel, 50M Wire	91
EARTH STAKE	4325492	Geo Earth Ground Tester, Earth stake	82
EI-1623	2577115	Stakeless Clamp Set For 1623,Consists of EI-162X and EI-162AC	819
EI-1625	2577126	Stakeless Clamp Set,With EI-162X,EI-162AC and 2-3 Wire Cable	984
EI-162BN	2577159	12.7 Inch (320mm) split core transformer	2419
ES-162P3-2	4359377	Earth Ground Stake Set for 3 Pole Measurement	313
ES-162P4-2	4359389	Earth Ground Stake Set for 4 Pole Measurement	415
FLUKE-1623-2	4325155	Basic Geo Earth Ground Tester	1693
FLUKE-1623-2 KIT	4325170	Basic Geo Earth Ground Tester, Kit	2793
FLUKE-1625-2	4325162	Advanced Geo Earth Ground Tester	2710
FLUKE-1625-2 KIT	4325181	Advanced Geo Earth Ground Tester, Kit	3947
FLUKE-1630-2	4829515	Earth Ground Loop and Leakage Clamp (non FC)	1671
FLUKE-1630-2 FC	4829532	Earth Ground Loop and Leakage Clamp	1671
<b>Indoor Air Quality Tools</b>			
FLUKE-922	2679822	Airflow Meter	824
FLUKE-922/KIT	2679831	Airflow Meter Kit	965
FLUKE-971	2418208	Temperature Humidity Meter	326
FLUKE-985	4131397	Airborne Particle Counter	5723
FLUKE-CO-205	664714	Aspirator Kit	221
FLUKE-CO-220	664711	Carbon Monoxide Meter	738
PT12	2740212	Pitot Tube, 12	139
RLD2	3387163	Leak Detector Flashlight	73
<b>Digital Thermometers</b>			
80PR-60	2148313	RTD Temperature Probe (Fluke 66/68)	95
FL62MAX+/323/1AC	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	295
FLUKE-116/62 MAX+	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	374
FLUKE-51-2 50HZ	1281142	Thermometer	385
FLUKE-52-2 50HZ	1281139	Thermometer	518
FLUKE-53-2 B 50HZ	3821096	Single Input Thermometer, 50Hz	572
FLUKE-53-2 B 60HZ	3821062	Single Input Thermometer, 60Hz	572
FLUKE-54-2 B 50HZ	3821081	Dual Input Thermometer, 50Hz	693
FLUKE-54-2 B 60HZ	3821070	Dual Input Thermometer, 60Hz	693
FLUKE-561	2558118	Multipurpose Thermometer	190
FLUKE-566	2837799	Multipurpose Thermometer	532
FLUKE-568	2837806	Multipurpose Thermometer	678
FLUKE-568EX	4321662	Intrinsically safe Infrared Thermometer	1624
FLUKE-572-2	4328074	Infrared Thermometer	798
FLUKE-62 MAX	4130474	Infrared thermometer	115
FLUKE-62 MAX +	4130488	Infrared Thermometer	133
FLUKE-64 MAX	4856105	Multifunction IR Thermometer 20:1 D:S	171
T5-600/62MAX+/1ACE	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	311
<b>Industrial Imaging</b>			
EDBC290	5077735	EDBC290, EXTERNAL DUAL BAY CHARGER W/ POWER ADAPTER & CONNECTORS	427
FLK-3.8MM/1M PROBE	4962690	3.8 mm Scope, 1 m Probe, Forward View	791

Model	Article Nr.	Description	GBP
FLK-5.5MM/0.7M ART	5344767	FLK-5.5MM,0.7M SCOPE, BORESCOPE PROBE ACC- 0.7M SCOPE W/ ARTICULATING PROBE	1495
FLK-5.5MM/1M PROBE	4962713	5.5 mm Scope, 1 m Probe, Dual View	571
FLK-8.5MM/1.2M PROBE	4962749	8.5 mm Scope, 1.2 m Probe, Dual View	449
FLK-8.5MM/3M PROBE	4962708	8.5 mm Scope, 3 m Probe, Dual View	670
FLK-9MM/20M PROBE	4962760	9 mm Scope, Forward View, 20 m Probe Reel	2230
FLK-DS NECK STRAP	4962772	DS 7XX Neckstrap	64
FLK-DS703 FC	4962665	High Resolution Diagnostic Videoscope with FC	2639
FLK-II900	5075603	Fluke ii900 Sonic Industrial Imager	17383
FLK-II900 ARRAY CVRS	5075982	FLK-II900 ARRAY CVRS, REPL. ARRAY COVERS FLKII900 SONIC INDUSTRIAL IMAGER,SET OF 2	77
FLK-II900 HAND STRAP	5075994	FLK-II900 HAND STRAP,REPL. HAND STRAP FLKII900 SONIC INDUSTRIAL IMAGER	33
FLK-II910	5233904	ii910 Precision Acoustic Imager	21628
<b>Thermal Imagers</b>			
<b>Handheld thermal cameras</b>			
FLK-PTI120 9HZ 400C	5302512	Fluke PTi120 Pocket Thermal Imager; 120x90; 9HZ; 400C	784
FLK-TIS20+ 9HZ	5124518	Fluke TiS20+ Thermal Imager; 120x90; 9HZ	1270
FLK-TIS20+ MAX 9HZ	5206249	Fluke TiS20+ MAX Thermal Imager; 120x90; 9HZ	1501
FLK-TIS55+ 27HZ	5160004	Fluke TiS55+ Thermal Camera 27HZ	2543
FLK-TIS55+ 9HZ	5159990	Fluke TiS55+ Thermal Camera 9HZ	2543
<b>High resolution thermal cameras</b>			
FLK-TI480-PRO 60HZ	4947326	Fluke Ti480 PRO 60Hz Thermal Imager	11022
FLK-TI480-PRO 9HZ	4947332	Fluke Ti480 PRO 9Hz Thermal Imager	11022
FLK-TIS60+ 30HZ	5133399	Fluke TiS60+ Infrared Camera 30Hz	3350
FLK-TIS60+ 9HZ	5133402	Fluke TiS60+ Infrared Camera 9Hz	3350
FLK-TIS75+ 27HZ	5160043	Fluke TiS75+ Thermal Camera 27HZ	4239
FLK-TIS75+ 9HZ	5160037	Fluke TiS75+ Thermal Camera 9HZ	4239
FLK-TIX580 60HZ	4842073	Thermal Imager; 640x480; 60 HZ, SR	14851
FLK-TIX580 9HZ	4841945	Thermal Imager; 640x480; 9 HZ, SR	13864
<b>High definition mounted thermal cameras</b>			
FLK-0.75X-WIDE-LENS	4961174	Wide Angle Infrared Lens	1279
FLK-2X- LENS	4961163	2x Telephoto Infrared Smart Lens	2504
FLK-4X-LENS	4961188	4x Telephoto Infrared Smart Lens	5644
FLK-RSE300/C 60HZ	5293715	Fluke RSE300 Mounted Infrared Camera	12376
FLK-RSE300/C 9HZ	5293732	Fluke RSE300 Mounted Infrared Camera	12376
FLK-RSE600/C 60HZ	5293744	Fluke RSE600 Mounted Infrared Camera	17783
FLK-RSE600/C 9HZ	5293767	Fluke RSE600 Mounted Infrared Camera	17783
FLK-RSE-MB	4961344	Fluke Infrared Camera Mounting Bracket	156
FLK-RSE-ST	4973844	Infrared Camera Mounting Stand	183
<b>Thermal Imagers Accessories (general)</b>			
FLK-LENS/25MAC2	4607064	25Micron Macro IR lens for TiX560-TiX520	4603
FLK-LENS/4XTELE2	4607058	4x Telephoto IR lens for TiX560-TiX520-Ti400-Ti300-Ti200	6371
FLK-LENS/TELE2	4335350	Telephoto Infrared Lens (Ti200/Ti300/Ti400)	1714
FLK-LENS/WIDE2	4335361	Wide-angle Infrared Lens (Ti200/Ti300/Ti400)	1582
FLK-MACRO-LENS	4961195	Macro Infrared Lens	3798
FLK-TI-BLUETOOTH	4603258	Bluetooth headset	105

Model	Article Nr.	Description	GBP
FLK-TI-SBC3B	4354922	Charging base (Ti200/Ti300/Ti400)	261
FLK-TI-SBP3	3440365	Extra battery (Ti32/TiR32)	174
FLK-TI-TRIP0D2	3996517	Mounting Base	130
FLK-TI-TRIP0D3	4335389	Tripod mounting base accessory	130
FLK-TI-VISOR2	3996500	Sun Visor	105
FLK-TI-VISOR3	4335377	Thermal imager visor	105
FLK-TIX5X-LENS CAP	4550697	Lens cap	21
FLUKE-TIX5XX HAND	4574703	Adjustable hand strap	21
FLUKE-TIX5XX-HDMI	4615511	HDMI video cable	25
FLUKE-TIX5XX-NECK	4574715	Adjustable neck strap	41
FLUKE-TIX5XX-SBP4	4597142	Additional Smart Battery	169
TI20-RBP	2577796	Rechargeable Battery Pack (Ti20)	210
TI-CAR CHARGER	3039779	Ti Car Charger (TiR/TiR1/Ti10/Ti20/Ti25)	130
<b>Thermal Imagers IR-Windows</b>			
FLK-050-CLKT	3460346	50mm C-Range IR Windows, Kwik twist	204
FLK-075-CLKT	3460387	75 mm C-Range IR Window, Kwik Twist	258
FLK-100-CLKT	3460439	100mm C-Range IR Window, Kwik Twist	352
FLUKE-CV200	4326955	50mm IR Window, hand turn door latch	252
FLUKE-CV300	4326962	75mm IR Windows, hand turn door latch	352
FLUKE-CV301	4338164	75mm IR Windows, security turn door latch	352
FLUKE-CV400	4326996	100 mm IR Windows, hand turn door latch	487
FLUKE-CV401	4338173	100 mm IR Windows, security turn door latch	500
<b>ScopeMeters</b>			
<b>Industrial ScopeMeter</b>			
FLUKE-123B/EU	4755659	Industrial ScopeMeter 20MHZ, EU	1682
FLUKE-123B/EU/S	4755890	Industrial ScopeMeter + SCC 20MHZ, EU	2131
FLUKE-123B/INT	4755710	Industrial ScopeMeter 20MHZ, INT	1682
FLUKE-123B/INT/S	4755953	Industrial ScopeMeter + SCC 20MHZ, INT	2131
FLUKE-123B/UK	4755671	Industrial Scopemeter 20Mhz, Uk	1682
FLUKE-123B/UK/S	4755911	Industrial Scopemeter + Scc 20Mhz, Uk	2131
FLUKE-124B/EU	4755731	Industrial ScopeMeter 40MHZ, EU	2020
FLUKE-124B/EU/S	4755975	Industrial ScopeMeter + SCC 40MHZ, EU	2466
FLUKE-124B/INT	4755793	Industrial ScopeMeter 40MHZ, INT	2020
FLUKE-124B/INT/S	4756031	Industrial ScopeMeter + SCC 40MHZ, INT	2466
FLUKE-124B/UK	4755754	Industrial Scopemeter 40Mhz, Uk	2020
FLUKE-124B/UK/S	4755994	Industrial Scopemeter + Scc 40Mhz, Uk	2466
FLUKE-125B/EU	4755818	Industrial ScopeMeter 40MHZ, EU	2409
FLUKE-125B/EU/S	4756054	Industrial ScopeMeter + SCC 40MHZ, EU	2859
FLUKE-125B/INT	4755876	Industrial ScopeMeter 40MHZ, INT	2409
FLUKE-125B/INT/S	4756112	Industrial ScopeMeter + SCC 40MHZ, INT	2859
FLUKE-125B/UK	4755834	Industrial Scopemeter 40Mhz, Uk	2409
FLUKE-125B/UK/S	4756079	Industrial Scopemeter + Scc 40Mhz, Uk	2859
<b>190 Series ScopeMeters</b>			
FLUKE-190-062-III	5282331	ScopeMeter 190-062-III Test Tool	3449
FLUKE-190-062-III-S	5282354	ScopeMeter 190-062-III/S Test Tool with kit	3926
FLUKE-190-102-III	5282368	ScopeMeter 190-102-III Test Tool	4299
FLUKE-190-102-III-S	5282379	ScopeMeter 190-102-III/S Test Tool with kit	4773

Model	Article Nr.	Description	GBP
FLUKE-190-104-III	5282393	ScopeMeter 190-104-III Test Tool	4714
FLUKE-190-104-III-S	5282417	ScopeMeter 190-104-III/S Test Tool with kit	5191
FLUKE-190-202-III	5282439	ScopeMeter 190-202-III Test Tool	4874
FLUKE-190-202-III-S	5282442	ScopeMeter 190-202-III/S Test Tool with kit	5350
FLUKE-190-204-III	5282463	ScopeMeter 190-204-III Test Tool	5432
FLUKE-190-204-III-S	5282474	ScopeMeter 190-204-III/S Test Tool with kit	5908
FLUKE-190-502-III	5282495	ScopeMeter 190-502-III Test Tool	5295
FLUKE-190-502-III-S	5282508	ScopeMeter 190-502-III/S Test Tool with kit	5716
FLUKE-190-504-III	5282513	ScopeMeter 190-504-III Test Tool	5700
FLUKE-190-504-III-S	5282524	ScopeMeter 190-504-III/S Test Tool with kit	6124
<b>Motor Drive Analyzers</b>			
FLUKE-MDA-550-III	5282560	MDA-550 Motor Drive Analyzer	7583
SB-500	5011046	Shaft brushes set, repl brushes for SVS-500 and MDA-500	329
SVS-500	5011031	Shaft voltage set and magnetic base	441
<b>ScopeMeter Accessories</b>			
AC120	646163	Heavy Duty Alligator Clips	60
AS400	3894880	Probe Extension Set, for VPS400 Probes	135
BB120	646171	Banana to BNC Adapter Plug	63
BC190/830	4821057	Fluke BC190/830 Universal Mains-Power Adapter	226
BHT190	3379374	Set of Break-out Adapters	372
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	125
BP190	677390	NiMH Battery Pack (190 Series)	266
BP290	4025762	Battery Pack Single Cap 190-series II	315
BP291	3894688	Battery Pack, Fluke 190 Series	404
C120B	4744391	Soft carrying case for 120B series	152
C125	646858	Soft Meter Case	63
C190	677401	Hard Case (190 Series)	328
C195	677408	Soft Case	311
C290	3894803	Hard-Shell Carrying Case	275
CS20MA	677393	Current Shunt 4-20 mA	120
CXT293	5292356	RUGGED PROTECTIVE CARRYING CASE, 190-III SERIES	229
EBC290	3894906	External Battery Charger	127
FLUKEVIEW-2 SCM	5292374	SOFTWARE, FLUKEVIEW-2 SCOPEMETER PC SOFTWARE PACKAGE	270
HC120	646668	Hook Clips	72
HC200	2086410	Hook Clips	50
HH290	3894844	Hanging Hook, ScopeMeter Series 190 II	91
MA190	1567481	Medical Accessory Kit (190 Series)	565
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	204
PM9080/101	1641983	Serial Interface Adapter/Cable (RS232)	335
PM9081/001	916093	Dual Banana Plug to Female BNC Adapter	64
PM9082/001	916163	Dual Banana Jack to Male BNC Adapter	71
PM9091/001	935598	Coaxial BNC Cables (1.5 m)	152
PM9092/001	935601	Coaxial BNC Cables (0.5 m)	130
PM9093/001	935593	Male BNC to Female BNC Adapter	94
RS120-III	4023947	Probe Accessory Replacement Set	135
RS400	3894867	Probe Replacement Set, for VPS400 Probes	105
RS500	4025886	Probe accessory replacement set for VPS500 probes	187

Model	Article Nr.	Description	GBP
SCC 198	2100208	Automotive Accessory Kit (190 Series)	1113
SCC120B	4744423	Software soft carry case accessory kit 120B series	561
SCC190EFG	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	807
SCC290	3894826	Software and Carrying Case for 190 Series II	520
SCC293	5292363	SOFTWARE, CXT293 CASE AND WI/FI CONNECTIVITY KIT, 190-III SERIES	475
SCC298	4138312	Automotive troubleshooting Kit 190-Series-II	1187
SP120B	4744414	Screen protector for 120B series	54
STL120-III	4023901	Shielded Test Lead	236
STL120-IV	4744340	Shielded test lead set 600V CAT IV	181
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	315
SW90W	3894923	FlukeView Software	471
TAS90	614187	Automotive Accessory Set (120/190 Series)	84
TRM50	4025864	50 Ohm feed-through terminator BNC	224
UA120	4744384	USB Connector adapter	54
VPS101	3086317	1:1 Voltage Probe Set, black, 30 MHz, 1.2m	286
VPS210-G	3086247	10:1 Voltage Probe Set, grey, 200 MHz, 1.2m	286
VPS210-R	3086235	10:1 Voltage Probe Set, 1 red, 200 MHz, 1.2m	286
VPS212-G	3086286	10:1 Voltage Probe Set, grey, 200 MHz, 2.5m	286
VPS212-R	3086273	10:1 Voltage Probe Set, red, 200 MHz, 2.5m	286
VPS220-G	3086300	100:1 Voltage Probe Set, grey, 200 MHz, 1.2m	286
VPS220-R	3086299	100:1 Voltage Probe Set, red, 200 MHz, 1.2m	286
VPS40-III	4023920	Voltage Probe	148
VPS41	4744378	Voltage probe set 40 MHz 600V CAT IV	174
VPS410-II-B	4276937	Industrial Voltage Probe Set 500 MHz 10:1 Blue	253
VPS410-II-G	4276943	Industrial Voltage Probe Set 500 MHz 10:1 Grey	253
VPS410-II-R	4276928	Industrial Voltage Probe Set 500 MHz 10:1 Red	253
VPS410-II-V	4276955	Industrial Voltage Probe Set 500 MHz 10:1 Green	253
VPS510-B	4025796	Voltage probe set 500 MHZ 10:1 Blue	257
VPS510-G	4025801	Voltage probe set 500 MHZ 10:1 Grey	257
VPS510-R	4025781	Voltage Probe set 500 MHZ 10:1 Red	257
VPS510-V	4025812	Voltage probe set 500 MHZ 10:1 Green	257
<b>Power Quality Tools</b>			
1742-6/UPGRADE	4920964	1742 to 1746 Upgrade	2334
1742-8/UPGRADE	4920973	1742 to 1748 Upgrade	4316
1746-8/UPGRADE	4920986	1746 to 1748 Upgrade	2334
C437-II	4116743	Hard case 430 Series II with rollers	659
FLUKE-1732/B	4706566	Energy Logger, basic version	2690
FLUKE-1732/EUS	4706548	Energy Logger, EU/US version	3014
FLUKE-1732/INTL	4706553	Energy Logger, international version	3014
FLUKE-1734/B	4706582	Energy Logger, advanced version no flexis	3065
FLUKE-1734/EUS	4706594	Energy Logger, EU/US advanced version	3365
FLUKE-1734/INTL	4706608	Energy Logger, international advanced version	3365
FLUKE-1736/B	4563561	3-Phase Poser Logger, basic version	4373
FLUKE-1736/EUS	4534519	3-Phase Power Logger, EU/US version	4505
FLUKE-1736/EUS-GOLD	4891678	Fluke 1736 Three-Phase Power Quality Logger Gold Edition	3213
FLUKE-1736/INTL	4563550	3-Phase Power Logger, International version	4505

Model	Article Nr.	Description	GBP
FLUKE-1738/B	4588378	3-Phase Power Logger, advanced version no flexis	4199
FLUKE-1738/EUS	4563577	3-Phase Power Logger, EU/US Advanced version including flexis	5296
FLUKE-1738/INTL	4588384	3-Phase Power Logger, international advanced version	5296
FLUKE-1742/15/EUS	4920613	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	4455
FLUKE-1742/15/INTL	4920672	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	4455
FLUKE-1742/30/EUS	4920651	Power Quality Logger with 60 cm 3,000A iflex, EUS version	4455
FLUKE-1742/30/INTL	4920685	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	4455
FLUKE-1742/B/EUS	4920660	Power Quality Logger without iFlex, EUS version	4071
FLUKE-1742/B/INTL	4920697	Power Quality Logger without iFlex, INTL version	4071
FLUKE-1746/15/EUS	4920703	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	6110
FLUKE-1746/15/INTL	4920732	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	6110
FLUKE-1746/30/EUS	4920715	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	6110
FLUKE-1746/30/INTL	4920744	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	6110
FLUKE-1746/B/EUS	4920726	Power Quality Logger without iFlex, EUS version	5728
FLUKE-1746/B/INTL	4920759	Power Quality Logger without iFlex, INTL version	5728
FLUKE-1748/15/EUS	4920767	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	7643
FLUKE-1748/15/INTL	4920798	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	7643
FLUKE-1748/30/EUS	4920771	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	7643
FLUKE-1748/30/INTL	4920800	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	7643
FLUKE-1748/B/EUS	4920780	Power Quality Logger without iFlex, EUS version	7258
FLUKE-1748/B/INTL	4920817	Power Quality Logger without iFlex, INTL version	7258
FLUKE-1760 BASIC	2630732	Power Quality Recorder (three-phase), Topas	14746
FLUKE-1760 INTL	2630744	Power Quality Recorder (three-phase), Topas	17080
FLUKE-1760 TR INTL	2637634	Power Quality Recorder (three-phase), Topas	22543
FLUKE-1760TR BASIC	2637629	Power Quality Recorder (three-phase), Topas	20203
FLUKE-1773	5117269	Fluke 1773 Power Quality Analyzer	5545
FLUKE-1773/BASIC	5272757	Fluke 1773/Basic Power Quality Analyzer (No probes)	4938
FLUKE-1775	5117278	Fluke 1775 Power Quality Analyzer	7393
FLUKE-1775/BASIC	5272784	Fluke 1775/Basic Power Quality Analyzer (No probes)	6755
FLUKE-1777	5126630	Fluke 1777 Power Quality Analyzer	9358
FLUKE-1777/BASIC	5272819	Fluke 1777/Basic Power Quality Analyzer (No probes)	8685
FLUKE-430-II/MA	4779032	430-II Motor Analyzer Upgrade Kit	2519
FLUKE-VR1710	3030923	Single-Phase Voltage Quality Recorder	998
<b>Power Quality Tools Accessories</b>			
177X BATT W/HOUSING	5272862	177X LI-ION BATTERY	95
17XX CABLE MARKER	5312406	FLUKE-17XX CABLE MARKER SET	103
3140R	2650136	Clip-on Current Transformer 2A-400A (Fluke 1750)	533
3210-PR-TF-II	4531769	1000A Fluke 1750 Thin flexi 61cm	845
3310-PR-TF-II	4531778	5000A Fluke 1750 Thin flexi 61cm	1178
3PHVL-17XX	5014802	3PHVL-17XX,CABLE ASSEMBLY, VOLTAGE TEST LEAD 3-PHASE+N	111
3PHVL-17XX-5M	5014816	3PHVL-17XX-5M,CABLE ASSEMBLY, VOLTAGE TEST LEAD 3-PHASE+N 5M	155
ANTENNA CABLE	5263915	ANTENNA CABLE, 5M	415
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	125
BP1730-BATTERY	4389436	Li Ion Battery Pack 3.7V 2500mAh (1730)	52
C1777	5307460	C1777 HARD CASE	676
C177X/6000	5307472	C177X SOFT CASE	277
C17XX	4637381	Soft Case	134



Model	Article Nr.	Description	GBP
CS1750/1760	2673962	Soft Case (Fluke 1750/1760)	355
DEMO PQ CASE	4483703	Fluke Power Quality Democase	2444
FLK-1736/UPGRADE EUS	4941258	UPGRADE KIT FOR 1736 TO 1738	774
FLK-174X_3541-HANGER	4890129	Hanger Kit	81
FLK-WIFI/BLE	4591273	Dongle to USB adapter, WiFi/BLE	172
FLUKE MA-C8	4945842	Wall outlet adapter, Fluke-174X	27
FLUKE-1730-CABLE	4395217	Cable,AUX input cable (1730)	31
FLUKE-1730-HANGER	4358028	Hanger kit (1730)	73
FLUKE-174X GPS-REC	4921133	GPS Receiver Antenna	416
FLUKE-1750/CASE	2650124	Hard Case (Fluke 1750)	753
FLUKE-1750/SEAT-L	2673937	Fluke Power Analyze - Additional SEAT LICENSE	1196
FLUKE-1750/SITE-L	2673928	Fluke Power Analyze - Additional SITE LICENCE	5985
FLUKE-17XX AUX	4717827	AUX input adapter, 173X	153
FLUKE-17XX-TL	5016873	FLUKE-17XX-TL,TEST LEAD SET; 1000V CAT III, NONSTACK/STACK 0.18M	45
FLUKE-17XX-TL 2M	5020006	FLUKE-17XX-TL 2M,BLUE, NON-STACKABLE PLUG AND 2X ALLIGATOR CLIPS	35
FLUKE-I400S-EL	4974743	FLUKE-I400S-EL, 17XX 400A CURRENT CLAMP	286
FLUKE-I400S-EL-3PK	4974755	FLUKE-I400S-EL-3PK, 17XX 400A CURRENT CLAMP/3PACK	764
FLUKE-PQ400	4920947	Electrical Measurement Window with 4 x male-male cable 2m	2045
FLUKE-PQ400/B	5075807	Basic Electrical Measurement Window without accessories	1612
FLUKE-PQ-MARKER	5046009	Cable marker set 3P+N+PE	12
FS17X5-TF-II	4531791	3000A 4-PH Fluke 1735 & 1745 Thin flexi set	1980
FS17XX IP65-TF-II	4531804	3000A IP65 4-PH Fluke 1743/4 Thin flexi set	2213
FS17XX-1PH-TF-II	4531819	FS3000A/6000A 4-PH 36-Inch Thin flexi set	514
FS3KA/6KA-TF-4-II	4531828	FS3000A/6000A 4-PH 36-Inch thin flexi set	2066
F7P17XXPQ	4954311	Fused test probes set, Three Phase PQ, AC285, R/B	205
GPS-TIME SYNC	2539223	GPS Time Synchronization Module (Fluke 1760)	514
I17XX-BNC-M2F	5076304	4 pin male to BNC female cable 0.1m (1 piece)	108
I17XX-BNC-M2M	5076297	4 pin male to BNC male cable 2m (1 piece)	108
I17XX-FLEX1.5KIP	4921003	IP65 iFlexi 1.5KA 60 cm	287
I17XX-FLEX1.5KIP/3PK	4921015	IP65 iFlexi 1.5KA 60 cm, 3 Pack	689
I17XX-FLEX1.5KIP/4PK	4921026	IP65 iFlexi 1.5KA 60 cm, 4 Pack	920
I17XX-FLEX1500	4637328	Fluke-17xx iFlexi 1500A 12 IN	192
I17XX-FLEX1500/24	5171005	I17XX-FLEX1500 24 Current Probe	191
I17XX-FLEX1500/3PK	4637337	Fluke-17xx iFlexi 1500A 12 IN, 3 pack	552
I17XX-FLEX1500/4PK	4637411	Fluke-17xx iFlexi 1500A 12 IN, 4 Pack	723
I17XX-FLEX2M-M2M1P	5076285	iFlex® male-male cable 2m, (1 piece)	162
I17XX-FLEX2M-M2M4P	5076272	iFlex® male-male cable 2m, (4 pieces)	619
I17XX-FLEX3000	4637343	Fluke-17xx iFlexi 3000A 24 IN	204
I17XX-FLEX3000/3PK	4637355	Fluke-17xx iFlexi 3000A 24 IN, 3 pack	592
I17XX-FLEX3000/4PK	4637427	Fluke-17xx iFlexi 3000A 24 IN, 4 Pack	776
I17XX-FLEX3KIP	4921032	IP65 iFlexi 3KA 60 cm	287
I17XX-FLEX3KIP/3PK	4921044	IP65 iFlexi 3KA 60 cm, 3 Pack	689
I17XX-FLEX3KIP/4PK	4921067	IP65 iFlexi 3KA 60 cm, 4 Pack	920
I17XX-FLEX5M-EXT	4921116	iFlexi Extension Cable, 5m	172
I17XX-FLEX6000	4637362	Fluke-17xx iFlexi 6000A 36 IN	216
I17XX-FLEX6000/3PK	4637370	Fluke-17xx iFlexi 6000A 36 IN, 3 pack	631
I17XX-FLEX6000/4PK	4637430	Fluke-17xx iFlexi 6000A 36 IN, 4 Pack	824

Model	Article Nr.	Description	GBP
I17XX-FLEX6KIP	4921071	IP65 iFlexi 6KA 90 cm	344
I17XX-FLEX6KIP/3PK	4921080	iFlexi 6KA 90 cm, 3 Pack	806
I17XX-FLEX6KIP/4PK	4921098	iFlexi 6KA 90 cm, 4 Pack	1035
I1A/10A CLAMP PQ1	3345753	1-phase Mini Current Clamp Set	601
I1A/10A CLAMP PQ3	3024413	3-phase Mini Current Clamp Set	659
I1A/10A CLAMP PQ4	3024424	4-phase Mini Current Clamp Set	951
I20/200A CLAMP PQ3	3024451	3-phase Mini Current Clamp Set	659
I20/200A CLAMP PQ4	3024460	4-phase Mini Current Clamp Set	951
I400	2277225	AC Current Clamp (400 A)	193
I400S	2277202	AC Current Clamp (400A)	348
I40S-EL3X	4637396	Fluke-17xx i40s-EL Clamp-on Current Transformer	251
I40S-EL3X/3PK	4637409	Fluke-17xx i40s-EL Clamp-on Current Transformer, 3 pack	674
I430-FLEXI-TF-II	4531725	6000A Fluke 430 Thin Flexi 61cm	548
I430-FLEXI-TFII-4P	4531733	6000A Fluke 430 Thin Flexi 61cm 4 Pack	1640
I430-FLX-TFII-12	4621205	Iflex 6000A probe, 12 "(30cm)	490
I430-FLX-TFII-48	4621231	Iflex 6000A probe, 48 "(122cm)	606
I5A/50A CLAMP PQ1	3345766	1-Phase 5A/50A Mini Current Clamp set for PQ	601
I5A/50A CLAMP PQ3	3024436	3-phase Mini Current Clamp Set	659
I5A/50A CLAMP PQ4	3024449	4-phase Mini Current Clamp Set	951
I5S	2508467	AC Current Clamp (5 A)	646
I5SPQ3	2457508	AC Current Clamp (5 A), 3-pack	1534
I5S-PR	3949761	1750, 5A Current Clamp	427
IEEE519/REPORT	4589748	SOFTWARE LICENSE FOR IEEE519 REPORTING	578
IP65 ADAPTER SET	4946241	IP65 rated Voltage Connector	287
MBX USB-RS232	2539565	EPO328Z, USB to Serial RS232 Adapter	74
MP1-3R/1B	4944790	3 red/1 black Magnet probe for 4 mm banana	115
MP1-MAGNET PROBE 1	4589220	Magnet probes for 4 mm banana, set of 4	115
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	204
PM9080/101	1641983	Serial Interface Adapter/Cable (RS232)	335
TLS430	2157713	Test Leads and Alligator Clips (4 black, 1 green) - 430 Series	154
TPS CLAMP 10A/1A	2540445	Clip-on Current Transformer 10A/1A (Fluke 1760)	572
TPS CLAMP 200/20	2540450	Clip-on Current Transformer 200A/20A (Fluke 1760)	572
TPS CLAMP 50A/5A	2540461	Clip-on Current Transformer 50A/5A (Fluke 1760)	572
TPS FLEX 18-TF-II	4531837	100/500A Fluke 1760 Thin Flexi 45cm (18in)	617
TPS FLEX 24-TF-II	4531843	200/1000A Fluke 1760 Thin Flexi 61cm (24in)	617
TPS FLEX 36-TF-II	4531855	3000/6000A Fluke 1760 Thin Flexi 91cm (36in)	1233
TPS SHUNT 1A	2540548	A680501054, Shunt 1 A AC/DC	476
TPS SHUNT 20MA	2540553	Shunt 20mA AC/DC (Fluke 1760)	476
TPS VOLTPROBE 100V	2540624	Voltage Probe 100V (Fluke 1760)	409
TPS VOLTPROBE 10V	2540636	Voltage Probe 10V (Fluke 1760)	409
TPS VOLTPROBE 1KV	2540649	Voltage Probe 1000V (Fluke 1760)	747
TPS VOLTPROBE 400V	2540660	Voltage Probe 400V (Fluke 1760)	409
TPS VOLTPROBE 600V	2540697	Voltage Probe 600V (Fluke 1760)	409
TPS/MBX DOLPH RED	2540744	EPO326Z, Dolphin Clip, Red	49
U1500S/APC	5132942	Fluke U1500s High Voltage Differential Probe	779
VL1735/45	3276205	Banana 4-Phase Voltage Lead set for Fluke-1735/45	316
WI-FI/BLE MODULE	5280639	WI-FI/BLE MODULE FLUKE-177X	124

Model	Article Nr.	Description	GBP
<b>Power Analyzers</b>			
<b>Norma 4000</b>			
FLUKE-N4K 1PP42	3108534	1 PH N4k power analyzer w/42	6995
FLUKE-N4K 2PP42I	3387174	2 PH N4K Power Analyzer w/42/IFC2	9891
FLUKE-N4K 3PP42	3108541	3 PH N4k power analyzer w/42	11827
FLUKE-N4K 3PP42B	3110957	3 PH N4k power analyzer w/42BP	13104
FLUKE-N4K 3PP42I	3108552	3 PH N4k power analyzer w/42/IFC2	14123
FLUKE-N4K 3PP42IB	3110969	3 PH N4k power analyzer w/42BP/IFC2	15392
FLUKE-N4K 3PP42IP	3108565	3 PH N4k power analyzer w/42/IFC2 & PI1	17086
FLUKE-N4K 3PP42IPB	3110978	3 PH N4k power analyzer w/42BP/IFC2 & PI1	18793
FLUKE-N4K 3PP50	3108576	3 PH N4k power analyzer w/50	18793
FLUKE-N4K 3PP50I	3108583	3 PH N4k power analyzer w/50/IFC2	21120
FLUKE-N4K 3PP50IP	3108590	3 PH N4k power analyzer w/50/IFC2 & PI1	23423
FLUKE-N4K 3PP52IB	3312894	3 PH N4k power analyzer w/52BP/IFC2	26165
FLUKE-N4K 3PP54I	3108601	3 PH N4k power analyzer w/54/IFC2	19490
FLUKE-N4K 3PP54IP	3108612	3 PH N4k power analyzer w/54/IFC2 & PI1	22264
<b>Norma 5000</b>			
FLUKE-N5K 3PP50	3108620	3 PH N5k power analyzer w/50	23123
FLUKE-N5K 3PP50I	3108635	3 PH N5k power analyzer w/50/IFC2	25375
FLUKE-N5K 3PP50IP	3108647	3 PH N5k power analyzer w/50/IFC2 & PI1	28918
FLUKE-N5K 3PP50IR	3387195	3PH N5K PowerAnalyzer w/50/IFC2/PRNTR	29227
FLUKE-N5K 3PP54	3108658	3 PH N5k power analyzer w/54	21622
FLUKE-N5K 3PP54I	3108664	3 PH N5k power analyzer w/54/IFC2	23876
FLUKE-N5K 3PP54IP	3108673	3 PH N5k power analyzer w/54/IFC2 & PI1	26876
FLUKE-N5K 3PP54IR	3312941	3 PH N5K power analyzer w/54/IFC2/printer	26015
FLUKE-N5K 3PP54R	3312934	3 PH N5K power analyzer w/54/printer	23272
FLUKE-N5K 3PP64	3108686	3 PH N5k power analyzer w/64	26124
FLUKE-N5K 3PP64I	3108699	3 PH N5k power analyzer w/64/IFC2	28918
FLUKE-N5K 3PP64IP	3108702	3 PH N5k power analyzer w/64/IFC2 & PI1	31378
FLUKE-N5K 3PP64IPR	3312976	3 PH N5K power analyzer w/64/IFC2 & PI1/printer	33029
FLUKE-N5K 3PP64IR	3312965	3 PH N5K power analyzer w/64/IFC2/printer	30033
FLUKE-N5K 3PP64R	3312952	3 PH N5K power analyzer w/64/printer	27777
FLUKE-N5K 4PP54	3108716	4 PH N5k power analyzer w/54	25673
FLUKE-N5K 4PP54IP	3108725	4 PH N5k power analyzer w/54/IFC2 & PI1	31546
FLUKE-N5K 6PP42IB	3312929	6 PH N5K power analyzer w/42BP/IFC2	32002
FLUKE-N5K 6PP42IBR	3313044	6 PH N5K power analyzer W/42BP/IFC2/printer	33183
FLUKE-N5K 6PP50I	3312907	6 PH N5k power analyzer w/50/IFC2	42667
FLUKE-N5K 6PP50IP	3312918	6 PH N5K power analyzer w/50/IFC2 & PI1	46585
FLUKE-N5K 6PP50IPR	3313015	6 PH N5K power analyzers W/50/IFC2 & PI1/printer	49842
FLUKE-N5K 6PP50IR	3313003	6 PH N5K power analyzers w/50/IFC2/printer	46843
FLUKE-N5K 6PP54I	3108733	FLUKE-N5K 6PP54I,6 PH N5K POWER ANALYZER W/54/IFC2	39465
FLUKE-N5K 6PP54IP	3108740	FLUKE-N5K 6PP54IP,6 PH N5K POWER ANALYZER W/54/IFC2 & PI1	42512
FLUKE-N5K 6PP54IPR	3312990	6 PH N5K power analyzer w/54/IFC2 & PI1/printer	43539
FLUKE-N5K 6PP54IR	3312983	6 PH N5K power analyzer w/54/IFC2/printer	40541
FLUKE-N5K 6PP64I	3108757	6 PH N5k power analyzer w/64/IFC2	45192
FLUKE-N5K 6PP64IP	3108769	6 PH N5k power analyzer w/64/IFC2 & PI1	48192
FLUKE-N5K 6PP64IPR	3313032	6 PH N5K power analyzer w/64/IFC2 & PI1/Printer	49842

Model	Article Nr.	Description	GBP
FLUKE-N5K 6PP64IR	3313026	6 PH N5K power analyzer w/64/IFC2/printer	46843
<b>Norma 4000/5000 Accessories</b>			
FLUKE-N4K RACK KIT	3313059	N4K 19 inch rack mount kit with handles	279
FLUKE-N5K RACK KIT	3313067	N5K 19 inch rack mount kit with handles	258
NORMA 32A CABLES	3024689	Cables for 32A planar shunt	271
NORMA 32A SHUNT	3024677	32A planar shunt	1019
NORMA LG SHUNT/CBL	3024692	LG Shunt Cables for High Current Shunts	409
NORMA STAR POINT	3024704	External accessory box	1019
<b>Vibration Testers</b>			
81OPA	3986002	AC Power Adapter with International Plug Set	100
81OQDC	3530837	Quick Disconnect Cable	181
81OS	3530828	Sensor	1899
81OSMM	3530862	Sensor Magnet Mount	253
81OSMP	3530855	Sensor Mounting Pads (10-pack)	33
FLUKE-805	4094385	Vibration Meter	2059
FLUKE-805 FC	4489229	Vibration Meter with Fluke Connect	2059
FLUKE-805 FC/805 ES	4918373	Vibration tester package	2790
FLUKE-805/805 ES	4918364	Vibration tester package	2560
FLUKE-805/ES	4636786	External Vibration Sensor	1197
FLUKE-810	3542635	Vibration Tester	11876
FLUKE-820-2	4550041	LED Stroboscope	1133
FLUKE-830/MAGNET	4528249	Magnetic Bracket	1025
FLUKE-830/SHIMS	4551330	Laser Alignment Tool, Shims	1019
FLUKE-831	5346724	Fluke 831 Laser Shaft Alignment Tool	7541
FLUKE-835	5255306	Fluke 835 Laser Belt Alignment Tool	1536
SBP810	3530843	Smart Battery Pack	316
<b>Process Calibrators</b>			
<b>700 Series Process Calibrators</b>			
FLK-729 150G	4856983	Automatic Pressure Calibrator (10 Bar)	10409
FLK-729 150G FC	4856894	Automatic Pressure Calibrator, w/FC (10 Bar)	10409
FLK-729 300G	4856976	Automatic Pressure Calibrator (20 Bar)	10409
FLK-729 300G FC	4856882	Automatic Pressure Calibrator, w/FC (20 Bar)	10409
FLK-729 30G	4856990	Automatic Pressure Calibrator (2 Bar)	10409
FLK-729 30G FC	4856907	Automatic Pressure Calibrator , w/FC (2 Bar)	10409
FLK-789/IR3000FC	4604605	Process Meter and FC connector	1356
FLK-789FC-MA/KIT	4722828	Kit Fluke 789, IR3000FC, A3004FC	1974
FLUKE-154 INTL	4805625	Hart Calibration Assistant	4380
FLUKE-705	665091	Loop Calibrator	854
FLUKE-707	1617262	Loop Calibrator	1085
FLUKE-709	4234350	Precision Loop Calibrator	1168
FLUKE-709H	4234361	Precision HART Loop Calibrator	1743
FLUKE-710	4991049	Fluke-710 Valve Testing Loop Calibrator with HART	2732
FLUKE-712B/EN	4387857	RTD Temperature Calibrator	1357
FLUKE-714B/EN	4387869	TC Temperature Calibrator	1357
FLUKE-715	620101	Volt/mA Calibrator	1642
FLUKE-717 30G	662897	Pressure Calibrator (2 bar)	1669
FLUKE-717 10000G	4058813	Pressure Calibrator (690 bar)	1892

Model	Article Nr.	Description	GBP
FLUKE-717 1000G	2547194	Pressure Calibrator (69 bar)	1732
FLUKE-717 100G	1630430	Pressure Calibrator (7 bar)	1683
FLUKE-717 1500G	2547203	Pressure Calibrator (103.4 bar)	1892
FLUKE-717 15G	4058808	Pressure Calibrator (1 bar)	1660
FLUKE-717 1G	2547166	Pressure Calibrator (68.9 mbar)	1732
FLUKE-717 3000G	2547215	Pressure Calibrator (207 bar)	1892
FLUKE-717 300G	2547175	Pressure Calibrator (20 bar)	1732
FLUKE-717 5000G	2547232	Pressure Calibrator (345 bar)	1892
FLUKE-717 500G	2547182	Pressure Calibrator (34.7 bar)	1732
FLUKE-718 100US	665080	Pressure Calibrator (7 bar)	3051
FLUKE-718 30US	665075	Pressure Calibrator (2 bar)	3051
FLUKE-718 1G	2547148	Pressure Calibrator (68.9 mbar)	3158
FLUKE-718 300G	2547153	Pressure Calibrator (20 bar)	3158
FLUKE-718EX 100	2096322	Intrinsically Safe Pressure Calibrator (7 bar)	4525
FLUKE-718EX 30	2096310	Intrinsically Safe Pressure Calibrator (2 bar)	4525
FLUKE-718EX 300	3023328	Intrinsically Safe Pressure Calibrator (20 bar)	4590
FLUKE-719 100G	3315344	Electric Pressure Calibrator (7 bar)	3978
FLUKE-719 30G	3315332	Electric Pressure Calibrator (2 bar)	3978
FLUKE-719PRO-150G	4353229	Electric Pressure Calibrator, 10 bar	3978
FLUKE-719PRO-300G	4353234	Electric Pressure Calibrator, 20 bar	3978
FLUKE-719PRO-30G	4353218	Electric Pressure Calibrator, 2 bar	3978
FLUKE-720URTD	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	228
FLUKE-721-1601	4353241	Dual Sensor Pressure Calibrator, 1.1 bar, 6.9 bar	2607
FLUKE-721-1603	4353283	Dual Sensor Pressure Calibrator, 1.1 bar, 20 bar	2607
FLUKE-721-1605	4353327	Dual Sensor Pressure Calibrator, 1.1 bar, 34 bar	2607
FLUKE-721-1610	4353366	Dual Sensor Pressure Calibrator, 1.1 bar, 69 bar	2607
FLUKE-721-1615	4353401	Dual Sensor Pressure Calibrator, 1.1 bar, 103 bar	2607
FLUKE-721-1630	4353447	Dual Sensor Pressure Calibrator, 1.1 bar, 200 bar	2607
FLUKE-721-1650	4353486	Dual Sensor Pressure Calibrator, 1.1 bar, 345 bar	2607
FLUKE-721-3601	4353252	Dual Sensor Pressure Calibrator, 2.48 bar, 6.9 bar	2607
FLUKE-721-3603	4353290	Dual Sensor Pressure Calibrator, 2.48 bar, 20 bar	2607
FLUKE-721-3605	4353330	Dual Sensor Pressure Calibrator, 2.48 bar, 34 bar	2607
FLUKE-721-3610	4353375	Dual Sensor Pressure Calibrator, 2.48 bar, 69 bar	2607
FLUKE-721-3615	4353412	Dual Sensor Pressure Calibrator, 2.48 bar, 103 bar	2607
FLUKE-721-3630	4353458	Dual Sensor Pressure Calibrator, 2.48 bar, 200 bar	2607
FLUKE-721-3650	4353499	Dual Sensor Pressure Calibrator, 2.48 bar, 345 bar	2607
FLUKE-721EX-1603	4353309	Dual Sensor Pressure Calibrator, 16, 300 PSIG	3034
FLUKE-721EX-1615	4353420	Dual Sensor Pressure Calibrator, 16, 1500 PSIG	3034
FLUKE-721EX-1630	4353464	Dual Sensor Pressure Calibrator, 16, 3000 PSIG	3034
FLUKE-721EX-3615	4353435	Dual Sensor Pressure Calibrator, 36, 1500 PSIG	3034
FLUKE-721EX-3630	4353473	Dual Sensor Pressure Calibrator, 36, 3000 PSIG	3034
FLUKE-721EX-3650	4353514	Dual Sensor Pressure Calibrator, 36, 5000 PSIG	3034
FLUKE-724/APAC/EMEA	5131125	Temperature Calibrator	2832
FLUKE-725/APAC/EMEA	5131140	Multifunction Process Calibrator	3771
FLUKE-726/APAC/EMEA	5131133	Precision Multifunction Process Calibrator	4505
FLUKE-729/750SW BU	4972518	Fluke-729 300G FC with software	12220
FLUKE-753	3977641	Documenting Process Calibrator	6701

Model	Article Nr.	Description	GBP
FLUKE-754	3405771	Documenting Process Calibrator	8452
FLUKE-771	2646347	Milliamp Process Clamp Meter	740
FLUKE-772	3362352	Milliamp Process Clamp Meter	1023
FLUKE-773	3362365	Milliamp Process Clamp Meter	1401
FLUKE-787B	4777186	Process Meter	1261
FLUKE-789/E	3977194	Fluke 789 ProcessMeter™	1513
<b>Pressure Modules</b>			
700G/TRACK	4123225	Data Logging Cable & Software	538
FLUKE-700G01	4353523	Pressure Gauge, -10" to 10" WC (27 mbar)	967
FLUKE-700G02	4353538	Pressure Gauge, -30" to 30" WC (69 mbar)	967
FLUKE-700G04	4096972	Pressure Gauge, +/- 1 bar	967
FLUKE-700G05	4097514	Pressure Gauge, 2 bar	967
FLUKE-700G06	4097538	Pressure Gauge, 6.9 bar	967
FLUKE-700G07	4097561	Pressure Gauge, 34 bar	967
FLUKE-700G08	4097592	Pressure Gauge, 69 bar	967
FLUKE-700G10	4353654	Pressure Gauge, 140 bar	967
FLUKE-700G27	4097545	Pressure Gauge, 20 bar	967
FLUKE-700G29	4097605	Pressure Gauge, 200 bar	967
FLUKE-700G30	4097610	Pressure Gauge, 345 bar	967
FLUKE-700G31	4097622	Pressure Gauge, 690 bar	967
FLUKE-700GA27	4353577	Pressure Gauge, 20 bar absolute	967
FLUKE-700GA4	4353545	Pressure Gauge, 1 bar absolute	967
FLUKE-700GA5	4353550	Pressure Gauge, 2 bar absolute	967
FLUKE-700GA6	4353561	Pressure Gauge, 6.9 bar absolute	967
FLUKE-700HTPK	4124358	Hydraulic Test Pump Kit, 0 to 690 bar	1360
FLUKE-700HTPK2	4623314	Premium hydraulic test pump kit	1621
FLUKE-700M20TH	4623338	Premium M20 pressure test hose	597
FLUKE-700MTH	4623345	Premium metric pressure test hose	606
FLUKE-700PCK	100062	Pressure Module Calibration Kit	1581
FLUKE-700PTPK	4124364	Pneumatic Test Pump Kit, 0 to 41 bar	1044
FLUKE-700PTPK2	4623306	Premium pneumatic test pump kit	1325
FLUKE-700RG05	4353589	Pressure Gauge, Reference, +2 bar	1056
FLUKE-700RG06	4353592	Pressure Gauge, Reference, 6.9 bar	1056
FLUKE-700RG07	4353605	Pressure Gauge, Reference, 34 bar	1056
FLUKE-700RG08	4353610	Pressure Gauge, Reference, 69 bar	1056
FLUKE-700RG29	4353622	Pressure Gauge, Reference, 200 bar	1056
FLUKE-700RG30	4353631	Pressure Gauge, Reference, 345 bar	1056
FLUKE-700RG31	4353646	Pressure Gauge, Reference, 690 bar	1056
FLUKE-700TTH10K	4636393	Premium pressure transmitter test hose kit, 10K	707
FLUKE-700TTH5K	4623323	Premium pressure transmitter test hose	606
FLUKE-750P00	4352270	Pressure Module (0 - 2.5 mbar)	2078
FLUKE-750P01	4352281	Pressure Module (0 - 25 mbar)	1619
FLUKE-750P01EX	4558658	Ex Pressure Module (0 - 25 Mbar)	2954
FLUKE-750P02	4352750	Pressure Module (0 - 70 mbar)	1619
FLUKE-750P03	4352738	Pressure Module (0 - 350 mbar)	1619
FLUKE-750P04	4352313	Pressure Module (0 - 1 bar)	1619
FLUKE-750P05	4352336	Pressure Module (0 - 2 bar)	1619



Model	Article Nr.	Description	GBP
FLUKE-75OP05EX	4558664	Ex Pressure Module (0 - 2 Bar)	3102
FLUKE-75OP06	4352349	Pressure Module (0 - 7 bar)	1619
FLUKE-75OP06EX	4558673	Ex Pressure Module (0 - 7 Bar)	3102
FLUKE-75OP07	4352360	Pressure Module (0 - 35 bar)	1619
FLUKE-75OP08	4352372	Pressure Module (0 - 70 bar)	1619
FLUKE-75OP09	4352385	Pressure Module (0 - 100 bar)	1619
FLUKE-75OP09EX	4558725	Ex Pressure Module (0 - 100 Bar)	3102
FLUKE-75OP2000	4352397	Pressure Module (0 - 140 bar)	1619
FLUKE-75OP22	4352296	Pressure Module (0 - 70 mbar)	1619
FLUKE-75OP23	4352308	Pressure Module (0 - 350 mbar)	1619
FLUKE-75OP24	4352324	Pressure Module (0 - 1 bar)	1619
FLUKE-75OP24EX	4558686	Ex Pressure Module (0 - 1 Bar)	3102
FLUKE-75OP27	4352351	Pressure Module (0 - 20 bar)	1619
FLUKE-75OP27EX	4558699	Ex Pressure Module (0 - 20 Bar)	3102
FLUKE-75OP29	4352403	Pressure Module (0 - 200 bar)	2560
FLUKE-75OP29EX	4558702	Ex Pressure Module (0 - 200 Bar)	5046
FLUKE-75OP30	4352415	Pressure Module (0 - 340 bar)	2560
FLUKE-75OP31	4352426	Pressure Module (0 - 700 bar)	2560
FLUKE-75OP3IN	4555281	Pressure Module (0 - 7.5 mbar)	1679
FLUKE-75OP5IN	4555296	Pressure Module (0 - 12.5 mbar)	1679
FLUKE-75OPA27	4352471	Pressure Module (0 - 20 bar)	1860
FLUKE-75OPA3	4352432	Pressure Module (0 - 350 mbar)	1860
FLUKE-75OPA4	4352444	Pressure Module (0 - 1 bar)	1860
FLUKE-75OPA4EX	4558716	Ex Pressure Module (0 - 1 Bar)	3201
FLUKE-75OPA5	4352459	Pressure Module (0 - 2 bar)	1860
FLUKE-75OPA6	4352467	Pressure Module (0 - 7 bar)	1860
FLUKE-75OPA7	4352480	Pressure Module (0 - 35 bar)	1860
FLUKE-75OPA8	4352498	Pressure Module (0 - 70 bar)	1860
FLUKE-75OPA9	4352500	Pressure Module (0 - 100 bar)	1860
FLUKE-75OPD10	4352556	Pressure Module (-700 - 700 mbar)	1860
FLUKE-75OPD2	4352539	Pressure Module (-70 - 70 mbar)	1860
FLUKE-75OPD27	4352616	Pressure Module (-1 - 20 bar)	1860
FLUKE-75OPD3	4352542	Pressure Module (-350 - 350 mbar)	1860
FLUKE-75OPD4	4352563	Pressure Module (-1 - 1 bar)	1860
FLUKE-75OPD5	4352574	Pressure Module (-1 - 2 bar)	1860
FLUKE-75OPD50	4352588	Pressure Module (-1 - 3.5 bar)	1860
FLUKE-75OPD6	4352595	Pressure Module (-1 - 7 bar)	1860
FLUKE-75OPD7	4352602	Pressure Module (-1 - 14 bar)	1860
FLUKE-75OPV3	4352517	Pressure Module (-350 mbar)	1860
FLUKE-75OPV4	4352521	Pressure Module (-1 bar)	1860
FLUKE-75OR04	4352625	Pressure Module (0 - 1 bar)	1860
FLUKE-75OR06	4352633	Pressure Module (0 - 7 bar)	1860
FLUKE-75OR07	4352657	Pressure Module (0 - 35 bar)	1860
FLUKE-75OR08	4352669	Pressure Module (0 - 70 bar)	1860
FLUKE-75OR27	4352640	Pressure Module (0 - 20 bar)	1860
FLUKE-75OR29	4352678	Pressure Module (0 - 200 bar)	2744
FLUKE-75OR30	4352684	Pressure Module (0 - 340 bar)	2744

Model	Article Nr.	Description	GBP
FLUKE-75OR31	4352691	Pressure Module (0 - 700 bar)	2744
FLUKE-75ORD27	4352723	Pressure Module (-0.8 - 20 bar)	2009
FLUKE-75ORD5	4352706	Pressure Module (-1 - 2 bar)	2009
FLUKE-75ORD6	4352714	Pressure Module (-1 - 7 bar)	2009
<b>Process Calibrator Accessories</b>			
709H/TRACK	4281225	Logging software with cable	570
754HCC	3829410	HART communication cable for Fluke 754	114
BC-7240	4022655	Battery Charger (753/754)	67
BP7235	668225	NiMH Battery Pack	318
BP7240	4022220	753/754 Spare Battery	225
C789	946694	Soft Meter Case	211
FLUKE-70OHTH-1	2811795	Hydraulic Test Hose	1056
FLUKE-70OHTP-2	4096855	Hydraulic Test Pump, 690 bar	1413
FLUKE-70OILF	1566730	In-Line Filter	122
FLUKE-700-IV	202561	Current Shunt	559
FLUKE-70OLTTP-1	2811763	Low Pressure Test Pump	1179
FLUKE-70OPMP	617131	Pressure Pump (10 bar)	786
FLUKE-70OPRV-1	2811808	Pressure Relief Valve for 70OHTP	1243
FLUKE-70OFTP-1	2811774	Pneumatic Test Pump	797
FLUKE-70OSC	667425	Serial Interface Cable (Fluke 725/725Ex/726)	285
FLUKE-70OTC1	620119	Thermocouple Plug Kits (10 types)	163
FLUKE-70OTC2	620127	Thermocouple Plug Kits (5 types)	132
FLUKE-70OTLK	3829398	Process Test Lead Kit	190
FLUKE-71X	3345825	Hose kit	119
FLUKE-71X-TRAP	4380747	Liquid dirt filter for Fluke 718 and 719 PRO	403
FLUKE-72ORTD	4366669	RTD Probe for 721, 721Ex and 719PRO	335
FLUKE-72OURTDA	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	228
FLUKE-75OSW	4090343	DPC/TRACK2-software	4212
FVF-BASIC	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	194
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	332
HART DRYWELL CABLE	2111088	Cable Kit, HART Drywellcontrol	202
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	60
<b>General Accessories</b>			
<b>Test Leads, Probes and Clips</b>			
80K-15	618113	Probe, Electronic Air Cleaner	333
AC175	4101772	Threaded Alligator Clip Set	36
AC220	1610103	SureGrip Alligator Clip Set	59
AC280	1610115	SureGrip Hook Clip Set	41
AC283A	5130530	SureGrip Pincer Clip Set	55
AC285	1610159	SureGrip Alligator Clip Set	29
AC285-FTP	4073928	Alligator Clips and adaptors (FTP-1, FTPL-1)	37
AC288	4617784	SureGrip™ Terminal block probe	41
AC87	1278079	Heavy Duty Bus Bar Clip Set	59
AC89	873448	Heavy Duty Insulation Piercing Test Clip	61
BP980	1616807	Dual Banana Plug Kit	61
FTL-660	2280204	Fused Test Lead Set	73
FTP-1	3869437	Fuse test probe set	124

Model	Article Nr.	Description	GBP
FTPL-1	3869443	Fuse test probe set with test leads	146
H900	1616818	Test Lead Holder	37
LEADWRAP	4083525	Durable Nylon Hook and Loop Fastener, 3 pack	9
T5-KIT-1	3971169	T5 Tester Accessory Starter Kit	64
T5-RLS	4089137	Replacement Test Lead Set (T5)	33
TL175	3521976	Twist Guard Test Leads	36
TL175E	3565554	Twist Guard Test Leads, 4mm	41
TL220-1	3971178	SureGrip Industrial Test Lead Set	96
TL221	2003602	SureGrip Extension Lead Set	40
TL222	2003616	SureGrip Silicone Test Lead Set	40
TL223-1	3971184	SureGrip Electrical Test Lead Set	94
TL224	1610198	SureGrip Silicone Test Lead Set	38
TL225-1	3971191	Stray Voltage Eliminator test Lead Set	133
TL238	2132831	SureGrip High Energy Test Lead Kit	96
TL27	668571	Heavy Duty Test Lead Set	41
TL40	1590606	Retractable Tip Test Lead Set	60
TL71-1	3971207	TL71, Test Lead Set	36
TL75-1	3971218	TL75, Test Lead Set	31
TL76	2032684	All-in-one Test Lead Set	52
TL80A-1	3971229	TL80A, Test Lead Set	95
TL81A	1277073	Deluxe Electronic Test Lead Kit	196
TL910	1616632	Electronic Test Lead Set (with replacement tips)	97
TL930	1616671	Patch Cords (60 cm)	24
TL932	1616680	Patch Cords (90 cm)	27
TL935	1616698	Patch Cord Kit (60, 90, 120 cm)	66
TL940	1616705	Mini-Hook Test Lead Set	27
TL950	1616710	Mini-Pincer Test Lead Set	41
TL960	1616722	Micro-Hook Test Lead Set	27
TL970	1616793	Hook and Pincer Test Lead Kit	95
TLK1550-RTLK	4112351	Integral test lead & 10 kV clamp	322
TLK-220 EUR	2097022	SureGrip Accessory Kit	178
TLK-225-1	3971234	TLK225, SureGrip Master Set	196
TLK281-1	3971241	TLK281, Automotive Test Lead Kit	178
TLK282-1	3971252	TLK282, DeLuxe Automotive Test Lead Kit	222
TLK287	3045631	Electronic Master Test Lead Kit	226
TLK289 EUR	3092521	Industrial Master Test Lead Kit	231
TLK290	2435092	Test Probe Kit	73
TLK291	2435108	Fused Test Probe Set	79
TP1-1	3971265	TP1, Test Probes	24
TP175	3521983	TwistGuard test Probes, 2MM dia probe tips	26
TP175E	3565568	TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters	31
TP2-1	3971283	TP2, Test Probes	24
TP220-1	3971276	TP220, SureGrip Test Probes	23
TP38	1541636	Slim Reach Test Probe Set (insulated)	24
TP38-2001-OSP	2438858	Slim Reach Test Probe, red	20
TP74	1541649	Lantern Tip Test Probe Set	27
TP80	873455	Electronic Test Probe Set	47

Model	Article Nr.	Description	GBP
TP912	1616644	Replacement tips for TL910	40
TP920	1616659	Test Probe Adapter Kit	61
<b>Current Clamps</b>			
80I-110S	114519	AC/DC Current Clamp (100 A)	939
I1000S	1568487	AC Current Clamp (1000 A)	812
I1010	617735	AC/DC Current Clamp (1000 A)	574
I1010-KIT	2096998	AC/DC Current Clamp (1000 A) with Soft Case	589
I200	664755	AC Current Clamp (200 A)	205
I2000 FLEX	2584912	AC Flexible Current Clamp (2000 A)	385
I200S	664760	AC Current Clamp (200 A)	348
I30	2584920	AC/DC Current Clamp (30A)	491
I3000 FLEX-4PK	2696367	AC Flexible Current Clamp (3000 A), 4-pack	1648
I3000S	657202	AC Current Clamp (3000 A)	866
I3000S FLEX-24	2584888	AC Flexible Current Clamp (3000 A), 610 mm	592
I3000S FLEX-36	2584901	AC Flexible Current Clamp (3000 A), 915 mm	698
I30S	2584935	AC/DC Current Clamp (30A)	698
I310S	2840309	AC/DC Current Clamp (300A)	436
I400	2277225	AC Current Clamp (400 A)	193
I400S	2277202	AC Current Clamp (400A)	348
I40S-PR	3949777	40A Current Clamp (1750)	531
I410	617727	AC/DC Current Clamp (400 A)	329
I410-KIT	2097005	AC/DC Current Clamp (400 A) with Soft Case	373
I6000S FLEX-24	2840311	AC Current Clamp (6000 A)	751
I6000S FLEX-36	2840327	AC Current Clamp (6000 A)	857
I800	2840283	AC Current Clamp (800 A)	277
<b>Temperature Accessories</b>			
80AK-A	2747812	Thermocouple Adapter	39
80BK-A	2747801	Integrated DMM Temperature Probe (Type K)	43
80CJ-M	833046	Male Mini Connectors (Type J)	31
80CK-M	779942	Male Mini Connectors (Type K)	31
80PJ-1	1288191	Bead Probe (Type J)	35
80PJ-9	1288218	General Purpose Probe (Type J)	89
80PJ-EXT	1288234	Extension Wire Kit (Type J)	79
80PK-1	750422	Bead Probe (Type K)	39
80PK-10	3439199	Pipe Clamp Temperature Probe (Type K)	299
80PK-11	2724500	Velcro Temperature Probe	52
80PK-18	3448859	Pipe Clamp Temperature Probe Kit	470
80PK-22	2098684	SureGrip Immersion Probe	134
80PK-24	2098691	SureGrip Air Probe	172
80PK-25	2098706	SureGrip Piercing Probe	152
80PK-26	2098714	SureGrip General Purpose Probe	172
80PK-27	2098723	SureGrip Industrial Surface Probe	494
80PK-3A	874610	Surface Probe (Type K)	283
80PK-8	200360	Pipe Clamp Temperature Probe (Type K)	231
80PK-9	1288229	General Purpose Probe (Type K)	89
80PK-EXT	1288241	Extension Wire Kit (Type K)	79
80PR-60	2148313	RTD Temperature Probe (Fluke 66/68)	95

Model	Article Nr.	Description	GBP
8OPT-25	2104397	SureGrip Piercing Probe	138
8OPT-EXT	1288252	Extension Wire Kit (Type T)	79
8OT-150UA	3190456	Universal Temperature Probe (for DMMs)	375
8OTK	736736	Thermocouple Module (Type K)	189
<b>Cases and Holsters</b>			
C101	2437514	Hard Case	78
C115	2826063	Soft Meter Case	74
C116	2826074	Soft Meter Case	90
C11XT	5308996	Fluke C11XT Protective Hard Case	33
C125	646858	Soft Meter Case	63
C12A	930529	Soft Meter Case	36
C150	4111540	Zippered Soft Carrying Case	36
C1600	2091049	Meter and Accessory Case	50
C1620	4359042	Carrying Case	265
C190	677401	Hard Case (190 Series)	328
C195	677408	Soft Case	311
C23	1663209	Soft Meter Case	33
C25	681114	Soft Meter Case	67
C280	3182785	Soft Meter Case	83
C33	1664120	Soft Meter Case	35
C345	3311173	Soft Case	105
C35	2826056	Soft Meter Case	57
C37XT	5309001	Fluke C37XT Protective Hard Case	44
C43	1663230	Soft Meter Case	104
C50	762823	Soft Meter Case	50
C520A	1629104	Leather Tester Case	76
C550	1547919	Tool Bag	153
C75	865535	Soft Accessory Case	23
C781	619988	Soft Meter Case	113
C789	946694	Soft Meter Case	211
C799	4021731	Soft case for Fluke 75x series	129
C90	466029	Soft Meter Case	49
CAM0-C25	4110632	Camouflage carrying case for Fluke multimeters	48
CXT1000	4628917	Extreme Hard case	227
CXT170	3352567	Rugged Pelican Hard Case	227
CXT280	3352571	Rugged Pelican Hard Case	227
CXT80	3352559	Rugged Pelican Hard Case	227
FLK-C3003	4582928	3-Compartment soft case	51
FLUKEPACK30	4983088	Professional Tool Backpack	187
H15	4111533	Belt Holster for T100 series	35
H3	1608458	Holster (330 Series)	52
H5	649365	Electrical Tester Holster (Fluke T5)	37
H80M	2138458	Holster + Magnetic Hanger	54
H-T6	4910585	T6 Belt Holster	37
TB25	5308970	Fluke TB25 Toolbag	73
<b>Automotive Accessories</b>			
BP880	2150594	BNC to Female Double Stacking Banana Plug	24

Model	Article Nr.	Description	GBP
BP881	2151015	BNC to Male Double Stacking Banana Plug	25
RPM80	880849	Inductive Pick-up	124
SCC 198	2100208	Automotive Accessory Kit (190 Series)	1113
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	315
TAS90	614187	Automotive Accessory Set (120/190 Series)	84
TL28A	1273185	Automotive Test Lead Set	66
TL82	2150636	Automotive Pin and Socket Adapter Set	148
TP40	1567573	Automotive Back Probe Pins (5 pcs) (4 mm)	52
TP81	2149098	Insulation Piercing Clip Set (4 mm)	67
TP82	2149080	Insulation Piercing Clip Set (2 mm)	67
TP88	2149102	Rigid Back Probe Pin Set	22
<b>Other Accessories</b>			
80K-40	382846	High Voltage Probe	348
80K-6	532424	High Voltage Probe	193
EBC290	3894906	External Battery Charger	127
FL-120 EX	4972431	120 lumen intrinsically safe flashlight	93
FL-150 EX	4972446	150 lumen intrinsically safe flashlight	115
FL-45 EX	4972422	45 lumen intrinsically safe flashlight	57
HL-200 EX	4972410	200 lumen intrinsically safe headlamp	115
L200	2096346	Probe Light	31
L205	2098588	Mini Hat Light	37
L206	2098595	Deluxe Hat Light	50
L210	2096379	Probe light and probe extender	52
L215	2096368	SureGrip kit with probe light and probe extender	114
LVD1A	4571403	Volt Light	34
LVD2	2740300	Volt Light	50
SV225	3100477	Stray Voltage Adapter	89
TPAK	1281997	ToolPak, Meter Hanging Kit	52
<b>Fuses</b>			
7017240.0	2279339	Fuse, A:315mA (f), V:1000V, IR:10kA, 6.35x32 mm	12,4
FUSE	740670	Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm	4,05
FUSE	803293	Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm	9,6
FUSE	830828	Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm	8,6
FUSE	943121	Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm	5,35
<b>Software</b>			
FVF-BASIC	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	194
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	358
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	194
FVF-UG	1576741	FlukeView Forms Upgrade	174
SCC190EFG	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	807
SW90W	3894923	FlukeView Software	471
<b>Seminar Boxes</b>			
1/2D-GEN-TRN-1PEXT	5339114	1/2 DAY GENERIC END-USER TRAINING BY FLUKE 1 PERSON ADDITION	112
1/2D-GEN-TRN-4P	5339097	1/2 DAY GENERIC END-USER TRAINING BY FLUKE UPTO 4 PERSONS	445
1/2D-GEN-TRN-6P-OSIC	5339138	1/2 DAY GENERIC END-USER TRAINING BY FLUKE UPTO 6 PERSONS ON SITE IN COUNTRY	1124



Model	Article Nr.	Description	GBP
1D-BS-TRN-VOUCH	5339659	1-DAY-BS 7671 TRAINING VOUCHER FOR 1 PERSON	389
1D-GEN-TRN-1PEXT	5339123	1-DAY GENERIC END-USER TRAINING BY FLUKE 1 PERSON ADDITION	157
1D-GEN-TRN-1P-VOUCH	5339161	1-DAY GENERIC END-USER TRAINING BY FLUKE FOR 1 PERSON (MIN 6 PERSON ATTENDANCE)	247
1D-GEN-TRN-4P	5339106	1-DAY GENERIC END-USER TRAINING BY FLUKE UPTO 4 PERSONS	895
1D-GEN-TRN-6P-OSIC	5339145	1-DAY GENERIC END-USER TRAINING BY FLUKE UPTO 6 PERSONS ON SITE IN COUNTRY	1794
1-GEN-TRN-TRV	5339150	1 GENERIC END-USER TRAINING FOREIGN TRAVEL EXPENSE UNIT	90
3D-BS-TRN-VOUCH	5339667	3-DAY-BS 7671 TRAINING VOUCHER FOR 1 PERSON	1167

Every effort has been made to ensure this guide is as accurate as possible.

Fluke (UK) Ltd. reserve the right to alter details without prior notification.

**Fluke.** *Keeping your world up and running.*<sup>®</sup>

**Fluke UK Ltd**  
 52 Hurricane Way  
 Norwich  
 Norfolk, NR6 6JB  
 United Kingdom  
 Email: cs.uk@fluke.com  
 Phone +44 (0)20 7942 0708

©2023 Fluke Corporation. All rights reserved.  
 Data subject to alteration without notice.  
 03/2023 uken

**Modification of this document is not permitted without written permission from Fluke Corporation.**