

Fluke Test Tools Price List

FLUKE®

Valid from: 02-01-2020

| Model | Art. nr | Description | EUR |
|------------------------------------|---------|---|---------|
| Fluke Connect | | | |
| Fluke Connect - 3000 Series | | | |
| FLK-3000 FC | 4401595 | FC Wireless Digital Multimeter | 314.00 |
| FLK-3000 FC GM | 4467750 | FC Wireless General Maintenance System | 899.00 |
| FLK-3000 FC HVAC | 4465607 | FC Wireless HVAC System | 652.00 |
| FLK-3000 FC IND | 4465599 | FC Wireless Industrial System | 1123.00 |
| FLK-3000FC/TPAK | 4699340 | Fluke 3000FC with TPAK meter hanging kit | 348.00 |
| Fluke 3000FC/EDA2 | 4699333 | Electronics DMM and deluxe accessory kit | 404.00 |
| Fluke 3000FC/1AC-II | 4699302 | Electrician's DMM voltage tester and accessory kit | 448.00 |
| FLK-A3000 FC | 4401588 | FC Wireless AC Current Clamp Module | 202.00 |
| FLK-A3000 FC KIT | 4465618 | FC Wireless Essential Kit with A3000 | 448.00 |
| FLK-A3001 FC | 4459439 | FC Wireless iFlex AC Current Module | 235.00 |
| FLK-A3001 FC KIT | 4465665 | FC Wireless Essential Kit with i3000 | 483.00 |
| FLK-A3002 FC | 4459442 | FC Wireless AC/DC Current Module | 134.00 |
| FLK-A3003 FC | 4629295 | FC Wireless 2000A DC Clamp meter | 561.00 |
| FLK-A3004 FC | 4629301 | FC Wireless 4-20mA DC Clamp meter | 673.00 |
| FLK-T3000 FC | 4401563 | FC Wireless K-Type Temperature Module | 202.00 |
| FLK-T3000 FC KIT | 4465652 | FC Wireless Essential Kit with T3000 | 448.00 |
| FLK-V3000 FC | 4401556 | FC Wireless AC Voltage Module | 213.00 |
| FLK-V3000 FC KIT | 4465641 | FC Wireless Essential Kit with V3000 | 448.00 |
| FLK-V3001 FC | 4459421 | FC Wireless DC Voltage Module | 213.00 |
| FLK-V3001 FC KIT | 4467777 | FC Wireless essential Kit with V3001 | 448.00 |
| FLK-V3003 FC KIT | 4467789 | FC Wireless Kit w. DMM, AC+DC Voltage Modules | 729.00 |
| Fluke Connect - Accessories | | | |
| FLK-FC_SD Card | 4463628 | Fluke Connect Wireless SD Card | 102.00 |
| FLK-PC3000 FC | 4401602 | FC Wireless PC Adapter | 112.00 |
| FLUKE-IR3000FC | 4460436 | Connector, Infrared, FC | 147.00 |
| Digital Multimeters | | | |
| 110 Series Multimeters | | | |
| Fluke 113 | 3088053 | True RMS Multimeter | 135.00 |
| Fluke 114 | 2583552 | True RMS Multimeter | 178.00 |
| Fluke 115 | 2583583 | True RMS Multimeter | 211.00 |
| Fluke 116 | 2583601 | True RMS Multimeter | 253.00 |
| 116/62MAX+ Kit | 4296018 | Fluke HVAC Multimeter and IR Thermometer Combo Kit | 324.00 |
| Fluke 116/323 Kit | 4296029 | Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit | 358.00 |
| Fluke 117 | 2583647 | True RMS Multimeter | 264.00 |
| Fluke 117/323 Kit | 4296034 | Fluke Electrician's Multimeter Combo Kit | 342.00 |
| C50 | 762823 | Soft Meter Case | 44.00 |
| 170 Series Multimeters | | | |
| Fluke 175 | 1592901 | True RMS Multimeter | 253.00 |
| Fluke 177 | 1592874 | True RMS Multimeter | 307.00 |
| Fluke 179 | 1592842 | True RMS Multimeter | 362.00 |
| C90 | 466029 | Soft Meter Case | 44.00 |
| Fluke 179/EDA2/EUR | 3947719 | Electronics Combo Kit | 430.00 |
| Fluke-179-2/IMSK | 4370598 | industrial Multimeter Service kit | 449.00 |
| 200 Series Multimeters | | | |
| Fluke 233 | 3469334 | Remote Display Multimeter | 358.00 |
| Fluke 279FC/iFlex | 4684050 | Wireless TRMS Thermal Multimeter w/iFlex | 999.00 |
| Fluke 279FC I/B | 4989200 | Wireless TRMS Thermal Multimeter with iFlex & extra battery | 1099.00 |
| Fluke 287/EUR | 3947781 | True RMS Electronic Logging Multimeter with TrendCapture | 652.00 |
| Fluke 287/FVF/EUR | 3947796 | FlukeView Forms Combo Kit | 764.00 |
| Fluke 289/EUR | 3947801 | True RMS Industrial Logging Multimeter with TrendCapture | 708.00 |
| Fluke 289/FVF/EUR | 3947812 | Industrial Logging Multimeter and Software Combo Kit | 820.00 |
| C280 | 3182785 | Soft Meter Case | 73.00 |

| Model | Art. nr | Description | EUR |
|------------------------------|---------|--|---------|
| Fluke 287/FVF/IR3000 | 4699316 | Fluke 287 FlukeView® Forms Combo Kit | 843.00 |
| Fluke 289/FVF/IR3000 | 4699325 | Fluke 289 FlukeView® Forms Combo Kit | 899.00 |
| Fluke-289/IMSK | 3449156 | industrial Multimeter Service kit | 699.00 |
| 20 Series Multimeters | | | |
| Fluke 27II/EUR | 3947770 | Industrial Multimeter (IP67) | 569.00 |
| Fluke 28II/EUR | 3947820 | True RMS Industrial Multimeter (IP67) | 569.00 |
| Fluke 28 II Ex | 4017165 | Intrinsically safe true-rms digital multimeter | 1373.00 |
| C25 | 681114 | Soft Meter Case | 63.00 |
| 70 Series Multimeters | | | |
| Fluke 77-4/EUR | 3947835 | Multimeter | 448.00 |
| C90 | 466029 | Soft Meter Case | 44.00 |
| 80 Series Multimeters | | | |
| Fluke 83-V/EUR | 3947847 | Multimeter | 504.00 |
| Fluke 87-V/EUR | 3947858 | True RMS Multimeter | 499.00 |
| Fluke 87-V/E2K/EUR | 3947864 | Industrial Electricians Combo Kit | 599.00 |
| C25 | 681114 | Soft Meter Case | 63.00 |
| Fluke 87V-MAX | 5140033 | industrial True RMS Heavy Duty Multimeter | 549.00 |
| Fluke 87V-MAX/E2 kit | 5160712 | industrial True-RMS Heavy Duty Multimeter E2 kit | 649.00 |
| Fluke-87V/IMSK | 3448783 | industrial Multimeter Service kit | 579.00 |
| Bench Multimeters | | | |
| Fluke 8808A 220V | 2802372 | 5.5 Digit Multimeter | 736.00 |
| Fluke 8808A 240V | 2802385 | 5.5 Digit Multimeter | 736.00 |
| Fluke 8808A/SU 220V | 2802459 | 5.5 Digit Multimeter (software & cable) | 942.00 |
| Fluke 8808A/SU 240V | 2802467 | 5.5 Digit Multimeter (software & cable) | 942.00 |
| Fluke 8808A/TL 220V | 3111085 | 5.5 Digit Multimeter, 2X4W Test Lead Kit | 818.00 |
| Fluke 8808A/TL 240V | 3111097 | 5.5 Digit Multimeter, 2X4W Test Lead Kit | 818.00 |
| Fluke 8845A 220V | 2577352 | 6.5 Digit Precision Multimeter | 1100.00 |
| Fluke 8845A 240V | 2577365 | 6.5 Digit Precision Multimeter | 1100.00 |
| Fluke 8845A/SU 220V | 2675315 | 6.5 Digit Precision Multimeter (incl. software + cable) | 1295.00 |
| Fluke 8845A/SU 240V | 2675332 | 6.5 Digit Precision Multimeter (incl. software + cable) | 1295.00 |
| Fluke 8846A 220V | 2577383 | 6.5 Digit Precision Multimeter | 1445.00 |
| Fluke 8846A 240V | 2577390 | 6.5 Digit Precision Multimeter | 1445.00 |
| Fluke 8846A/SU 220V | 2675367 | 6.5 Digit Precision Multimeter (incl. software + cable) | 1645.00 |
| Fluke 8846A/SU 240V | 2675380 | 6.5 Digit Precision Multimeter (incl. software + cable) | 1645.00 |
| 884X-CASE | 2675552 | Hard Case (8845A/8846A) | 453.00 |
| 884X-RTD | 2675468 | 100 OHM RTD Temperature Probe | 592.00 |
| 884X-SHORT | 2653346 | 4-wire short | 31.90 |
| 884X-USB | 2675479 | USB to RS232 Cable Adapter | 170.00 |
| 884X-1G | 2675534 | USB Memory 1 GB | 41.16 |
| 8845A-EFPT | 2742690 | Extended Fine Point Tip Adapter Set | 20.58 |
| 8845A-TPIT | 2742683 | Test Probe IC Tip Set | 15.44 |
| FVF-UG | 1576741 | FlukeView Forms Upgrade | 146.00 |
| FVF-SC4 | 2687335 | FlukeView Forms Software + Cable (8845A/8846A) | 312.00 |
| FVF-SC5 | 2791314 | FlukeView Forms Basic (8845A/8846A) | 179.00 |
| RS43 | 946470 | Serial Interface Cable | 92.00 |
| TL2X4W-PTII | 2826215 | 2x4 Wire Ohms Test Lead 2 mm Probe Tip | 82.00 |
| TL2x4W-TWZ | 2723629 | 2X4-Wire Ohms Tweezers Test Leads | 103.00 |
| Y8021 | 708289 | IEEE-488 Shielded Interface Cable, 1 m | 466.00 |
| Y8022 | 708297 | IEEE-488 Shielded Interface Cable, 2 m | 545.00 |
| Y8846S | 2675518 | Rack mount kit single (8845A/8846A) | 129.00 |
| Y8846D | 2771721 | Rack mount kit dual (8845A/8846A) | 175.00 |
| Automotive Meters | | | |
| Fluke 88V/A | 2117440 | Automotive Meter Combo Kit | 729.00 |
| Hand Tools | | | |
| IB117L | 5133953 | 117EUR + 3 screwdrivers Bundle (ISLS3+ISLS5+IPHS2) | 269.00 |
| IB117M | 5133966 | 117EUR + 5 screwdrivers Bundle (ISLS3+ISLS5+IPHS2+IPHS1+ISLS8) | 279.00 |
| IB117KEUR | 5195045 | 117 EUR multimeter + Hand Tools Starter Kit | 349.00 |
| IB179L-EGFID | 5133975 | 179 EGFID + 3 screwdrivers Bundle (ISLS3+ ISLS5+ IPHS2) | 369.00 |
| IB179M-EGFID | 5133982 | 179EGFID + 5 screwdrivers Bundle ISLS3+ISLS5+IPHS2+IPHS1+ISLS8 | 379.00 |
| IB179K-EGFID | 5133994 | 179 EGFID + Hand Tool Starter kit Bundle | 469.00 |
| IB179L-EDSNF | 5134004 | 179 EDSNF + 3 screwdrivers Bundle (ISLS3+ ISLS5+ IPHS2) | 369.00 |
| IB179M-EDSNF | 5134019 | 179EDSNF + 5 screwdrivers Bundle ISLS3+ISLS5+IPHS2+IPHS1+ISLS8 | 379.00 |
| IB179K-EDSNF | 5134028 | 179 EDSNF + Hand Tool Starter kit Bundle | 469.00 |
| IB875L | 5134096 | 87-5/EUR + 3 screwdrivers Bundle (ISLS3+ ISLS5+ IPHS2) | 509.00 |
| IB875M | 5134107 | 87-5/EUR + 5 screwdrivers Bundle ISLS3+ISLS5+IPHS2+IPHS1+ISLS8 | 519.00 |
| IB875KEUR | 5195050 | 87V EUR multimeter + Hand Tools Starter Kit | 599.00 |
| IBT6L | 5134118 | T6-1000/EU + 3 screwdrivers Bundle (ISLS3+ ISLS5+ IPHS2) | 289.00 |
| IBT6M | 5134129 | T6-1000/EU+5 screwdrivers Bundle ISLS3+ISLS5+IPHS2+IPHS1+ISLS8 | 299.00 |
| IBT6KEUR | 5195077 | T6-1000 Electrical Tester + Hand Tools Starter Kit | 399.00 |

| Model | Art. nr | Description | EUR |
|-----------|---------|--|--------|
| IB376L | 5134134 | 376 FC + 3 screwdrivers Bundle (ISLS3+ ISLS5+ IPHS2) | 529.00 |
| IB376M | 5134141 | 376 FC + 5 screwdrivers Bundle ISLS3+ISLS5+IPHS2+IPHS1+ISLS8 | 549.00 |
| IB376KEUR | 5195061 | 376 FC Clamp Meter + Hand Tools Starter Kit | 629.00 |
| inLP8 | 5067232 | insulated Long nose /w side cutter, 8 in, 200mm, 1000V | 54.99 |
| inDC8 | 5067244 | insulated High leverage diagonal cutter, 8 in, 200mm, 1000V | 59.99 |
| inPP10 | 5067259 | insulated Pump plier fast adjustable, 10 in, 250 mm, 1000V | 69.99 |
| inCP8 | 5067267 | insulated Linesman combination plier, 8 in, 200 mm, 1000V | 49.99 |
| ISLS3 | 5067271 | insulated Slotted screwdriver 3/32X3 in, 2.5 mm X 75 mm, 1000V | 15.99 |
| ISLS5 | 5067280 | insulated Slotted screwdriver 5/32X4 in, 4 mm X 100 mm, 1000V | 15.99 |
| ISLS8 | 5067298 | insulated Slotted screwdriver 1/4X5 in, 6 mm X 125 mm, 1000V | 23.00 |
| IPHS1 | 5067306 | insulated Phillips screwdriver #1, 3 in, 75 mm, 1000V | 18.00 |
| IPHS2 | 5067314 | insulated Phillips screwdriver #2, 4 in, 100 mm, 1000V | 23.00 |
| ISQS1 | 5067323 | insulated Squared screwdriver #1, 4 in, 100 mm, 1000V | 21.99 |
| ISQS2 | 5067338 | insulated Squared screwdriver #2, 5 in, 125 mm, 1000V | 21.99 |
| IKSC7 | 5067345 | insulated 7 units screwdriver kit, 1000V | 119.00 |
| RUP8 | 5081598 | insulated Hand Tools roll up pouch | 19.99 |
| IKST7 | 5067389 | insulated 5 screwdriver + 3 Plier tools starter kit, 1000V | 239.00 |
| IKPL3 | 5067377 | insulated 3 units Plier kit, 1000V | 149.00 |
| IKPK7 | 5067392 | PACK30 insulated 5 screwdriver + 3 Plier kit, 1000V | 359.00 |
| CPAK8 | 5081580 | insulated Hand Tools pouch case with hanging kit | 39.99 |

| Clamp Meters | | | |
|--------------------|---------|--|--------|
| Fluke 323 | 4152628 | True RMS Clamp Meter | 138.00 |
| Fluke 324 | 4152637 | True RMS Clamp Meter | 180.00 |
| Fluke 325 | 4152643 | True RMS Clamp Meter | 250.00 |
| Fluke 353 | 2840252 | AC/DC True RMS Clamp Meter | 667.00 |
| Fluke 355 | 2840265 | AC/DC True RMS Clamp Meter | 834.00 |
| Fluke 365 | 3790607 | Detachable TRMS Clamp Meter | 277.00 |
| Fluke 368 FC | 4709907 | Wireless leakage current clamp, 40mm jaw | 741.00 |
| Fluke 369 FC | 4709934 | Wireless leakage current clamp, 61mm jaw | 741.00 |
| Fluke 373 | 3790564 | 600A TRMS Clamp Meter | 277.00 |
| Fluke 374FC | 4696001 | 600A AC/DC TRMS Wireless Clamp Meter | 389.00 |
| Fluke 375FC | 4695932 | 600A AC/DC TRMS Wireless Clamp Meter | 465.00 |
| Fluke 376FC | 4695861 | 1000A AC/DC TRMS Wireless Clamp Meter with iFlex | 529.00 |
| Fluke 381 | 3610452 | Remote Display TRMS Clamp Meter | 622.00 |
| Fluke 902 FC | 4695814 | TRMS Wireless HVAC ClampMeter | 312.00 |
| 62MAX+/323/1AC Kit | 4296076 | IR Thermometer, Clamp Meter and Voltage Detector Kit | 269.00 |
| Fluke 116/323 Kit | 4296029 | Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit | 358.00 |
| Fluke i2500-18 | 3676405 | iFlex Probe | 144.00 |
| Fluke i2500-10 | 3676410 | iFlex Probe | 144.00 |
| H3 | 1608458 | Holster (330 Series) | 48.00 |

| Electrical Testers | | | |
|------------------------|---------|--|--------|
| Fluke 1000FLT | 4472387 | Fluorescent Light Tester | 256.00 |
| T6-1000/EU | 4910257 | Electrical Tester with FieldSense™, round | 279.00 |
| T6-600/EU | 4910322 | Electrical Tester with FieldSense™, round | 219.00 |
| H-T6 | 4910585 | T6 Belt Holster | 37.00 |
| Fluke T5-600 | 659612 | Electrical Tester | 164.00 |
| T5-600/62MAX+/1AC kit | 4297126 | Electrical Tester, IR Thermometer and Voltage Detector Kit | 267.00 |
| Fluke T5-1000 | 659570 | Electrical Tester | 184.00 |
| Fluke T5-H5-1AC II Kit | 2098657 | Electrical Tester Kit with Holster and 1AC | 205.00 |
| Fluke T90 | 4016945 | Voltage/continuity tester | 61.00 |
| Fluke T110 | 4016950 | Voltage/continuity tester with switchable load | 87.00 |
| Fluke T130 | 4016961 | Voltage/continuity tester with LCD, switchable load | 128.00 |
| Fluke T150 | 4016977 | Voltage/continuity tester with LCD, Ohms, switchable load | 148.00 |
| Fluke 2042 | 2435038 | Cable Locator (Transmitter + Receiver) | 812.00 |
| Fluke 2042T | 2435045 | Cable Locator Transmitter | 422.00 |
| Fluke 9040EUR | 4014969 | Phase Rotation Indicator | 217.00 |
| Fluke 9062 | 2435077 | Motor and Phase Rotation Indicator | 199.00 |
| LVD1 | 4571403 | Volt Light | 38.00 |
| LVD2 | 2740300 | Volt Light | 42.00 |
| H5 | 649365 | Electrical Tester Holster (Fluke T5) | 37.00 |
| FTL660 | 2280204 | Fused Test Lead Set | 67.00 |
| Fluke 1AC II | 2432932 | Volt Alert | 33.00 |
| Fluke 1AC II | 2432971 | Volt Alert | 33.00 |
| Fluke 1AC II 5PK | 2433042 | Volt Alert 5-pack | 119.00 |
| Fluke 1AC II 5PK | 2433056 | Volt Alert 5-pack | 119.00 |
| FLK2AC/200-1000VCL | 3611985 | ACV Detector 200-1000V | 31.00 |
| PRV240 | 4566209 | Proving unit | 168.00 |
| Fluke 117/PRV240 | 4636971 | Proving unit, Fluke 117 DMM Kit | 336.00 |
| PRV240FS | 4910310 | Proving unit, T6/NCV | 164.00 |

| Model | Art. nr | Description | EUR |
|------------------------------------|---------|---|---------|
| Laser Levels | | | |
| 3 point lasers | | | |
| PLS 3R Z | 5009340 | 3-Point Red Laser Bare Tool | 169.00 |
| PLS 3R KIT | 5009357 | 3-Point Red Laser Kit | 211.00 |
| PLS 3G Z | 5009369 | 3-Point Green Laser Bare Tool | 209.00 |
| PLS 3G KIT | 5009378 | 3-Point Green Laser Kit | 251.00 |
| 5 point lasers | | | |
| PLS 5R Z | 5009384 | 5-Point Red Laser Bare Tool | 260.00 |
| PLS 5R KIT | 5009391 | 5-Point Red Laser Kit | 290.00 |
| PLS 5G Z | 5009406 | 5-Point Green Laser Bare Tool | 297.00 |
| PLS 5G KIT | 5009414 | 5-Point Green Laser Kit | 335.00 |
| Cross line and point lasers | | | |
| PLS 6R Z | 5009423 | Cross Line and Point Red Laser Bare Tool | 306.00 |
| PLS 6R KIT | 5009438 | Cross Line and Point Red Laser Kit | 391.00 |
| PLS 6R SYS | 5009445 | Cross Line and Point Red Laser System | 501.00 |
| PLS 6G Z | 5009461 | Cross Line and Point Green Bare Tool | 399.00 |
| PLS 6G KIT | 5009489 | Cross Line and Point Green Laser Kit | 484.00 |
| PLS 6G SYS | 5009492 | Cross Line and Point Green Laser System | 594.00 |
| Cross line lasers | | | |
| PLS 180R Z | 5017279 | Cross Line Red Laser Bare Tool | 228.00 |
| PLS 180R KIT | 5009450 | Cross Line Red Laser Kit | 265.00 |
| PLS 180R SYS | 5019428 | Cross Line Red Laser System | 337.00 |
| PLS 180G Z | 5017287 | Cross Line Green Laser Bare Tool | 294.00 |
| PLS 180G KIT | 5009509 | Cross Line Green Laser Kit | 326.00 |
| PLS 180G SYS | 5019437 | Cross Line Green Laser System | 388.00 |
| Rotary lasers | | | |
| Horizontal rotary lasers | | | |
| PLS H2 Z | 5022470 | Horizontal red rotary laser bare tool | 588.00 |
| PLS H2 SYS | 5022481 | Horizontal red rotary laser system | 834.00 |
| PLS H2 KIT | 5022496 | Horizontal red rotary laser kit | 1073.00 |
| Manual slope rotary lasers | | | |
| PLS HV2R Z | 5022501 | Manual slope red rotary laser bare tool | 766.00 |
| PLS HV2R SYS | 5022512 | Manual slope red rotary laser system | 1073.00 |
| PLS HV2R KIT | 5022558 | Manual slope red rotary laser kit | 1319.00 |
| PLS JV2G Z | 5022535 | Manual slope green rotary laser bare tool | 889.00 |
| PLS HV2G SYS | 5022547 | Manual slope green rotary laser system | 1196.00 |
| PLS HV2G KIT | 5022520 | Manual slope green rotary laser kit | 1431.00 |
| Accessories lasers | | | |
| PLS-20513 | 4791765 | Tripod Telescope 9 FT 6 IN | 190.00 |
| PLS-21502 | 4919812 | Tripod Extender PLS3/180 | 10.00 |
| PLS FS | 5031929 | Floor Stand for PLS 3, 5, 6 | 15.00 |
| PLS MLB | 5031934 | Magnetic L-Bracket, PLS 3, 5, 6, 180 | 42.00 |
| PLS BP5 | 5031952 | BP5 Alkaline Battery Pack | 40.00 |
| PLS UB9 | 4966636 | UB9 Universal Ceiling/Wall Bracket | 89.00 |
| PLS SLD RED | 4978515 | SLD Red Detector W/ Bracket | 159.00 |
| PLS SLD GREEN | 4978526 | SLD Green Detector W/ Bracket | 173.00 |
| PLS RRT4 | 5022629 | Red Magnetic Reflective Target | 13.00 |
| PLS GRT4 | 5022634 | Green Magnetic Reflective Target | 13.00 |
| PLS C18 | 4985124 | Laser Level Tool Box | 79.00 |
| PLS BC20 | 5022618 | Charging Cord for PLS RBP10 | 35.00 |
| PLS TPOD500 | 5022665 | Elevating Tripod | 270.00 |
| PLS RC2 | 5022564 | Rotary laser remote control | 59.00 |
| PLS XLD | 5037696 | Rotary laser detector with clamp | 198.00 |
| PLS XLD CLAMP | 5037709 | Rotary detector clamp | 35.00 |
| PLS C19 | 5022586 | Rotary laser carrying case | 70.00 |
| PLS BP10 | 5022599 | Rotary alkaline battery for H2, HV2 | 49.00 |
| PLS RBP10 | 5022607 | Rechargeable battery for H2, HV2 | 70.00 |
| PLS WCB10 | 5022641 | Rotary wall and ceiling mount | 89.00 |
| PLS GR16 | 5022652 | Grade rod with US and Metric | 49.00 |
| Distance Meters | | | |
| Fluke 414D | 4106830 | Laser Distance Meter | 144.00 |
| Fluke 419D | 4106853 | Laser Distance Meter | 277.00 |
| Fluke 424D | 4106866 | Laser Distance Meter | 401.00 |

| Model | Art. nr | Description | EUR |
|-------------------------|---------|---|--------|
| 414D/62MAX+ Kit | 4296052 | Fluke Laser distance meter and IR thermometer kit | 244.00 |
| FLUKE-417D | 5099292 | Laser Distance Meter | 102.00 |
| FLUKE-417D + 62MAX+ kit | 5112860 | 417D Laser Distance Meter and 62MAX+ IR Thermometer kit | 179.00 |

Battery Analyzers

| | | | |
|-------------|---------|---------------------------|---------|
| Fluke BT510 | 4489970 | Battery Analyzer | 2949.00 |
| Fluke BT520 | 4489981 | Battery Analyzer | 3750.00 |
| Fluke BT521 | 4489996 | Advanced Battery Analyzer | 4109.00 |

Battery Analyzer Accessories

| | | | |
|-------|---------|--|--------|
| BTL10 | 4542264 | Standard Battery Analyzer Probes | 358.00 |
| BTL20 | 4542273 | Intelligent Test Probe Set, w/Extenders (no temp sensor) | 552.00 |
| BTL21 | 4542286 | Intelligent Test Probe Set, w/Extenders & Temp Sensor | 687.00 |
| BTL-A | 4542258 | Voltage/Current Probe Adapter | 44.00 |
| BC500 | 4542299 | AC Power Charger | 133.00 |
| BP500 | 4542300 | Lithium-ion battery, 7.4V 3000 mAh | 111.00 |
| BT500 | 4561297 | Probe tip, 10x replacement Probe tips, 2x long probe tip covers, 2x short probe tip covers | 133.00 |
| i410 | 617727 | AC/DC Current Clamp (400 A) | 283.00 |

Insulation Testers

| | | | |
|-------------------------------|---------|--|---------|
| Fluke 1503 | 2427883 | Insulation Tester | 427.00 |
| Fluke 1507 | 2427890 | Insulation Tester | 530.00 |
| Fluke 1550C | 3665021 | Insulation Resistance Tester (5kV) | 4242.00 |
| Fluke 1550C/Kit | 3665127 | Insulation Resistance Tester Kit (5kV) | 4676.00 |
| Fluke 1550C FC w/IR3000FC | 4977402 | Insulation Resistance Tester (5kV) with IR3000FC | 4242.00 |
| Fluke 1550C FC Kit w/IR3000FC | 4977457 | Insulation Resistance Tester Kit (5kV) with IR3000FC | 4676.00 |
| Fluke 1555 | 3665056 | Insulation Resistance Tester (10kV) | 4676.00 |
| Fluke 1555/Kit | 3665111 | Insulation Resistance Tester Kit (10kV) | 5107.00 |
| Fluke 1555 FC w/IR3000FC | 4977519 | Insulation Resistance Tester (10kV) with IR3000FC | 4676.00 |
| Fluke 1555 FC Kit w/IR3000FC | 4977469 | Insulation Resistance Tester Kit (10kV) with IR3000FC | 5107.00 |
| Fluke 1577 | 2157280 | Insulation Multimeter | 672.00 |
| Fluke 1587T | 2517605 | Insulation Multimeter (Telecom) | 751.00 |
| Fluke 1587 FC | 4691215 | 2-IN-1 Insulation Multimeter | 810.00 |
| Fluke 1587/MDT FC | 4692716 | 2-IN-1 Advanced Motor & Drive Troubleshooting Kit with 9040, 1400 | 1081.00 |
| 1587KIT/62MAX+ FC | 4692778 | 2-IN-1 Advanced Electrical Troubleshooting Insulation Multi Kit with 62MAX+ I400 | 973.00 |
| Fluke 1587/I400 FC | 4692725 | 2-IN-1 Insulation Multimeter with Clamp i400 | 864.00 |
| FVF-Basic | 2396957 | FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B) | 166.00 |
| FVF-SC2 | 1576734 | FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B) | 272.00 |
| IR189USB | 2428108 | IR Cable - USB (280/180 Series, 1653, 789, 1550B) | 53.00 |

Installation Testers

| | | | |
|----------------------|---------|--|---------|
| Fluke 1662 SCH | 4546944 | Installation Tester w/mem Schuko | 999.00 |
| Fluke 1663 SCH | 4546980 | Installation Tester w/RCD type B Schuko | 1299.00 |
| Fluke 1664FC SCH | 4547054 | FC Installation Tester w/insulation pre-test Schuko | 1649.00 |
| Fluke 166X-MTC-SCH | 4601081 | Fluke 166X-Main test cord, Schuko (EU) | 61.00 |
| Fluke DMS COMP | 4718790 | DMS Complete, Installation, PAT Software | 598.00 |
| Fluke DMS COMPL/PROF | 4718803 | DMS Complete/Professional, Installation, PAT Software | 796.00 |
| FVF-SC2 | 1576734 | FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B) | 272.00 |
| IR189USB | 2428108 | IR Cable - USB (280/180 Series, 1653, 789, 1550B) | 53.00 |
| ES165X | 2104706 | Earth Spike Test Kit | 167.00 |
| TP165X | 2107742 | Remote Control Probe (1650 Series) | 90.00 |
| TL165X | 2107756 | Standard Test Lead Set (1650 Series) | 124.00 |
| ZERO ADAPTER | 3261925 | Zero adapter (165xB) | 42.00 |

Portable Appliance Testers

| | | | |
|----------------------|---------|---|--------|
| Fluke DMS COMP | 4718790 | DMS Complete, Installation, PAT Software | 598.00 |
| Fluke DMS COMPL/PROF | 4718803 | DMS Complete/Professional, Installation, PAT Software | 796.00 |

Earth Ground Testers

| | | | |
|-------------------|---------|---|---------|
| Fluke 1630-2 FC | 4829532 | Earth Ground Loop and Leakage Clamp | 1538.00 |
| Fluke 1630-2 | 4829515 | Earth Ground Loop and Leakage Clamp (non FC) | 1538.00 |
| Fluke 1623-2 | 4325155 | Basic Geo Earth Ground Tester | 1512.00 |
| Fluke 1625-2 | 4325162 | Advanced Geo Earth Ground Tester | 2521.00 |
| Fluke 1623-2 Kit | 4325170 | Basic Geo Earth Ground Tester, Kit | 2578.00 |
| Fluke 1625-2 Kit | 4325181 | Advanced Geo Earth Ground Tester, Kit | 3699.00 |
| Earth Stake | 4325492 | Geo Earth Ground Tester, Earth stake | 70.00 |
| Cable Reel 25M BL | 4343731 | 25M Blue, Ground/Earth Cable Reel, 25M Wire | 70.00 |
| Cable Reel 25M GR | 4343746 | 25M Green, Ground/Earth Cable Reel, 25M Wire | 70.00 |
| Cable Reel 50M RD | 4343754 | 50M Red, Ground/Earth Cable Reel, 50M Wire | 78.00 |
| C1620 | 4359042 | Carrying Case | 216.00 |
| ES-162P3-2 | 4359377 | Earth Ground Stake Set for 3 Pole Measurement | 268.00 |
| ES-162P4-2 | 4359389 | Earth Ground Stake Set for 4 Pole Measurement | 391.00 |

| Model | Art. nr | Description | EUR |
|--|---------|--|----------|
| Indoor Air Quality Tools | | | |
| Fluke 922 | 2679822 | Airflow Meter | 667.00 |
| Fluke 922/Kit | 2679831 | Airflow Meter Kit | 777.00 |
| Fluke 971 | 2418208 | Temperature Humidity Meter | 266.00 |
| Fluke 975 | 2519364 | AirMeter | 2086.00 |
| Fluke 975V | 2666111 | AirMeter with Velocity | 2399.00 |
| Fluke CO-220 | 664711 | Carbon Monoxide Meter | 555.00 |
| Fluke RLD2 | 3387163 | Leak Detector Flashlight | 55.00 |
| CO-205 | 664714 | Aspirator Kit | 187.00 |
| 975VP | 2631538 | Air Velocity Probe | 469.00 |
| PT12 | 2740212 | Pitot Tube, 12 | 122.00 |
| Fluke 985 | 4131397 | Airborne Particle Counter | 4382.00 |
| Digital Thermometers | | | |
| Fluke 51 II | 1281142 | Thermometer | 339.00 |
| Fluke 52 II | 1281139 | Thermometer | 429.00 |
| Fluke 53 II B | 3821062 | Single Input Thermometer, 60Hz | 489.00 |
| Fluke 53 II B | 3821096 | Single Input Thermometer, 50Hz | 489.00 |
| Fluke 54 II B | 3821070 | Dual Input Thermometer, 60Hz | 599.00 |
| Fluke 54 II B | 3821081 | Dual Input Thermometer, 50Hz | 599.00 |
| Fluke 61 | 1643896 | Infrared Thermometer | 199.00 |
| Fluke 62 MAX | 4130474 | Infrared thermometer | 99.00 |
| Fluke 62 MAX+ | 4130488 | Infrared Thermometer | 109.00 |
| T5-600/62MAX+/1AC kit | 4297126 | Electrical Tester, IR Thermometer and Voltage Detector Kit | 267.00 |
| 414D/62MAX+ Kit | 4296052 | Fluke Laser distance meter and IR thermometer kit | 244.00 |
| 62MAX+/323/1AC Kit | 4296076 | IR Thermometer, Clamp Meter and Voltage Detector Kit | 269.00 |
| 116/62MAX+ Kit | 4296018 | Fluke HVAC Multimeter and IR Thermometer Combo Kit | 324.00 |
| Fluke 63 | 2148281 | Infrared Thermometer | 289.00 |
| Fluke 64 MAX | 4856105 | Multifunction IR Thermometer 20:1 D:S | 139.00 |
| Fluke 561 | 2558118 | Multipurpose Thermometer | 149.00 |
| Fluke 566 | 2837799 | Multipurpose Thermometer | 439.00 |
| Fluke 568 | 2837806 | Multipurpose Thermometer | 549.00 |
| Fluke 568Ex | 4321662 | Intrinsically safe Infrared Thermometer | 1359.00 |
| Fluke 572-2 | 4328074 | Infrared Thermometer | 649.00 |
| Fluke FP | 2644169 | FoodPro Thermometer | 129.00 |
| Fluke FP Plus | 2477950 | FoodPro Plus Thermometer | 219.00 |
| C50 | 762823 | Soft Meter Case | 44.00 |
| H6 | 2152040 | Infrared Thermometer Holster (Fluke 63/65/68/561) | 35.00 |
| 80PR-60 | 2148313 | RTD Temperature Probe (Fluke 66/68) | 80.00 |
| Visual Thermometers | | | |
| Fluke VT04 | 4366444 | Visual IR Thermometer | 589.00 |
| Fluke VT04A | 4485211 | Visual IR thermometer | 529.00 |
| Fluke charger VT04 | 4375752 | Charger & adapter set VT04 | 49.00 |
| Fluke Battery, VT04 | 4375741 | Li-ion battery VT04 | 49.00 |
| Industrial Imaging | | | |
| Fluke DS701 | 4962652 | Diagnostic Videoscope | 1749.00 |
| Fluke DS703 FC | 4962665 | High Resolution Diagnostic Videoscope with FC | 2059.00 |
| Fluke 3.8mm Scope | 4962690 | 3.8 mm Scope, 1 m Probe, Forward View | 719.00 |
| Fluke 8.5mm Scope | 4962708 | 8.5 mm Scope, 3 m Probe, Dual View | 619.00 |
| Fluke 5.5 mm Scope | 4962713 | 5.5 mm Scope, 1 m Probe, Dual View | 519.00 |
| Fluke 8.5 mm Scope | 4962749 | 8.5 mm Scope, 1.2 m Probe, Dual View | 209.00 |
| Fluke 8.5 mm UV Scope | 4962751 | 8.5 mm UV Scope, 1 m Probe, Dual View | 719.00 |
| Fluke 9 mm Scope | 4962760 | 9 mm Scope, Forward View, 20 m Probe Reel | 2059.00 |
| Fluke DS 7XX Neckstrap | 4962772 | DS 7XX Neckstrap | 49.00 |
| FLK-ii900 | 5075603 | Sonic Industrial Imager | 17499.00 |
| Thermal Imagers | | | |
| Handheld thermal cameras | | | |
| FLK-TIS20+ 9HZ | 5124518 | Thermal Imager; 9 HZ | 1199.00 |
| FLK-PTI120 9Hz | 5074148 | Thermal Imager 120x90 9Hz | 769.00 |
| High resolution thermal cameras | | | |
| FLK-TiS60+ 9HZ | 5133402 | Thermal Imager; GT2; 9 HZ | 2999.00 |
| FLK-TiS60+ 30HZ | 5133399 | Thermal Imager; GT1; 30 HZ | 2999.00 |
| FLK-TI300+ 9HZ | 5127977 | Thermal Imager; GS1; 320x240; 9 Hz | 4499.00 |
| FLK-TI300+ 60HZ | 5127961 | Thermal Imager; GS1; 320x240; 60 Hz | 4499.00 |
| FLK-Ti401 Pro 9Hz | 5085052 | Thermal Imager 640x480 9Hz | 7169.00 |
| FLK-Ti401 Pro 60 Hz | 5085041 | Thermal Imager 640x480 60 Hz | 7169.00 |
| Fluke Ti480 PRO 9HZ | 4947332 | Fluke Ti480 PRO 9Hz Thermal Imager | 9529.00 |
| Fluke Ti480 PRO 60HZ | 4947326 | Fluke Ti480 PRO 60Hz Thermal Imager | 9529.00 |
| FLK-TiX501 9Hz | 5085128 | Thermal Imager 640x480 9Hz | 10249.00 |

| Model | Art. nr | Description | EUR |
|-------------------|---------|------------------------------------|----------|
| FLK-TiX501 60 Hz | 5085119 | Thermal Imager 640x480 60Hz | 10249.00 |
| Fluke TiX580 9Hz | 4841945 | Thermal Imager; 640x480; 9 HZ, SR | 12599.00 |
| Fluke TiX580 60Hz | 4842073 | Thermal Imager; 640x480; 60 HZ, SR | 12599.00 |

High definition mounted thermal cameras

| | | | |
|----------------------|---------|--|----------|
| Fluke RSE300 9Hz | 4948166 | Thermal Imager; 320x240; 9 Hz | 12259.00 |
| Fluke RSE300 60Hz | 4944776 | Thermal Imager; 320x240; 60 Hz | 11259.00 |
| Fluke RSE600 9HZ | 4948175 | Thermal Imager; 640x480; 9 Hz | 15999.00 |
| Fluke RSE600 60HZ | 4944826 | Thermal Imager; 640x480; 60 Hz | 15999.00 |
| Fluke 2x lens | 4961163 | Infrared Telephoto Lens (2X magnification) | 2099.00 |
| Fluke 4x lens | 4961188 | Infrared Telephoto Lens (4X magnification) | 4699.00 |
| Fluke RSE-MB | 4961344 | Mounting bracket | 129.00 |
| Fluke RSE-Stand | 4973844 | RSE Stand | 139.00 |
| Fluke 0.75 Wide lens | 4961174 | Infrared Wide Angle Lens | 1049.00 |

Gas detection thermal cameras

| | | | |
|----------------------|---------|--|----------|
| Fluke Ti450 SF6 60Hz | 4907176 | SF6 Gas leak detection, Thermal Imager | 17499.00 |
|----------------------|---------|--|----------|

Thermal Imagers Accessories (general)

| | | | |
|----------------------|---------|--|---------|
| Ti-Visor2 | 3996500 | Sun Visor | 79.00 |
| Ti-Visor3 | 4335377 | Thermal imager visor | 79.00 |
| Ti-Tripod | 3511872 | Tripod Mounting Base | 109.00 |
| Ti-Tripod2 | 3996517 | Mounting Base | 99.00 |
| Ti-Tripod3 | 4335389 | Tripod mounting base accessory | 99.00 |
| FLK-LENS/TELE2 | 4335350 | Telephoto Infrared Lens (Ti200/Ti300/Ti400) | 1329.00 |
| FLK-LENS/WIDE2 | 4335361 | Wide-angle Infrared Lens (Ti200/Ti300/Ti400) | 1329.00 |
| Fluke lens/4xTELE2 | 4607058 | 4x Telephoto IR lens for TiX560-TiX520-Ti400-Ti300-Ti200 | 6029.00 |
| Fluke lens/25MAC2 | 4607064 | 25Micron Macro IR lens for TiX560-TiX520 | 4359.00 |
| Ti-Car Charger | 3039779 | Ti Car Charger (TiR/TiR1/Ti10/Ti20/Ti25) | 129.00 |
| Ti20-RBP | 2577796 | Rechargeable Battery Pack (Ti20) | 179.00 |
| FLK-TI-SBP3 | 3440365 | Extra battery (Ti32/TiR32) | 139.00 |
| Fluke Ti-SBC3B | 4354922 | Charging base (Ti200/Ti300/Ti400) | 179.00 |
| Fluke TiX5xx-Neck | 4574715 | Adjustable neck strap | 31.00 |
| Fluke TiX5xx-SBP4 | 4597142 | Additional Smart Battery | 129.00 |
| Fluke TiX5xx Hand | 4574703 | Adjustable hand strap | 16.00 |
| Fluke TiX5xx-HDMI | 4615511 | HDMI video cable | 19.00 |
| Fluke TiX5x-Lens Cap | 4550697 | Lens cap | 16.00 |
| Fluke Ti-Bluetooth | 4603258 | Bluetooth headset | 79.00 |

Thermal Imagers IR-Windows

| | | | |
|--------------|---------|---|--------|
| FLK-050-CLKT | 3460346 | 50mm C-Range IR Windows, Kwik twist | 169.00 |
| FLK-075-CLKT | 3460387 | 75 mm C-Range IR Window, Kwik Twist | 229.00 |
| FLK-100-CLKT | 3460439 | 100mm C-Range IR Window, Kwik Twist | 309.00 |
| Fluke CV200 | 4326955 | 50mm IR Window, hand turn door latch | 219.00 |
| Fluke CV300 | 4326962 | 75mm IR Windows, hand turn door latch | 299.00 |
| Fluke CV301 | 4338164 | 75mm IR Windows, security turn door latch | 319.00 |
| Fluke CV400 | 4326996 | 100 mm IR Windows, hand turn door latch | 419.00 |
| Fluke CV401 | 4338173 | 100 mm IR Windows, security turn door latch | 419.00 |

ScopeMeters

Industrial ScopeMeter

| | | | |
|------------------|---------|--|---------|
| Fluke 123B/EU | 4755659 | Industrial ScopeMeter 20MHZ, EU | 1576.00 |
| Fluke 123B/INT | 4755710 | Industrial ScopeMeter 20MHZ, INT | 1576.00 |
| Fluke 124B/EU | 4755731 | Industrial ScopeMeter 40MHZ, EU | 1891.00 |
| Fluke 124B/INT | 4755793 | Industrial ScopeMeter 40MHZ, INT | 1891.00 |
| Fluke 125B/EU | 4755818 | Industrial ScopeMeter 40MHZ, EU | 2258.00 |
| Fluke 125B/INT | 4755876 | Industrial ScopeMeter 40MHZ, INT | 2258.00 |
| Fluke 123B/EU/S | 4755890 | Industrial ScopeMeter + SCC 20MHZ, EU | 1996.00 |
| Fluke 123B/INT/S | 4755953 | Industrial ScopeMeter + SCC 20MHZ, INT | 1996.00 |
| Fluke 124B/EU/S | 4755975 | Industrial ScopeMeter + SCC 40MHZ, EU | 2311.00 |
| Fluke 124B/INT/S | 4756031 | Industrial ScopeMeter + SCC 40MHZ, INT | 2311.00 |
| Fluke 125B/EU/S | 4756054 | Industrial ScopeMeter + SCC 40MHZ, EU | 2679.00 |
| Fluke 125B/INT/S | 4756112 | Industrial ScopeMeter + SCC 40MHZ, INT | 2679.00 |

190 Series ScopeMeters

| | | | |
|--------------------|---------|--|---------|
| Fluke 190-204/EU | 3894409 | ScopeMeter 4 Channel 200 MHZ Color | 4627.00 |
| Fluke 190-204/UN | 3894411 | ScopeMeter 4 Channel 200 MHZ Color | 5040.00 |
| Fluke 190-204/EU/S | 3894475 | ScopeMeter 4 Channel 200 MHZ Color SCC | 5040.00 |
| Fluke 190-204/UN/S | 3894482 | ScopeMeter 4 Channel 200 MHZ Color UNI SCC | 5040.00 |
| Fluke 190-104/EU | 3894540 | ScopeMeter 4 Channel 100 MHZ Color EU | 4045.00 |
| Fluke 190-104/UN | 3894557 | ScopeMeter 4 Channel 100 MHZ Color UNI | 4045.00 |
| Fluke 190-104/EU/S | 3894617 | ScopeMeter 4 Channel 100 MHZ Color EU SCC | 4458.00 |
| Fluke 190-104/UN/S | 3894621 | ScopeMeter 4 Channel 100 MHZ Color UNI SCC | 4458.00 |

| Model | Art. nr | Description | EUR |
|--------------------|---------|---|---------|
| Fluke 190-062/EU | 4025159 | ScopeMeter 2 Channel 60 MHZ Color | 2921.00 |
| Fluke 190-062/UN | 4025171 | ScopeMeter 2 Channel 60MHZ Color | 2921.00 |
| Fluke 190-062/EU/S | 4025230 | ScopeMeter 2 Channel Color SCC | 3333.00 |
| Fluke 190-062/UN/S | 4025248 | ScopeMeter 2 Channel 60MHZ Color SCC | 3333.00 |
| Fluke 190-102/EU | 4025318 | ScopeMeter 2 Channel 100MHZ Color | 3593.00 |
| Fluke 190-102/UN | 4025329 | ScopeMeter 2 Channel 100MHZ Color SCC | 3593.00 |
| Fluke 190-102/EU/S | 4025383 | ScopeMeter 2 Channel 100MHZ Color SCC | 4006.00 |
| Fluke 190-102/UN/S | 4025390 | ScopeMeter 2 Channel 100MHZ Color SCC | 4006.00 |
| Fluke 190-202/EU | 4025460 | ScopeMeter 2 Channel 200MHZ Color | 4055.00 |
| Fluke 190-202/UN | 4025472 | ScopeMeter 2 Channel 200MHZ Color | 4055.00 |
| Fluke 190-202/EU/S | 4025554 | ScopeMeter 2 Channel 200MHZ Color SCC | 4468.00 |
| Fluke 190-202/UN/S | 4025568 | ScopeMeter 2 Channel 200MHZ Color SCC | 4468.00 |
| Fluke 190-502/EU | 4025623 | ScopeMeter 2 Channel 500 MHZ Color | 4995.00 |
| Fluke 190-502/UN | 4025638 | ScopeMeter 2 Channel 500 MHZColor UNI | 4995.00 |
| Fluke 190-502/EU/S | 4025692 | ScopeMeter 2 Channel 500 MHZ Color Europe SCC | 5409.00 |
| Fluke-190-502/UN/S | 4025704 | ScopeMeter 2 Channel 500 MHZ Color UNI SCC | 5409.00 |
| Fluke 190-504/EU | 4419875 | ScopeMeter 4 Channel 500MHz Color | 5178.00 |
| Fluke 190-504/UN | 4419929 | ScopeMeter 4 Channel 500MHz Color UNI | 5178.00 |
| Fluke 190-504/EU/S | 4419941 | ScopeMeter 4 Channel 500MHz Color Europe SCC | 5590.00 |
| Fluke 190-504/UN/S | 4419990 | ScopeMeter 4 Channel 500MHz Color UNI SCC | 5590.00 |

Motor Drive Analyzers

| | | | |
|---------------|---------|---|---------|
| Fluke MDA-510 | 4984691 | Motor Drive Analyzer 510, 4-channel color | 5732.00 |
| Fluke MDA-550 | 4984706 | Motor Drive Analyzer 550, 4-channel color, PRO | 6616.00 |
| SVS-500 | 5011031 | Shaft voltage set and magnetic base | 352.00 |
| SB-500 | 5011046 | Shaft brushes set, repl brushes for SVS-500 and MDA-500 | 264.00 |

ScopeMeter Accessories

| | | | |
|------------|---------|--|--------|
| AC120 | 646163 | Heavy Duty Alligator Clips | 48.00 |
| AS400 | 3894880 | Probe Extension Set, for VPS400 Probes | 114.00 |
| BB120 | 646171 | Banana to BNC Adapter Plug | 53.00 |
| BB120-II | 4744369 | Set of 2 banana to BNC adapter | 47.00 |
| BHT190 | 3379374 | Set of Break-out Adapters | 372.00 |
| BP120MH | 2544081 | NiMH Battery Pack (120 Series/43B) | 104.00 |
| BP190 | 677390 | NiMH Battery Pack (190 Series) | 209.00 |
| BP290 | 4025762 | Battery Pack Single Cap 190-series II | 247.00 |
| BP291 | 3894688 | Battery Pack, Fluke 190 Series | 346.00 |
| C120 | 646189 | Hard Case (43B/120 Series) | 113.00 |
| C120B | 4744391 | Soft carrying case for 120B series | 142.00 |
| C125 | 646858 | Soft Meter Case | 53.00 |
| C190 | 677401 | Hard Case (190 Series) | 266.00 |
| C195 | 677408 | Soft Case | 246.00 |
| C290 | 3894803 | Hard-Shell Carrying Case | 221.00 |
| CS20MA | 677393 | Current Shunt 4-20 mA | 102.00 |
| EBC290 | 3894906 | External Battery Charger | 109.00 |
| HC120 | 646668 | Hook Clips | 60.00 |
| HC120-II | 4744357 | Set of 2 hook clips | 53.00 |
| HC200 | 2086410 | Hook Clips | 42.00 |
| HH290 | 3894844 | Hanging Hook, ScopeMeter Series 190 II | 78.00 |
| MA190 | 1567481 | Medical Accessory Kit (190 Series) | 469.00 |
| OC4USB | 2166266 | Serial Interface Adapter/Cable (USB) | 169.00 |
| PM8907/807 | 624764 | POWER ADAPTOR/BATTERY CHARGER | 126.00 |
| PM8907/808 | 614039 | Battery Charger/Line Voltage Adapter UNIVERSAL (120 Series) | 149.00 |
| PM9080 | 1641983 | Serial Interface Adapter/Cable (RS232) | 280.00 |
| PM9081 | 916093 | Dual Banana Plug to Female BNC Adapter | 54.00 |
| PM9082 | 916163 | Dual Banana Jack to Male BNC Adapter | 54.00 |
| PM9091 | 935598 | Coaxial BNC Cables (1.5 m) | 126.00 |
| PM9092 | 935601 | Coaxial BNC Cables (0.5 m) | 109.00 |
| PM9093 | 935593 | Male BNC to Female BNC Adapter | 73.00 |
| PM9096/201 | 651742 | Secondary Pick-up | 349.00 |
| RS120-III | 4023947 | Probe Accessory Replacement Set | 114.00 |
| RS400 | 3894867 | Probe Replacement Set, for VPS400 Probes | 91.00 |
| RS500 | 4025886 | Probe accessory replacement set for VPS500 probes | 163.00 |
| SCC120B | 4744423 | Software soft carry case accessory kit 120B series | 525.00 |
| SCC120E | 646684 | FlukeView Software + USB Cable + Case (120 Series) - English | 482.00 |
| SCC128 | 2100199 | Automotive Accessory Kit (120 Series) | 749.00 |
| SCC198 | 2100208 | Automotive Accessory Kit (190 Series) | 942.00 |
| SCC190 | 671826 | FlukeView Software + Cable + Case (190 Series) - English, French, German | 675.00 |
| SCC290 | 3894826 | Software and Carrying Case for 190 Series II | 412.00 |
| SP120B | 4744414 | Screen protector for 120B series | 47.00 |
| STL190 | 201233 | Automotive Shielded Test Lead Set (120/190 Series) | 261.00 |
| STL120-III | 4023901 | Shielded Test Lead | 200.00 |
| STL120-IV | 4744340 | Shielded test lead set 600V CAT IV | 168.00 |
| SW90W | 3894923 | FlukeView Software | 373.00 |
| TAS90 | 614187 | Automotive Accessory Set (120/190 Series) | 73.00 |

| Model | Art. nr | Description | EUR |
|-------------|---------|--|--------|
| TRM50 | 4025864 | 50 Ohm feed-through terminator BNC | 196.00 |
| UA120 | 4744384 | USB Connector adapter | 47.00 |
| VPS41 | 4744378 | Voltage probe set 40 MHZ 600V CAT IV | 163.00 |
| VPS101 | 3086317 | 1:1 Voltage Probe Set, black, 30 MHz, 1.2m | 227.00 |
| VPS210-G | 3086247 | 10:1 Voltage Probe Set, grey, 200 MHz, 1.2m | 227.00 |
| VPS210-R | 3086235 | 10:1 Voltage Probe Set, 1 red, 200 MHz, 1.2m | 227.00 |
| VPS212-G | 3086286 | 10:1 Voltage Probe Set, grey, 200 MHz, 2.5m | 227.00 |
| VPS212-R | 3086273 | 10:1 Voltage Probe Set, red, 200 MHz, 2.5m | 227.00 |
| VPS220-G | 3086300 | 100:1 Voltage Probe Set, grey, 200 MHz, 1.2m | 227.00 |
| VPS220-R | 3086299 | 100:1 Voltage Probe Set, red, 200 MHz, 1.2m | 227.00 |
| VPS40-III | 4023920 | Voltage Probe | 132.00 |
| VPS410-II-B | 4276937 | Industrial Voltage Probe Set 500 MHz 10:1 Blue | 217.00 |
| VPS410-II-G | 4276943 | Industrial Voltage Probe Set 500 MHz 10:1 Grey | 217.00 |
| VPS410-II-R | 4276928 | Industrial Voltage Probe Set 500 MHz 10:1 Red | 217.00 |
| VPS410-II-V | 4276955 | Industrial Voltage Probe Set 500 MHz 10:1 Green | 217.00 |
| VPS420-R | 3894783 | High Working Voltage Probe 100:1 Red & Black | 250.00 |
| VPS420-B | 4411541 | High Working Voltage Ruggedized Probe; Blue/Black | 253.00 |
| VPS420-G | 4411565 | High Working Voltage Ruggedized Probe; Grey/Black | 250.00 |
| VPS420-V | 4411583 | High Working Voltage Ruggedized Probe; Green/Black | 253.00 |
| VPS510-R | 4025781 | Voltage Probe set 500 MHZ 10:1 Red | 217.00 |
| VPS510-B | 4025796 | Voltage probe set 500 MHZ 10:1 Blue | 217.00 |
| VPS510-G | 4025801 | Voltage probe set 500 MHZ 10:1 Grey | 217.00 |
| VPS510-V | 4025812 | Voltage probe set 500 MHZ 10:1 Green | 217.00 |

| Power Quality Tools | | | |
|---------------------|---------|--|----------|
| Fluke 345 | 2584181 | Power Quality Clamp Meter | 1656.00 |
| Fluke 430-II/MA | 4779032 | 430-II Motor Analyzer Upgrade Kit | 2091.00 |
| Fluke 434-II/BASIC | 4116650 | Power Quality and energy analyzer (w/o clamps) | 4181.00 |
| Fluke 434-II | 4116638 | Power Quality and energy analyzer | 4830.00 |
| Fluke 434-II/INTL | 4778918 | Power Quality and energy analyzer/International | 4830.00 |
| Fluke 435-II | 4116661 | Power Quality& Energy Analyzer | 6209.00 |
| Fluke 435-II/BASIC | 4116689 | Advanced Power Quality and energy analyzer (w/o clamps) | 5586.00 |
| Fluke 435-II/INTL | 4778929 | Power Quality and energy analyzer/International | 6209.00 |
| Fluke 437-II | 4116692 | Power Quality& Energy Analyzer | 8559.00 |
| Fluke 437-II/BASIC | 4116719 | 400 Hz Power Quality and Energy Analyzer (w/o clamps) | 7917.00 |
| Fluke 437-II/INTL | 4778934 | Power Quality and energy analyzer/International | 8559.00 |
| Fluke 438-II | 4778976 | Power Quality & Motor Analyzer | 7649.00 |
| Fluke 438-II/BASIC | 4778990 | Power Quality & Motor Analyzer, without clamps and FC WiFi SD Card | 6988.00 |
| Fluke 438-II/INTL | 4779015 | Power Quality & Motor Analyzer, without FC WiFi SD Card | 7649.00 |
| Fluke 1732/EUS | 4706548 | Energy Logger, EU/US version | 2569.00 |
| Fluke 1732/INTL | 4706553 | Energy Logger, international version | 2569.00 |
| Fluke 1732/B | 4706566 | Energy Logger, basic version | 2304.00 |
| Fluke 1734/EUS | 4706594 | Energy Logger, EU/US advanced version | 2879.00 |
| Fluke 1734/INTL | 4706608 | Energy Logger, international advanced version | 2879.00 |
| Fluke 1734/B | 4706582 | Energy Logger, advanced version no flexis | 2619.00 |
| Fluke 1736/EUS | 4534519 | 3-Phase Power Logger, EU/US version | 3999.00 |
| Fluke 1736/B | 4563561 | 3-Phase Power Logger, basic version | 3989.00 |
| Fluke 1736/INTL | 4563550 | 3-Phase Power Logger, International version | 3999.00 |
| Fluke 1738/EUS | 4563577 | 3-Phase Power Logger, EU/US Advanced version no flexis | 4619.00 |
| Fluke 1738/B | 4588378 | 3-Phase Power Logger, advanced version no flexis | 4109.00 |
| Fluke 1738/INTL | 4588384 | 3-Phase Power Logger, international advanced version | 4619.00 |
| Fluke 1742/15/EUS | 4920613 | Power Quality Logger with 60 cm 1,500A iFlex, EUS version | 3661.00 |
| Fluke 1742/30/EUS | 4920651 | Power Quality Logger with 60 cm 3,000A iFlex, EUS version | 3661.00 |
| Fluke 1742/B/EUS | 4920660 | Power Quality Logger without iFlex, EUS version | 3348.00 |
| Fluke 1742/15/INTL | 4920672 | Power Quality Logger with 60 cm 1,500A iFlex, INTL version | 3661.00 |
| Fluke 1742/30/INTL | 4920685 | Power Quality Logger with 60 cm 3,000A iFlex, INTL version | 3661.00 |
| Fluke 1742/B/INTL | 4920697 | Power Quality Logger without iFlex, INTL version | 3348.00 |
| 1742-6/Upgrade | 4920964 | 1742 to 1746 Upgrade | 1791.00 |
| 1742-8/Upgrade | 4920973 | 1742 to 1748 Upgrade | 3312.00 |
| Fluke 1746/15/EUS | 4920703 | Power Quality Logger with 60 cm 1,500A iFlex, EUS version | 5029.00 |
| Fluke 1746/30/EUS | 4920715 | Power Quality Logger with 60 cm 3,000A iFlex, EUS version | 5029.00 |
| Fluke 1746/B/EUS | 4920726 | Power Quality Logger without iFlex, EUS version | 4709.00 |
| Fluke 1746/15/INTL | 4920732 | Power Quality Logger with 60 cm 1,500A iFlex, INTL version | 5029.00 |
| Fluke 1746/30/INTL | 4920744 | Power Quality Logger with 60 cm 3,000A iFlex, INTL version | 5029.00 |
| Fluke 1746/B/INTL | 4920759 | Power Quality Logger without iFlex, INTL version | 4709.00 |
| 1746-8/Upgrade | 4920986 | 1746 to 1748 Upgrade | 1791.00 |
| Fluke 1748/15/EUS | 4920767 | Power Quality Logger with 60 cm 1,500A iFlex, EUS version | 6299.00 |
| Fluke 1748/30/EUS | 4920771 | Power Quality Logger with 60 cm 3,000A iFlex, EUS version | 6299.00 |
| Fluke 1748/B/EUS | 4920780 | Power Quality Logger without iFlex, EUS version | 5999.00 |
| Fluke 1748/15/INTL | 4920798 | Power Quality Logger with 60 cm 1,500A iFlex, INTL version | 6299.00 |
| Fluke 1748/30/INTL | 4920800 | Power Quality Logger with 60 cm 3,000A iFlex, INTL version | 6299.00 |
| Fluke 1748/B/INTL | 4920817 | Power Quality Logger without iFlex, INTL version | 5999.00 |
| Fluke 1760 Basic | 2630732 | Power Quality Recorder (three-phase), Topas | 12171.00 |
| Fluke 1760 | 2630744 | Power Quality Recorder (three-phase), Topas | 14102.00 |

| Model | Art. nr | Description | EUR |
|---------------------|---------|---|----------|
| Fluke 1760TR Basic | 2637629 | Power Quality Recorder (three-phase), Topas | 16679.00 |
| Fluke 1760TR | 2637634 | Power Quality Recorder (three-phase), Topas | 18608.00 |
| Fluke VR1710 | 3030923 | Single-Phase Voltage Quality Recorder | 899.00 |
| C1740 | 4116762 | Softcase for 174X and 43X-II PQ analyzer | 212.00 |
| C437-II | 4116743 | Hard case 430 Series II with rollers | 511.00 |
| EPE-Training-E/EMEA | 4792349 | Fluke EPE Training Set - English | 199.00 |

| Power Quality Tools Accessories | | | |
|---------------------------------|---------|--|---------|
| 1743/1744 Poleset | 3024485 | Pole Mounting Kit (Fluke 1743/1744) | 42.00 |
| 3140R | 2650136 | Clip-on Current Transformer 2A-400A (Fluke 1750) | 412.00 |
| 3210-PR-TF-II | 4531769 | 1000A Fluke 1750 Thin flexi 61cm | 640.00 |
| 3310-PR-TF-II | 4531778 | 5000A Fluke 1750 Thin flexi 61cm | 854.00 |
| 3312-PR-TF-II | 4531784 | 5000A Fluke 1750 Thin flexi 122cm | 1051.00 |
| BP120MH | 2544081 | NiMH Battery Pack (120 Series/43B) | 104.00 |
| BE345 | 2839604 | Battery Eliminator (Fluke 345) | 158.00 |
| BP1730 | 4389436 | Li Ion Battery Pack 3.7V 2500mAh (1730) | 41.00 |
| C120 | 646189 | Hard Case (43B/120 Series) | 113.00 |
| C17xx | 4637381 | Soft Case | 119.00 |
| CS1750 | 2673962 | Soft Case (Fluke 1750/1760) | 262.00 |
| 1730 Hanger | 4358028 | Hanger kit (1730) | 59.00 |
| 1730 Cable | 4395217 | Cable,AUX input cable (1730) | 30.00 |
| 1750/Case | 2650124 | Hard Case (Fluke 1750) | 565.00 |
| 1750/Seat-L | 2673937 | Fluke Power Analyze - Additional SEAT LICENSE | 1118.00 |
| 1750/Site-L | 2673928 | Fluke Power Analyze - Additional SITE LICENCE | 5592.00 |
| FS17X5-TF-II | 4531791 | 3000A 4-PH Fluke 1735 & 1745 Thin flexi set | 1647.00 |
| FS17XX IP65-TF-II | 4531804 | 3000A IP65 4-PH Fluke 1743/4 Thin flexi set | 1929.00 |
| FS17XX-1PH-TF-II | 4531819 | FS3000A/6000A 4-PH 36-Inch Thin flexi set | 415.00 |
| FLUKE-173X ADPT | 4717827 | AUX input adapter, 173X | 138.00 |
| Fluke 17xx TL 0.1M | 4715389 | Test lead set for Fluke 173x; 0.1m | 41.00 |
| FS3000/6000A-TF-4-II | 4531828 | FS3000A/6000A 4-PH 36-Inch thin flexi set | 1642.00 |
| GPS430-II | 4693803 | GPS Synchronization module (430-II series) | 1579.00 |
| GPS-Time Sync | 2539223 | GPS Time Synchronization Module (Fluke 1760) | 439.00 |
| i17XX-flex1500 | 4637328 | Fluke-17xx iFlexi 1500A 12 IN | 169.00 |
| i17XX-flex3000 | 4637343 | Fluke-17xx iFlexi 3000A 24 IN | 181.00 |
| i17XX-flex6000 | 4637362 | Fluke-17xx iFlexi 6000A 36 IN | 192.00 |
| i17XX-flex1500/3pk | 4637337 | Fluke-17xx iFlexi 1500A 12 IN, 3 pack | 491.00 |
| i17XX-flex3000/3pk | 4637355 | Fluke-17xx iFlexi 3000A 24 IN, 3 pack | 522.00 |
| i17XX-flex6000/3pk | 4637370 | Fluke-17xx iFlexi 6000A 36 IN, 3 pack | 555.00 |
| i17XX-Flex1500/4PK | 4637411 | Fluke-17xx iFlexi 1500A 12 IN, 4 Pack | 640.00 |
| i17XX-Flex3000/4PK | 4637427 | Fluke-17xx iFlexi 3000A 24 IN, 4 Pack | 683.00 |
| i17XX-Flex6000/4PK | 4637430 | Fluke-17xx iFlexi 6000A 36 IN, 4 Pack | 726.00 |
| i1A/10A Clamp PQ1 | 3345753 | 1-phase Mini Current Clamp Set | 481.00 |
| i1A/10A Clamp PQ3 | 3024413 | 3-phase Mini Current Clamp Set | 590.00 |
| i1A/10A Clamp PQ4 | 3024424 | 4-phase Mini Current Clamp Set | 780.00 |
| i5A/50A Clamp PQ1 | 3345766 | 1-Phase 5A/50A Mini Current Clamp set for PQ | 481.00 |
| i5A/50A Clamp PQ3 | 3024436 | 3-phase Mini Current Clamp Set | 590.00 |
| i5A/50A Clamp PQ4 | 3024449 | 4-phase Mini Current Clamp Set | 780.00 |
| i20/200A Clamp PQ3 | 3024451 | 3-phase Mini Current Clamp Set | 590.00 |
| i20/200A Clamp PQ4 | 3024460 | 4-phase Mini Current Clamp Set | 780.00 |
| i40S-EL | 4637396 | Fluke-17xx i40s-EL Clamp-on Current Transformer | 218.00 |
| i40S-EL/3pk | 4637409 | Fluke-17xxx i40s-EL Clamp-on Current Transformer, 3 pack | 608.00 |
| i400 | 2277225 | AC Current Clamp (400 A) | 170.00 |
| i400s | 2277202 | AC Current Clamp (400A) | 305.00 |
| i430-Flexi-TF-II | 4531725 | 6000A Fluke 430 Thin Flexi 61cm | 415.00 |
| i430-Flexi-TF-II-4PK | 4531733 | 6000A Fluke 430 Thin Flexi 61cm 4 Pack | 1263.00 |
| i5s | 2508467 | AC Current Clamp (5 A) | 567.00 |
| i5S-PR | 3949761 | 1750, 5A Current Clamp | 330.00 |
| i5sPQ3 | 2457508 | AC Current Clamp (5 A), 3-pack | 1363.00 |
| IEEE519/REPORT | 4589748 | SOFTWARE LICENSE FOR IEEE519 REPORTING | 533.00 |
| MP1-Magnet Probe 1 | 4589220 | Magnet probes for 4 mm banana, set of 4 | 95.00 |
| MBX USB-RS232 | 2539565 | EPO328Z, USB to Serial RS232 Adapter | 60.00 |
| OC4USB | 2166266 | Serial Interface Adapter/Cable (USB) | 169.00 |
| PM9080 | 1641983 | Serial Interface Adapter/Cable (RS232) | 280.00 |
| TLS430 | 2157713 | Test Leads and Alligator Clips (4 black, 1 green) - 430 Series | 136.00 |
| TPS Clamp 10A/1A | 2540445 | Clip-on Current Transformer 10A/1A (Fluke 1760) | 450.00 |
| TPS Clamp 50A/5A | 2540461 | Clip-on Current Transformer 50A/5A (Fluke 1760) | 450.00 |
| TPS Clamp 200A/20A | 2540450 | Clip-on Current Transformer 200A/20A (Fluke 1760) | 450.00 |
| TPS Flex 18-TF-II | 4531837 | 100/500A Fluke 1760 Thin Flexi 45cm (18in) | 469.00 |
| TPS Flex 24-TF-II | 4531843 | 200/1000A Fluke 1760 Thin Flexi 61cm (24in) | 469.00 |
| TPS Flex 36-TF-II | 4531855 | 3000/6000A Fluke 1760 Thin Flexi 91cm (36in) | 920.00 |
| TPS/MBX Dolph red | 2540744 | EPO326Z, Dolphin Clip, Red | 40.00 |
| TPS Nullmodem Cable | 2540511 | A550500510, RS232 Cross Link Cable, 3M | 50.00 |
| TPS Shunt 1A | 2540548 | A680501054, Shunt 1 A AC/DC | 400.00 |
| TPS Shunt 20MA | 2540553 | Shunt 20mA AC/DC (Fluke 1760) | 400.00 |
| TPS Voltprobe 10V | 2540636 | Voltage Probe 10V (Fluke 1760) | 350.00 |

| Model | Art. nr | Description | EUR |
|------------------------|---------|---|---------|
| TPS Voltprobe 100V | 2540624 | Voltage Probe 100V (Fluke 1760) | 350.00 |
| TPS Voltprobe 400V | 2540660 | Voltage Probe 400V (Fluke 1760) | 350.00 |
| TPS Voltprobe 600V | 2540697 | Voltage Probe 600V (Fluke 1760) | 350.00 |
| TPS Voltprobe 1KV | 2540649 | Voltage Probe 1000V (Fluke 1760) | 600.00 |
| VL1735/45 | 3276205 | Banana 4-Phase Voltage Lead set for Fluke-1735/45 | 251.00 |
| Fluke MA-C8 | 4945842 | Wall outlet adapter, Fluke-174X | 21.00 |
| IP65 Adapter Set | 4946241 | IP65 rated Voltage Connector | 221.00 |
| I17XX-FLEX1.5KIP | 4921003 | IP65 iFlexi 1.5KA 60 cm | 221.00 |
| I17XX-FLEX1.5KIP/3PK | 4921015 | IP65 iFlexi 1.5KA 60 cm, 3 Pack | 529.00 |
| I17XX-FLEX1.5KIP/4PK | 4921026 | IP65 iFlexi 1.5KA 60 cm, 4 Pack | 706.00 |
| I17XX-FLEX3KIPK | 4921032 | IP65 iFlexi 3KA 60 cm | 221.00 |
| I17XX-FLEX3KIP/3PK | 4921044 | IP65 iFlexi 3KA 60 cm, 3 Pack | 529.00 |
| I17XX-FLEX3KIP/4PK | 4921067 | IP65 iFlexi 3KA 60 cm, 4 Pack | 706.00 |
| I17XX-FLEX6KIPK | 4921071 | IP65 iFlexi 6KA 90 cm | 264.00 |
| I17XX-FLEX6KIP/3PK | 4921080 | iFlexi 6KA 90 cm, 3 Pack | 617.00 |
| I17XX-FLEX6KIP/4PK | 4921098 | iFlexi 6KA 90 cm, 4 Pack | 793.00 |
| I17XX-FLEX5M-EXT | 4921116 | iFlexi Extension Cable, 5m | 133.00 |
| Fluke 174X_3541-HANGER | 4890129 | Hanger Kit | 63.00 |
| Fluke 174X GPS-REC | 4921133 | GPS Receiver Antenna | 340.00 |
| F17XX Cable Markers | 4921140 | Cable Marker set, 05MM | 53.00 |
| MP1-3R/1B | 4944790 | 3 red/1 black Magnet probe for 4 mm banana | 95.00 |
| 3PHVL-17XX-5M | 5014816 | Cable assembly, Voltage test lead 3-phase+N 5M | 124.00 |
| FLUKE-17XX-TL | 5016873 | Test lead set; 1000V CAT III, nonstack/stack 0.18M | 35.00 |
| FLUKE-17XX-TL-2M | 5020006 | Blue, non-stackable plug and 2x alligator clips | 26.00 |
| FLUKE-PQ400 | 4920947 | Power Quality Window | 1693.00 |
| FLUKE-PQ400/B | 5075807 | Power Quality Window, basic | 1337.00 |
| I17XX-FLEX2M-M2M4P | 5076272 | Male-male cable 2m, 4 pcs | 513.00 |
| I17XX-FLEX2M-M2M1P | 5076285 | Male-male cable 2m, 1 pce | 134.00 |
| FLUKE-PQ-MARKER | 5046009 | Cable market set 3P+N+PE | 9.00 |
| I17XX-BNC-M2M | 5076297 | Fluke-17xx 4 pin male to BNC male cable 2m (1x) | 89.00 |
| I17XX-BNC-M2F | 5076304 | Fluke-17xx 4 pin male to BNC female cable 0.1m (1x) | 89.00 |

Vibration Testers

| | | | |
|------------------|---------|--|---------|
| Fluke 805 | 4094385 | Vibration Meter | 1859.00 |
| Fluke 805 FC | 4489229 | Vibration Meter with Fluke Connect | 1859.00 |
| Fluke 805/ES | 4636786 | External Vibration Sensor | 1084.00 |
| Fluke 810 | 3542635 | Vibration Tester | 9695.00 |
| Fluke 820-2 | 4550041 | LED Stroboscope | 949.00 |
| Fluke 830 | 4454396 | Laser Alignment Tool | 7250.00 |
| Fluke 830/Magnet | 4528249 | Magnetic Bracket | 860.00 |
| Fluke 830/Shims | 4551330 | Laser Alignment Tool, Shims | 854.00 |
| 810S | 3530828 | Sensor | 1478.00 |
| 810QDC | 3530837 | Quick Disconnect Cable | 154.00 |
| 810SMM | 3530862 | Sensor Magnet Mount | 217.00 |
| 810SMP | 3530855 | Sensor Mounting Pads (10-pack) | 30.00 |
| SBP-810 | 3530843 | Smart Battery Pack | 275.00 |
| Fluke-810PA | 3986002 | AC Power Adapter with International Plug Set | 87.00 |

Process Calibrators

700 Series Process Calibrators

| | | | |
|------------------|---------|------------------------------------|---------|
| Fluke 154 INTL | 4805625 | HART Calibration Assistant | 3875.00 |
| Fluke 705 | 665091 | Loop Calibrator | 780.00 |
| Fluke 707 | 1617262 | Loop Calibrator | 897.00 |
| Fluke 707Ex | 2032187 | Intrinsically Safe Loop Calibrator | 1261.00 |
| Fluke 709 | 4234350 | Precision Loop Calibrator | 910.00 |
| Fluke 709H | 4234361 | Precision HART Loop Calibrator | 1432.00 |
| Fluke 710 | 4991049 | mA Loop, Valve Tester, with HART | 2209.00 |
| Fluke 712B | 4387857 | RTD Temperature Calibrator | 1157.00 |
| Fluke 714B | 4387869 | TC Temperature Calibrator | 1157.00 |
| Fluke 715 | 620101 | Volt/mA Calibrator | 1301.00 |
| Fluke 717 1G | 2547166 | Pressure Calibrator (68.9 mbar) | 1477.00 |
| Fluke 717-15G | 4058808 | Pressure Calibrator (1 bar) | 1477.00 |
| Fluke 717 100G | 1630430 | Pressure Calibrator (7 bar) | 1477.00 |
| Fluke 717 30G | 662897 | Pressure Calibrator (2 bar) | 1532.00 |
| Fluke 717 300G | 2547175 | Pressure Calibrator (20 bar) | 1477.00 |
| Fluke 717 500G | 2547182 | Pressure Calibrator (34.7 bar) | 1477.00 |
| Fluke 717 1000G | 2547194 | Pressure Calibrator (69 bar) | 1477.00 |
| Fluke 717 1500G | 2547203 | Pressure Calibrator (103.4 bar) | 1637.00 |
| Fluke 717 3000G | 2547215 | Pressure Calibrator (207 bar) | 1637.00 |
| Fluke 717 5000G | 2547232 | Pressure Calibrator (345 bar) | 1637.00 |
| Fluke 717-10000G | 4058813 | Pressure Calibrator (690 bar) | 1637.00 |
| Fluke 718 30G | 665075 | Pressure Calibrator (2 bar) | 2781.00 |
| Fluke 718 1G | 2547148 | Pressure Calibrator (68.9 mbar) | 2831.00 |

| Model | Art. nr | Description | EUR |
|--------------------|---------|---|---------|
| Fluke 718 100G | 665080 | Pressure Calibrator (7 bar) | 2781.00 |
| Fluke 718 300G | 2547153 | Pressure Calibrator (20 bar) | 2831.00 |
| Fluke 718Ex 30G | 2096310 | Intrinsically Safe Pressure Calibrator (2 bar) | 3576.00 |
| Fluke 718Ex 100G | 2096322 | Intrinsically Safe Pressure Calibrator (7 bar) | 3576.00 |
| Fluke 718Ex 300G | 3023328 | Intrinsically Safe Pressure Calibrator (20 bar) | 3576.00 |
| Fluke 719 30G | 3315332 | Electric Pressure Calibrator (2 bar) | 3604.00 |
| Fluke 719 100G | 3315344 | Electric Pressure Calibrator (7 bar) | 3604.00 |
| Fluke-719PRO 30G | 4353218 | Electric Pressure Calibrator, 2 bar | 3299.00 |
| Fluke-719PRO 150G | 4353229 | Electric Pressure Calibrator, 10 bar | 3299.00 |
| Fluke-719PRO 300G | 4353234 | Electric Pressure Calibrator, 20 bar | 3299.00 |
| Fluke 720URTD | 4382695 | Universal RTD adapter for 721, 721Ex and 719PRO | 189.00 |
| Fluke-721-1601 | 4353241 | Dual Sensor Pressure Calibrator, 1.1 bar, 6.9 bar | 2100.00 |
| Fluke-721-1603 | 4353283 | Dual Sensor Pressure Calibrator, 1.1 bar, 20 bar | 2100.00 |
| Fluke-721-1605 | 4353327 | Dual Sensor Pressure Calibrator, 1.1 bar, 34 bar | 2100.00 |
| Fluke-721-1610 | 4353366 | Dual Sensor Pressure Calibrator, 1.1 bar, 69 bar | 2100.00 |
| Fluke-721-1615 | 4353401 | Dual Sensor Pressure Calibrator, 1.1 bar, 103 bar | 2100.00 |
| Fluke-721-1630 | 4353447 | Dual Sensor Pressure Calibrator, 1.1 bar, 200 bar | 2100.00 |
| Fluke-721-1650 | 4353486 | Dual Sensor Pressure Calibrator, 1.1 bar, 345 bar | 2100.00 |
| Fluke-721-3601 | 4353252 | Dual Sensor Pressure Calibrator, 2.48 bar, 6.9 bar | 2100.00 |
| Fluke-721-3603 | 4353290 | Dual Sensor Pressure Calibrator, 2.48 bar, 20 bar | 2100.00 |
| Fluke-721-3605 | 4353330 | Dual Sensor Pressure Calibrator, 2.48 bar, 34 bar | 2100.00 |
| Fluke-721-3610 | 4353375 | Dual Sensor Pressure Calibrator, 2.48 bar, 69 bar | 2100.00 |
| Fluke-721-3615 | 4353412 | Dual Sensor Pressure Calibrator, 2.48 bar, 103 bar | 2100.00 |
| Fluke-721-3630 | 4353458 | Dual Sensor Pressure Calibrator, 2.48 bar, 200 bar | 2100.00 |
| Fluke-721-3650 | 4353499 | Dual Sensor Pressure Calibrator, 2.48 bar, 345 bar | 2100.00 |
| Fluke 721EX-1601 | 4353265 | Dual Sensor Pressure Calibrator, 16, 100 PSIG | 2713.00 |
| Fluke 721EX-1603 | 4353309 | Dual Sensor Pressure Calibrator, 16, 300 PSIG | 2713.00 |
| Fluke 721EX-1605 | 4353348 | Dual Sensor Pressure Calibrator, 16, 500 PSIG | 2713.00 |
| Fluke 721EX-1610 | 4353382 | Dual Sensor Pressure Calibrator, 16, 1000 PSIG | 2713.00 |
| Fluke 721EX-1615 | 4353420 | Dual Sensor Pressure Calibrator, 16, 1500 PSIG | 2713.00 |
| Fluke 721EX-1630 | 4353464 | Dual Sensor Pressure Calibrator, 16, 3000 PSIG | 2713.00 |
| Fluke 721EX-1650 | 4353506 | Dual Sensor Pressure Calibrator, 16, 5000 PSIG | 2713.00 |
| Fluke 721EX-3601 | 4353276 | Dual Sensor Pressure Calibrator, 36, 100 PSIG | 2713.00 |
| Fluke 721EX-3603 | 4353311 | Dual Sensor Pressure Calibrator, 36, 300 PSIG | 2713.00 |
| Fluke 721EX-3605 | 4353353 | Dual Sensor Pressure Calibrator, 36, 500 PSIG | 2713.00 |
| Fluke 721EX-3610 | 4353394 | Dual Sensor Pressure Calibrator, 36, 1000 PSIG | 2713.00 |
| Fluke 721EX-3615 | 4353435 | Dual Sensor Pressure Calibrator, 36, 1500 PSIG | 2713.00 |
| Fluke 721EX-3630 | 4353473 | Dual Sensor Pressure Calibrator, 36, 3000 PSIG | 2713.00 |
| Fluke 721EX-3650 | 4353514 | Dual Sensor Pressure Calibrator, 36, 5000 PSIG | 2713.00 |
| Fluke 724 | 1553041 | Temperature Calibrator | 2373.00 |
| Fluke 725 | 664133 | Multifunction Process Calibrator | 3314.00 |
| Fluke 725Ex | 2098179 | Intrinsically Safe Multifunction Process Calibrator | 4145.00 |
| Fluke 726 | 2452080 | Precision Multifunction Process Calibrator | 3882.00 |
| Fluke 729 30G FC | 4856907 | Automatic Pressure Calibrator , w/FC (2 Bar) | 8593.00 |
| Fluke 729 150G FC | 4856894 | Automatic Pressure Calibrator, w/FC (10 Bar) | 8593.00 |
| Fluke 729 300G FC | 4856882 | Automatic Pressure Calibrator, w/FC (20 Bar) | 8593.00 |
| Fluke 729 30G | 4856990 | Automatic Pressure Calibrator (2 Bar) | 8593.00 |
| Fluke 729 150G | 4856983 | Automatic Pressure Calibrator (10 Bar) | 8593.00 |
| Fluke 729 300G | 4856976 | Automatic Pressure Calibrator (20 Bar) | 8593.00 |
| Fluke 729/750SW BU | 4972518 | Automatic Pressure Calibrator, w/DPC Track2 Bundle | 9984.00 |
| Fluke 753 EU | 4411027 | Documenting Process Calibrator | 5600.00 |
| Fluke 754 EU | 4400387 | Documenting Process Calibrator | 7057.00 |
| Fluke 771 | 2646347 | Milliamp Process Clamp Meter | 629.00 |
| Fluke 772 | 3362352 | Milliamp Process Clamp Meter | 899.00 |
| Fluke 773 | 3362365 | Milliamp Process Clamp Meter | 1149.00 |
| Fluke 787B | 4777186 | Process Meter | 1050.00 |
| Fluke 789/E | 3977194 | Process Meter | 1180.00 |
| Fluke 789/IR3000FC | 4604605 | Process Meter and FC connector | 1205.00 |

Pressure Modules

| | | | |
|---------------|---------|--|--------|
| Fluke-700G01 | 4353523 | Pressure Gauge, -10" to 10" WC (27 mbar) | 799.00 |
| Fluke-700G02 | 4353538 | Pressure Gauge, -30" to 30" WC (69 mbar) | 799.00 |
| 700G04 | 4096972 | Pressure Gauge, +/- 1 bar | 799.00 |
| 700G05 | 4097514 | Pressure Gauge, 2 bar | 799.00 |
| 700G06 | 4097538 | Pressure Gauge, 6.9 bar | 799.00 |
| 700G07 | 4097561 | Pressure Gauge, 34 bar | 799.00 |
| 700G08 | 4097592 | Pressure Gauge, 69 bar | 799.00 |
| 700G27 | 4097545 | Pressure Gauge, 20 bar | 799.00 |
| 700G29 | 4097605 | Pressure Gauge, 200 bar | 799.00 |
| 700G30 | 4097610 | Pressure Gauge, 345 bar | 799.00 |
| 700G31 | 4097622 | Pressure Gauge, 690 bar | 799.00 |
| Fluke-700GA4 | 4353545 | Pressure Gauge, 1 bar absolute | 799.00 |
| Fluke-700GA5 | 4353550 | Pressure Gauge, 2 bar absolute | 799.00 |
| Fluke-700GA6 | 4353561 | Pressure Gauge, 6.9 bar absolute | 799.00 |
| Fluke-700GA27 | 4353577 | Pressure Gauge, 20 bar absolute | 799.00 |

| Model | Art. nr | Description | EUR |
|-----------------|---------|---|---------|
| 700HTPK | 4124358 | Hydraulic Test Pump Kit, 0 to 690 bar | 1215.00 |
| Fluke 700HTPK2 | 4623314 | Premium hydraulic test pump kit | 1539.00 |
| Fluke 700MTH | 4623345 | Premium metric pressure test hose | 566.00 |
| Fluke 700M20TH | 4623338 | Premium M20 pressure test hose | 566.00 |
| 700PCK | 100062 | Pressure Module Calibration Kit | 1412.00 |
| Fluke 700PTPK | 4124364 | Pneumatic Test Pump Kit, 0 to 41 bar | 649.00 |
| Fluke 700PTPK2 | 4623306 | Premium pneumatic test pump kit | 1422.00 |
| 700G/TRACK | 4123225 | Data Logging Cable & Software | 469.00 |
| Fluke-700RG05 | 4353589 | Pressure Gauge, Reference, +2 bar | 884.00 |
| Fluke-700RG06 | 4353592 | Pressure Gauge, Reference, 6.9 bar | 884.00 |
| Fluke-700RG07 | 4353605 | Pressure Gauge, Reference, 34 bar | 884.00 |
| Fluke-700RG08 | 4353610 | Pressure Gauge, Reference, 69 bar | 884.00 |
| Fluke-700G10 | 4353654 | Pressure Gauge, 140 bar | 799.00 |
| Fluke-700RG29 | 4353622 | Pressure Gauge, Reference, 200 bar | 884.00 |
| Fluke-700RG30 | 4353631 | Pressure Gauge, Reference, 345 bar | 884.00 |
| Fluke-700RG31 | 4353646 | Pressure Gauge, Reference, 690 bar | 884.00 |
| Fluke 700TTH5K | 4623323 | Premium pressure transmitter test hose | 566.00 |
| Fluke 700TTH10K | 4636393 | Premium pressure transmitter test hose kit, 10K | 673.00 |
| 750P00 | 4352270 | Pressure Module (0 - 2.5 mbar) | 1695.00 |
| 750P01 | 4352281 | Pressure Module (0 - 25 mbar) | 1325.00 |
| 750P02 | 4352750 | Pressure Module (0 - 70 mbar) | 1325.00 |
| 750P22 | 4352296 | Pressure Module (0 - 70 mbar) | 1325.00 |
| 750P03 | 4352738 | Pressure Module (0 - 350 mbar) | 1325.00 |
| 750P23 | 4352308 | Pressure Module (0 - 350 mbar) | 1325.00 |
| 750P04 | 4352313 | Pressure Module (0 - 1 bar) | 1325.00 |
| 750P24 | 4352324 | Pressure Module (0 - 1 bar) | 1325.00 |
| 750P05 | 4352336 | Pressure Module (0 - 2 bar) | 1325.00 |
| 750P06 | 4352349 | Pressure Module (0 - 7 bar) | 1325.00 |
| 750P27 | 4352351 | Pressure Module (0 - 20 bar) | 1325.00 |
| 750P07 | 4352360 | Pressure Module (0 - 35 bar) | 1325.00 |
| 750P08 | 4352372 | Pressure Module (0 - 70 bar) | 1325.00 |
| 750P09 | 4352385 | Pressure Module (0 - 100 bar) | 1325.00 |
| 750P2000 | 4352397 | Pressure Module (0 - 140 bar) | 1325.00 |
| 750P29 | 4352403 | Pressure Module (0 - 200 bar) | 2100.00 |
| 750P30 | 4352415 | Pressure Module (0 - 340 bar) | 2100.00 |
| 750P31 | 4352426 | Pressure Module (0 - 700 bar) | 2100.00 |
| 750PA3 | 4352432 | Pressure Module (0 - 350 mbar) | 1525.00 |
| 750PA4 | 4352444 | Pressure Module (0 - 1 bar) | 1525.00 |
| 750PA5 | 4352459 | Pressure Module (0 - 2 bar) | 1525.00 |
| 750PA6 | 4352467 | Pressure Module (0 - 7 bar) | 1525.00 |
| 750PA27 | 4352471 | Pressure Module (0 - 20 bar) | 1525.00 |
| 750PA7 | 4352480 | Pressure Module (0 - 35 bar) | 1525.00 |
| 750PA8 | 4352498 | Pressure Module (0 - 70 bar) | 1525.00 |
| 750PA9 | 4352500 | Pressure Module (0 - 100 bar) | 1525.00 |
| 750PV3 | 4352517 | Pressure Module (-350 mbar) | 1525.00 |
| 750PV4 | 4352521 | Pressure Module (-1 bar) | 1525.00 |
| 750PD2 | 4352539 | Pressure Module (-70 - 70 mbar) | 1525.00 |
| 750PD3 | 4352542 | Pressure Module (-350 - 350 mbar) | 1525.00 |
| 750PD10 | 4352556 | Pressure Module (-700 - 700 mbar) | 1525.00 |
| 750PD4 | 4352563 | Pressure Module (-1 - 1 bar) | 1525.00 |
| 750PD5 | 4352574 | Pressure Module (-1 - 2 bar) | 1525.00 |
| 750PD50 | 4352588 | Pressure Module (-1 - 3.5 bar) | 1525.00 |
| 750PD6 | 4352595 | Pressure Module (-1 - 7 bar) | 1525.00 |
| 750PD7 | 4352602 | Pressure Module (-1 - 14 bar) | 1525.00 |
| 750PD27 | 4352616 | Pressure Module (-1 - 20 bar) | 1525.00 |
| 750R04 | 4352625 | Pressure Module (0 - 1 bar) | 1525.00 |
| 750R06 | 4352633 | Pressure Module (0 - 7 bar) | 1525.00 |
| 750R27 | 4352640 | Pressure Module (0 - 20 bar) | 1525.00 |
| 750R07 | 4352657 | Pressure Module (0 - 35 bar) | 1525.00 |
| 750R08 | 4352669 | Pressure Module (0 - 70 bar) | 1525.00 |
| 750R29 | 4352678 | Pressure Module (0 - 200 bar) | 2213.00 |
| 750R30 | 4352684 | Pressure Module (0 - 340 bar) | 2213.00 |
| 750R31 | 4352691 | Pressure Module (0 - 700 bar) | 2213.00 |
| 750RD5 | 4352706 | Pressure Module (-1 - 2 bar) | 1670.00 |
| 750RD6 | 4352714 | Pressure Module (-1 - 7 bar) | 1670.00 |
| 750RD27 | 4352723 | Pressure Module (-0.8 - 20 bar) | 1670.00 |
| 750P01Ex | 4558658 | Ex Pressure Module (0 - 25 mbar) | 2467.00 |
| 750P24Ex | 4558686 | Ex Pressure Module (0 - 1 bar) | 2524.00 |
| 750P05Ex | 4558664 | Ex Pressure Module (0 - 2 bar) | 2524.00 |
| 750P06Ex | 4558673 | Ex Pressure Module (0 - 7 bar) | 2524.00 |
| 750P27Ex | 4558699 | Ex Pressure Module (0 - 20 bar) | 2524.00 |
| 750P09Ex | 4558725 | Ex Pressure Module (0 - 100 bar) | 2524.00 |
| 750P29Ex | 4558702 | Ex Pressure Module (0 - 200 bar) | 4215.00 |
| 750PA4Ex | 4558716 | Ex Pressure Module (0 - 1 bar) | 2673.00 |

| Model | Art. nr | Description | EUR |
|---------------------------------------|---------|--|---------|
| Process Calibrator Accessories | | | |
| 700HTH-1 | 2811795 | Hydraulic Test Hose | 944.00 |
| 700ILF | 1566730 | In-Line Filter | 110.00 |
| 700LTP-1 | 2811763 | Low Pressure Test Pump | 1007.00 |
| 700-IV | 202561 | Current Shunt | 499.00 |
| 700PMP | 617131 | Pressure Pump (10 bar) | 704.00 |
| 700PRV-1 | 2811808 | Pressure Relief Valve for 700HTP | 1135.00 |
| 700PTP-1 | 2811774 | Pneumatic Test Pump | 907.00 |
| 700SC | 667425 | Serial Interface Cable (Fluke 725/725Ex/726) | 243.00 |
| 700TC1 | 620119 | Thermocouple Plug Kits (10 types) | 145.00 |
| 700TC2 | 620127 | Thermocouple Plug Kits (5 types) | 119.00 |
| Fluke 720RTD | 4366669 | RTD Probe for 721, 721Ex and 719PRO | 279.00 |
| 787CAL 230 | 662996 | Calibration Module (Fluke 787) | 1134.00 |
| BC7217 | 668217 | Battery Charger | 323.00 |
| BE9005 240 | 946652 | Battery Eliminator | 299.00 |
| BE9005 220 | 946657 | Battery Eliminator | 299.00 |
| BP7235 | 668225 | NiMH Battery Pack | 265.00 |
| C700 | 606928 | Hard Case (700 Series) | 359.00 |
| C789 | 946694 | Soft Meter Case | 207.00 |
| FVF-SC2 | 1576734 | FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B) | 272.00 |
| FVF-Basic | 2396957 | FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B) | 166.00 |
| Fluke 700HTP-2 | 4096855 | Hydraulic Test Pump, 690 bar | 1158.00 |
| IR189USB | 2428108 | IR Cable - USB (280/180 Series, 1653, 789, 1550B) | 53.00 |
| BP7240 | 4022220 | 753/754 Spare Battery | 180.00 |
| Fluke 750SW | 4090343 | DPC/TRACK2-software | 3539.00 |
| BC7240 | 4022655 | Battery Charger (753/754) | 59.00 |
| HART Drywell Cable | 2111088 | Cable Kit, HART Drywellcontrol | 171.00 |
| Fluke-71x | 3345825 | Hose kit | 107.00 |
| Fluke 700TLK | 3829398 | Process Test Lead Kit | 145.00 |
| Fluke 709H/TRACK | 4281225 | Logging software with cable | 457.00 |
| Fluke 720URTD | 4382695 | Universal RTD adapter for 721, 721Ex and 719PRO | 189.00 |
| 754HCC | 3829410 | HART-Communication Cable | 91.00 |
| Fluke-71X-TRAP | 4380747 | Liquid dirt trap for 718 and 719Pro | 370.00 |

General Accessories

| | | | |
|-------------------------------------|---------|--|--------|
| Test Leads, Probes and Clips | | | |
| 80K-15 | 618113 | Probe, Electronic Air Cleaner | 310.00 |
| AC175 | 4101772 | Threaded Alligator Clip Set | 31.00 |
| AC220 | 1610103 | SureGrip Alligator Clip Set | 49.00 |
| AC280 | 1610115 | SureGrip Hook Clip Set | 39.00 |
| AC283 | 1610144 | SureGrip Pincer Clip Set | 44.00 |
| AC285 | 1610159 | SureGrip Alligator Clip Set | 25.00 |
| AC285-FTP | 4073928 | Alligator Clips and adaptors (FTP-1, FTPL-1) | 29.00 |
| AC288 | 4617784 | SureGrip™ Terminal block probe | 39.00 |
| AC87 | 1278079 | Heavy Duty Bus Bar Clip Set | 52.00 |
| AC89 | 873448 | Heavy Duty Insulation Piercing Test Clip | 58.00 |
| BP980 | 1616807 | Dual Banana Plug Kit | 59.00 |
| FTL660 | 2280204 | Fused Test Lead Set | 67.00 |
| FTP-1 | 3869437 | Fuse test probe set | 102.00 |
| FTPL-1 | 3869443 | Fuse test probe set with test leads | 112.00 |
| H900 | 1616818 | Test Lead Holder | 35.00 |
| Leadwrap | 4083525 | Durable Nylon Hook and Loop Fastener, 3 pack | 9.00 |
| T5-Kit | 3971169 | T5 Tester Accessory Starter Kit | 57.00 |
| T5-RLS | 4089137 | Replacement Test Lead Set (T5) | 25.00 |
| TL175 | 3521976 | Twist Guard Test Leads | 31.00 |
| TL175E | 3565554 | Twist Guard Test Leads, 4mm | 34.00 |
| TL220-1 | 3971178 | SureGrip Industrial Test Lead Set | 85.00 |
| TL221 | 2003602 | SureGrip Extension Lead Set | 38.00 |
| TL222 | 2003616 | SureGrip Silicone Test Lead Set | 38.00 |
| TL223-1 | 3971184 | SureGrip Electrical Test Lead Set | 78.00 |
| TL224 | 1610198 | SureGrip Silicone Test Lead Set | 34.00 |
| TL225-1 | 3971191 | Stray Voltage Eliminator test Lead Set | 113.00 |
| TL238 | 2132831 | SureGrip High Energy Test Lead Kit | 85.00 |
| TL27 | 668571 | Heavy Duty Test Lead Set | 39.00 |
| TL40 | 1590606 | Retractable Tip Test Lead Set | 57.00 |
| TL71-1 | 3971207 | TL71, Test Lead Set | 31.00 |
| TL75-1 | 3971218 | TL75, Test Lead Set | 26.00 |
| TL76 | 2032684 | All-in-one Test Lead Set | 44.00 |
| TL80A-1 | 3971229 | TL80A, Test Lead Set | 81.00 |
| TL81A | 1277073 | Deluxe Electronic Test Lead Kit | 170.00 |
| TL910 | 1616632 | Electronic Test Lead Set (with replacement tips) | 78.00 |
| TL930 | 1616671 | Patch Cords (60 cm) | 20.00 |
| TL932 | 1616680 | Patch Cords (90 cm) | 22.00 |

| Model | Art. nr | Description | EUR |
|--------------------------------|---------|--|---------|
| TL935 | 1616698 | Patch Cord Kit (60, 90, 120 cm) | 65.00 |
| TL940 | 1616705 | Mini-Hook Test Lead Set | 22.00 |
| TL950 | 1616710 | Mini-Pincer Test Lead Set | 39.00 |
| TL960 | 1616722 | Micro-Hook Test Lead Set | 22.00 |
| TL970 | 1616793 | Hook and Pincer Test Lead Kit | 81.00 |
| TLK1550-RTLK | 4112351 | Integral test lead & 10 kV clamp | 246.00 |
| TLK220 | 2097022 | SureGrip Accessory Kit | 158.00 |
| TLK-225 | 3971234 | TLK225, SureGrip Master Set | 170.00 |
| TLK281-1 | 3971241 | TLK281, Automotive Test Lead Kit | 150.00 |
| TLK-282-1 | 3971252 | TLK282, DeLuxe Automotive Test Lead Kit | 192.00 |
| TLK287 | 3045631 | Electronic Master Test Lead Kit | 180.00 |
| TLK289 | 3092521 | Industrial Master Test Lead Kit | 180.00 |
| TLK290 | 2435092 | Test Probe Kit | 67.00 |
| TLK291 | 2435108 | Fused Test Probe Set | 67.00 |
| TP1-1 | 3971265 | TP1, Test Probes | 20.00 |
| TP175 | 3521983 | TwistGuard test Probes, 2MM dia probe tips | 22.00 |
| TP175E | 3565568 | TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters | 24.00 |
| TP2-1 | 3971283 | TP2, Test Probes | 22.00 |
| TP220-1 | 3971276 | TP220, SureGrip Test Probes | 22.00 |
| TP38 | 1541636 | Slim Reach Test Probe Set (insulated) | 20.00 |
| TP74 | 1541649 | Lantern Tip Test Probe Set | 22.00 |
| TP80 | 873455 | Electronic Test Probe Set | 42.00 |
| TP912 | 1616644 | Replacement tips for TL910 | 39.00 |
| TP920 | 1616659 | Test Probe Adapter Kit | 57.00 |
| Current Clamps | | | |
| 80i-110s | 114519 | AC/DC Current Clamp (100 A) | 787.00 |
| i1000s | 1568487 | AC Current Clamp (1000 A) | 680.00 |
| i1010 | 617735 | AC/DC Current Clamp (1000 A) | 488.00 |
| i1010 Kit | 2096998 | AC/DC Current Clamp (1000 A) with Soft Case | 499.00 |
| i200 | 664755 | AC Current Clamp (200 A) | 170.00 |
| i2000 flex | 2584912 | AC Flexible Current Clamp (2000 A) | 340.00 |
| i200s | 664760 | AC Current Clamp (200 A) | 283.00 |
| i30 | 2584920 | AC/DC Current Clamp (30A) | 453.00 |
| i3000 flex-4PK | 2696367 | AC Flexible Current Clamp (3000 A), 4-pack | 1363.00 |
| i3000s | 657202 | AC Current Clamp (3000 A) | 818.00 |
| i3000s flex-24 | 2584888 | AC Flexible Current Clamp (3000 A), 610 mm | 521.00 |
| i3000s flex-36 | 2584901 | AC Flexible Current Clamp (3000 A), 915 mm | 624.00 |
| i30s | 2584935 | AC/DC Current Clamp (30A) | 624.00 |
| i310s | 2840309 | AC/DC Current Clamp (300A) | 374.00 |
| i400 | 2277225 | AC Current Clamp (400 A) | 170.00 |
| i400s | 2277202 | AC Current Clamp (400A) | 305.00 |
| I40S-PR (1750) | 3949777 | 40A Current Clamp (1750) | 392.00 |
| i410 | 617727 | AC/DC Current Clamp (400 A) | 283.00 |
| i410 Kit | 2097005 | AC/DC Current Clamp (400 A) with Soft Case | 329.00 |
| i6000s flex-24 | 2840311 | AC Current Clamp (6000 A) | 680.00 |
| i6000s flex-36 | 2840327 | AC Current Clamp (6000 A) | 794.00 |
| i800 | 2840283 | AC Current Clamp (800 A) | 244.00 |
| Temperature Accessories | | | |
| 80AK-A | 2747812 | Thermocouple Adapter | 36.00 |
| 80BK-A | 2747801 | Integrated DMM Temperature Probe (Type K) | 40.00 |
| 80CJ-M | 833046 | Male Mini Connectors (Type J) | 27.00 |
| 80CK-M | 779942 | Male Mini Connectors (Type K) | 27.00 |
| 80PJ-1 | 1288191 | Bead Probe (Type J) | 29.00 |
| 80PJ-9 | 1288218 | General Purpose Probe (Type J) | 73.00 |
| 80PJ-EXT | 1288234 | Extension Wire Kit (Type J) | 66.00 |
| 80PK-1 | 750422 | Bead Probe (Type K) | 38.00 |
| 80PK-10 | 3439199 | Pipe Clamp Temperature Probe (Type K) | 224.00 |
| 80PK-11 | 2724500 | Velcro Temperature Probe | 43.00 |
| 80PK-18 Kit | 3448859 | Pipe Clamp Temperature Probe Kit | 363.00 |
| 80PK-22 | 2098684 | SureGrip Immersion Probe | 111.24 |
| 80PK-24 | 2098691 | SureGrip Air Probe | 145.00 |
| 80PK-25 | 2098706 | SureGrip Piercing Probe | 131.00 |
| 80PK-26 | 2098714 | SureGrip General Purpose Probe | 145.00 |
| 80PK-27 | 2098723 | SureGrip Industrial Surface Probe | 397.00 |
| 80PK-3A | 874610 | Surface Probe (Type K) | 249.00 |
| 80PK-8 | 200360 | Pipe Clamp Temperature Probe (Type K) | 203.00 |
| 80PK-9 | 1288229 | General Purpose Probe (Type K) | 73.00 |
| 80PK-EXT | 1288241 | Extension Wire Kit (Type K) | 66.00 |
| 80PR-60 | 2148313 | RTD Temperature Probe (Fluke 66/68) | 80.00 |
| 80PT-25 | 2104397 | SureGrip Piercing Probe | 115.00 |
| 80PT-EXT | 1288252 | Extension Wire Kit (Type T) | 66.00 |
| 80T-150UA | 3190456 | Universal Temperature Probe (for DMMs) | 312.00 |
| 80TK | 736736 | Thermocouple Module (Type K) | 158.00 |

| Model | Art. nr | Description | EUR |
|-------------------------------|---------|--|--------|
| Cases and Holsters | | | |
| C10 | 897744 | Meter Holster | 30.00 |
| C100 | 827055 | Hard Meter and Accessory Case | 79.00 |
| C101 | 2437514 | Hard Case | 73.00 |
| C115 | 2826063 | Soft Meter Case | 70.00 |
| C116 | 2826074 | Soft Meter Case | 83.00 |
| C120 | 646189 | Hard Case (43B/120 Series) | 113.00 |
| C125 | 646858 | Soft Meter Case | 53.00 |
| C12A | 930529 | Soft Meter Case | 37.00 |
| C150 | 4111540 | Zippered Soft Carrying Case | 34.00 |
| C1600 | 2091049 | Meter and Accessory Case | 44.00 |
| C1620 | 4359042 | Carrying Case | 216.00 |
| C190 | 677401 | Hard Case (190 Series) | 266.00 |
| C195 | 677408 | Soft Case | 246.00 |
| C20 | 708396 | Hard Meter Case | 74.00 |
| C23 | 1663209 | Soft Meter Case | 30.00 |
| C25 | 681114 | Soft Meter Case | 63.00 |
| C280 | 3182785 | Soft Meter Case | 73.00 |
| C33 | 1664120 | Soft Meter Case | 34.00 |
| C345 | 3311173 | Soft Case | 89.00 |
| C35 | 2826056 | Soft Meter Case | 50.00 |
| C43 | 1663230 | Soft Meter Case | 94.00 |
| C50 | 762823 | Soft Meter Case | 44.00 |
| C510 | 1547885 | Leather Meter Case | 88.00 |
| C520A | 1629104 | Leather Tester Case | 67.00 |
| C550 | 1547919 | Tool Bag | 147.00 |
| C75 | 865535 | Soft Accessory Case | 21.00 |
| C781 | 619988 | Soft Meter Case | 108.00 |
| C789 | 946694 | Soft Meter Case | 207.00 |
| C799 Softcase | 4021731 | Field Softcase for 75X | 120.00 |
| C800 | 896220 | Hard Meter and Accessory Case | 80.00 |
| C90 | 466029 | Soft Meter Case | 44.00 |
| CXT170 | 3352567 | Rugged Pelican Hard Case | 191.00 |
| CXT280 | 3352571 | Rugged Pelican Hard Case | 191.00 |
| CXT80 | 3352559 | Rugged Pelican Hard Case | 191.00 |
| CXT1000 | 4628917 | Extreme Hard case | 191.00 |
| FLUKEPACK30 | 4983088 | Professional Tool Backpack | 169.00 |
| H3 | 1608458 | Holster (330 Series) | 48.00 |
| H5 | 649365 | Electrical Tester Holster (Fluke T5) | 37.00 |
| H6 | 2152040 | Infrared Thermometer Holster (Fluke 63/65/68/561) | 35.00 |
| H-T6 | 4910585 | T6 Belt Holster | 37.00 |
| H15 | 4111533 | Belt Holster for T100 series | 33.00 |
| H80M | 2138458 | Holster + Magnetic Hanger | 46.00 |
| Automotive Accessories | | | |
| BP880 | 2150594 | BNC to Female Double Stacking Banana Plug | 16.00 |
| BP881 | 2151015 | BNC to Male Double Stacking Banana Plug | 21.00 |
| PV350 | 919811 | Pressure Vacuum Module | 318.00 |
| RPM80 | 880849 | Inductive Pick-up | 108.00 |
| SCC128 | 2100199 | Automotive Accessory Kit (120 Series) | 749.00 |
| SCC198 | 2100208 | Automotive Accessory Kit (190 Series) | 942.00 |
| STL90 | 201233 | Automotive Shielded Test Lead Set (120/190 Series) | 261.00 |
| TAS90 | 614187 | Automotive Accessory Set (120/190 Series) | 73.00 |
| TL28A | 1273185 | Automotive Test Lead Set | 65.00 |
| TL82 | 2150636 | Automotive Pin and Socket Adapter Set | 129.00 |
| TP40 | 1567573 | Automotive Back Probe Pins (5 pcs) (4 mm) | 45.00 |
| TP81 | 2149098 | Insulation Piercing Clip Set (4 mm) | 63.00 |
| TP82 | 2149080 | Insulation Piercing Clip Set (2 mm) | 60.00 |
| TP88 | 2149102 | Rigid Back Probe Pin Set | 15.00 |
| Other Accessories | | | |
| 80K-40 | 382846 | High Voltage Probe | 318.00 |
| 80K-6 | 532424 | High Voltage Probe | 177.00 |
| EBC290 | 3894906 | External Battery Charger | 109.00 |
| FOM | 200428 | Fiber Optic Meter | 610.00 |
| FOS-850 | 200433 | Fiber Optic Light Source | 368.00 |
| FOS-850/1300 | 200441 | Fiber Optic Light Source | 901.00 |
| L200 | 2096346 | Probe Light | 27.00 |
| L205 | 2098588 | Mini Hat Light | 35.00 |
| L206 | 2098595 | Deluxe Hat Light | 44.00 |
| L210 | 2096379 | Probe light and probe extender | 43.00 |
| L215 | 2096368 | SureGrip kit with probe light and probe extender | 100.00 |
| LVD1 | 4571403 | Volt Light | 38.00 |
| LVD2 | 2740300 | Volt Light | 42.00 |
| MC50 | 2092300 | MeterCleaner Wipes, 50-pack | 100.00 |

| Model | Art. nr | Description | EUR |
|-----------|---------|---|--------|
| MC6 | 2092212 | MeterCleaner Wipes, 6-pack | 14.00 |
| PV350 | 919811 | Pressure Vacuum Module | 318.00 |
| SV225 | 3100477 | Stray Voltage Adapter | 76.00 |
| TPAK | 1281997 | ToolPak, Meter Hanging Kit | 44.00 |
| FL-45 EX | 4972422 | 45 lumen intrinsically safe flashlight | 46.00 |
| FL-120 EX | 4972431 | 120 lumen intrinsically safe flashlight | 71.00 |
| FL-150 EX | 4972446 | 150 lumen intrinsically safe flashlight | 92.00 |
| HL-200 EX | 4972410 | 200 lumen intrinsically safe headlamp | 92.00 |

| Fuses | | | |
|---------|---------|---|-------|
| 943121 | 943121 | Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm | 4.90 |
| 803293 | 803293 | Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm | 9.00 |
| 830828 | 830828 | Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm | 8.05 |
| 2279339 | 2279339 | Fuse, A:315mA (f), V:1000V, IR:10kA, 6.35x32 mm | 11.60 |
| 740670 | 740670 | Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm | 3.80 |

| Software | | | |
|-----------|---------|--|--------|
| FVF-Basic | 2396957 | FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B) | 166.00 |
| FVF-SC2 | 1576734 | FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B) | 272.00 |
| FVF-SC4 | 2687335 | FlukeView Forms Software + Cable (8845A/8846A) | 312.00 |
| FVF-SC5 | 2791314 | FlukeView Forms Basic (8845A/8846A) | 179.00 |
| FVF-UG | 1576741 | FlukeView Forms Upgrade | 146.00 |
| IR189USB | 2428108 | IR Cable - USB (280/180 Series, 1653, 789, 1550B) | 53.00 |
| SCC120E | 646684 | FlukeView Software + USB Cable + Case (120 Series) - English | 482.00 |
| SCC120F | 646692 | FlukeView Software + USB Cable + Case (Fluke 123) - French | 482.00 |
| SCC190 | 671826 | FlukeView Software + Cable + Case (190 Series) - English, French, German | 675.00 |
| SW90W | 3894923 | FlukeView Software | 373.00 |

