

Model	Description	Recommended End-user Price SAR	Oracle Article Nr	Part Nr.	EAN Code
<b>Fluke Connect - 3000 Series</b>					
Fluke 3000FC/EDA2	Electronics DMM and deluxe accessory kit	SAR 1,466.40	4699333	FLK-3000FC/EDA2	0095969799676
Fluke 3000FC/1AC-II	Electrician's DMM voltage tester and accessory kit	SAR 1,417.52	4699302	FLK-3000FC/1AC-II	0095969799645
<b>110 Series Multimeters</b>					
Fluke 113	True RMS Multimeter	SAR 590.32	3088053	FLUKE-113 EUR	0095969436298
Fluke 114	True RMS Multimeter	SAR 710.64	2583552	FLUKE-114 EUR	0095969344791
Fluke 115	True RMS Multimeter	SAR 921.20	2583583	FLUKE-115 EUR	0095969344814
Fluke 116	True RMS Multimeter	SAR 985.12	2583601	FLUKE-116 EUR	0095969344838
116/62MAX+ Kit	Fluke HVAC Multimeter and IR Thermometer Combo Kit	SAR 1,379.92	4296018	FLUKE-116/62 MAX+	0095969659192
Fluke 116/323 Kit	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	SAR 1,214.48	4296029	FLUKE-116/323 KIT	0095969659208
Fluke 117	True RMS Multimeter	SAR 1,082.88	2583647	FLUKE-117 EUR	0095969344852
Fluke 117/323 Kit	Fluke Electrician's Multimeter Combo Kit	SAR 1,458.88	4296034	FLUKE-117/323 EUR	0095969659215
C50	Soft Meter Case	SAR 188.00	762823	C50	0095969009874
<b>170 Series Multimeters</b>					
Fluke 175	True RMS Multimeter	SAR 1,199.44	1592901	FLUKE-175 EGFID	0095969095921
Fluke 177	True RMS Multimeter	SAR 1,488.96	1592874	FLUKE-177 EGFID	0095969095891
Fluke 179	True RMS Multimeter	SAR 1,541.60	1592842	FLUKE-179 EGFID	0095969095860
C90	Soft Meter Case	SAR 188.00	466029	C90	0095969003537
Fluke 179/EDA2/EUR	Electronics Combo Kit	SAR 1,654.40	3947719	FLUKE-179/EDA2/EUR	0095969586634
<b>200 Series Multimeters</b>					
Fluke 233	Remote Display Multimeter	SAR 1,575.44	3469334	FLUKE-233 EU	0095969498173
Fluke 279FC/iFlex	Wireless TRMS Thermal Multimeter w/iFlex	SAR 4,560.88	4684050	FLUKE-279FC/iFLEX	0095969794466
Fluke 287/EUR	True RMS Electronic Logging Multimeter with TrendCapture	SAR 2,538.00	3947781	FLUKE-287/EUR	0095969586665
Fluke 287/FVF/EUR	FlukeView Forms Combo Kit	SAR 3,218.56	3947796	FLUKE-287/FVF/EUR	0095969586672
Fluke 289/EUR	True RMS Industrial Logging Multimeter with TrendCapture	SAR 3,019.28	3947801	FLUKE-289/EUR	0095969586689
Fluke 289/FVF/EUR	Industrial Logging Multimeter and Software Combo Kit	SAR 3,421.60	3947812	FLUKE-289/FVF/EUR	0095969586696
C280	Soft Meter Case	SAR 180.48	3182785	C280	0095969443807
Fluke 287/FVF/IR3000	Fluke 287 FlukeView® Forms Combo Kit	SAR 3,353.92	4699316	FLK-287/FVF/IR3000	0095969799652
Fluke 289/FVF/IR3000	Fluke 289 FlukeView® Forms Combo Kit	SAR 3,748.72	4699325	FLK-289/FVF/IR3000	0095969799669
<b>20 Series Multimeters</b>					
Fluke 27II/EUR	Industrial Multimeter (IP67)	SAR 2,361.28	3947770	FLUKE-27II/EUR	0095969586658
Fluke 28II/EUR	True RMS Industrial Multimeter (IP67)	SAR 2,515.44	3947820	FLUKE-28II/EUR	0095969586702
Fluke 28 II Ex	Intrinsically safe true-rms digital multimeter	SAR 6,873.28	4017165	FLUKE-28IIEX	0095969599733
C25	Soft Meter Case	SAR 188.00	681114	C25	0095969006378
<b>70 Series Multimeters</b>					
Fluke 77-4/EUR	Multimeter	SAR 1,488.96	3947835	FLUKE-77-4/EUR	0095969586719
C90	Soft Meter Case	SAR 188.00	466029	C90	0095969003537
<b>80 Series Multimeters</b>					
Fluke 83-V/EUR	Multimeter	SAR 2,034.16	3947847	FLUKE-83-V/EUR	0095969586726
Fluke 87-V/EUR	True RMS Multimeter	SAR 1,966.48	3947858	FLUKE-87-V/EUR	0095969586733
Fluke 87-V/E2K/EUR	Industrial Electricians Combo Kit	SAR 2,699.68	3947864	FLUKE-87-V/E2K/EUR	0095969586740
C25	Soft Meter Case	SAR 188.00	681114	C25	0095969006378
<b>Bench Multimeters</b>					
Fluke 8808A 220V	5.5 Digit Multimeter	SAR 3,365.20	2802372	8808A 220V	0095969393522
Fluke 8808A 240V	5.5 Digit Multimeter	SAR 3,365.20	2802385	8808A 240V	0095969393539
Fluke 8808A/SU 220V	5.5 Digit Multimeter (software & cable)	SAR 4,286.40	2802459	8808A/SU 220V	0095969393607
Fluke 8808A/SU 240V	5.5 Digit Multimeter (software & cable)	SAR 4,286.40	2802467	8808A/SU 240V	0095969393614
Fluke 8808A/TL 220V	5.5 Digit Multimeter, 2X4W Test Lead Kit	SAR 3,722.40	3111085	8808A/TL 220V	0095969441520
Fluke 8808A/TL 240V	5.5 Digit Multimeter, 2X4W Test Lead Kit	SAR 3,722.40	3111097	8808A/TL 240V	0095969441537
Fluke 8845A 220V	6.5 Digit Precision Multimeter	SAR 4,324.00	2577352	8845A 220V	0095969344302
Fluke 8845A 240V	6.5 Digit Precision Multimeter	SAR 4,324.00	2577365	8845A 240V	0095969344319
Fluke 8845A/SU 220V	6.5 Digit Precision Multimeter (incl. software + cable)	SAR 5,188.80	2675315	8845A/SU 220V	0095969353915
Fluke 8845A/SU 240V	6.5 Digit Precision Multimeter (incl. software + cable)	SAR 5,188.80	2675332	8845A/SU 240V	0095969353939
Fluke 8846A 220V	6.5 Digit Precision Multimeter	SAR 6,053.60	2577383	8846A 220V	0095969344333
Fluke 8846A 240V	6.5 Digit Precision Multimeter	SAR 6,053.60	2577390	8846A 240V	0095969344340
Fluke 8846A/SU 220V	6.5 Digit Precision Multimeter (incl. software + cable)	SAR 6,937.20	2675367	8846A/SU 220V	0095969353960
Fluke 8846A/SU 240V	6.5 Digit Precision Multimeter (incl. software + cable)	SAR 6,937.20	2675380	8846A/SU 240V	0095969353984
884X-CASE	Hard Case (8845A/8846A)	SAR 1,297.20	2675552	884X-CASE	0095969354097
884X-RTD	100 OHM RTD Temperature Probe	SAR 2,162.00	2675468	884X-RTD	0095969354011
884X-SHORT	4-wire short	SAR 127.84	2653346	884X-SHORT	0095969352864
884X-USB	USB to RS232 Cable Adapter	SAR 639.20	2675479	884X-USB	0095969354028
884X-1G	USB Memory 1 GB	SAR 188.00	2675534	884X-1G	0095969354080
8845A-EFPT	Extended Fine Point Tip Adapter Set	SAR 56.40	2742690	8845A-EFPT	0095969370547
8845A-TPIT	Test Probe IC Tip Set	SAR 56.40	2742683	8845A-TPIT	0095969370530
FVF-UG	FlukeView Forms Upgrade	SAR 590.32	1576741	FVF-UG	0095969090469
FVF-SC4	FlukeView Forms Software + Cable (8845A/8846A)	SAR 1,500.24	2687335	FVF-SC4	0095969361811
FVF-SC5	FlukeView Forms Basic (8845A/8846A)	SAR 639.20	2791314	FVF-SC5	0095969390798
RS43	Serial Interface Cable	SAR 259.44	946470	RS43	0095969025256
TL2X4W-PTII	2x4 Wire Ohms Test Lead 2 mm Probe Tip	SAR 338.40	2826215	TL2X4W-PTII	0095969400114
TL2X4W-TWZ	2X4-Wire Ohms Tweezers Test Leads	SAR 432.40	2723629	TL2X4W-TWZ	0095969364126
Y8021	IEEE-488 Shielded Interface Cable, 1 m	SAR 1,331.04	708289	Y8021	0095969083553
Y8022	IEEE-488 Shielded Interface Cable, 2 m	SAR 1,605.52	708297	Y8022	0095969083560
Y8846S	Rack mount kit single (8845A/8846A)	SAR 413.60	2675518	Y8846S	0095969354066
Y8846D	Rack mount kit dual (8845A/8846A)	SAR 526.40	2771721	Y8846D	0095969378680
<b>Automotive Meters</b>					
Fluke 88V/A	Automotive Meter Combo Kit	SAR 3,226.08	2117440	FLUKE-88-V/A KIT	0095969249072
<b>Clamp Meters</b>					
Ti400	True RMS Clamp Meter	SAR 579.04	4152628	FLUKE-323	0095969623742
Fluke 324	True RMS Clamp Meter	SAR 808.40	4152637	FLUKE-324	0095969623759
Fluke 325	True RMS Clamp Meter	SAR 1,222.00	4152643	FLUKE-325	0095969623766
Fluke 353	AC/DC True RMS Clamp Meter	SAR 3,365.20	2840252	FLUKE-353	0095969401197
Fluke 355	AC/DC True RMS Clamp Meter	SAR 3,955.52	2840265	FLUKE-355	0095969401203
Fluke 365	Detachable TRMS Clamp Meter	SAR 1,274.64	3790607	FLUKE-365/E	0095969559874
Fluke 368	Leakage current clamp meter, 40mm jaw	SAR 3,237.36	4709866	FLUKE-368	0095969803045
Fluke 369	Leakage current clamp meter, 61mm jaw	SAR 3,237.36	4709882	FLUKE-369	0095969803069

Fluke 368 FC	Wireless leakage current clamp, 40mm jaw	SAR	3,237.36	4709907	FLUKE-368 FC	0095969803083
Fluke 369 FC	Wireless leakage current clamp, 61mm jaw	SAR	3,237.36	4709934	FLUKE-369 FC	0095969803113
Fluke 373	600A TRMS Clamp Meter	SAR	1,105.44	3790564	FLUKE-373/E	0095969559836
Fluke 374FC	600A AC/DC TRMS Wireless Clamp Meter	SAR	1,470.16	4696001	FLUKE-374 FC	0095969798532
Fluke 375FC	600A AC/DC TRMS Wireless Clamp Meter	SAR	1,740.88	4695932	FLUKE-375 FC	0095969798464
Fluke 376FC	1000A AC/DC TRMS Wireless Clamp Meter with iFlex	SAR	1,989.04	4695861	FLUKE-376 FC	0095969798396
Fluke 374	600A TRMS Clamp meter	SAR	1,470.16	3790599	FLUKE-374/E	0095969559867
Fluke 375	600A TRMS Clamp Meter	SAR	1,740.88	3790586	FLUKE-375/E	0095969559850
Fluke 376	TRMS Clamp meter	SAR	2,049.20	3790573	FLUKE-376/E	0095969559843
Fluke 381	Remote Display TRMS Clamp Meter	SAR	2,692.16	3610452	FLUKE-381	0095969537483
Fluke 902 FC	TRMS Wireless HVAC ClampMeter	SAR	1,353.60	4695814	FLUKE-902 FC	0095969798341
62MAX+/323/1AC Kit	IR Thermometer, Clamp Meter and Voltage Detector Kit	SAR	1,214.48	4296076	FL62MAX+/323/1AC	0095969659253
Fluke 116/323 Kit	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	SAR	1,214.48	4296029	FLUKE-116/323 KIT	0095969659208
Fluke i2500-18	iFlex Probe	SAR	695.60	3676405	FLUKE-i2500-18	0095969559690
Fluke i2500-10	iFlex Probe	SAR	695.60	3676410	FLUKE-i2500-10	0095969559706
H3	Holster (330 Series)	SAR	169.20	1608458	H3	0095969102728
<b>CNX Wireless System</b>						
Fluke CNX v3000	CNX Wireless AC Voltage Module	SAR	834.72	4141973	FLK-CNX V3000	0095969621755
<b>Electrical Testers</b>						
Fluke 1000FLT	Fluorescent Light Tester	SAR	1,105.44	4472387	FLUKE-1000FLT	0095969724760
T6-1000/EU	Electrical Tester with FieldSense™, round	SAR	1,064.08	4910257	T6-1000/EU	0095969854030
T6-600/EU	Electrical Tester with FieldSense™, round	SAR	767.04	4910322	T6-600/EU	0095969854108
H-T6	T6 Belt Holster	SAR	150.40	4910585	H-T6	0095969854313
Fluke T5-600	Electrical Tester	SAR	548.96	659612	T5-600 EUR1	0095969059503
T5-600/62MAX+/1AC kit	Electrical Tester, IR Thermometer and Voltage Detector Kit	SAR	1,184.40	4297126	T5-600/62MAX+/1ACE	0095969659475
Fluke T5-1000	Electrical Tester	SAR	710.64	659570	T5-1000 EUR1	0095969059466
Fluke T5-H5-1AC II Kit	Electrical Tester Kit with Holster and 1AC	SAR	864.80	2098657	T5-H5-1AC KIT/EUR	0095969242660
Fluke T90	Voltage/continuity tester	SAR	274.48	4016945	FLUKE-T90	0095969599672
Fluke T110	Voltage/continuity tester with switchable load	SAR	391.04	4016950	FLUKE-T110	0095969599689
Fluke T130	Voltage/continuity tester with LCD, switchable load	SAR	590.32	4016961	FLUKE-T130	0095969599696
Fluke T150	Voltage/continuity tester with LCD, Ohms, switchable load	SAR	710.64	4016977	FLUKE-T150	0095969599702
Fluke SM100	Socket Tester	SAR	127.84	2406958	FLUKE-SM100	0095969284615
Fluke 2042	Cable Locator (Transmitter + Receiver)	SAR	3,688.56	2435038	FLUKE-2042	0095969291347
Fluke 2042T	Cable Locator Transmitter	SAR	2,049.20	2435045	FLUKE-2042T	0095969291354
Fluke 9040EUR	Phase Rotation Indicator	SAR	1,135.52	4014969	FLUKE-9040EUR	0095969599474
Fluke 9062	Motor and Phase Rotation Indicator	SAR	1,135.52	2435077	FLUKE-9062	0095969291385
LVD1	Volt Light	SAR	142.88	4571403	LVD1A	0095969773188
LVD2	Volt Light	SAR	191.76	2740300	LVD2	0095969369978
H5	Electrical Tester Holster (Fluke T5)	SAR	157.92	649365	H5	0095969057196
FTL660	Fused Test Lead Set	SAR	169.20	2280204	FTL-660	0095969269155
Fluke 1AC II	Volt Alert	SAR	142.88	2432971	FLUKE-1AC-E2-II	0095969290821
Fluke 1AC II 5PK	Volt Alert 5-pack	SAR	620.40	2433056	FLK-1AC-E1-II-5PK	0095969290906
FLK2AC/200-1000VCL	ACV Detector 200-1000V	SAR	142.88	3611985	FLK2AC/200-1000VCL	0095969537728
FLK2AC/90-1000V	ACV Detector 90-1000V, Flat-tip	SAR	142.88	3807928	FLK2AC/90-1000V	0095969564434
PRV240	Proving unit	SAR	691.84	4566209	PRV240	0095969772983
Fluke 117/PRV240	Proving unit, Fluke 117 DMM Kit	SAR	1,346.08	4636971	FLUKE-117/PRV240	0095969786621
PRV240FS	Proving unit, T6/NCV	SAR	680.56	4910310	PRV240FS	0095969854092
<b>Laser Levels</b>						
Fluke-3PR	3 Point laser level, red	SAR	838.48	4811457	FLUKE-3PR	0095969826884
Fluke-3PG	3 Point laser level, green	SAR	924.96	4811469	FLUKE-3PG	0095969826891
Fluke-180LR	2 Line laser level, red	SAR	1,094.16	4811504	FLUKE-180LR	0095969826938
Fluke-180LG	2 Line laser level, green	SAR	1,346.08	4811491	FLUKE-180LG	0095969826921
Fluke-180LG System	Green line laser with LDG detector	SAR	1,598.00	4811519	FLUKE-180LG SYSTEM	0095969826945
Fluke-180LR System	Red line laser with LDR detector	SAR	1,387.44	4811528	FLUKE-180LR SYSTEM	0095969826952
Fluke-LDR	Laser line detector red	SAR	379.76	4811543	FLUKE-LDR	0095969826969
Fluke-LDG	Laser line detector green	SAR	421.12	4819919	FLUKE-LDG	0095969828949
PLS-20513	Tripod Telescope 9 FT 6 IN	SAR	812.16	4791765	PLS-20513	0673740205136
PLS-20295	Magnetic Wall Bracket for PLS 3, 5, 180, 480	SAR	233.12	4845009	PLS-20295	0673740202951
PLS-20512	Tripod Standard, 5/8 X 11	SAR	485.04	4845027	PLS-20512	0673740205129
PLS-21502	Tripod Extender PLS3/180	SAR	48.88	4919812	PLS-21502	0095969856690
<b>Distance Meters</b>						
Fluke 414D	Laser Distance Meter	SAR	658.00	4106830	FLUKE-414D	0095969613552
Fluke 419D	Laser Distance Meter	SAR	1,364.88	4106853	FLUKE-419D	0095969613569
Fluke 424D	Laser Distance Meter	SAR	1,989.04	4106866	FLUKE-424D	0095969613576
414D/62MAX+ Kit	Fluke Laser distance meter and IR thermometer kit	SAR	1,143.04	4296052	FLUKE-414D/62MAX+	0095969659239
<b>Battery Analyzers</b>						
Fluke BT508	Battery Analyzer	SAR	11,874.08	4489962	FLUKE-BT508	0095969727235
Fluke BT510	Battery Analyzer	SAR	14,073.68	4489970	FLUKE-BT510	0095969727242
Fluke BT520	Battery Analyzer	SAR	17,593.04	4489981	FLUKE-BT520	0095969727259
Fluke BT521	Advanced Battery Analyzer	SAR	19,330.16	4489996	FLUKE-BT521	0095969727266
<b>Battery Analyzer Accessories</b>						
BT110	Standard Battery Analyzer Probes	SAR	1,767.20	4542264	BT110	0095969765510
BT120	Intelligent Test Probe Set, w/Extenders (no temp sensor)	SAR	2,654.56	4542273	BT120	0095969765527
BT121	Intelligent Test Probe Set, w/Extenders & Temp Sensor	SAR	3,301.28	4542286	BT121	0095969765534
BT1-A	Voltage/Current Probe Adapter	SAR	214.32	4542258	BT1-A	0095969765503
BC500	AC Power Charger	SAR	665.52	4542299	BC500	0095969765541
BP500	Lithium-Ion battery, 7.4V 3000 mAh	SAR	571.52	4542300	BP500	0095969765558
BT500	Probe tip, 10x replacement Probe tips, 2x long probe tip covers, 2x short probe	SAR	590.32	4561297	BT500-PROBE-TIP	0095969771207
i410	AC/DC Current Clamp (400 A)	SAR	1,188.16	6177277	i410	0095969048194
<b>Insulation Testers</b>						
Fluke 1503	Insulation Tester	SAR	2,064.24	2427883	FLUKE-1503	0095969288668
Fluke 1507	Insulation Tester	SAR	2,477.84	2427890	FLUKE-1507	0095969288675
Fluke 1550C	Insulation Resistance Tester (5kV)	SAR	15,299.44	3665021	FLUKE-1550C	0095969550918
Fluke 1550C/Kit	Insulation Resistance Tester Kit (5kV)	SAR	16,487.60	3665127	FLUKE-1550C/KIT	0095969550987
Fluke 1555	Insulation Resistance Tester (10kV)	SAR	18,021.68	3665056	FLUKE-1555	0095969550925
Fluke 1555/Kit	Insulation Resistance Tester Kit (10kV)	SAR	20,322.80	3665111	FLUKE-1555/KIT	0095969550970
Fluke 1577	Insulation Multimeter	SAR	2,680.88	2157280	FLUKE-1577	0095969262965
Fluke 1587	Insulation Multimeter	SAR	3,305.04	2157271	FLUKE-1587	0095969262958
Fluke 1587T	Insulation Multimeter (Telecom)	SAR	3,632.16	2517605	FLUKE-1587 T	0095969319768
Fluke 1587 FC	2-IN-1 Insulation Multimeter	SAR	3,338.88	4691215	FLUKE-1587 FC	0095969796620





FLK-100-CLKT	100mm C-Range IR Window, Kwik Twist	SAR	1,349.84	3460439	FLK-100-CLKT	0095969495905
Fluke CV200	50mm IR Window, hand turn door latch	SAR	1,000.16	4326955	FLUKE-CV200	009596967067
Fluke CV300	75mm IR Windows, hand turn door latch	SAR	1,398.72	4326962	FLUKE-CV300	009596967074
Fluke CV301	75mm IR Windows, security turn door latch	SAR	1,349.84	4338164	FLUKE-CV301	0095969670562
Fluke CV400	100 mm IR Windows, hand turn door latch	SAR	1,801.04	4326996	FLUKE-CV400	009596967081
Fluke CV401	100 mm IR Windows, security turn door latch	SAR	1,838.64	4338173	FLUKE-CV401	0095969670579
<b>ScopeMeters</b>						
<b>Industrial ScopeMeter</b>						
Fluke 123B/EU	Industrial ScopeMeter 20MHZ, EU	SAR	6,459.68	4755659	FLUKE-123B/EU	0095969814720
Fluke 123B/INT	Industrial ScopeMeter 20MHZ, INT	SAR	6,459.68	4755710	FLUKE-123B/INT	0095969814782
Fluke 124B/EU	Industrial ScopeMeter 40MHZ, EU	SAR	7,756.88	4755731	FLUKE-124B/EU	0095969814805
Fluke 124B/INT	Industrial ScopeMeter 40MHZ, INT	SAR	7,756.88	4755793	FLUKE-124B/INT	0095969814867
Fluke 125B/EU	Industrial ScopeMeter 40MHZ, EU	SAR	9,260.88	4755818	FLUKE-125B/EU	0095969814881
Fluke 125B/INT	Industrial ScopeMeter 40MHZ, INT	SAR	9,260.88	4755876	FLUKE-125B/INT	0095969814942
Fluke 123B/EU/S	Industrial ScopeMeter + SCC 20MHZ, EU	SAR	8,185.52	4755890	FLUKE-123B/EU/S	0095969814966
Fluke 123B/INT/S	Industrial ScopeMeter + SCC 20MHZ, INT	SAR	8,185.52	4755953	FLUKE-123B/INT/S	0095969815024
Fluke 124B/EU/S	Industrial ScopeMeter + SCC 40MHZ, EU	SAR	9,478.96	4755975	FLUKE-124B/EU/S	0095969815048
Fluke 124B/INT/S	Industrial ScopeMeter + SCC 40MHZ, INT	SAR	9,478.96	4756031	FLUKE-124B/INT/S	0095969815109
Fluke 125B/EU/S	Industrial ScopeMeter + SCC 40MHZ, EU	SAR	10,986.72	4756054	FLUKE-125B/EU/S	0095969815123
Fluke 125B/INT/S	Industrial ScopeMeter + SCC 40MHZ, INT	SAR	10,986.72	4756112	FLUKE-125B/INT/S	0095969815185
<b>190 Series ScopeMeters</b>						
Fluke 190-204/EU	ScopeMeter 4 Channel 200 MHz Color	SAR	21,432.00	3894409	FLUKE-190-204/EU	0095969579919
Fluke 190-204/UN	ScopeMeter 4 Channel 200 MHz Color	SAR	21,432.00	3894411	FLUKE-190-204/UN	0095969579926
Fluke 190-204/EU/S	ScopeMeter 4 Channel 200 MHz Color SCC	SAR	23,447.36	3894475	FLUKE-190-204/EU/S	0095969579988
Fluke 190-204/UN/S	ScopeMeter 4 Channel 200 MHz Color UNI SCC	SAR	23,447.36	3894482	FLUKE-190-204/UN/S	0095969579995
Fluke 190-104/EU	ScopeMeter 4 Channel 100 MHz Color EU	SAR	18,909.04	3894540	FLUKE-190-104/EU	0095969580052
Fluke 190-104/UN	ScopeMeter 4 Channel 100 MHz Color UNI	SAR	18,909.04	3894557	FLUKE-190-104/UN	0095969580069
Fluke 190-104/EU/S	ScopeMeter 4 Channel 100 MHz Color EU SCC	SAR	20,939.44	3894617	FLUKE-190-104/EU/S	0095969580120
Fluke 190-104/UN/S	ScopeMeter 4 Channel 100 MHz Color UNI SCC	SAR	20,939.44	3894621	FLUKE-190-104/UN/S	0095969580137
Fluke 190-062/EU	ScopeMeter 2 Channel 60 MHz Color	SAR	14,310.56	4025159	FLUKE-190-062/EU	0095969601276
Fluke 190-062/UN	ScopeMeter 2 Channel 60MHz Color	SAR	14,310.56	4025171	FLUKE-190-062/UN	0095969601283
Fluke 190-062/EU/S	ScopeMeter 2 Channel Color SCC	SAR	16,284.56	4025230	FLUKE-190-062/EU/S	0095969601344
Fluke 190-062/UN/S	ScopeMeter 2 Channel 60MHz Color SCC	SAR	16,284.56	4025248	FLUKE-190-062/UN/S	0095969601351
Fluke 190-102/EU	ScopeMeter 2 Channel 100MHz Color	SAR	16,792.16	4025318	FLUKE-190-102/EU	0095969601412
Fluke 190-102/UN	ScopeMeter 4 Channel 100MHz Color SCC	SAR	16,792.16	4025329	FLUKE-190-102/UN	0095969601429
Fluke 190-102/EU/S	ScopeMeter 2 Channel 100MHz Color SCC	SAR	18,811.28	4025383	FLUKE-190-102/EU/S	0095969601481
Fluke 190-102/UN/S	ScopeMeter 2 Channel 100MHz Color SCC	SAR	18,811.28	4025390	FLUKE-190-102/UN/S	0095969601498
Fluke 190-202/EU	ScopeMeter 2 Channel 200MHz Color	SAR	18,608.24	4025460	FLUKE-190-202/EU	0095969601559
Fluke 190-202/UN	ScopeMeter 2 Channel 200MHz Color	SAR	18,608.24	4025472	FLUKE-190-202/UN	0095969601566
Fluke 190-202/EU/S	ScopeMeter 2 Channel 200MHz Color SCC	SAR	20,619.84	4025554	FLUKE-190-202/EU/S	0095969601634
Fluke 190-202/UN/S	ScopeMeter 2 Channel 200MHz Color SCC	SAR	20,619.84	4025568	FLUKE-190-202/UN/S	0095969601641
Fluke 190-502/EU	ScopeMeter 2 Channel 500 MHz Color	SAR	23,161.60	4025623	FLUKE-190-502/EU	0095969601702
Fluke 190-502/UN	ScopeMeter 2 Channel 500 MHz Color UNI	SAR	23,161.60	4025638	FLUKE-190-502/UN	0095969601719
Fluke 190-502/EU/S	ScopeMeter 2 Channel 500 MHz Color Europe SCC	SAR	25,139.36	4025692	FLUKE-190-502/EU/S	0095969601771
Fluke 190-502/UN/S	ScopeMeter 2 Channel 500 MHz Color UNI SCC	SAR	25,139.36	4025704	FLUKE-190-502/UN/S	0095969601788
Fluke 190-504/EU	ScopeMeter 4 Channel 500MHz Color	SAR	24,650.56	4419875	FLUKE-190-504/EU	0095969696272
Fluke 190-504/UN	ScopeMeter 4 Channel 500MHz Color UNI	SAR	24,650.56	4419929	FLUKE-190-504/UN	0095969696326
Fluke 190-504/EU/S	ScopeMeter 4 Channel 500MHz Color Europe SCC	SAR	26,677.20	4419941	FLUKE-190-504/EU/S	0095969696340
Fluke 190-504/UN/S	ScopeMeter 4 Channel 500MHz Color UNI SCC	SAR	26,677.20	4419990	FLUKE-190-504/UN/S	0095969696395
<b>ScopeMeter Accessories</b>						
AC120	Heavy Duty Alligator Clips	SAR	180.48	646163	AC120	0095969052122
AS400	Probe Extension Set, for VPS400 Probes	SAR	548.96	3894880	AS400	0095969580397
BB120	Banana to BNC Adapter Plug	SAR	172.96	646171	BB120	0095969052139
BB120-II	Set of 2 banana to BNC adapter	SAR	195.52	4744369	BB120-II	0095969812771
BC190/808	Battery Charger/Line Voltage Adapter UNIVERSAL (190 Series)	SAR	590.32	1282244	BC190/808	0095969077903
BHT190	Set of Break-out Adapters	SAR	2,402.64	3379374	BHT190	0095969483032
BP120MH	NiMH Battery Pack (120 Series/43B)	SAR	496.32	2544081	BP120MH	0095969327237
BP190	NiMH Battery Pack (190 Series)	SAR	759.52	677390	BP190	0095969075725
BP290	Battery Pack Single Cap 190-series II	SAR	1,165.60	4025762	BP290	0095969601849
BP291	Battery Pack, Fluke 190 Series	SAR	1,515.28	3894688	BP291	0095969580199
C120	Hard Case (43B/120 Series)	SAR	533.92	646189	C120	0095969052146
C120B	Soft carrying case for 120B series	SAR	582.80	4744391	C120B	0095969812801
C125	Soft Meter Case	SAR	195.52	646858	C125	0095969052894
C190	Hard Case (190 Series)	SAR	853.52	677401	C190	0095969075749
C195	Soft Case	SAR	812.16	677408	C195	0095969075756
C290	Hard-Shell Carrying Case	SAR	1,011.44	3894803	C290	0095969580311
CS20MA	Current Shunt 4-20 mA	SAR	413.60	677393	CS20MA	0095969075732
EBC290	External Battery Charger	SAR	507.60	3894906	EBC290	0095969580410
HC120	Hook Clips	SAR	203.04	646668	HC120	0095969052634
HC120-II	Set of 2 hook clips	SAR	214.32	4744357	HC120-II	0095969812764
HC200	Hook Clips	SAR	180.48	2086410	HC200	0095969240154
HH290	Hanging Hook, ScopeMeter Series 190 II	SAR	394.80	3894844	HH290	0095969580359
MA190	Medical Accessory Kit (190 Series)	SAR	1,767.20	1567481	MA190	0095969087407
OC4USB	Serial Interface Adapter/Cable (USB)	SAR	891.12	2166266	OC4USB	0095969265430
PM8907/801	Battery Charger/Line Voltage Adapter EUR (120 Series)	SAR	421.12	613999	PM8907/801	0095969047364
PM8907/807	POWER ADAPTOR/BATTERY CHARGER	SAR	421.12	624764	PM8907/807	0095969052065
PM8907/808	Battery Charger/Line Voltage Adapter UNIVERSAL (120 Series)	SAR	496.32	614039	PM8907/808	0095969047388
PM9080	Serial Interface Adapter/Cable (RS232)	SAR	936.24	1641983	PM9080/101	0095969118071
PM9081	Dual Banana Plug to Female BNC Adapter	SAR	218.08	916093	PM9081/001	0095969014922
PM9082	Dual Banana Jack to Male BNC Adapter	SAR	218.08	916163	PM9082/001	0095969015011
PM9091	Coaxial BNC Cables (1.5 m)	SAR	421.12	935598	PM9091/001	0095969022064
PM9092	Coaxial BNC Cables (0.5 m)	SAR	376.00	935601	PM9092/001	0095969022071
PM9093	Male BNC to Female BNC Adapter	SAR	255.68	935593	PM9093/001	0095969022057
PM9096/201	Secondary Pick-up	SAR	1,455.12	651742	PM9096/201	0095969055260
RS120-III	Probe Accessory Replacement Set	SAR	466.24	4023947	RS120-III	0095969011123
RS400	Probe Replacement Set, for VPS400 Probes	SAR	642.96	3894867	RS400	0095969580373
RS500	Probe accessory replacement set for VPS500 probes	SAR	808.40	4025886	RS500	0095969601962
SCC120B	Software soft carry case accessory kit 120B series	SAR	2,154.48	4744423	SCC120B	0095969812832
SCC120E	FlukeView Software + USB Cable + Case (120 Series) - English	SAR	1,808.56	646684	SCC120E	0095969052658
SCC128	Automotive Accessory Kit (120 Series)	SAR	3,703.60	2100199	SCC 128	0095969243131
SCC198	Automotive Accessory Kit (190 Series)	SAR	4,316.48	2100208	SCC 198	0095969243148
SCC190	FlukeView Software + Cable + Case (190 Series) - English, French, German	SAR	2,601.92	671826	SCC190EFG	0095969075602
SCC290	Software and Carrying Case for 190 Series II	SAR	2,090.56	3894826	SCC290	0095969580335
SP120B	Screen protector for 120B series	SAR	195.52	4744414	SP120B	0095969812825
ST190	Automotive Shielded Test Lead Set (120/190 Series)	SAR	1,022.72	201233	ST190	0095969043076











750P30	Pressure Module (0 - 340 bar)	SAR	10,618.24	4352415	FLUKE-750P30	0095969673433
750P31	Pressure Module (0 - 700 bar)	SAR	10,618.24	4352426	FLUKE-750P31	0095969673440
750PA3	Pressure Module (0 - 350 mbar)	SAR	8,674.32	4352432	FLUKE-750PA3	0095969673457
750PA4	Pressure Module (0 - 1 bar)	SAR	7,708.00	4352444	FLUKE-750PA4	0095969673464
750PA5	Pressure Module (0 - 2 bar)	SAR	7,708.00	4352459	FLUKE-750PA5	0095969673471
750PA6	Pressure Module (0 - 7 bar)	SAR	7,708.00	4352467	FLUKE-750PA6	0095969673488
750PA27	Pressure Module (0 - 20 bar)	SAR	7,708.00	4352471	FLUKE-750PA27	0095969673495
750PA7	Pressure Module (0 - 35 bar)	SAR	7,708.00	4352480	FLUKE-750PA7	0095969673501
750PA8	Pressure Module (0 - 70 bar)	SAR	7,561.36	4352498	FLUKE-750PA8	0095969673518
750PA9	Pressure Module (0 - 100 bar)	SAR	7,561.36	4352500	FLUKE-750PA9	0095969673525
750PV3	Pressure Module (-350 mbar)	SAR	7,561.36	4352517	FLUKE-750PV3	0095969673532
750PV4	Pressure Module (-1 bar)	SAR	7,561.36	4352521	FLUKE-750PV4	0095969673549
750PD2	Pressure Module (-70 - 70 mbar)	SAR	7,561.36	4352539	FLUKE-750PD2	0095969673556
750PD3	Pressure Module (-350 - 350 mbar)	SAR	7,561.36	4352542	FLUKE-750PD3	0095969673563
750PD10	Pressure Module (-700 - 700 mbar)	SAR	7,561.36	4352556	FLUKE-750PD10	0095969673570
750PD4	Pressure Module (-1 - 1 bar)	SAR	7,561.36	4352563	FLUKE-750PD4	0095969673587
750PD5	Pressure Module (-1 - 2 bar)	SAR	7,561.36	4352574	FLUKE-750PD5	0095969673594
750PD50	Pressure Module (-1 - 3.5 bar)	SAR	7,561.36	4352588	FLUKE-750PD50	0095969673600
750PD6	Pressure Module (-1 - 7 bar)	SAR	7,561.36	4352595	FLUKE-750PD6	0095969673617
750PD7	Pressure Module (-1 - 14 bar)	SAR	7,561.36	4352602	FLUKE-750PD7	0095969673624
750PD27	Pressure Module (-1 - 20 bar)	SAR	7,561.36	4352616	FLUKE-750PD27	0095969673631
750R04	Pressure Module (0 - 1 bar)	SAR	7,561.36	4352625	FLUKE-750R04	0095969673648
750R06	Pressure Module (0 - 7 bar)	SAR	7,561.36	4352633	FLUKE-750R06	0095969673655
750R27	Pressure Module (0 - 20 bar)	SAR	7,561.36	4352640	FLUKE-750R27	0095969673662
750R07	Pressure Module (0 - 35 bar)	SAR	7,561.36	4352657	FLUKE-750R07	0095969673679
750R08	Pressure Module (0 - 70 bar)	SAR	7,561.36	4352669	FLUKE-750R08	0095969673686
750R29	Pressure Module (0 - 200 bar)	SAR	11,362.72	4352678	FLUKE-750R29	0095969673693
750R30	Pressure Module (0 - 340 bar)	SAR	11,362.72	4352684	FLUKE-750R30	0095969673709
750R31	Pressure Module (0 - 700 bar)	SAR	11,362.72	4352691	FLUKE-750R31	0095969673716
750RD5	Pressure Module (-1 - 2 bar)	SAR	8,505.12	4352706	FLUKE-750RD5	0095969673723
750RD6	Pressure Module (-1 - 7 bar)	SAR	8,505.12	4352714	FLUKE-750RD6	0095969673730
750RD27	Pressure Module (-0.8 - 20 bar)	SAR	8,505.12	4352723	FLUKE-750RD27	0095969673747
750P01Ex	Ex Pressure Module (0 - 25 mbar)	SAR	9,204.48	4558658	FLUKE-750P01EX	0095969769327
750P24Ex	Ex Pressure Module (0 - 1 bar)	SAR	9,204.48	4558686	FLUKE-750P24EX	0095969769358
750P05Ex	Ex Pressure Module (0 - 2 bar)	SAR	9,204.48	4558664	FLUKE-750P05EX	0095969769334
750P06Ex	Ex Pressure Module (0 - 7 bar)	SAR	9,204.48	4558673	FLUKE-750P06EX	0095969769341
750P27Ex	Ex Pressure Module (0 - 20 bar)	SAR	9,204.48	4558699	FLUKE-750P27EX	0095969769365
750P09Ex	Ex Pressure Module (0 - 100 bar)	SAR	9,204.48	4558725	FLUKE-750P09EX	0095969769396
750P29Ex	Ex Pressure Module (0 - 200 bar)	SAR	15,724.32	4558702	FLUKE-750P29EX	0095969769372
750PA4Ex	Ex Pressure Module (0 - 1 bar)	SAR	9,971.52	4558716	FLUKE-750PA4EX	0095969769389
<b>Process Calibrator Accessories</b>						
700HTH-1	Hydraulic Test Hose	SAR	2,553.04	2811795	FLUKE-700HTH-1	0095969397735
700ILF	In-Line Filter	SAR	345.92	1566730	FLUKE-700ILF	0095969087278
700LTP-1	Low Pressure Test Pump	SAR	3,481.76	2811763	FLUKE-700LTP-1	0095969397704
700-IV	Current Shunt	SAR	1,801.04	202561	FLUKE-700-IV	0095969045896
700PMP	Pressure Pump (10 bar)	SAR	2,180.80	617131	FLUKE-700PMP	0095969047999
700PRV-1	Pressure Relief Valve for 700HTP	SAR	3,019.28	2811808	FLUKE-700PRV-1	0095969397742
700PTP-1	Pneumatic Test Pump	SAR	3,267.44	2811774	FLUKE-700PTP-1	0095969397711
700SC	Serial Interface Cable (Fluke 725/725Ex/726)	SAR	770.80	667425	FLUKE-700SC	0095969071352
700TC1	Thermocouple Plug Kits (10 types)	SAR	470.00	620119	FLUKE-700TC1	0095969050791
700TC2	Thermocouple Plug Kits (5 types)	SAR	432.40	620127	FLUKE-700TC2	0095969050807
Fluke 720RTD	RTD Probe for 721, 721Ex and 719PRO	SAR	1,312.24	4366669	FLUKE-720RTD	0095969678285
787CAL 230	Calibration Module (Fluke 787)	SAR	3,650.96	662996	FLUKE-787CAL230	0095969063975
BC7217	Battery Charger	SAR	1,082.88	668217	BC7217 INTL	0095969066280
BE9005 240	Battery Eliminator	SAR	1,082.88	946652	BE9005 240	0095969024730
BP7235	NIMH Battery Pack	SAR	1,082.88	668225	BP7235	0095969066297
C700	Hard Case (700 Series)	SAR	1,146.80	606928	C700	0095969043342
C789	Soft Meter Case	SAR	609.12	946694	C789	0095969025089
FVF-SC2	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	SAR	1,150.56	1576734	FVF-SC2	0095969090483
FVF-Basic	FlukeView Forms Basic + IR USB cable (189, 287, 789, 1550B)	SAR	740.72	2396957	FVF-BASIC	0095969283236
Fluke 700HTP-2	Hydraulic Test Pump, 690 bar	SAR	4,816.56	4096855	FLUKE-700HTP-2	0095969610995
IR189USB	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	SAR	274.48	2428108	IR189USB	0095969288705
BP7240	753/754 Spare Battery	SAR	782.08	4022220	BP7240	0095969600927
Fluke 750SW	DPC/TRACK2-software	SAR	15,449.84	4090343	FLUKE-750SW	0095969610063
BC7240	Battery Charger (753/754)	SAR	214.32	4022655	BC-7240	0095969600972
HART Drywell Cable	Cable Kit, HART Drywell/control	SAR	887.36	2111088	HART DRYWELL CABLE	0095969246255
Fluke-71x	Hose kit	SAR	556.48	3345825	FLUKE-71X	0095969471756
Fluke 700TLK	Process Test Lead Kit	SAR	627.92	3829398	FLUKE-700TLK	0095969565608
Fluke 709H/TRACK	Logging software with cable	SAR	1,928.88	4281225	709H/TRACK	0095969565635
Fluke 720URTD	Universal RTD adapter for 721, 721Ex and 719PRO	SAR	894.88	4382695	FLUKE-720URTD	0095969683074
<b>General Accessories</b>						
<b>Test Leads, Probes and Clips</b>						
80K-15	Probe, Electronic Air Cleaner	SAR	1,150.56	618113	80K-15	0095969063517
AC175	Threaded Alligator Clip Set	SAR	135.36	4101772	AC175	0095969612425
AC220	SureGrip Alligator Clip Set	SAR	188.00	1610103	AC220	0095969103398
AC280	SureGrip Hook Clip Set	SAR	169.20	1610115	AC280	0095969103404
AC283	SureGrip Pincer Clip Set	SAR	188.00	1610144	AC283	0095969103411
AC285	SureGrip Alligator Clip Set	SAR	112.80	1610159	AC285	0095969103428
AC285-FTP	Alligator Clips and adaptors (FTP-1, FTPL-1)	SAR	157.92	4073928	AC285-FTP	0095969060448
AC288	SureGrip™ Terminal block probe	SAR	161.68	4617784	AC288	0095969783538
AC87	Heavy Duty Bus Bar Clip Set	SAR	195.52	1278079	AC87	0095969073223
AC89	Heavy Duty Insulation Piercing Test Clip	SAR	195.52	873448	AC89	0095969012287
BP980	Dual Banana Plug Kit	SAR	188.00	1616807	BP980	0095969107006
FTL660	Fused Test Lead Set	SAR	169.20	2280204	FTL-660	0095969269155
FTP-1	Fuse test probe set	SAR	432.40	3869437	FTP-1	0095969577144
FTPL-1	Fuse test probe set with test leads	SAR	492.56	3869443	FTPL-1	0095969577151
H900	Test Lead Holder	SAR	116.56	1616818	H900	0095969107013
Leadwrap	Durable Nylon Hook and Loop Fastener, 3 pack	SAR	30.08	4083525	LEADWRAP	0095969608312
TS-Kit	TS Tester Accessory Starter Kit	SAR	274.48	3971169	TS-KIT-1	0095969589840
TS-RLS	Replacement Test Lead Set (TS)	SAR	131.60	4089137	TS-RLS	0095969609791
TL175	Twist Guard Test Leads	SAR	135.36	3521976	TL175	0095969521543
TL175E	Twist Guard Test Leads, 4mm	SAR	150.40	3565554	TL175E	0095969528887
TL220-1	SureGrip Industrial Test Lead Set	SAR	360.96	3971178	TL220-1	0095969589857
TL221	SureGrip Extension Lead Set	SAR	139.12	2003602	TL221	0095969206433
TL222	SureGrip Silicone Test Lead Set	SAR	139.12	2003616	TL222	0095969206440
TL223-1	SureGrip Electrical Test Lead Set	SAR	338.40	3971184	TL223-1	0095969589864

TL224	SureGrip Silicone Test Lead Set	SAR	139.12	1610198	TL224	0095969103442
TL225-1	Stray Voltage Eliminator test Lead Set	SAR	522.64	3971191	TL225-1	0095969589871
TL238	SureGrip High Energy Test Lead Kit	SAR	349.68	2132831	TL238	0095969255417
TL27	Heavy Duty Test Lead Set	SAR	169.20	668571	TL27	0095969076739
TL40	Retractable Tip Test Lead Set	SAR	206.80	1590606	TL40	0095969096188
TL71-1	TL71, Test Lead Set	SAR	135.36	3971207	TL71-1	0095969589888
TL75-1	TL75, Test Lead Set	SAR	112.80	3971218	TL75-1	0095969589895
TL76	All-in-one Test Lead Set	SAR	157.92	2032684	TL76	0095969207607
TL80A-1	TL80A, Test Lead Set	SAR	330.88	3971229	TL80A-1	0095969589901
TL81A	Deluxe Electronic Test Lead Kit	SAR	703.12	1277073	TL81A	0095969079549
TL910	Electronic Test Lead Set (with replacement tips)	SAR	293.28	1616632	TL910	0095969106887
TL930	Patch Cords (60 cm)	SAR	78.96	1616671	TL930	0095969106924
TL932	Patch Cords (90 cm)	SAR	86.48	1616680	TL932	0095969106931
TL935	Patch Cord Kit (60, 90, 120 cm)	SAR	214.32	1616698	TL935	0095969106948
TL940	Mini-Hook Test Lead Set	SAR	116.56	1616705	TL940	0095969106955
TL950	Mini-Pincer Test Lead Set	SAR	195.52	1616710	TL950	0095969106962
TL960	Micro-Hook Test Lead Set	SAR	150.40	1616722	TL960	0095969106979
TL970	Hook and Pincer Test Lead Kit	SAR	421.12	1616793	TL970	0095969106993
TLK1550-RTLC	Integral test lead & 10 kV clamp	SAR	1,308.48	4112351	TLK1550-RTLC	0095969614931
TLK220	SureGrip Accessory Kit	SAR	650.48	2097022	TLK-220 EUR	0095969241861
TLK-225	TLK225, SureGrip Master Set	SAR	703.12	3971234	TLK-225-1	0095969589918
TLK281-1	TLK281, Automotive Test Lead Kit	SAR	650.48	3971241	TLK281-1	0095969589925
TLK-282-1	TLK282, Deluxe Automotive Test Lead Kit	SAR	827.20	3971252	TLK282-1	0095969589932
TLK287	Electronic Master Test Lead Kit	SAR	729.44	3045631	TLK287	0095969417853
TLK289	Industrial Master Test Lead Kit	SAR	729.44	3092521	TLK289 EUR	0095969436441
TLK290	Test Probe Kit	SAR	360.96	2435092	TLK290	0095969291408
TLK291	Fused Test Probe Set	SAR	360.96	2435108	TLK291	0095969291415
TP1-1	TP1, Test Probes	SAR	86.48	3971265	TP1-1	0095969589949
TP175	TwistGuard test Probes, 2MM dia probe tips	SAR	86.48	3521983	TP175	0095969521550
TP175E	TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters	SAR	97.76	3565568	TP175E	0095969528894
TP2-1	TP2, Test Probes	SAR	86.48	3971283	TP2-1	0095969589963
TP220-1	TP220, SureGrip Test Probes	SAR	86.48	3971276	TP220-1	0095969589956
TP38	Slim Reach Test Probe Set (insulated)	SAR	86.48	1541636	TP38	0095969078771
TP74	Lantern Tip Test Probe Set	SAR	86.48	1541649	TP74	0095969078788
TP80	Electronic Test Probe Set	SAR	169.20	873455	TP80	0095969012300
TP912	Replacement tips for TL910	SAR	150.40	1616644	TP912	0095969106894
TP920	Test Probe Adapter Kit	SAR	188.00	1616659	TP920	0095969106900
<b>Current Clamps</b>						
80i-110s	AC/DC Current Clamp (100 A)	SAR	3,350.16	114519	80i-110S	0095969040549
i1000s	AC Current Clamp (1000 A)	SAR	2,729.76	1568487	i1000S	0095969090476
i1010	AC/DC Current Clamp (1000 A)	SAR	1,913.84	617735	i1010	0095969048200
i1010 Kit	AC/DC Current Clamp (1000 A) with Soft Case	SAR	2,060.48	2096998	i1010-KIT	0095969241830
i200	AC Current Clamp (200 A)	SAR	755.76	664755	i200	0095969063937
i2000 flex	AC Flexible Current Clamp (2000 A)	SAR	1,808.56	2584912	i2000 FLEX	0095969345088
i200s	AC Current Clamp (200 A)	SAR	1,165.60	664760	i200S	0095969063944
i30	AC/DC Current Clamp (30A)	SAR	2,297.36	2584920	i30	0095969345095
i3000 flex-4PK	AC Flexible Current Clamp (3000 A), 4-pack	SAR	6,143.84	2696367	i3000 FLEX-4PK	0095969362474
i3000s	AC Current Clamp (3000 A)	SAR	3,030.56	657202	i3000S	0095969062022
i3000s flex-24	AC Flexible Current Clamp (3000 A), 610 mm	SAR	2,519.20	2584888	i3000S FLEX-24	0095969345057
i3000s flex-36	AC Flexible Current Clamp (3000 A), 915 mm	SAR	3,056.88	2584901	i3000S FLEX-36	0095969345071
i30s	AC/DC Current Clamp (30A)	SAR	3,056.88	2584935	i30S	0095969345101
i310s	AC/DC Current Clamp (300A)	SAR	2,037.92	2840309	i310S	0095969401241
i400	AC Current Clamp (400 A)	SAR	755.76	2277225	i400	0095969268608
i400s	AC Current Clamp (400A)	SAR	1,349.84	2277202	i400S	0095969268585
i40S-PR (1750)	40A Current Clamp (1750)	SAR	1,966.48	3949777	i40S-PR	0095969587051
i410	AC/DC Current Clamp (400 A)	SAR	1,188.16	617727	i410	0095969048194
i410 Kit	AC/DC Current Clamp (400 A) with Soft Case	SAR	1,470.16	2097005	i410-KIT	0095969241847
i6000s flex-24	AC Current Clamp (6000 A)	SAR	3,192.24	2840311	i6000S FLEX-24	0095969401258
i6000s flex-36	AC Current Clamp (6000 A)	SAR	3,684.80	2840327	i6000S FLEX-36	0095969401265
i800	AC Current Clamp (800 A)	SAR	1,500.24	2840283	i800	0095969401227
<b>Temperature Accessories</b>						
80AK-A	Thermocouple Adapter	SAR	135.36	2747812	80AK-A	0095969370974
80BK-A	Integrated DMM Temperature Probe (Type K)	SAR	195.52	2747801	80BK-A	0095969370967
80CJ-M	Male Mini Connectors (Type J)	SAR	139.12	833046	80CJ-M	0095969011280
80CK-M	Male Mini Connectors (Type K)	SAR	139.12	779942	80CK-M	0095969010177
80PJ-1	Bead Probe (Type J)	SAR	150.40	1288191	80PJ-1	0095969078443
80PJ-9	General Purpose Probe (Type J)	SAR	274.48	1288218	80PJ-9	0095969078467
80PJ-EXT	Extension Wire Kit (Type J)	SAR	266.96	1288234	80PJ-EXT	0095969078481
80PK-1	Bead Probe (Type K)	SAR	157.92	750422	80PK-1	0095969009744
80PK-10	Pipe Clamp Temperature Probe (Type K)	SAR	1,037.76	3439199	80PK-10	0095969493260
80PK-11	Velcro Temperature Probe	SAR	195.52	2724500	80PK-11	0095969364362
80PK-18 Kit	Pipe Clamp Temperature Probe Kit	SAR	1,643.12	3448859	80PK-18	0095969493826
80PK-22	SureGrip Immersion Probe	SAR	451.20	2098684	80PK-22	0095969242684
80PK-24	SureGrip Air Probe	SAR	560.24	2098691	80PK-24	0095969242691
80PK-25	SureGrip Piercing Probe	SAR	522.64	2098706	80PK-25	0095969242707
80PK-26	SureGrip General Purpose Probe	SAR	560.24	2098714	80PK-26	0095969242714
80PK-27	SureGrip Industrial Surface Probe	SAR	1,571.68	2098723	80PK-27	0095969242721
80PK-3A	Surface Probe (Type K)	SAR	740.72	874610	80PK-3A	0095969012379
80PK-8	Pipe Clamp Temperature Probe (Type K)	SAR	815.92	200360	80PK-8	0095969040778
80PK-9	General Purpose Probe (Type K)	SAR	274.48	1288229	80PK-9	0095969078474
80PK-EXT	Extension Wire Kit (Type K)	SAR	266.96	1288241	80PK-EXT	0095969078498
80PR-60	RTD Temperature Probe (Fluke 66/68)	SAR	421.12	2148313	80PR-60	0095969261173
80PT-25	SureGrip Piercing Probe	SAR	522.64	2104397	80PT-25	0095969244961
80PT-EXT	Extension Wire Kit (Type T)	SAR	266.96	1288252	80PT-EXT	0095969078504
80T-150UA	Universal Temperature Probe (for DMMs)	SAR	1,165.60	3190456	80T-150UA	0095969446617
80TK	Thermocouple Module (Type K)	SAR	650.48	736736	80TK	0095969009423
<b>Cases and Holsters</b>						
C10	Meter Holster	SAR	157.92	897744	C10	0095969013871
C100	Hard Meter and Accessory Case	SAR	266.96	827055	C100	0095969010641
C101	Hard Case	SAR	293.28	2437514	C101	0095969291743
C115	Soft Meter Case	SAR	157.92	2826063	C115	0095969400084
C116	Soft Meter Case	SAR	188.00	2826074	C116	0095969400091
C120	Hard Case (43B/120 Series)	SAR	533.92	646189	C120	0095969052146
C125	Soft Meter Case	SAR	195.52	646858	C125	0095969052894
C12A	Soft Meter Case	SAR	157.92	930529	C12A	0095969028257
C150	Zippered Soft Carrying Case	SAR	180.48	4111540	C150	0095969614832

C1600	Meter and Accessory Case	SAR	282.00	2091049	C1600	0095969240659
C1620	Carrying Case	SAR	1,128.00	4359042	C1620	0095969674836
C190	Hard Case (190 Series)	SAR	853.52	677401	C190	0095969075749
C195	Soft Case	SAR	812.16	677408	C195	0095969075756
C20	Hard Meter Case	SAR	293.28	708396	C20	0095969006521
C23	Soft Meter Case	SAR	157.92	1663209	C23	0095969130073
C25	Soft Meter Case	SAR	188.00	681114	C25	0095969006378
C280	Soft Meter Case	SAR	180.48	3182785	C280	0095969443807
C33	Soft Meter Case	SAR	157.92	1664120	C33	0095969130202
C345	Soft Case	SAR	409.84	3311173	C345	0095969463645
C35	Soft Meter Case	SAR	116.56	2826056	C35	0095969400077
C43	Soft Meter Case	SAR	360.96	1663230	C43	0095969130080
C50	Soft Meter Case	SAR	188.00	762823	C50	0095969009874
C510	Leather Meter Case	SAR	330.88	1547885	C510	0095969080613
C520A	Leather Tester Case	SAR	266.96	1629104	C520A	0095969110976
C550	Tool Bag	SAR	458.72	1547919	C550	0095969080644
C75	Soft Accessory Case	SAR	97.76	865535	C75	0095969012010
C781	Soft Meter Case	SAR	293.28	619988	C781	0095969048415
C789	Soft Meter Case	SAR	609.12	946694	C789	0095969025089
C800	Hard Meter and Accessory Case	SAR	266.96	896220	C800	0095969013383
C90	Soft Meter Case	SAR	188.00	466029	C90	0095969003537
CXT170	Rugged Pelican Hard Case	SAR	928.72	3352567	CXT170	0095969472944
CXT280	Rugged Pelican Hard Case	SAR	928.72	3352571	CXT280	0095969472951
CXT80	Rugged Pelican Hard Case	SAR	928.72	3352559	CXT80	0095969472937
CXT1000	Extreme Hard case	SAR	823.44	4628917	CXT1000	0095969785266
H3	Holster (330 Series)	SAR	169.20	1608458	H3	0095969102728
H5	Electrical Tester Holster (Fluke T5)	SAR	157.92	649365	H5	0095969057196
H6	Infrared Thermometer Holster (Fluke 63/65/68/561)	SAR	214.32	2152040	H6	0095969261883
H-T6	T6 Belt Holster	SAR	150.40	4910585	H-T6	0095969854313
H15	Belt Holster for T100 series	SAR	169.20	4111533	H15	0095969614825
H80M	Holster + Magnetic Hanger	SAR	214.32	2138458	H80M	0095969257251
<b>Automotive Accessories</b>						
BP880	BNC to Female Double Stacking Banana Plug	SAR	97.76	2150594	BP880	0095969261463
BP881	BNC to Male Double Stacking Banana Plug	SAR	116.56	2151015	BP881	0095969261609
PV350	Pressure Vacuum Module	SAR	2,162.00	919811	PV350	0095969017060
RPM80	Inductive Pick-up	SAR	398.56	880849	RPM80	0095969012058
SCC128	Automotive Accessory Kit (120 Series)	SAR	3,703.60	2100199	SCC 128	0095969243131
SCC198	Automotive Accessory Kit (190 Series)	SAR	4,316.48	2100208	SCC 198	0095969243148
STL90	Automotive Shielded Test Lead Set (120/190 Series)	SAR	1,022.72	201233	STL90	0095969043076
TAS90	Automotive Accessory Set (120/190 Series)	SAR	338.40	614187	TAS90	0095969047647
TL28A	Automotive Test Lead Set	SAR	225.60	1273185	TL28A	0095969083539
TL8	Automotive Pin and Socket Adapter Set	SAR	496.32	2150636	TL8	0095969261470
TP40	Automotive Back Probe Pins (5 pcs) (4 mm)	SAR	188.00	1567573	TP40	0095969087513
TP81	Insulation Piercing Clip Set (4 mm)	SAR	266.96	2149098	TP81	0095969261272
TP82	Insulation Piercing Clip Set (2 mm)	SAR	266.96	2149080	TP82	0095969261265
TP88	Rigid Back Probe Pin Set	SAR	78.96	2149102	TP88	0095969261289
<b>Other Accessories</b>						
80K-40	High Voltage Probe	SAR	1,037.76	382846	80K-40	0095969001120
80K-6	High Voltage Probe	SAR	590.32	532424	80K-6	0095969005333
EBC290	External Battery Charger	SAR	507.60	3894906	EBC290	0095969580410
FOM	Fiber Optic Meter	SAR	2,601.92	200428	FOM	0095969046275
FOS-850	Fiber Optic Light Source	SAR	1,680.72	200433	FOS-850	0095969046282
FOS-850/1300	Fiber Optic Light Source	SAR	4,038.24	200441	FOS-850/1300	0095969046305
L200	Probe Light	SAR	139.12	2096346	L200	0095969241663
L205	Mini Hat Light	SAR	157.92	2098588	L205	0095969242608
L206	Deluxe Hat Light	SAR	214.32	2098595	L206	0095969242615
L210	Probe light and probe extender	SAR	195.52	2096379	L210	0095969241694
L215	SureGrip kit with probe light and probe extender	SAR	443.68	2096368	L215	0095969241687
LVD1	Volt Light	SAR	142.88	4571403	LVD1A	0095969773188
LVD2	Volt Light	SAR	191.76	2740300	LVD2	0095969369978
MCS0	MeterCleaner Wipes, 50-pack	SAR	466.24	2092300	MCS0	0095969241014
MC6	MeterCleaner Wipes, 6-pack	SAR	86.48	2092212	MC6	0095969241007
PV350	Pressure Vacuum Module	SAR	2,162.00	919811	PV350	0095969017060
SV225	Stray Voltage Adapter	SAR	282.00	3100477	SV225	0095969437660
TPAK	ToolPak, Meter Hanging Kit	SAR	203.04	1281997	TPAK	0095969082631
<b>Fuses</b>						
943121	Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm	SAR	24.06	943121	FUSE	0095969089906
803293	Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm	SAR	44.37	803293	FUSE	0095969095761
830828	Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm	SAR	34.59	830828	FUSE	0095969096164
2279339	Fuse, A:315mA (F), V:1000V, IR:10kA, 6.35x32 mm	SAR	57.53	2279339	7017240.0	0095969348119
740670	Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm	SAR	16.54	740670	FUSE	0095969096157
<b>Software</b>						
FVF-Basic	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	SAR	740.72	2396957	FVF-BASIC	0095969283236
FVF-SC2	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	SAR	1,150.56	1576734	FVF-SC2	0095969090483
FVF-SC4	FlukeView Forms Software + Cable (8845A/8846A)	SAR	1,500.24	2687335	FVF-SC4	0095969361811
FVF-SC5	FlukeView Forms Basic (8845A/8846A)	SAR	639.20	2791314	FVF-SC5	0095969390798
FVF-UG	FlukeView Forms Upgrade	SAR	590.32	1576741	FVF-UG	0095969090469
IR189USB	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	SAR	274.48	2428108	IR189USB	0095969288705
SCC120E	FlukeView Software + USB Cable + Case (120 Series) - English	SAR	1,808.56	646684	SCC120E	0095969052658
SCC120F	FlukeView Software + USB Cable + Case (Fluke 123) - French	SAR	1,808.56	646692	SCC120F	0095969052665
SCC190	FlukeView Software + Cable + Case (190 Series) - English, French, German	SAR	2,601.92	671826	SCC190EFG	0095969075602
SW90W	FlukeView Software	SAR	1,304.72	3894923	SW90W	0095969580434