

# Fluke Test Tools Price List

**FLUKE®**

Valid from: 02-07-2019

| Model                              | Art. nr | Description   | EUR     |
|------------------------------------|---------|---|---------|
| <b>Fluke Connect</b>               |         |   |         |
| <b>Fluke Connect - 3000 Series</b> |         |   |         |
| FLK-3000 FC                        | 4401595 | FC Wireless Digital Multimeter                              | 307.00  |
| FLK-3000 FC GM                     | 4467750 | FC Wireless General Maintenance System                      | 879.00  |
| FLK-3000 FC HVAC                   | 4465607 | FC Wireless HVAC System                                     | 637.00  |
| FLK-3000 FC IND                    | 4465599 | FC Wireless Industrial System                               | 1098.00 |
| FLK-3000FC/TPAK                    | 4699340 | Fluke 3000FC with TPAK meter hanging kit                    | 340.00  |
| Fluke 3000FC/EDA2                  | 4699333 | Electronics DMM and deluxe accessory kit                    | 395.00  |
| Fluke 3000FC/1AC-II                | 4699302 | Electrician's DMM voltage tester and accessory kit          | 438.00  |
| FLK-A3000 FC                       | 4401588 | FC Wireless AC Current Clamp Module                         | 197.00  |
| FLK-A3000 FC KIT                   | 4465618 | FC Wireless Essential Kit with A3000                        | 438.00  |
| FLK-A3001 FC                       | 4459439 | FC Wireless iFlex AC Current Module                         | 230.00  |
| FLK-A3002 FC                       | 4459442 | FC Wireless AC/DC Current Module                            | 131.00  |
| FLK-A3003 FC                       | 4629295 | FC Wireless 2000A DC Clamp meter                            | 548.00  |
| FLK-A3004 FC                       | 4629301 | FC Wireless 4-20mA DC Clamp meter                           | 658.00  |
| FLK-T3000 FC                       | 4401563 | FC Wireless K-Type Temperature Module                       | 197.00  |
| FLK-T3000 FC KIT                   | 4465652 | FC Wireless Essential Kit with T3000                        | 438.00  |
| FLK-V3000 FC                       | 4401556 | FC Wireless AC Voltage Module                               | 208.00  |
| FLK-V3000 FC KIT                   | 4465641 | FC Wireless Essential Kit with V3000                        | 438.00  |
| FLK-V3001 FC                       | 4459421 | FC Wireless DC Voltage Module                               | 208.00  |
| FLK-V3001 FC KIT                   | 4467777 | FC Wireless essential Kit with V3001                        | 438.00  |
| FLK-V3003 FC KIT                   | 4467789 | FC Wireless Kit w. DMM, AC+DC Voltage Modules               | 713.00  |
| <b>Fluke Connect - Accessories</b> |         |   |         |
| FLK-FC_SD Card                     | 4463628 | Fluke Connect Wireless SD Card                              | 99.00   |
| FLK-PC3000 FC                      | 4401602 | FC Wireless PC Adapter                                      | 109.00  |
| FLUKE-IR3000FC                     | 4460436 | Connector, Infrared, FC                                     | 143.00  |
| <b>Digital Multimeters</b>         |         |   |         |
| <b>110 Series Multimeters</b>      |         |   |         |
| Fluke 113                          | 3088053 | True RMS Multimeter   | 135.00  |
| Fluke 114                          | 2583552 | True RMS Multimeter   | 178.00  |
| Fluke 115                          | 2583583 | True RMS Multimeter   | 206.00  |
| Fluke 116                          | 2583601 | True RMS Multimeter   | 247.00  |
| 116/62MAX+ Kit                     | 4296018 | Fluke HVAC Multimeter and IR Thermometer Combo Kit          | 317.00  |
| Fluke 116/323 Kit                  | 4296029 | Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit    | 350.00  |
| Fluke 117                          | 2583647 | True RMS Multimeter   | 258.00  |
| Fluke 117/323 Kit                  | 4296034 | Fluke Electrician's Multimeter Combo Kit                    | 334.00  |
| C50                                | 762823  | Soft Meter Case   | 43.00   |
| <b>170 Series Multimeters</b>      |         |   |         |
| Fluke 175                          | 1592901 | True RMS Multimeter   | 247.00  |
| Fluke 177                          | 1592874 | True RMS Multimeter   | 300.00  |
| Fluke 179                          | 1592842 | True RMS Multimeter   | 354.00  |
| C90                                | 466029  | Soft Meter Case   | 43.00   |
| Fluke 179/EDA2/EUR                 | 3947719 | Electronics Combo Kit                                       | 420.00  |
| <b>200 Series Multimeters</b>      |         |   |         |
| Fluke 233                          | 3469334 | Remote Display Multimeter                                   | 350.00  |
| Fluke 279FC/iFlex                  | 4684050 | Wireless TRMS Thermal Multimeter w/iFlex                    | 999.00  |
| Fluke 279FC I/B                    | 4989200 | Wireless TRMS Thermal Multimeter with iFlex & extra battery | 1099.00 |
| Fluke 287/EUR                      | 3947781 | True RMS Electronic Logging Multimeter with TrendCapture    | 637.00  |
| Fluke 287/FVF/EUR                  | 3947796 | FlukeView Forms Combo Kit                                   | 747.00  |
| Fluke 289/EUR                      | 3947801 | True RMS Industrial Logging Multimeter with TrendCapture    | 692.00  |
| Fluke 289/FVF/EUR                  | 3947812 | Industrial Logging Multimeter and Software Combo Kit        | 802.00  |
| C280                               | 3182785 | Soft Meter Case   | 71.00   |
| Fluke 287/FVF/IR3000               | 4699316 | Fluke 287 FlukeView® Forms Combo Kit                        | 824.00  |
| Fluke 289/FVF/IR3000               | 4699325 | Fluke 289 FlukeView® Forms Combo Kit                        | 879.00  |

| Model                        | Art. nr | Description  | EUR     |
|------------------------------|---------|--|---------|
| <b>20 Series Multimeters</b> |         |  |         |
| Fluke 27II/EUR               | 3947770 | Industrial Multimeter (IP67)                             | 527.00  |
| Fluke 28II/EUR               | 3947820 | True RMS Industrial Multimeter (IP67)                    | 527.00  |
| Fluke 28 II Ex               | 4017165 | Intrinsically safe true-rms digital multimeter           | 1373.00 |
| C25                          | 681114  | Soft Meter Case  | 61.00   |
| <b>70 Series Multimeters</b> |         |  |         |
| Fluke 77-4/EUR               | 3947835 | Multimeter   | 438.00  |
| C90                          | 466029  | Soft Meter Case  | 43.00   |
| <b>80 Series Multimeters</b> |         |  |         |
| Fluke 83-V/EUR               | 3947847 | Multimeter   | 493.00  |
| Fluke 87-V/EUR               | 3947858 | True RMS Multimeter                                      | 499.00  |
| Fluke 87-V/E2K/EUR           | 3947864 | Industrial Electricians Combo Kit                        | 599.00  |
| C25                          | 681114  | Soft Meter Case  | 61.00   |
| <b>Bench Multimeters</b>     |         |  |         |
| Fluke 8808A 220V             | 2802372 | 5.5 Digit Multimeter                                     | 715.00  |
| Fluke 8808A 240V             | 2802385 | 5.5 Digit Multimeter                                     | 715.00  |
| Fluke 8808A/SU 220V          | 2802459 | 5.5 Digit Multimeter (software & cable)                  | 915.00  |
| Fluke 8808A/SU 240V          | 2802467 | 5.5 Digit Multimeter (software & cable)                  | 915.00  |
| Fluke 8808A/TL 220V          | 3111085 | 5.5 Digit Multimeter, 2X4W Test Lead Kit                 | 795.00  |
| Fluke 8808A/TL 240V          | 3111097 | 5.5 Digit Multimeter, 2X4W Test Lead Kit                 | 795.00  |
| Fluke 8845A 220V             | 2577352 | 6.5 Digit Precision Multimeter                           | 1070.00 |
| Fluke 8845A 240V             | 2577365 | 6.5 Digit Precision Multimeter                           | 1070.00 |
| Fluke 8845A/SU 220V          | 2675315 | 6.5 Digit Precision Multimeter (incl. software + cable)  | 1260.00 |
| Fluke 8845A/SU 240V          | 2675332 | 6.5 Digit Precision Multimeter (incl. software + cable)  | 1260.00 |
| Fluke 8846A 220V             | 2577383 | 6.5 Digit Precision Multimeter                           | 1405.00 |
| Fluke 8846A 240V             | 2577390 | 6.5 Digit Precision Multimeter                           | 1405.00 |
| Fluke 8846A/SU 220V          | 2675367 | 6.5 Digit Precision Multimeter (incl. software + cable)  | 1600.00 |
| Fluke 8846A/SU 240V          | 2675380 | 6.5 Digit Precision Multimeter (incl. software + cable)  | 1600.00 |
| 884X-CASE                    | 2675552 | Hard Case (8845A/8846A)                                  | 440.00  |
| 884X-RTD                     | 2675468 | 100 OHM RTD Temperature Probe                            | 575.00  |
| 884X-SHORT                   | 2653346 | 4-wire short   | 31.00   |
| 884X-USB                     | 2675479 | USB to RS232 Cable Adapter                               | 165.00  |
| 884X-1G                      | 2675534 | USB Memory 1 GB  | 40.00   |
| 8845A-EFPT                   | 2742690 | Extended Fine Point Tip Adapter Set                      | 20.00   |
| 8845A-TPIT                   | 2742683 | Test Probe IC Tip Set                                    | 15.00   |
| FVF-UG                       | 1576741 | FlukeView Forms Upgrade                                  | 142.00  |
| FVF-SC4                      | 2687335 | FlukeView Forms Software + Cable (8845A/8846A)           | 303.00  |
| FVF-SC5                      | 2791314 | FlukeView Forms Basic (8845A/8846A)                      | 174.00  |
| RS43                         | 946470  | Serial Interface Cable                                   | 89.00   |
| TL2X4W-PTII                  | 2826215 | 2x4 Wire Ohms Test Lead 2 mm Probe Tip                   | 80.00   |
| TL2x4W-TWZ                   | 2723629 | 2X4-Wire Ohms Tweezers Test Leads                        | 100.00  |
| Y8021                        | 708289  | IEEE-488 Shielded Interface Cable, 1 m                   | 458.00  |
| Y8022                        | 708297  | IEEE-488 Shielded Interface Cable, 2 m                   | 535.00  |
| Y8846S                       | 2675518 | Rack mount kit single (8845A/8846A)                      | 125.00  |
| Y8846D                       | 2771721 | Rack mount kit dual (8845A/8846A)                        | 170.00  |
| <b>Automotive Meters</b>     |         |  |         |
| Fluke 88V/A                  | 2117440 | Automotive Meter Combo Kit                               | 713.00  |
| <b>Clamp Meters</b>          |         |  |         |
| Fluke 323                    | 4152628 | True RMS Clamp Meter                                     | 138.00  |
| Fluke 324                    | 4152637 | True RMS Clamp Meter                                     | 180.00  |
| Fluke 325                    | 4152643 | True RMS Clamp Meter                                     | 244.00  |
| Fluke 353                    | 2840252 | AC/DC True RMS Clamp Meter                               | 652.00  |
| Fluke 355                    | 2840265 | AC/DC True RMS Clamp Meter                               | 815.00  |
| Fluke 365                    | 3790607 | Detachable TRMS Clamp Meter                              | 271.00  |
| Fluke 368 FC                 | 4709907 | Wireless leakage current clamp, 40mm jaw                 | 724.00  |
| Fluke 369 FC                 | 4709934 | Wireless leakage current clamp, 61mm jaw                 | 724.00  |
| Fluke 373                    | 3790564 | 600A TRMS Clamp Meter                                    | 271.00  |
| Fluke 374FC                  | 4696001 | 600A AC/DC TRMS Wireless Clamp Meter                     | 380.00  |
| Fluke 375FC                  | 4695932 | 600A AC/DC TRMS Wireless Clamp Meter                     | 455.00  |
| Fluke 376FC                  | 4695861 | 1000A AC/DC TRMS Wireless Clamp Meter with iFlex         | 517.00  |
| Fluke 381                    | 3610452 | Remote Display TRMS Clamp Meter                          | 608.00  |
| Fluke 902 FC                 | 4695814 | TRMS Wireless HVAC ClampMeter                            | 305.00  |
| 62MAX+/323/1AC Kit           | 4296076 | IR Thermometer, Clamp Meter and Voltage Detector Kit     | 265.00  |
| Fluke 116/323 Kit            | 4296029 | Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit | 350.00  |
| Fluke i2500-18               | 3676405 | iFlex Probe  | 141.00  |
| Fluke i2500-10               | 3676410 | iFlex Probe  | 141.00  |
| H3                           | 1608458 | Holster (330 Series)                                     | 47.00   |

| Model                              | Art. nr | Description  | EUR     |
|------------------------------------|---------|--|---------|
| <b>Electrical Testers</b>          |         |  |         |
| Fluke 1000FLT                      | 4472387 | Fluorescent Light Tester                                   | 250.00  |
| T6-1000/EU                         | 4910257 | Electrical Tester with FieldSense™, round                  | 279.00  |
| T6-600/EU                          | 4910322 | Electrical Tester with FieldSense™, round                  | 219.00  |
| H-T6                               | 4910585 | T6 Belt Holster  | 36.00   |
| Fluke T5-600                       | 659612  | Electrical Tester  | 164.00  |
| T5-600/62MAX+/1AC kit              | 4297126 | Electrical Tester, IR Thermometer and Voltage Detector Kit | 267.00  |
| Fluke T5-1000                      | 659570  | Electrical Tester  | 184.00  |
| Fluke T5-H5-1AC II Kit             | 2098657 | Electrical Tester Kit with Holster and 1AC                 | 205.00  |
| Fluke T90                          | 4016945 | Voltage/continuity tester                                  | 61.00   |
| Fluke T110                         | 4016950 | Voltage/continuity tester with switchable load             | 87.00   |
| Fluke T130                         | 4016961 | Voltage/continuity tester with LCD, switchable load        | 128.00  |
| Fluke T150                         | 4016977 | Voltage/continuity tester with LCD, Ohms, switchable load  | 148.00  |
| Fluke 2042                         | 2435038 | Cable Locator (Transmitter + Receiver)                     | 794.00  |
| Fluke 2042T                        | 2435045 | Cable Locator Transmitter                                  | 413.00  |
| Fluke 9040EUR                      | 4014969 | Phase Rotation Indicator                                   | 212.00  |
| Fluke 9062                         | 2435077 | Motor and Phase Rotation Indicator                         | 195.00  |
| LVD1                               | 4571403 | Volt Light   | 37.00   |
| LVD2                               | 2740300 | Volt Light   | 41.00   |
| H5                                 | 649365  | Electrical Tester Holster (Fluke T5)                       | 36.00   |
| FTL660                             | 2280204 | Fused Test Lead Set  | 65.00   |
| Fluke 1AC II                       | 2432932 | Volt Alert   | 32.00   |
| Fluke 1AC II 5PK                   | 2433042 | Volt Alert 5-pack  | 116.00  |
| FLK2AC/90-1000V                    | 3807928 | ACV Detector 90-1000V, Flat-tip                            | 30.00   |
| FLK2AC/90-1000V5PK                 | 3807937 | Volt Alert 90-1000V, 5-pack, Flat-tip                      | 106.00  |
| PRV240                             | 4566209 | Proving unit   | 164.00  |
| Fluke 117/PRV240                   | 4636971 | Proving unit, Fluke 117 DMM Kit                            | 328.00  |
| PRV240FS                           | 4910310 | Proving unit, T6/NCV                                       | 164.00  |
| <b>Laser Levels</b>                |         |  |         |
| <b>3 point lasers</b>              |         |  |         |
| PLS 3R Z                           | 5009340 | 3-Point Red Laser Bare Tool                                | 165.00  |
| PLS 3R KIT                         | 5009357 | 3-Point Red Laser Kit                                      | 206.00  |
| PLS 3G Z                           | 5009369 | 3-Point Green Laser Bare Tool                              | 204.00  |
| PLS 3G KIT                         | 5009378 | 3-Point Green Laser Kit                                    | 245.00  |
| <b>5 point lasers</b>              |         |  |         |
| PLS 5R Z                           | 5009384 | 5-Point Red Laser Bare Tool                                | 254.00  |
| PLS 5R KIT                         | 5009391 | 5-Point Red Laser Kit                                      | 283.00  |
| PLS 5G Z                           | 5009406 | 5-Point Green Laser Bare Tool                              | 290.00  |
| PLS 5G KIT                         | 5009414 | 5-Point Green Laser Kit                                    | 327.00  |
| <b>Cross line and point lasers</b> |         |  |         |
| PLS 6R Z                           | 5009423 | Cross Line and Point Red Laser Bare Tool                   | 299.00  |
| PLS 6R KIT                         | 5009438 | Cross Line and Point Red Laser Kit                         | 382.00  |
| PLS 6R SYS                         | 5009445 | Cross Line and Point Red Laser System                      | 490.00  |
| PLS 6G Z                           | 5009461 | Cross Line and Point Green Bare Tool                       | 390.00  |
| PLS 6G KIT                         | 5009489 | Cross Line and Point Green Laser Kit                       | 473.00  |
| PLS 6G SYS                         | 5009492 | Cross Line and Point Green Laser System                    | 581.00  |
| <b>Cross line lasers</b>           |         |  |         |
| PLS 180R Z                         | 5017279 | Cross Line Red Laser Bare Tool                             | 223.00  |
| PLS 180R KIT                       | 5009450 | Cross Line Red Laser Kit                                   | 259.00  |
| PLS 180R SYS                       | 5019428 | Cross Line Red Laser System                                | 329.00  |
| PLS 180G Z                         | 5017287 | Cross Line Green Laser Bare Tool                           | 287.00  |
| PLS 180G KIT                       | 5009509 | Cross Line Green Laser Kit                                 | 319.00  |
| PLS 180G SYS                       | 5019437 | Cross Line Green Laser System                              | 379.00  |
| <b>Rotary lasers</b>               |         |  |         |
| <b>Horizontal rotary lasers</b>    |         |  |         |
| PLS H2 Z                           | 5022470 | Horizontal red rotary laser bare tool                      | 575.00  |
| PLS H2 SYS                         | 5022481 | Horizontal red rotary laser system                         | 815.00  |
| PLS H2 KIT                         | 5022496 | Horizontal red rotary laser kit                            | 1049.00 |
| <b>Manual slope rotary lasers</b>  |         |  |         |
| PLS HV2R Z                         | 5022501 | Manual slope red rotary laser bare tool                    | 749.00  |
| PLS HV2R SYS                       | 5022512 | Manual slope red rotary laser system                       | 1049.00 |
| PLS HV2R KIT                       | 5022558 | Manual slope red rotary laser kit                          | 1289.00 |
| PLS JV2G Z                         | 5022535 | Manual slope green rotary laser bare tool                  | 869.00  |
| PLS HV2G SYS                       | 5022547 | Manual slope green rotary laser system                     | 1169.00 |
| PLS HV2G KIT                       | 5022520 | Manual slope green rotary laser kit                        | 1399.00 |

| Model                               | Art. nr | Description  | EUR     |
|-------------------------------------|---------|--|---------|
| <b>Accessories lasers</b>           |         |  |         |
| PLS-20513                           | 4791765 | Tripod Telescope 9 FT 6 IN   | 186.00  |
| PLS-21502                           | 4919812 | Tripod Extender PLS3/180   | 10.00   |
| PLS FS                              | 5031929 | Floor Stand for PLS 3, 5, 6  | 15.00   |
| PLS MLB                             | 5031934 | Magnetic L-Bracket, PLS 3, 5, 6, 180   | 41.00   |
| PLS BP5                             | 5031952 | BP5 Alkaline Battery Pack  | 39.00   |
| PLS UB9                             | 4966636 | UB9 Universal Ceiling/Wall Bracket   | 87.00   |
| PLS SLD RED                         | 4978515 | SLD Red Detector W/ Bracket  | 155.00  |
| PLS SLD GREEN                       | 4978526 | SLD Green Detector W/ Bracket  | 169.00  |
| PLS RRT4                            | 5022629 | Red Magnetic Reflective Target   | 13.00   |
| PLS GRT4                            | 5022634 | Green Magnetic Reflective Target   | 13.00   |
| PLS C18                             | 4985124 | Laser Level Tool Box   | 77.00   |
| PLS BC20                            | 5022618 | Charging Cord for PLS RBP10  | 34.00   |
| PLS TPOD500                         | 5022665 | Elevating Tripod   | 264.00  |
| PLS RC2                             | 5022564 | Rotary laser remote control  | 58.00   |
| PLS XLD                             | 5037696 | Rotary laser detector with clamp   | 194.00  |
| PLS XLD CLAMP                       | 5037709 | Rotary detector clamp  | 34.00   |
| PLS C19                             | 5022586 | Rotary laser carrying case   | 68.00   |
| PLS BP10                            | 5022599 | Rotary alkaline battery for H2, HV2  | 48.00   |
| PLS RBP10                           | 5022607 | Rechargeable battery for H2, HV2   | 68.00   |
| PLS WCB10                           | 5022641 | Rotary wall and ceiling mount  | 87.00   |
| PLS GR16                            | 5022652 | Grade rod with US and Metric   | 48.00   |
| <b>Distance Meters</b>              |         |  |         |
| Fluke 414D                          | 4106830 | Laser Distance Meter   | 140.00  |
| Fluke 419D                          | 4106853 | Laser Distance Meter   | 269.00  |
| Fluke 424D                          | 4106866 | Laser Distance Meter   | 389.00  |
| 414D/62MAX+ Kit                     | 4296052 | Fluke Laser distance meter and IR thermometer kit  | 237.00  |
| <b>Battery Analyzers</b>            |         |  |         |
| Fluke BT510                         | 4489970 | Battery Analyzer   | 2809.00 |
| Fluke BT520                         | 4489981 | Battery Analyzer   | 3492.00 |
| Fluke BT521                         | 4489996 | Advanced Battery Analyzer  | 3914.00 |
| <b>Battery Analyzer Accessories</b> |         |  |         |
| BTL10                               | 4542264 | Standard Battery Analyzer Probes   | 341.00  |
| BTL20                               | 4542273 | Intelligent Test Probe Set, w/Extenders (no temp sensor)                                   | 526.00  |
| BTL21                               | 4542286 | Intelligent Test Probe Set, w/Extenders & Temp Sensor                                      | 654.00  |
| BTL-A                               | 4542258 | Voltage/Current Probe Adapter  | 42.00   |
| BC500                               | 4542299 | AC Power Charger   | 127.00  |
| BP500                               | 4542300 | Lithium-ion battery, 7.4V 3000 mAh   | 106.00  |
| BT500                               | 4561297 | Probe tip, 10x replacement Probe tips, 2x long probe tip covers, 2x short probe tip covers | 127.00  |
| i410                                | 617727  | AC/DC Current Clamp (400 A)  | 275.00  |
| <b>Insulation Testers</b>           |         |  |         |
| Fluke 1503                          | 2427883 | Insulation Tester  | 415.00  |
| Fluke 1507                          | 2427890 | Insulation Tester  | 515.00  |
| Fluke 1550C                         | 3665021 | Insulation Resistance Tester (5kV)   | 4119.00 |
| Fluke 1550C/Kit                     | 3665127 | Insulation Resistance Tester Kit (5kV)   | 4540.00 |
| Fluke 1550C FC w/IR3000FC           | 4977402 | Insulation Resistance Tester (5kV) with IR3000FC   | 4119.00 |
| Fluke 1550C FC Kit w/IR3000FC       | 4977457 | Insulation Resistance Tester Kit (5kV) with IR3000FC                                       | 4540.00 |
| Fluke 1555                          | 3665056 | Insulation Resistance Tester (10kV)  | 4540.00 |
| Fluke 1555/Kit                      | 3665111 | Insulation Resistance Tester Kit (10kV)  | 4959.00 |
| Fluke 1555 FC w/IR3000FC            | 4977519 | Insulation Resistance Tester (10kV) with IR3000FC  | 4540.00 |
| Fluke 1555 FC Kit w/IR3000FC        | 4977469 | Insulation Resistance Tester Kit (10kV) with IR3000FC                                      | 4959.00 |
| Fluke 1577                          | 2157280 | Insulation Multimeter  | 652.00  |
| Fluke 1587T                         | 2517605 | Insulation Multimeter (Telecom)  | 734.00  |
| Fluke 1587 FC                       | 4691215 | 2-IN-1 Insulation Multimeter   | 787.00  |
| Fluke 1587/MDT FC                   | 4692716 | 2-IN-1 Advanced Motor & Drive Troubleshooting Kit with 9040, I400                          | 1050.00 |
| 1587KIT/62MAX+ FC                   | 4692778 | 2-IN-1 Advanced Electrical Troubleshooting Insulation Multi Kit with 62MAX+ I400           | 945.00  |
| Fluke 1587/I400 FC                  | 4692725 | 2-IN-1 Insulation Multimeter with Clamp i400   | 839.00  |
| FVF-Basic                           | 2396957 | FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)                           | 161.00  |
| FVF-SC2                             | 1576734 | FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)                     | 264.00  |
| IR189USB                            | 2428108 | IR Cable - USB (280/180 Series, 1653, 789, 1550B)  | 51.00   |
| <b>Installation Testers</b>         |         |  |         |
| Fluke 1662 SCH                      | 4546944 | Installation Tester w/mem Schuko   | 999.00  |
| Fluke 1663 SCH                      | 4546980 | Installation Tester w/RCD type B Schuko  | 1299.00 |
| Fluke 1664FC SCH                    | 4547054 | FC Installation Tester w/insulation pre-test Schuko  | 1649.00 |
| Fluke 166X-MTC-SCH                  | 4601081 | Fluke 166X-Main test cord, Schuko (EU)   | 61.00   |
| Fluke DMS COMP                      | 4718790 | DMS Complete, Installation, PAT Software   | 585.00  |
| Fluke DMS COMPL/PROF                | 4718803 | DMS Complete/Professional, Installation, PAT Software                                      | 778.00  |
| FVF-SC2                             | 1576734 | FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)                     | 264.00  |
| IR189USB                            | 2428108 | IR Cable - USB (280/180 Series, 1653, 789, 1550B)  | 51.00   |



| Model        | Art. nr | Description                          | EUR    |
|--------------|---------|--------------------------------------|--------|
| ES165X       | 2104706 | Earth Spike Test Kit                 | 163.00 |
| TP165X       | 2107742 | Remote Control Probe (1650 Series)   | 87.00  |
| TL165X       | 2107756 | Standard Test Lead Set (1650 Series) | 120.00 |
| ZERO ADAPTER | 3261925 | Zero adapter (165xB)                 | 42.00  |

### Portable Appliance Testers

|                      |         |   |        |
|----------------------|---------|---|--------|
| Fluke DMS COMP       | 4718790 | DMS Complete, Installation, PAT Software              | 585.00 |
| Fluke DMS COMPL/PROF | 4718803 | DMS Complete/Professional, Installation, PAT Software | 778.00 |

### Earth Ground Testers

|                   |         |   |         |
|-------------------|---------|---|---------|
| Fluke 1630-2 FC   | 4829532 | Earth Ground Loop and Leakage Clamp           | 1493.00 |
| Fluke 1630-2      | 4829515 | Earth Ground Loop and Leakage Clamp (non FC)  | 1493.00 |
| Fluke 1623-2      | 4325155 | Basic Geo Earth Ground Tester                 | 1468.00 |
| Fluke 1625-2      | 4325162 | Advanced Geo Earth Ground Tester              | 2448.00 |
| Fluke 1623-2 Kit  | 4325170 | Basic Geo Earth Ground Tester, Kit            | 2502.00 |
| Fluke 1625-2 Kit  | 4325181 | Advanced Geo Earth Ground Tester, Kit         | 3591.00 |
| Earth Stake       | 4325492 | Geo Earth Ground Tester, Earth stake          | 67.00   |
| Cable Reel 25M BL | 4343731 | 25M Blue, Ground/Earth Cable Reel, 25M Wire   | 67.00   |
| Cable Reel 25M GR | 4343746 | 25M Green, Ground/Earth Cable Reel, 25M Wire  | 67.00   |
| Cable Reel 50M RD | 4343754 | 50M Red, Ground/Earth Cable Reel, 50M Wire    | 75.00   |
| C1620             | 4359042 | Carrying Case                                 | 210.00  |
| ES-162P3-2        | 4359377 | Earth Ground Stake Set for 3 Pole Measurement | 260.00  |
| ES-162P4-2        | 4359389 | Earth Ground Stake Set for 4 Pole Measurement | 380.00  |

### Indoor Air Quality Tools

|               |         |                            |         |
|---------------|---------|----------------------------|---------|
| Fluke 922     | 2679822 | Airflow Meter              | 652.00  |
| Fluke 922/Kit | 2679831 | Airflow Meter Kit          | 760.00  |
| Fluke 971     | 2418208 | Temperature Humidity Meter | 260.00  |
| Fluke 975     | 2519364 | AirMeter                   | 2039.00 |
| Fluke 975V    | 2666111 | AirMeter with Velocity     | 2345.00 |
| Fluke CO-220  | 664711  | Carbon Monoxide Meter      | 543.00  |
| Fluke RLD2    | 3387163 | Leak Detector Flashlight   | 54.00   |
| CO-205        | 664714  | Aspirator Kit              | 183.00  |
| 975VP         | 2631538 | Air Velocity Probe         | 458.00  |
| PT12          | 2740212 | Pitot Tube, 12             | 119.00  |
| Fluke 985     | 4131397 | Airborne Particle Counter  | 4283.00 |

### Digital Thermometers

|                       |         |  |         |
|-----------------------|---------|--|---------|
| Fluke 51 II           | 1281142 | Thermometer  | 337.00  |
| Fluke 52 II           | 1281139 | Thermometer  | 429.00  |
| Fluke 53 II B         | 3821062 | Single Input Thermometer, 60Hz                             | 481.00  |
| Fluke 53 II B         | 3821096 | Single Input Thermometer, 50Hz                             | 491.00  |
| Fluke 54 II B         | 3821070 | Dual Input Thermometer, 60Hz                               | 583.00  |
| Fluke 54 II B         | 3821081 | Dual Input Thermometer, 50Hz                               | 583.00  |
| Fluke 61              | 1643896 | Infrared Thermometer                                       | 200.00  |
| Fluke 62 MAX          | 4130474 | Infrared thermometer                                       | 97.00   |
| Fluke 62 MAX+         | 4130488 | Infrared Thermometer                                       | 105.00  |
| T5-600/62MAX+/1AC kit | 4297126 | Electrical Tester, IR Thermometer and Voltage Detector Kit | 267.00  |
| 414D/62MAX+ Kit       | 4296052 | Fluke Laser distance meter and IR thermometer kit          | 237.00  |
| 62MAX+/323/1AC Kit    | 4296076 | IR Thermometer, Clamp Meter and Voltage Detector Kit       | 265.00  |
| 116/62MAX+ Kit        | 4296018 | Fluke HVAC Multimeter and IR Thermometer Combo Kit         | 317.00  |
| Fluke 63              | 2148281 | Infrared Thermometer                                       | 276.00  |
| Fluke 64 MAX          | 4856105 | Multifunction IR Thermometer 20:1 D:S                      | 132.00  |
| Fluke 561             | 2558118 | Multipurpose Thermometer                                   | 200.00  |
| Fluke 566             | 2837799 | Multipurpose Thermometer                                   | 425.00  |
| Fluke 568             | 2837806 | Multipurpose Thermometer                                   | 532.00  |
| Fluke 568Ex           | 4321662 | Intrinsically safe Infrared Thermometer                    | 1331.00 |
| Fluke 572-2           | 4328074 | Infrared Thermometer                                       | 634.00  |
| Fluke FP              | 2644169 | FoodPro Thermometer  | 128.00  |
| Fluke FP Plus         | 2477950 | FoodPro Plus Thermometer                                   | 214.00  |
| C50                   | 762823  | Soft Meter Case  | 43.00   |
| H6                    | 2152040 | Infrared Thermometer Holster (Fluke 63/65/68/561)          | 34.00   |
| 8OPR-60               | 2148313 | RTD Temperature Probe (Fluke 66/68)                        | 78.00   |

### Visual Thermometers

|                     |         |                            |        |
|---------------------|---------|----------------------------|--------|
| Fluke VTO4          | 4366444 | Visual IR Thermometer      | 569.00 |
| Fluke VTO4A         | 4485211 | Visual IR thermometer      | 515.00 |
| Fluke charger VTO4  | 4375752 | Charger & adapter set VTO4 | 45.00  |
| Fluke Battery, VTO4 | 4375741 | Li-ion battery VTO4        | 45.00  |

### Industrial Imaging

|                |         |   |         |
|----------------|---------|---|---------|
| Fluke DS701    | 4962652 | Diagnostic Videoscope                         | 1699.00 |
| Fluke DS703 FC | 4962665 | High Resolution Diagnostic Videoscope with FC | 1999.00 |

| Model                  | Art. nr | Description                               | EUR      |
|------------------------|---------|---|----------|
| Fluke 3.8mm Scope      | 4962690 | 3.8 mm Scope, 1 m Probe, Forward View     | 699.00   |
| Fluke 8.5mm Scope      | 4962708 | 8.5 mm Scope, 3 m Probe, Dual View        | 599.00   |
| Fluke 5.5 mm Scope     | 4962713 | 5.5 mm Scope, 1 m Probe, Dual View        | 499.00   |
| Fluke 8.5 mm Scope     | 4962749 | 8.5 mm Scope, 1.2 m Probe, Dual View      | 199.00   |
| Fluke 8.5 mm UV Scope  | 4962751 | 8.5 mm UV Scope, 1 m Probe, Dual View     | 699.00   |
| Fluke 9 mm Scope       | 4962760 | 9 mm Scope, Forward View, 20 m Probe Reel | 1999.00  |
| Fluke DS 7XX Neckstrap | 4962772 | DS 7XX Neckstrap                          | 49.00    |
| FLK-ii900              | 5075603 | Sonic Industrial Imager                   | 17499.00 |

## Thermal Imagers

### Handheld thermal cameras

|                |         |                           |        |
|----------------|---------|---------------------------|--------|
| FLK-PTI120 9Hz | 5074148 | Thermal Imager 120x90 9Hz | 749.00 |
|----------------|---------|---------------------------|--------|

### High resolution thermal cameras

|                      |         |                                     |          |
|----------------------|---------|-------------------------------------|----------|
| FLK-Ti401 Pro 9Hz    | 5085052 | Thermal Imager 640x480 9Hz          | 6999.00  |
| FLK-Ti401 Pro 60 Hz  | 5085041 | Thermal Imager 640x480 60 Hz        | 6999.00  |
| Fluke Ti480 PRO 9HZ  | 4947332 | Fluke Ti480 PRO 9Hz Thermal Imager  | 9299.00  |
| Fluke Ti480 PRO 60HZ | 4947326 | Fluke Ti480 PRO 60Hz Thermal Imager | 9299.00  |
| FLK-TiX501 9Hz       | 5085128 | Thermal Imager 640x480 9Hz          | 9999.00  |
| FLK-TiX501 60 Hz     | 5085119 | Thermal Imager 640x480 60Hz         | 9999.00  |
| Fluke TiX580 9Hz     | 4841945 | Thermal Imager; 640x480; 9 HZ, SR   | 12299.00 |
| Fluke TiX580 60Hz    | 4842073 | Thermal Imager; 640x480; 60 HZ, SR  | 12299.00 |

### High definition mounted thermal cameras

|                      |         |  |          |
|----------------------|---------|--|----------|
| Fluke RSE300 9Hz     | 4948166 | Thermal Imager; 320x240; 9 Hz              | 10999.00 |
| Fluke RSE300 60Hz    | 4944776 | Thermal Imager; 320x240; 60 Hz             | 10999.00 |
| Fluke RSE600 9Hz     | 4948175 | Thermal Imager; 640x480; 9 Hz              | 15849.00 |
| Fluke RSE600 60Hz    | 4944826 | Thermal Imager; 640x480; 60 Hz             | 15849.00 |
| Fluke 2x lens        | 4961163 | Infrared Telephoto Lens (2X magnification) | 2049.00  |
| Fluke 4x lens        | 4961188 | Infrared Telephoto Lens (4X magnification) | 4579.00  |
| Fluke RSE-MB         | 4961344 | Mounting bracket                           | 129.00   |
| Fluke RSE-Stand      | 4973844 | RSE Stand                                  | 139.00   |
| Fluke 0.75 Wide lens | 4961174 | Infrared Wide Angle Lens                   | 1029.00  |

### Gas detection thermal cameras

|                      |         |  |          |
|----------------------|---------|--|----------|
| Fluke Ti450 SF6 60Hz | 4907176 | SF6 Gas leak detection, Thermal Imager | 16999.00 |
|----------------------|---------|--|----------|

### Thermal Imagers Accessories (general)

|                      |         |  |         |
|----------------------|---------|--|---------|
| Ti-Visor2            | 3996500 | Sun Visor  | 79.00   |
| Ti-Visor3            | 4335377 | Thermal imager visor                                     | 79.00   |
| Ti-Tripod            | 3511872 | Tripod Mounting Base                                     | 109.00  |
| Ti-Tripod2           | 3996517 | Mounting Base  | 100.00  |
| Ti-Tripod3           | 4335389 | Tripod mounting base accessory                           | 99.00   |
| FLK-LENS/TELE2       | 4335350 | Telephoto Infrared Lens (Ti200/Ti300/Ti400)              | 1299.00 |
| FLK-LENS/WIDE2       | 4335361 | Wide-angle Infrared Lens (Ti200/Ti300/Ti400)             | 1299.00 |
| Fluke lens/4xTELE2   | 4607058 | 4x Telephoto IR lens for TiX560-TiX520-Ti400-Ti300-Ti200 | 5889.00 |
| Fluke lens/25MAC2    | 4607064 | 25Micron Macro IR lens for TiX560-TiX520                 | 4259.00 |
| Ti-Car Charger       | 3039779 | Ti Car Charger (TiR/TiR1/Ti10/Ti20/Ti25)                 | 125.00  |
| Ti20-RBP             | 2577796 | Rechargeable Battery Pack (Ti20)                         | 176.00  |
| FLK-TI-SBP3          | 3440365 | Extra battery (Ti32/TiR32)                               | 139.00  |
| Fluke TI-SBC3B       | 4354922 | Charging base (Ti200/Ti300/Ti400)                        | 175.00  |
| Fluke TiX5xx-Neck    | 4574715 | Adjustable neck strap                                    | 30.00   |
| Fluke TiX5xx-SBP4    | 4597142 | Additional Smart Battery                                 | 129.00  |
| Fluke TiX5xx Hand    | 4574703 | Adjustable hand strap                                    | 15.00   |
| Fluke TiX5xx-HDMI    | 4615511 | HDMI video cable   | 20.00   |
| Fluke TiX5x-Lens Cap | 4550697 | Lens cap   | 15.00   |
| Fluke TI-Bluetooth   | 4603258 | Bluetooth headset  | 79.00   |

### Thermal Imagers IR-Windows

|              |         |   |        |
|--------------|---------|---|--------|
| FLK-050-CLKT | 3460346 | 50mm C-Range IR Windows, Kwik twist         | 169.00 |
| FLK-075-CLKT | 3460387 | 75 mm C-Range IR Window, Kwik Twist         | 219.00 |
| FLK-100-CLKT | 3460439 | 100mm C-Range IR Window, Kwik Twist         | 299.00 |
| Fluke CV200  | 4326955 | 50mm IR Window, hand turn door latch        | 219.00 |
| Fluke CV300  | 4326962 | 75mm IR Windows, hand turn door latch       | 295.00 |
| Fluke CV301  | 4338164 | 75mm IR Windows, security turn door latch   | 309.00 |
| Fluke CV400  | 4326996 | 100 mm IR Windows, hand turn door latch     | 409.00 |
| Fluke CV401  | 4338173 | 100 mm IR Windows, security turn door latch | 409.00 |

## ScopeMeters

| Model                         | Art. nr | Description   | EUR     |
|-------------------------------|---------|---|---------|
| <b>Industrial ScopeMeter</b>  |         |   |         |
| Fluke 123B/EU                 | 4755659 | Industrial ScopeMeter 20MHZ, EU                         | 1560.00 |
| Fluke 123B/INT                | 4755710 | Industrial ScopeMeter 20MHZ, INT                        | 1560.00 |
| Fluke 124B/EU                 | 4755731 | Industrial ScopeMeter 40MHZ, EU                         | 1872.00 |
| Fluke 124B/INT                | 4755793 | Industrial ScopeMeter 40MHZ, INT                        | 1872.00 |
| Fluke 125B/EU                 | 4755818 | Industrial ScopeMeter 40MHZ, EU                         | 2236.00 |
| Fluke 125B/INT                | 4755876 | Industrial ScopeMeter 40MHZ, INT                        | 2236.00 |
| Fluke 123B/EU/S               | 4755890 | Industrial ScopeMeter + SCC 20MHZ, EU                   | 1976.00 |
| Fluke 123B/INT/S              | 4755953 | Industrial ScopeMeter + SCC 20MHZ, INT                  | 1976.00 |
| Fluke 124B/EU/S               | 4755975 | Industrial ScopeMeter + SCC 40MHZ, EU                   | 2288.00 |
| Fluke 124B/INT/S              | 4756031 | Industrial ScopeMeter + SCC 40MHZ, INT                  | 2288.00 |
| Fluke 125B/EU/S               | 4756054 | Industrial ScopeMeter + SCC 40MHZ, EU                   | 2652.00 |
| Fluke 125B/INT/S              | 4756112 | Industrial ScopeMeter + SCC 40MHZ, INT                  | 2652.00 |
| <b>190 Series ScopeMeters</b> |         |   |         |
| Fluke 190-204/EU              | 3894409 | ScopeMeter 4 Channel 200 MHZ Color                      | 4581.00 |
| Fluke 190-204/UN              | 3894411 | ScopeMeter 4 Channel 200 MHZ Color                      | 4990.00 |
| Fluke 190-204/EU/S            | 3894475 | ScopeMeter 4 Channel 200 MHZ Color SCC                  | 4990.00 |
| Fluke 190-204/UN/S            | 3894482 | ScopeMeter 4 Channel 200 MHZ Color UNI SCC              | 4990.00 |
| Fluke 190-104/EU              | 3894540 | ScopeMeter 4 Channel 100 MHZ Color EU                   | 4005.00 |
| Fluke 190-104/UN              | 3894557 | ScopeMeter 4 Channel 100 MHZ Color UNI                  | 4005.00 |
| Fluke 190-104/EU/S            | 3894617 | ScopeMeter 4 Channel 100 MHZ Color EU SCC               | 4414.00 |
| Fluke 190-104/UN/S            | 3894621 | ScopeMeter 4 Channel 100 MHZ Color UNI SCC              | 4414.00 |
| Fluke 190-062/EU              | 4025159 | ScopeMeter 2 Channel 60 MHZ Color                       | 2892.00 |
| Fluke 190-062/UN              | 4025171 | ScopeMeter 2 Channel 60MHZ Color                        | 2892.00 |
| Fluke 190-062/EU/S            | 4025230 | ScopeMeter 2 Channel Color SCC                          | 3300.00 |
| Fluke 190-062/UN/S            | 4025248 | ScopeMeter 2 Channel 60MHZ Color SCC                    | 3300.00 |
| Fluke 190-102/EU              | 4025318 | ScopeMeter 2 Channel 100MHZ Color                       | 3557.00 |
| Fluke 190-102/UN              | 4025329 | ScopeMeter 2 Channel 100MHZ Color SCC                   | 3557.00 |
| Fluke 190-102/EU/S            | 4025383 | ScopeMeter 2 Channel 100MHZ Color SCC                   | 3966.00 |
| Fluke 190-102/UN/S            | 4025390 | ScopeMeter 2 Channel 100MHZ Color SCC                   | 3966.00 |
| Fluke 190-202/EU              | 4025460 | ScopeMeter 2 Channel 200MHZ Color                       | 4015.00 |
| Fluke 190-202/UN              | 4025472 | ScopeMeter 2 Channel 200MHZ Color                       | 4015.00 |
| Fluke 190-202/EU/S            | 4025554 | ScopeMeter 2 Channel 200MHZ Color SCC                   | 4424.00 |
| Fluke 190-202/UN/S            | 4025568 | ScopeMeter 2 Channel 200MHZ Color SCC                   | 4424.00 |
| Fluke 190-502/EU              | 4025623 | ScopeMeter 2 Channel 500 MHZ Color                      | 4946.00 |
| Fluke 190-502/UN              | 4025638 | ScopeMeter 2 Channel 500 MHZColor UNI                   | 4946.00 |
| Fluke 190-502/EU/S            | 4025692 | ScopeMeter 2 Channel 500 MHZ Color Europe SCC           | 5355.00 |
| Fluke-190-502/UN/S            | 4025704 | ScopeMeter 2 Channel 500 MHZ Color UNI SCC              | 5355.00 |
| Fluke 190-504/EU              | 4419875 | ScopeMeter 4 Channel 500MHz Color                       | 5127.00 |
| Fluke 190-504/UN              | 4419929 | ScopeMeter 4 Channel 500MHz Color UNI                   | 5127.00 |
| Fluke 190-504/EU/S            | 4419941 | ScopeMeter 4 Channel 500MHz Color Europe SCC            | 5535.00 |
| Fluke 190-504/UN/S            | 4419990 | ScopeMeter 4 Channel 500MHz Color UNI SCC               | 5535.00 |
| <b>Motor Drive Analyzers</b>  |         |   |         |
| Fluke MDA-510                 | 4984691 | Motor Drive Analyzer 510, 4-channel color               | 5675.00 |
| Fluke MDA-550                 | 4984706 | Motor Drive Analyzer 550, 4-channel color, PRO          | 6550.00 |
| SVS-500                       | 5011031 | Shaft voltage set and magnetic base                     | 349.00  |
| SB-500                        | 5011046 | Shaft brushes set, repl brushes for SVS-500 and MDA-500 | 261.00  |
| <b>ScopeMeter Accessories</b> |         |   |         |
| AC120                         | 646163  | Heavy Duty Alligator Clips                              | 47.00   |
| AS400                         | 3894880 | Probe Extension Set, for VPS400 Probes                  | 113.00  |
| BB120                         | 646171  | Banana to BNC Adapter Plug                              | 52.00   |
| BB120-II                      | 4744369 | Set of 2 banana to BNC adapter                          | 47.00   |
| BHT190                        | 3379374 | Set of Break-out Adapters                               | 368.00  |
| BP120MH                       | 2544081 | NiMH Battery Pack (120 Series/43B)                      | 103.00  |
| BP190                         | 677390  | NiMH Battery Pack (190 Series)                          | 207.00  |
| BP290                         | 4025762 | Battery Pack Single Cap 190-series II                   | 245.00  |
| BP291                         | 3894688 | Battery Pack, Fluke 190 Series                          | 343.00  |
| C120                          | 646189  | Hard Case (43B/120 Series)                              | 112.00  |
| C120B                         | 4744391 | Soft carrying case for 120B series                      | 141.00  |
| C125                          | 646858  | Soft Meter Case   | 52.00   |
| C190                          | 677401  | Hard Case (190 Series)                                  | 263.00  |
| C195                          | 677408  | Soft Case   | 244.00  |
| C290                          | 3894803 | Hard-Shell Carrying Case                                | 219.00  |
| CS20MA                        | 677393  | Current Shunt 4-20 mA                                   | 101.00  |
| EBC290                        | 3894906 | External Battery Charger                                | 108.00  |
| HC120                         | 646668  | Hook Clips  | 59.00   |
| HC120-II                      | 4744357 | Set of 2 hook clips                                     | 52.00   |
| HC200                         | 2086410 | Hook Clips  | 42.00   |
| HH290                         | 3894844 | Hanging Hook, ScopeMeter Series 190 II                  | 77.00   |
| MA190                         | 1567481 | Medical Accessory Kit (190 Series)                      | 464.00  |
| OC4USB                        | 2166266 | Serial Interface Adapter/Cable (USB)                    | 167.00  |
| PM8907/807                    | 624764  | POWER ADAPTOR/BATTERY CHARGER                           | 125.00  |

| Model       | Art. nr | Description  | EUR    |
|-------------|---------|--|--------|
| PM8907/808  | 614039  | Battery Charger/Line Voltage Adapter UNIVERSAL (120 Series)              | 149.00 |
| PM9080      | 1641983 | Serial Interface Adapter/Cable (RS232)                                   | 277.00 |
| PM9081      | 916093  | Dual Banana Plug to Female BNC Adapter                                   | 53.00  |
| PM9082      | 916163  | Dual Banana Jack to Male BNC Adapter                                     | 53.00  |
| PM9091      | 935598  | Coaxial BNC Cables (1.5 m)   | 125.00 |
| PM9092      | 935601  | Coaxial BNC Cables (0.5 m)   | 108.00 |
| PM9093      | 935593  | Male BNC to Female BNC Adapter   | 72.00  |
| PM9096/201  | 651742  | Secondary Pick-up  | 346.00 |
| RS120-III   | 4023947 | Probe Accessory Replacement Set  | 113.00 |
| RS400       | 3894867 | Probe Replacement Set, for VPS400 Probes                                 | 90.00  |
| RS500       | 4025886 | Probe accessory replacement set for VPS500 probes                        | 161.00 |
| SCC120B     | 4744423 | Software soft carry case accessory kit 120B series                       | 520.00 |
| SCC120E     | 646684  | FlukeView Software + USB Cable + Case (120 Series) - English             | 477.00 |
| SCC128      | 2100199 | Automotive Accessory Kit (120 Series)                                    | 742.00 |
| SCC198      | 2100208 | Automotive Accessory Kit (190 Series)                                    | 933.00 |
| SCC190      | 671826  | FlukeView Software + Cable + Case (190 Series) - English, French, German | 668.00 |
| SCC290      | 3894826 | Software and Carrying Case for 190 Series II                             | 408.00 |
| SP120B      | 4744414 | Screen protector for 120B series   | 47.00  |
| STL90       | 201233  | Automotive Shielded Test Lead Set (120/190 Series)                       | 258.00 |
| STL120-III  | 4023901 | Shielded Test Lead   | 198.00 |
| STL120-IV   | 4744340 | Shielded test lead set 600V CAT IV                                       | 166.00 |
| SW90W       | 3894923 | FlukeView Software   | 369.00 |
| TAS90       | 614187  | Automotive Accessory Set (120/190 Series)                                | 72.00  |
| TRM50       | 4025864 | 50 Ohm feed-through terminator BNC                                       | 194.00 |
| UA120       | 4744384 | USB Connector adapter  | 47.00  |
| VPS41       | 4744378 | Voltage probe set 40 MHZ 600V CAT IV                                     | 161.00 |
| VPS101      | 3086317 | 1:1 Voltage Probe Set, black, 30 MHz, 1.2m                               | 225.00 |
| VPS210-G    | 3086247 | 10:1 Voltage Probe Set, grey, 200 MHz, 1.2m                              | 225.00 |
| VPS210-R    | 3086235 | 10:1 Voltage Probe Set, 1 red, 200 MHz, 1.2m                             | 225.00 |
| VPS212-G    | 3086286 | 10:1 Voltage Probe Set, grey, 200 MHz, 2.5m                              | 225.00 |
| VPS212-R    | 3086273 | 10:1 Voltage Probe Set, red, 200 MHz, 2.5m                               | 225.00 |
| VPS220-G    | 3086300 | 100:1 Voltage Probe Set, grey, 200 MHz, 1.2m                             | 225.00 |
| VPS220-R    | 3086299 | 100:1 Voltage Probe Set, red, 200 MHz, 1.2m                              | 225.00 |
| VPS40-III   | 4023920 | Voltage Probe  | 131.00 |
| VPS410-II-B | 4276937 | Industrial Voltage Probe Set 500 MHz 10:1 Blue                           | 215.00 |
| VPS410-II-G | 4276943 | Industrial Voltage Probe Set 500 MHz 10:1 Grey                           | 215.00 |
| VPS410-II-R | 4276928 | Industrial Voltage Probe Set 500 MHz 10:1 Red                            | 215.00 |
| VPS410-II-V | 4276955 | Industrial Voltage Probe Set 500 MHz 10:1 Green                          | 215.00 |
| VPS420-R    | 3894783 | High Working Voltage Probe 100:1 Red & Black                             | 250.00 |
| VPS420-B    | 4411541 | High Working Voltage Ruggedized Probe; Blue/Black                        | 250.00 |
| VPS420-G    | 4411565 | High Working Voltage Ruggedized Probe; Grey/Black                        | 250.00 |
| VPS420-V    | 4411583 | High Working Voltage Ruggedized Probe; Green/Black                       | 250.00 |
| VPS510-R    | 4025781 | Voltage Probe set 500 MHZ 10:1 Red                                       | 215.00 |
| VPS510-B    | 4025796 | Voltage probe set 500 MHZ 10:1 Blue                                      | 215.00 |
| VPS510-G    | 4025801 | Voltage probe set 500 MHZ 10:1 Grey                                      | 215.00 |
| VPS510-V    | 4025812 | Voltage probe set 500 MHZ 10:1 Green                                     | 215.00 |

### Power Quality Tools

|                    |         |  |         |
|--------------------|---------|--|---------|
| Fluke 345          | 2584181 | Power Quality Clamp Meter  | 1636.00 |
| Fluke 430-II/MA    | 4779032 | 430-II Motor Analyzer Upgrade Kit                                  | 2066.00 |
| Fluke 434-II/BASIC | 4116650 | Power Quality and energy analyzer (w/o clamps)                     | 4131.00 |
| Fluke 434-II       | 4116638 | Power Quality and energy analyzer                                  | 4773.00 |
| Fluke 434-II/INTL  | 4778918 | Power Quality and energy analyzer/International                    | 4773.00 |
| Fluke 435-II       | 4116661 | Power Quality& Energy Analyzer                                     | 6128.00 |
| Fluke 435-II/BASIC | 4116689 | Advanced Power Quality and energy analyzer (w/o clamps)            | 5520.00 |
| Fluke 435-II/INTL  | 4778929 | Power Quality and energy analyzer/International                    | 6129.00 |
| Fluke 437-II       | 4116692 | Power Quality& Energy Analyzer                                     | 8478.00 |
| Fluke 437-II/BASIC | 4116719 | 400 Hz Power Quality and Energy Analyzer (w/o clamps)              | 7823.00 |
| Fluke 437-II/INTL  | 4778934 | Power Quality and energy analyzer/International                    | 8478.00 |
| Fluke 438-II       | 4778976 | Power Quality & Motor Analyzer                                     | 7547.00 |
| Fluke 438-II/BASIC | 4778990 | Power Quality & Motor Analyzer, without clamps and FC WiFi SD Card | 6905.00 |
| Fluke 438-II/INTL  | 4779015 | Power Quality & Motor Analyzer, without FC WiFi SD Card            | 7547.00 |
| Fluke 1732/EUS     | 4706548 | Energy Logger, EU/US version                                       | 2536.00 |
| Fluke 1732/INTL    | 4706553 | Energy Logger, international version                               | 2536.00 |
| Fluke 1732/B       | 4706566 | Energy Logger, basic version                                       | 2277.00 |
| Fluke 1734/EUS     | 4706594 | Energy Logger, EU/US advanced version                              | 2841.00 |
| Fluke 1734/INTL    | 4706608 | Energy Logger, international advanced version                      | 2841.00 |
| Fluke 1734/B       | 4706582 | Energy Logger, advanced version no flexis                          | 2587.00 |
| Fluke 1736/EUS     | 4534519 | 3-Phase Power Logger, EU/US version                                | 4059.00 |
| Fluke 1736/B       | 4563561 | 3-Phase Power Logger, basic version                                | 3933.00 |
| Fluke 1736/INTL    | 4563550 | 3-Phase Power Logger, International version                        | 4059.00 |
| Fluke 1738/EUS     | 4563577 | 3-Phase Power Logger, EU/US Advanced version no flexis             | 4566.00 |
| Fluke 1738/B       | 4588378 | 3-Phase Power Logger, advanced version no flexis                   | 4059.00 |
| Fluke 1738/INTL    | 4588384 | 3-Phase Power Logger, international advanced version               | 4566.00 |



| Model               | Art. nr | Description  | EUR      |
|---------------------|---------|--|----------|
| Fluke 1742/15/EUS   | 4920613 | Power Quality Logger with 60 cm 1,500A iFlex, EUS version  | 3618.00  |
| Fluke 1742/30/EUS   | 4920651 | Power Quality Logger with 60 cm 3,000A iFlex, EUS version  | 3618.00  |
| Fluke 1742/B/EUS    | 4920660 | Power Quality Logger without iFlex, EUS version            | 3308.00  |
| Fluke 1742/15/INTL  | 4920672 | Power Quality Logger with 60 cm 1,500A iFlex, INTL version | 3618.00  |
| Fluke 1742/30/INTL  | 4920685 | Power Quality Logger with 60 cm 3,000A iFlex, INTL version | 3618.00  |
| Fluke 1742/B/INTL   | 4920697 | Power Quality Logger without iFlex, INTL version           | 3308.00  |
| 1742-6/Upgrade      | 4920964 | 1742 to 1746 Upgrade                                       | 1770.00  |
| 1742-8/Upgrade      | 4920973 | 1742 to 1748 Upgrade                                       | 3273.00  |
| Fluke 1746/15/EUS   | 4920703 | Power Quality Logger with 60 cm 1,500A iFlex, EUS version  | 4964.00  |
| Fluke 1746/30/EUS   | 4920715 | Power Quality Logger with 60 cm 3,000A iFlex, EUS version  | 4964.00  |
| Fluke 1746/B/EUS    | 4920726 | Power Quality Logger without iFlex, EUS version            | 4653.00  |
| Fluke 1746/15/INTL  | 4920732 | Power Quality Logger with 60 cm 1,500A iFlex, INTL version | 4964.00  |
| Fluke 1746/30/INTL  | 4920744 | Power Quality Logger with 60 cm 3,000A iFlex, INTL version | 4964.00  |
| Fluke 1746/B/INTL   | 4920759 | Power Quality Logger without iFlex, INTL version           | 4653.00  |
| 1746-8/Upgrade      | 4920986 | 1746 to 1748 Upgrade                                       | 1770.00  |
| Fluke 1748/15/EUS   | 4920767 | Power Quality Logger with 60 cm 1,500A iFlex, EUS version  | 6207.00  |
| Fluke 1748/30/EUS   | 4920771 | Power Quality Logger with 60 cm 3,000A iFlex, EUS version  | 6207.00  |
| Fluke 1748/B/EUS    | 4920780 | Power Quality Logger without iFlex, EUS version            | 5896.00  |
| Fluke 1748/15/INTL  | 4920798 | Power Quality Logger with 60 cm 1,500A iFlex, INTL version | 6207.00  |
| Fluke 1748/30/INTL  | 4920800 | Power Quality Logger with 60 cm 3,000A iFlex, INTL version | 6207.00  |
| Fluke 1748/B/INTL   | 4920817 | Power Quality Logger without iFlex, INTL version           | 5896.00  |
| Fluke 1760 Basic    | 2630732 | Power Quality Recorder (three-phase), Topas                | 12027.00 |
| Fluke 1760          | 2630744 | Power Quality Recorder (three-phase), Topas                | 13935.00 |
| Fluke 1760TR Basic  | 2637629 | Power Quality Recorder (three-phase), Topas                | 16481.00 |
| Fluke 1760TR        | 2637634 | Power Quality Recorder (three-phase), Topas                | 18387.00 |
| Fluke VR1710        | 3030923 | Single-Phase Voltage Quality Recorder                      | 887.00   |
| C1740               | 4116762 | Softcase for 174X and 43X-II PQ analyzer                   | 209.00   |
| C437-II             | 4116743 | Hard case 430 Series II with rollers                       | 505.00   |
| EPE-Training-E/EMEA | 4792349 | Fluke EPE Training Set - English                           | 199.00   |
| EPE-Training-F/EU   | 4792360 | Fluke EPE Training Set - French                            | 199.00   |

#### Power Quality Tools Accessories

|                      |         |  |         |
|----------------------|---------|--|---------|
| 1743/1744 Poleset    | 3024485 | Pole Mounting Kit (Fluke 1743/1744)                      | 42.00   |
| 3140R                | 2650136 | Clip-on Current Transformer 2A-400A (Fluke 1750)         | 407.00  |
| 3210-PR-TF-II        | 4531769 | 1000A Fluke 1750 Thin flexi 61cm                         | 632.00  |
| 3310-PR-TF-II        | 4531778 | 5000A Fluke 1750 Thin flexi 61cm                         | 844.00  |
| 3312-PR-TF-II        | 4531784 | 5000A Fluke 1750 Thin flexi 122cm                        | 1039.00 |
| BP120MH              | 2544081 | NiMH Battery Pack (120 Series/43B)                       | 103.00  |
| BE345                | 2839604 | Battery Eliminator (Fluke 345)                           | 156.00  |
| BP1730               | 4389436 | Li Ion Battery Pack 3.7V 2500mAh (1730)                  | 41.00   |
| C120                 | 646189  | Hard Case (43B/120 Series)                               | 112.00  |
| C17xx                | 4637381 | Soft Case  | 118.00  |
| CS1750               | 2673962 | Soft Case (Fluke 1750/1760)                              | 259.00  |
| 1730 Hanger          | 4358028 | Hanger kit (1730)  | 57.00   |
| 1730 Cable           | 4395217 | Cable,AUX input cable (1730)                             | 30.00   |
| 1750/Case            | 2650124 | Hard Case (Fluke 1750)                                   | 558.00  |
| 1750/Seat-L          | 2673937 | Fluke Power Analyze - Additional SEAT LICENSE            | 1105.00 |
| 1750/Site-L          | 2673928 | Fluke Power Analyze - Additional SITE LICENCE            | 5526.00 |
| FS17X5-TF-II         | 4531791 | 3000A 4-PH Fluke 1735 & 1745 Thin flexi set              | 1627.00 |
| FS17XX IP65-TF-II    | 4531804 | 3000A IP65 4-PH Fluke 1743/4 Thin flexi set              | 1806.00 |
| FS17XX-1PH-TF-II     | 4531819 | FS3000A/6000A 4-PH 36-Inch Thin flexi set                | 407.00  |
| FLUKE-173X ADPT      | 4717827 | AUX input adapter, 173X                                  | 136.00  |
| Fluke 17xx TL 0.1M   | 4715389 | Test lead set for Fluke 173x; 0.1m                       | 41.00   |
| FS3000/6000A-TF-4-II | 4531828 | FS3000A/6000A 4-PH 36-Inch thin flexi set                | 1623.00 |
| GPS430-II            | 4693803 | GPS Synchronization module (430-II series)               | 1560.00 |
| GPS-Time Sync        | 2539223 | GPS Time Synchronization Module (Fluke 1760)             | 434.00  |
| i17XX-flex1500       | 4637328 | Fluke-17xx iFlexi 1500A 12 IN                            | 167.00  |
| i17XX-flex3000       | 4637343 | Fluke-17xx iFlexi 3000A 24 IN                            | 179.00  |
| i17XX-flex6000       | 4637362 | Fluke-17xx iFlexi 6000A 36 IN                            | 190.00  |
| i17XX-flex1500/3pk   | 4637337 | Fluke-17xx iFlexi 1500A 12 IN, 3 pack                    | 485.00  |
| i17XX-flex3000/3pk   | 4637355 | Fluke-17xx iFlexi 3000A 24 IN, 3 pack                    | 516.00  |
| i17XX-flex6000/3pk   | 4637370 | Fluke-17xx iFlexi 6000A 36 IN, 3 pack                    | 548.00  |
| i17XX-Flex1500/4PK   | 4637411 | Fluke-17xx iFlexi 1500A 12 IN, 4 Pack                    | 632.00  |
| i17XX-Flex3000/4PK   | 4637427 | Fluke-17xx iFlexi 3000A 24 IN, 4 Pack                    | 675.00  |
| i17XX-Flex6000/4PK   | 4637430 | Fluke-17xx iFlexi 6000A 36 IN, 4 Pack                    | 717.00  |
| i1A/10A Clamp PQ1    | 3345753 | 1-phase Mini Current Clamp Set                           | 475.00  |
| i1A/10A Clamp PQ3    | 3024413 | 3-phase Mini Current Clamp Set                           | 546.00  |
| i1A/10A Clamp PQ4    | 3024424 | 4-phase Mini Current Clamp Set                           | 734.00  |
| i5A/50A Clamp PQ1    | 3345766 | 1-Phase 5A/50A Mini Current Clamp set for PQ             | 475.00  |
| i5A/50A Clamp PQ3    | 3024436 | 3-phase Mini Current Clamp Set                           | 546.00  |
| i5A/50A Clamp PQ4    | 3024449 | 4-phase Mini Current Clamp Set                           | 734.00  |
| i20/200A Clamp PQ3   | 3024451 | 3-phase Mini Current Clamp Set                           | 546.00  |
| i20/200A Clamp PQ4   | 3024460 | 4-phase Mini Current Clamp Set                           | 734.00  |
| i40S-EL              | 4637396 | Fluke-17xx i40s-EL Clamp-on Current Transformer          | 215.00  |
| i40S-EL/3pk          | 4637409 | Fluke-17xxx i40s-EL Clamp-on Current Transformer, 3 pack | 601.00  |

| Model                  | Art. nr | Description  | EUR     |
|------------------------|---------|--|---------|
| i400                   | 2277225 | AC Current Clamp (400 A)                                       | 165.00  |
| i400s                  | 2277202 | AC Current Clamp (400A)  | 296.00  |
| i430-Flexi-TF-II       | 4531725 | 6000A Fluke 430 Thin Flexi 61cm                                | 410.00  |
| i430-Flexi-TF-II-4PK   | 4531733 | 6000A Fluke 430 Thin Flexi 61cm 4 Pack                         | 1248.00 |
| i5s                    | 2508467 | AC Current Clamp (5 A)   | 550.00  |
| i5S-PR                 | 3949761 | 1750, 5A Current Clamp   | 326.00  |
| i5sPQ3                 | 2457508 | AC Current Clamp (5 A), 3-pack                                 | 1323.00 |
| IEEE519/REPORT         | 4589748 | SOFTWARE LICENSE FOR IEEE519 REPORTING                         | 527.00  |
| MP1-Magnet Probe 1     | 4589220 | Magnet probes for 4 mm banana, set of 4                        | 94.00   |
| MBX USB-RS232          | 2539565 | EP0328Z, USB to Serial RS232 Adapter                           | 47.00   |
| OC4USB                 | 2166266 | Serial Interface Adapter/Cable (USB)                           | 167.00  |
| PM9080                 | 1641983 | Serial Interface Adapter/Cable (RS232)                         | 277.00  |
| TLS430                 | 2157713 | Test Leads and Alligator Clips (4 black, 1 green) - 430 Series | 132.00  |
| TPS Clamp 10A/1A       | 2540445 | Clip-on Current Transformer 10A/1A (Fluke 1760)                | 395.00  |
| TPS Clamp 50A/5A       | 2540461 | Clip-on Current Transformer 50A/5A (Fluke 1760)                | 395.00  |
| TPS Clamp 200A/20A     | 2540450 | Clip-on Current Transformer 200A/20A (Fluke 1760)              | 395.00  |
| TPS Flex 18-TF-II      | 4531837 | 100/500A Fluke 1760 Thin Flexi 45cm (18in)                     | 463.00  |
| TPS Flex 24-TF-II      | 4531843 | 200/1000A Fluke 1760 Thin Flexi 61cm (24in)                    | 463.00  |
| TPS Flex 36-TF-II      | 4531855 | 3000/6000A Fluke 1760 Thin Flexi 91cm (36in)                   | 909.00  |
| TPS/MBX Dolph red      | 2540744 | EP0326Z, Dolphin Clip, Red                                     | 21.00   |
| TPS Nullmodem Cable    | 2540511 | A550500510, RS232 Cross Link Cable, 3M                         | 40.00   |
| TPS Shunt 1A           | 2540548 | A680501054, Shunt 1 A AC/DC                                    | 321.00  |
| TPS Shunt 20MA         | 2540553 | Shunt 20mA AC/DC (Fluke 1760)                                  | 332.00  |
| TPS Voltprobe 10V      | 2540636 | Voltage Probe 10V (Fluke 1760)                                 | 311.00  |
| TPS Voltprobe 100V     | 2540624 | Voltage Probe 100V (Fluke 1760)                                | 311.00  |
| TPS Voltprobe 400V     | 2540660 | Voltage Probe 400V (Fluke 1760)                                | 315.00  |
| TPS Voltprobe 600V     | 2540697 | Voltage Probe 600V (Fluke 1760)                                | 315.00  |
| TPS Voltprobe 1KV      | 2540649 | Voltage Probe 1000V (Fluke 1760)                               | 500.00  |
| VL1735/45              | 3276205 | Banana 4-Phase Voltage Lead set for Fluke-1735/45              | 248.00  |
| Fluke MA-C8            | 4945842 | Wall outlet adapter, Fluke-174X                                | 21.00   |
| IP65 Adapter Set       | 4946241 | IP65 rated Voltage Connector                                   | 218.00  |
| I17XX-FLEX1.5KIP       | 4921003 | IP65 iFlexi 1.5KA 60 cm  | 218.00  |
| I17XX-FLEX1.5KIP/3PK   | 4921015 | IP65 iFlexi 1.5KA 60 cm, 3 Pack                                | 523.00  |
| I17XX-FLEX1.5KIP/4PK   | 4921026 | IP65 iFlexi 1.5KA 60 cm, 4 Pack                                | 698.00  |
| I17XX-FLEX3KIPK        | 4921032 | IP65 iFlexi 3KA 60 cm  | 218.00  |
| I17XX-FLEX3KIP/3PK     | 4921044 | IP65 iFlexi 3KA 60 cm, 3 Pack                                  | 523.00  |
| I17XX-FLEX3KIP/4PK     | 4921067 | IP65 iFlexi 3KA 60 cm, 4 Pack                                  | 698.00  |
| I17XX-FLEX6KIPK        | 4921071 | IP65 iFlexi 6KA 90 cm  | 261.00  |
| I17XX-FLEX6KIP/3PK     | 4921080 | iFlexi 6KA 90 cm, 3 Pack                                       | 610.00  |
| I17XX-FLEX6KIP/4PK     | 4921098 | iFlexi 6KA 90 cm, 4 Pack                                       | 784.00  |
| I17XX-FLEX5M-EXT       | 4921116 | iFlexi Extension Cable, 5m                                     | 131.00  |
| Fluke 174X_3541-HANGER | 4890129 | Hanger Kit   | 62.00   |
| Fluke 174X GPS-REC     | 4921133 | GPS Receiver Antenna   | 336.00  |
| F17XX Cable Markers    | 4921140 | Cable Marker set, 05MM   | 52.00   |
| MP1-3R/1B              | 4944790 | 3 red/1 black Magnet probe for 4 mm banana                     | 87.00   |
| 3PHVL-17XX-5M          | 5014816 | Cable assembly, Voltage test lead 3-phase+N 5M                 | 123.00  |
| FLUKE-17XX-TL          | 5016873 | Test lead set; 1000V CAT III, nonstack/stack 0.18M             | 35.00   |
| FLUKE-17XX-TL-2M       | 5020006 | Blue, non-stackable plug and 2x alligator clips                | 26.00   |
| FLUKE-PQ400            | 4920947 | Power Quality Window   | 1673.00 |
| FLUKE-PQ400/B          | 5075807 | Power Quality Window, basic                                    | 1321.00 |
| I17XX-FLEX2M-M2M4P     | 5076272 | Male-male cable 2m, 4 pcs                                      | 507.00  |
| I17XX-FLEX2M-M2M1P     | 5076285 | Male-male cable 2m, 1 pce                                      | 132.00  |
| FLUKE-PQ-MARKER        | 5046009 | Cable market set 3P+N+PE                                       | 9.00    |
| I17XX-BNC-M2M          | 5076297 | Fluke-17xx 4 pin male to BNC male cable 2m (1x)                | 88.00   |
| I17XX-BNC-M2F          | 5076304 | Fluke-17xx 4 pin male to BNC female cable 0.1m (1x)            | 88.00   |

### Vibration Testers

|                  |         |  |         |
|------------------|---------|--|---------|
| Fluke 805        | 4094385 | Vibration Meter                              | 1784.00 |
| Fluke 805 FC     | 4489229 | Vibration Meter with Fluke Connect           | 1784.00 |
| Fluke 805/ES     | 4636786 | External Vibration Sensor                    | 1060.00 |
| Fluke 810        | 3542635 | Vibration Tester                             | 9571.00 |
| Fluke 820-2      | 4550041 | LED Stroboscope                              | 907.00  |
| Fluke 830        | 4454396 | Laser Alignment Tool                         | 7241.00 |
| Fluke 830/Magnet | 4528249 | Magnetic Bracket                             | 835.00  |
| Fluke 830/Shims  | 4551330 | Laser Alignment Tool, Shims                  | 835.00  |
| 810S             | 3530828 | Sensor                                       | 1445.00 |
| 810QDC           | 3530837 | Quick Disconnect Cable                       | 151.00  |
| 810SMM           | 3530862 | Sensor Magnet Mount                          | 212.00  |
| 810SMP           | 3530855 | Sensor Mounting Pads (10-pack)               | 29.00   |
| SBP-810          | 3530843 | Smart Battery Pack                           | 269.00  |
| Fluke-810PA      | 3986002 | AC Power Adapter with International Plug Set | 85.00   |

| Model | Art. nr | Description | EUR |
|-------|---------|-------------|-----|
|-------|---------|-------------|-----|

## Process Calibrators

### 700 Series Process Calibrators

|                   |         |   |         |
|-------------------|---------|---|---------|
| Fluke 154 INTL    | 4805625 | HART Calibration Assistant                          | 3875.00 |
| Fluke 705         | 665091  | Loop Calibrator                                     | 780.00  |
| Fluke 707         | 1617262 | Loop Calibrator                                     | 897.00  |
| Fluke 707Ex       | 2032187 | Intrinsically Safe Loop Calibrator                  | 1261.00 |
| Fluke 709         | 4234350 | Precision Loop Calibrator                           | 890.00  |
| Fluke 709H        | 4234361 | Precision HART Loop Calibrator                      | 1432.00 |
| Fluke 710         | 4991049 | mA Loop, Valve Tester, with HART                    | 2159.00 |
| Fluke 712B        | 4387857 | RTD Temperature Calibrator                          | 1105.00 |
| Fluke 714B        | 4387869 | TC Temperature Calibrator                           | 1131.00 |
| Fluke 715         | 620101  | Volt/mA Calibrator                                  | 1272.00 |
| Fluke 717 1G      | 2547166 | Pressure Calibrator (68.9 mbar)                     | 1444.00 |
| Fluke 717-15G     | 4058808 | Pressure Calibrator (1 bar)                         | 1444.00 |
| Fluke 717 100G    | 1630430 | Pressure Calibrator (7 bar)                         | 1444.00 |
| Fluke 717 30G     | 662897  | Pressure Calibrator (2 bar)                         | 1498.00 |
| Fluke 717 300G    | 2547175 | Pressure Calibrator (20 bar)                        | 1444.00 |
| Fluke 717 500G    | 2547182 | Pressure Calibrator (34.7 bar)                      | 1444.00 |
| Fluke 717 1000G   | 2547194 | Pressure Calibrator (69 bar)                        | 1444.00 |
| Fluke 717 1500G   | 2547203 | Pressure Calibrator (103.4 bar)                     | 1600.00 |
| Fluke 717 3000G   | 2547215 | Pressure Calibrator (207 bar)                       | 1600.00 |
| Fluke 717 5000G   | 2547232 | Pressure Calibrator (345 bar)                       | 1600.00 |
| Fluke 717-10000G  | 4058813 | Pressure Calibrator (690 bar)                       | 1600.00 |
| Fluke 718 30G     | 665075  | Pressure Calibrator (2 bar)                         | 2718.00 |
| Fluke 718 1G      | 2547148 | Pressure Calibrator (68.9 mbar)                     | 2831.00 |
| Fluke 718 100G    | 665080  | Pressure Calibrator (7 bar)                         | 2718.00 |
| Fluke 718 300G    | 2547153 | Pressure Calibrator (20 bar)                        | 2823.00 |
| Fluke 718Ex 30G   | 2096310 | Intrinsically Safe Pressure Calibrator (2 bar)      | 3496.00 |
| Fluke 718Ex 100G  | 2096322 | Intrinsically Safe Pressure Calibrator (7 bar)      | 3496.00 |
| Fluke 718Ex 300G  | 3023328 | Intrinsically Safe Pressure Calibrator (20 bar)     | 3496.00 |
| Fluke 719 30G     | 3315332 | Electric Pressure Calibrator (2 bar)                | 3604.00 |
| Fluke 719 100G    | 3315344 | Electric Pressure Calibrator (7 bar)                | 3604.00 |
| Fluke-719PRO 30G  | 4353218 | Electric Pressure Calibrator, 2 bar                 | 3200.00 |
| Fluke-719PRO 150G | 4353229 | Electric Pressure Calibrator, 10 bar                | 3200.00 |
| Fluke-719PRO 300G | 4353234 | Electric Pressure Calibrator, 20 bar                | 3200.00 |
| Fluke 720URTD     | 4382695 | Universal RTD adapter for 721, 721Ex and 719PRO     | 167.00  |
| Fluke-721-1601    | 4353241 | Dual Sensor Pressure Calibrator, 1.1 bar, 6.9 bar   | 2029.00 |
| Fluke-721-1603    | 4353283 | Dual Sensor Pressure Calibrator, 1.1 bar, 20 bar    | 2029.00 |
| Fluke-721-1605    | 4353327 | Dual Sensor Pressure Calibrator, 1.1 bar, 34 bar    | 2029.00 |
| Fluke-721-1610    | 4353366 | Dual Sensor Pressure Calibrator, 1.1 bar, 69 bar    | 2029.00 |
| Fluke-721-1615    | 4353401 | Dual Sensor Pressure Calibrator, 1.1 bar, 103 bar   | 2029.00 |
| Fluke-721-1630    | 4353447 | Dual Sensor Pressure Calibrator, 1.1 bar, 200 bar   | 2029.00 |
| Fluke-721-1650    | 4353486 | Dual Sensor Pressure Calibrator, 1.1 bar, 345 bar   | 2029.00 |
| Fluke-721-3601    | 4353252 | Dual Sensor Pressure Calibrator, 2.48 bar, 6.9 bar  | 2029.00 |
| Fluke-721-3603    | 4353290 | Dual Sensor Pressure Calibrator, 2.48 bar, 20 bar   | 2029.00 |
| Fluke-721-3605    | 4353330 | Dual Sensor Pressure Calibrator, 2.48 bar, 34 bar   | 2029.00 |
| Fluke-721-3610    | 4353375 | Dual Sensor Pressure Calibrator, 2.48 bar, 69 bar   | 2029.00 |
| Fluke-721-3615    | 4353412 | Dual Sensor Pressure Calibrator, 2.48 bar, 103 bar  | 2029.00 |
| Fluke-721-3630    | 4353458 | Dual Sensor Pressure Calibrator, 2.48 bar, 200 bar  | 2029.00 |
| Fluke-721-3650    | 4353499 | Dual Sensor Pressure Calibrator, 2.48 bar, 345 bar  | 2029.00 |
| Fluke 721EX-1601  | 4353265 | Dual Sensor Pressure Calibrator, 16, 100 PSIG       | 2652.00 |
| Fluke 721EX-1603  | 4353309 | Dual Sensor Pressure Calibrator, 16, 300 PSIG       | 2652.00 |
| Fluke 721EX-1605  | 4353348 | Dual Sensor Pressure Calibrator, 16, 500 PSIG       | 2652.00 |
| Fluke 721EX-1610  | 4353382 | Dual Sensor Pressure Calibrator, 16, 1000 PSIG      | 2652.00 |
| Fluke 721EX-1615  | 4353420 | Dual Sensor Pressure Calibrator, 16, 1500 PSIG      | 2652.00 |
| Fluke 721EX-1630  | 4353464 | Dual Sensor Pressure Calibrator, 16, 3000 PSIG      | 2652.00 |
| Fluke 721EX-1650  | 4353506 | Dual Sensor Pressure Calibrator, 16, 5000 PSIG      | 2652.00 |
| Fluke 721EX-3601  | 4353276 | Dual Sensor Pressure Calibrator, 36, 100 PSIG       | 2652.00 |
| Fluke 721EX-3603  | 4353311 | Dual Sensor Pressure Calibrator, 36, 300 PSIG       | 2652.00 |
| Fluke 721EX-3605  | 4353353 | Dual Sensor Pressure Calibrator, 36, 500 PSIG       | 2652.00 |
| Fluke 721EX-3610  | 4353394 | Dual Sensor Pressure Calibrator, 36, 1000 PSIG      | 2652.00 |
| Fluke 721EX-3615  | 4353435 | Dual Sensor Pressure Calibrator, 36, 1500 PSIG      | 2652.00 |
| Fluke 721EX-3630  | 4353473 | Dual Sensor Pressure Calibrator, 36, 3000 PSIG      | 2652.00 |
| Fluke 721EX-3650  | 4353514 | Dual Sensor Pressure Calibrator, 36, 5000 PSIG      | 2652.00 |
| Fluke 724         | 1553041 | Temperature Calibrator                              | 2373.00 |
| Fluke 725         | 664133  | Multifunction Process Calibrator                    | 3314.00 |
| Fluke 725Ex       | 2098179 | Intrinsically Safe Multifunction Process Calibrator | 4052.00 |
| Fluke 726         | 2452080 | Precision Multifunction Process Calibrator          | 3795.00 |
| Fluke 729 30G FC  | 4856907 | Automatic Pressure Calibrator, w/FC (2 Bar)         | 8593.00 |
| Fluke 729 150G FC | 4856894 | Automatic Pressure Calibrator, w/FC (10 Bar)        | 8593.00 |
| Fluke 729 300G FC | 4856882 | Automatic Pressure Calibrator, w/FC (20 Bar)        | 8593.00 |
| Fluke 729 30G     | 4856990 | Automatic Pressure Calibrator (2 Bar)               | 8383.00 |
| Fluke 729 150G    | 4856983 | Automatic Pressure Calibrator (10 Bar)              | 8383.00 |



| Model              | Art. nr | Description  | EUR     |
|--------------------|---------|--|---------|
| Fluke 729 300G     | 4856976 | Automatic Pressure Calibrator (20 Bar)             | 8383.00 |
| Fluke 729/750SW BU | 4972518 | Automatic Pressure Calibrator, w/DPC Track2 Bundle | 9760.00 |
| Fluke 753 EU       | 4411027 | Documenting Process Calibrator                     | 5474.00 |
| Fluke 754 EU       | 4400387 | Documenting Process Calibrator                     | 6898.00 |
| Fluke 771          | 2646347 | Milliamp Process Clamp Meter                       | 575.00  |
| Fluke 772          | 3362352 | Milliamp Process Clamp Meter                       | 820.00  |
| Fluke 773          | 3362365 | Milliamp Process Clamp Meter                       | 1090.00 |
| Fluke 787B         | 4777186 | Process Meter                                      | 1037.00 |
| Fluke 789/E        | 3977194 | Process Meter                                      | 1165.00 |
| Fluke 789/IR3000FC | 4604605 | Process Meter and FC connector                     | 1098.00 |

### Pressure Modules

|                 |         |   |         |
|-----------------|---------|---|---------|
| Fluke-700G01    | 4353523 | Pressure Gauge, -10" to 10" WC (27 mbar)        | 756.00  |
| Fluke-700G02    | 4353538 | Pressure Gauge, -30" to 30" WC (69 mbar)        | 756.00  |
| 700G04          | 4096972 | Pressure Gauge, +/- 1 bar                       | 770.00  |
| 700G05          | 4097514 | Pressure Gauge, 2 bar                           | 770.00  |
| 700G06          | 4097538 | Pressure Gauge, 6.9 bar                         | 770.00  |
| 700G07          | 4097561 | Pressure Gauge, 34 bar                          | 770.00  |
| 700G08          | 4097592 | Pressure Gauge, 69 bar                          | 770.00  |
| 700G27          | 4097545 | Pressure Gauge, 20 bar                          | 770.00  |
| 700G29          | 4097605 | Pressure Gauge, 200 bar                         | 779.00  |
| 700G30          | 4097610 | Pressure Gauge, 345 bar                         | 779.00  |
| 700G31          | 4097622 | Pressure Gauge, 690 bar                         | 779.00  |
| Fluke-700GA4    | 4353545 | Pressure Gauge, 1 bar absolute                  | 756.00  |
| Fluke-700GA5    | 4353550 | Pressure Gauge, 2 bar absolute                  | 756.00  |
| Fluke-700GA6    | 4353561 | Pressure Gauge, 6.9 bar absolute                | 756.00  |
| Fluke-700GA27   | 4353577 | Pressure Gauge, 20 bar absolute                 | 756.00  |
| 700HTPK         | 4124358 | Hydraulic Test Pump Kit, 0 to 690 bar           | 1175.00 |
| Fluke 700HTPK2  | 4623314 | Premium hydraulic test pump kit                 | 1539.00 |
| Fluke 700MTH    | 4623345 | Premium metric pressure test hose               | 566.00  |
| Fluke 700M20TH  | 4623338 | Premium M20 pressure test hose                  | 566.00  |
| 700PCK          | 100062  | Pressure Module Calibration Kit                 | 1412.00 |
| Fluke 700PTPK   | 4124364 | Pneumatic Test Pump Kit, 0 to 41 bar            | 616.00  |
| Fluke 700PTPK2  | 4623306 | Premium pneumatic test pump kit                 | 1422.00 |
| 700G/TRACK      | 4123225 | Data Logging Cable & Software                   | 431.00  |
| Fluke-700RG05   | 4353589 | Pressure Gauge, Reference, +2 bar               | 797.00  |
| Fluke-700RG06   | 4353592 | Pressure Gauge, Reference, 6.9 bar              | 797.00  |
| Fluke-700RG07   | 4353605 | Pressure Gauge, Reference, 34 bar               | 797.00  |
| Fluke-700RG08   | 4353610 | Pressure Gauge, Reference, 69 bar               | 797.00  |
| Fluke-700G10    | 4353654 | Pressure Gauge, 140 bar                         | 756.00  |
| Fluke-700RG29   | 4353622 | Pressure Gauge, Reference, 200 bar              | 864.00  |
| Fluke-700RG30   | 4353631 | Pressure Gauge, Reference, 345 bar              | 864.00  |
| Fluke-700RG31   | 4353646 | Pressure Gauge, Reference, 690 bar              | 864.00  |
| Fluke 700TTH5K  | 4623323 | Premium pressure transmitter test hose          | 566.00  |
| Fluke 700TTH10K | 4636393 | Premium pressure transmitter test hose kit, 10K | 673.00  |
| 750P00          | 4352270 | Pressure Module (0 - 2.5 mbar)                  | 1653.00 |
| 750P01          | 4352281 | Pressure Module (0 - 25 mbar)                   | 1277.00 |
| 750P02          | 4352750 | Pressure Module (0 - 70 mbar)                   | 1277.00 |
| 750P22          | 4352296 | Pressure Module (0 - 70 mbar)                   | 1277.00 |
| 750P03          | 4352738 | Pressure Module (0 - 350 mbar)                  | 1277.00 |
| 750P23          | 4352308 | Pressure Module (0 - 350 mbar)                  | 1277.00 |
| 750P04          | 4352313 | Pressure Module (0 - 1 bar)                     | 1277.00 |
| 750P24          | 4352324 | Pressure Module (0 - 1 bar)                     | 1277.00 |
| 750P05          | 4352336 | Pressure Module (0 - 2 bar)                     | 1277.00 |
| 750P06          | 4352349 | Pressure Module (0 - 7 bar)                     | 1277.00 |
| 750P27          | 4352351 | Pressure Module (0 - 20 bar)                    | 1277.00 |
| 750P07          | 4352360 | Pressure Module (0 - 35 bar)                    | 1277.00 |
| 750P08          | 4352372 | Pressure Module (0 - 70 bar)                    | 1277.00 |
| 750P09          | 4352385 | Pressure Module (0 - 100 bar)                   | 1277.00 |
| 750P2000        | 4352397 | Pressure Module (0 - 140 bar)                   | 1277.00 |
| 750P29          | 4352403 | Pressure Module (0 - 200 bar)                   | 2026.00 |
| 750P30          | 4352415 | Pressure Module (0 - 340 bar)                   | 2026.00 |
| 750P31          | 4352426 | Pressure Module (0 - 700 bar)                   | 2026.00 |
| 750PA3          | 4352432 | Pressure Module (0 - 350 mbar)                  | 1469.00 |
| 750PA4          | 4352444 | Pressure Module (0 - 1 bar)                     | 1469.00 |
| 750PA5          | 4352459 | Pressure Module (0 - 2 bar)                     | 1469.00 |
| 750PA6          | 4352467 | Pressure Module (0 - 7 bar)                     | 1469.00 |
| 750PA27         | 4352471 | Pressure Module (0 - 20 bar)                    | 1469.00 |
| 750PA7          | 4352480 | Pressure Module (0 - 35 bar)                    | 1469.00 |
| 750PA8          | 4352498 | Pressure Module (0 - 70 bar)                    | 1440.00 |
| 750PA9          | 4352500 | Pressure Module (0 - 100 bar)                   | 1440.00 |
| 750PV3          | 4352517 | Pressure Module (-350 mbar)                     | 1440.00 |
| 750PV4          | 4352521 | Pressure Module (-1 bar)                        | 1440.00 |
| 750PD2          | 4352539 | Pressure Module (-70 - 70 mbar)                 | 1440.00 |
| 750PD3          | 4352542 | Pressure Module (-350 - 350 mbar)               | 1440.00 |



| Model    | Art. nr | Description                       | EUR     |
|----------|---------|-----------------------------------|---------|
| 750PD10  | 4352556 | Pressure Module (-700 - 700 mbar) | 1440.00 |
| 750PD4   | 4352563 | Pressure Module (-1 - 1 bar)      | 1440.00 |
| 750PD5   | 4352574 | Pressure Module (-1 - 2 bar)      | 1440.00 |
| 750PD50  | 4352588 | Pressure Module (-1 - 3.5 bar)    | 1440.00 |
| 750PD6   | 4352595 | Pressure Module (-1 - 7 bar)      | 1440.00 |
| 750PD7   | 4352602 | Pressure Module (-1 - 14 bar)     | 1440.00 |
| 750PD27  | 4352616 | Pressure Module (-1 - 20 bar)     | 1440.00 |
| 750R04   | 4352625 | Pressure Module (0 - 1 bar)       | 1440.00 |
| 750R06   | 4352633 | Pressure Module (0 - 7 bar)       | 1440.00 |
| 750R27   | 4352640 | Pressure Module (0 - 20 bar)      | 1440.00 |
| 750R07   | 4352657 | Pressure Module (0 - 35 bar)      | 1440.00 |
| 750R08   | 4352669 | Pressure Module (0 - 70 bar)      | 1440.00 |
| 750R29   | 4352678 | Pressure Module (0 - 200 bar)     | 2163.00 |
| 750R30   | 4352684 | Pressure Module (0 - 340 bar)     | 2163.00 |
| 750R31   | 4352691 | Pressure Module (0 - 700 bar)     | 2163.00 |
| 750RD5   | 4352706 | Pressure Module (-1 - 2 bar)      | 1619.00 |
| 750RD6   | 4352714 | Pressure Module (-1 - 7 bar)      | 1619.00 |
| 750RD27  | 4352723 | Pressure Module (-0.8 - 20 bar)   | 1619.00 |
| 750P01Ex | 4558658 | Ex Pressure Module (0 - 25 mbar)  | 2467.00 |
| 750P24Ex | 4558686 | Ex Pressure Module (0 - 1 bar)    | 2467.00 |
| 750P05Ex | 4558664 | Ex Pressure Module (0 - 2 bar)    | 2467.00 |
| 750P06Ex | 4558673 | Ex Pressure Module (0 - 7 bar)    | 2467.00 |
| 750P27Ex | 4558699 | Ex Pressure Module (0 - 20 bar)   | 2467.00 |
| 750P09Ex | 4558725 | Ex Pressure Module (0 - 100 bar)  | 2467.00 |
| 750P29Ex | 4558702 | Ex Pressure Module (0 - 200 bar)  | 4215.00 |
| 750PA4Ex | 4558716 | Ex Pressure Module (0 - 1 bar)    | 2673.00 |

#### Process Calibrator Accessories

|                    |         |  |         |
|--------------------|---------|--|---------|
| 700HTH-1           | 2811795 | Hydraulic Test Hose  | 944.00  |
| 700ILF             | 1566730 | In-Line Filter   | 108.00  |
| 700LTP-1           | 2811763 | Low Pressure Test Pump   | 1007.00 |
| 700-IV             | 202561  | Current Shunt  | 499.00  |
| 700PMP             | 617131  | Pressure Pump (10 bar)   | 704.00  |
| 700PRV-1           | 2811808 | Pressure Relief Valve for 700HTP                                       | 1135.00 |
| 700PTP-1           | 2811774 | Pneumatic Test Pump  | 907.00  |
| 700SC              | 667425  | Serial Interface Cable (Fluke 725/725Ex/726)                           | 238.00  |
| 700TC1             | 620119  | Thermocouple Plug Kits (10 types)                                      | 145.00  |
| 700TC2             | 620127  | Thermocouple Plug Kits (5 types)                                       | 119.00  |
| Fluke 720RTD       | 4366669 | RTD Probe for 721, 721Ex and 719PRO                                    | 267.00  |
| 787CAL 230         | 662996  | Calibration Module (Fluke 787)   | 1134.00 |
| BC7217             | 668217  | Battery Charger  | 323.00  |
| BE9005 240         | 946652  | Battery Eliminator   | 299.00  |
| BP7235             | 668225  | NiMH Battery Pack  | 259.00  |
| C700               | 606928  | Hard Case (700 Series)   | 359.00  |
| C789               | 946694  | Soft Meter Case  | 201.00  |
| FVF-SC2            | 1576734 | FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B) | 264.00  |
| FVF-Basic          | 2396957 | FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)       | 161.00  |
| Fluke 700HTP-2     | 4096855 | Hydraulic Test Pump, 690 bar   | 1158.00 |
| IR189USB           | 2428108 | IR Cable - USB (280/180 Series, 1653, 789, 1550B)                      | 51.00   |
| BP7240             | 4022220 | 753/754 Spare Battery  | 176.00  |
| Fluke 750SW        | 4090343 | DPC/TRACK2-software  | 3459.00 |
| BC7240             | 4022655 | Battery Charger (753/754)  | 50.00   |
| HART Drywell Cable | 2111088 | Cable Kit, HART Drywellcontrol   | 167.00  |
| Fluke-71x          | 3345825 | Hose kit   | 105.00  |
| Fluke 700TLK       | 3829398 | Process Test Lead Kit  | 142.00  |
| Fluke 709H/TRACK   | 4281225 | Logging software with cable  | 457.00  |
| Fluke 720URTD      | 4382695 | Universal RTD adapter for 721, 721Ex and 719PRO                        | 167.00  |
| 754HCC             | 3829410 | HART-Communication Cable   | 89.00   |
| Fluke-71X-TRAP     | 4380747 | Liquid dirt trap for 718 and 719Pro                                    | 326.00  |

#### General Accessories

##### Test Leads, Probes and Clips

|           |         |  |        |
|-----------|---------|--|--------|
| 80K-15    | 618113  | Probe, Electronic Air Cleaner                | 301.00 |
| AC175     | 4101772 | Threaded Alligator Clip Set                  | 30.00  |
| AC220     | 1610103 | SureGrip Alligator Clip Set                  | 48.00  |
| AC280     | 1610115 | SureGrip Hook Clip Set                       | 38.00  |
| AC283     | 1610144 | SureGrip Pincer Clip Set                     | 43.00  |
| AC285     | 1610159 | SureGrip Alligator Clip Set                  | 24.00  |
| AC285-FTP | 4073928 | Alligator Clips and adaptors (FTP-1, FTPL-1) | 28.00  |
| AC288     | 4617784 | SureGrip™ Terminal block probe               | 38.00  |
| AC87      | 1278079 | Heavy Duty Bus Bar Clip Set                  | 50.00  |
| AC89      | 873448  | Heavy Duty Insulation Piercing Test Clip     | 56.00  |
| BP980     | 1616807 | Dual Banana Plug Kit                         | 57.00  |

| Model                 | Art. nr | Description  | EUR     |
|-----------------------|---------|--|---------|
| FTL660                | 2280204 | Fused Test Lead Set  | 65.00   |
| FTP-1                 | 3869437 | Fuse test probe set  | 99.00   |
| FTPL-1                | 3869443 | Fuse test probe set with test leads                          | 109.00  |
| H900                  | 1616818 | Test Lead Holder   | 34.00   |
| Leadwrap              | 4083525 | Durable Nylon Hook and Loop Fastener, 3 pack                 | 9.00    |
| T5-Kit                | 3971169 | T5 Tester Accessory Starter Kit                              | 55.00   |
| T5-RLS                | 4089137 | Replacement Test Lead Set (T5)                               | 24.00   |
| TL175                 | 3521976 | Twist Guard Test Leads                                       | 30.00   |
| TL175E                | 3565554 | Twist Guard Test Leads, 4mm                                  | 33.00   |
| TL220-1               | 3971178 | SureGrip Industrial Test Lead Set                            | 83.00   |
| TL221                 | 2003602 | SureGrip Extension Lead Set                                  | 37.00   |
| TL222                 | 2003616 | SureGrip Silicone Test Lead Set                              | 37.00   |
| TL223-1               | 3971184 | SureGrip Electrical Test Lead Set                            | 76.00   |
| TL224                 | 1610198 | SureGrip Silicone Test Lead Set                              | 33.00   |
| TL225-1               | 3971191 | Stray Voltage Eliminator test Lead Set                       | 110.00  |
| TL238                 | 2132831 | SureGrip High Energy Test Lead Kit                           | 83.00   |
| TL27                  | 668571  | Heavy Duty Test Lead Set                                     | 38.00   |
| TL40                  | 1590606 | Retractable Tip Test Lead Set                                | 55.00   |
| TL71-1                | 3971207 | TL71, Test Lead Set  | 30.00   |
| TL75-1                | 3971218 | TL75, Test Lead Set  | 25.00   |
| TL76                  | 2032684 | All-in-one Test Lead Set                                     | 43.00   |
| TL80A-1               | 3971229 | TL80A, Test Lead Set   | 79.00   |
| TL81A                 | 1277073 | Deluxe Electronic Test Lead Kit                              | 165.00  |
| TL910                 | 1616632 | Electronic Test Lead Set (with replacement tips)             | 76.00   |
| TL930                 | 1616671 | Patch Cords (60 cm)  | 19.00   |
| TL932                 | 1616680 | Patch Cords (90 cm)  | 21.00   |
| TL935                 | 1616698 | Patch Cord Kit (60, 90, 120 cm)                              | 63.00   |
| TL940                 | 1616705 | Mini-Hook Test Lead Set                                      | 21.00   |
| TL950                 | 1616710 | Mini-Pincer Test Lead Set                                    | 38.00   |
| TL960                 | 1616722 | Micro-Hook Test Lead Set                                     | 21.00   |
| TL970                 | 1616793 | Hook and Pincer Test Lead Kit                                | 79.00   |
| TLK1550-RTLK          | 4112351 | Integral test lead & 10 kV clamp                             | 239.00  |
| TLK220                | 2097022 | SureGrip Accessory Kit                                       | 153.00  |
| TLK-225               | 3971234 | TLK225, SureGrip Master Set                                  | 165.00  |
| TLK281-1              | 3971241 | TLK281, Automotive Test Lead Kit                             | 146.00  |
| TLK-282-1             | 3971252 | TLK282, DeLuxe Automotive Test Lead Kit                      | 186.00  |
| TLK287                | 3045631 | Electronic Master Test Lead Kit                              | 175.00  |
| TLK289                | 3092521 | Industrial Master Test Lead Kit                              | 175.00  |
| TLK290                | 2435092 | Test Probe Kit   | 65.00   |
| TLK291                | 2435108 | Fused Test Probe Set   | 65.00   |
| TP1-1                 | 3971265 | TP1, Test Probes   | 19.00   |
| TP175                 | 3521983 | TwistGuard test Probes, 2MM dia probe tips                   | 21.00   |
| TP175E                | 3565568 | TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters | 23.00   |
| TP2-1                 | 3971283 | TP2, Test Probes   | 21.00   |
| TP220-1               | 3971276 | TP220, SureGrip Test Probes                                  | 21.00   |
| TP38                  | 1541636 | Slim Reach Test Probe Set (insulated)                        | 19.00   |
| TP74                  | 1541649 | Lantern Tip Test Probe Set                                   | 21.00   |
| TP80                  | 873455  | Electronic Test Probe Set                                    | 41.00   |
| TP912                 | 1616644 | Replacement tips for TL910                                   | 38.00   |
| TP920                 | 1616659 | Test Probe Adapter Kit                                       | 55.00   |
| <b>Current Clamps</b> |         |  |         |
| 80i-110s              | 114519  | AC/DC Current Clamp (100 A)                                  | 779.00  |
| i1000s                | 1568487 | AC Current Clamp (1000 A)                                    | 660.00  |
| i1010                 | 617735  | AC/DC Current Clamp (1000 A)                                 | 474.00  |
| i1010 Kit             | 2096998 | AC/DC Current Clamp (1000 A) with Soft Case                  | 484.00  |
| i200                  | 664755  | AC Current Clamp (200 A)                                     | 165.00  |
| i2000 flex            | 2584912 | AC Flexible Current Clamp (2000 A)                           | 330.00  |
| i200s                 | 664760  | AC Current Clamp (200 A)                                     | 275.00  |
| i30                   | 2584920 | AC/DC Current Clamp (30A)                                    | 440.00  |
| i3000 flex-4PK        | 2696367 | AC Flexible Current Clamp (3000 A), 4-pack                   | 1323.00 |
| i3000s                | 657202  | AC Current Clamp (3000 A)                                    | 794.00  |
| i3000s flex-24        | 2584888 | AC Flexible Current Clamp (3000 A), 610 mm                   | 506.00  |
| i3000s flex-36        | 2584901 | AC Flexible Current Clamp (3000 A), 915 mm                   | 606.00  |
| i30s                  | 2584935 | AC/DC Current Clamp (30A)                                    | 606.00  |
| i310s                 | 2840309 | AC/DC Current Clamp (300A)                                   | 363.00  |
| i400                  | 2277225 | AC Current Clamp (400 A)                                     | 165.00  |
| i400s                 | 2277202 | AC Current Clamp (400A)                                      | 296.00  |
| I40S-PR (1750)        | 3949777 | 40A Current Clamp (1750)                                     | 387.00  |
| i410                  | 617727  | AC/DC Current Clamp (400 A)                                  | 275.00  |
| i410 Kit              | 2097005 | AC/DC Current Clamp (400 A) with Soft Case                   | 319.00  |
| i6000s flex-24        | 2840311 | AC Current Clamp (6000 A)                                    | 660.00  |
| i6000s flex-36        | 2840327 | AC Current Clamp (6000 A)                                    | 771.00  |
| i800                  | 2840283 | AC Current Clamp (800 A)                                     | 237.00  |

| Model                          | Art. nr | Description                                       | EUR    |
|--------------------------------|---------|---|--------|
| <b>Temperature Accessories</b> |         |   |        |
| 80AK-A                         | 2747812 | Thermocouple Adapter                              | 35.00  |
| 80BK-A                         | 2747801 | Integrated DMM Temperature Probe (Type K)         | 39.00  |
| 80CJ-M                         | 833046  | Male Mini Connectors (Type J)                     | 26.00  |
| 80CK-M                         | 779942  | Male Mini Connectors (Type K)                     | 26.00  |
| 80PJ-1                         | 1288191 | Bead Probe (Type J)                               | 28.00  |
| 80PJ-9                         | 1288218 | General Purpose Probe (Type J)                    | 71.00  |
| 80PJ-EXT                       | 1288234 | Extension Wire Kit (Type J)                       | 64.00  |
| 80PK-1                         | 750422  | Bead Probe (Type K)                               | 37.00  |
| 80PK-10                        | 3439199 | Pipe Clamp Temperature Probe (Type K)             | 217.00 |
| 80PK-11                        | 2724500 | Velcro Temperature Probe                          | 42.00  |
| 80PK-18 Kit                    | 3448859 | Pipe Clamp Temperature Probe Kit                  | 352.00 |
| 80PK-22                        | 2098684 | SureGrip Immersion Probe                          | 108.00 |
| 80PK-24                        | 2098691 | SureGrip Air Probe                                | 141.00 |
| 80PK-25                        | 2098706 | SureGrip Piercing Probe                           | 127.00 |
| 80PK-26                        | 2098714 | SureGrip General Purpose Probe                    | 141.00 |
| 80PK-27                        | 2098723 | SureGrip Industrial Surface Probe                 | 385.00 |
| 80PK-3A                        | 874610  | Surface Probe (Type K)                            | 242.00 |
| 80PK-8                         | 200360  | Pipe Clamp Temperature Probe (Type K)             | 197.00 |
| 80PK-9                         | 1288229 | General Purpose Probe (Type K)                    | 71.00  |
| 80PK-EXT                       | 1288241 | Extension Wire Kit (Type K)                       | 64.00  |
| 80PR-60                        | 2148313 | RTD Temperature Probe (Fluke 66/68)               | 78.00  |
| 80PT-25                        | 2104397 | SureGrip Piercing Probe                           | 112.00 |
| 80PT-EXT                       | 1288252 | Extension Wire Kit (Type T)                       | 64.00  |
| 80T-150UA                      | 3190456 | Universal Temperature Probe (for DMMs)            | 303.00 |
| 80TK                           | 736736  | Thermocouple Module (Type K)                      | 153.00 |
| <b>Cases and Holsters</b>      |         |   |        |
| C10                            | 897744  | Meter Holster                                     | 29.00  |
| C100                           | 827055  | Hard Meter and Accessory Case                     | 77.00  |
| C101                           | 2437514 | Hard Case   | 71.00  |
| C115                           | 2826063 | Soft Meter Case                                   | 68.00  |
| C116                           | 2826074 | Soft Meter Case                                   | 81.00  |
| C120                           | 646189  | Hard Case (43B/120 Series)                        | 112.00 |
| C125                           | 646858  | Soft Meter Case                                   | 52.00  |
| C12A                           | 930529  | Soft Meter Case                                   | 36.00  |
| C150                           | 4111540 | Zippered Soft Carrying Case                       | 33.00  |
| C1600                          | 2091049 | Meter and Accessory Case                          | 43.00  |
| C1620                          | 4359042 | Carrying Case                                     | 210.00 |
| C190                           | 677401  | Hard Case (190 Series)                            | 263.00 |
| C195                           | 677408  | Soft Case   | 244.00 |
| C20                            | 708396  | Hard Meter Case                                   | 72.00  |
| C23                            | 1663209 | Soft Meter Case                                   | 29.00  |
| C25                            | 681114  | Soft Meter Case                                   | 61.00  |
| C280                           | 3182785 | Soft Meter Case                                   | 71.00  |
| C33                            | 1664120 | Soft Meter Case                                   | 33.00  |
| C345                           | 3311173 | Soft Case   | 86.00  |
| C35                            | 2826056 | Soft Meter Case                                   | 49.00  |
| C43                            | 1663230 | Soft Meter Case                                   | 91.00  |
| C50                            | 762823  | Soft Meter Case                                   | 43.00  |
| C510                           | 1547885 | Leather Meter Case                                | 85.00  |
| C520A                          | 1629104 | Leather Tester Case                               | 65.00  |
| C550                           | 1547919 | Tool Bag  | 143.00 |
| C75                            | 865535  | Soft Accessory Case                               | 20.00  |
| C781                           | 619988  | Soft Meter Case                                   | 105.00 |
| C789                           | 946694  | Soft Meter Case                                   | 201.00 |
| C799 Softcase                  | 4021731 | Field Softcase for 75X                            | 91.00  |
| C800                           | 896220  | Hard Meter and Accessory Case                     | 78.00  |
| C90                            | 466029  | Soft Meter Case                                   | 43.00  |
| CXT170                         | 3352567 | Rugged Pelican Hard Case                          | 185.00 |
| CXT280                         | 3352571 | Rugged Pelican Hard Case                          | 185.00 |
| CXT80                          | 3352559 | Rugged Pelican Hard Case                          | 185.00 |
| CXT1000                        | 4628917 | Extreme Hard case                                 | 185.00 |
| FLUKEPACK30                    | 4983088 | Professional Tool Backpack                        | 169.00 |
| H3                             | 1608458 | Holster (330 Series)                              | 47.00  |
| H5                             | 649365  | Electrical Tester Holster (Fluke T5)              | 36.00  |
| H6                             | 2152040 | Infrared Thermometer Holster (Fluke 63/65/68/561) | 34.00  |
| H-T6                           | 4910585 | T6 Belt Holster                                   | 36.00  |
| H15                            | 4111533 | Belt Holster for T100 series                      | 32.00  |
| H80M                           | 2138458 | Holster + Magnetic Hanger                         | 45.00  |
| <b>Automotive Accessories</b>  |         |   |        |
| BP880                          | 2150594 | BNC to Female Double Stacking Banana Plug         | 16.00  |
| BP881                          | 2151015 | BNC to Male Double Stacking Banana Plug           | 20.00  |
| PV350                          | 919811  | Pressure Vacuum Module                            | 309.00 |

| Model  | Art. nr | Description  | EUR    |
|--------|---------|--|--------|
| RPM80  | 880849  | Inductive Pick-up                                  | 105.00 |
| SCC128 | 2100199 | Automotive Accessory Kit (120 Series)              | 742.00 |
| SCC198 | 2100208 | Automotive Accessory Kit (190 Series)              | 933.00 |
| STL90  | 201233  | Automotive Shielded Test Lead Set (120/190 Series) | 258.00 |
| TAS90  | 614187  | Automotive Accessory Set (120/190 Series)          | 72.00  |
| TL28A  | 1273185 | Automotive Test Lead Set                           | 63.00  |
| TL82   | 2150636 | Automotive Pin and Socket Adapter Set              | 125.00 |
| TP40   | 1567573 | Automotive Back Probe Pins (5 pcs) (4 mm)          | 44.00  |
| TP81   | 2149098 | Insulation Piercing Clip Set (4 mm)                | 61.00  |
| TP82   | 2149080 | Insulation Piercing Clip Set (2 mm)                | 58.00  |
| TP88   | 2149102 | Rigid Back Probe Pin Set                           | 15.00  |

#### Other Accessories

|              |         |  |        |
|--------------|---------|--|--------|
| 80K-40       | 382846  | High Voltage Probe                               | 309.00 |
| 80K-6        | 532424  | High Voltage Probe                               | 172.00 |
| EBC290       | 3894906 | External Battery Charger                         | 108.00 |
| FOM          | 200428  | Fiber Optic Meter                                | 610.00 |
| FOS-850      | 200433  | Fiber Optic Light Source                         | 368.00 |
| FOS-850/1300 | 200441  | Fiber Optic Light Source                         | 901.00 |
| L200         | 2096346 | Probe Light                                      | 26.00  |
| L205         | 2098588 | Mini Hat Light                                   | 34.00  |
| L206         | 2098595 | Deluxe Hat Light                                 | 43.00  |
| L210         | 2096379 | Probe light and probe extender                   | 42.00  |
| L215         | 2096368 | SureGrip kit with probe light and probe extender | 97.00  |
| LVD1         | 4571403 | Volt Light                                       | 37.00  |
| LVD2         | 2740300 | Volt Light                                       | 41.00  |
| MC50         | 2092300 | MeterCleaner Wipes, 50-pack                      | 97.00  |
| MC6          | 2092212 | MeterCleaner Wipes, 6-pack                       | 14.00  |
| PV350        | 919811  | Pressure Vacuum Module                           | 309.00 |
| SV225        | 3100477 | Stray Voltage Adapter                            | 74.00  |
| TPAK         | 1281997 | ToolPak, Meter Hanging Kit                       | 43.00  |
| FL-45 EX     | 4972422 | 45 lumen intrinsically safe flashlight           | 45.00  |
| FL-120 EX    | 4972431 | 120 lumen intrinsically safe flashlight          | 69.00  |
| FL-150 EX    | 4972446 | 150 lumen intrinsically safe flashlight          | 89.00  |
| HL-200 EX    | 4972410 | 200 lumen intrinsically safe headlamp            | 89.00  |

#### Fuses

|         |         |   |       |
|---------|---------|---|-------|
| 943121  | 943121  | Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm | 4.90  |
| 803293  | 803293  | Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm   | 9.00  |
| 830828  | 830828  | Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm     | 7.90  |
| 2279339 | 2279339 | Fuse, A:315mA (f), V:1000V, IR:10kA, 6.35x32 mm   | 11.60 |
| 740670  | 740670  | Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm      | 3.80  |

#### Software

|           |         |  |        |
|-----------|---------|--|--------|
| FVF-Basic | 2396957 | FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)         | 161.00 |
| FVF-SC2   | 1576734 | FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)   | 264.00 |
| FVF-SC4   | 2687335 | FlukeView Forms Software + Cable (8845A/8846A)                           | 303.00 |
| FVF-SC5   | 2791314 | FlukeView Forms Basic (8845A/8846A)                                      | 174.00 |
| FVF-UG    | 1576741 | FlukeView Forms Upgrade  | 142.00 |
| IR189USB  | 2428108 | IR Cable - USB (280/180 Series, 1653, 789, 1550B)                        | 51.00  |
| SCC120E   | 646684  | FlukeView Software + USB Cable + Case (120 Series) - English             | 477.00 |
| SCC120F   | 646692  | FlukeView Software + USB Cable + Case (Fluke 123) - French               | 477.00 |
| SCC190    | 671826  | FlukeView Software + Cable + Case (190 Series) - English, French, German | 668.00 |
| SW90W     | 3894923 | FlukeView Software   | 369.00 |

#### N.V. Fluke Belgium

Langeveldpark - Unit 5  
P. Basteleusstraat 2-4-6  
1600 St.-Pieters-Leeuw  
Tel.: 02/402 21 00  
Fax: 02/402 21 01  
E-mail: info@fluke.be  
Web: www.fluke.be

De genoemde prijzen zijn adviesprijzen en exclusief BTW. Prijswijzigingen voorbehouden.

Les prix annoncés sont des prix de revente H.T. conseillés et peuvent être adaptés à tout moment sans avis préalable.

16 Prijzen zijn excl. BTW. / Prix hors TVA.

10001 - Fluke Test Tools Price List End  
Customer - English  
Rev. 40