

# Fluke Test Tools Price List

**FLUKE®**

Valid from: 02-07-2018

Model	Art. nr	Description	EUR
-------	---------	-------------	-----

## Fluke Connect - 3000 Series

Fluke Connect - 3000 Series			
FLK-3000 FC	4401595	FC Wireless Digital Multimeter	296.00
FLK-3000 FC GM	4467750	FC Wireless General Maintenance System	848.00
FLK-3000 FC HVAC	4465607	FC Wireless HVAC System	615.00
FLK-3000 FC IND	4465599	FC Wireless Industrial System	1060.00
FLK-3000FC/TPAK	4699340	Fluke 3000FC with TPAK meter hanging kit	328.00
Fluke 3000FC/EDA2	4699333	Electronics DMM and deluxe accessory kit	381.00
Fluke 3000FC/1AC-II	4699302	Electrician's DMM voltage tester and accessory kit	423.00
FLK-A3000 FC	4401588	FC Wireless AC Current Clamp Module	190.00
FLK-A3000 FC KIT	4465618	FC Wireless Essential Kit with A3000	423.00
FLK-A3001 FC	4459439	FC Wireless iFlex AC Current Module	222.00
FLK-A3001 FC KIT	4465665	FC Wireless Essential Kit with i3000	456.00
FLK-A3002 FC	4459442	FC Wireless AC/DC Current Module	126.00
FLK-A3003 FC	4629295	FC Wireless 2000A DC Clamp meter	529.00
FLK-A3004 FC	4629301	FC Wireless 4-20mA DC Clamp meter	635.00
FLK-T3000 FC	4401563	FC Wireless K-Type Temperature Module	190.00
FLK-T3000 FC KIT	4465652	FC Wireless Essential Kit with T3000	423.00
FLK-V3000 FC	4401556	FC Wireless AC Voltage Module	201.00
FLK-V3000 FC KIT	4465641	FC Wireless Essential Kit with V3000	423.00
FLK-V3001 FC	4459421	FC Wireless DC Voltage Module	201.00
FLK-V3001 FC KIT	4467777	FC Wireless essential Kit with V3001	423.00
FLK-V3003 FC KIT	4467789	FC Wireless Kit w. DMM, AC+DC Voltage Modules	688.00

## Fluke Connect - Accessories

FLK-FC_SD Card	4463628	Fluke Connect Wireless SD Card	99.00
FLK-PC3000 FC	4401602	FC Wireless PC Adapter	105.00
FLUKE-IR3000FC	4460436	Connector, Infrared, FC	136.00

## Digital Multimeters

### 110 Series Multimeters

Fluke 113	3088053	True RMS Multimeter	130.00
Fluke 114	2583552	True RMS Multimeter	172.00
Fluke 115	2583583	True RMS Multimeter	199.00
Fluke 116	2583601	True RMS Multimeter	238.00
116/62MAX+ Kit	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	432.00
Fluke 116/323 Kit	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	338.00
Fluke 117	2583647	True RMS Multimeter	249.00
Fluke 117/323 Kit	4296034	Fluke Electrician's Multimeter Combo Kit	322.00
C50	762823	Soft Meter Case	41.00

### 170 Series Multimeters

Fluke 175	1592901	True RMS Multimeter	238.00
Fluke 177	1592874	True RMS Multimeter	290.00
Fluke 179	1592842	True RMS Multimeter	342.00
C90	466029	Soft Meter Case	41.00
Fluke 179/EDA2/EUR	3947719	Electronics Combo Kit	405.00

### 200 Series Multimeters

Fluke 233	3469334	Remote Display Multimeter	338.00
Fluke 279FC/iFlex	4684050	Wireless TRMS Thermal Multimeter w/iFlex	999.00
Fluke 279FC I/B	4989200	Wireless TRMS Thermal Multimeter with iFlex & extra battery	1099.00
Fluke 287/EUR	3947781	True RMS Electronic Logging Multimeter with TrendCapture	615.00
Fluke 287/FVF/EUR	3947796	FlukeView Forms Combo Kit	721.00
Fluke 289/EUR	3947801	True RMS Industrial Logging Multimeter with TrendCapture	668.00
Fluke 289/FVF/EUR	3947812	Industrial Logging Multimeter and Software Combo Kit	774.00
C280	3182785	Soft Meter Case	68.00
Fluke 287/FVF/IR3000	4699316	Fluke 287 FlukeView® Forms Combo Kit	795.00
Fluke 289/FVF/IR3000	4699325	Fluke 289 FlukeView® Forms Combo Kit	848.00

Model	Art. nr	Description	EUR
<b>20 Series Multimeters</b>			
Fluke 27II/EUR	3947770	Industrial Multimeter (IP67)	509.00
Fluke 28II/EUR	3947820	True RMS Industrial Multimeter (IP67)	509.00
Fluke 28 II Ex	4017165	Intrinsically safe true-rms digital multimeter	1325.00
C25	681114	Soft Meter Case	58.00
<b>70 Series Multimeters</b>			
Fluke 77-4/EUR	3947835	Multimeter	423.00
C90	466029	Soft Meter Case	41.00
<b>80 Series Multimeters</b>			
Fluke 83-V/EUR	3947847	Multimeter	476.00
Fluke 87-V/EUR	3947858	True RMS Multimeter	499.00
Fluke 87-V/E2K/EUR	3947864	Industrial Electricians Combo Kit	599.00
C25	681114	Soft Meter Case	58.00
<b>Bench Multimeters</b>			
Fluke 8808A 220V	2802372	5.5 Digit Multimeter	700.00
Fluke 8808A 240V	2802385	5.5 Digit Multimeter	700.00
Fluke 8808A/SU 220V	2802459	5.5 Digit Multimeter (software & cable)	895.00
Fluke 8808A/SU 240V	2802467	5.5 Digit Multimeter (software & cable)	895.00
Fluke 8808A/TL 220V	3111085	5.5 Digit Multimeter, 2X4W Test Lead Kit	780.00
Fluke 8808A/TL 240V	3111097	5.5 Digit Multimeter, 2X4W Test Lead Kit	780.00
Fluke 8845A 220V	2577352	6.5 Digit Precision Multimeter	1045.00
Fluke 8845A 240V	2577365	6.5 Digit Precision Multimeter	1045.00
Fluke 8845A/SU 220V	2675315	6.5 Digit Precision Multimeter (incl. software + cable)	1235.00
Fluke 8845A/SU 240V	2675332	6.5 Digit Precision Multimeter (incl. software + cable)	1235.00
Fluke 8846A 220V	2577383	6.5 Digit Precision Multimeter	1375.00
Fluke 8846A 240V	2577390	6.5 Digit Precision Multimeter	1375.00
Fluke 8846A/SU 220V	2675367	6.5 Digit Precision Multimeter (incl. software + cable)	1565.00
Fluke 8846A/SU 240V	2675380	6.5 Digit Precision Multimeter (incl. software + cable)	1565.00
884X-CASE	2675552	Hard Case (8845A/8846A)	430.00
884X-RTD	2675468	100 OHM RTD Temperature Probe	565.00
884X-SHORT	2653346	4-wire short	31.00
884X-USB	2675479	USB to RS232 Cable Adapter	160.00
884X-1G	2675534	USB Memory 1 GB	40.00
8845A-EFPT	2742690	Extended Fine Point Tip Adapter Set	20.00
8845A-TPIT	2742683	Test Probe IC Tip Set	15.00
FVF-UG	1576741	FlukeView Forms Upgrade	135.00
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	289.00
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	166.00
RS43	946470	Serial Interface Cable	87.00
TL2X4W-PTII	2826215	2x4 Wire Ohms Test Lead 2 mm Probe Tip	77.00
TL2x4W-TWZ	2723629	2X4-Wire Ohms Tweezers Test Leads	100.00
Y8021	708289	IEEE-488 Shielded Interface Cable, 1 m	448.00
Y8022	708297	IEEE-488 Shielded Interface Cable, 2 m	523.00
Y8846S	2675518	Rack mount kit single (8845A/8846A)	122.00
Y8846D	2771721	Rack mount kit dual (8845A/8846A)	165.00
<b>Automotive Meters</b>			
Fluke 88V/A	2117440	Automotive Meter Combo Kit	713.00
<b>Clamp Meters</b>			
Fluke 323	4152628	True RMS Clamp Meter	133.00
Fluke 324	4152637	True RMS Clamp Meter	174.00
Fluke 325	4152643	True RMS Clamp Meter	236.00
Fluke 353	2840252	AC/DC True RMS Clamp Meter	629.00
Fluke 355	2840265	AC/DC True RMS Clamp Meter	787.00
Fluke 365	3790607	Detachable TRMS Clamp Meter	262.00
Fluke 368 FC	4709907	Wireless leakage current clamp, 40mm jaw	699.00
Fluke 369 FC	4709934	Wireless leakage current clamp, 61mm jaw	699.00
Fluke 373	3790564	600A TRMS Clamp Meter	262.00
Fluke 374FC	4696001	600A AC/DC TRMS Wireless Clamp Meter	367.00
Fluke 375FC	4695932	600A AC/DC TRMS Wireless Clamp Meter	439.00
Fluke 376FC	4695861	1000A AC/DC TRMS Wireless Clamp Meter with iFlex	499.00
Fluke 381	3610452	Remote Display TRMS Clamp Meter	587.00
Fluke 902 FC	4695814	TRMS Wireless HVAC ClampMeter	294.00
62MAX+/323/1AC Kit	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	259.00
Fluke 116/323 Kit	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	338.00
Fluke i2500-18	3676405	iFlex Probe	136.00
Fluke i2500-10	3676410	iFlex Probe	136.00
H3	1608458	Holster (330 Series)	45.00

Model	Art. nr	Description	EUR
<b>Electrical Testers</b>			
Fluke 1000FLT	4472387	Fluorescent Light Tester	241.00
T6-1000/EU	4910257	Electrical Tester with FieldSense™, round	279.00
T6-600/EU	4910322	Electrical Tester with FieldSense™, round	219.00
H-T6	4910585	T6 Belt Holster	34.00
Fluke T5-600	659612	Electrical Tester	164.00
T5-600/62MAX+/1AC kit	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	267.00
Fluke T5-1000	659570	Electrical Tester	184.00
Fluke T5-H5-1AC II Kit	2098657	Electrical Tester Kit with Holster and 1AC	205.00
Fluke T90	4016945	Voltage/continuity tester	61.00
Fluke T110	4016950	Voltage/continuity tester with switchable load	87.00
Fluke T130	4016961	Voltage/continuity tester with LCD, switchable load	128.00
Fluke T150	4016977	Voltage/continuity tester with LCD, Ohms, switchable load	148.00
Fluke 2042	2435038	Cable Locator (Transmitter + Receiver)	766.00
Fluke 2042T	2435045	Cable Locator Transmitter	399.00
Fluke 9040EUR	4014969	Phase Rotation Indicator	205.00
Fluke 9062	2435077	Motor and Phase Rotation Indicator	188.00
LVD1	4571403	Volt Light	36.00
LVD2	2740300	Volt Light	40.00
H5	649365	Electrical Tester Holster (Fluke T5)	34.00
FTL660	2280204	Fused Test Lead Set	62.00
Fluke 1AC II	2432932	Volt Alert	31.00
Fluke 1AC II 5PK	2433056	Volt Alert 5-pack	112.00
FLK2AC/200-1000VCL	3611985	ACV Detector 200-1000V	29.00
FLK2AC/90-1000V	3807928	ACV Detector 90-1000V, Flat-tip	29.00
FLK2AC/90-1000V5PK	3807937	Volt Alert 90-1000V, 5-pack, Flat-tip	102.00
PRV240	4566209	Proving unit	158.00
Fluke 117/PRV240	4636971	Proving unit, Fluke 117 DMM Kit	317.00
PRV240FS	4910310	Proving unit, T6/NCV	164.00
<b>Laser Levels</b>			
Fluke-3PR	4811457	3 Point laser level, red	199.00
Fluke-3PG	4811469	3 Point laser level, green	219.00
Fluke-180LR	4811504	2 Line laser level, red	259.00
Fluke-180LG	4811491	2 Line laser level, green	319.00
Fluke-180LG System	4811519	Green line laser with LDG detector	379.00
Fluke-180LR System	4811528	Red line laser with LDR detector	329.00
Fluke-LDR	4811543	Laser line detector red	89.00
Fluke-LDG	4819919	Laser line detector green	99.00
PLS-20513	4791765	Tripod Telescope 9 FT 6 IN	180.00
PLS-20295	4845009	Magnetic Wall Bracket for PLS 3, 5,180,480	51.00
PLS-20512	4845027	Tripod Standard, 5/8 X 11	107.00
PLS-21502	4919812	Tripod Extender PLS3/180	10.00
<b>Distance Meters</b>			
Fluke 414D	4106830	Laser Distance Meter	133.00
Fluke 419D	4106853	Laser Distance Meter	256.00
Fluke 424D	4106866	Laser Distance Meter	370.00
414D/62MAX+ Kit	4296052	Fluke Laser distance meter and IR thermometer kit	226.00
<b>Battery Analyzers</b>			
Fluke BT510	4489970	Battery Analyzer	2719.00
Fluke BT520	4489981	Battery Analyzer	3380.00
Fluke BT521	4489996	Advanced Battery Analyzer	3789.00
<b>Battery Analyzer Accessories</b>			
BTL10	4542264	Standard Battery Analyzer Probes	330.00
BTL20	4542273	Intelligent Test Probe Set, w/Extenders (no temp sensor)	509.00
BTL21	4542286	Intelligent Test Probe Set, w/Extenders & Temp Sensor	633.00
BTL-A	4542258	Voltage/Current Probe Adapter	41.00
BC500	4542299	AC Power Charger	123.00
BP500	4542300	Lithium-ion battery, 7.4V 3000 mAh	103.00
BT500	4561297	Probe tip, 10x replacement Probe tips, 2x long probe tip covers, 2x short probe tip covers	123.00
i410	617727	AC/DC Current Clamp (400 A)	262.00
<b>Insulation Testers</b>			
Fluke 1503	2427883	Insulation Tester	415.00
Fluke 1507	2427890	Insulation Tester	515.00
Fluke 1550C	3665021	Insulation Resistance Tester (5kV)	3976.00
Fluke 1550C/Kit	3665127	Insulation Resistance Tester Kit (5kV)	4382.00
Fluke 1550C FC w/IR3000FC	4977402	Insulation Resistance Tester (5kV) with IR3000FC	3976.00
Fluke 1550C FC Kit w/IR3000FC	4977457	Insulation Resistance Tester Kit (5kV) with IR3000FC	4382.00
Fluke 1555	3665056	Insulation Resistance Tester (10kV)	4382.00
Fluke 1555/Kit	3665111	Insulation Resistance Tester Kit (10kV)	4787.00

Model	Art. nr	Description	EUR
Fluke 1555 FC w/IR3000FC	4977519	Insulation Resistance Tester (10kV) with IR3000FC	4382.00
Fluke 1555 FC Kit w/IR3000FC	4977469	Insulation Resistance Tester Kit (10kV) with IR3000FC	4787.00
Fluke 1577	2157280	Insulation Multimeter	629.00
Fluke 1587T	2517605	Insulation Multimeter (Telecom)	734.00
Fluke 1587 FC	4691215	2-IN-1 Insulation Multimeter	787.00
Fluke 1587/MDT FC	4692716	2-IN-1 Advanced Motor & Drive Troubleshooting Kit with 9040, I400	1050.00
1587KIT/62MAX+ FC	4692778	2-IN-1 Advanced Electrical Troubleshooting Insulation Multi Kit with 62MAX+ I400	945.00
Fluke 1587/I400 FC	4692725	2-IN-1 Insulation Multimeter with Clamp i400	839.00
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	153.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	251.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	49.00

### Installation Testers

Fluke 1662 SCH	4546944	Installation Tester w/mem Schuko	999.00
Fluke 1663 SCH	4546980	Installation Tester w/RCD type B Schuko	1299.00
Fluke 1664FC SCH	4547054	FC Installation Tester w/insulation pre-test Schuko	1649.00
Fluke 166X-MTC-SCH	4601081	Fluke 166X-Main test cord, Schuko (EU)	61.00
Fluke DMS COMP	4718790	DMS Complete, Installation, PAT Software	565.00
Fluke DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	751.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	251.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	49.00
ES165X	2104706	Earth Spike Test Kit	157.00
TP165X	2107742	Remote Control Probe (1650 Series)	83.00
TL165X	2107756	Standard Test Lead Set (1650 Series)	114.00
ZERO ADAPTER	3261925	Zero adapter (165xB)	41.00

### Portable Appliance Testers

Fluke 6200-2 NL	4325052	Portable Appliance Tester NL	999.00
Fluke 6500-2 NL	4325065	Portable Appliance Tester NL	1699.00
Fluke 6500-2 NL Basic Kit	4377180	Portable Appliance Tester, Basic Kit, NL	1699.00
APP1000	1992611	Barcode Appliance Number Labels 0-1000	136.00
APP2000	1992627	Barcode Appliance Number Labels 1001-2000	136.00
AUTO200B	2141239	Auto Code Label	47.00
BDST3	2796907	Snap Tag (cable tie)	39.00
BDST4	2796918	Snap Tag (clip on)	39.00
CD-Card	4045991	Compact Flash Memory Card	40.00
Fluke DMS COMP	4718790	DMS Complete, Installation, PAT Software	565.00
Fluke DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	751.00
EXTL100	2389684	Extension Lead Test Adaptor	18.00
PASS560R	2141217	Appliance Pass Labels	83.00
SP6000 Printer	4325128	Printer for Portable Appliance Testers	629.00
SPSCAN6000	4325143	Scanner for Portable Appliance Testers	399.00

### Earth Ground Testers

Fluke 1630-2 FC	4829532	Earth Ground Loop and Leakage Clamp	1441.00
Fluke 1630-2	4829515	Earth Ground Loop and Leakage Clamp (non FC)	1441.00
Fluke 1623-2	4325155	Basic Geo Earth Ground Tester	1417.00
Fluke 1625-2	4325162	Advanced Geo Earth Ground Tester	2363.00
Fluke 1623-2 Kit	4325170	Basic Geo Earth Ground Tester, Kit	2415.00
Fluke 1625-2 Kit	4325181	Advanced Geo Earth Ground Tester, Kit	3466.00
Earth Stake	4325492	Geo Earth Ground Tester, Earth stake	65.00
Cable Reel 25M BL	4343731	25M Blue, Ground/Earth Cable Reel, 25M Wire	65.00
Cable Reel 25M GR	4343746	25M Green, Ground/Earth Cable Reel, 25M Wire	65.00
Cable Reel 50M RD	4343754	50M Red, Ground/Earth Cable Reel, 50M Wire	72.00
C1620	4359042	Carrying Case	203.00
ES-162P3-2	4359377	Earth Ground Stake Set for 3 Pole Measurement	251.00
ES-162P4-2	4359389	Earth Ground Stake Set for 4 Pole Measurement	367.00

### Indoor Air Quality Tools

Fluke 922	2679822	Airflow Meter	629.00
Fluke 922/Kit	2679831	Airflow Meter Kit	734.00
Fluke 971	2418208	Temperature Humidity Meter	251.00
Fluke 975	2519364	AirMeter	2039.00
Fluke 975V	2666111	AirMeter with Velocity	2345.00
Fluke CO-220	664711	Carbon Monoxide Meter	524.00
Fluke RLD2	3387163	Leak Detector Flashlight	52.00
CO-205	664714	Aspirator Kit	177.00
975VP	2631538	Air Velocity Probe	458.00
PT12	2740212	Pitot Tube, 12	115.00
Fluke 985	4131397	Airborne Particle Counter	4283.00

Model	Art. nr	Description	EUR
<b>Digital Thermometers</b>			
Fluke 51 II	1281142	Thermometer	329.00
Fluke 52 II	1281139	Thermometer	419.00
Fluke 53 II B	3821062	Single Input Thermometer, 60Hz	469.00
Fluke 53 II B	3821096	Single Input Thermometer, 50Hz	479.00
Fluke 54 II B	3821070	Dual Input Thermometer, 60Hz	569.00
Fluke 54 II B	3821081	Dual Input Thermometer, 50Hz	569.00
Fluke 61	1643896	Infrared Thermometer	195.00
Fluke 62 MAX	4130474	Infrared thermometer	95.00
Fluke 62 MAX+	4130488	Infrared Thermometer	105.00
T5-600/62MAX+/1AC kit	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	267.00
414D/62MAX+ Kit	4296052	Fluke Laser distance meter and IR thermometer kit	226.00
62MAX+/323/1AC Kit	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	259.00
116/62MAX+ Kit	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	432.00
Fluke 63	2148281	Infrared Thermometer	269.00
Fluke 64 MAX	4856105	Multifunction IR Thermometer 20:1 D:S	129.00
Fluke 561	2558118	Multipurpose Thermometer	195.00
Fluke 566	2837799	Multipurpose Thermometer	415.00
Fluke 568	2837806	Multipurpose Thermometer	519.00
Fluke 568Ex	4321662	Intrinsically safe Infrared Thermometer	1299.00
Fluke 572-2	4328074	Infrared Thermometer	619.00
Fluke FP	2644169	FoodPro Thermometer	125.00
Fluke FP Plus	2477950	FoodPro Plus Thermometer	209.00
C50	762823	Soft Meter Case	41.00
H6	2152040	Infrared Thermometer Holster (Fluke 63/65/68/561)	32.00
80PR-60	2148313	RTD Temperature Probe (Fluke 66/68)	74.00

<b>Visual Thermometers</b>			
Fluke VT04	4366444	Visual IR Thermometer	569.00
Fluke VT04A	4485211	Visual IR thermometer	515.00
Fluke charger VT04	4375752	Charger & adapter set VT04	45.00
Fluke Battery, VT04	4375741	Li-ion battery VT04	45.00

<b>Industrial Imaging</b>			
Fluke DS701	4962652	Diagnostic Videoscope	1699.00
Fluke DS703 FC	4962665	High Resolution Diagnostic Videoscope with FC	1999.00
Fluke 3.8mm Scope	4962690	3.8 mm Scope, 1 m Probe, Forward View	699.00
Fluke 8.5mm Scope	4962708	8.5 mm Scope, 3 m Probe, Dual View	599.00
Fluke 5.5 mm Scope	4962713	5.5 mm Scope, 1 m Probe, Dual View	499.00
Fluke 8.5 mm Scope	4962749	8.5 mm Scope, 1.2 m Probe, Dual View	199.00
Fluke 8.5 mm UV Scope	4962751	8.5 mm UV Scope, 1 m Probe, Dual View	699.00
Fluke 9 mm Scope	4962760	9 mm Scope, Forward View, 20 m Probe Reel	1999.00
Fluke DS 7XX Neckstrap	4962772	DS 7XX Neckstrap	49.00

## Thermal Imagers

<b>Thermal Imagers - Performance Series</b>			
Fluke TIS10 9Hz	4697036	Thermal imager, fixed focus	1199.00
Fluke TIS20 9Hz	4697049	Thermal imager, fixed focus	1399.00
Fluke TIS40 9Hz	4697051	Thermal imager, fixed focus	1999.00
Fluke TIS45 30Hz	4697072	Thermal imager, manual focus	2399.00
Fluke TIS45 9Hz	4697060	Thermal imager, manual focus	2399.00
Fluke TIS50 9Hz	4697085	Thermal imager, fixed focus	2699.00
Fluke TIS55 30Hz	4697106	Thermal imager, manual focus	2999.00
Fluke TIS55 9Hz	4697097	Thermal imager, manual focus	2999.00
Fluke TIS60 9Hz	4697114	Thermal imager, fixed focus	3399.00
Fluke TIS65 30Hz	4697138	Thermal imager, manual focus	3699.00
Fluke TIS65 9Hz	4697123	Thermal imager, manual focus	3699.00
Fluke TIS75 30HZ	4754443	Thermal Imager, Manual Focus	3999.00
Fluke TIS75 9HZ	4754437	Thermal Imager, Manual Focus	3999.00

<b>Thermal Imagers - Professional Series</b>			
Fluke Ti200 9Hz	4335298	Thermal Imager, 9Hz	5169.00
Fluke Ti200 60Hz	4335306	Thermal Imager, 60Hz	5169.00
Fluke Ti300 9Hz	4335314	Thermal Imager, 9Hz	5579.00
Fluke Ti300 60Hz	4335323	Thermal Imager, 60Hz	5579.00
Fluke Ti300-PRO 9 Hz	4947261	Thermal Imager, 240x180; 9 Hz	5999.00
Fluke Ti300-PRO 60 Hz	4947250	Thermal Imager, 240x180; 60 Hz	5999.00
Fluke Ti400 9Hz	4335338	Thermal Imager, 9Hz	6899.00
Fluke Ti400 60Hz	4335345	Thermal Imager, 60Hz	6899.00
Fluke Ti400-PRO 9 Hz	4947289	Thermal Imager, 320x240; 9 Hz	8149.00
Fluke Ti400-PRO 60 Hz	4947277	Thermal Imager, 320x240; 60 Hz	8149.00
Fluke TI450 9HZ	4764729	Thermal Imager, Manual Focus	8149.00
Fluke TI450 60Hz	4764707	Thermal Imager, Manual Focus	8149.00

Model	Art. nr	Description	EUR
Fluke Ti450 PRO 9HZ	4947303	Fluke Ti450 PRO 9Hz Thermal Imager	8249.00
Fluke Ti450 PRO 60HZ	4947292	Fluke Ti450 PRO 60Hz Thermal Imager	8249.00
Fluke Ti450 SF6 60Hz	4907176	SF6 Gas leak detection, Thermal Imager	15399.00
Fluke Ti480 9Hz	4842105	Thermal Imager; 640x480; 9 HZ, SR	13199.00
Fluke Ti480 60Hz	4842086	Thermal Imager; 640x480; 60 HZ, SR	13199.00
Fluke Ti480 PRO 9Hz	4947332	Fluke Ti480 PRO 9Hz Thermal Imager	13499.00
Fluke Ti480 PRO 60Hz	4947326	Fluke Ti480 PRO 60Hz Thermal Imager	13499.00

#### Thermal Imagers - Expert Series

Fluke TiX500 9Hz	4736664	Thermal Imager; 320x240; 9 HZ	8599.00
Fluke TiX500 60Hz	4736635	Thermal Imager; 320x240; 60 HZ	8599.00
Fluke TiX520 9 Hz	4596742	Thermal Imager; 320 x 240; 9 Hz	11199.00
Fluke TiX520 9Hz/NFC	4597027	Thermal Imager; 320 x 240; Non-FC; 9 Hz	11199.00
Fluke TiX520 60 Hz	4596717	Thermal Imager; 320 x 240; 60 Hz	11199.00
Fluke TiX560 9Hz	4597094	Thermal Imager; 320 x 240; IS	13199.00
Fluke TiX560 9Hz/NFC	4597100	Thermal Imager; 320 x 240; Non-FC; 9 Hz	13199.00
Fluke TiX560 60 Hz	4597066	Thermal Imager; 320 x 240; IS	13199.00
Fluke TiX580 60Hz	4842073	Thermal Imager; 640x480; 60 HZ, SR	16299.00
Fluke TiX580 9Hz	4841945	Thermal Imager; 640x480; 9 HZ, SR	16299.00
Fluke RSE300 9Hz	4948166	Thermal Imager; 320x240; 9 Hz	12099.00
Fluke RSE300 60Hz	4944776	Thermal Imager; 320x240; 60 Hz	12099.00
Fluke RSE600 9Hz	4948175	Thermal Imager; 640x480; 9 Hz	15849.00
Fluke RSE600 60Hz	4944826	Thermal Imager; 640x480; 60 Hz	15849.00

#### Thermal Imagers Accessories (general)

Ti-Visor2	3996500	Sun Visor	79.00
Ti-Visor3	4335377	Thermal imager visor	79.00
Ti-Tripod	3511872	Tripod Mounting Base	109.00
Ti-Tripod2	3996517	Mounting Base	100.00
Ti-Tripod3	4335389	Tripod mounting base accessory	99.00
FLK-LENS/TELE1	3441176	Telephoto Infrared Lens (Ti32/TiR32)	1346.00
FLK-LENS/WIDE1	3441183	Wide-angle Infrared Lens (Ti32/TiR32)	1346.00
FLK-LENS/TELE2	4335350	Telephoto Infrared Lens (Ti200/Ti300/Ti400)	1299.00
FLK-LENS/WIDE2	4335361	Wide-angle Infrared Lens (Ti200/Ti300/Ti400)	1299.00
Fluke lens/4xTELE2	4607058	4x Telephoto IR lens for TiX560-TiX520-Ti400-Ti300-Ti200	5889.00
Fluke lens/25MAC2	4607064	25Micron Macro IR lens for TiX560-TiX520	4259.00
Ti-Car Charger	3039779	Ti Car Charger (TiR/TiR1/Ti10/Ti20/Ti25)	125.00
Ti20-RBP	2577796	Rechargeable Battery Pack (Ti20)	176.00
FLK-TI-SBP3	3440365	Extra battery (Ti32/TiR32)	139.00
Fluke TI-SBC3B	4354922	Charging base (Ti200/Ti300/Ti400)	175.00
Fluke TiX5xx-Neck	4574715	Adjustable neck strap	30.00
Fluke TiX5xx-SBP4	4597142	Additional Smart Battery	129.00
Fluke TiX5xx Hand	4574703	Adjustable hand strap	15.00
Fluke TiX5xx-HDMI	4615511	HDMI video cable	20.00
Fluke TiX5x-Lens Cap	4550697	Lens cap	15.00
Fluke TI-Bluetooth	4603258	Bluetooth headset	79.00

#### Thermal Imagers IR-Windows

FLK-050-CLKT	3460346	50mm C-Range IR Windows, Kwik twist	169.00
FLK-075-CLKT	3460387	75 mm C-Range IR Window, Kwik Twist	219.00
FLK-100-CLKT	3460439	100mm C-Range IR Window, Kwik Twist	299.00
Fluke CV200	4326955	50mm IR Window, hand turn door latch	219.00
Fluke CV300	4326962	75mm IR Windows, hand turn door latch	295.00
Fluke CV301	4338164	75mm IR Windows, security turn door latch	309.00
Fluke CV400	4326996	100 mm IR Windows, hand turn door latch	409.00
Fluke CV401	4338173	100 mm IR Windows, security turn door latch	409.00

#### ScopeMeters

##### Industrial ScopeMeter

Fluke 123B/EU	4755659	Industrial ScopeMeter 20MHZ, EU	1560.00
Fluke 123B/INT	4755710	Industrial ScopeMeter 20MHZ, INT	1560.00
Fluke 124B/EU	4755731	Industrial ScopeMeter 40MHZ, EU	1872.00
Fluke 124B/INT	4755793	Industrial ScopeMeter 40MHZ, INT	1872.00
Fluke 125B/EU	4755818	Industrial ScopeMeter 40MHZ, EU	2236.00
Fluke 125B/INT	4755876	Industrial ScopeMeter 40MHZ, INT	2236.00
Fluke 123B/EU/S	4755890	Industrial ScopeMeter + SCC 20MHZ, EU	1976.00
Fluke 123B/INT/S	4755953	Industrial ScopeMeter + SCC 20MHZ, INT	1976.00
Fluke 124B/EU/S	4755975	Industrial ScopeMeter + SCC 40MHZ, EU	2288.00
Fluke 124B/INT/S	4756031	Industrial ScopeMeter + SCC 40MHZ, INT	2288.00
Fluke 125B/EU/S	4756054	Industrial ScopeMeter + SCC 40MHZ, EU	2652.00
Fluke 125B/INT/S	4756112	Industrial ScopeMeter + SCC 40MHZ, INT	2652.00

Model	Art. nr	Description	EUR
<b>190 Series ScopeMeters</b>			
Fluke 190-204/EU	3894409	ScopeMeter 4 Channel 200 MHZ Color	4577.00
Fluke 190-204/UN	3894411	ScopeMeter 4 Channel 200 MHZ Color	4581.00
Fluke 190-204/EU/S	3894475	ScopeMeter 4 Channel 200 MHZ Color SCC	4990.00
Fluke 190-204/UN/S	3894482	ScopeMeter 4 Channel 200 MHZ Color UNI SCC	4990.00
Fluke 190-104/EU	3894540	ScopeMeter 4 Channel 100 MHZ Color EU	4005.00
Fluke 190-104/UN	3894557	ScopeMeter 4 Channel 100 MHZ Color UNI	4005.00
Fluke 190-104/EU/S	3894617	ScopeMeter 4 Channel 100 MHZ Color EU SCC	4414.00
Fluke 190-104/UN/S	3894621	ScopeMeter 4 Channel 100 MHZ Color UNI SCC	4414.00
Fluke 190-062/EU	4025159	ScopeMeter 2 Channel 60 MHZ Color	2892.00
Fluke 190-062/UN	4025171	ScopeMeter 2 Channel 60MHZ Color	2892.00
Fluke 190-062/EU/S	4025230	ScopeMeter 2 Channel Color SCC	3300.00
Fluke 190-062/UN/S	4025248	ScopeMeter 2 Channel 60MHZ Color SCC	3300.00
Fluke 190-102/EU	4025318	ScopeMeter 2 Channel 100MHZ Color	3557.00
Fluke 190-102/UN	4025329	ScopeMeter 2 Channel 100MHZ Color SCC	3557.00
Fluke 190-102/EU/S	4025383	ScopeMeter 2 Channel 100MHZ Color SCC	3966.00
Fluke 190-102/UN/S	4025390	ScopeMeter 2 Channel 100MHZ Color SCC	3966.00
Fluke 190-202/EU	4025460	ScopeMeter 2 Channel 200MHZ Color	4015.00
Fluke 190-202/UN	4025472	ScopeMeter 2 Channel 200MHZ Color	4015.00
Fluke 190-202/EU/S	4025554	ScopeMeter 2 Channel 200MHZ Color SCC	4424.00
Fluke 190-202/UN/S	4025568	ScopeMeter 2 Channel 200MHZ Color SCC	4424.00
Fluke 190-502/EU	4025623	ScopeMeter 2 Channel 500 MHZ Color	4946.00
Fluke 190-502/UN	4025638	ScopeMeter 2 Channel 500 MHZColor UNI	4946.00
Fluke 190-502/EU/S	4025692	ScopeMeter 2 Channel 500 MHZ Color Europe SCC	5355.00
Fluke-190-502/UN/S	4025704	ScopeMeter 2 Channel 500 MHZ Color UNI SCC	5355.00
Fluke 190-504/EU	4419875	ScopeMeter 4 Channel 500MHz Color	5127.00
Fluke 190-504/UN	4419929	ScopeMeter 4 Channel 500MHz Color UNI	5127.00
Fluke 190-504/EU/S	4419941	ScopeMeter 4 Channel 500MHz Color Europe SCC	5535.00
Fluke 190-504/UN/S	4419990	ScopeMeter 4 Channel 500MHz Color UNI SCC	5535.00
<b>ScopeMeter Accessories</b>			
AC120	646163	Heavy Duty Alligator Clips	45.00
AS400	3894880	Probe Extension Set, for VPS400 Probes	113.00
BB120	646171	Banana to BNC Adapter Plug	52.00
BB120-II	4744369	Set of 2 banana to BNC adapter	47.00
BC190/808	1282244	Battery Charger/Line Voltage Adapter UNIVERSAL (190 Series)	192.00
BHT190	3379374	Set of Break-out Adapters	368.00
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	103.00
BP190	677390	NiMH Battery Pack (190 Series)	207.00
BP290	4025762	Battery Pack Single Cap 190-series II	245.00
BP291	3894688	Battery Pack, Fluke 190 Series	343.00
C120	646189	Hard Case (43B/120 Series)	112.00
C120B	4744391	Soft carrying case for 120B series	141.00
C125	646858	Soft Meter Case	52.00
C190	677401	Hard Case (190 Series)	263.00
C195	677408	Soft Case	244.00
C290	3894803	Hard-Shell Carrying Case	219.00
CS20MA	677393	Current Shunt 4-20 mA	101.00
EBC290	3894906	External Battery Charger	108.00
HC120	646668	Hook Clips	59.00
HC120-II	4744357	Set of 2 hook clips	52.00
HC200	2086410	Hook Clips	42.00
HH290	3894844	Hanging Hook, ScopeMeter Series 190 II	77.00
MA190	1567481	Medical Accessory Kit (190 Series)	464.00
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	167.00
PM8907/801	613999	Battery Charger/Line Voltage Adapter EUR (120 Series)	125.00
PM8907/807	624764	POWER ADAPTOR/BATTERY CHARGER	125.00
PM8907/808	614039	Battery Charger/Line Voltage Adapter UNIVERSAL (120 Series)	149.00
PM9080	1641983	Serial Interface Adapter/Cable (RS232)	277.00
PM9081	916093	Dual Banana Plug to Female BNC Adapter	53.00
PM9082	916163	Dual Banana Jack to Male BNC Adapter	53.00
PM9091	935598	Coaxial BNC Cables (1.5 m)	125.00
PM9092	935601	Coaxial BNC Cables (0.5 m)	108.00
PM9093	935593	Male BNC to Female BNC Adapter	72.00
PM9096/201	651742	Secondary Pick-up	346.00
RS120-III	4023947	Probe Accessory Replacement Set	113.00
RS400	3894867	Probe Replacement Set, for VPS400 Probes	90.00
RS500	4025886	Probe accessory replacement set for VPS500 probes	161.00
SCC120B	4744423	Software soft carry case accessory kit 120B series	520.00
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	477.00
SCC128	2100199	Automotive Accessory Kit (120 Series)	742.00
SCC198	2100208	Automotive Accessory Kit (190 Series)	933.00
SCC190	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	668.00
SCC290	3894826	Software and Carrying Case for 190 Series II	408.00
SP120B	4744414	Screen protector for 120B series	47.00

Model	Art. nr	Description	EUR
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	258.00
STL120-III	4023901	Shielded Test Lead	198.00
STL120-IV	4744340	Shielded test lead set 600V CAT IV	166.00
SW90W	3894923	FlukeView Software	369.00
TAS90	614187	Automotive Accessory Set (120/190 Series)	72.00
TRM50	4025864	50 Ohm feed-through terminator BNC	194.00
UA120	4744384	USB Connector adapter	47.00
VPS41	4744378	Voltage probe set 40 MHz 600V CAT IV	161.00
VPS101	3086317	1:1 Voltage Probe Set, black, 30 MHz, 1.2m	225.00
VPS210-G	3086247	10:1 Voltage Probe Set, grey, 200 MHz, 1.2m	225.00
VPS210-R	3086235	10:1 Voltage Probe Set, 1 red, 200 MHz, 1.2m	225.00
VPS212-G	3086286	10:1 Voltage Probe Set, grey, 200 MHz, 2.5m	225.00
VPS212-R	3086273	10:1 Voltage Probe Set, red, 200 MHz, 2.5m	225.00
VPS220-G	3086300	100:1 Voltage Probe Set, grey, 200 MHz, 1.2m	225.00
VPS220-R	3086299	100:1 Voltage Probe Set, red, 200 MHz, 1.2m	225.00
VPS40-III	4023920	Voltage Probe	131.00
VPS410-II-B	4276937	Industrial Voltage Probe Set 500 MHz 10:1 Blue	215.00
VPS410-II-G	4276943	Industrial Voltage Probe Set 500 MHz 10:1 Grey	215.00
VPS410-II-R	4276928	Industrial Voltage Probe Set 500 MHz 10:1 Red	215.00
VPS410-II-V	4276955	Industrial Voltage Probe Set 500 MHz 10:1 Green	215.00
VPS420-R	3894783	High Working Voltage Probe 100:1 Red & Black	250.00
VPS420-B	4411541	High Working Voltage Ruggedized Probe; Blue/Black	250.00
VPS420-G	4411565	High Working Voltage Ruggedized Probe; Grey/Black	250.00
VPS420-V	4411583	High Working Voltage Ruggedized Probe; Green/Black	250.00
VPS510-R	4025781	Voltage Probe set 500 MHz 10:1 Red	215.00
VPS510-B	4025796	Voltage probe set 500 MHz 10:1 Blue	215.00
VPS510-G	4025801	Voltage probe set 500 MHz 10:1 Grey	215.00
VPS510-V	4025812	Voltage probe set 500 MHz 10:1 Green	215.00

### Power Quality Tools

Fluke 345	2584181	Power Quality Clamp Meter	1604.00
Fluke 430-II/MA	4779032	430-II Motor Analyzer Upgrade Kit	2025.00
Fluke 434-II/BASIC	4116650	Power Quality and energy analyzer (w/o clamps)	4050.00
Fluke 434-II	4116638	Power Quality and energy analyzer	4679.00
Fluke 434-II/INTL	4778918	Power Quality and energy analyzer/International	4679.00
Fluke 435-II	4116661	Power Quality& Energy Analyzer	6008.00
Fluke 435-II/BASIC	4116689	Advanced Power Quality and energy analyzer (w/o clamps)	5412.00
Fluke 435-II/INTL	4778929	Power Quality and energy analyzer/International	6009.00
Fluke 437-II	4116692	Power Quality& Energy Analyzer	8312.00
Fluke 437-II/BASIC	4116719	400 Hz Power Quality and Energy Analyzer (w/o clamps)	7670.00
Fluke 437-II/INTL	4778934	Power Quality and energy analyzer/International	8312.00
Fluke 438-II	4778976	Power Quality & Motor Analyzer	7399.00
Fluke 438-II/BASIC	4778990	Power Quality & Motor Analyzer, without clamps and FC WiFi SD Card	6770.00
Fluke 438-II/INTL	4779015	Power Quality & Motor Analyzer, without FC WiFi SD Card	7399.00
Fluke 1732/EUS	4706548	Energy Logger, EU/US version	2536.00
Fluke 1732/INTL	4706553	Energy Logger, international version	2536.00
Fluke 1732/B	4706566	Energy Logger, basic version	2232.00
Fluke 1732/Upgrade	4920958	Upgrade kit for 1732 to 1734	256.00
Fluke 1734/EUS	4706594	Energy Logger, EU/US advanced version	2841.00
Fluke 1734/INTL	4706608	Energy Logger, international advanced version	2841.00
Fluke 1734/B	4706582	Energy Logger, advanced version no flexis	2536.00
Fluke 1734/WINTL	4710227	Energy Logger, wireless international	2841.00
Fluke 1736/EUS	4534519	3-Phase Power Logger, EU/US version	4059.00
Fluke 1736/B	4563561	3-Phase Power Logger, basic version	3856.00
Fluke 1736/INTL	4563550	3-Phase Power Logger, International version	4059.00
Fluke 1738/EUS	4563577	3-Phase Power Logger, EU/US Advanced version no flexis	4566.00
Fluke 1738/B	4588378	3-Phase Power Logger, advanced version no flexis	4059.00
Fluke 1738/INTL	4588384	3-Phase Power Logger, international advanced version	4566.00
Fluke 1742/15/EUS	4920613	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	3547.00
Fluke 1742/30/EUS	4920651	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	3547.00
Fluke 1742/B/EUS	4920660	Power Quality Logger without iFlex, EUS version	3243.00
Fluke 1742/15/INTL	4920672	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	3547.00
Fluke 1742/30/INTL	4920685	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	3547.00
Fluke 1742/B/INTL	4920697	Power Quality Logger without iFlex, INTL version	3243.00
1742-6/Upgrade	4920964	1742 to 1746 Upgrade	1735.00
1742-8/Upgrade	4920973	1742 to 1748 Upgrade	3209.00
Fluke 1746/15/EUS	4920703	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	4867.00
Fluke 1746/30/EUS	4920715	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	4867.00
Fluke 1746/B/EUS	4920726	Power Quality Logger without iFlex, EUS version	4562.00
Fluke 1746/15/INTL	4920732	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	4867.00
Fluke 1746/30/INTL	4920744	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	4867.00
Fluke 1746/B/INTL	4920759	Power Quality Logger without iFlex, INTL version	4562.00
1746-8/Upgrade	4920986	1746 to 1748 Upgrade	1735.00
Fluke 1748/15/EUS	4920767	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	6085.00



Model	Art. nr	Description	EUR
Fluke 1748/30/EUS	4920771	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	6085.00
Fluke 1748/B/EUS	4920780	Power Quality Logger without iFlex, EUS version	5780.00
Fluke 1748/15/INTL	4920798	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	6085.00
Fluke 1748/30/INTL	4920800	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	6085.00
Fluke 1748/B/INTL	4920817	Power Quality Logger without iFlex, INTL version	5780.00
Fluke 1760 Basic	2630732	Power Quality Recorder (three-phase), Topas	11791.00
Fluke 1760	2630744	Power Quality Recorder (three-phase), Topas	13662.00
Fluke 1760TR Basic	2637629	Power Quality Recorder (three-phase), Topas	16158.00
Fluke 1760TR	2637634	Power Quality Recorder (three-phase), Topas	18026.00
Fluke VR1710	3030923	Single-Phase Voltage Quality Recorder	870.00
C1740	4116762	Softcase for 174X and 43X-II PQ analyzer	205.00
C437-II	4116743	Hard case 430 Series II with rollers	495.00
EPE-Training-E/EMEA	4792349	Fluke EPE Training Set - English	199.00
Fluke-435-II/EPE-E	4816735	Fluke-435-II, PQ and Energy Analyzer plus EPE training - English	6020.00

Power Quality Tools Accessories			
1743/1744 Poleset	3024485	Pole Mounting Kit (Fluke 1743/1744)	41.00
3140R	2650136	Clip-on Current Transformer 2A-400A (Fluke 1750)	399.00
3210-PR-TF-II	4531769	1000A Fluke 1750 Thin flexi 61cm	620.00
3310-PR-TF-II	4531778	5000A Fluke 1750 Thin flexi 61cm	827.00
3PHVL-1730	4344712	Cable Assembly, Voltage Test Lead 3-Phase+N (1730)	84.00
3312-PR-TF-II	4531784	5000A Fluke 1750 Thin flexi 122cm	1019.00
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	103.00
BE345	2839604	Battery Eliminator (Fluke 345)	153.00
BP1730	4389436	Li Ion Battery Pack 3.7V 2500mAh (1730)	40.00
C120	646189	Hard Case (43B/120 Series)	112.00
C17xx	4637381	Soft Case	116.00
CS1750	2673962	Soft Case (Fluke 1750/1760)	254.00
1730 Hanger	4358028	Hanger kit (1730)	56.00
1730 Cable	4395217	Cable,AUX input cable (1730)	29.00
1750/Case	2650124	Hard Case (Fluke 1750)	547.00
FLUKE-1736/UPGRADE	4563589	UPGRADE KIT FOR 1736 TO 1738	799.00
1750/Seat-L	2673937	Fluke Power Analyze - Additional SEAT LICENSE	1083.00
1750/Site-L	2673928	Fluke Power Analyze - Additional SITE LICENCE	5418.00
FS17X5-TF-II	4531791	3000A 4-PH Fluke 1735 & 1745 Thin flexi set	1595.00
FS17XX IP65-TF-II	4531804	3000A IP65 4-PH Fluke 1743/4 Thin flexi set	1771.00
FS17XX-1PH-TF-II	4531819	FS3000A/6000A 4-PH 36-Inch Thin flexi set	399.00
FLUKE-173X ADPT	4717827	AUX input adapter, 173X	133.00
Fluke 17xx TL 0.1M	4715389	Test lead set for Fluke 173x; 0.1m	40.00
Fluke 17xx TL 1.5M	4715392	Test lead set for Fluke 173x; 1.5m	30.00
FS3000/6000A-TF-4-II	4531828	FS3000A/6000A 4-PH 36-Inch thin flexi set	1591.00
GPS430-II	4693803	GPS Synchronization module (430-II series)	1529.00
GPS-Time Sync	2539223	GPS Time Synchronization Module (Fluke 1760)	425.00
i17XX-flex1500	4637328	Fluke-17xx iFlexi 1500A 12 IN	164.00
i17XX-flex3000	4637343	Fluke-17xx iFlexi 3000A 24 IN	175.00
i17XX-flex6000	4637362	Fluke-17xx iFlexi 6000A 36 IN	186.00
i17XX-flex1500/3pk	4637337	Fluke-17xx iFlexi 1500A 12 IN, 3 pack	475.00
i17XX-flex3000/3pk	4637355	Fluke-17xx iFlexi 3000A 24 IN, 3 pack	506.00
i17XX-flex6000/3pk	4637370	Fluke-17xx iFlexi 6000A 36 IN, 3 pack	537.00
i17XX-Flex1500/4PK	4637411	Fluke-17xx iFlexi 1500A 12 IN, 4 Pack	620.00
i17XX-Flex3000/4PK	4637427	Fluke-17xx iFlexi 3000A 24 IN, 4 Pack	662.00
i17XX-Flex6000/4PK	4637430	Fluke-17xx iFlexi 6000A 36 IN, 4 Pack	703.00
i1A/10A Clamp PQ1	3345753	1-phase Mini Current Clamp Set	466.00
i1A/10A Clamp PQ3	3024413	3-phase Mini Current Clamp Set	535.00
i1A/10A Clamp PQ4	3024424	4-phase Mini Current Clamp Set	720.00
i5A/50A Clamp PQ1	3345766	1-Phase 5A/50A Mini Current Clamp set for PQ	466.00
i5A/50A Clamp PQ3	3024436	3-phase Mini Current Clamp Set	535.00
i5A/50A Clamp PQ4	3024449	4-phase Mini Current Clamp Set	720.00
i20/200A Clamp PQ3	3024451	3-phase Mini Current Clamp Set	535.00
i20/200A Clamp PQ4	3024460	4-phase Mini Current Clamp Set	720.00
i40S-EL	4637396	Fluke-17xx i40s-EL Clamp-on Current Transformer	206.00
i40S-EL/3pk	4637409	Fluke-17xxx i40s-EL Clamp-on Current Transformer, 3 pack	589.00
i400	2277225	AC Current Clamp (400 A)	157.00
i400s	2277202	AC Current Clamp (400A)	282.00
i430-Flexi-TF-II	4531725	6000A Fluke 430 Thin Flexi 61cm	402.00
i430-Flexi-TF-II-4PK	4531733	6000A Fluke 430 Thin Flexi 61cm 4 Pack	1224.00
i5s	2508467	AC Current Clamp (5 A)	524.00
i5S-PR	3949761	1750, 5A Current Clamp	320.00
i5sPQ3	2457508	AC Current Clamp (5 A), 3-pack	1260.00
IEEE519/REPORT	4589748	SOFTWARE LICENSE FOR IEEE519 REPORTING	517.00
MP1-Magnet Probe 1	4589220	Magnet probes for 4 mm banana, set of 4	92.00
MBX USB-RS232	2539565	EPO328Z, USB to Serial RS232 Adapter	46.00
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	167.00
PM9080	1641983	Serial Interface Adapter/Cable (RS232)	277.00
TLS430	2157713	Test Leads and Alligator Clips (4 black, 1 green) - 430 Series	126.00

Model	Art. nr	Description	EUR
TPS Clamp 10A/1A	2540445	Clip-on Current Transformer 10A/1A (Fluke 1760)	387.00
TPS Clamp 50A/5A	2540461	Clip-on Current Transformer 50A/5A (Fluke 1760)	387.00
TPS Clamp 200A/20A	2540450	Clip-on Current Transformer 200A/20A (Fluke 1760)	387.00
TPS Flex 18-TF-II	4531837	100/500A Fluke 1760 Thin Flexi 45cm (18in)	454.00
TPS Flex 24-TF-II	4531843	200/1000A Fluke 1760 Thin Flexi 61cm (24in)	454.00
TPS Flex 36-TF-II	4531855	3000/6000A Fluke 1760 Thin Flexi 91cm (36in)	891.00
TPS/MBX Dolph red	2540744	EPO326Z, Dolphin Clip, Red	21.00
TPS Nullmodem Cable	2540511	A550500510, RS232 Cross Link Cable, 3M	39.00
TPS Shunt 1A	2540548	A680501054, Shunt 1 A AC/DC	315.00
TPS Shunt 20MA	2540553	Shunt 20mA AC/DC (Fluke 1760)	325.00
TPS Voltprobe 10V	2540636	Voltage Probe 10V (Fluke 1760)	305.00
TPS Voltprobe 100V	2540624	Voltage Probe 100V (Fluke 1760)	305.00
TPS Voltprobe 400V	2540660	Voltage Probe 400V (Fluke 1760)	309.00
TPS Voltprobe 600V	2540697	Voltage Probe 600V (Fluke 1760)	309.00
TPS Voltprobe 1KV	2540649	Voltage Probe 1000V (Fluke 1760)	490.00
VL1735/45	3276205	Banana 4-Phase Voltage Lead set for Fluke-1735/45	243.00
Fluke MA-C8	4945842	Wall outlet adapter, Fluke-174X	21.00
IP65 Adapter Set	4946241	IP65 rated Voltage Connector	214.00
3PHVL-1730-5M	4920999	Cable assembly, voltage est lead 3-phase+N 5m	111.00
I17XX-FLEX1.5KIP	4921003	IP65 iFlexi 1.5KA 60 cm	214.00
I17XX-FLEX1.5KIP/3PK	4921015	IP65 iFlexi 1.5KA 60 cm, 3 Pack	513.00
I17XX-FLEX1.5KIP/4PK	4921026	IP65 iFlexi 1.5KA 60 cm, 4 Pack	684.00
I17XX-FLEX3KIPK	4921032	IP65 iFlexi 3KA 60 cm	214.00
I17XX-FLEX3KIP/3PK	4921044	IP65 iFlexi 3KA 60 cm, 3 Pack	513.00
I17XX-FLEX3KIP/4PK	4921067	IP65 iFlexi 3KA 60 cm, 4 Pack	684.00
I17XX-FLEX6KIPK	4921071	IP65 iFlexi 6KA 90 cm	256.00
I17XX-FLEX6KIP/3PK	4921080	iFlexi 6KA 90 cm, 3 Pack	598.00
I17XX-FLEX6KIP/4PK	4921098	iFlexi 6KA 90 cm, 4 Pack	769.00
I17XX-FLEX5M-EXT	4921116	iFlexi Extension Cable, 5m	128.00
Fluke 17XX-TL 0.18M	4921125	Test lead set; 1000V CAT III, Non-stack conn; 0.18 m; Red/Blk	34.00
Fluke 174X_3541-HANGER	4890129	Hanger Kit	61.00
Fluke 174X GPS-REC	4921133	GPS Receiver Antenna	329.00
F17XX Cable Markers	4921140	Cable Marker set, 05MM	51.00
MP1-3R/1B	4944790	3 red/1 black Magnet probe for 4 mm banana	85.00

### Vibration Testers

Fluke 805	4094385	Vibration Meter	1749.00
Fluke 805 FC	4489229	Vibration Meter with Fluke Connect	1749.00
Fluke 805/ES	4636786	External Vibration Sensor	1039.00
Fluke 810	3542635	Vibration Tester	9383.00
Fluke 820-2	4550041	LED Stroboscope	889.00
Fluke 830	4454396	Laser Alignment Tool	7099.00
Fluke 830/Magnet	4528249	Magnetic Bracket	835.00
Fluke 830/Shims	4551330	Laser Alignment Tool, Shims	835.00
810S	3530828	Sensor	1417.00
810QDC	3530837	Quick Disconnect Cable	148.00
810SMM	3530862	Sensor Magnet Mount	208.00
810SMP	3530855	Sensor Mounting Pads (10-pack)	28.00
SBP-810	3530843	Smart Battery Pack	264.00
Fluke-810PA	3986002	AC Power Adapter with International Plug Set	85.00

### Process Calibrators

#### 700 Series Process Calibrators

Fluke 154 INTL	4805625	HART Calibration Assistant	3769.00
Fluke 705	665091	Loop Calibrator	759.00
Fluke 707	1617262	Loop Calibrator	873.00
Fluke 707Ex	2032187	Intrinsically Safe Loop Calibrator	1227.00
Fluke 709	4234350	Precision Loop Calibrator	866.00
Fluke 709H	4234361	Precision HART Loop Calibrator	1393.00
Fluke 712B	4387857	RTD Temperature Calibrator	1075.00
Fluke 714B	4387869	TC Temperature Calibrator	1100.00
Fluke 715	620101	Volt/mA Calibrator	1237.00
Fluke 717 1G	2547166	Pressure Calibrator (68.9 mbar)	1405.00
Fluke 717-15G	4058808	Pressure Calibrator (1 bar)	1405.00
Fluke 717 100G	1630430	Pressure Calibrator (7 bar)	1405.00
Fluke 717 30G	662897	Pressure Calibrator (2 bar)	1457.00
Fluke 717 300G	2547175	Pressure Calibrator (20 bar)	1405.00
Fluke 717 500G	2547182	Pressure Calibrator (34.7 bar)	1405.00
Fluke 717 1000G	2547194	Pressure Calibrator (69 bar)	1405.00
Fluke 717 1500G	2547203	Pressure Calibrator (103.4 bar)	1556.00
Fluke 717 3000G	2547215	Pressure Calibrator (207 bar)	1556.00
Fluke 717 5000G	2547232	Pressure Calibrator (345 bar)	1556.00
Fluke 717-10000G	4058813	Pressure Calibrator (690 bar)	1556.00

Model	Art. nr	Description	EUR
Fluke 718 30G	665075	Pressure Calibrator (2 bar)	2644.00
Fluke 718 1G	2547148	Pressure Calibrator (68.9 mbar)	2754.00
Fluke 718 100G	665080	Pressure Calibrator (7 bar)	2644.00
Fluke 718 300G	2547153	Pressure Calibrator (20 bar)	2746.00
Fluke 718Ex 30G	2096310	Intrinsically Safe Pressure Calibrator (2 bar)	3401.00
Fluke 718Ex 100G	2096322	Intrinsically Safe Pressure Calibrator (7 bar)	3401.00
Fluke 718Ex 300G	3023328	Intrinsically Safe Pressure Calibrator (20 bar)	3401.00
Fluke 719 30G	3315332	Electric Pressure Calibrator (2 bar)	3506.00
Fluke 719 100G	3315344	Electric Pressure Calibrator (7 bar)	3506.00
Fluke-719PRO 30G	4353218	Electric Pressure Calibrator, 2 bar	2915.00
Fluke-719PRO 150G	4353229	Electric Pressure Calibrator, 10 bar	2915.00
Fluke-719PRO 300G	4353234	Electric Pressure Calibrator, 20 bar	2915.00
Fluke 720URTD	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	162.00
Fluke-721-1601	4353241	Dual Sensor Pressure Calibrator, 1.1 bar, 6.9 bar	1974.00
Fluke-721-1603	4353283	Dual Sensor Pressure Calibrator, 1.1 bar, 20 bar	1974.00
Fluke-721-1605	4353327	Dual Sensor Pressure Calibrator, 1.1 bar, 34 bar	1974.00
Fluke-721-1610	4353366	Dual Sensor Pressure Calibrator, 1.1 bar, 69 bar	1974.00
Fluke-721-1615	4353401	Dual Sensor Pressure Calibrator, 1.1 bar, 103 bar	1974.00
Fluke-721-1630	4353447	Dual Sensor Pressure Calibrator, 1.1 bar, 200 bar	1974.00
Fluke-721-1650	4353486	Dual Sensor Pressure Calibrator, 1.1 bar, 345 bar	1974.00
Fluke-721-3601	4353252	Dual Sensor Pressure Calibrator, 2.48 bar, 6.9 bar	1974.00
Fluke-721-3603	4353290	Dual Sensor Pressure Calibrator, 2.48 bar, 20 bar	1974.00
Fluke-721-3605	4353330	Dual Sensor Pressure Calibrator, 2.48 bar, 34 bar	1974.00
Fluke-721-3610	4353375	Dual Sensor Pressure Calibrator, 2.48 bar, 69 bar	1974.00
Fluke-721-3615	4353412	Dual Sensor Pressure Calibrator, 2.48 bar, 103 bar	1974.00
Fluke-721-3630	4353458	Dual Sensor Pressure Calibrator, 2.48 bar, 200 bar	1974.00
Fluke-721-3650	4353499	Dual Sensor Pressure Calibrator, 2.48 bar, 345 bar	1974.00
Fluke 721EX-1601	4353265	Dual Sensor Pressure Calibrator, 16, 100 PSIG	2580.00
Fluke 721EX-1603	4353309	Dual Sensor Pressure Calibrator, 16, 300 PSIG	2580.00
Fluke 721EX-1605	4353348	Dual Sensor Pressure Calibrator, 16, 500 PSIG	2580.00
Fluke 721EX-1610	4353382	Dual Sensor Pressure Calibrator, 16, 1000 PSIG	2580.00
Fluke 721EX-1615	4353420	Dual Sensor Pressure Calibrator, 16, 1500 PSIG	2580.00
Fluke 721EX-1630	4353464	Dual Sensor Pressure Calibrator, 16, 3000 PSIG	2580.00
Fluke 721EX-1650	4353506	Dual Sensor Pressure Calibrator, 16, 5000 PSIG	2580.00
Fluke 721EX-3601	4353276	Dual Sensor Pressure Calibrator, 36, 100 PSIG	2580.00
Fluke 721EX-3603	4353311	Dual Sensor Pressure Calibrator, 36, 300 PSIG	2580.00
Fluke 721EX-3605	4353353	Dual Sensor Pressure Calibrator, 36, 500 PSIG	2580.00
Fluke 721EX-3610	4353394	Dual Sensor Pressure Calibrator, 36, 1000 PSIG	2580.00
Fluke 721EX-3615	4353435	Dual Sensor Pressure Calibrator, 36, 1500 PSIG	2580.00
Fluke 721EX-3630	4353473	Dual Sensor Pressure Calibrator, 36, 3000 PSIG	2580.00
Fluke 721EX-3650	4353514	Dual Sensor Pressure Calibrator, 36, 5000 PSIG	2580.00
Fluke 724	1553041	Temperature Calibrator	2308.00
Fluke 725	664133	Multifunction Process Calibrator	3224.00
Fluke 725Ex	2098179	Intrinsically Safe Multifunction Process Calibrator	3942.00
Fluke 726	2452080	Precision Multifunction Process Calibrator	3692.00
Fluke 729 30G FC	4856907	Automatic Pressure Calibrator, w/FC (2 Bar)	8359.00
Fluke 729 150G FC	4856894	Automatic Pressure Calibrator, w/FC (10 Bar)	8359.00
Fluke 729 300G FC	4856882	Automatic Pressure Calibrator, w/FC (20 Bar)	8359.00
Fluke 729 30G	4856990	Automatic Pressure Calibrator (2 Bar)	8155.00
Fluke 729 150G	4856983	Automatic Pressure Calibrator (10 Bar)	8155.00
Fluke 729 300G	4856976	Automatic Pressure Calibrator (20 Bar)	8155.00
Fluke 753 EU	4411027	Documenting Process Calibrator	5325.00
Fluke 754 EU	4400387	Documenting Process Calibrator	6710.00
Fluke 771	2646347	Milliamp Process Clamp Meter	551.00
Fluke 772	3362352	Milliamp Process Clamp Meter	749.00
Fluke 773	3362365	Milliamp Process Clamp Meter	1049.00
Fluke 787B	4777186	Process Meter	1009.00
Fluke 789/E	3977194	Process Meter	1133.00
Fluke 789/IR3000FC	4604605	Process Meter and FC connector	1098.00

#### Pressure Modules

Fluke-700G01	4353523	Pressure Gauge, -10" to 10" WC (27 mbar)	735.00
Fluke-700G02	4353538	Pressure Gauge, -30" to 30" WC (69 mbar)	735.00
700G04	4096972	Pressure Gauge, +/- 1 bar	749.00
700G05	4097514	Pressure Gauge, 2 bar	749.00
700G06	4097538	Pressure Gauge, 6.9 bar	749.00
700G07	4097561	Pressure Gauge, 34 bar	749.00
700G08	4097592	Pressure Gauge, 69 bar	749.00
700G27	4097545	Pressure Gauge, 20 bar	749.00
700G29	4097605	Pressure Gauge, 200 bar	758.00
700G30	4097610	Pressure Gauge, 345 bar	758.00
700G31	4097622	Pressure Gauge, 690 bar	758.00
Fluke-700GA4	4353545	Pressure Gauge, 1 bar absolute	735.00
Fluke-700GA5	4353550	Pressure Gauge, 2 bar absolute	735.00
Fluke-700GA6	4353561	Pressure Gauge, 6.9 bar absolute	735.00

Model	Art. nr	Description	EUR
Fluke-700GA27	4353577	Pressure Gauge, 20 bar absolute	735.00
700HTPK	4124358	Hydraulic Test Pump Kit, 0 to 690 bar	1143.00
Fluke 700HTPK2	4623314	Premium hydraulic test pump kit	1497.00
Fluke 700MTH	4623345	Premium metric pressure test hose	551.00
Fluke 700M20TH	4623338	Premium M20 pressure test hose	551.00
700PCK	100062	Pressure Module Calibration Kit	1374.00
Fluke 700PTPK	4124364	Pneumatic Test Pump Kit, 0 to 41 bar	599.00
Fluke 700PTPK2	4623306	Premium pneumatic test pump kit	1383.00
700G/TRACK	4123225	Data Logging Cable & Software	419.00
Fluke-700RG05	4353589	Pressure Gauge, Reference, +2 bar	775.00
Fluke-700RG06	4353592	Pressure Gauge, Reference, 6.9 bar	775.00
Fluke-700RG07	4353605	Pressure Gauge, Reference, 34 bar	775.00
Fluke-700RG08	4353610	Pressure Gauge, Reference, 69 bar	775.00
Fluke-700G10	4353654	Pressure Gauge, 140 bar	735.00
Fluke-700RG29	4353622	Pressure Gauge, Reference, 200 bar	840.00
Fluke-700RG30	4353631	Pressure Gauge, Reference, 345 bar	840.00
Fluke-700RG31	4353646	Pressure Gauge, Reference, 690 bar	840.00
Fluke 700TTH5K	4623323	Premium pressure transmitter test hose	551.00
Fluke 700TTH10K	4636393	Premium pressure transmitter test hose kit, 10K	655.00
750P00	4352270	Pressure Module (0 - 2.5 mbar)	1608.00
750P01	4352281	Pressure Module (0 - 25 mbar)	1242.00
750P02	4352750	Pressure Module (0 - 70 mbar)	1242.00
750P22	4352296	Pressure Module (0 - 70 mbar)	1242.00
750P03	4352738	Pressure Module (0 - 350 mbar)	1242.00
750P23	4352308	Pressure Module (0 - 350 mbar)	1242.00
750P04	4352313	Pressure Module (0 - 1 bar)	1242.00
750P24	4352324	Pressure Module (0 - 1 bar)	1242.00
750P05	4352336	Pressure Module (0 - 2 bar)	1242.00
750P06	4352349	Pressure Module (0 - 7 bar)	1242.00
750P27	4352351	Pressure Module (0 - 20 bar)	1242.00
750P07	4352360	Pressure Module (0 - 35 bar)	1242.00
750P08	4352372	Pressure Module (0 - 70 bar)	1242.00
750P09	4352385	Pressure Module (0 - 100 bar)	1242.00
750P2000	4352397	Pressure Module (0 - 140 bar)	1242.00
750P29	4352403	Pressure Module (0 - 200 bar)	1971.00
750P30	4352415	Pressure Module (0 - 340 bar)	1971.00
750P31	4352426	Pressure Module (0 - 700 bar)	1971.00
750PA3	4352432	Pressure Module (0 - 350 mbar)	1429.00
750PA4	4352444	Pressure Module (0 - 1 bar)	1429.00
750PA5	4352459	Pressure Module (0 - 2 bar)	1429.00
750PA6	4352467	Pressure Module (0 - 7 bar)	1429.00
750PA27	4352471	Pressure Module (0 - 20 bar)	1429.00
750PA7	4352480	Pressure Module (0 - 35 bar)	1429.00
750PA8	4352498	Pressure Module (0 - 70 bar)	1401.00
750PA9	4352500	Pressure Module (0 - 100 bar)	1401.00
750PV3	4352517	Pressure Module (-350 mbar)	1401.00
750PV4	4352521	Pressure Module (-1 bar)	1401.00
750PD2	4352539	Pressure Module (-70 - 70 mbar)	1401.00
750PD3	4352542	Pressure Module (-350 - 350 mbar)	1401.00
750PD10	4352556	Pressure Module (-700 - 700 mbar)	1401.00
750PD4	4352563	Pressure Module (-1 - 1 bar)	1401.00
750PD5	4352574	Pressure Module (-1 - 2 bar)	1401.00
750PD50	4352588	Pressure Module (-1 - 3.5 bar)	1401.00
750PD6	4352595	Pressure Module (-1 - 7 bar)	1401.00
750PD7	4352602	Pressure Module (-1 - 14 bar)	1401.00
750PD27	4352616	Pressure Module (-1 - 20 bar)	1401.00
750R04	4352625	Pressure Module (0 - 1 bar)	1401.00
750R06	4352633	Pressure Module (0 - 7 bar)	1401.00
750R27	4352640	Pressure Module (0 - 20 bar)	1401.00
750R07	4352657	Pressure Module (0 - 35 bar)	1401.00
750R08	4352669	Pressure Module (0 - 70 bar)	1401.00
750R29	4352678	Pressure Module (0 - 200 bar)	2104.00
750R30	4352684	Pressure Module (0 - 340 bar)	2104.00
750R31	4352691	Pressure Module (0 - 700 bar)	2104.00
750RD5	4352706	Pressure Module (-1 - 2 bar)	1575.00
750RD6	4352714	Pressure Module (-1 - 7 bar)	1575.00
750RD27	4352723	Pressure Module (-0.8 - 20 bar)	1575.00
750P01Ex	4558658	Ex Pressure Module (0 - 25 mbar)	2400.00
750P24Ex	4558686	Ex Pressure Module (0 - 1 bar)	2400.00
750P05Ex	4558664	Ex Pressure Module (0 - 2 bar)	2400.00
750P06Ex	4558673	Ex Pressure Module (0 - 7 bar)	2400.00
750P27Ex	4558699	Ex Pressure Module (0 - 20 bar)	2400.00
750P09Ex	4558725	Ex Pressure Module (0 - 100 bar)	2400.00
750P29Ex	4558702	Ex Pressure Module (0 - 200 bar)	4100.00
750PA4Ex	4558716	Ex Pressure Module (0 - 1 bar)	2600.00

Model	Art. nr	Description	EUR
<b>Process Calibrator Accessories</b>			
700HTH-1	2811795	Hydraulic Test Hose	918.00
700ILF	1566730	In-Line Filter	105.00
700LTP-1	2811763	Low Pressure Test Pump	980.00
700-IV	202561	Current Shunt	485.00
700PMP	617131	Pressure Pump (10 bar)	685.00
700PRV-1	2811808	Pressure Relief Valve for 700HTP	1104.00
700PTP-1	2811774	Pneumatic Test Pump	882.00
700SC	667425	Serial Interface Cable (Fluke 725/725Ex/726)	232.00
700TC1	620119	Thermocouple Plug Kits (10 types)	141.00
700TC2	620127	Thermocouple Plug Kits (5 types)	116.00
Fluke 720RTD	4366669	RTD Probe for 721, 721Ex and 719PRO	260.00
787CAL 230	662996	Calibration Module (Fluke 787)	1134.00
BC7217	668217	Battery Charger	314.00
BE9005 240	946652	Battery Eliminator	167.00
BP7235	668225	NiMH Battery Pack	249.00
C700	606928	Hard Case (700 Series)	349.00
C789	946694	Soft Meter Case	191.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	251.00
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	153.00
Fluke 700HTP-2	4096855	Hydraulic Test Pump, 690 bar	1126.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	49.00
BP7240	4022220	753/754 Spare Battery	171.00
Fluke 750SW	4090343	DPC/TRACK2-software	3365.00
BC7240	4022655	Battery Charger (753/754)	46.00
HART Drywell Cable	2111088	Cable Kit, HART Drywellcontrol	162.00
Fluke-71x	3345825	Hose kit	102.00
Fluke 700TLK	3829398	Process Test Lead Kit	138.00
Fluke 709H/TRACK	4281225	Logging software with cable	445.00
Fluke 720URTD	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	162.00

## General Accessories

<b>Test Leads, Probes and Clips</b>			
80K-15	618113	Probe, Electronic Air Cleaner	287.00
AC175	4101772	Threaded Alligator Clip Set	29.00
AC220	1610103	SureGrip Alligator Clip Set	46.00
AC280	1610115	SureGrip Hook Clip Set	36.00
AC283	1610144	SureGrip Pincer Clip Set	41.00
AC285	1610159	SureGrip Alligator Clip Set	23.00
AC285-FTP	4073928	Alligator Clips and adaptors (FTP-1, FTPL-1)	27.00
AC288	4617784	SureGrip™ Terminal block probe	36.00
AC87	1278079	Heavy Duty Bus Bar Clip Set	48.00
AC89	873448	Heavy Duty Insulation Piercing Test Clip	53.00
BP980	1616807	Dual Banana Plug Kit	54.00
FTL660	2280204	Fused Test Lead Set	62.00
FTP-1	3869437	Fuse test probe set	94.00
FTPL-1	3869443	Fuse test probe set with test leads	104.00
H900	1616818	Test Lead Holder	32.00
Leadwrap	4083525	Durable Nylon Hook and Loop Fastener, 3 pack	9.00
T5-Kit	3971169	T5 Tester Accessory Starter Kit	52.00
T5-RLS	4089137	Replacement Test Lead Set (T5)	23.00
TL175	3521976	Twist Guard Test Leads	29.00
TL175E	3565554	Twist Guard Test Leads, 4mm	31.00
TL220-1	3971178	SureGrip Industrial Test Lead Set	79.00
TL221	2003602	SureGrip Extension Lead Set	35.00
TL222	2003616	SureGrip Silicone Test Lead Set	35.00
TL223-1	3971184	SureGrip Electrical Test Lead Set	72.00
TL224	1610198	SureGrip Silicone Test Lead Set	31.00
TL225-1	3971191	Stray Voltage Eliminator test Lead Set	105.00
TL238	2132831	SureGrip High Energy Test Lead Kit	79.00
TL27	668571	Heavy Duty Test Lead Set	36.00
TL40	1590606	Retractable Tip Test Lead Set	52.00
TL71-1	3971207	TL71, Test Lead Set	29.00
TL75-1	3971218	TL75, Test Lead Set	24.00
TL76	2032684	All-in-one Test Lead Set	41.00
TL80A-1	3971229	TL80A, Test Lead Set	75.00
TL81A	1277073	Deluxe Electronic Test Lead Kit	157.00
TL910	1616632	Electronic Test Lead Set (with replacement tips)	72.00
TL930	1616671	Patch Cords (60 cm)	18.00
TL932	1616680	Patch Cords (90 cm)	20.00
TL935	1616698	Patch Cord Kit (60, 90, 120 cm)	60.00
TL940	1616705	Mini-Hook Test Lead Set	20.00
TL950	1616710	Mini-Pincer Test Lead Set	36.00

Model	Art. nr	Description	EUR
TL960	1616722	Micro-Hook Test Lead Set	20.00
TL970	1616793	Hook and Pincer Test Lead Kit	75.00
TLK1550-RTLCL	4112351	Integral test lead & 10 kV clamp	228.00
TLK220	2097022	SureGrip Accessory Kit	146.00
TLK-225	3971234	TLK225, SureGrip Master Set	157.00
TLK281-1	3971241	TLK281, Automotive Test Lead Kit	139.00
TLK-282-1	3971252	TLK282, DeLuxe Automotive Test Lead Kit	177.00
TLK287	3045631	Electronic Master Test Lead Kit	167.00
TLK289	3092521	Industrial Master Test Lead Kit	167.00
TLK290	2435092	Test Probe Kit	62.00
TLK291	2435108	Fused Test Probe Set	62.00
TP1-1	3971265	TP1, Test Probes	18.00
TP175	3521983	TwistGuard test Probes, 2MM dia probe tips	20.00
TP175E	3565568	TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters	22.00
TP2-1	3971283	TP2, Test Probes	20.00
TP220-1	3971276	TP220, SureGrip Test Probes	20.00
TP38	1541636	Slim Reach Test Probe Set (insulated)	18.00
TP74	1541649	Lantern Tip Test Probe Set	20.00
TP80	873455	Electronic Test Probe Set	39.00
TP912	1616644	Replacement tips for TL910	36.00
TP920	1616659	Test Probe Adapter Kit	52.00
<b>Current Clamps</b>			
80i-110s	114519	AC/DC Current Clamp (100 A)	779.00
i1000s	1568487	AC Current Clamp (1000 A)	629.00
i1010	617735	AC/DC Current Clamp (1000 A)	451.00
i1010 Kit	2096998	AC/DC Current Clamp (1000 A) with Soft Case	461.00
i200	664755	AC Current Clamp (200 A)	157.00
i2000 flex	2584912	AC Flexible Current Clamp (2000 A)	314.00
i200s	664760	AC Current Clamp (200 A)	262.00
i30	2584920	AC/DC Current Clamp (30A)	419.00
i3000 flex-4PK	2696367	AC Flexible Current Clamp (3000 A), 4-pack	1260.00
i3000s	657202	AC Current Clamp (3000 A)	756.00
i3000s flex-24	2584888	AC Flexible Current Clamp (3000 A), 610 mm	482.00
i3000s flex-36	2584901	AC Flexible Current Clamp (3000 A), 915 mm	577.00
i30s	2584935	AC/DC Current Clamp (30A)	577.00
i310s	2840309	AC/DC Current Clamp (300A)	346.00
i400	2277225	AC Current Clamp (400 A)	157.00
i400s	2277202	AC Current Clamp (400A)	282.00
I40S-PR (1750)	3949777	40A Current Clamp (1750)	379.00
i410	617727	AC/DC Current Clamp (400 A)	262.00
i410 Kit	2097005	AC/DC Current Clamp (400 A) with Soft Case	304.00
i6000s flex-24	2840311	AC Current Clamp (6000 A)	629.00
i6000s flex-36	2840327	AC Current Clamp (6000 A)	734.00
i800	2840283	AC Current Clamp (800 A)	226.00
<b>Temperature Accessories</b>			
80AK-A	2747812	Thermocouple Adapter	33.00
80BK-A	2747801	Integrated DMM Temperature Probe (Type K)	37.00
80CJ-M	833046	Male Mini Connectors (Type J)	25.00
80CK-M	779942	Male Mini Connectors (Type K)	25.00
80PJ-1	1288191	Bead Probe (Type J)	27.00
80PJ-9	1288218	General Purpose Probe (Type J)	68.00
80PJ-EXT	1288234	Extension Wire Kit (Type J)	61.00
80PK-1	750422	Bead Probe (Type K)	35.00
80PK-10	3439199	Pipe Clamp Temperature Probe (Type K)	207.00
80PK-11	2724500	Velcro Temperature Probe	40.00
80PK-18 Kit	3448859	Pipe Clamp Temperature Probe Kit	335.00
80PK-22	2098684	SureGrip Immersion Probe	103.00
80PK-24	2098691	SureGrip Air Probe	134.00
80PK-25	2098706	SureGrip Piercing Probe	121.00
80PK-26	2098714	SureGrip General Purpose Probe	134.00
80PK-27	2098723	SureGrip Industrial Surface Probe	367.00
80PK-3A	874610	Surface Probe (Type K)	230.00
80PK-8	200360	Pipe Clamp Temperature Probe (Type K)	188.00
80PK-9	1288229	General Purpose Probe (Type K)	68.00
80PK-EXT	1288241	Extension Wire Kit (Type K)	61.00
80PR-60	2148313	RTD Temperature Probe (Fluke 66/68)	74.00
80PT-25	2104397	SureGrip Piercing Probe	107.00
80PT-EXT	1288252	Extension Wire Kit (Type T)	61.00
80T-150UA	3190456	Universal Temperature Probe (for DMMs)	289.00
80TK	736736	Thermocouple Module (Type K)	146.00

Model	Art. nr	Description	EUR
<b>Cases and Holsters</b>			
C10	897744	Meter Holster	28.00
C100	827055	Hard Meter and Accessory Case	73.00
C101	2437514	Hard Case	68.00
C115	2826063	Soft Meter Case	65.00
C116	2826074	Soft Meter Case	77.00
C120	646189	Hard Case (43B/120 Series)	112.00
C125	646858	Soft Meter Case	52.00
C12A	930529	Soft Meter Case	34.00
C150	4111540	Zippered Soft Carrying Case	31.00
C1600	2091049	Meter and Accessory Case	41.00
C1620	4359042	Carrying Case	203.00
C190	677401	Hard Case (190 Series)	263.00
C195	677408	Soft Case	244.00
C20	708396	Hard Meter Case	69.00
C23	1663209	Soft Meter Case	28.00
C25	681114	Soft Meter Case	58.00
C280	3182785	Soft Meter Case	68.00
C33	1664120	Soft Meter Case	31.00
C345	3311173	Soft Case	82.00
C35	2826056	Soft Meter Case	47.00
C43	1663230	Soft Meter Case	87.00
C50	762823	Soft Meter Case	41.00
C510	1547885	Leather Meter Case	81.00
C520A	1629104	Leather Tester Case	62.00
C550	1547919	Tool Bag	136.00
C75	865535	Soft Accessory Case	19.00
C781	619988	Soft Meter Case	100.00
C789	946694	Soft Meter Case	191.00
C800	896220	Hard Meter and Accessory Case	74.00
C90	466029	Soft Meter Case	41.00
CXT170	3352567	Rugged Pelican Hard Case	176.00
CXT280	3352571	Rugged Pelican Hard Case	176.00
CXT80	3352559	Rugged Pelican Hard Case	176.00
CXT1000	4628917	Extreme Hard case	176.00
FLUKEPACK30	4983088	Professional Tool Backpack	169.00
H3	1608458	Holster (330 Series)	45.00
H5	649365	Electrical Tester Holster (Fluke T5)	34.00
H6	2152040	Infrared Thermometer Holster (Fluke 63/65/68/561)	32.00
H-T6	4910585	T6 Belt Holster	34.00
H15	4111533	Belt Holster for T100 series	30.00
H80M	2138458	Holster + Magnetic Hanger	43.00
<b>Automotive Accessories</b>			
BP880	2150594	BNC to Female Double Stacking Banana Plug	15.00
BP881	2151015	BNC to Male Double Stacking Banana Plug	19.00
PV350	919811	Pressure Vacuum Module	294.00
RPM80	880849	Inductive Pick-up	100.00
SCC128	2100199	Automotive Accessory Kit (120 Series)	742.00
SCC198	2100208	Automotive Accessory Kit (190 Series)	933.00
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	258.00
TAS90	614187	Automotive Accessory Set (120/190 Series)	72.00
TL28A	1273185	Automotive Test Lead Set	60.00
TL82	2150636	Automotive Pin and Socket Adapter Set	119.00
TP40	1567573	Automotive Back Probe Pins (5 pcs) (4 mm)	42.00
TP81	2149098	Insulation Piercing Clip Set (4 mm)	58.00
TP82	2149080	Insulation Piercing Clip Set (2 mm)	55.00
TP88	2149102	Rigid Back Probe Pin Set	14.00
<b>Other Accessories</b>			
80K-40	382846	High Voltage Probe	294.00
80K-6	532424	High Voltage Probe	164.00
EBC290	3894906	External Battery Charger	108.00
FOM	200428	Fiber Optic Meter	581.00
FOS-850	200433	Fiber Optic Light Source	350.00
FOS-850/1300	200441	Fiber Optic Light Source	858.00
L200	2096346	Probe Light	25.00
L205	2098588	Mini Hat Light	32.00
L206	2098595	Deluxe Hat Light	41.00
L210	2096379	Probe light and probe extender	40.00
L215	2096368	SureGrip kit with probe light and probe extender	92.00
LVD1	4571403	Volt Light	36.00
LVD2	2740300	Volt Light	40.00
MC50	2092300	MeterCleaner Wipes, 50-pack	92.00
MC6	2092212	MeterCleaner Wipes, 6-pack	13.00

Model	Art. nr	Description	EUR
PV350	919811	Pressure Vacuum Module	294.00
SV225	3100477	Stray Voltage Adapter	70.00
TPAK	1281997	ToolPak, Meter Hanging Kit	41.00

Fuses			
943121	943121	Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm	4.80
803293	803293	Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm	8.80
830828	830828	Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm	7.70
2279339	2279339	Fuse, A:315mA (f), V:1000V, IR:10kA, 6.35x32 mm	11.30
740670	740670	Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm	3.70

Software			
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	153.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	251.00
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	289.00
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	166.00
FVF-UG	1576741	FlukeView Forms Upgrade	135.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	49.00
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	477.00
SCC120F	646692	FlukeView Software + USB Cable + Case (Fluke 123) - French	477.00
SCC190	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	668.00
SW90W	3894923	FlukeView Software	369.00

### Fluke Nederland B.V.

Postbus 1337

5602 BH Eindhoven

Tel.: (040) 267 51 00

Fax: (040) 267 51 11

E-mail: [info@fluke.nl](mailto:info@fluke.nl)

Web: [www.fluke.nl](http://www.fluke.nl)

10001 - Fluke Test Tools Price List End

Customer - English

Rev. 48

De genoemde prijzen zijn adviesprijzen en exclusief BTW. Prijswijzigingen voorbehouden.