

# Fluke Test Tools Price List

**FLUKE®**

Valid from: 02-07-2019

Model	Art. nr	Description	EUR
<b>Fluke Connect</b>			
<b>Fluke Connect - 3000 Series</b>			
FLK-3000 FC	4401595	FC Wireless Digital Multimeter	307.00
FLK-3000 FC GM	4467750	FC Wireless General Maintenance System	879.00
FLK-3000 FC HVAC	4465607	FC Wireless HVAC System	637.00
FLK-3000 FC IND	4465599	FC Wireless Industrial System	1098.00
FLK-3000FC/TPAK	4699340	Fluke 3000FC with TPAK meter hanging kit	340.00
Fluke 3000FC/EDA2	4699333	Electronics DMM and deluxe accessory kit	395.00
Fluke 3000FC/1AC-II	4699302	Electrician's DMM voltage tester and accessory kit	438.00
FLK-A3000 FC	4401588	FC Wireless AC Current Clamp Module	197.00
FLK-A3000 FC KIT	4465618	FC Wireless Essential Kit with A3000	438.00
FLK-A3001 FC	4459439	FC Wireless iFlex AC Current Module	230.00
FLK-A3001 FC KIT	4465665	FC Wireless Essential Kit with i3000	472.00
FLK-A3002 FC	4459442	FC Wireless AC/DC Current Module	131.00
FLK-A3003 FC	4629295	FC Wireless 2000A DC Clamp meter	548.00
FLK-A3004 FC	4629301	FC Wireless 4-20mA DC Clamp meter	658.00
FLK-T3000 FC	4401563	FC Wireless K-Type Temperature Module	197.00
FLK-T3000 FC KIT	4465652	FC Wireless Essential Kit with T3000	438.00
FLK-V3000 FC	4401556	FC Wireless AC Voltage Module	208.00
FLK-V3000 FC KIT	4465641	FC Wireless Essential Kit with V3000	438.00
FLK-V3001 FC	4459421	FC Wireless DC Voltage Module	208.00
FLK-V3001 FC KIT	4467777	FC Wireless essential Kit with V3001	438.00
FLK-V3003 FC KIT	4467789	FC Wireless Kit w. DMM, AC+DC Voltage Modules	713.00
<b>Fluke Connect - Accessories</b>			
FLK-FC_SD Card	4463628	Fluke Connect Wireless SD Card	99.00
FLK-PC3000 FC	4401602	FC Wireless PC Adapter	109.00
FLUKE-IR3000FC	4460436	Connector, Infrared, FC	143.00
<b>Digital Multimeters</b>			
<b>110 Series Multimeters</b>			
Fluke 113	3088053	True RMS Multimeter	135.00
Fluke 114	2583552	True RMS Multimeter	178.00
Fluke 115	2583583	True RMS Multimeter	206.00
Fluke 116	2583601	True RMS Multimeter	247.00
116/62MAX+ Kit	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	317.00
Fluke 116/323 Kit	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	350.00
Fluke 117	2583647	True RMS Multimeter	258.00
Fluke 117/323 Kit	4296034	Fluke Electrician's Multimeter Combo Kit	334.00
C50	762823	Soft Meter Case	43.00
<b>170 Series Multimeters</b>			
Fluke 175	1592901	True RMS Multimeter	247.00
Fluke 177	1592874	True RMS Multimeter	300.00
Fluke 179	1592842	True RMS Multimeter	354.00
C90	466029	Soft Meter Case	43.00
Fluke 179/EDA2/EUR	3947719	Electronics Combo Kit	420.00
<b>200 Series Multimeters</b>			
Fluke 233	3469334	Remote Display Multimeter	350.00
Fluke 279FC/iFlex	4684050	Wireless TRMS Thermal Multimeter w/iFlex	999.00
Fluke 279FC I/B	4989200	Wireless TRMS Thermal Multimeter with iFlex & extra battery	1099.00
Fluke 287/EUR	3947781	True RMS Electronic Logging Multimeter with TrendCapture	637.00
Fluke 287/FVF/EUR	3947796	FlukeView Forms Combo Kit	747.00
Fluke 289/EUR	3947801	True RMS Industrial Logging Multimeter with TrendCapture	692.00
Fluke 289/FVF/EUR	3947812	Industrial Logging Multimeter and Software Combo Kit	802.00
C280	3182785	Soft Meter Case	71.00
Fluke 287/FVF/IR3000	4699316	Fluke 287 FlukeView® Forms Combo Kit	824.00
Fluke 289/FVF/IR3000	4699325	Fluke 289 FlukeView® Forms Combo Kit	879.00

Model	Art. nr	Description	EUR
<b>20 Series Multimeters</b>			
Fluke 27II/EUR	3947770	Industrial Multimeter (IP67)	527.00
Fluke 28II/EUR	3947820	True RMS Industrial Multimeter (IP67)	527.00
Fluke 28 II Ex	4017165	Intrinsically safe true-rms digital multimeter	1373.00
C25	681114	Soft Meter Case	61.00
<b>70 Series Multimeters</b>			
Fluke 77-4/EUR	3947835	Multimeter	438.00
C90	466029	Soft Meter Case	43.00
<b>80 Series Multimeters</b>			
Fluke 83-V/EUR	3947847	Multimeter	493.00
Fluke 87-V/EUR	3947858	True RMS Multimeter	499.00
Fluke 87-V/E2K/EUR	3947864	Industrial Electricians Combo Kit	599.00
C25	681114	Soft Meter Case	61.00
<b>Bench Multimeters</b>			
Fluke 8808A 220V	2802372	5.5 Digit Multimeter	715.00
Fluke 8808A 240V	2802385	5.5 Digit Multimeter	715.00
Fluke 8808A/SU 220V	2802459	5.5 Digit Multimeter (software & cable)	915.00
Fluke 8808A/SU 240V	2802467	5.5 Digit Multimeter (software & cable)	915.00
Fluke 8808A/TL 220V	3111085	5.5 Digit Multimeter, 2X4W Test Lead Kit	795.00
Fluke 8808A/TL 240V	3111097	5.5 Digit Multimeter, 2X4W Test Lead Kit	795.00
Fluke 8845A 220V	2577352	6.5 Digit Precision Multimeter	1070.00
Fluke 8845A 240V	2577365	6.5 Digit Precision Multimeter	1070.00
Fluke 8845A/SU 220V	2675315	6.5 Digit Precision Multimeter (incl. software + cable)	1260.00
Fluke 8845A/SU 240V	2675332	6.5 Digit Precision Multimeter (incl. software + cable)	1260.00
Fluke 8846A 220V	2577383	6.5 Digit Precision Multimeter	1405.00
Fluke 8846A 240V	2577390	6.5 Digit Precision Multimeter	1405.00
Fluke 8846A/SU 220V	2675367	6.5 Digit Precision Multimeter (incl. software + cable)	1600.00
Fluke 8846A/SU 240V	2675380	6.5 Digit Precision Multimeter (incl. software + cable)	1600.00
884X-CASE	2675552	Hard Case (8845A/8846A)	440.00
884X-RTD	2675468	100 OHM RTD Temperature Probe	575.00
884X-SHORT	2653346	4-wire short	31.00
884X-USB	2675479	USB to RS232 Cable Adapter	165.00
884X-1G	2675534	USB Memory 1 GB	40.00
8845A-EFPT	2742690	Extended Fine Point Tip Adapter Set	20.00
8845A-TPIT	2742683	Test Probe IC Tip Set	15.00
FVF-UG	1576741	FlukeView Forms Upgrade	142.00
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	303.00
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	174.00
RS43	946470	Serial Interface Cable	89.00
TL2X4W-PTII	2826215	2x4 Wire Ohms Test Lead 2 mm Probe Tip	80.00
TL2x4W-TWZ	2723629	2X4-Wire Ohms Tweezers Test Leads	100.00
Y8021	708289	IEEE-488 Shielded Interface Cable, 1 m	458.00
Y8022	708297	IEEE-488 Shielded Interface Cable, 2 m	535.00
Y8846S	2675518	Rack mount kit single (8845A/8846A)	125.00
Y8846D	2771721	Rack mount kit dual (8845A/8846A)	170.00
<b>Automotive Meters</b>			
Fluke 88V/A	2117440	Automotive Meter Combo Kit	713.00
<b>Clamp Meters</b>			
Fluke 323	4152628	True RMS Clamp Meter	138.00
Fluke 324	4152637	True RMS Clamp Meter	180.00
Fluke 325	4152643	True RMS Clamp Meter	244.00
Fluke 353	2840252	AC/DC True RMS Clamp Meter	652.00
Fluke 355	2840265	AC/DC True RMS Clamp Meter	815.00
Fluke 365	3790607	Detachable TRMS Clamp Meter	271.00
Fluke 368 FC	4709907	Wireless leakage current clamp, 40mm jaw	724.00
Fluke 369 FC	4709934	Wireless leakage current clamp, 61mm jaw	724.00
Fluke 373	3790564	600A TRMS Clamp Meter	271.00
Fluke 374FC	4696001	600A AC/DC TRMS Wireless Clamp Meter	380.00
Fluke 375FC	4695932	600A AC/DC TRMS Wireless Clamp Meter	455.00
Fluke 376FC	4695861	1000A AC/DC TRMS Wireless Clamp Meter with iFlex	517.00
Fluke 381	3610452	Remote Display TRMS Clamp Meter	608.00
Fluke 902 FC	4695814	TRMS Wireless HVAC ClampMeter	305.00
62MAX+/323/1AC Kit	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	265.00
Fluke 116/323 Kit	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	350.00
Fluke i2500-18	3676405	iFlex Probe	141.00
Fluke i2500-10	3676410	iFlex Probe	141.00
H3	1608458	Holster (330 Series)	47.00

Model	Art. nr	Description	EUR
<b>Electrical Testers</b>			
Fluke 1000FLT	4472387	Fluorescent Light Tester	250.00
T6-1000/EU	4910257	Electrical Tester with FieldSense™, round	279.00
T6-600/EU	4910322	Electrical Tester with FieldSense™, round	219.00
H-T6	4910585	T6 Belt Holster	36.00
Fluke T5-600	659612	Electrical Tester	164.00
T5-600/62MAX+/1AC kit	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	267.00
Fluke T5-1000	659570	Electrical Tester	184.00
Fluke T5-H5-1AC II Kit	2098657	Electrical Tester Kit with Holster and 1AC	205.00
Fluke T90	4016945	Voltage/continuity tester	61.00
Fluke T110	4016950	Voltage/continuity tester with switchable load	87.00
Fluke T130	4016961	Voltage/continuity tester with LCD, switchable load	128.00
Fluke T150	4016977	Voltage/continuity tester with LCD, Ohms, switchable load	148.00
Fluke 2042	2435038	Cable Locator (Transmitter + Receiver)	794.00
Fluke 2042T	2435045	Cable Locator Transmitter	413.00
Fluke 9040EUR	4014969	Phase Rotation Indicator	212.00
Fluke 9062	2435077	Motor and Phase Rotation Indicator	195.00
LVD1	4571403	Volt Light	37.00
LVD2	2740300	Volt Light	41.00
H5	649365	Electrical Tester Holster (Fluke T5)	36.00
FTL660	2280204	Fused Test Lead Set	65.00
Fluke 1AC II	2432932	Volt Alert	32.00
Fluke 1AC II	2432971	Volt Alert	32.00
Fluke 1AC II 5PK	2433042	Volt Alert 5-pack	116.00
Fluke 1AC II 5PK	2433056	Volt Alert 5-pack	116.00
FLK2AC/200-1000VCL	3611985	ACV Detector 200-1000V	30.00
PRV240	4566209	Proving unit	164.00
Fluke 117/PRV240	4636971	Proving unit, Fluke 117 DMM Kit	328.00
PRV240FS	4910310	Proving unit, T6/NCV	164.00
<b>Laser Levels</b>			
<b>3 point lasers</b>			
PLS 3R Z	5009340	3-Point Red Laser Bare Tool	165.00
PLS 3R KIT	5009357	3-Point Red Laser Kit	206.00
PLS 3G Z	5009369	3-Point Green Laser Bare Tool	204.00
PLS 3G KIT	5009378	3-Point Green Laser Kit	245.00
<b>5 point lasers</b>			
PLS 5R Z	5009384	5-Point Red Laser Bare Tool	254.00
PLS 5R KIT	5009391	5-Point Red Laser Kit	283.00
PLS 5G Z	5009406	5-Point Green Laser Bare Tool	290.00
PLS 5G KIT	5009414	5-Point Green Laser Kit	327.00
<b>Cross line and point lasers</b>			
PLS 6R Z	5009423	Cross Line and Point Red Laser Bare Tool	299.00
PLS 6R KIT	5009438	Cross Line and Point Red Laser Kit	382.00
PLS 6R SYS	5009445	Cross Line and Point Red Laser System	490.00
PLS 6G Z	5009461	Cross Line and Point Green Bare Tool	390.00
PLS 6G KIT	5009489	Cross Line and Point Green Laser Kit	473.00
PLS 6G SYS	5009492	Cross Line and Point Green Laser System	581.00
<b>Cross line lasers</b>			
PLS 180R Z	5017279	Cross Line Red Laser Bare Tool	223.00
PLS 180R KIT	5009450	Cross Line Red Laser Kit	259.00
PLS 180R SYS	5019428	Cross Line Red Laser System	329.00
PLS 180G Z	5017287	Cross Line Green Laser Bare Tool	287.00
PLS 180G KIT	5009509	Cross Line Green Laser Kit	319.00
PLS 180G SYS	5019437	Cross Line Green Laser System	379.00
<b>Rotary lasers</b>			
<b>Horizontal rotary lasers</b>			
PLS H2 Z	5022470	Horizontal red rotary laser bare tool	575.00
PLS H2 SYS	5022481	Horizontal red rotary laser system	815.00
PLS H2 KIT	5022496	Horizontal red rotary laser kit	1049.00
<b>Manual slope rotary lasers</b>			
PLS HV2R Z	5022501	Manual slope red rotary laser bare tool	749.00
PLS HV2R SYS	5022512	Manual slope red rotary laser system	1049.00
PLS HV2R KIT	5022558	Manual slope red rotary laser kit	1289.00
PLS JV2G Z	5022535	Manual slope green rotary laser bare tool	869.00
PLS HV2G SYS	5022547	Manual slope green rotary laser system	1169.00
PLS HV2G KIT	5022520	Manual slope green rotary laser kit	1399.00

Model	Art. nr	Description	EUR
<b>Accessories lasers</b>			
PLS-20513	4791765	Tripod Telescope 9 FT 6 IN	186.00
PLS-21502	4919812	Tripod Extender PLS3/180	10.00
PLS FS	5031929	Floor Stand for PLS 3, 5, 6	15.00
PLS MLB	5031934	Magnetic L-Bracket, PLS 3, 5, 6, 180	41.00
PLS BP5	5031952	BP5 Alkaline Battery Pack	39.00
PLS UB9	4966636	UB9 Universal Ceiling/Wall Bracket	87.00
PLS SLD RED	4978515	SLD Red Detector W/ Bracket	155.00
PLS SLD GREEN	4978526	SLD Green Detector W/ Bracket	169.00
PLS RRT4	5022629	Red Magnetic Reflective Target	13.00
PLS GRT4	5022634	Green Magnetic Reflective Target	13.00
PLS C18	4985124	Laser Level Tool Box	77.00
PLS BC20	5022618	Charging Cord for PLS RBP10	34.00
PLS TPOD500	5022665	Elevating Tripod	264.00
PLS RC2	5022564	Rotary laser remote control	58.00
PLS XLD	5037696	Rotary laser detector with clamp	194.00
PLS XLD CLAMP	5037709	Rotary detector clamp	34.00
PLS C19	5022586	Rotary laser carrying case	68.00
PLS BP10	5022599	Rotary alkaline battery for H2, HV2	48.00
PLS RBP10	5022607	Rechargeable battery for H2, HV2	68.00
PLS WCB10	5022641	Rotary wall and ceiling mount	87.00
PLS GR16	5022652	Grade rod with US and Metric	48.00
<b>Distance Meters</b>			
Fluke 414D	4106830	Laser Distance Meter	140.00
Fluke 419D	4106853	Laser Distance Meter	269.00
Fluke 424D	4106866	Laser Distance Meter	389.00
414D/62MAX+ Kit	4296052	Fluke Laser distance meter and IR thermometer kit	237.00
<b>Battery Analyzers</b>			
Fluke BT510	4489970	Battery Analyzer	2809.00
Fluke BT520	4489981	Battery Analyzer	3492.00
Fluke BT521	4489996	Advanced Battery Analyzer	3914.00
<b>Battery Analyzer Accessories</b>			
BTL10	4542264	Standard Battery Analyzer Probes	341.00
BTL20	4542273	Intelligent Test Probe Set, w/Extenders (no temp sensor)	526.00
BTL21	4542286	Intelligent Test Probe Set, w/Extenders & Temp Sensor	654.00
BTL-A	4542258	Voltage/Current Probe Adapter	42.00
BC500	4542299	AC Power Charger	127.00
BP500	4542300	Lithium-ion battery, 7.4V 3000 mAh	106.00
BT500	4561297	Probe tip, 10x replacement Probe tips, 2x long probe tip covers, 2x short probe tip covers	127.00
i410	617727	AC/DC Current Clamp (400 A)	275.00
<b>Insulation Testers</b>			
Fluke 1503	2427883	Insulation Tester	415.00
Fluke 1507	2427890	Insulation Tester	515.00
Fluke 1550C	3665021	Insulation Resistance Tester (5kV)	4119.00
Fluke 1550C/Kit	3665127	Insulation Resistance Tester Kit (5kV)	4540.00
Fluke 1550C FC w/IR3000FC	4977402	Insulation Resistance Tester (5kV) with IR3000FC	4119.00
Fluke 1550C FC Kit w/IR3000FC	4977457	Insulation Resistance Tester Kit (5kV) with IR3000FC	4540.00
Fluke 1555	3665056	Insulation Resistance Tester (10kV)	4540.00
Fluke 1555/Kit	3665111	Insulation Resistance Tester Kit (10kV)	4959.00
Fluke 1555 FC w/IR3000FC	4977519	Insulation Resistance Tester (10kV) with IR3000FC	4540.00
Fluke 1555 FC Kit w/IR3000FC	4977469	Insulation Resistance Tester Kit (10kV) with IR3000FC	4959.00
Fluke 1577	2157280	Insulation Multimeter	652.00
Fluke 1587T	2517605	Insulation Multimeter (Telecom)	734.00
Fluke 1587 FC	4691215	2-IN-1 Insulation Multimeter	787.00
Fluke 1587/MDT FC	4692716	2-IN-1 Advanced Motor & Drive Troubleshooting Kit with 9040, I400	1050.00
1587KIT/62MAX+ FC	4692778	2-IN-1 Advanced Electrical Troubleshooting Insulation Multi Kit with 62MAX+ I400	945.00
Fluke 1587/I400 FC	4692725	2-IN-1 Insulation Multimeter with Clamp i400	839.00
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	161.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	264.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	51.00
<b>Installation Testers</b>			
Fluke 1662 SCH	4546944	Installation Tester w/mem Schuko	999.00
Fluke 1663 SCH	4546980	Installation Tester w/RCD type B Schuko	1299.00
Fluke 1664FC SCH	4547054	FC Installation Tester w/insulation pre-test Schuko	1649.00
Fluke 166X-MTC-SCH	4601081	Fluke 166X-Main test cord, Schuko (EU)	61.00
Fluke DMS COMP	4718790	DMS Complete, Installation, PAT Software	585.00
Fluke DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	778.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	264.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	51.00

Model	Art. nr	Description	EUR
ES165X	2104706	Earth Spike Test Kit	163.00
TP165X	2107742	Remote Control Probe (1650 Series)	87.00
TL165X	2107756	Standard Test Lead Set (1650 Series)	120.00
ZERO ADAPTER	3261925	Zero adapter (165xB)	42.00

### Portable Appliance Testers

Fluke DMS COMP	4718790	DMS Complete, Installation, PAT Software	585.00
Fluke DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	778.00

### Earth Ground Testers

Fluke 1630-2 FC	4829532	Earth Ground Loop and Leakage Clamp	1493.00
Fluke 1630-2	4829515	Earth Ground Loop and Leakage Clamp (non FC)	1493.00
Fluke 1623-2	4325155	Basic Geo Earth Ground Tester	1468.00
Fluke 1625-2	4325162	Advanced Geo Earth Ground Tester	2448.00
Fluke 1623-2 Kit	4325170	Basic Geo Earth Ground Tester, Kit	2502.00
Fluke 1625-2 Kit	4325181	Advanced Geo Earth Ground Tester, Kit	3591.00
Earth Stake	4325492	Geo Earth Ground Tester, Earth stake	67.00
Cable Reel 25M BL	4343731	25M Blue, Ground/Earth Cable Reel, 25M Wire	67.00
Cable Reel 25M GR	4343746	25M Green, Ground/Earth Cable Reel, 25M Wire	67.00
Cable Reel 50M RD	4343754	50M Red, Ground/Earth Cable Reel, 50M Wire	75.00
C1620	4359042	Carrying Case	210.00
ES-162P3-2	4359377	Earth Ground Stake Set for 3 Pole Measurement	260.00
ES-162P4-2	4359389	Earth Ground Stake Set for 4 Pole Measurement	380.00

### Indoor Air Quality Tools

Fluke 922	2679822	Airflow Meter	652.00
Fluke 922/Kit	2679831	Airflow Meter Kit	760.00
Fluke 971	2418208	Temperature Humidity Meter	260.00
Fluke 975	2519364	AirMeter	2039.00
Fluke 975V	2666111	AirMeter with Velocity	2345.00
Fluke CO-220	664711	Carbon Monoxide Meter	543.00
Fluke RLD2	3387163	Leak Detector Flashlight	54.00
CO-205	664714	Aspirator Kit	183.00
975VP	2631538	Air Velocity Probe	458.00
PT12	2740212	Pitot Tube, 12	119.00
Fluke 985	4131397	Airborne Particle Counter	4283.00

### Digital Thermometers

Fluke 51 II	1281142	Thermometer	337.00
Fluke 52 II	1281139	Thermometer	429.00
Fluke 53 II B	3821062	Single Input Thermometer, 60Hz	481.00
Fluke 53 II B	3821096	Single Input Thermometer, 50Hz	491.00
Fluke 54 II B	3821070	Dual Input Thermometer, 60Hz	583.00
Fluke 54 II B	3821081	Dual Input Thermometer, 50Hz	583.00
Fluke 61	1643896	Infrared Thermometer	200.00
Fluke 62 MAX	4130474	Infrared thermometer	97.00
Fluke 62 MAX+	4130488	Infrared Thermometer	105.00
T5-600/62MAX+/1AC kit	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	267.00
414D/62MAX+ Kit	4296052	Fluke Laser distance meter and IR thermometer kit	237.00
62MAX+/323/1AC Kit	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	265.00
116/62MAX+ Kit	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	317.00
Fluke 63	2148281	Infrared Thermometer	276.00
Fluke 64 MAX	4856105	Multifunction IR Thermometer 20:1 D:S	132.00
Fluke 561	2558118	Multipurpose Thermometer	200.00
Fluke 566	2837799	Multipurpose Thermometer	425.00
Fluke 568	2837806	Multipurpose Thermometer	532.00
Fluke 568Ex	4321662	Intrinsically safe Infrared Thermometer	1331.00
Fluke 572-2	4328074	Infrared Thermometer	634.00
Fluke FP	2644169	FoodPro Thermometer	128.00
Fluke FP Plus	2477950	FoodPro Plus Thermometer	214.00
C50	762823	Soft Meter Case	43.00
H6	2152040	Infrared Thermometer Holster (Fluke 63/65/68/561)	34.00
8OPR-60	2148313	RTD Temperature Probe (Fluke 66/68)	78.00

### Visual Thermometers

Fluke VTO4	4366444	Visual IR Thermometer	569.00
Fluke VTO4A	4485211	Visual IR thermometer	515.00
Fluke charger VTO4	4375752	Charger & adapter set VTO4	45.00
Fluke Battery, VTO4	4375741	Li-ion battery VTO4	45.00

### Industrial Imaging

Fluke DS701	4962652	Diagnostic Videoscope	1699.00
Fluke DS703 FC	4962665	High Resolution Diagnostic Videoscope with FC	1999.00

Model	Art. nr	Description	EUR
Fluke 3.8mm Scope	4962690	3.8 mm Scope, 1 m Probe, Forward View	699.00
Fluke 8.5mm Scope	4962708	8.5 mm Scope, 3 m Probe, Dual View	599.00
Fluke 5.5 mm Scope	4962713	5.5 mm Scope, 1 m Probe, Dual View	499.00
Fluke 8.5 mm Scope	4962749	8.5 mm Scope, 1.2 m Probe, Dual View	199.00
Fluke 8.5 mm UV Scope	4962751	8.5 mm UV Scope, 1 m Probe, Dual View	699.00
Fluke 9 mm Scope	4962760	9 mm Scope, Forward View, 20 m Probe Reel	1999.00
Fluke DS 7XX Neckstrap	4962772	DS 7XX Neckstrap	49.00
FLK-ii900	5075603	Sonic Industrial Imager	17499.00

## Thermal Imagers

### Handheld thermal cameras

FLK-PTI120 9Hz	5074148	Thermal Imager 120x90 9Hz	749.00
----------------	---------	---------------------------	--------

### High resolution thermal cameras

FLK-Ti401 Pro 9Hz	5085052	Thermal Imager 640x480 9Hz	6999.00
FLK-Ti401 Pro 60 Hz	5085041	Thermal Imager 640x480 60 Hz	6999.00
Fluke Ti480 PRO 9HZ	4947332	Fluke Ti480 PRO 9Hz Thermal Imager	9299.00
Fluke Ti480 PRO 60HZ	4947326	Fluke Ti480 PRO 60Hz Thermal Imager	9299.00
FLK-TiX501 9Hz	5085128	Thermal Imager 640x480 9Hz	9999.00
FLK-TiX501 60 Hz	5085119	Thermal Imager 640x480 60Hz	9999.00
Fluke TiX580 9Hz	4841945	Thermal Imager; 640x480; 9 HZ, SR	12299.00
Fluke TiX580 60Hz	4842073	Thermal Imager; 640x480; 60 HZ, SR	12299.00

### High definition mounted thermal cameras

Fluke RSE300 9Hz	4948166	Thermal Imager; 320x240; 9 Hz	10999.00
Fluke RSE300 60Hz	4944776	Thermal Imager; 320x240; 60 Hz	10999.00
Fluke RSE600 9Hz	4948175	Thermal Imager; 640x480; 9 Hz	15849.00
Fluke RSE600 60Hz	4944826	Thermal Imager; 640x480; 60 Hz	15849.00
Fluke 2x lens	4961163	Infrared Telephoto Lens (2X magnification)	2049.00
Fluke 4x lens	4961188	Infrared Telephoto Lens (4X magnification)	4579.00
Fluke RSE-MB	4961344	Mounting bracket	129.00
Fluke RSE-Stand	4973844	RSE Stand	139.00
Fluke 0.75 Wide lens	4961174	Infrared Wide Angle Lens	1029.00

### Gas detection thermal cameras

Fluke Ti450 SF6 60Hz	4907176	SF6 Gas leak detection, Thermal Imager	16999.00
----------------------	---------	--	----------

### Thermal Imagers Accessories (general)

Ti-Visor2	3996500	Sun Visor	79.00
Ti-Visor3	4335377	Thermal imager visor	79.00
Ti-Tripod	3511872	Tripod Mounting Base	109.00
Ti-Tripod2	3996517	Mounting Base	100.00
Ti-Tripod3	4335389	Tripod mounting base accessory	99.00
FLK-LENS/TELE2	4335350	Telephoto Infrared Lens (Ti200/Ti300/Ti400)	1299.00
FLK-LENS/WIDE2	4335361	Wide-angle Infrared Lens (Ti200/Ti300/Ti400)	1299.00
Fluke lens/4xTELE2	4607058	4x Telephoto IR lens for TiX560-TiX520-Ti400-Ti300-Ti200	5889.00
Fluke lens/25MAC2	4607064	25Micron Macro IR lens for TiX560-TiX520	4259.00
Ti-Car Charger	3039779	Ti Car Charger (TiR/TiR1/Ti10/Ti20/Ti25)	125.00
Ti20-RBP	2577796	Rechargeable Battery Pack (Ti20)	176.00
FLK-TI-SBP3	3440365	Extra battery (Ti32/TiR32)	139.00
Fluke TI-SBC3B	4354922	Charging base (Ti200/Ti300/Ti400)	175.00
Fluke TiX5xx-Neck	4574715	Adjustable neck strap	30.00
Fluke TiX5xx-SBP4	4597142	Additional Smart Battery	129.00
Fluke TiX5xx Hand	4574703	Adjustable hand strap	15.00
Fluke TiX5xx-HDMI	4615511	HDMI video cable	20.00
Fluke TiX5x-Lens Cap	4550697	Lens cap	15.00
Fluke TI-Bluetooth	4603258	Bluetooth headset	79.00

### Thermal Imagers IR-Windows

FLK-050-CLKT	3460346	50mm C-Range IR Windows, Kwik twist	169.00
FLK-075-CLKT	3460387	75 mm C-Range IR Window, Kwik Twist	219.00
FLK-100-CLKT	3460439	100mm C-Range IR Window, Kwik Twist	299.00
Fluke CV200	4326955	50mm IR Window, hand turn door latch	219.00
Fluke CV300	4326962	75mm IR Windows, hand turn door latch	295.00
Fluke CV301	4338164	75mm IR Windows, security turn door latch	309.00
Fluke CV400	4326996	100 mm IR Windows, hand turn door latch	409.00
Fluke CV401	4338173	100 mm IR Windows, security turn door latch	409.00

## ScopeMeters

Model	Art. nr	Description	EUR
<b>Industrial ScopeMeter</b>			
Fluke 123B/EU	4755659	Industrial ScopeMeter 20MHZ, EU	1560.00
Fluke 123B/INT	4755710	Industrial ScopeMeter 20MHZ, INT	1560.00
Fluke 124B/EU	4755731	Industrial ScopeMeter 40MHZ, EU	1872.00
Fluke 124B/INT	4755793	Industrial ScopeMeter 40MHZ, INT	1872.00
Fluke 125B/EU	4755818	Industrial ScopeMeter 40MHZ, EU	2236.00
Fluke 125B/INT	4755876	Industrial ScopeMeter 40MHZ, INT	2236.00
Fluke 123B/EU/S	4755890	Industrial ScopeMeter + SCC 20MHZ, EU	1976.00
Fluke 123B/INT/S	4755953	Industrial ScopeMeter + SCC 20MHZ, INT	1976.00
Fluke 124B/EU/S	4755975	Industrial ScopeMeter + SCC 40MHZ, EU	2288.00
Fluke 124B/INT/S	4756031	Industrial ScopeMeter + SCC 40MHZ, INT	2288.00
Fluke 125B/EU/S	4756054	Industrial ScopeMeter + SCC 40MHZ, EU	2652.00
Fluke 125B/INT/S	4756112	Industrial ScopeMeter + SCC 40MHZ, INT	2652.00
<b>190 Series ScopeMeters</b>			
Fluke 190-204/EU	3894409	ScopeMeter 4 Channel 200 MHZ Color	4581.00
Fluke 190-204/UN	3894411	ScopeMeter 4 Channel 200 MHZ Color	4990.00
Fluke 190-204/EU/S	3894475	ScopeMeter 4 Channel 200 MHZ Color SCC	4990.00
Fluke 190-204/UN/S	3894482	ScopeMeter 4 Channel 200 MHZ Color UNI SCC	4990.00
Fluke 190-104/EU	3894540	ScopeMeter 4 Channel 100 MHZ Color EU	4005.00
Fluke 190-104/UN	3894557	ScopeMeter 4 Channel 100 MHZ Color UNI	4005.00
Fluke 190-104/EU/S	3894617	ScopeMeter 4 Channel 100 MHZ Color EU SCC	4414.00
Fluke 190-104/UN/S	3894621	ScopeMeter 4 Channel 100 MHZ Color UNI SCC	4414.00
Fluke 190-062/EU	4025159	ScopeMeter 2 Channel 60 MHZ Color	2892.00
Fluke 190-062/UN	4025171	ScopeMeter 2 Channel 60MHZ Color	2892.00
Fluke 190-062/EU/S	4025230	ScopeMeter 2 Channel Color SCC	3300.00
Fluke 190-062/UN/S	4025248	ScopeMeter 2 Channel 60MHZ Color SCC	3300.00
Fluke 190-102/EU	4025318	ScopeMeter 2 Channel 100MHZ Color	3557.00
Fluke 190-102/UN	4025329	ScopeMeter 2 Channel 100MHZ Color SCC	3557.00
Fluke 190-102/EU/S	4025383	ScopeMeter 2 Channel 100MHZ Color SCC	3966.00
Fluke 190-102/UN/S	4025390	ScopeMeter 2 Channel 100MHZ Color SCC	3966.00
Fluke 190-202/EU	4025460	ScopeMeter 2 Channel 200MHZ Color	4015.00
Fluke 190-202/UN	4025472	ScopeMeter 2 Channel 200MHZ Color	4015.00
Fluke 190-202/EU/S	4025554	ScopeMeter 2 Channel 200MHZ Color SCC	4424.00
Fluke 190-202/UN/S	4025568	ScopeMeter 2 Channel 200MHZ Color SCC	4424.00
Fluke 190-502/EU	4025623	ScopeMeter 2 Channel 500 MHZ Color	4946.00
Fluke 190-502/UN	4025638	ScopeMeter 2 Channel 500 MHZColor UNI	4946.00
Fluke 190-502/EU/S	4025692	ScopeMeter 2 Channel 500 MHZ Color Europe SCC	5355.00
Fluke-190-502/UN/S	4025704	ScopeMeter 2 Channel 500 MHZ Color UNI SCC	5355.00
Fluke 190-504/EU	4419875	ScopeMeter 4 Channel 500MHz Color	5127.00
Fluke 190-504/UN	4419929	ScopeMeter 4 Channel 500MHz Color UNI	5127.00
Fluke 190-504/EU/S	4419941	ScopeMeter 4 Channel 500MHz Color Europe SCC	5535.00
Fluke 190-504/UN/S	4419990	ScopeMeter 4 Channel 500MHz Color UNI SCC	5535.00
<b>Motor Drive Analyzers</b>			
Fluke MDA-510	4984691	Motor Drive Analyzer 510, 4-channel color	5675.00
Fluke MDA-550	4984706	Motor Drive Analyzer 550, 4-channel color, PRO	6550.00
SVS-500	5011031	Shaft voltage set and magnetic base	349.00
SB-500	5011046	Shaft brushes set, repl brushes for SVS-500 and MDA-500	261.00
<b>ScopeMeter Accessories</b>			
AC120	646163	Heavy Duty Alligator Clips	47.00
AS400	3894880	Probe Extension Set, for VPS400 Probes	113.00
BB120	646171	Banana to BNC Adapter Plug	52.00
BB120-II	4744369	Set of 2 banana to BNC adapter	47.00
BHT190	3379374	Set of Break-out Adapters	368.00
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	103.00
BP190	677390	NiMH Battery Pack (190 Series)	207.00
BP290	4025762	Battery Pack Single Cap 190-series II	245.00
BP291	3894688	Battery Pack, Fluke 190 Series	343.00
C120	646189	Hard Case (43B/120 Series)	112.00
C120B	4744391	Soft carrying case for 120B series	141.00
C125	646858	Soft Meter Case	52.00
C190	677401	Hard Case (190 Series)	263.00
C195	677408	Soft Case	244.00
C290	3894803	Hard-Shell Carrying Case	219.00
CS20MA	677393	Current Shunt 4-20 mA	101.00
EBC290	3894906	External Battery Charger	108.00
HC120	646668	Hook Clips	59.00
HC120-II	4744357	Set of 2 hook clips	52.00
HC200	2086410	Hook Clips	42.00
HH290	3894844	Hanging Hook, ScopeMeter Series 190 II	77.00
MA190	1567481	Medical Accessory Kit (190 Series)	464.00
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	167.00
PM8907/807	624764	POWER ADAPTOR/BATTERY CHARGER	125.00

Model	Art. nr	Description	EUR
PM8907/808	614039	Battery Charger/Line Voltage Adapter UNIVERSAL (120 Series)	149.00
PM9080	1641983	Serial Interface Adapter/Cable (RS232)	277.00
PM9081	916093	Dual Banana Plug to Female BNC Adapter	53.00
PM9082	916163	Dual Banana Jack to Male BNC Adapter	53.00
PM9091	935598	Coaxial BNC Cables (1.5 m)	125.00
PM9092	935601	Coaxial BNC Cables (0.5 m)	108.00
PM9093	935593	Male BNC to Female BNC Adapter	72.00
PM9096/201	651742	Secondary Pick-up	346.00
RS120-III	4023947	Probe Accessory Replacement Set	113.00
RS400	3894867	Probe Replacement Set, for VPS400 Probes	90.00
RS500	4025886	Probe accessory replacement set for VPS500 probes	161.00
SCC120B	4744423	Software soft carry case accessory kit 120B series	520.00
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	477.00
SCC128	2100199	Automotive Accessory Kit (120 Series)	742.00
SCC198	2100208	Automotive Accessory Kit (190 Series)	933.00
SCC190	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	668.00
SCC290	3894826	Software and Carrying Case for 190 Series II	408.00
SP120B	4744414	Screen protector for 120B series	47.00
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	258.00
STL120-III	4023901	Shielded Test Lead	198.00
STL120-IV	4744340	Shielded test lead set 600V CAT IV	166.00
SW90W	3894923	FlukeView Software	369.00
TAS90	614187	Automotive Accessory Set (120/190 Series)	72.00
TRM50	4025864	50 Ohm feed-through terminator BNC	194.00
UA120	4744384	USB Connector adapter	47.00
VPS41	4744378	Voltage probe set 40 MHz 600V CAT IV	161.00
VPS101	3086317	1:1 Voltage Probe Set, black, 30 MHz, 1.2m	225.00
VPS210-G	3086247	10:1 Voltage Probe Set, grey, 200 MHz, 1.2m	225.00
VPS210-R	3086235	10:1 Voltage Probe Set, 1 red, 200 MHz, 1.2m	225.00
VPS212-G	3086286	10:1 Voltage Probe Set, grey, 200 MHz, 2.5m	225.00
VPS212-R	3086273	10:1 Voltage Probe Set, red, 200 MHz, 2.5m	225.00
VPS220-G	3086300	100:1 Voltage Probe Set, grey, 200 MHz, 1.2m	225.00
VPS220-R	3086299	100:1 Voltage Probe Set, red, 200 MHz, 1.2m	225.00
VPS40-III	4023920	Voltage Probe	131.00
VPS410-II-B	4276937	Industrial Voltage Probe Set 500 MHz 10:1 Blue	215.00
VPS410-II-G	4276943	Industrial Voltage Probe Set 500 MHz 10:1 Grey	215.00
VPS410-II-R	4276928	Industrial Voltage Probe Set 500 MHz 10:1 Red	215.00
VPS410-II-V	4276955	Industrial Voltage Probe Set 500 MHz 10:1 Green	215.00
VPS420-R	3894783	High Working Voltage Probe 100:1 Red & Black	250.00
VPS420-B	4411541	High Working Voltage Ruggedized Probe; Blue/Black	250.00
VPS420-G	4411565	High Working Voltage Ruggedized Probe; Grey/Black	250.00
VPS420-V	4411583	High Working Voltage Ruggedized Probe; Green/Black	250.00
VPS510-R	4025781	Voltage Probe set 500 MHz 10:1 Red	215.00
VPS510-B	4025796	Voltage probe set 500 MHz 10:1 Blue	215.00
VPS510-G	4025801	Voltage probe set 500 MHz 10:1 Grey	215.00
VPS510-V	4025812	Voltage probe set 500 MHz 10:1 Green	215.00

### Power Quality Tools

Fluke 345	2584181	Power Quality Clamp Meter	1636.00
Fluke 430-II/MA	4779032	430-II Motor Analyzer Upgrade Kit	2066.00
Fluke 434-II/BASIC	4116650	Power Quality and energy analyzer (w/o clamps)	4131.00
Fluke 434-II	4116638	Power Quality and energy analyzer	4773.00
Fluke 434-II/INTL	4778918	Power Quality and energy analyzer/International	4773.00
Fluke 435-II	4116661	Power Quality& Energy Analyzer	6128.00
Fluke 435-II/BASIC	4116689	Advanced Power Quality and energy analyzer (w/o clamps)	5520.00
Fluke 435-II/INTL	4778929	Power Quality and energy analyzer/International	6129.00
Fluke 437-II	4116692	Power Quality& Energy Analyzer	8478.00
Fluke 437-II/BASIC	4116719	400 Hz Power Quality and Energy Analyzer (w/o clamps)	7823.00
Fluke 437-II/INTL	4778934	Power Quality and energy analyzer/International	8478.00
Fluke 438-II	4778976	Power Quality & Motor Analyzer	7547.00
Fluke 438-II/BASIC	4778990	Power Quality & Motor Analyzer, without clamps and FC WiFi SD Card	6905.00
Fluke 438-II/INTL	4779015	Power Quality & Motor Analyzer, without FC WiFi SD Card	7547.00
Fluke 1732/EUS	4706548	Energy Logger, EU/US version	2536.00
Fluke 1732/INTL	4706553	Energy Logger, international version	2536.00
Fluke 1732/B	4706566	Energy Logger, basic version	2277.00
Fluke 1734/EUS	4706594	Energy Logger, EU/US advanced version	2841.00
Fluke 1734/INTL	4706608	Energy Logger, international advanced version	2841.00
Fluke 1734/B	4706582	Energy Logger, advanced version no flexis	2587.00
Fluke 1736/EUS	4534519	3-Phase Power Logger, EU/US version	4059.00
Fluke 1736/B	4563561	3-Phase Power Logger, basic version	3933.00
Fluke 1736/INTL	4563550	3-Phase Power Logger, International version	4059.00
Fluke 1738/EUS	4563577	3-Phase Power Logger, EU/US Advanced version no flexis	4566.00
Fluke 1738/B	4588378	3-Phase Power Logger, advanced version no flexis	4059.00
Fluke 1738/INTL	4588384	3-Phase Power Logger, international advanced version	4566.00



Model	Art. nr	Description	EUR
Fluke 1742/15/EUS	4920613	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	3618.00
Fluke 1742/30/EUS	4920651	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	3618.00
Fluke 1742/B/EUS	4920660	Power Quality Logger without iFlex, EUS version	3308.00
Fluke 1742/15/INTL	4920672	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	3618.00
Fluke 1742/30/INTL	4920685	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	3618.00
Fluke 1742/B/INTL	4920697	Power Quality Logger without iFlex, INTL version	3308.00
1742-6/Upgrade	4920964	1742 to 1746 Upgrade	1770.00
1742-8/Upgrade	4920973	1742 to 1748 Upgrade	3273.00
Fluke 1746/15/EUS	4920703	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	4964.00
Fluke 1746/30/EUS	4920715	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	4964.00
Fluke 1746/B/EUS	4920726	Power Quality Logger without iFlex, EUS version	4653.00
Fluke 1746/15/INTL	4920732	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	4964.00
Fluke 1746/30/INTL	4920744	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	4964.00
Fluke 1746/B/INTL	4920759	Power Quality Logger without iFlex, INTL version	4653.00
1746-8/Upgrade	4920986	1746 to 1748 Upgrade	1770.00
Fluke 1748/15/EUS	4920767	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	6207.00
Fluke 1748/30/EUS	4920771	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	6207.00
Fluke 1748/B/EUS	4920780	Power Quality Logger without iFlex, EUS version	5896.00
Fluke 1748/15/INTL	4920798	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	6207.00
Fluke 1748/30/INTL	4920800	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	6207.00
Fluke 1748/B/INTL	4920817	Power Quality Logger without iFlex, INTL version	5896.00
Fluke 1760 Basic	2630732	Power Quality Recorder (three-phase), Topas	12027.00
Fluke 1760	2630744	Power Quality Recorder (three-phase), Topas	13935.00
Fluke 1760TR Basic	2637629	Power Quality Recorder (three-phase), Topas	16481.00
Fluke 1760TR	2637634	Power Quality Recorder (three-phase), Topas	18387.00
Fluke VR1710	3030923	Single-Phase Voltage Quality Recorder	887.00
C1740	4116762	Softcase for 174X and 43X-II PQ analyzer	209.00
C437-II	4116743	Hard case 430 Series II with rollers	505.00
EPE-Training-E/EMEA	4792349	Fluke EPE Training Set - English	199.00

#### Power Quality Tools Accessories

1743/1744 Poleset	3024485	Pole Mounting Kit (Fluke 1743/1744)	42.00
3140R	2650136	Clip-on Current Transformer 2A-400A (Fluke 1750)	407.00
3210-PR-TF-II	4531769	1000A Fluke 1750 Thin flexi 61cm	632.00
3310-PR-TF-II	4531778	5000A Fluke 1750 Thin flexi 61cm	844.00
3312-PR-TF-II	4531784	5000A Fluke 1750 Thin flexi 122cm	1039.00
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	103.00
BE345	2839604	Battery Eliminator (Fluke 345)	156.00
BP1730	4389436	Li Ion Battery Pack 3.7V 2500mAh (1730)	41.00
C120	646189	Hard Case (43B/120 Series)	112.00
C17xx	4637381	Soft Case	118.00
CS1750	2673962	Soft Case (Fluke 1750/1760)	259.00
1730 Hanger	4358028	Hanger kit (1730)	57.00
1730 Cable	4395217	Cable,AUX input cable (1730)	30.00
1750/Case	2650124	Hard Case (Fluke 1750)	558.00
1750/Seat-L	2673937	Fluke Power Analyze - Additional SEAT LICENSE	1105.00
1750/Site-L	2673928	Fluke Power Analyze - Additional SITE LICENSE	5526.00
FS17X5-TF-II	4531791	3000A 4-PH Fluke 1735 & 1745 Thin flexi set	1627.00
FS17XX IP65-TF-II	4531804	3000A IP65 4-PH Fluke 1743/4 Thin flexi set	1806.00
FS17XX-1PH-TF-II	4531819	FS3000A/6000A 4-PH 36-Inch Thin flexi set	407.00
FLUKE-173X ADPT	4717827	AUX input adapter, 173X	136.00
Fluke 17xx TL 0.1M	4715389	Test lead set for Fluke 173x; 0.1m	41.00
FS3000/6000A-TF-4-II	4531828	FS3000A/6000A 4-PH 36-Inch thin flexi set	1623.00
GPS430-II	4693803	GPS Synchronization module (430-II series)	1560.00
GPS-Time Sync	2539223	GPS Time Synchronization Module (Fluke 1760)	434.00
i17XX-flex1500	4637328	Fluke-17xx iFlexi 1500A 12 IN	167.00
i17XX-flex3000	4637343	Fluke-17xx iFlexi 3000A 24 IN	179.00
i17XX-flex6000	4637362	Fluke-17xx iFlexi 6000A 36 IN	190.00
i17XX-flex1500/3pk	4637337	Fluke-17xx iFlexi 1500A 12 IN, 3 pack	485.00
i17XX-flex3000/3pk	4637355	Fluke-17xx iFlexi 3000A 24 IN, 3 pack	516.00
i17XX-flex6000/3pk	4637370	Fluke-17xx iFlexi 6000A 36 IN, 3 pack	548.00
i17XX-Flex1500/4PK	4637411	Fluke-17xx iFlexi 1500A 12 IN, 4 Pack	632.00
i17XX-Flex3000/4PK	4637427	Fluke-17xx iFlexi 3000A 24 IN, 4 Pack	675.00
i17XX-Flex6000/4PK	4637430	Fluke-17xx iFlexi 6000A 36 IN, 4 Pack	717.00
i1A/10A Clamp PQ1	3345753	1-phase Mini Current Clamp Set	475.00
i1A/10A Clamp PQ3	3024413	3-phase Mini Current Clamp Set	546.00
i1A/10A Clamp PQ4	3024424	4-phase Mini Current Clamp Set	734.00
i5A/50A Clamp PQ1	3345766	1-Phase 5A/50A Mini Current Clamp set for PQ	475.00
i5A/50A Clamp PQ3	3024436	3-phase Mini Current Clamp Set	546.00
i5A/50A Clamp PQ4	3024449	4-phase Mini Current Clamp Set	734.00
i20/200A Clamp PQ3	3024451	3-phase Mini Current Clamp Set	546.00
i20/200A Clamp PQ4	3024460	4-phase Mini Current Clamp Set	734.00
i40S-EL	4637396	Fluke-17xx i40s-EL Clamp-on Current Transformer	215.00
i40S-EL/3pk	4637409	Fluke-17xxx i40s-EL Clamp-on Current Transformer, 3 pack	601.00
i400	2277225	AC Current Clamp (400 A)	165.00

Model	Art. nr	Description	EUR
i400s	2277202	AC Current Clamp (400A)	296.00
i430-Flexi-TF-II	4531725	6000A Fluke 430 Thin Flexi 61cm	410.00
i430-Flexi-TF-II-4PK	4531733	6000A Fluke 430 Thin Flexi 61cm 4 Pack	1248.00
i5s	2508467	AC Current Clamp (5 A)	550.00
i5S-PR	3949761	1750, 5A Current Clamp	326.00
i5sPQ3	2457508	AC Current Clamp (5 A), 3-pack	1323.00
IEEE519/REPORT	4589748	SOFTWARE LICENSE FOR IEEE519 REPORTING	527.00
MP1-Magnet Probe 1	4589220	Magnet probes for 4 mm banana, set of 4	94.00
MBX USB-RS232	2539565	EP0328Z, USB to Serial RS232 Adapter	47.00
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	167.00
PM9080	1641983	Serial Interface Adapter/Cable (RS232)	277.00
TLS430	2157713	Test Leads and Alligator Clips (4 black, 1 green) - 430 Series	132.00
TPS Clamp 10A/1A	2540445	Clip-on Current Transformer 10A/1A (Fluke 1760)	395.00
TPS Clamp 50A/5A	2540461	Clip-on Current Transformer 50A/5A (Fluke 1760)	395.00
TPS Clamp 200A/20A	2540450	Clip-on Current Transformer 200A/20A (Fluke 1760)	395.00
TPS Flex 18-TF-II	4531837	100/500A Fluke 1760 Thin Flexi 45cm (18in)	463.00
TPS Flex 24-TF-II	4531843	200/1000A Fluke 1760 Thin Flexi 61cm (24in)	463.00
TPS Flex 36-TF-II	4531855	3000/6000A Fluke 1760 Thin Flexi 91cm (36in)	909.00
TPS/MBX Dolph red	2540744	EP0326Z, Dolphin Clip, Red	21.00
TPS Nullmodem Cable	2540511	A550500510, RS232 Cross Link Cable, 3M	40.00
TPS Shunt 1A	2540548	A680501054, Shunt 1 A AC/DC	321.00
TPS Shunt 20MA	2540553	Shunt 20mA AC/DC (Fluke 1760)	332.00
TPS Voltprobe 10V	2540636	Voltage Probe 10V (Fluke 1760)	311.00
TPS Voltprobe 100V	2540624	Voltage Probe 100V (Fluke 1760)	311.00
TPS Voltprobe 400V	2540660	Voltage Probe 400V (Fluke 1760)	315.00
TPS Voltprobe 600V	2540697	Voltage Probe 600V (Fluke 1760)	315.00
TPS Voltprobe 1KV	2540649	Voltage Probe 1000V (Fluke 1760)	500.00
VL1735/45	3276205	Banana 4-Phase Voltage Lead set for Fluke-1735/45	248.00
Fluke MA-C8	4945842	Wall outlet adapter, Fluke-174X	21.00
IP65 Adapter Set	4946241	IP65 rated Voltage Connector	218.00
I17XX-FLEX1.5KIP	4921003	IP65 iFlexi 1.5KA 60 cm	218.00
I17XX-FLEX1.5KIP/3PK	4921015	IP65 iFlexi 1.5KA 60 cm, 3 Pack	523.00
I17XX-FLEX1.5KIP/4PK	4921026	IP65 iFlexi 1.5KA 60 cm, 4 Pack	698.00
I17XX-FLEX3KIPK	4921032	IP65 iFlexi 3KA 60 cm	218.00
I17XX-FLEX3KIP/3PK	4921044	IP65 iFlexi 3KA 60 cm, 3 Pack	523.00
I17XX-FLEX3KIP/4PK	4921067	IP65 iFlexi 3KA 60 cm, 4 Pack	698.00
I17XX-FLEX6KIPK	4921071	IP65 iFlexi 6KA 90 cm	261.00
I17XX-FLEX6KIP/3PK	4921080	iFlexi 6KA 90 cm, 3 Pack	610.00
I17XX-FLEX6KIP/4PK	4921098	iFlexi 6KA 90 cm, 4 Pack	784.00
I17XX-FLEX5M-EXT	4921116	iFlexi Extension Cable, 5m	131.00
Fluke 174X_3541-HANGER	4890129	Hanger Kit	62.00
Fluke 174X GPS-REC	4921133	GPS Receiver Antenna	336.00
F17XX Cable Markers	4921140	Cable Marker set, 05MM	52.00
MP1-3R/1B	4944790	3 red/1 black Magnet probe for 4 mm banana	87.00
3PHVL-17XX-5M	5014816	Cable assembly, Voltage test lead 3-phase+N 5M	123.00
FLUKE-17XX-TL	5016873	Test lead set; 1000V CAT III, nonstack/stack 0.18M	35.00
FLUKE-17XX-TL-2M	5020006	Blue, non-stackable plug and 2x alligator clips	26.00
FLUKE-PQ400	4920947	Power Quality Window	1673.00
FLUKE-PQ400/B	5075807	Power Quality Window, basic	1321.00
I17XX-FLEX2M-M2M4P	5076272	Male-male cable 2m, 4 pcs	507.00
I17XX-FLEX2M-M2M1P	5076285	Male-male cable 2m, 1 pce	132.00
FLUKE-PQ-MARKER	5046009	Cable market set 3P+N+PE	9.00
I17XX-BNC-M2M	5076297	Fluke-17xx 4 pin male to BNC male cable 2m (1x)	88.00
I17XX-BNC-M2F	5076304	Fluke-17xx 4 pin male to BNC female cable 0.1m (1x)	88.00

### Vibration Testers

Fluke 805	4094385	Vibration Meter	1784.00
Fluke 805 FC	4489229	Vibration Meter with Fluke Connect	1784.00
Fluke 805/ES	4636786	External Vibration Sensor	1060.00
Fluke 810	3542635	Vibration Tester	9571.00
Fluke 820-2	4550041	LED Stroboscope	907.00
Fluke 830	4454396	Laser Alignment Tool	7241.00
Fluke 830/Magnet	4528249	Magnetic Bracket	835.00
Fluke 830/Shims	4551330	Laser Alignment Tool, Shims	835.00
810S	3530828	Sensor	1445.00
810QDC	3530837	Quick Disconnect Cable	151.00
810SMM	3530862	Sensor Magnet Mount	212.00
810SMP	3530855	Sensor Mounting Pads (10-pack)	29.00
SBP-810	3530843	Smart Battery Pack	269.00
Fluke-810PA	3986002	AC Power Adapter with International Plug Set	85.00

### Process Calibrators

Model	Art. nr	Description	EUR
<b>700 Series Process Calibrators</b>			
Fluke 154 INTL	4805625	HART Calibration Assistant	3875.00
Fluke 705	665091	Loop Calibrator	780.00
Fluke 707	1617262	Loop Calibrator	897.00
Fluke 707Ex	2032187	Intrinsically Safe Loop Calibrator	1261.00
Fluke 709	4234350	Precision Loop Calibrator	890.00
Fluke 709H	4234361	Precision HART Loop Calibrator	1432.00
Fluke 710	4991049	mA Loop, Valve Tester, with HART	2159.00
Fluke 712B	4387857	RTD Temperature Calibrator	1105.00
Fluke 714B	4387869	TC Temperature Calibrator	1131.00
Fluke 715	620101	Volt/mA Calibrator	1272.00
Fluke 717 1G	2547166	Pressure Calibrator (68.9 mbar)	1444.00
Fluke 717-15G	4058808	Pressure Calibrator (1 bar)	1444.00
Fluke 717 100G	1630430	Pressure Calibrator (7 bar)	1444.00
Fluke 717 30G	662897	Pressure Calibrator (2 bar)	1498.00
Fluke 717 300G	2547175	Pressure Calibrator (20 bar)	1444.00
Fluke 717 500G	2547182	Pressure Calibrator (34.7 bar)	1444.00
Fluke 717 1000G	2547194	Pressure Calibrator (69 bar)	1444.00
Fluke 717 1500G	2547203	Pressure Calibrator (103.4 bar)	1600.00
Fluke 717 3000G	2547215	Pressure Calibrator (207 bar)	1600.00
Fluke 717 5000G	2547232	Pressure Calibrator (345 bar)	1600.00
Fluke 717-10000G	4058813	Pressure Calibrator (690 bar)	1600.00
Fluke 718 30G	665075	Pressure Calibrator (2 bar)	2718.00
Fluke 718 1G	2547148	Pressure Calibrator (68.9 mbar)	2831.00
Fluke 718 100G	665080	Pressure Calibrator (7 bar)	2718.00
Fluke 718 300G	2547153	Pressure Calibrator (20 bar)	2823.00
Fluke 718Ex 30G	2096310	Intrinsically Safe Pressure Calibrator (2 bar)	3496.00
Fluke 718Ex 100G	2096322	Intrinsically Safe Pressure Calibrator (7 bar)	3496.00
Fluke 718Ex 300G	3023328	Intrinsically Safe Pressure Calibrator (20 bar)	3496.00
Fluke 719 30G	3315332	Electric Pressure Calibrator (2 bar)	3604.00
Fluke 719 100G	3315344	Electric Pressure Calibrator (7 bar)	3604.00
Fluke-719PRO 30G	4353218	Electric Pressure Calibrator, 2 bar	3200.00
Fluke-719PRO 150G	4353229	Electric Pressure Calibrator, 10 bar	3200.00
Fluke-719PRO 300G	4353234	Electric Pressure Calibrator, 20 bar	3200.00
Fluke 720URTD	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	167.00
Fluke-721-1601	4353241	Dual Sensor Pressure Calibrator, 1.1 bar, 6.9 bar	2029.00
Fluke-721-1603	4353283	Dual Sensor Pressure Calibrator, 1.1 bar, 20 bar	2029.00
Fluke-721-1605	4353327	Dual Sensor Pressure Calibrator, 1.1 bar, 34 bar	2029.00
Fluke-721-1610	4353366	Dual Sensor Pressure Calibrator, 1.1 bar, 69 bar	2029.00
Fluke-721-1615	4353401	Dual Sensor Pressure Calibrator, 1.1 bar, 103 bar	2029.00
Fluke-721-1630	4353447	Dual Sensor Pressure Calibrator, 1.1 bar, 200 bar	2029.00
Fluke-721-1650	4353486	Dual Sensor Pressure Calibrator, 1.1 bar, 345 bar	2029.00
Fluke-721-3601	4353252	Dual Sensor Pressure Calibrator, 2.48 bar, 6.9 bar	2029.00
Fluke-721-3603	4353290	Dual Sensor Pressure Calibrator, 2.48 bar, 20 bar	2029.00
Fluke-721-3605	4353330	Dual Sensor Pressure Calibrator, 2.48 bar, 34 bar	2029.00
Fluke-721-3610	4353375	Dual Sensor Pressure Calibrator, 2.48 bar, 69 bar	2029.00
Fluke-721-3615	4353412	Dual Sensor Pressure Calibrator, 2.48 bar, 103 bar	2029.00
Fluke-721-3630	4353458	Dual Sensor Pressure Calibrator, 2.48 bar, 200 bar	2029.00
Fluke-721-3650	4353499	Dual Sensor Pressure Calibrator, 2.48 bar, 345 bar	2029.00
Fluke 721EX-1601	4353265	Dual Sensor Pressure Calibrator, 16, 100 PSIG	2652.00
Fluke 721EX-1603	4353309	Dual Sensor Pressure Calibrator, 16, 300 PSIG	2652.00
Fluke 721EX-1605	4353348	Dual Sensor Pressure Calibrator, 16, 500 PSIG	2652.00
Fluke 721EX-1610	4353382	Dual Sensor Pressure Calibrator, 16, 1000 PSIG	2652.00
Fluke 721EX-1615	4353420	Dual Sensor Pressure Calibrator, 16, 1500 PSIG	2652.00
Fluke 721EX-1630	4353464	Dual Sensor Pressure Calibrator, 16, 3000 PSIG	2652.00
Fluke 721EX-1650	4353506	Dual Sensor Pressure Calibrator, 16, 5000 PSIG	2652.00
Fluke 721EX-3601	4353276	Dual Sensor Pressure Calibrator, 36, 100 PSIG	2652.00
Fluke 721EX-3603	4353311	Dual Sensor Pressure Calibrator, 36, 300 PSIG	2652.00
Fluke 721EX-3605	4353353	Dual Sensor Pressure Calibrator, 36, 500 PSIG	2652.00
Fluke 721EX-3610	4353394	Dual Sensor Pressure Calibrator, 36, 1000 PSIG	2652.00
Fluke 721EX-3615	4353435	Dual Sensor Pressure Calibrator, 36, 1500 PSIG	2652.00
Fluke 721EX-3630	4353473	Dual Sensor Pressure Calibrator, 36, 3000 PSIG	2652.00
Fluke 721EX-3650	4353514	Dual Sensor Pressure Calibrator, 36, 5000 PSIG	2652.00
Fluke 724	1553041	Temperature Calibrator	2373.00
Fluke 725	664133	Multifunction Process Calibrator	3314.00
Fluke 725Ex	2098179	Intrinsically Safe Multifunction Process Calibrator	4052.00
Fluke 726	2452080	Precision Multifunction Process Calibrator	3795.00
Fluke 729 30G FC	4856907	Automatic Pressure Calibrator, w/FC (2 Bar)	8593.00
Fluke 729 150G FC	4856894	Automatic Pressure Calibrator, w/FC (10 Bar)	8593.00
Fluke 729 300G FC	4856882	Automatic Pressure Calibrator, w/FC (20 Bar)	8593.00
Fluke 729 30G	4856990	Automatic Pressure Calibrator (2 Bar)	8383.00
Fluke 729 150G	4856983	Automatic Pressure Calibrator (10 Bar)	8383.00
Fluke 729 300G	4856976	Automatic Pressure Calibrator (20 Bar)	8383.00
Fluke 729/750SW BU	4972518	Automatic Pressure Calibrator, w/DPC Track2 Bundle	9760.00
Fluke 753 EU	4411027	Documenting Process Calibrator	5474.00

Model	Art. nr	Description	EUR
Fluke 754 EU	4400387	Documenting Process Calibrator	6898.00
Fluke 771	2646347	Milliamp Process Clamp Meter	575.00
Fluke 772	3362352	Milliamp Process Clamp Meter	820.00
Fluke 773	3362365	Milliamp Process Clamp Meter	1090.00
Fluke 787B	4777186	Process Meter	1037.00
Fluke 789/E	3977194	Process Meter	1165.00
Fluke 789/IR3000FC	4604605	Process Meter and FC connector	1098.00
<b>Pressure Modules</b>			
Fluke-700G01	4353523	Pressure Gauge, -10" to 10" WC (27 mbar)	756.00
Fluke-700G02	4353538	Pressure Gauge, -30" to 30" WC (69 mbar)	756.00
700G04	4096972	Pressure Gauge, +/- 1 bar	770.00
700G05	4097514	Pressure Gauge, 2 bar	770.00
700G06	4097538	Pressure Gauge, 6.9 bar	770.00
700G07	4097561	Pressure Gauge, 34 bar	770.00
700G08	4097592	Pressure Gauge, 69 bar	770.00
700G27	4097545	Pressure Gauge, 20 bar	770.00
700G29	4097605	Pressure Gauge, 200 bar	779.00
700G30	4097610	Pressure Gauge, 345 bar	779.00
700G31	4097622	Pressure Gauge, 690 bar	779.00
Fluke-700GA4	4353545	Pressure Gauge, 1 bar absolute	756.00
Fluke-700GA5	4353550	Pressure Gauge, 2 bar absolute	756.00
Fluke-700GA6	4353561	Pressure Gauge, 6.9 bar absolute	756.00
Fluke-700GA27	4353577	Pressure Gauge, 20 bar absolute	756.00
700HTPK	4124358	Hydraulic Test Pump Kit, 0 to 690 bar	1175.00
Fluke 700HTPK2	4623314	Premium hydraulic test pump kit	1539.00
Fluke 700MTH	4623345	Premium metric pressure test hose	566.00
Fluke 700M20TH	4623338	Premium M20 pressure test hose	566.00
700PCK	100062	Pressure Module Calibration Kit	1412.00
Fluke 700PTPK	4124364	Pneumatic Test Pump Kit, 0 to 41 bar	616.00
Fluke 700PTPK2	4623306	Premium pneumatic test pump kit	1422.00
700G/TRACK	4123225	Data Logging Cable & Software	431.00
Fluke-700RG05	4353589	Pressure Gauge, Reference, +2 bar	797.00
Fluke-700RG06	4353592	Pressure Gauge, Reference, 6.9 bar	797.00
Fluke-700RG07	4353605	Pressure Gauge, Reference, 34 bar	797.00
Fluke-700RG08	4353610	Pressure Gauge, Reference, 69 bar	797.00
Fluke-700G10	4353654	Pressure Gauge, 140 bar	756.00
Fluke-700RG29	4353622	Pressure Gauge, Reference, 200 bar	864.00
Fluke-700RG30	4353631	Pressure Gauge, Reference, 345 bar	864.00
Fluke-700RG31	4353646	Pressure Gauge, Reference, 690 bar	864.00
Fluke 700TTH5K	4623323	Premium pressure transmitter test hose	566.00
Fluke 700TTH10K	4636393	Premium pressure transmitter test hose kit, 10K	673.00
750P00	4352270	Pressure Module (0 - 2.5 mbar)	1653.00
750P01	4352281	Pressure Module (0 - 25 mbar)	1277.00
750P02	4352750	Pressure Module (0 - 70 mbar)	1277.00
750P22	4352296	Pressure Module (0 - 70 mbar)	1277.00
750P03	4352738	Pressure Module (0 - 350 mbar)	1277.00
750P23	4352308	Pressure Module (0 - 350 mbar)	1277.00
750P04	4352313	Pressure Module (0 - 1 bar)	1277.00
750P24	4352324	Pressure Module (0 - 1 bar)	1277.00
750P05	4352336	Pressure Module (0 - 2 bar)	1277.00
750P06	4352349	Pressure Module (0 - 7 bar)	1277.00
750P27	4352351	Pressure Module (0 - 20 bar)	1277.00
750P07	4352360	Pressure Module (0 - 35 bar)	1277.00
750P08	4352372	Pressure Module (0 - 70 bar)	1277.00
750P09	4352385	Pressure Module (0 - 100 bar)	1277.00
750P2000	4352397	Pressure Module (0 - 140 bar)	1277.00
750P29	4352403	Pressure Module (0 - 200 bar)	2026.00
750P30	4352415	Pressure Module (0 - 340 bar)	2026.00
750P31	4352426	Pressure Module (0 - 700 bar)	2026.00
750PA3	4352432	Pressure Module (0 - 350 mbar)	1469.00
750PA4	4352444	Pressure Module (0 - 1 bar)	1469.00
750PA5	4352459	Pressure Module (0 - 2 bar)	1469.00
750PA6	4352467	Pressure Module (0 - 7 bar)	1469.00
750PA27	4352471	Pressure Module (0 - 20 bar)	1469.00
750PA7	4352480	Pressure Module (0 - 35 bar)	1469.00
750PA8	4352498	Pressure Module (0 - 70 bar)	1440.00
750PA9	4352500	Pressure Module (0 - 100 bar)	1440.00
750PV3	4352517	Pressure Module (-350 mbar)	1440.00
750PV4	4352521	Pressure Module (-1 bar)	1440.00
750PD2	4352539	Pressure Module (-70 - 70 mbar)	1440.00
750PD3	4352542	Pressure Module (-350 - 350 mbar)	1440.00
750PD10	4352556	Pressure Module (-700 - 700 mbar)	1440.00
750PD4	4352563	Pressure Module (-1 - 1 bar)	1440.00
750PD5	4352574	Pressure Module (-1 - 2 bar)	1440.00

Model	Art. nr	Description	EUR
750PD50	4352588	Pressure Module (-1 - 3.5 bar)	1440.00
750PD6	4352595	Pressure Module (-1 - 7 bar)	1440.00
750PD7	4352602	Pressure Module (-1 - 14 bar)	1440.00
750PD27	4352616	Pressure Module (-1 - 20 bar)	1440.00
750R04	4352625	Pressure Module (0 - 1 bar)	1440.00
750R06	4352633	Pressure Module (0 - 7 bar)	1440.00
750R27	4352640	Pressure Module (0 - 20 bar)	1440.00
750R07	4352657	Pressure Module (0 - 35 bar)	1440.00
750R08	4352669	Pressure Module (0 - 70 bar)	1440.00
750R29	4352678	Pressure Module (0 - 200 bar)	2163.00
750R30	4352684	Pressure Module (0 - 340 bar)	2163.00
750R31	4352691	Pressure Module (0 - 700 bar)	2163.00
750RD5	4352706	Pressure Module (-1 - 2 bar)	1619.00
750RD6	4352714	Pressure Module (-1 - 7 bar)	1619.00
750RD27	4352723	Pressure Module (-0.8 - 20 bar)	1619.00
750P01Ex	4558658	Ex Pressure Module (0 - 25 mbar)	2467.00
750P24Ex	4558686	Ex Pressure Module (0 - 1 bar)	2467.00
750P05Ex	4558664	Ex Pressure Module (0 - 2 bar)	2467.00
750P06Ex	4558673	Ex Pressure Module (0 - 7 bar)	2467.00
750P27Ex	4558699	Ex Pressure Module (0 - 20 bar)	2467.00
750P09Ex	4558725	Ex Pressure Module (0 - 100 bar)	2467.00
750P29Ex	4558702	Ex Pressure Module (0 - 200 bar)	4215.00
750PA4Ex	4558716	Ex Pressure Module (0 - 1 bar)	2673.00

### Process Calibrator Accessories

700HTH-1	2811795	Hydraulic Test Hose	944.00
700ILF	1566730	In-Line Filter	108.00
700LTP-1	2811763	Low Pressure Test Pump	1007.00
700-IV	202561	Current Shunt	499.00
700PMP	617131	Pressure Pump (10 bar)	704.00
700PRV-1	2811808	Pressure Relief Valve for 700HTP	1135.00
700PTP-1	2811774	Pneumatic Test Pump	907.00
700SC	667425	Serial Interface Cable (Fluke 725/725Ex/726)	238.00
700TC1	620119	Thermocouple Plug Kits (10 types)	145.00
700TC2	620127	Thermocouple Plug Kits (5 types)	119.00
Fluke 720RTD	4366669	RTD Probe for 721, 721Ex and 719PRO	267.00
787CAL 230	662996	Calibration Module (Fluke 787)	1134.00
BC7217	668217	Battery Charger	323.00
BE9005 240	946652	Battery Eliminator	299.00
BP7235	668225	NiMH Battery Pack	259.00
C700	606928	Hard Case (700 Series)	359.00
C789	946694	Soft Meter Case	201.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	264.00
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	161.00
Fluke 700HTP-2	4096855	Hydraulic Test Pump, 690 bar	1158.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	51.00
BP7240	4022220	753/754 Spare Battery	176.00
Fluke 750SW	4090343	DPC/TRACK2-software	3459.00
BC7240	4022655	Battery Charger (753/754)	50.00
HART Drywell Cable	2111088	Cable Kit, HART Drywellcontrol	167.00
Fluke-71x	3345825	Hose kit	105.00
Fluke 700TLK	3829398	Process Test Lead Kit	142.00
Fluke 709H/TRACK	4281225	Logging software with cable	457.00
Fluke 720URTD	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	167.00
754HCC	3829410	HART-Communication Cable	89.00
Fluke-71X-TRAP	4380747	Liquid dirt trap for 718 and 719Pro	326.00

### General Accessories

#### Test Leads, Probes and Clips

80K-15	618113	Probe, Electronic Air Cleaner	301.00
AC175	4101772	Threaded Alligator Clip Set	30.00
AC220	1610103	SureGrip Alligator Clip Set	48.00
AC280	1610115	SureGrip Hook Clip Set	38.00
AC283	1610144	SureGrip Pincer Clip Set	43.00
AC285	1610159	SureGrip Alligator Clip Set	24.00
AC285-FTP	4073928	Alligator Clips and adaptors (FTP-1, FTPL-1)	28.00
AC288	4617784	SureGrip™ Terminal block probe	38.00
AC87	1278079	Heavy Duty Bus Bar Clip Set	50.00
AC89	873448	Heavy Duty Insulation Piercing Test Clip	56.00
BP980	1616807	Dual Banana Plug Kit	57.00
FTL660	2280204	Fused Test Lead Set	65.00
FTP-1	3869437	Fuse test probe set	99.00
FTPL-1	3869443	Fuse test probe set with test leads	109.00

Model	Art. nr	Description	EUR
H900	1616818	Test Lead Holder	34.00
Leadwrap	4083525	Durable Nylon Hook and Loop Fastener, 3 pack	9.00
T5-Kit	3971169	T5 Tester Accessory Starter Kit	55.00
T5-RLS	4089137	Replacement Test Lead Set (T5)	24.00
TL175	3521976	Twist Guard Test Leads	30.00
TL175E	3565554	Twist Guard Test Leads, 4mm	33.00
TL220-1	3971178	SureGrip Industrial Test Lead Set	83.00
TL221	2003602	SureGrip Extension Lead Set	37.00
TL222	2003616	SureGrip Silicone Test Lead Set	37.00
TL223-1	3971184	SureGrip Electrical Test Lead Set	76.00
TL224	1610198	SureGrip Silicone Test Lead Set	33.00
TL225-1	3971191	Stray Voltage Eliminator test Lead Set	110.00
TL238	2132831	SureGrip High Energy Test Lead Kit	83.00
TL27	668571	Heavy Duty Test Lead Set	38.00
TL40	1590606	Retractable Tip Test Lead Set	55.00
TL71-1	3971207	TL71, Test Lead Set	30.00
TL75-1	3971218	TL75, Test Lead Set	25.00
TL76	2032684	All-in-one Test Lead Set	43.00
TL80A-1	3971229	TL80A, Test Lead Set	79.00
TL81A	1277073	Deluxe Electronic Test Lead Kit	165.00
TL910	1616632	Electronic Test Lead Set (with replacement tips)	76.00
TL930	1616671	Patch Cords (60 cm)	19.00
TL932	1616680	Patch Cords (90 cm)	21.00
TL935	1616698	Patch Cord Kit (60, 90, 120 cm)	63.00
TL940	1616705	Mini-Hook Test Lead Set	21.00
TL950	1616710	Mini-Pincer Test Lead Set	38.00
TL960	1616722	Micro-Hook Test Lead Set	21.00
TL970	1616793	Hook and Pincer Test Lead Kit	79.00
TLK1550-RTLCL	4112351	Integral test lead & 10 kV clamp	239.00
TLK220	2097022	SureGrip Accessory Kit	153.00
TLK-225	3971234	TLK225, SureGrip Master Set	165.00
TLK281-1	3971241	TLK281, Automotive Test Lead Kit	146.00
TLK-282-1	3971252	TLK282, DeLuxe Automotive Test Lead Kit	186.00
TLK287	3045631	Electronic Master Test Lead Kit	175.00
TLK289	3092521	Industrial Master Test Lead Kit	175.00
TLK290	2435092	Test Probe Kit	65.00
TLK291	2435108	Fused Test Probe Set	65.00
TP1-1	3971265	TP1, Test Probes	19.00
TP175	3521983	TwistGuard test Probes, 2MM dia probe tips	21.00
TP175E	3565568	TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters	23.00
TP2-1	3971283	TP2, Test Probes	21.00
TP220-1	3971276	TP220, SureGrip Test Probes	21.00
TP38	1541636	Slim Reach Test Probe Set (insulated)	19.00
TP74	1541649	Lantern Tip Test Probe Set	21.00
TP80	873455	Electronic Test Probe Set	41.00
TP912	1616644	Replacement tips for TL910	38.00
TP920	1616659	Test Probe Adapter Kit	55.00
<b>Current Clamps</b>			
80i-110s	114519	AC/DC Current Clamp (100 A)	779.00
i1000s	1568487	AC Current Clamp (1000 A)	660.00
i1010	617735	AC/DC Current Clamp (1000 A)	474.00
i1010 Kit	2096998	AC/DC Current Clamp (1000 A) with Soft Case	484.00
i200	664755	AC Current Clamp (200 A)	165.00
i2000 flex	2584912	AC Flexible Current Clamp (2000 A)	330.00
i200s	664760	AC Current Clamp (200 A)	275.00
i30	2584920	AC/DC Current Clamp (30A)	440.00
i3000 flex-4PK	2696367	AC Flexible Current Clamp (3000 A), 4-pack	1323.00
i3000s	657202	AC Current Clamp (3000 A)	794.00
i3000s flex-24	2584888	AC Flexible Current Clamp (3000 A), 610 mm	506.00
i3000s flex-36	2584901	AC Flexible Current Clamp (3000 A), 915 mm	606.00
i30s	2584935	AC/DC Current Clamp (30A)	606.00
i310s	2840309	AC/DC Current Clamp (300A)	363.00
i400	2277225	AC Current Clamp (400 A)	165.00
i400s	2277202	AC Current Clamp (400A)	296.00
I40S-PR (1750)	3949777	40A Current Clamp (1750)	387.00
i410	617727	AC/DC Current Clamp (400 A)	275.00
i410 Kit	2097005	AC/DC Current Clamp (400 A) with Soft Case	319.00
i6000s flex-24	2840311	AC Current Clamp (6000 A)	660.00
i6000s flex-36	2840327	AC Current Clamp (6000 A)	771.00
i800	2840283	AC Current Clamp (800 A)	237.00

Model	Art. nr	Description	EUR
<b>Temperature Accessories</b>			
80AK-A	2747812	Thermocouple Adapter	35.00
80BK-A	2747801	Integrated DMM Temperature Probe (Type K)	39.00
80CJ-M	833046	Male Mini Connectors (Type J)	26.00
80CK-M	779942	Male Mini Connectors (Type K)	26.00
80PJ-1	1288191	Bead Probe (Type J)	28.00
80PJ-9	1288218	General Purpose Probe (Type J)	71.00
80PJ-EXT	1288234	Extension Wire Kit (Type J)	64.00
80PK-1	750422	Bead Probe (Type K)	37.00
80PK-10	3439199	Pipe Clamp Temperature Probe (Type K)	217.00
80PK-11	2724500	Velcro Temperature Probe	42.00
80PK-18 Kit	3448859	Pipe Clamp Temperature Probe Kit	352.00
80PK-22	2098684	SureGrip Immersion Probe	108.00
80PK-24	2098691	SureGrip Air Probe	141.00
80PK-25	2098706	SureGrip Piercing Probe	127.00
80PK-26	2098714	SureGrip General Purpose Probe	141.00
80PK-27	2098723	SureGrip Industrial Surface Probe	385.00
80PK-3A	874610	Surface Probe (Type K)	242.00
80PK-8	200360	Pipe Clamp Temperature Probe (Type K)	197.00
80PK-9	1288229	General Purpose Probe (Type K)	71.00
80PK-EXT	1288241	Extension Wire Kit (Type K)	64.00
80PR-60	2148313	RTD Temperature Probe (Fluke 66/68)	78.00
80PT-25	2104397	SureGrip Piercing Probe	112.00
80PT-EXT	1288252	Extension Wire Kit (Type T)	64.00
80T-150UA	3190456	Universal Temperature Probe (for DMMs)	303.00
80TK	736736	Thermocouple Module (Type K)	153.00
<b>Cases and Holsters</b>			
C10	897744	Meter Holster	29.00
C100	827055	Hard Meter and Accessory Case	77.00
C101	2437514	Hard Case	71.00
C115	2826063	Soft Meter Case	68.00
C116	2826074	Soft Meter Case	81.00
C120	646189	Hard Case (43B/120 Series)	112.00
C125	646858	Soft Meter Case	52.00
C12A	930529	Soft Meter Case	36.00
C150	4111540	Zippered Soft Carrying Case	33.00
C1600	2091049	Meter and Accessory Case	43.00
C1620	4359042	Carrying Case	210.00
C190	677401	Hard Case (190 Series)	263.00
C195	677408	Soft Case	244.00
C20	708396	Hard Meter Case	72.00
C23	1663209	Soft Meter Case	29.00
C25	681114	Soft Meter Case	61.00
C280	3182785	Soft Meter Case	71.00
C33	1664120	Soft Meter Case	33.00
C345	3311173	Soft Case	86.00
C35	2826056	Soft Meter Case	49.00
C43	1663230	Soft Meter Case	91.00
C50	762823	Soft Meter Case	43.00
C510	1547885	Leather Meter Case	85.00
C520A	1629104	Leather Tester Case	65.00
C550	1547919	Tool Bag	143.00
C75	865535	Soft Accessory Case	20.00
C781	619988	Soft Meter Case	105.00
C789	946694	Soft Meter Case	201.00
C799 Softcase	4021731	Field Softcase for 75X	91.00
C800	896220	Hard Meter and Accessory Case	78.00
C90	466029	Soft Meter Case	43.00
CXT170	3352567	Rugged Pelican Hard Case	185.00
CXT280	3352571	Rugged Pelican Hard Case	185.00
CXT80	3352559	Rugged Pelican Hard Case	185.00
CXT1000	4628917	Extreme Hard case	185.00
FLUKEPACK30	4983088	Professional Tool Backpack	169.00
H3	1608458	Holster (330 Series)	47.00
H5	649365	Electrical Tester Holster (Fluke T5)	36.00
H6	2152040	Infrared Thermometer Holster (Fluke 63/65/68/561)	34.00
H-T6	4910585	T6 Belt Holster	36.00
H15	4111533	Belt Holster for T100 series	32.00
H80M	2138458	Holster + Magnetic Hanger	45.00
<b>Automotive Accessories</b>			
BP880	2150594	BNC to Female Double Stacking Banana Plug	16.00
BP881	2151015	BNC to Male Double Stacking Banana Plug	20.00
PV350	919811	Pressure Vacuum Module	309.00

Model	Art. nr	Description	EUR
RPM80	880849	Inductive Pick-up	105.00
SCC128	2100199	Automotive Accessory Kit (120 Series)	742.00
SCC198	2100208	Automotive Accessory Kit (190 Series)	933.00
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	258.00
TAS90	614187	Automotive Accessory Set (120/190 Series)	72.00
TL28A	1273185	Automotive Test Lead Set	63.00
TL82	2150636	Automotive Pin and Socket Adapter Set	125.00
TP40	1567573	Automotive Back Probe Pins (5 pcs) (4 mm)	44.00
TP81	2149098	Insulation Piercing Clip Set (4 mm)	61.00
TP82	2149080	Insulation Piercing Clip Set (2 mm)	58.00
TP88	2149102	Rigid Back Probe Pin Set	15.00

#### Other Accessories

80K-40	382846	High Voltage Probe	309.00
80K-6	532424	High Voltage Probe	172.00
EBC290	3894906	External Battery Charger	108.00
FOM	200428	Fiber Optic Meter	610.00
FOS-850	200433	Fiber Optic Light Source	368.00
FOS-850/1300	200441	Fiber Optic Light Source	901.00
L200	2096346	Probe Light	26.00
L205	2098588	Mini Hat Light	34.00
L206	2098595	Deluxe Hat Light	43.00
L210	2096379	Probe light and probe extender	42.00
L215	2096368	SureGrip kit with probe light and probe extender	97.00
LVD1	4571403	Volt Light	37.00
LVD2	2740300	Volt Light	41.00
MC50	2092300	MeterCleaner Wipes, 50-pack	97.00
MC6	2092212	MeterCleaner Wipes, 6-pack	14.00
PV350	919811	Pressure Vacuum Module	309.00
SV225	3100477	Stray Voltage Adapter	74.00
TPAK	1281997	ToolPak, Meter Hanging Kit	43.00
FL-45 EX	4972422	45 lumen intrinsically safe flashlight	45.00
FL-120 EX	4972431	120 lumen intrinsically safe flashlight	69.00
FL-150 EX	4972446	150 lumen intrinsically safe flashlight	89.00
HL-200 EX	4972410	200 lumen intrinsically safe headlamp	89.00

#### Fuses

943121	943121	Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm	4.90
803293	803293	Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm	9.00
830828	830828	Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm	7.90
2279339	2279339	Fuse, A:315mA (f), V:1000V, IR:10kA, 6.35x32 mm	11.60
740670	740670	Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm	3.80

#### Software

FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	161.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	264.00
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	303.00
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	174.00
FVF-UG	1576741	FlukeView Forms Upgrade	142.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	51.00
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	477.00
SCC120F	646692	FlukeView Software + USB Cable + Case (Fluke 123) - French	477.00
SCC190	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	668.00
SW90W	3894923	FlukeView Software	369.00