

# Fluke Test Tools Price List

**FLUKE®**

Valid from: 02-07-2018

Model	Art. nr	Description	GBP
<b>Fluke Connect - 3000 Series</b>			
<b>Fluke Connect - 3000 Series</b>			
FLK-3000 FC	4401595	FC Wireless Digital Multimeter	253.00
FLK-3000 FC GM	4467750	FC Wireless General Maintenance System	783.00
FLK-3000 FC HVAC	4465607	FC Wireless HVAC System	518.00
FLK-3000 FC IND	4465599	FC Wireless Industrial System	806.00
FLK-3000FC/TPAK	4699340	Fluke 3000FC with TPAK meter hanging kit	271.00
Fluke 3000FC/EDA2	4699333	Electronics DMM and deluxe accessory kit	317.00
Fluke 3000FC/1AC-II	4699302	Electrician's DMM voltage tester and accessory kit	350.00
FLK-A3000 FC	4401588	FC Wireless AC Current Clamp Module	150.00
FLK-A3000 FC KIT	4465618	FC Wireless Essential Kit with A3000	349.00
FLK-A3001 FC	4459439	FC Wireless iFlex AC Current Module	173.00
FLK-A3001 FC KIT	4465665	FC Wireless Essential Kit with i3000	380.00
FLK-A3002 FC	4459442	FC Wireless AC/DC Current Module	104.00
FLK-A3003 FC	4629295	FC Wireless 2000A DC Clamp meter	415.00
FLK-A3004 FC	4629301	FC Wireless 4-20mA DC Clamp meter	495.00
FLK-T3000 FC	4401563	FC Wireless K-Type Temperature Module	150.00
FLK-T3000 FC KIT	4465652	FC Wireless Essential Kit with T3000	346.00
FLK-V3000 FC	4401556	FC Wireless AC Voltage Module	161.00
FLK-V3000 FC KIT	4465641	FC Wireless Essential Kit with V3000	346.00
FLK-V3001 FC	4459421	FC Wireless DC Voltage Module	161.00
FLK-V3001 FC KIT	4467777	FC Wireless essential Kit with V3001	346.00
FLK-V3003 FC KIT	4467789	FC Wireless Kit w. DMM, AC+DC Voltage Modules	576.00
<b>Fluke Connect - Accessories</b>			
FLK-FC_SD Card	4463628	Fluke Connect Wireless SD Card	95.00
FLK-PC3000 FC	4401602	FC Wireless PC Adapter	92.00
FLUKE-IR3000FC	4460436	Connector, Infrared, FC	109.00
<b>Digital Multimeters</b>			
<b>110 Series Multimeters</b>			
Fluke 113	3088053	True RMS Multimeter	113.00
Fluke 114	2583552	True RMS Multimeter	151.00
Fluke 115	2583583	True RMS Multimeter	176.00
Fluke 116	2583601	True RMS Multimeter	203.00
116/62MAX+ Kit	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	279.00
Fluke 116/323 Kit	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	290.00
Fluke 117	2583647	True RMS Multimeter	207.00
Fluke 117/323 Kit	4296034	Fluke Electrician's Multimeter Combo Kit	265.00
C50	762823	Soft Meter Case	33.00
<b>170 Series Multimeters</b>			
Fluke 175	1592901	True RMS Multimeter	223.00
Fluke 177	1592874	True RMS Multimeter	257.00
Fluke 179	1592842	True RMS Multimeter	279.00
C90	466029	Soft Meter Case	33.00
Fluke 179/EDA2/EUR	3947719	Electronics Combo Kit	333.00
<b>200 Series Multimeters</b>			
Fluke 233	3469334	Remote Display Multimeter	288.00
Fluke 279FC/iFlex	4684050	Wireless TRMS Thermal Multimeter w/iFlex	839.00
Fluke 279FC I/B	4989200	Wireless TRMS Thermal Multimeter with iFlex & extra battery	923.00
Fluke 287/EUR	3947781	True RMS Electronic Logging Multimeter with TrendCapture	519.00
Fluke 287/FVF/EUR	3947796	FlukeView Forms Combo Kit	566.00
Fluke 289/EUR	3947801	True RMS Industrial Logging Multimeter with TrendCapture	566.00
Fluke 289/FVF/EUR	3947812	Industrial Logging Multimeter and Software Combo Kit	644.00
C280	3182785	Soft Meter Case	57.00
Fluke 287/FVF/IR3000	4699316	Fluke 287 FlukeView® Forms Combo Kit	664.00
Fluke 289/FVF/IR3000	4699325	Fluke 289 FlukeView® Forms Combo Kit	719.00

Model	Art. nr	Description	GBP
<b>20 Series Multimeters</b>			
Fluke 27II/EUR	3947770	Industrial Multimeter (IP67)	430.00
Fluke 28II/EUR	3947820	True RMS Industrial Multimeter (IP67)	451.00
Fluke 28 II Ex	4017165	Intrinsically safe true-rms digital multimeter	1017.00
C25	681114	Soft Meter Case	47.00
<b>70 Series Multimeters</b>			
Fluke 77-4/EUR	3947835	Multimeter	335.00
C90	466029	Soft Meter Case	33.00
<b>80 Series Multimeters</b>			
Fluke 83-V/EUR	3947847	Multimeter	379.00
Fluke 87-V/EUR	3947858	True RMS Multimeter	428.00
Fluke 87-V/E2K/EUR	3947864	Industrial Electricians Combo Kit	482.00
C25	681114	Soft Meter Case	47.00
<b>Bench Multimeters</b>			
Fluke 8808A 220V	2802372	5.5 Digit Multimeter	546.00
Fluke 8808A 240V	2802385	5.5 Digit Multimeter	546.00
Fluke 8808A/SU 220V	2802459	5.5 Digit Multimeter (software & cable)	698.00
Fluke 8808A/SU 240V	2802467	5.5 Digit Multimeter (software & cable)	698.00
Fluke 8808A/TL 220V	3111085	5.5 Digit Multimeter, 2X4W Test Lead Kit	562.00
Fluke 8808A/TL 240V	3111097	5.5 Digit Multimeter, 2X4W Test Lead Kit	562.00
Fluke 8845A 220V	2577352	6.5 Digit Precision Multimeter	798.00
Fluke 8845A 240V	2577365	6.5 Digit Precision Multimeter	798.00
Fluke 8845A/SU 220V	2675315	6.5 Digit Precision Multimeter (incl. software + cable)	945.00
Fluke 8845A/SU 240V	2675332	6.5 Digit Precision Multimeter (incl. software + cable)	945.00
Fluke 8846A 220V	2577383	6.5 Digit Precision Multimeter	1055.00
Fluke 8846A 240V	2577390	6.5 Digit Precision Multimeter	1055.00
Fluke 8846A/SU 220V	2675367	6.5 Digit Precision Multimeter (incl. software + cable)	1200.00
Fluke 8846A/SU 240V	2675380	6.5 Digit Precision Multimeter (incl. software + cable)	1200.00
884X-CASE	2675552	Hard Case (8845A/8846A)	336.00
884X-RTD	2675468	100 OHM RTD Temperature Probe	441.00
884X-SHORT	2653346	4-wire short	26.00
884X-USB	2675479	USB to RS232 Cable Adapter	126.00
884X-1G	2675534	USB Memory 1 GB	35.00
8845A-EFPT	2742690	Extended Fine Point Tip Adapter Set	16.00
8845A-TPIT	2742683	Test Probe IC Tip Set	11.00
FVF-UG	1576741	FlukeView Forms Upgrade	114.00
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	237.00
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	129.00
RS43	946470	Serial Interface Cable	65.00
TL2X4W-PTII	2826215	2x4 Wire Ohms Test Lead 2 mm Probe Tip	63.00
TL2x4W-TWZ	2723629	2X4-Wire Ohms Tweezers Test Leads	95.00
Y8021	708289	IEEE-488 Shielded Interface Cable, 1 m	346.00
Y8022	708297	IEEE-488 Shielded Interface Cable, 2 m	407.00
Y8846S	2675518	Rack mount kit single (8845A/8846A)	105.00
Y8846D	2771721	Rack mount kit dual (8845A/8846A)	126.00
<b>Automotive Meters</b>			
Fluke 88V/A	2117440	Automotive Meter Combo Kit	577.00
<b>Clamp Meters</b>			
Fluke 323	4152628	True RMS Clamp Meter	113.00
Fluke 324	4152637	True RMS Clamp Meter	136.00
Fluke 325	4152643	True RMS Clamp Meter	181.00
Fluke 353	2840252	AC/DC True RMS Clamp Meter	492.00
Fluke 355	2840265	AC/DC True RMS Clamp Meter	645.00
Fluke 365	3790607	Detachable TRMS Clamp Meter	231.00
Fluke 368 FC	4709907	Wireless leakage current clamp, 40mm jaw	579.00
Fluke 369 FC	4709934	Wireless leakage current clamp, 61mm jaw	579.00
Fluke 373	3790564	600A TRMS Clamp Meter	212.00
Fluke 374FC	4696001	600A AC/DC TRMS Wireless Clamp Meter	319.00
Fluke 375FC	4695932	600A AC/DC TRMS Wireless Clamp Meter	363.00
Fluke 376FC	4695861	1000A AC/DC TRMS Wireless Clamp Meter with iFlex	442.00
Fluke 381	3610452	Remote Display TRMS Clamp Meter	528.00
Fluke 902 FC	4695814	TRMS Wireless HVAC ClampMeter	219.00
62MAX+/323/1AC Kit	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	219.00
Fluke 116/323 Kit	4296029	Fluke HVAC True RMS Multimeter and Clamp Meter Combo Kit	290.00
Fluke i2500-18	3676405	iFlex Probe	106.00
Fluke i2500-10	3676410	iFlex Probe	106.00
H3	1608458	Holster (330 Series)	36.00

Model	Art. nr	Description	GBP
<b>Electrical Testers</b>			
Fluke 1000FLT	4472387	Fluorescent Light Tester	216.00
T6-1000/EU	4910257	Electrical Tester with FieldSense™, round	245.00
T6-600/EU	4910322	Electrical Tester with FieldSense™, round	194.00
H-T6	4910585	T6 Belt Holster	26.00
Fluke T5-600	609377	Electrical Tester	137.00
T5-600/62MAX+/1AC kit	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	228.00
Fluke T5-1000	609385	Electrical Tester	147.00
Fluke T5-H5-1AC II Kit	2098640	Electrical Tester Kit with Holster and IAC	163.00
Fluke T90	4016945	Voltage/continuity tester	50.00
Fluke T110	4016950	Voltage/continuity tester with switchable load	71.00
Fluke T130	4016961	Voltage/continuity tester with LCD, switchable load	106.00
Fluke T150	4016977	Voltage/continuity tester with LCD, Ohms, switchable load	129.00
Fluke SM100	2406958	Socket Tester	22.00
Fluke 2042	2435038	Cable Locator (Transmitter + Receiver)	633.00
Fluke 2042T	2435045	Cable Locator Transmitter	323.00
Fluke 9040	2435061	Phase Rotation Indicator	198.00
Fluke 9062	2435089	Motor and Phase Rotation Indicator	173.00
LVD1	4571403	Volt Light	24.00
LVD2	2740300	Volt Light	33.00
H5	649365	Electrical Tester Holster (Fluke T5)	26.00
FTL660	2280204	Fused Test Lead Set	49.00
Fluke 1AC II	2432971	Volt Alert	26.00
Fluke 1AC II 5PK	2433056	Volt Alert 5-pack	100.00
FLK2AC/200-1000VC	3611972	ACV Detector 200-1000V	23.00
FLK2AC/200-1000VCL	3611985	ACV Detector 200-1000V	23.00
FLK2AC/200-1000V5L	3806493	Volt Alert, 200-1000V, 5-pack	87.00
FLK2AC/90-1000V	3807928	ACV Detector 90-1000V, Flat-tip	23.00
FLK2AC/90-1000V5PK	3807937	Volt Alert 90-1000V, 5-pack, Flat-tip	83.00
PRV240	4566209	Proving unit	115.00
Fluke 117/PRV240	4636971	Proving unit, Fluke 117 DMM Kit	249.00
PRV240FS	4910310	Proving unit, T6/NCV	123.00
<b>Laser Levels</b>			
Fluke-3PR	4811457	3 Point laser level, red	166.00
Fluke-3PG	4811469	3 Point laser level, green	183.00
Fluke-180LR	4811504	2 Line laser level, red	215.00
Fluke-180LG	4811491	2 Line laser level, green	255.00
Fluke-180LG System	4811519	Green line laser with LDG detector	313.00
Fluke-180LR System	4811528	Red line laser with LDR detector	271.00
Fluke-LDR	4811543	Laser line detector red	75.00
Fluke-LDG	4819919	Laser line detector green	85.00
PLS-20513	4791765	Tripod Telescope 9 FT 6 IN	154.00
PLS-20295	4845009	Magnetic Wall Bracket for PLS 3, 5,180,480	44.00
PLS-20512	4845027	Tripod Standard, 5/8 X 11	92.00
PLS-21502	4919812	Tripod Extender PLS3/180	9.00
<b>Distance Meters</b>			
Fluke 414D	4106830	Laser Distance Meter	115.00
Fluke 419D	4106853	Laser Distance Meter	219.00
Fluke 424D	4106866	Laser Distance Meter	336.00
414D/62MAX+ Kit	4296052	Fluke Laser distance meter and IR thermometer kit	193.00
<b>Battery Analyzers</b>			
Fluke BT510	4489970	Battery Analyzer	2239.00
Fluke BT520	4489981	Battery Analyzer	2800.00
Fluke BT521	4489996	Advanced Battery Analyzer	3149.00
<b>Battery Analyzer Accessories</b>			
BTL10	4542264	Standard Battery Analyzer Probes	277.00
BTL20	4542273	Intelligent Test Probe Set, w/Extenders (no temp sensor)	424.00
BTL21	4542286	Intelligent Test Probe Set, w/Extenders & Temp Sensor	527.00
BTL-A	4542258	Voltage/Current Probe Adapter	36.00
BC500	4542299	AC Power Charger	104.00
BP500	4542300	Lithium-ion battery, 7.4V 3000 mAh	92.00
BT500	4561297	Probe tip, 10x replacement Probe tips, 2x long probe tip covers, 2x short probe tip covers	107.00
i410	617727	AC/DC Current Clamp (400 A)	222.00
<b>Insulation Testers</b>			
Fluke 1503	2427883	Insulation Tester	329.00
Fluke 1507	2427890	Insulation Tester	429.00
Fluke 1550C	3665021	Insulation Resistance Tester (5kV)	3116.00
Fluke 1550C/Kit	3665127	Insulation Resistance Tester Kit (5kV)	3434.00
Fluke 1550C FC w/IR3000FC	4977402	Insulation Resistance Tester (5kV) with IR3000FC	3116.00

Model	Art. nr	Description	GBP
Fluke 1550C FC Kit w/IR3000FC	4977457	Insulation Resistance Tester Kit (5kV) with IR3000FC	3434.00
Fluke 1555	3665056	Insulation Resistance Tester (10kV)	3434.00
Fluke 1555/Kit	3665111	Insulation Resistance Tester Kit (10kV)	3752.00
Fluke 1555 FC w/IR3000FC	4977519	Insulation Resistance Tester (10kV) with IR3000FC	3434.00
Fluke 1555 FC Kit w/IR3000FC	4977469	Insulation Resistance Tester Kit (10kV) with IR3000FC	3752.00
Fluke 1577	2157280	Insulation Multimeter	518.00
Fluke 1587T	2517605	Insulation Multimeter (Telecom)	622.00
Fluke 1587 FC	4691215	2-IN-1 Insulation Multimeter	605.00
Fluke 1587/MDT FC	4692716	2-IN-1 Advanced Motor & Drive Troubleshooting Kit with 9040, I400	768.00
1587KIT/62MAX+ FC	4692778	2-IN-1 Advanced Electrical Troubleshooting Insulation Multi Kit with 62MAX+ I400	747.00
Fluke 1587/I400 FC	4692725	2-IN-1 Insulation Multimeter with Clamp i400	637.00
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	129.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	219.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	40.00

### Installation Testers

Fluke 1662 UK	4546915	Installation Tester w/mem UK	830.00
Fluke 1663 UK	4546971	Installation Tester w/RCD type B UK	1195.00
Fluke 1664FC UK	4547031	FC Installation Tester w/insulation pre-test UK	1345.00
Fluke 1664FC DMS UK	4547046	FC Installation Tester w/insulation pre-test DMS/UK	1559.00
Fluke 166X-MTC-UK	4601070	Fluke 166X-Main test cord, UK	45.00
Fluke DMS COMP	4718790	DMS Complete, Installation, PAT Software	464.00
Fluke DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	626.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	219.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	40.00
ES165X	2104706	Earth Spike Test Kit	129.00
MTC1363	2457400	Main Test Cord (BS1363)	48.00
TP165X	2107742	Remote Control Probe (1650 Series)	66.00
TL165X	2107756	Standard Test Lead Set (1650 Series)	94.00
ZERO ADAPTER	3261925	Zero adapter (165xB)	42.00

### Portable Appliance Testers

Fluke 6200-2 UK	4324466	Portable Appliance Tester UK	997.00
Fluke 6500-2 UK	4324475	Portable Appliance Tester UK	1420.00
Fluke 6500-2 UK Kit	4377132	Portable Appliance Tester, Kit UK	2025.00
Fluke 6200-2 UK Kit	4377198	Portable Appliance Tester, Kit, UK	936.70
APP1000	1992611	Barcode Appliance Number Labels 0-1000	111.00
APP2000	1992627	Barcode Appliance Number Labels 1001-2000	111.00
AUTO200B	2141221	Auto Code Label	38.00
BDST3	2796907	Snap Tag (cable tie)	28.00
BDST4	2796918	Snap Tag (clip on)	28.00
CD-Card	4045991	Compact Flash Memory Card	29.00
Fluke DMS COMP	4718790	DMS Complete, Installation, PAT Software	464.00
Fluke DMS COMPL/PROF	4718803	DMS Complete/Professional, Installation, PAT Software	626.00
EXTL100	2414348	Extension Lead Test Adaptor	16.00
IRP1	1993496	PAT Register	13.00
SP1000	1597281	Mini Printer	492.00
TA700	2389678	Appliance Adaptor for 110V tools	36.00
PASS500S	2141138	Appliance Pass Labels (rectangular)	29.00
PASS560R	2141192	Appliance Pass Labels (round)	57.00
SP6000 Printer	4325128	Printer for Portable Appliance Testers	510.00
SPSCAN6000	4325143	Scanner for Portable Appliance Testers	325.00
FAIL250	2095376	Appliance Fail Labels	22.00

### Earth Ground Testers

Fluke 1630-2 FC	4829532	Earth Ground Loop and Leakage Clamp	1158.00
Fluke 1630-2	4829515	Earth Ground Loop and Leakage Clamp (non FC)	1158.00
Fluke 1623-2	4325155	Basic Geo Earth Ground Tester	1175.00
Fluke 1625-2	4325162	Advanced Geo Earth Ground Tester	1880.00
Fluke 1623-2 Kit	4325170	Basic Geo Earth Ground Tester, Kit	1937.00
Fluke 1625-2 Kit	4325181	Advanced Geo Earth Ground Tester, Kit	2737.00
Earth Stake	4325492	Geo Earth Ground Tester, Earth stake	57.00
Cable Reel 25M BL	4343731	25M Blue, Ground/Earth Cable Reel, 25M Wire	57.00
Cable Reel 25M GR	4343746	25M Green, Ground/Earth Cable Reel, 25M Wire	57.00
Cable Reel 50M RD	4343754	50M Red, Ground/Earth Cable Reel, 50M Wire	63.00
C1620	4359042	Carrying Case	183.00
ES-162P3-2	4359377	Earth Ground Stake Set for 3 Pole Measurement	217.00
ES-162P4-2	4359389	Earth Ground Stake Set for 4 Pole Measurement	288.00

### Indoor Air Quality Tools

Fluke 922	2679822	Airflow Meter	523.00
Fluke 922/Kit	2679831	Airflow Meter Kit	614.00
Fluke 971	2418208	Temperature Humidity Meter	207.00
Fluke 975	2519364	AirMeter	1675.00

Model	Art. nr	Description	GBP
Fluke 975V	2666111	AirMeter with Velocity	1913.00
Fluke CO-220	664711	Carbon Monoxide Meter	470.00
Fluke RLD2	3387163	Leak Detector Flashlight	47.00
CO-205	664714	Aspirator Kit	141.00
975VP	2631538	Air Velocity Probe	356.00
PT12	2740212	Pitot Tube, 12	89.00
Fluke 985	4131397	Airborne Particle Counter	3775.00

### Digital Thermometers

Fluke 51 II	1281142	Thermometer	275.00
Fluke 52 II	1281139	Thermometer	355.00
Fluke 53 II B	3821062	Single Input Thermometer, 60Hz	399.00
Fluke 53 II B	3821096	Single Input Thermometer, 50Hz	399.00
Fluke 54 II B	3821070	Dual Input Thermometer, 60Hz	479.00
Fluke 54 II B	3821081	Dual Input Thermometer, 50Hz	479.00
Fluke 61	1643896	Infrared Thermometer	159.00
Fluke 62 MAX	4130474	Infrared thermometer	85.00
Fluke 62 MAX+	4130488	Infrared Thermometer	89.00
T5-600/62MAX+/1AC kit	4297126	Electrical Tester, IR Thermometer and Voltage Detector Kit	228.00
414D/62MAX+ Kit	4296052	Fluke Laser distance meter and IR thermometer kit	193.00
62MAX+/323/1AC Kit	4296076	IR Thermometer, Clamp Meter and Voltage Detector Kit	219.00
116/62MAX+ Kit	4296018	Fluke HVAC Multimeter and IR Thermometer Combo Kit	279.00
Fluke 63	2148281	Infrared Thermometer	219.00
Fluke 64 MAX	4856105	Multifunction IR Thermometer 20:1 D:S	109.00
Fluke 561	2558118	Multipurpose Thermometer	159.00
Fluke 566	2837799	Multipurpose Thermometer	375.00
Fluke 568	2837806	Multipurpose Thermometer	475.00
Fluke 568Ex	4321662	Intrinsically safe Infrared Thermometer	1129.00
Fluke 572-2	4328074	Infrared Thermometer	559.00
Fluke FP	2644169	FoodPro Thermometer	89.00
Fluke FP Plus	2477950	FoodPro Plus Thermometer	169.00
C50	762823	Soft Meter Case	33.00
H6	2152040	Infrared Thermometer Holster (Fluke 63/65/68/561)	25.00
80PR-60	2148313	RTD Temperature Probe (Fluke 66/68)	64.00

### Visual Thermometers

Fluke VT04	4366444	Visual IR Thermometer	465.00
Fluke VT04A	4485211	Visual IR thermometer	429.00
Fluke charger VT04	4375752	Charger & adapter set VT04	40.00
Fluke Battery, VT04	4375741	Li-ion battery VT04	40.00

### Industrial Imaging

Fluke DS701	4962652	Diagnostic Videoscope	1499.00
Fluke DS703 FC	4962665	High Resolution Diagnostic Videoscope with FC	1759.00
Fluke 3.8mm Scope	4962690	3.8 mm Scope, 1 m Probe, Forward View	619.00
Fluke 8.5mm Scope	4962708	8.5 mm Scope, 3 m Probe, Dual View	529.00
Fluke 5.5 mm Scope	4962713	5.5 mm Scope, 1 m Probe, Dual View	439.00
Fluke 8.5 mm Scope	4962749	8.5 mm Scope, 1.2 m Probe, Dual View	179.00
Fluke 8.5 mm UV Scope	4962751	8.5 mm UV Scope, 1 m Probe, Dual View	619.00
Fluke 9 mm Scope	4962760	9 mm Scope, Forward View, 20 m Probe Reel	1759.00
Fluke DS 7XX Neckstrap	4962772	DS 7XX Neckstrap	49.00

### Thermal Imagers

#### Thermal Imagers - Performance Series

Fluke TIS10 9Hz	4697036	Thermal imager, fixed focus	1039.00
Fluke TIS20 9Hz	4697049	Thermal imager, fixed focus	1249.00
Fluke TIS40 9Hz	4697051	Thermal imager, fixed focus	1719.00
Fluke TIS45 30Hz	4697072	Thermal imager, manual focus	2129.00
Fluke TIS45 9Hz	4697060	Thermal imager, manual focus	2129.00
Fluke TIS50 9Hz	4697085	Thermal imager, fixed focus	2329.00
Fluke TIS55 30Hz	4697106	Thermal imager, manual focus	2649.00
Fluke TIS55 9Hz	4697097	Thermal imager, manual focus	2649.00
Fluke TIS60 9Hz	4697114	Thermal imager, fixed focus	2949.00
Fluke TIS65 30Hz	4697138	Thermal imager, manual focus	3243.00
Fluke TIS65 9Hz	4697123	Thermal imager, manual focus	3249.00
Fluke TIS75 30Hz	4754443	Thermal Imager, Manual Focus	3499.00
Fluke TIS75 9Hz	4754437	Thermal Imager, Manual Focus	3499.00

#### Thermal Imagers - Professional Series

Fluke Ti200 9Hz	4335298	Thermal Imager, 9Hz	4359.00
Fluke Ti200 60Hz	4335306	Thermal Imager, 60Hz	4359.00
Fluke Ti300 9Hz	4335314	Thermal Imager, 9Hz	4765.00
Fluke Ti300 60Hz	4335323	Thermal Imager, 60Hz	4765.00

Model	Art. nr	Description	GBP
Fluke Ti300-PRO 9 Hz	4947261	Thermal Imager, 240x180; 9 Hz	5299.00
Fluke Ti300-PRO 60 Hz	4947250	Thermal Imager, 240x180; 60 Hz	5299.00
Fluke Ti400 9Hz	4335338	Thermal Imager, 9Hz	5780.00
Fluke Ti400 60Hz	4335345	Thermal Imager, 60Hz	5780.00
Fluke Ti400-PRO 9 Hz	4947289	Thermal Imager, 320x240; 9 Hz	7169.00
Fluke Ti400-PRO 60 Hz	4947277	Thermal Imager, 320x240; 60 Hz	7169.00
Fluke TI450 9HZ	4764729	Thermal Imager, Manual Focus	7149.00
Fluke TI450 60Hz	4764707	Thermal Imager, Manual Focus	7149.00
Fluke Ti450 PRO 9HZ	4947303	Fluke Ti450 PRO 9Hz Thermal Imager	7249.00
Fluke Ti450 PRO 60Hz	4947292	Fluke Ti450 PRO 60Hz Thermal Imager	7249.00
Fluke Ti450 SF6 60Hz	4907176	SF6 Gas leak detection, Thermal Imager	14399.00
Fluke TI480 9Hz	4842105	Thermal Imager; 640x480; 9 HZ, SR	11999.00
Fluke TI480 60Hz	4842086	Thermal Imager; 640x480; 60 HZ, SR	11999.00
Fluke Ti480 PRO 9HZ	4947332	Fluke Ti480 PRO 9Hz Thermal Imager	12099.00
Fluke Ti480 PRO 60HZ	4947326	Fluke Ti480 PRO 60Hz Thermal Imager	12099.00

### Thermal Imagers - Expert Series

Fluke TiX500 9HZ	4736664	Thermal Imager; 320x240; 9 HZ	7299.00
Fluke TiX500 60HZ	4736635	Thermal Imager; 320x240; 60 HZ	7399.00
Fluke TiX520 9 Hz	4596742	Thermal Imager; 320 x 240; 9 Hz	9539.00
Fluke TiX520 9Hz/NFC	4597027	Thermal Imager; 320 x 240; Non-FC; 9 Hz	9539.00
Fluke TiX520 60 Hz	4596717	Thermal Imager; 320 x 240; 60 Hz	9539.00
Fluke TiX560 9Hz	4597094	Thermal Imager; 320 x 240; IS	11159.00
Fluke TiX560 9Hz/NFC	4597100	Thermal Imager; 320 x 240; Non-FC; 9 Hz	11159.00
Fluke TiX560 60 Hz	4597066	Thermal Imager; 320 x 240; IS	11159.00
Fluke TiX580 60Hz	4842073	Thermal Imager; 640x480; 60 HZ, SR	14299.00
Fluke TiX580 9Hz	4841945	Thermal Imager; 640x480; 9 HZ, SR	14299.00
Fluke RSE300 9Hz	4948166	Thermal Imager; 320x240; 9 Hz	10779.00
Fluke RSE300 60Hz	4944776	Thermal Imager; 320x240; 60 Hz	10779.00
Fluke RSE600 9Hz	4948175	Thermal Imager; 640x480; 9 Hz	14099.00
Fluke RSE600 60Hz	4944826	Thermal Imager; 640x480; 60 Hz	14099.00

### Thermal Imagers Accessories (general)

Ti-Visor2	3996500	Sun Visor	69.00
Ti-Visor3	4335377	Thermal imager visor	75.00
Ti-Tripod	3511872	Tripod Mounting Base	95.00
Ti-Tripod2	3996517	Mounting Base	79.00
Ti-Tripod3	4335389	Tripod mounting base accessory	93.00
FLK-LENS/TELE1	3441176	Telephoto Infrared Lens (Ti32/TiR32)	1154.00
FLK-LENS/WIDE1	3441183	Wide-angle Infrared Lens (Ti32/TiR32)	1154.00
FLK-LENS/TELE2	4335350	Telephoto Infrared Lens (Ti200/Ti300/Ti400)	1234.00
FLK-LENS/WIDE2	4335361	Wide-angle Infrared Lens (Ti200/Ti300/Ti400)	1139.00
Fluke lens/4xTELE2	4607058	4x Telephoto IR lens for TiX560-TiX520-Ti400-Ti300-Ti200	4599.00
Fluke lens/25MAC2	4607064	25Micron Macro IR lens for TiX560-TiX520	3319.00
Ti-Car Charger	3039779	Ti Car Charger (TiR/TiR1/Ti10/Ti20/Ti25)	99.00
Ti20-RBP	2577796	Rechargeable Battery Pack (Ti20)	151.00
FLK-TI-SBP3	3440365	Extra battery (Ti32/TiR32)	116.00
Fluke TI-SBC3B	4354922	Charging base (Ti200/Ti300/Ti400)	169.00
Fluke TiX5xx-Neck	4574715	Adjustable neck strap	29.00
Fluke TiX5xx-SBP4	4597142	Additional Smart Battery	119.00
Fluke TiX5xx Hand	4574703	Adjustable hand strap	15.00
Fluke TiX5xx-HDMI	4615511	HDMI video cable	19.00
Fluke TiX5x-Lens Cap	4550697	Lens cap	15.00
Fluke TI-Bluetooth	4603258	Bluetooth headset	69.00

### Thermal Imagers IR-Windows

FLK-050-CLKT	3460346	50mm C-Range IR Windows, Kwik twist	139.00
FLK-075-CLKT	3460387	75 mm C-Range IR Window, Kwik Twist	179.00
FLK-100-CLKT	3460439	100mm C-Range IR Window, Kwik Twist	249.00
Fluke CV200	4326955	50mm IR Window, hand turn door latch	179.00
Fluke CV300	4326962	75mm IR Windows, hand turn door latch	249.00
Fluke CV301	4338164	75mm IR Windows, security turn door latch	249.00
Fluke CV400	4326996	100 mm IR Windows, hand turn door latch	339.00
Fluke CV401	4338173	100 mm IR Windows, security turn door latch	349.00

## ScopeMeters

### Industrial ScopeMeter

Fluke 123B/EU	4755659	Industrial ScopeMeter 20MHZ, EU	1190.00
Fluke 123B/UK	4755671	Industrial ScopeMeter 20MHZ, UK	1190.00
Fluke 123B/INT	4755710	Industrial ScopeMeter 20MHZ, INT	1190.00
Fluke 124B/EU	4755731	Industrial ScopeMeter 40MHZ, EU	1429.00
Fluke 124B/UK	4755754	Industrial ScopeMeter 40MHZ, UK	1429.00
Fluke 124B/INT	4755793	Industrial ScopeMeter 40MHZ, INT	1429.00

Model	Art. nr	Description	GBP
Fluke 125B/EU	4755818	Industrial ScopeMeter 40MHZ, EU	1705.00
Fluke 125B/UK	4755834	Industrial ScopeMeter 40MHZ, UK	1705.00
Fluke 125B/INT	4755876	Industrial ScopeMeter 40MHZ, INT	1705.00
Fluke 123B/EU/S	4755890	Industrial ScopeMeter + SCC 20MHZ, EU	1508.00
Fluke 123B/UK/S	4755911	Industrial ScopeMeter + SCC 20MHZ, UK	1508.00
Fluke 123B/INT/S	4755953	Industrial ScopeMeter + SCC 20MHZ, INT	1508.00
Fluke 124B/EU/S	4755975	Industrial ScopeMeter + SCC 40MHZ, EU	1745.00
Fluke 124B/UK/S	4755994	Industrial ScopeMeter + SCC 40MHZ, UK	1745.00
Fluke 124B/INT/S	4756031	Industrial ScopeMeter + SCC 40MHZ, INT	1745.00
Fluke 125B/EU/S	4756054	Industrial ScopeMeter + SCC 40MHZ, EU	2023.00
Fluke 125B/UK/S	4756079	Industrial ScopeMeter + SCC 40MHZ, UK	2023.00
Fluke 125B/INT/S	4756112	Industrial ScopeMeter + SCC 40MHZ, INT	2023.00

### 190 Series ScopeMeters

Fluke 190-204/UN	3894411	ScopeMeter 4 Channel 200 MHZ Color	4190.00
Fluke 190-204/UK	3894453	ScopeMeter 4 Channel 200 MHZ Color	4190.00
Fluke 190-204/UN/S	3894482	ScopeMeter 4 Channel 200 MHZ Color UNI SCC	4557.00
Fluke 190-204/UK/S	3894525	ScopeMeter 4 Channel 200 MHZ Color UK SCC	4557.00
Fluke 190-104/UN	3894557	ScopeMeter 4 Channel 100 MHZ Color UNI	3637.00
Fluke-190-104/UK	3894591	ScopeMeter 4 Channel 100 MHZ Color UK	3637.00
Fluke 190-104/UN/S	3894621	ScopeMeter 4 Channel 100 MHZ Color UNI SCC	4005.00
Fluke 190-104/UK/S	3894663	ScopeMeter 4 Channel 100 MHZ Color UK SCC	3926.00
Fluke 190-062/UN	4025171	ScopeMeter 2 Channel 60MHZ Color	2661.00
Fluke 190-062/UK	4025198	ScopeMeter 2 Channel 60MHZ Color	2661.00
Fluke 190-062/UN/S	4025248	ScopeMeter 2 Channel 60MHZ Color SCC	3029.00
Fluke 190-062/UK/S	4025266	ScopeMeter 2 Channel 60MHZ Color SCC	3029.00
Fluke 190-102/UN	4025329	ScopeMeter 2 Channel 100MHZ Color SCC	3316.00
Fluke 190-102/UK	4025341	ScopeMeter 2 Channel 100MHZ Color	3316.00
Fluke 190-102/UN/S	4025390	ScopeMeter 2 Channel 100MHZ Color SCC	3682.00
Fluke 190-102/UK/S	4025424	ScopeMeter 2 Channel 100MHZ Color SCC	3682.00
Fluke 190-202/UN	4025472	ScopeMeter 2 Channel 200MHZ Color	3759.00
Fluke 190-202/UK	4025497	ScopeMeter 2 Channel 200MHZ Color	3759.00
Fluke 190-202/UN/S	4025568	ScopeMeter 2 Channel 200MHZ Color SCC	4127.00
Fluke 190-202/UK/S	4025587	ScopeMeter 2 Channel 200MHZ Color SCC	4127.00
Fluke 190-502/EU	4025623	ScopeMeter 2 Channel 500 MHZ Color	4085.00
Fluke 190-502/UN	4025638	ScopeMeter 2 Channel 500 MHZColor UNI	4085.00
Fluke 190-502/UK	4025650	ScopeMeter 2 Channel 500 MHZ Color UK	4085.00
Fluke 190-502/EU/S	4025692	ScopeMeter 2 Channel 500 MHZ Color Europe SCC	4409.00
Fluke-190-502/UN/S	4025704	ScopeMeter 2 Channel 500 MHZ Color UNI SCC	4409.00
Fluke 190-502/UK/S	4025728	ScopeMeter 2 Channel 500 MHZ Color UK SCC	4409.00
Fluke 190-504/EU	4419875	ScopeMeter 4 Channel 500MHz Color	4397.00
Fluke 190-504/UK	4419918	ScopeMeter 4 Channel 500MHz Color UK	4397.00
Fluke 190-504/UN	4419929	ScopeMeter 4 Channel 500MHz Color UNI	4397.00
Fluke 190-504/UK/S	4419983	ScopeMeter 4 Channel 500MHz Color UK SCC	4724.00
Fluke 190-504/UN/S	4419990	ScopeMeter 4 Channel 500MHz Color UNI SCC	4724.00

### ScopeMeter Accessories

AC120	646163	Heavy Duty Alligator Clips	40.00
AS400	3894880	Probe Extension Set, for VPS400 Probes	95.00
BB120	646171	Banana to BNC Adapter Plug	45.00
BB120-II	4744369	Set of 2 banana to BNC adapter	37.00
BC190/808	1282244	Battery Charger/Line Voltage Adapter UNIVERSAL (190 Series)	163.00
BHT190	3379374	Set of Break-out Adapters	262.00
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	89.00
BP190	677390	NiMH Battery Pack (190 Series)	189.00
BP290	4025762	Battery Pack Single Cap 190-series II	222.00
BP291	3894688	Battery Pack, Fluke 190 Series	286.00
C120	646189	Hard Case (43B/120 Series)	95.00
C120B	4744391	Soft carrying case for 120B series	108.00
C125	646858	Soft Meter Case	45.00
C190	677401	Hard Case (190 Series)	232.00
C195	677408	Soft Case	219.00
C290	3894803	Hard-Shell Carrying Case	194.00
CS20MA	677393	Current Shunt 4-20 mA	85.00
EBC290	3894906	External Battery Charger	90.00
HC120	646668	Hook Clips	51.00
HC120-II	4744357	Set of 2 hook clips	41.00
HC200	2086410	Hook Clips	34.00
HH290	3894844	Hanging Hook, ScopeMeter Series 190 II	64.00
MA190	1567481	Medical Accessory Kit (190 Series)	399.00
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	144.00
PM8907/804	614013	Battery Charger/Line Voltage Adapter UK (120 Series)	108.00
PM8907/807	624764	POWER ADAPTOR/BATTERY CHARGER	106.00
PM8907/808	614039	Battery Charger/Line Voltage Adapter UNIVERSAL (120 Series)	129.00
PM9080	1641983	Serial Interface Adapter/Cable (RS232)	238.00

Model	Art. nr	Description	GBP
PM9081	916093	Dual Banana Plug to Female BNC Adapter	46.00
PM9082	916163	Dual Banana Jack to Male BNC Adapter	50.00
PM9091	935598	Coaxial BNC Cables (1.5 m)	108.00
PM9092	935601	Coaxial BNC Cables (0.5 m)	92.00
PM9093	935593	Male BNC to Female BNC Adapter	67.00
PM9096/201	651742	Secondary Pick-up	298.00
RS120-III	4023947	Probe Accessory Replacement Set	95.00
RS400	3894867	Probe Replacement Set, for VPS400 Probes	73.00
RS500	4025886	Probe accessory replacement set for VPS500 probes	132.00
SCC120B	4744423	Software soft carry case accessory kit 120B series	397.00
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	409.00
SCC128	2100199	Automotive Accessory Kit (120 Series)	628.00
SCC198	2100208	Automotive Accessory Kit (190 Series)	787.00
SCC190	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	570.00
SCC290	3894826	Software and Carrying Case for 190 Series II	368.00
SP120B	4744414	Screen protector for 120B series	37.00
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	222.00
STL120-III	4023901	Shielded Test Lead	168.00
STL120-IV	4744340	Shielded test lead set 600V CAT IV	128.00
SW90W	3894923	FlukeView Software	333.00
TAS90	614187	Automotive Accessory Set (120/190 Series)	59.00
TRM50	4025864	50 Ohm feed-through terminator BNC	159.00
UA120	4744384	USB Connector adapter	37.00
VPS41	4744378	Voltage probe set 40 MHZ 600V CAT IV	123.00
VPS101	3086317	1:1 Voltage Probe Set, black, 30 MHz, 1.2m	203.00
VPS210-G	3086247	10:1 Voltage Probe Set, grey, 200 MHz, 1.2m	203.00
VPS210-R	3086235	10:1 Voltage Probe Set, 1 red, 200 MHz, 1.2m	203.00
VPS212-G	3086286	10:1 Voltage Probe Set, grey, 200 MHz, 2.5m	203.00
VPS212-R	3086273	10:1 Voltage Probe Set, red, 200 MHz, 2.5m	203.00
VPS220-G	3086300	100:1 Voltage Probe Set, grey, 200 MHz, 1.2m	203.00
VPS220-R	3086299	100:1 Voltage Probe Set, red, 200 MHz, 1.2m	203.00
VPS40-III	4023920	Voltage Probe	104.00
VPS410-II-B	4276937	Industrial Voltage Probe Set 500 MHz 10:1 Blue	179.00
VPS410-II-G	4276943	Industrial Voltage Probe Set 500 MHz 10:1 Grey	179.00
VPS410-II-R	4276928	Industrial Voltage Probe Set 500 MHz 10:1 Red	179.00
VPS410-II-V	4276955	Industrial Voltage Probe Set 500 MHz 10:1 Green	179.00
VPS420-R	3894783	High Working Voltage Probe 100:1 Red & Black	221.00
VPS420-B	4411541	High Working Voltage Ruggedized Probe; Blue/Black	217.00
VPS420-G	4411565	High Working Voltage Ruggedized Probe; Grey/Black	217.00
VPS420-V	4411583	High Working Voltage Ruggedized Probe; Green/Black	217.00
VPS510-R	4025781	Voltage Probe set 500 MHZ 10:1 Red	179.00
VPS510-B	4025796	Voltage probe set 500 MHZ 10:1 Blue	179.00
VPS510-G	4025801	Voltage probe set 500 MHZ 10:1 Grey	179.00
VPS510-V	4025812	Voltage probe set 500 MHZ 10:1 Green	179.00

### Power Quality Tools

Fluke 345	2584181	Power Quality Clamp Meter	1355.00
Fluke 430-II/MA	4779032	430-II Motor Analyzer Upgrade Kit	1698.00
Fluke 434-II/BASIC	4116650	Power Quality and energy analyzer (w/o clamps)	3643.00
Fluke 434-II	4116638	Power Quality and energy analyzer	4210.00
Fluke 434-II/INTL	4778918	Power Quality and energy analyzer/International	4210.00
Fluke 435-II	4116661	Power Quality & Energy Analyzer	5265.00
Fluke 435-II/BASIC	4116689	Advanced Power Quality and energy analyzer (w/o clamps)	4684.00
Fluke 435-II/INTL	4778929	Power Quality and energy analyzer/International	5265.00
Fluke 437-II	4116692	Power Quality & Energy Analyzer	7640.00
Fluke 437-II/BASIC	4116719	400 Hz Power Quality and Energy Analyzer (w/o clamps)	7035.00
Fluke 437-II/INTL	4778934	Power Quality and energy analyzer/International	7640.00
Fluke 438-II	4778976	Power Quality & Motor Analyzer	6204.00
Fluke 438-II/BASIC	4778990	Power Quality & Motor Analyzer, without clamps and FC WiFi SD Card	5676.00
Fluke 438-II/INTL	4779015	Power Quality & Motor Analyzer, without FC WiFi SD Card	6204.00
Fluke 1732/EUS	4706548	Energy Logger, EU/US version	2201.00
Fluke 1732/INTL	4706553	Energy Logger, international version	2201.00
Fluke 1732/B	4706566	Energy Logger, basic version	1927.00
Fluke 1732/Upgrade	4920958	Upgrade kit for 1732 to 1734	237.00
Fluke 1734/EUS	4706594	Energy Logger, EU/US advanced version	2464.00
Fluke 1734/INTL	4706608	Energy Logger, international advanced version	2464.00
Fluke 1734/B	4706582	Energy Logger, advanced version no flexis	2201.00
Fluke 1734/WINTL	4710227	Energy Logger, wireless international	2464.00
Fluke 1736/EUS	4534519	3-Phase Power Logger, EU/US version	3227.00
Fluke 1736/B	4563561	3-Phase Power Logger, basic version	3067.00
Fluke 1736/INTL	4563550	3-Phase Power Logger, International version	3227.00
Fluke 1738/EUS	4563577	3-Phase Power Logger, EU/US Advanced version no flexis	3805.00
Fluke 1738/B	4588378	3-Phase Power Logger, advanced version no flexis	3017.00
Fluke 1738/INTL	4588384	3-Phase Power Logger, international advanced version	3805.00



Model	Art. nr	Description	GBP
Fluke 1742/15/EUS	4920613	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	3279.00
Fluke 1742/30/EUS	4920651	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	3279.00
Fluke 1742/B/EUS	4920660	Power Quality Logger without iFlex, EUS version	2997.00
Fluke 1742/15/INTL	4920672	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	3279.00
Fluke 1742/30/INTL	4920685	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	3279.00
Fluke 1742/B/INTL	4920697	Power Quality Logger without iFlex, INTL version	2997.00
1742-6/Upgrade	4920964	1742 to 1746 Upgrade	1604.00
1742-8/Upgrade	4920973	1742 to 1748 Upgrade	2967.00
Fluke 1746/15/EUS	4920703	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	4498.00
Fluke 1746/30/EUS	4920715	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	4498.00
Fluke 1746/B/EUS	4920726	Power Quality Logger without iFlex, EUS version	4217.00
Fluke 1746/15/INTL	4920732	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	4498.00
Fluke 1746/30/INTL	4920744	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	4498.00
Fluke 1746/B/INTL	4920759	Power Quality Logger without iFlex, INTL version	4217.00
1746-8/Upgrade	4920986	1746 to 1748 Upgrade	1604.00
Fluke 1748/15/EUS	4920767	Power Quality Logger with 60 cm 1,500A iFlex, EUS version	5625.00
Fluke 1748/30/EUS	4920771	Power Quality Logger with 60 cm 3,000A iFlex, EUS version	5625.00
Fluke 1748/B/EUS	4920780	Power Quality Logger without iFlex, EUS version	5343.00
Fluke 1748/15/INTL	4920798	Power Quality Logger with 60 cm 1,500A iFlex, INTL version	5625.00
Fluke 1748/30/INTL	4920800	Power Quality Logger with 60 cm 3,000A iFlex, INTL version	5625.00
Fluke 1748/B/INTL	4920817	Power Quality Logger without iFlex, INTL version	5343.00
Fluke 1760 Basic	2630732	Power Quality Recorder (three-phase), Topas	10854.00
Fluke 1760	2630744	Power Quality Recorder (three-phase), Topas	12574.00
Fluke 1760TR Basic	2637629	Power Quality Recorder (three-phase), Topas	14872.00
Fluke 1760TR	2637634	Power Quality Recorder (three-phase), Topas	16596.00
Fluke VR1710	3030923	Single-Phase Voltage Quality Recorder	671.00
C1740	4116762	Softcase for 174X and 43X-II PQ analyzer	193.00
C437-II	4116743	Hard case 430 Series II with rollers	444.00
EPE-Training-E/EMEA	4792349	Fluke EPE Training Set - English	159.00
Fluke-435-II/EPE-E	4816735	Fluke-435-II, PQ and Energy Analyzer plus EPE training - English	5271.00

#### Power Quality Tools Accessories

1743/1744 Poleset	3024485	Pole Mounting Kit (Fluke 1743/1744)	38.00
3140R	2650136	Clip-on Current Transformer 2A-400A (Fluke 1750)	366.00
3210-PR-TF-II	4531769	1000A Fluke 1750 Thin flexi 61cm	579.00
3310-PR-TF-II	4531778	5000A Fluke 1750 Thin flexi 61cm	810.00
3PHVL-1730	4344712	Cable Assembly, Voltage Test Lead 3-Phase+N (1730)	73.00
3312-PR-TF-II	4531784	5000A Fluke 1750 Thin flexi 122cm	980.00
BP120MH	2544081	NiMH Battery Pack (120 Series/43B)	89.00
BE345	2839604	Battery Eliminator (Fluke 345)	131.00
BP1730	4389436	Li Ion Battery Pack 3.7V 2500mAh (1730)	36.00
C120	646189	Hard Case (43B/120 Series)	95.00
C17xx	4637381	Soft Case	92.00
CS1750	2673962	Soft Case (Fluke 1750/1760)	243.00
1730 Hanger	4358028	Hanger kit (1730)	51.00
1730 Cable	4395217	Cable,AUX input cable (1730)	23.00
1750/Case	2650124	Hard Case (Fluke 1750)	518.00
FLUKE-1736/UPGRADE	4563589	UPGRADE KIT FOR 1736 TO 1738	628.00
1750/Seat-L	2673937	Fluke Power Analyze - Additional SEAT LICENSE	1018.00
1750/Site-L	2673928	Fluke Power Analyze - Additional SITE LICENCE	5090.00
FS17X5-TF-II	4531791	3000A 4-PH Fluke 1735 & 1745 Thin flexi set	1361.00
FS17XX IP65-TF-II	4531804	3000A IP65 4-PH Fluke 1743/4 Thin flexi set	1478.00
FS17XX-1PH-TF-II	4531819	FS3000A/6000A 4-PH 36-Inch Thin flexi set	343.00
FLUKE-173X ADPT	4717827	AUX input adapter, 173X	106.00
Fluke 17xx TL 0.1M	4715389	Test lead set for Fluke 173x; 0.1m	35.00
Fluke 17xx TL 1.5M	4715392	Test lead set for Fluke 173x; 1.5m	24.00
FS3000/6000A-TF-4-II	4531828	FS3000A/6000A 4-PH 36-Inch thin flexi set	1456.00
GPS430-II	4693803	GPS Synchronization module (430-II series)	1220.00
GPS-Time Sync	2539223	GPS Time Synchronization Module (Fluke 1760)	354.00
i17XX-flex1500	4637328	Fluke-17xx iFlexi 1500A 12 IN	131.00
i17XX-flex3000	4637343	Fluke-17xx iFlexi 3000A 24 IN	139.00
i17XX-flex6000	4637362	Fluke-17xx iFlexi 6000A 36 IN	149.00
i17XX-flex1500/3pk	4637337	Fluke-17xx iFlexi 1500A 12 IN, 3 pack	380.00
i17XX-flex3000/3pk	4637355	Fluke-17xx iFlexi 3000A 24 IN, 3 pack	407.00
i17XX-flex6000/3pk	4637370	Fluke-17xx iFlexi 6000A 36 IN, 3 pack	433.00
i17XX-Flex1500/4PK	4637411	Fluke-17xx iFlexi 1500A 12 IN, 4 Pack	497.00
i17XX-Flex3000/4PK	4637427	Fluke-17xx iFlexi 3000A 24 IN, 4 Pack	533.00
i17XX-Flex6000/4PK	4637430	Fluke-17xx iFlexi 6000A 36 IN, 4 Pack	566.00
i1A/10A Clamp PQ1	3345753	1-phase Mini Current Clamp Set	441.00
i1A/10A Clamp PQ3	3024413	3-phase Mini Current Clamp Set	445.00
i1A/10A Clamp PQ4	3024424	4-phase Mini Current Clamp Set	599.00
i5A/50A Clamp PQ1	3345766	1-Phase 5A/50A Mini Current Clamp set for PQ	441.00
i5A/50A Clamp PQ3	3024436	3-phase Mini Current Clamp Set	445.00
i5A/50A Clamp PQ4	3024449	4-phase Mini Current Clamp Set	599.00
i20/200A Clamp PQ3	3024451	3-phase Mini Current Clamp Set	435.00

Model	Art. nr	Description	GBP
i20/200A Clamp PQ4	3024460	4-phase Mini Current Clamp Set	599.00
i40S-EL	4637396	Fluke-17xx i40s-EL Clamp-on Current Transformer	162.00
i40S-EL/3pk	4637409	Fluke-17xxx i40s-EL Clamp-on Current Transformer, 3 pack	463.00
i400	2277225	AC Current Clamp (400 A)	130.00
i400s	2277202	AC Current Clamp (400A)	235.00
i430-Flexi-TF-II	4531725	6000A Fluke 430 Thin Flexi 61cm	370.00
i430-Flexi-TF-II-4PK	4531733	6000A Fluke 430 Thin Flexi 61cm 4 Pack	1106.00
i5s	2508467	AC Current Clamp (5 A)	435.00
i5S-PR	3949761	1750, 5A Current Clamp	294.00
i5sPQ3	2457508	AC Current Clamp (5 A), 3-pack	1034.00
IEEE519/REPORT	4589748	SOFTWARE LICENSE FOR IEEE519 REPORTING	397.00
MP1-Magnet Probe 1	4589220	Magnet probes for 4 mm banana, set of 4	68.00
MBX USB-RS232	2539565	EPO328Z, USB to Serial RS232 Adapter	38.00
OC4USB	2166266	Serial Interface Adapter/Cable (USB)	144.00
PM9080	1641983	Serial Interface Adapter/Cable (RS232)	238.00
TLS430	2157713	Test Leads and Alligator Clips (4 black, 1 green) - 430 Series	103.00
TPS Clamp 10A/1A	2540445	Clip-on Current Transformer 10A/1A (Fluke 1760)	325.00
TPS Clamp 50A/5A	2540461	Clip-on Current Transformer 50A/5A (Fluke 1760)	325.00
TPS Clamp 200A/20A	2540450	Clip-on Current Transformer 200A/20A (Fluke 1760)	325.00
TPS Flex 18-TF-II	4531837	100/500A Fluke 1760 Thin Flexi 45cm (18in)	424.00
TPS Flex 24-TF-II	4531843	200/1000A Fluke 1760 Thin Flexi 61cm (24in)	424.00
TPS Flex 36-TF-II	4531855	3000/6000A Fluke 1760 Thin Flexi 91cm (36in)	847.00
TPS/MBX Dolph red	2540744	EPO326Z, Dolphin Clip, Red	19.00
TPS Nullmodem Cable	2540511	A550500510, RS232 Cross Link Cable, 3M	35.00
TPS Shunt 1A	2540548	A680501054, Shunt 1 A AC/DC	160.00
TPS Shunt 20MA	2540553	Shunt 20mA AC/DC (Fluke 1760)	270.00
TPS Voltprobe 10V	2540636	Voltage Probe 10V (Fluke 1760)	255.00
TPS Voltprobe 100V	2540624	Voltage Probe 100V (Fluke 1760)	255.00
TPS Voltprobe 400V	2540660	Voltage Probe 400V (Fluke 1760)	259.00
TPS Voltprobe 600V	2540697	Voltage Probe 600V (Fluke 1760)	259.00
TPS Voltprobe 1KV	2540649	Voltage Probe 1000V (Fluke 1760)	415.00
VL1735/45	3276205	Banana 4-Phase Voltage Lead set for Fluke-1735/45	217.00
Fluke MA-C8	4945842	Wall outlet adapter, Fluke-174X	19.00
IP65 Adapter Set	4946241	IP65 rated Voltage Connector	198.00
3PHVL-1730-5M	4920999	Cable assembly, voltage est lead 3-phase+N 5m	103.00
I17XX-FLEX1.5KIP	4921003	IP65 iFlexi 1.5KA 60 cm	198.00
I17XX-FLEX1.5KIP/3PK	4921015	IP65 iFlexi 1.5KA 60 cm, 3 Pack	474.00
I17XX-FLEX1.5KIP/4PK	4921026	IP65 iFlexi 1.5KA 60 cm, 4 Pack	632.00
I17XX-FLEX3KIPK	4921032	IP65 iFlexi 3KA 60 cm	198.00
I17XX-FLEX3KIP/3PK	4921044	IP65 iFlexi 3KA 60 cm, 3 Pack	474.00
I17XX-FLEX3KIP/4PK	4921067	IP65 iFlexi 3KA 60 cm, 4 Pack	632.00
I17XX-FLEX6KIPK	4921071	IP65 iFlexi 6KA 90 cm	237.00
I17XX-FLEX6KIP/3PK	4921080	iFlexi 6KA 90 cm, 3 Pack	553.00
I17XX-FLEX6KIP/4PK	4921098	iFlexi 6KA 90 cm, 4 Pack	711.00
I17XX-FLEX5M-EXT	4921116	iFlexi Extension Cable, 5m	118.00
Fluke 17XX-TL 0.18M	4921125	Test lead set; 1000V CAT III, Non-stack conn; 0.18 m; Red/Blk	31.00
Fluke 174X_3541-HANGER	4890129	Hanger Kit	56.00
Fluke 174X GPS-REC	4921133	GPS Receiver Antenna	285.00
F17XX Cable Markers	4921140	Cable Marker set, 05MM	47.00
MP1-3R/1B	4944790	3 red/1 black Magnet probe for 4 mm banana	79.00

### Vibration Testers

Fluke 805	4094385	Vibration Meter	1390.00
Fluke 805 FC	4489229	Vibration Meter with Fluke Connect	1390.00
Fluke 805/ES	4636786	External Vibration Sensor	820.00
Fluke 810	3542635	Vibration Tester	8131.00
Fluke 820-2	4550041	LED Stroboscope	769.00
Fluke 830	4454396	Laser Alignment Tool	6091.00
Fluke 830/Magnet	4528249	Magnetic Bracket	717.00
Fluke 830/Shims	4551330	Laser Alignment Tool, Shims	718.00
810S	3530828	Sensor	1302.00
810QDC	3530837	Quick Disconnect Cable	123.00
810SMM	3530862	Sensor Magnet Mount	174.00
810SMP	3530855	Sensor Mounting Pads (10-pack)	22.00
SBP-810	3530843	Smart Battery Pack	216.00
Fluke-810PA	3986002	AC Power Adapter with International Plug Set	70.00

### Process Calibrators

#### 700 Series Process Calibrators

Fluke 154 INTL	4805625	HART Calibration Assistant	3160.00
Fluke 705	665091	Loop Calibrator	616.00
Fluke 707	1617262	Loop Calibrator	745.00
Fluke 707Ex	2032187	Intrinsically Safe Loop Calibrator	987.00

Model	Art. nr	Description	GBP
Fluke 709	4234350	Precision Loop Calibrator	803.00
Fluke 709H	4234361	Precision HART Loop Calibrator	1257.00
Fluke 712B	4387857	RTD Temperature Calibrator	932.00
Fluke 714B	4387869	TC Temperature Calibrator	932.00
Fluke 715	620101	Volt/mA Calibrator	1128.00
Fluke 717 1G	2547166	Pressure Calibrator (68.9 mbar)	1190.00
Fluke 717-15G	4058808	Pressure Calibrator (1 bar)	1140.00
Fluke 717 100G	1630430	Pressure Calibrator (7 bar)	1157.00
Fluke 717 30G	662897	Pressure Calibrator (2 bar)	1148.00
Fluke 717 300G	2547175	Pressure Calibrator (20 bar)	1190.00
Fluke 717 500G	2547182	Pressure Calibrator (34.7 bar)	1190.00
Fluke 717 1000G	2547194	Pressure Calibrator (69 bar)	1190.00
Fluke 717 1500G	2547203	Pressure Calibrator (103.4 bar)	1299.00
Fluke 717 3000G	2547215	Pressure Calibrator (207 bar)	1299.00
Fluke 717 5000G	2547232	Pressure Calibrator (345 bar)	1299.00
Fluke 717-10000G	4058813	Pressure Calibrator (690 bar)	1257.00
Fluke 718 30G	665075	Pressure Calibrator (2 bar)	2096.00
Fluke 718 1G	2547148	Pressure Calibrator (68.9 mbar)	2278.00
Fluke 718 100G	665080	Pressure Calibrator (7 bar)	2096.00
Fluke 718 300G	2547153	Pressure Calibrator (20 bar)	2278.00
Fluke 718Ex 30G	2096310	Intrinsically Safe Pressure Calibrator (2 bar)	3108.00
Fluke 718Ex 100G	2096322	Intrinsically Safe Pressure Calibrator (7 bar)	3108.00
Fluke 718Ex 300G	3023328	Intrinsically Safe Pressure Calibrator (20 bar)	3153.00
Fluke 719 30G	3315332	Electric Pressure Calibrator (2 bar)	2870.00
Fluke 719 100G	3315344	Electric Pressure Calibrator (7 bar)	2870.00
Fluke-719PRO 30G	4353218	Electric Pressure Calibrator, 2 bar	2560.00
Fluke-719PRO 150G	4353229	Electric Pressure Calibrator, 10 bar	2560.00
Fluke-719PRO 300G	4353234	Electric Pressure Calibrator, 20 bar	2547.00
Fluke 720URTDA	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	152.00
Fluke-721-1601	4353241	Dual Sensor Pressure Calibrator, 1.1 bar, 6.9 bar	1791.00
Fluke-721-1603	4353283	Dual Sensor Pressure Calibrator, 1.1 bar, 20 bar	1791.00
Fluke-721-1605	4353327	Dual Sensor Pressure Calibrator, 1.1 bar, 34 bar	1791.00
Fluke-721-1610	4353366	Dual Sensor Pressure Calibrator, 1.1 bar, 69 bar	1759.00
Fluke-721-1615	4353401	Dual Sensor Pressure Calibrator, 1.1 bar, 103 bar	1791.00
Fluke-721-1630	4353447	Dual Sensor Pressure Calibrator, 1.1 bar, 200 bar	1759.00
Fluke-721-1650	4353486	Dual Sensor Pressure Calibrator, 1.1 bar, 345 bar	1759.00
Fluke-721-3601	4353252	Dual Sensor Pressure Calibrator, 2.48 bar, 6.9 bar	1791.00
Fluke-721-3603	4353290	Dual Sensor Pressure Calibrator, 2.48 bar, 20 bar	1791.00
Fluke-721-3605	4353330	Dual Sensor Pressure Calibrator, 2.48 bar, 34 bar	1791.00
Fluke-721-3610	4353375	Dual Sensor Pressure Calibrator, 2.48 bar, 69 bar	1791.00
Fluke-721-3615	4353412	Dual Sensor Pressure Calibrator, 2.48 bar, 103 bar	1759.00
Fluke-721-3630	4353458	Dual Sensor Pressure Calibrator, 2.48 bar, 200 bar	1791.00
Fluke-721-3650	4353499	Dual Sensor Pressure Calibrator, 2.48 bar, 345 bar	1791.00
Fluke 721EX-1601	4353265	Dual Sensor Pressure Calibrator, 16, 100 PSIG	2050.00
Fluke 721EX-1603	4353309	Dual Sensor Pressure Calibrator, 16, 300 PSIG	2050.00
Fluke 721EX-1605	4353348	Dual Sensor Pressure Calibrator, 16, 500 PSIG	2050.00
Fluke 721EX-1610	4353382	Dual Sensor Pressure Calibrator, 16, 1000 PSIG	2012.00
Fluke 721EX-1615	4353420	Dual Sensor Pressure Calibrator, 16, 1500 PSIG	2012.00
Fluke 721EX-1630	4353464	Dual Sensor Pressure Calibrator, 16, 3000 PSIG	2012.00
Fluke 721EX-1650	4353506	Dual Sensor Pressure Calibrator, 16, 5000 PSIG	2012.00
Fluke 721EX-3601	4353276	Dual Sensor Pressure Calibrator, 36, 100 PSIG	2012.00
Fluke 721EX-3603	4353311	Dual Sensor Pressure Calibrator, 36, 300 PSIG	2012.00
Fluke 721EX-3605	4353353	Dual Sensor Pressure Calibrator, 36, 500 PSIG	2012.00
Fluke 721EX-3610	4353394	Dual Sensor Pressure Calibrator, 36, 1000 PSIG	2012.00
Fluke 721EX-3615	4353435	Dual Sensor Pressure Calibrator, 36, 1500 PSIG	2012.00
Fluke 721EX-3630	4353473	Dual Sensor Pressure Calibrator, 36, 3000 PSIG	2012.00
Fluke 721EX-3650	4353514	Dual Sensor Pressure Calibrator, 36, 5000 PSIG	2012.00
Fluke 724	1553041	Temperature Calibrator	1931.00
Fluke 725	664133	Multifunction Process Calibrator	2721.00
Fluke 725Ex	2098179	Intrinsically Safe Multifunction Process Calibrator	3292.00
Fluke 726	2452080	Precision Multifunction Process Calibrator	3095.00
Fluke 729 30G FC	4856907	Automatic Pressure Calibrator , w/FC (2 Bar)	7152.00
Fluke 729 150G FC	4856894	Automatic Pressure Calibrator, w/FC (10 Bar)	7152.00
Fluke 729 300G FC	4856882	Automatic Pressure Calibrator, w/FC (20 Bar)	7152.00
Fluke 729 30G	4856990	Automatic Pressure Calibrator (2 Bar)	6978.00
Fluke 729 150G	4856983	Automatic Pressure Calibrator (10 Bar)	6978.00
Fluke 729 300G	4856976	Automatic Pressure Calibrator (20 Bar)	6978.00
Fluke 753 EU	4411027	Documenting Process Calibrator	4932.00
Fluke 754 EU	4400387	Documenting Process Calibrator	6222.00
Fluke 771	2646347	Milliamp Process Clamp Meter	454.00
Fluke 772	3362352	Milliamp Process Clamp Meter	664.00
Fluke 773	3362365	Milliamp Process Clamp Meter	949.00
Fluke 787B	4777186	Process Meter	866.00
Fluke 789/E	3977194	Process Meter	987.00
Fluke 789/IR3000FC	4604605	Process Meter and FC connector	958.00

Model	Art. nr	Description	GBP
<b>Pressure Modules</b>			
Fluke-700G01	4353523	Pressure Gauge, -10" to 10" WC (27 mbar)	640.00
Fluke-700G02	4353538	Pressure Gauge, -30" to 30" WC (69 mbar)	639.00
700G04	4096972	Pressure Gauge, +/- 1 bar	640.00
700G05	4097514	Pressure Gauge, 2 bar	640.00
700G06	4097538	Pressure Gauge, 6.9 bar	640.00
700G07	4097561	Pressure Gauge, 34 bar	640.00
700G08	4097592	Pressure Gauge, 69 bar	640.00
700G27	4097545	Pressure Gauge, 20 bar	640.00
700G29	4097605	Pressure Gauge, 200 bar	665.00
700G30	4097610	Pressure Gauge, 345 bar	665.00
700G31	4097622	Pressure Gauge, 690 bar	665.00
Fluke-700GA4	4353545	Pressure Gauge, 1 bar absolute	639.00
Fluke-700GA5	4353550	Pressure Gauge, 2 bar absolute	639.00
Fluke-700GA6	4353561	Pressure Gauge, 6.9 bar absolute	639.00
Fluke-700GA27	4353577	Pressure Gauge, 20 bar absolute	639.00
700HTPK	4124358	Hydraulic Test Pump Kit, 0 to 690 bar	932.00
Fluke 700HTPK2	4623314	Premium hydraulic test pump kit	1169.00
Fluke 700MTH	4623345	Premium metric pressure test hose	438.00
Fluke 700M20TH	4623338	Premium M20 pressure test hose	430.00
700PCK	100062	Pressure Module Calibration Kit	1140.00
Fluke 700PTPK	4124364	Pneumatic Test Pump Kit, 0 to 41 bar	529.00
Fluke 700PTPK2	4623306	Premium pneumatic test pump kit	1101.00
700G/TRACK	4123225	Data Logging Cable & Software	365.00
Fluke-700RG05	4353589	Pressure Gauge, Reference, +2 bar	655.00
Fluke-700RG06	4353592	Pressure Gauge, Reference, 6.9 bar	655.00
Fluke-700RG07	4353605	Pressure Gauge, Reference, 34 bar	655.00
Fluke-700RG08	4353610	Pressure Gauge, Reference, 69 bar	655.00
Fluke-700G10	4353654	Pressure Gauge, 140 bar	639.00
Fluke-700RG29	4353622	Pressure Gauge, Reference, 200 bar	726.00
Fluke-700RG30	4353631	Pressure Gauge, Reference, 345 bar	712.00
Fluke-700RG31	4353646	Pressure Gauge, Reference, 690 bar	726.00
Fluke 700TTH5K	4623323	Premium pressure transmitter test hose	438.00
Fluke 700TTH10K	4636393	Premium pressure transmitter test hose kit, 10K	511.00
750P00	4352270	Pressure Module (0 - 2.5 mbar)	1426.00
750P01	4352281	Pressure Module (0 - 25 mbar)	1105.00
750P02	4352750	Pressure Module (0 - 70 mbar)	1084.00
750P22	4352296	Pressure Module (0 - 70 mbar)	1084.00
750P03	4352738	Pressure Module (0 - 350 mbar)	1084.00
750P23	4352308	Pressure Module (0 - 350 mbar)	1105.00
750P04	4352313	Pressure Module (0 - 1 bar)	1105.00
750P24	4352324	Pressure Module (0 - 1 bar)	1105.00
750P05	4352336	Pressure Module (0 - 2 bar)	1105.00
750P06	4352349	Pressure Module (0 - 7 bar)	1105.00
750P27	4352351	Pressure Module (0 - 20 bar)	1105.00
750P07	4352360	Pressure Module (0 - 35 bar)	1105.00
750P08	4352372	Pressure Module (0 - 70 bar)	1105.00
750P09	4352385	Pressure Module (0 - 100 bar)	1105.00
750P2000	4352397	Pressure Module (0 - 140 bar)	1105.00
750P29	4352403	Pressure Module (0 - 200 bar)	1757.00
750P30	4352415	Pressure Module (0 - 340 bar)	1757.00
750P31	4352426	Pressure Module (0 - 700 bar)	1757.00
750PA3	4352432	Pressure Module (0 - 350 mbar)	1278.00
750PA4	4352444	Pressure Module (0 - 1 bar)	1278.00
750PA5	4352459	Pressure Module (0 - 2 bar)	1278.00
750PA6	4352467	Pressure Module (0 - 7 bar)	1278.00
750PA27	4352471	Pressure Module (0 - 20 bar)	1254.00
750PA7	4352480	Pressure Module (0 - 35 bar)	1278.00
750PA8	4352498	Pressure Module (0 - 70 bar)	1252.00
750PA9	4352500	Pressure Module (0 - 100 bar)	1229.00
750PV3	4352517	Pressure Module (-350 mbar)	1229.00
750PV4	4352521	Pressure Module (-1 bar)	1252.00
750PD2	4352539	Pressure Module (-70 - 70 mbar)	1252.00
750PD3	4352542	Pressure Module (-350 - 350 mbar)	1252.00
750PD10	4352556	Pressure Module (-700 - 700 mbar)	1229.00
750PD4	4352563	Pressure Module (-1 - 1 bar)	1252.00
750PD5	4352574	Pressure Module (-1 - 2 bar)	1252.00
750PD50	4352588	Pressure Module (-1 - 3.5 bar)	1229.00
750PD6	4352595	Pressure Module (-1 - 7 bar)	1252.00
750PD7	4352602	Pressure Module (-1 - 14 bar)	1252.00
750PD27	4352616	Pressure Module (-1 - 20 bar)	1252.00
750R04	4352625	Pressure Module (0 - 1 bar)	1229.00
750R06	4352633	Pressure Module (0 - 7 bar)	1252.00
750R27	4352640	Pressure Module (0 - 20 bar)	1229.00
750R07	4352657	Pressure Module (0 - 35 bar)	1252.00

Model	Art. nr	Description	GBP
75OR08	4352669	Pressure Module (0 - 70 bar)	1229.00
75OR29	4352678	Pressure Module (0 - 200 bar)	1885.00
75OR30	4352684	Pressure Module (0 - 340 bar)	1850.00
75OR31	4352691	Pressure Module (0 - 700 bar)	1850.00
75ORD5	4352706	Pressure Module (-1 - 2 bar)	1371.00
75ORD6	4352714	Pressure Module (-1 - 7 bar)	1371.00
75ORD27	4352723	Pressure Module (-0.8 - 20 bar)	1371.00
75OP01Ex	4558658	Ex Pressure Module (0 - 25 mbar)	2131.00
75OP24Ex	4558686	Ex Pressure Module (0 - 1 bar)	2131.00
75OP05Ex	4558664	Ex Pressure Module (0 - 2 bar)	2131.00
75OP06Ex	4558673	Ex Pressure Module (0 - 7 bar)	2131.00
75OP27Ex	4558699	Ex Pressure Module (0 - 20 bar)	2131.00
75OP09Ex	4558725	Ex Pressure Module (0 - 100 bar)	2131.00
75OP29Ex	4558702	Ex Pressure Module (0 - 200 bar)	3640.00
75OPA4Ex	4558716	Ex Pressure Module (0 - 1 bar)	2309.00

#### Process Calibrator Accessories

700HTH-1	2811795	Hydraulic Test Hose	762.00
700ILF	1566730	In-Line Filter	85.00
700LTP-1	2811763	Low Pressure Test Pump	850.00
700-IV	202561	Current Shunt	403.00
700PMP	617131	Pressure Pump (10 bar)	567.00
700PRV-1	2811808	Pressure Relief Valve for 700HTP	896.00
700PTP-1	2811774	Pneumatic Test Pump	734.00
700SC	667425	Serial Interface Cable (Fluke 725/725Ex/726)	196.00
700TC1	620119	Thermocouple Plug Kits (10 types)	118.00
700TC2	620127	Thermocouple Plug Kits (5 types)	94.00
Fluke 720RTD	4366669	RTD Probe for 721, 721Ex and 719PRO	229.00
787CAL 230	662996	Calibration Module (Fluke 787)	940.00
BC7217	668217	Battery Charger	262.00
BE9005 240	946652	Battery Eliminator	128.00
BP7235	668225	NiMH Battery Pack	216.00
C700	606928	Hard Case (700 Series)	289.00
C789	946694	Soft Meter Case	145.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	219.00
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	129.00
Fluke 700HTP-2	4096855	Hydraulic Test Pump, 690 bar	1018.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	40.00
BP7240	4022220	753/754 Spare Battery	155.00
Fluke 750SW	4090343	DPC/TRACK2-software	3101.00
BC7240	4022655	Battery Charger (753/754)	42.00
HART Drywell Cable	2111088	Cable Kit, HART Drywellcontrol	139.00
Fluke-71x	3345825	Hose kit	82.00
Fluke 700TLK	3829398	Process Test Lead Kit	129.00
Fluke 709H/TRACK	4281225	Logging software with cable	411.00
Fluke 720URTD	4382695	Universal RTD adapter for 721, 721Ex and 719PRO	152.00

#### General Accessories

##### Test Leads, Probes and Clips

80K-15	618113	Probe, Electronic Air Cleaner	220.00
AC175	4101772	Threaded Alligator Clip Set	23.00
AC220	1610103	SureGrip Alligator Clip Set	39.00
AC280	1610115	SureGrip Hook Clip Set	28.00
AC283	1610144	SureGrip Pincer Clip Set	33.00
AC285	1610159	SureGrip Alligator Clip Set	20.00
AC285-FTP	4073928	Alligator Clips and adaptors (FTP-1, FTPL-1)	24.00
AC288	4617784	SureGrip™ Terminal block probe	28.00
AC87	1278079	Heavy Duty Bus Bar Clip Set	39.00
AC89	873448	Heavy Duty Insulation Piercing Test Clip	41.00
BP980	1616807	Dual Banana Plug Kit	41.00
FTL660	2280204	Fused Test Lead Set	49.00
FTP-1	3869437	Fuse test probe set	83.00
FTPL-1	3869443	Fuse test probe set with test leads	97.00
H900	1616818	Test Lead Holder	24.00
Leadwrap	4083525	Durable Nylon Hook and Loop Fastener, 3 pack	7.00
T5-Kit	3971169	T5 Tester Accessory Starter Kit	43.00
T5-RLS	4089137	Replacement Test Lead Set (T5)	22.00
TL175	3521976	Twist Guard Test Leads	23.00
TL175E	3565554	Twist Guard Test Leads, 4mm	28.00
TL220-1	3971178	SureGrip Industrial Test Lead Set	65.00
TL221	2003602	SureGrip Extension Lead Set	27.00
TL222	2003616	SureGrip Silicone Test Lead Set	27.00
TL223-1	3971184	SureGrip Electrical Test Lead Set	63.00

Model	Art. nr	Description	GBP
TL224	1610198	SureGrip Silicone Test Lead Set	25.00
TL225-1	3971191	Stray Voltage Eliminator test Lead Set	88.00
TL238	2132831	SureGrip High Energy Test Lead Kit	65.00
TL27	668571	Heavy Duty Test Lead Set	28.00
TL40	1590606	Retractable Tip Test Lead Set	40.00
TL71-1	3971207	TL71, Test Lead Set	23.00
TL75-1	3971218	TL75, Test Lead Set	21.00
TL76	2032684	All-in-one Test Lead Set	33.00
TL80A-1	3971229	TL80A, Test Lead Set	64.00
TL81A	1277073	Deluxe Electronic Test Lead Kit	130.00
TL910	1616632	Electronic Test Lead Set (with replacement tips)	65.00
TL930	1616671	Patch Cords (60 cm)	16.00
TL932	1616680	Patch Cords (90 cm)	19.00
TL935	1616698	Patch Cord Kit (60, 90, 120 cm)	45.00
TL940	1616705	Mini-Hook Test Lead Set	19.00
TL950	1616710	Mini-Pincer Test Lead Set	28.00
TL960	1616722	Micro-Hook Test Lead Set	19.00
TL970	1616793	Hook and Pincer Test Lead Kit	64.00
TLK1550-RTLK	4112351	Integral test lead & 10 kV clamp	212.00
TLK220	2097022	SureGrip Accessory Kit	117.00
TLK-225	3971234	TLK225, SureGrip Master Set	130.00
TLK281-1	3971241	TLK281, Automotive Test Lead Kit	117.00
TLK-282-1	3971252	TLK282, DeLuxe Automotive Test Lead Kit	147.00
TLK287	3045631	Electronic Master Test Lead Kit	150.00
TLK289	3092521	Industrial Master Test Lead Kit	152.00
TLK290	2435092	Test Probe Kit	49.00
TLK291	2435108	Fused Test Probe Set	52.00
TP1-1	3971265	TP1, Test Probes	16.00
TP175	3521983	TwistGuard test Probes, 2MM dia probe tips	18.00
TP175E	3565568	TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters	21.00
TP2-1	3971283	TP2, Test Probes	16.00
TP220-1	3971276	TP220, SureGrip Test Probes	15.00
TP38	1541636	Slim Reach Test Probe Set (insulated)	16.00
TP74	1541649	Lantern Tip Test Probe Set	19.00
TP80	873455	Electronic Test Probe Set	30.00
TP912	1616644	Replacement tips for TL910	27.00
TP920	1616659	Test Probe Adapter Kit	41.00

#### Current Clamps

80i-110s	114519	AC/DC Current Clamp (100 A)	666.00
i1000s	1568487	AC Current Clamp (1000 A)	547.00
i1010	617735	AC/DC Current Clamp (1000 A)	388.00
i1010 Kit	2096998	AC/DC Current Clamp (1000 A) with Soft Case	397.00
i200	664755	AC Current Clamp (200 A)	138.00
i2000 flex	2584912	AC Flexible Current Clamp (2000 A)	259.00
i200s	664760	AC Current Clamp (200 A)	235.00
i30	2584920	AC/DC Current Clamp (30A)	330.00
i3000 flex-4PK	2696367	AC Flexible Current Clamp (3000 A), 4-pack	1110.00
i3000s	657202	AC Current Clamp (3000 A)	583.00
i3000s flex-24	2584888	AC Flexible Current Clamp (3000 A), 610 mm	400.00
i3000s flex-36	2584901	AC Flexible Current Clamp (3000 A), 915 mm	470.00
i30s	2584935	AC/DC Current Clamp (30A)	470.00
i310s	2840309	AC/DC Current Clamp (300A)	293.00
i400	2277225	AC Current Clamp (400 A)	130.00
i400s	2277202	AC Current Clamp (400A)	235.00
i40S-PR (1750)	3949777	40A Current Clamp (1750)	365.00
i410	617727	AC/DC Current Clamp (400 A)	222.00
i410 Kit	2097005	AC/DC Current Clamp (400 A) with Soft Case	251.00
i6000s flex-24	2840311	AC Current Clamp (6000 A)	505.00
i6000s flex-36	2840327	AC Current Clamp (6000 A)	578.00
i800	2840283	AC Current Clamp (800 A)	188.00

#### Temperature Accessories

80AK-A	2747812	Thermocouple Adapter	26.00
80BK-A	2747801	Integrated DMM Temperature Probe (Type K)	29.00
80CJ-M	833046	Male Mini Connectors (Type J)	21.00
80CK-M	779942	Male Mini Connectors (Type K)	21.00
80PJ-1	1288191	Bead Probe (Type J)	23.00
80PJ-9	1288218	General Purpose Probe (Type J)	59.00
80PJ-EXT	1288234	Extension Wire Kit (Type J)	52.00
80PK-1	750422	Bead Probe (Type K)	26.00
80PK-10	3439199	Pipe Clamp Temperature Probe (Type K)	197.00
80PK-11	2724500	Velcro Temperature Probe	33.00
80PK-18 Kit	3448859	Pipe Clamp Temperature Probe Kit	311.00
80PK-22	2098684	SureGrip Immersion Probe	89.00

Model	Art. nr	Description	GBP
80PK-24	2098691	SureGrip Air Probe	113.00
80PK-25	2098706	SureGrip Piercing Probe	101.00
80PK-26	2098714	SureGrip General Purpose Probe	113.00
80PK-27	2098723	SureGrip Industrial Surface Probe	327.00
80PK-3A	874610	Surface Probe (Type K)	187.00
80PK-8	200360	Pipe Clamp Temperature Probe (Type K)	152.00
80PK-9	1288229	General Purpose Probe (Type K)	59.00
80PK-EXT	1288241	Extension Wire Kit (Type K)	52.00
80PR-60	2148313	RTD Temperature Probe (Fluke 66/68)	64.00
80PT-25	2104397	SureGrip Piercing Probe	91.00
80PT-EXT	1288252	Extension Wire Kit (Type T)	52.00
80T-150UA	3190456	Universal Temperature Probe (for DMMs)	248.00
80TK	736736	Thermocouple Module (Type K)	124.00

#### Cases and Holsters

C10	897744	Meter Holster	23.00
C100	827055	Hard Meter and Accessory Case	57.00
C101	2437514	Hard Case	53.00
C115	2826063	Soft Meter Case	50.00
C116	2826074	Soft Meter Case	62.00
C120	646189	Hard Case (43B/120 Series)	95.00
C125	646858	Soft Meter Case	45.00
C12A	930529	Soft Meter Case	26.00
C150	4111540	Zippered Soft Carrying Case	25.00
C1600	2091049	Meter and Accessory Case	33.00
C1620	4359042	Carrying Case	183.00
C190	677401	Hard Case (190 Series)	232.00
C195	677408	Soft Case	219.00
C20	708396	Hard Meter Case	56.00
C23	1663209	Soft Meter Case	23.00
C25	681114	Soft Meter Case	47.00
C280	3182785	Soft Meter Case	57.00
C33	1664120	Soft Meter Case	24.00
C345	3311173	Soft Case	71.00
C35	2826056	Soft Meter Case	39.00
C43	1663230	Soft Meter Case	70.00
C50	762823	Soft Meter Case	33.00
C510	1547885	Leather Meter Case	66.00
C520A	1629104	Leather Tester Case	52.00
C550	1547919	Tool Bag	106.00
C75	865535	Soft Accessory Case	16.00
C781	619988	Soft Meter Case	77.00
C789	946694	Soft Meter Case	145.00
C800	896220	Hard Meter and Accessory Case	57.00
C90	466029	Soft Meter Case	33.00
CXT170	3352567	Rugged Pelican Hard Case	156.00
CXT280	3352571	Rugged Pelican Hard Case	156.00
CXT80	3352559	Rugged Pelican Hard Case	156.00
CXT1000	4628917	Extreme Hard case	156.00
FLUKEPACK30	4983088	Professional Tool Backpack	149.00
H3	1608458	Holster (330 Series)	36.00
H5	649365	Electrical Tester Holster (Fluke T5)	26.00
H6	2152040	Infrared Thermometer Holster (Fluke 63/65/68/561)	25.00
H-T6	4910585	T6 Belt Holster	26.00
H15	4111533	Belt Holster for T100 series	24.00
H80M	2138458	Holster + Magnetic Hanger	36.00

#### Automotive Accessories

BP880	2150594	BNC to Female Double Stacking Banana Plug	15.00
BP881	2151015	BNC to Male Double Stacking Banana Plug	16.00
PV350	919811	Pressure Vacuum Module	251.00
RPM80	880849	Inductive Pick-up	82.00
SCC128	2100199	Automotive Accessory Kit (120 Series)	628.00
SCC198	2100208	Automotive Accessory Kit (190 Series)	787.00
STL90	201233	Automotive Shielded Test Lead Set (120/190 Series)	222.00
TAS90	614187	Automotive Accessory Set (120/190 Series)	59.00
TL28A	1273185	Automotive Test Lead Set	45.00
TL82	2150636	Automotive Pin and Socket Adapter Set	97.00
TP40	1567573	Automotive Back Probe Pins (5 pcs) (4 mm)	33.00
TP81	2149098	Insulation Piercing Clip Set (4 mm)	45.00
TP82	2149080	Insulation Piercing Clip Set (2 mm)	45.00
TP88	2149102	Rigid Back Probe Pin Set	14.00

Model	Art. nr	Description	GBP
<b>Other Accessories</b>			
80K-40	382846	High Voltage Probe	231.00
80K-6	532424	High Voltage Probe	128.00
EBC290	3894906	External Battery Charger	90.00
FOM	200428	Fiber Optic Meter	480.00
FOS-850	200433	Fiber Optic Light Source	290.00
FOS-850/1300	200441	Fiber Optic Light Source	707.00
L200	2096346	Probe Light	21.00
L205	2098588	Mini Hat Light	25.00
L206	2098595	Deluxe Hat Light	31.00
L210	2096379	Probe light and probe extender	33.00
L215	2096368	SureGrip kit with probe light and probe extender	74.00
LVD1	4571403	Volt Light	24.00
LVD2	2740300	Volt Light	33.00
MC50	2092300	MeterCleaner Wipes, 50-pack	74.00
MC6	2092212	MeterCleaner Wipes, 6-pack	13.00
PV350	919811	Pressure Vacuum Module	251.00
SV225	3100477	Stray Voltage Adapter	59.00
TPAK	1281997	ToolPak, Meter Hanging Kit	33.00
<b>Fuses</b>			
943121	943121	Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm	4.45
803293	803293	Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm	8.15
830828	830828	Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm	7.15
2279339	2279339	Fuse, A:315mA (f), V:1000V, IR:10kA, 6.35x32 mm	10.45
740670	740670	Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm	3.45
<b>Software</b>			
FVF-Basic	2396957	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	129.00
FVF-SC2	1576734	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	219.00
FVF-SC4	2687335	FlukeView Forms Software + Cable (8845A/8846A)	237.00
FVF-SC5	2791314	FlukeView Forms Basic (8845A/8846A)	129.00
FVF-UG	1576741	FlukeView Forms Upgrade	114.00
IR189USB	2428108	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	40.00
SCC120E	646684	FlukeView Software + USB Cable + Case (120 Series) - English	409.00
SCC120F	646692	FlukeView Software + USB Cable + Case (Fluke 123) - French	401.00
SCC190	671826	FlukeView Software + Cable + Case (190 Series) - English, French, German	570.00
SW90W	3894923	FlukeView Software	333.00

### Fluke (UK) Ltd.

52 Hurricane Way

Norwich

Norfolk

NR6 6JB

Tel: (020) 7942 0700

Fax: (020) 7942 0701

E-mail: industrial@uk.fluke.nl

Web: www.fluke.co.uk

**Please note** - Every effort has been made to ensure this guide is as accurate as possible.

Fluke (UK) Ltd. reserve the right to alter details without prior notification.

16 Prices are recommended list prices excl. VAT.

10001 - Fluke Test Tools Price List End

Customer - English

Rev. 36