

SEE IT. SAVE IT. SHARE IT.



All the facts, right in the field.

Introducing the largest suite of connected test tools in the world - Fluke Connect™.

The Fluke Connect[™] app and enabled tools are the best way to stay in contact with your team and tools without leaving the field.

- Connect your tools. Connect your data.
- · Share from anywhere.
- All your measurements. All in one place.
- Save time reporting and troubleshoot faster.







FLK-a3001 FC Wireless iFlex AC

Current Module

FLK-a3002 FC Wireless AC/DC Current Module

FLK-ir3000 FC FC connector



FLK-Ti95

Thermal Imager

FLK-v3000 FC

Wireless AC Voltage Module

FLK-3000 FC

Wireless Digital Multimeter

FLK-a3000 FC

Wireless AC Current Clamp Module

FLK-t3000 FC

Wireless K-Type Temperature Module

Learn more at flukeconnect.ie

The NEW Fluke Fluorescent Light Tester



Laser Distance Meters

Fluke laser distance meters will become the next essential item on your toolbelt.



Fluke 414D

Fluke 419D

Fluke 424D

VoltAlert™

When the tip of the

Fluke VoltAlert AC voltage detector glows red and the unit beeps, you know there is voltage on the line.

Fluke 2AC

FLUKE !

Fluke SM100

The fast way to check if your sockets are safe.

- Clear LED indication of wiring status
- Modern, ergonomic design
- · Compact and durable
- Simple to use, just plug into a socket for an autotest



Fluke SM100

Fluke TestGuide

The NEW TestGuide app shows electricians in short and clear steps what the actions are for the most common measurements, what to look at and how to interpret the results. You will also find background articles and in-depth application notes which can be downloaded or send to your email.

FREE DOWNLOAD! www.fluke.ie/testguide





Fluke Ti90 and Ti95 Thermal Cameras

The only wireless enabled industrial thermal imager at this price point.



Save more time than before and find potential problems before they become costly failures with these new thermal imagers from Fluke.



- Get up to 84% better spatial resolution for superior image quality
- View images on 16% larger screen the largest LCD in its class
- Communicate back to your supervisors with your smart phone without having to leave the site with the Fluke Connect app
- Built Fluke tough... durable enough to handle a 2-meter drop, and IP54-rated
- FREE SmartView® Imaging Analysis and Reporting Software

Fluke Ti95

Fluke 6200-2 and 6500-2 Portable Appliance Testers

Perform more tests each day! The low weight, small size, one-touch solutions.

Improved auto-test capabilities to help you increase the number of tests completed each day.

- 'One-touch' testing
- Save time: pre-set pass/fail levels
- Easy reading: large backlit display
- Rapid data entry
- Back-up data storage and transfer: additional USB memory drive
- Pre-set, auto-test sequences

NEW

- Colour Dot Matrix Display
- 250V Insulation Test
- 110V Test Functionality
- RCD Test





Optional accessories:

- DMS 0702/PAT software
- SP-SCAN-6000 barcode scanner
- SP6000 printer

Also available as a kit.



Special promotions New Fluke Multifunction Installation Tester Kits



Fast, lightweight, easy to use, robust and reliable installation tester. Now all models with great offers!

- · Fast high current loop test
- Reliable 3-wire loop test
- No complex multi-level menus: rotary dial clearly indicates selected function
- Easy test lead compensation:
 Zero adapter
- Extended memory*
- mΩ resolution: loop & line resistance*
- Variable RCD current mode for customised settings
- Test smooth DC sensitive RCDs*
- PASS/FAIL indication for RCD tests



Now with FREE
LED Puck
Alarm Light**

Fluke 1652C-CLAMPKIT







Fluke 1653B-CLAMPKIT/D









Fluke 1654B-CLAMPKIT/D

^{* 1654}B only

^{**} Free LED Puck Alarm Light offer valid until 31.12.2014, only available direct from Fluke by using special offer voucher, proof of purchase required. Go to www.fluke.ie/promotions to download the voucher and view full terms and conditions or contact Fluke directly.

Fluke Clamp Meters: Readings you can rely on



Wire in tight spaces - panels out of reach - extra large conductors. Noise free measurements for every workspace.



	Fluke 365	Fluke 323	Fluke 324	Fluke 325	Fluke 373	Fluke 374	Fluke 375	Fluke 376
Jaw opening	18 mm	30 mm	30 mm	30 mm	32 mm	34 mm	34 mm	34 mm
Current TRMS	200 A AC/DC	400 A AC	400 A AC	400 A AC/DC	600 A AC	600 A AC/DC	600 A AC/DC	1000 A AC/DC
Voltage AC/DC	600 V	600 V	600 V	600 V	600 V	600 V	600 V	1000 V
Continuity	•	•	•	•	•	•	•	•
Resistance	•	•	•	•	•	•	•	•
Capacitance	-	-	•	•	•	•	•	•
Frequency	-	-	-	•	-	-	•	•
Contact temperature	-	-	-10 to 400°C	-10 to 400°C	-	-	-	-
In-rush	-	-	-	-	•	•	•	•
i-Flex	-	-	-	-	-	optional	optional	included (18")

^{*} Free cabinet key offer valid until 31.12.2014, only available direct from Fluke by using special offer voucher, proof of purchase required. Go to www.fluke.ie/promotions to download the voucher and view full terms and conditions or contact Fluke directly.



CHECK OUR NEW ELECTRICIAN'S TOOLBELT PAGE!

www.fluke.ie/toolbelt



Fluke 110 series Digital Multimeters




Economic investment in accuracy, simple operation for easy and fast measurements.


	Fluke 113	Fluke 114	Fluke 115	Fluke 116	Fluke 117
True RMS readings	•	•	•	•	•
Display backlight	•	•	•	•	•
Voltalert™, Non-contact voltage detection		-	-	-	•
Built-in thermometer (probe included)	-	-	-	•	-
LoZ (low input impedance)	-	•	-	•	•
Frequency, Capacitance, Diode test	-/●/●	-	●/●/●	●/●/●	●/●/●
Category rating	CAT III/600 V				

Do you know Fluke has a full range of accessories? Below four "must haves" for every technician...









...many more can be found on www.fluke.ie/accessories

Electrical Testers



* Low input impedance or switchable load

			-			
	Fluke T90	Fluke T110	Fluke T130	Fluke T150	Fluke T5-600	Fluke T5-1000
Display	LED's	LED's	LED's/LCD	LED's/LCD	LCD	LCD
Current/Voltage AC/DC	12-690V	12-690V	6-690V	6-690V	100A/1-600V	100A/1-1000V
Other	-	LoZ*	LoZ*	LoZ*/Ohm	Ohm	Ohm

Temperature solutions: fit for your job, fit for your pocket.

Distance to spot

Temperature range



Fluke VT02, Fluke VT04, Fluke VT04A

- Hot/cold markers
- Image storage
- · Analysis software

Fluke 62MAX

- Min/max/avg/dif
- Dust/water resistant (IP54)

Fluke 561

- Combined
- IR + contact
 HVAC
 - applications

Fluke 566

- · Data logging
- Combined
 - IR + contact

Fluke 572-2

- · Data logging
- Hi/Lo alarm
- Min/max/avg/dif
- IR + contact

	Heat map			Exact spot positioning					
Features	VT02	VT04*	VT04A	62MAX	62MAX+	561	566	568	572-2
	Visual IR thermometer		Infrared the	ermometer	Multipurpose thermometer			High termperature	
Temperature	-10 to 250 °C			-30 to 500 °C	-30 to 650°C	-40 to 550 °C	-40 to 650 °C	-40 to 800 °C	-30 to 900 °C
D:S**	6:1	9:1	9:1	10:1	12:1	12:1	30:1	50:1	60:1
Laser sighting	No laser necessary			Single	Dual	Single-point	Single-point	Single-point	Offset dual

^{*} VTO4 has rechargeable lithium-ion batteries ** D:S (distance to spot)